


# Product data sheet

Specifications



ABS box IP66 IK07  
RAL7035 Int.H225W175D80  
Ext.H241W194D87 Transp.cover  
H20

NSYTBS24198T

## Main

Range	Thalassa
Product name	Thalassa TBS
Device application	Multi-purpose
Category	Industrial box
Height	241 mm
Width	194 mm
Depth	87 mm
Internal height	225 mm
Internal width	175 mm
Internal depth	80 mm
Enclosure mounting	Wall mounted
Device composition	1 body 1 cover 4 cover screw
Body type	One piece moulded
Type of front cover	Low transparent cover
Cover fixing	Plastic screws
Lock type	Captive screw flat outside sealed area
Removable parts	Cover by captive screws

## Complementary

Material	ABS (acrylonitrile butadiene-styrene)
Colour	Grey (RAL 7035) Transparent
Standards	IEC 62208
Product certifications	TÜV
Electrical insulation class	Class II
IP degree of protection	IP66 conforming to NEMA 4.4X
IK degree of protection	IK07 conforming to IEC 62262
Glow wire resistance	650 °C conforming to IEC 60695-2-11

Ambient air temperature for storage	-15...40 °C
Operating temperature	-25...60 °C
Net weight	0.64 kg

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	635.0 g
Package 1 Height	10.0 cm
Package 1 width	20.0 cm
Package 1 Length	26.0 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Weight	8.92 kg
Package 2 Height	40.5 cm
Package 2 width	40.0 cm
Package 2 Length	60.0 cm
Unit Type of Package 3	PAM
Number of Units in Package 3	300
Package 3 Weight	236.0 kg
Package 3 Height	220.0 cm
Package 3 width	100.0 cm
Package 3 Length	120.0 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------