



Thermal protection

TEMPICE 700

Temperature to -10°C | Wet environments

Reinforced Durability to push the limits of cold



DEXTERITY
EN420:
5/5

SPECIFIC ADVANTAGES



Comfort

- Stay dry when working in wet conditions



Durability

- Coating 5 times as durable than standard gloves on the market



Productivity

- Excellent grip when handling wet parts
- Grip and Proof coating ensures an excellent grip in very oily environment . It also reduces muscle strain and boosts productivity



Skin protection

- Free of harmful substances: DMF Free



Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting



Washability

- Washable up to 5 times at 60°C , allowing to extend glove lifespan, reducing costs and waste.

INDUSTRIES

- Local Authorities (Catering Services)
- Local Authorities (Roads and Highways)
- Local Authorities (Parks and Public Spaces)
- Local Authorities (Waste Collection and Processing)
- Other industries
- Transport, logistics

APPLICATIONS

- Maintaining the roads
- Public park maintenance
- Waste collection
- Construction materials handling
- Maintenance in wet or cold environments
- Order preparation



Thermal protection

TEMPICE 700

Temperature to -10°C | Wet environments


LEGENDS

EN388

MECHANICAL HAZARDS



PERFORMANCE LEVELS (X = NOT TESTED)




EN 511:2006

COLD HAZARDS



PERFORMANCE LEVELS (X = NOT TESTED)



PRODUCT DETAILS

Interior finish	Knitted thermal protection
Gauge	10
Exterior finish	Non-slip grip
Material	Nitrile GRIP&PROOF coating
Cuff characteristic	Knitted Cuff
Colour.s	Black Blue
European sizes	7 8 9 10
Surface resistance according to EN1149-1 (Value in palm area at 25% relative humidity)	7.6E+9 Ω
Vertical resistance according to EN1149-2 (Value in palm area at 25% relative humidity)	3.5E+11 Ω

LOGISTIC DETAILS

Packaging	1 pair/bag 12 pairs/bag 72 pairs/carton
-----------	---

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/08/18/1671
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE

Edit 05/01/2025

MAPA SAS capital de 35.000.010 €
420, rue d'Estienne d'Orves
92705 Colombes Cedex France
RCS Nanterre 314 307 720

mapa-pro.com

MAPA
PROFESSIONAL