



Part Number : [1201020002](#)
Product Description : PROFIBUS Micro-Change
(M12) Terminator Shield, 5 Poles
Series Number : 120102
Status : Active
Product Category : Circular Industrial Connectors
Engineering Number : B05S06

Documents & Resources

Drawings

[1201020002_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; Lead monoxide per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	120102
Description	PROFIBUS Micro-Change (M12) Terminator Shield, 5 Poles
IP Rating	IP67
Product Name	PROFIBUS
Type	Terminator
UPC	78678849805

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	Single
Material - Connector Body	PVC
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	107.000/g
Orientation	Straight
Poles	5

Temperature Range - Operating	-20°C to +80°C
Wire Size (AWG)	N/A

This document was generated on Sep 24, 2025