



Vertical busbar support non-cascaded, W: 400 mm, 1 set = 3 units

Model	
product brand name	SIVACON S4
product designation	Vertical busbar holder
design of the product	non-cascaded
General technical data	
number of poles	4
Main circuit	
operational current rated value maximum	2 810 A
type of connectable conductor cross-sections for copper conductor stranded	20x10, 30x10, 40x10, 50x10
Mechanical Design	
height	255 mm
width	350 mm
depth	30 mm
busbar center-to-center spacing	80 mm
net weight	8 760 g
Approvals Certificates	
General Product Approval	other



EG-Konf.



[Miscellaneous](#)



VDE



[Confirmation](#)

Environment

[Environmental Conformations](#)

[Environmental Conformations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ4000-0BA31>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ4000-0BA31>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ4000-0BA31

last modified:

4/6/2025 

