

M18 F2CHS50-802

M18 FUEL™ DUAL BATTERY CHAINSAW 50 CM

Outstanding speed of cut in hardwood compared to 60 cc petrol chainsaws

Peak torque levels of 9.5 Nm maintains the chain speed through tough application and prevents bog downs

50 cm cutting system and a peak power of 5.8 HP to tackle felling and bucking applications

High visibility felling sights to ensure precision and accuracy

Two power settings give the user the ability to decide between highest power or extended run time

Dual metal bucking spikes for increased leverage when cutting

FUEL™ technology to reach full throttle in under 1 second

Variable speed trigger allows the user to have full control over the power curve

No-spill oil reservoir with easy to access tank and clear viewing window

Supplied with 76cc of oil, chain tool and bar cover

The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability

Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



Chain bar length (cm)	50
Chain speed (m/s)	14.3
Chain pitch ["]	8.3 / .325
Gauge ["]	1.3 / 0.050
Weight with battery pack (EPTA) (kg)	9.0 (2x M18 FB8)
Kit included	2 x M18 FB8 Battery packs, M18 DFC Charger, No kitbox or bag supplied
Article number	4933480121