

Professional Construction site cable reel with Powerblock KC 3210 5 IP 44, 33+5 m H07BQ-F 3G2.5

For construction site use in accordance with DGUV 203-006 (formerly BGI 608) and permanent outdoor use IP 44.



MADE IN GERMANY

5 YEARS
MANUFACTURER
GUARANTEE



Product number
EAN

9212380210
4007123687589

DESCRIPTION

- With mobile power block and four additional sockets for handy use on scaffolding or roofs, etc.
- Powerblock with visual readiness indicator, hinged metal suspension hook and strap.
- In addition to the power block: four splash-proof socket outlets with self-closing lids.
- Professional drum with all-round roll-over protection.
- Stable on all four sides - perfect cable routing on all four sides.
- Large, sturdy folding swivel handle for effortless winding and unwinding of the cable.
- Robust carrying handles and plug garage on all four sides.
- The Rubbabren housing and drum material made of a plastic-rubber mix is extremely shock and impact resistant. For continuous use under the toughest conditions.
- Reel body cold impact resistant down to -25 °C and drum brake.
- BQ cable: acid- and oil-resistant, weather- and microbe-resistant and cold-resistant down to -40 °C.
- 5 splash-proof 230 V protective contact sockets.
- With extra robust safety plug.
- Overheating protection with indicator light in the event of overheating and overloading.
- Category 2 equipment (K2 DGUV 203-005): For use in harsh operating conditions with high mechanical, physical and chemical.

Professional Construction site cable reel with Powerblock KC 3210 5 IP 44, 33+5 m H07BQ-F 3G2.5

For construction site use in accordance with DGUV 203-006 (formerly BGI 608) and permanent outdoor use IP 44.



Product number 9212380210
EAN 4007123687589

TECHNICAL DATA

Cable quality	PUR (polyurethane)	Plug system socket	Type F (Protective contact)
Cable length	33 m + 5 m	Plug system plug	Type E and F (Protective contact with earth hole)
Cable designation	H07BQ-F 3G2,5	Max. current carrying capacity	16 A
Cable colour	red	Nominal input voltage	230 V
Reel diameter	320 mm	Degree of protection (IP)	IP44
Plug system CEE socket	Without		

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	9 kg
Weight of product (without packaging)	8.94 kg	Dimension LxWxH (incl. packing)	33 cm x 38.5 cm x 40.5 cm
Dimension LxWxH (without packing)	29 cm x 37 cm x 37 cm		

SCOPE OF DELIVERY

Professional Construction site cable reel with Powerblock KC 3210 5