


1928P Reversible impact wrench, made from composite material



Features:

- Double hammer impulse device
- Lightweight and well-balanced for enhanced ease of use
- Reversible lever
- Three power adjustable screwing positions
- Exhaust through handle
- Vibration-damping handle

Free speed	5,000 rpm
Max. torque	2,100 Nm
Bolt capacity	CI 8.8 M30 ● 46 mm
Bolt capacity	CI 12.9 M27 ● 41 mm
Air inlet	3/8" GAS
Operating pressure	6.2 bar
Internal hose size (Ø)	10 mm
Mean air consumption	221 l/min
Weight	3.7 kg

	art.	"	kg
019280006		3/4	3,7

