



## W4

Powerful miniature photoelectric sensors and photoelectric proximity sensors for automation

**SICK**  
Sensor Intelligence.

## Advantages



## Diverse application possibilities thanks to different product variants


**W4 photoelectric sensors are characterized by the range of individual variants available. With the ability to select from a variety of designs, you can obtain the most suitable sensor for your specific installation situation. Thanks to the compact sensor housing, the different designs can be integrated easily and in a space-saving manner even in very tight installation spaces. The availability of a variety of housing materials also opens up numerous applications. You also have freedom of choice when it comes to the light source. No matter what your particular application, SICK offers a reliable solution to precisely suit your specific requirements.**



W4 sensors are available in either a Slim or Flat design. The standardized mounting ensures uncomplicated installation regardless of the design selected.



The sensors come with a housing made from either VISTAL or stainless steel. A hygienic stainless steel version is available for applications in sterile environments.




Red laser light provides the ideal basis for detecting even very small objects. The other light sources available are the highly-visible PinPoint LED, or an infrared LED.




**Various designs, housing materials and light sources provide a great deal of flexibility when selecting the most suitable sensor for your needs**




## Impressive detection results in countless applications




Thanks to the integrated ApplicationSelect mode, the sensor functions can be adapted to the specific requirements of the application. Even objects in an oblique orientation or with a low remission factor can thereby be reliably detected.




The LineSpot technology ensures perforated, textured, and uneven objects can be reliably detected.




In the case of transparent objects such as glass bottles or cling film, the ClearSens technology guarantees reliable detection results.



The sensors can provide the distance value in millimeters and the remission value of the detected object via IO-Link.



Thanks to foreground suppression, the sensors reliably detect very flat, poorly reflecting, reflective, and uneven objects.



The integrated v-optics technology helps the device detect highly reflective and transparent objects such as wafers or displays by means of a very small, laser-like light spot.



**Thanks to innovative technologies, the sensors can solve the most demanding detection tasks in almost any application regardless of the object properties**



## High user-friendliness through easy commissioning and operation

Besides their high detection reliability, the latest generation of W4 photoelectric sensors stand out on account of their particularly easy handling. Thanks to the intuitive BluePilot operating concept, the sensors can be configured in a matter of seconds via a push-turn mechanism and tailored to the specific application. A blue LED indicator gives you immediate feedback on the optimal alignment of the sensor. If the detection quality drops due to contamination or vibrations, you are alerted to this via a well visible LED. This enables malfunctions to be corrected early, and unplanned system downtimes to be avoided.



Using a combination of teach-in button and potentiometer, the required settings can be easily configured directly on the device



The blue LED alignment aid accelerates the process of optimally aligning the sensor, and indicates any changes in the operational safety at a glance



Thanks to the intuitive operating concept, the mode selection can be effortlessly performed and read directly on the device



**The BluePilot operating concept allows convenient commissioning of the sensor in just a few seconds. The operating concept also minimizes the risk of unplanned downtimes.**



## Increased productivity thanks to innovative functions

The latest generation of W4 photoelectric sensors acquire a variety of performance parameters such as temperature, operating hours, remission values and distances values. The acquisition of these parameters provides the foundation for automated condition monitoring, which enables unplanned downtimes to be avoided. You can also flexibly and precisely tailor the sensor settings to your application. Condition monitoring and adjustments help increase your machine productivity. W4 photoelectric sensors therefore offer a future-proof solution for your system.



**Innovative monitoring and diagnostic features allow powerful process control and thereby increase the machine productivity**



## Technical data overview

<b>Dimensions (W x H x D)</b>	16 mm x 40.1 mm x 12.1 mm 12.1 mm x 41.9 mm x 18.6 mm 16 mm x 39.5 mm x 12 mm 16 mm x 36.5 mm x 12 mm 12.2 mm x 41.8 mm x 17.3 mm 22 mm x 42 mm x 21.8 mm 15.25 mm x 44.5 mm x 22.2 mm 15.25 mm x 48.6 mm x 22.2 mm 15.25 mm x 49.2 mm x 22.2 mm 15.25 mm x 44.9 mm x 22.2 mm 15.3 mm x 55.4 mm x 22.2 mm 15.25 mm x 48.6 mm x 22.15 mm 15.25 mm x 63.2 mm x 22.15 mm 15.3 mm x 48.5 mm x 22.3 mm 15.3 mm x 63.2 mm x 22.2 mm
<b>Functional principle detail</b>	Background suppression MultiSwitch LineSpot technology DoubleLine NarrowBeam MultiPulse V-optics Foreground suppression With minimum distance to reflector (dual lens system) ClearSens MultiMode Distance value Without reflector minimum distance (autocollimation/coaxial optics) (depending on type)
<b>Light source</b>	PinPoint LED LED Laser (depending on type)
<b>Type of light</b>	Visible red light / Infrared light (depending on type)
<b>Enclosure rating</b>	IP66 IP67 IP69 IP68 IP69K (depending on type)
<b>Housing material</b>	Plastic Metal (depending on type)
<b>Adjustment</b>	Teach-in button Potentiometer Cable Teach-Turn adjustment None (depending on type)

## Product description

W4 miniature photoelectric sensors and photoelectric proximity sensors are the ideal solution for the intelligent automation of industrial processes. The powerful sensors in the miniature housing reliably detect glossy, flat, uneven, perforated and transparent objects and detect a wide range of parameters such as remission and distance values. Due to the selection of different designs, housing materials and light sources, the sensors are well-suited to countless applications and nearly any assembly situation. The profile is rounded out with an intuitive operating concept and intelligent diagnostic functions.

## At a glance

- Intelligent sensor performance for nearly any application
- Housing available in either a “slim” or “flat” design
- Optionally with VISTAL or stainless-steel housing
- Light source: Laser red light, infrared or PinPoint LED
- Smart Sensors with innovative monitoring and diagnostic functions
- Intuitive operating concept

## Your benefits

- Fault-free system operation thanks to rugged and reliable object detection
- Space-saving assembly options and high flexibility in machine design thanks to different sizes
- Wide range of application possibilities due to various housing materials
- Solution for challenging detection tasks thanks to different light sources
- Powerful process control and increased machine productivity
- High user-friendliness thanks to quick and convenient commissioning and operation

## Ordering information

Other models and accessories → [www.sick.com/W4](http://www.sick.com/W4)

- **Sensing range min. / max.:** 4 mm / 220 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Dark switching	PNP	Connector M8, 3-pin	WTB4FP-21A12120ZZZ	1138642
		Cable with connector M8, 3-pin, 110 mm	WTB4FP-31312120ZZZ	1120713
	Push-pull: PNP/NPN	Cable, 3-wire, 2 m	WTB4FP-1G312120ZZZ	1120711
		Cable, 4-wire, 2 m	WTB4FP-1H56K120A00	1119982
		Connector M8, 3-pin	WTB4FP-21312120ZZZ	1119968
		Male connector M8, 4-pin	WTB4FP-2216K120A00	1119981
			WTB4FP-2216N120A00	1119984
Light switching	NPN	Cable with connector M8, 3-pin, 110 mm	WTB4FP-31E11120ZZZ	1137096
		PNP	Cable with connector M8, 3-pin, 110 mm	WTB4FP-31A11120ZZZ
	Connector M8, 3-pin		WTB4FP-21A11120ZZZ	1131021 1143741
	Push-pull: PNP/NPN		Cable with M12 male connector, 4-pin, 182 mm	WTB4FP-84167120A00
		Cable with M8 male connector, 4-pin, 110 mm	WTB4FP-32161120A00	1144629
			WTB4FP-32167120A00	1120894
			WTB4FP-3216A120A00	1119983
		Cable with connector M8, 3-pin, 110 mm	WTB4FP-31311120ZZZ	1107692 1139484
		Cable with connector M8, 3-pin, with knurled nuts, 340 mm	WTB4FP-97311120ZZZ	1124154
		Cable, 3-wire, 2 m	WTB4FP-1G311120ZZZ	1223018
		Cable, 3-wire, 5 m	WTB4FP-6G311120ZZZ	1123762
		Cable, 4-wire, 5 m	WTB4FP-6H167120A00	1123756
		Connector M8, 3-pin	WTB4FP-21311120ZZZ	1222999
	Male connector M8, 4-pin	WTB4FP-22167120A00	1119980	

Switching mode	Switching output	Connection type	Type	Part no.
Light/dark switching	PNP	Male connector M8, 4-pin	WTB4FP-22811120ZZZ	1143054
			WTB4FP-22861120A00	1140919
			WTB4FP-22862120A00	1140917
	Push-pull: PNP/NPN	Cable with M12 male connector, 4-pin, 182 mm	WTB4FP-84161120A00	1123751
			WTB4FP-32161120A00	1105505
		Cable with M8 male connector, 4-pin, 110 mm	WTB4FP-32162120A00	1127560
				1124614
		Cable, 4-wire, 2 m	WTB4FP-1H161120A00	1223017
			WTB4FP-1H162120A00	1119979
		Cable, 4-wire, 5 m	WTB4FP-6H161120A00	1123757
		Male connector M8, 4-pin	WTB4FP-22161100A00	1124609
			WTB4FP-22161120A00	1222998
				1119985
			WTB4FP-22162120A00	1126158



- **Sensing range min. / max.:** 4 mm / 100 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Connection type	Type	Part no.
Dark switching	Cable with connector M8, 3-pin, 110 mm	WTB4SP-31312100ZZZ	1139283
Light/dark switching	Male connector M8, 4-pin	WTB4FP-221111A0ZZZ	1120710
		WTB4FP-22161120A00	1122374
		WTB4SP-22161100A00	1140601

- **Sensing range min. / max.:** 4 mm / 200 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Male connector M8, 4-pin	Rectangular	WTB4FP-22161120A00	1122375

- **Sensing range min. / max.:** 4 mm / 80 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light switching
- **Switching output:** push-pull: PNP/NPN

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Cable, 3-wire, 2 m	Rectangular	WTB4FP-1G3111A0ZZZ	1134541

- **Sensing range min. / max.:** 4 mm / 95 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light switching
- **Switching output:** push-pull: PNP/NPN

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Cable, 3-wire, 3 m	Rectangular	WTB4FP-5G3111A0ZZZ	1138481

- **Sensing range min. / max.:** 4 mm / 47 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light switching
- **Switching output:** push-pull: PNP/NPN

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Cable with connector M8, 3-pin, 110 mm	Rectangular	WTB4FP-313111A0ZZZ	1126171

- **Sensing range min. / max.:** 4 mm / 48 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light switching
- **Switching output:** push-pull: PNP/NPN

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Cable with connector M8, 3-pin, 110 mm	Rectangular	WTB4FP-P02	1126426

- **Sensing range min. / max.:** 6 mm / 250 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint LED
- **Type of light:** Infrared light
- **Housing:** rectangular

Switching mode	Connection type	Type	Part no.
Dark switching	Connector M8, 3-pin	WTB4FI-21312120ZZZ	1135865
Light switching	Cable with connector M8, 3-pin, 110 mm	WTB4FI-31311120ZZZ	1113170
	Cable, 3-wire, 2 m	WTB4FI-1G311120ZZZ	1113168
	Connector M8, 3-pin	WTB4FI-21311120ZZZ	1113166
Light/dark switching	Cable with M8 male connector, 4-pin, 110 mm	WTB4FI-32161120A00	1113169
		WTB4FI-32162120A00	1120895
	Cable with connector M8, 4-pin, with knurled nuts, 220 mm	WTB4FI-88161120A00	1127192
	Cable, 4-wire, 2 m	WTB4FI-1H161120A00	1113167
	Male connector M8, 4-pin	WTB4FI-22161120A00	1105442

- **Sensing range min. / max.:** 4 mm / 220 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, MultiSwitch
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M8 male connector, 4-pin, 110 mm	WTB4FP-3216D150A00	1113164
Cable, 4-wire, 2 m	WTB4FP-1H16D150A00	1113165
Male connector M8, 4-pin	WTB4FP-2216D150A00	1107693
	WTB4FP-2216R150A00	1119989

- **Sensing range min. / max.:** 7 mm / 150 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, LineSpot technology
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Dark switching	PNP	Connector M8, 3-pin	WTB4FA-21A12120ZZZ	1138641
	Push-pull: PNP/NPN	Cable with connector M8, 3-pin, 110 mm	WTB4FA-31312120ZZZ	1131184
Light switching	PNP	Cable with connector M8, 3-pin, 110 mm	WTB4FA-31A11120ZZZ	1131022
		Cable with connector M8, 3-pin, with knurled nuts, 338 mm	WTB4FA-97A11120ZZZ	1138136
	Push-pull: PNP/NPN		WTB4FA-97311120ZZZ	1136747
Light/dark switching	PNP	Cable with M12 male connector, 4-pin, 182 mm	WTB4FA-84811120ZZZ	1139157
		Cable with M8 male connector, 4-pin	WTB4FA-22811120ZZZ	1144101
		Male connector M8, 4-pin	WTB4FA-22861120A00	1140918
	Push-pull: PNP/NPN	Cable with M8 male connector, 4-pin, 110 mm	WTB4FA-32161120A00	1128019
		Male connector M8, 4-pin	WTB4FA-22161120A00	1127193

- **Sensing range min. / max.:** 7 mm / 55 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, LineSpot technology
- **Switching mode:** Light switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Connector M8, 3-pin	Rectangular	WTB4FA-21A111A0ZZZ	1150068

- **Sensing range min. / max.:** 7 mm / 120 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, DoubleLine
- **Light source:** PinPoint LED
- **Housing:** rectangular

Switching mode	Switching output	Type of light	Connection type	Type	Part no.
Dark switching	PNP	Infrared light	Connector M8, 3-pin	WTB4FQ-21A12120ZZZ	1137888
		Visible red light	Cable with connector M8, 3-pin, 110 mm	WTB4FT-31312120ZZZ	1120715
	Cable, 3-wire, 2 m		WTB4FT-1G312120ZZZ	1120714	
	Connector M8, 3-pin		WTB4FT-21312120ZZZ	1119970	

Switching mode	Switching output	Type of light	Connection type	Type	Part no.
Light switching	PNP	Visible red light	Cable with connector M8, 3-pin, 110 mm	WTB4FT-31A11120ZZZ	1131023
			Cable with connector M8, 3-pin, with knurled nuts, 338 mm	WTB4FT-97A11120ZZZ	1148339
			Connector M8, 3-pin	WTB4FT-21A11120ZZZ	1129445
	Push-pull: PNP/NPN	Visible red light	Cable with connector M8, 3-pin, 110 mm	WTB4FT-31311120ZZZ	1113180
			Cable with connector M8, 3-pin, with knurled nuts, 340 mm	WTB4FT-97311120ZZZ	1129739
			Cable, 3-wire, 2 m	WTB4FT-1G311120ZZZ	1113178
			Connector M8, 3-pin	WTB4FT-21311120ZZZ	1113176
Light/dark switching	PNP	Visible red light	Cable with M8 male connector, 4-pin, 110 mm	WTB4FT-32862120A00	1140923
			Male connector M8, 4-pin	WTB4FT-22811120ZZZ	1130314
				WTB4FT-22862120A00	1140924
	Push-pull: PNP/NPN	Visible red light	Cable with M12 male connector, 4-pin, 182 mm	WTB4FT-84161120A00	1133356
			Cable with M8 male connector, 4-pin, 110 mm	WTB4FT-32161120A00	1113179
			Cable with connector M8, 4-pin, with knurled nuts, 115 mm	WTB4FT-38161120A00	1124151
			Cable with connector M8, 4-pin, with knurled nuts, 220 mm	WTB4FT-K8161120A00	1145046
			Cable, 4-wire, 2 m	WTB4FT-1H112120ZZZ	1144627
				WTB4FT-1H161120A00	1113177
				WTB4FT-1H162120A00	1119987
			Male connector M8, 4-pin	WTB4FT-22161120A00	1105435

- **Sensing range min. / max.:** 4 mm / 100 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, NarrowBeam
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Connection type	Type	Part no.
Light switching	Cable with connector M8, 3-pin, 110 mm	WTB4FP-31311220ZZZ	1119969
Light/dark switching	Cable with M8 male connector, 4-pin, 110 mm	WTB4FP-32161220A00	1115528
	Male connector M8, 4-pin	WTB4FP-22161220A00	1113724

- **Sensing range min. / max.:** 4 mm / 56 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, NarrowBeam
- **Switching mode:** Light switching
- **Switching output:** push-pull: PNP/NPN

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Connector M8, 3-pin	Rectangular	WTB4FP-213112A0ZZZ	1120706

- **Sensing range min. / max.:** 4 mm / 100 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, MultiSwitch, NarrowBeam
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Connection type	Type	Part no.
-	Cable with M8 male connector, 4-pin, 110 mm	WTB4FP-3216D250A00	1121416
	Cable, 4-wire, 2 m	WTB4FP-1H16D250A00	1121417
	Male connector M8, 4-pin	WTB4FP-2216R250A00	1121418
Light switching	Male connector M8, 4-pin	WTB4FP-2216D250A00	1120899

- **Sensing range min. / max.:** 4 mm / 220 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, MultiPulse
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with connector M8, 3-pin, with knurled nuts, 338 mm	WTB4FP-97311120ZZZ	1125734
Connector M8, 3-pin	WTB4FP-21311120ZZZ	1125736

- **Sensing range min. / max.:** 28 mm / 165 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, MultiPulse
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with connector M8, 3-pin, with knurled nuts, 318 mm	WTB4FP-97311A0ZZZ	1125738
Connector M8, 3-pin	WTB4FP-213111A0ZZZ	1125739
		1125740

- **Sensing range min. / max.:** 28 mm / 80 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, MultiPulse

Switching output	Light source	Type of light	Connection type	Housing	Type	Part no.
Push-pull: PNP/NPN	PinPoint LED	Visible red light	Connector M8, 3-pin	Rectangular	WTB4FP-213111A0ZZZ	1138152

- **Sensing range min. / max.:** 4 mm / 60 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, MultiPulse

Switching output	Light source	Type of light	Connection type	Housing	Type	Part no.
Push-pull: PNP/NPN	PinPoint LED	Visible red light	Connector M8, 3-pin	Rectangular	WTB4FP-213111A0ZZZ	1138006

- **Sensing range min. / max.:** 28 mm / 50 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, MultiPulse

Switching output	Light source	Type of light	Connection type	Housing	Type	Part no.
Push-pull: PNP/NPN	PinPoint LED	Visible red light	Connector M8, 3-pin	Rectangular	WTB4FP-213111A0ZZZ	1138151

- **Sensing range min. / max.:** 3 mm / 25 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, MultiPulse

Switching output	Light source	Type of light	Connection type	Housing	Type	Part no.
Push-pull: PNP/NPN	PinPoint LED	Visible red light	Connector M8, 3-pin	Rectangular	WTB4FP-213112A0ZZZ	1125737

- **Sensing range min. / max.:** 7 mm / 150 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, MultiPulse, LineSpot technology
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Connection type:** Cable with connector M8, 3-pin, with knurled nuts, 338 mm
- **Housing:** rectangular

Type	Part no.
WTB4FA-97311120ZZZ	1127216
	1130363

- **Sensing range min. / max.:** 2 mm / 50 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, V-optics
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Dark switching	Push-pull: PNP/NPN	Cable, 3-wire, 2 m	WTV4FE-1G312120ZZZ	1120716
		Connector M8, 3-pin	WTV4FE-21312120ZZZ	1119972
Light switching	PNP	Cable with connector M8, 3-pin, 110 mm	WTV4FE-31A11120ZZZ	1129444
		Connector M8, 3-pin	WTV4FE-21A11120ZZZ	1148753
	Push-pull: PNP/NPN	Cable with M12 male connector, 4-pin, 182 mm	WTV4FE-8416A120A00	1123755
		Cable with connector M8, 3-pin, 110 mm	WTV4FE-31311120ZZZ	1113190
		Cable with connector M8, 3-pin, with knurled nuts, 115 mm	WTV4FE-37311120ZZZ	1124152
		Cable with connector M8, 3-pin, with knurled nuts, 340 mm	WTV4FE-97311120ZZZ	1124153
		Cable, 3-wire, 2 m	WTV4FE-1G311120ZZZ	1113188
		Connector M8, 3-pin	WTV4FE-21311120ZZZ	1113186
Light/dark switching	Push-pull: PNP/NPN	Cable with M12 male connector, 4-pin, 182 mm	WTV4FE-84161120A00	1123753
		Cable with M8 male connector, 4-pin, 110 mm	WTV4FE-32161120A00	1113189
		Cable, 4-wire, 2 m	WTV4FE-1H161120A00	1113187
			WTV4FE-1H162120A00	1120896
		Male connector M8, 4-pin	WTV4FE-22161100A00	1124617
			WTV4FE-22161120A00	1105444
	WTV4FE-22162120A00	1119988		

- **Sensing range min. / max.:** 4 mm / 22 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, V-optics
- **Switching mode:** Light switching
- **Switching output:** push-pull: PNP/NPN

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Cable, 3-wire, 3 m	Rectangular	WTV4FE-5G3111A0ZZZ	1125733

- **Sensing range min. / max.:** 2 mm / 22 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, V-optics
- **Switching mode:** Light switching
- **Switching output:** push-pull: PNP/NPN

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Connector M8, 3-pin	Rectangular	WTV4FE-213111A0ZZZ	1120709

- **Sensing range min. / max.:** 0 mm / 100 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Foreground suppression
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Connection type	Type	Part no.
Dark switching	Connector M8, 3-pin	WTF4FD-21311220ZZZ	1119973
Light switching	Cable with connector M8, 3-pin, 110 mm	WTF4FD-31312220ZZZ	1113185
	Cable, 3-wire, 2 m	WTF4FD-1G312220ZZZ	1113183
Light/dark switching	Cable with M12 male connector, 4-pin, 182 mm	WTF4FD-84161220A00	1133355
	Cable with M8 male connector, 4-pin, 110 mm	WTF4FD-32161220A00	1118831
		WTF4FD-32162220A00	1113184
	Cable, 4-wire, 2 m	WTF4FD-1H161220A00	1118830
		WTF4FD-1H162220A00	1113182
	Male connector M8, 4-pin	WTF4FD-22161220A00	1105423
WTF4FD-22162220A00		1109266	



- **Sensing range min. / max.:** 0 m / 4.5 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** With minimum distance to reflector (dual lens system)
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Dark switching	PNP	Cable with connector M8, 3-pin, 110 mm	WLD4FP-31A111A0ZZZ	1138640
		Connector M8, 3-pin	WLD4FP-21A111A0ZZZ	1133952
	Push-pull: PNP/NPN	Cable with connector M8, 3-pin, 110 mm	WLD4FP-313111A0ZZZ	1121475
		Cable, 3-wire, 2 m	WLD4FP-1G3111A0ZZZ	1121470
		Connector M8, 3-pin	WLD4FP-213111A0ZZZ	1121473
		Male connector M8, 4-pin	WLD4FP-22163130A00	1124613
			WLD4FP-22164130A00	1124156
Light switching	PNP	Cable with connector M8, 3-pin, 110 mm	WLD4FP-31A121A0ZZZ	1138639
		Connector M8, 3-pin	WLD4FP-21A12100ZZZ	1149712
			WLD4FP-21A12130ZZZ	1129493
			WLD4FP-21A121A0ZZZ	1129443
	Push-pull: PNP/NPN	Cable with connector M8, 3-pin, 110 mm	WLD4FP-31312130ZZZ	1113195
			WLD4FP-313121A0ZZZ	1121474
		Cable, 3-wire, 2 m	WLD4FP-1G312130ZZZ	1113193
			WLD4FP-1G3121A0ZZZ	1121469
		Cable, 3-wire, 5 m	WLD4FP-6G3121A0ZZZ	1123761
		Connector M8, 3-pin	WLD4FP-21312100ZZZ	1124611
			WLD4FP-213121A0ZZZ	1121472
		Male connector M8, 4-pin	WLD4FP-22165130A00	1124612
			WLD4FP-22166130A00	1124157
		Light/dark switching	PNP	Cable with M8 male connector, 4-pin, 110 mm
Male connector M8, 4-pin	WLD4FP-228121A0ZZZ			1129442
Push-pull: PNP/NPN	Cable with M12 male connector, 4-pin, 182 mm		WLD4FP-841111A0ZZZ	1123748
			WLD4FP-841121A0ZZZ	1123746
	Cable with M8 male connector, 4-pin, 110 mm		WLD4FP-321121A0ZZZ	1121476
			WLD4FP-32162130A00	1113194
	Cable, 4-wire, 2 m		WLD4FP-1H161130A00	1107694
			WLD4FP-1H162130A00	1113192
	Male connector M8, 4-pin		WLD4FP-221121A0ZZZ	1121471
			WLD4FP-22162100A00	1124610

- **Sensing range min. / max.:** 0 mm / 4.5 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** With minimum distance to reflector (dual lens system)
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Dark switching	Push-pull: PNP/NPN	Cable with M12 male connector, 4-pin, 182 mm	WLD4FP-8416A130A00	1123749
		Connector M8, 3-pin	WLD4FP-21311130ZZZ	1119974
		Male connector M8, 4-pin	WLD4FP-22167130A00	1119990
			WLD4FP-2216A130A00	1119993
Light switching	Push-pull: PNP/NPN	Male connector M8, 4-pin	WLD4FP-2216K130A00	1119991
			WLD4FP-2216N130A00	1119994
			WLD4FP-2256K130A00	1119992
Light/dark switching	PNP	Male connector M8, 4-pin	WLD4FP-22861100A00	1140920
			WLD4FP-22862100A00	1140922
	Push-pull: PNP/NPN	Male connector M8, 4-pin	WLD4FP-22162130A00	1107303
				1122373

- **Sensing range min. / max.:** 15 mm / 4.5 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** With minimum distance to reflector (dual lens system)
- **Switching mode:** Light switching
- **Switching output:** push-pull: PNP/NPN

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Connector M8, 3-pin	Rectangular	WLD4FP-21312130ZZZ	1113191

- **Sensing range min. / max.:** 15 mm / 4.5 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** ClearSens, With minimum distance to reflector (dual lens system)
- **Switching mode:** Light switching
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching output	Connection type	Type	Part no.
PNP	Connector M8, 3-pin	WLG4FP-21A12130ZZZ	1146575
Push-pull: PNP/NPN	Cable, 3-wire, 2 m	WLG4FP-1G312130ZZZ	1150153
	Connector M8, 3-pin	WLG4FP-21312130ZZZ	1145223

- **Sensing range min. / max.:** 0 mm / 4.5 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** ClearSens, With minimum distance to reflector (dual lens system)
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Dark switching	PNP	Connector M8, 3-pin	WLG4FP-21A11130ZZZ	1146574
	Push-pull: PNP/NPN	Connector M8, 3-pin	WLG4FP-21311130ZZZ	1145222
Light/dark switching	Push-pull: PNP/NPN	Male connector M8, 4-pin	WLG4FP-22111130ZZZ	1145225

- **Sensing range min. / max.:** 0 m / 4.5 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** ClearSens, With minimum distance to reflector (dual lens system)
- **Switching mode:** Dark switching
- **Switching output:** push-pull: PNP/NPN

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Cable with connector M8, 3-pin, 110 mm	Rectangular	WLG4FP-31311130ZZZ	1145224

- **Sensing range min. / max.:** 0 m / 10 m
- **Functional principle:** Through-beam photoelectric sensor
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Dark switching	Push-pull: PNP/NPN	Cable with M12 male connector, 4-pin, 182 mm	WSE4FP-84161100A00	1123901
		Cable with connector M8, 3-pin, 110 mm	WSE4FP-31311100ZZZ	1123398
		Cable, 3-wire, 2 m	WSE4FP-1G311100ZZZ	1123397
		Connector M8, 3-pin	WSE4FP-21311100ZZZ	1123396
Light switching	PNP	Connector M8, 3-pin	WSE4FP-21A12100ZZZ	1149136
	Push-pull: PNP/NPN	Cable with connector M8, 3-pin, 110 mm	WSE4FP-31312100ZZZ	1120402
		Cable, 3-wire, 2 m	WSE4FP-1G312100ZZZ	1120403
		Cable, 3-wire, 5 m	WSE4FP-6G312100ZZZ	1123899
		Connector M8, 3-pin	WSE4FP-21312100ZZZ	1120404
Light/dark switching	Push-pull: PNP/NPN	Cable with M8 male connector, 4-pin, 110 mm	WSE4FP-32162100A00	1116538
		Cable, 4-wire, 2 m	WSE4FP-1H162100A00	1116539
		Male connector M8, 4-pin	WSE4FP-22162100A00	1116537

- **Sensing range min. / max.:** 0 m / 2 m
- **Functional principle:** Through-beam photoelectric sensor
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Dark switching	Push-pull: PNP/NPN	Cable with connector M8, 3-pin, 110 mm	WSE4FP-31311100ZZZ	1127055
			WSE4FP-31311600ZZZ	1124218
Light switching	PNP	Connector M8, 3-pin	WSE4FP-21A12600ZZZ	1149743
	Push-pull: PNP/NPN	Connector M8, 3-pin	WSE4FP-21312600ZZZ	1124217

- **Sensing range min. / max.:** 0 m / 1.5 m
- **Functional principle:** Through-beam photoelectric sensor
- **Switching mode:** Dark switching
- **Switching output:** push-pull: PNP/NPN

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Connector M8, 3-pin	Rectangular	WSE4FP-21311700ZZZ	1123902

- **Sensing range min. / max.:** 0 m / 10 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** With minimum distance to reflector (dual lens system)
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint LED
- **Type of light:** Infrared light
- **Housing:** rectangular

Switching mode	Connection type	Type	Part no.
Dark switching	Cable, 3-wire, 2 m	WLF4FI-1G3111A0ZZZ	1122376
Light switching	Cable with connector M8, 3-pin, with knurled nuts, 338 mm	WLF4FI-973121A0ZZZ	1124155
	Cable, 3-wire, 2 m	WLF4FI-1G3121A0ZZZ	1138208

- **Sensing range min. / max.:** 9 mm / 130 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, NarrowBeam
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Male connector M8, 4-pin	Rectangular	WTB4SP-22161420A00	1143092

- **Sensing range min. / max.:** 4 mm / 250 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Dark switching	Push-pull: PNP/NPN	Cable, 3-wire, 2 m	WTB4SP-1G312120ZZZ	1139077
		Connector M8, 3-pin	WTB4SP-21312120ZZZ	1139074
		Male connector M8, 4-pin	WTB4SP-2216N120A00	1140603
Light switching	NPN	Cable, 3-wire, 2 m	WTB4SP-1GE11120ZZZ	1132088
	Push-pull: PNP/NPN	Cable with M8 male connector, 4-pin, 114 mm	WTB4SP-32167120A00	1139486
		Cable with connector M8, 3-pin, 110 mm	WTB4SP-31311120ZZZ	1139085
		Cable, 3-wire, 2 m	WTB4SP-1G311120ZZZ	1139078
		Connector M8, 3-pin	WTB4SP-21311120ZZZ	1136382
		Male connector M8, 4-pin	WTB4SP-22167120A00	1139485
		Light/dark switching	Push-pull: PNP/NPN	Cable with M12 male connector, 4-pin, 190 mm
Cable with M8 male connector, 4-pin, 114 mm	WTB4SP-32161120A00			1132093
Cable, 4-wire, 2 m	WTB4SP-1H161120A00			1132094
	WTB4SP-1H162120A00			1139081
Male connector M8, 4-pin	WTB4SP-22161120A00			1131618
	WTB4SP-22162120A00	1136366		

- **Sensing range min. / max.:** 4 mm / 120 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light switching
- **Switching output:** push-pull: PNP/NPN

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Cable with M8 male connector, 4-pin, 114 mm	Rectangular	WTB4SP-3216A100A00	1140602

- **Sensing range min. / max.:** 4 mm / 130 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, NarrowBeam
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Dark switching	Push-pull: PNP/NPN	Cable with connector M8, 3-pin, 110 mm	WTB4SP-31312220ZZZ	1139072
		Cable, 3-wire, 2 m	WTB4SP-1G312220ZZZ	1139076
		Connector M8, 3-pin	WTB4SP-21312220ZZZ	1139071

Switching mode	Switching output	Connection type	Type	Part no.
Light switching	NPN	Cable, 3-wire, 2 m	WTB4SP-1GE11220ZZZ	1139284
	Push-pull: PNP/NPN	Cable with M8 male connector, 4-pin, 114 mm	WTB4SP-32167220A00	1139488
		Cable with connector M8, 3-pin, 110 mm	WTB4SP-31311220ZZZ	1139073
		Cable, 3-wire, 2 m	WTB4SP-1G311220ZZZ	1138660
		Connector M8, 3-pin	WTB4SP-21311220ZZZ	1139075
		Male connector M8, 4-pin	WTB4SP-22167220A00	1139487
1147084				
Light/dark switching	Push-pull: PNP/NPN	Cable with M12 male connector, 4-pin, 190 mm	WTB4SP-84161220A00	1136370
		Cable with M8 male connector, 4-pin, 114 mm	WTB4SP-32161220A00	1132087
		Cable, 4-wire, 2 m	WTB4SP-1H161220A00	1132793
			WTB4SP-1H162220A00	1139082
		Cable, 4-wire, 3 m	WTB4SP-5H162220A00	1142135
		Male connector M8, 4-pin	WTB4SP-22161220A00	1132792
WTB4SP-22162220A00	1139083			

- **Sensing range min. / max.:** 4 mm / 500 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Connection type	Type	Part no.
Light switching	Cable with M8 male connector, 4-pin, 114 mm	WTB4SP-32167A20A00	1139489
Light/dark switching	Cable with M12 male connector, 4-pin, 190 mm	WTB4SP-84161A20A00	1136384
		WTB4SP-84162A20A00	1147631
	Cable with M8 male connector, 4-pin, 114 mm	WTB4SP-32161A20A00	1136385
		Cable, 4-wire, 2 m	WTB4SP-1H161A20A00
	WTB4SP-1H162A20A00		1136383
	Cable, 4-wire, 5 m	WTB4SP-6H161A20A00	1142947
Male connector M8, 4-pin	WTB4SP-22161A20A00	1131621	

- **Sensing range min. / max.:** 0 mm / 150 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, DoubleLine
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Connection type	Type	Part no.
Dark switching	Cable with connector M8, 3-pin, 110 mm	WTB4ST-31312120ZZZ	1140101
	Connector M8, 3-pin	WTB4ST-21312120ZZZ	1138661
Light/dark switching	Cable with M12 male connector, 4-pin, 190 mm	WTB4ST-84161120A00	1136371
	Cable with M8 male connector, 4-pin, 114 mm	WTB4ST-32161120A00	1132090
	Cable, 4-wire, 2 m	WTB4ST-1H161120A00	1139080
		WTB4ST-1H162120A00	1136372
	Male connector M8, 4-pin	WTB4ST-22161120A00	1131620

- **Sensing range min. / max.:** 4 mm / 250 mm, 0 mm / 250 mm, 4 mm / 500 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression, Foreground suppression, MultiMode, distance value
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 190 mm	WTM4SP-84161120A00	1136368
Cable with M8 male connector, 4-pin, 114 mm	WTM4SP-32161120A00	1136367
Cable, 4-wire, 2 m	WTM4SP-1H161120A00	1139115
	WTM4SP-1H162120A00	1136369
Male connector M8, 4-pin	WTM4SP-22161120A00	1131619

- **Sensing range min. / max.:** 0 mm / 130 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Foreground suppression
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M12 male connector, 4-pin, 190 mm	WTF4SD-84161220A00	1139113
	WTF4SD-84162220A00	1136374
Cable with M8 male connector, 4-pin, 114 mm	WTF4SD-32161220A00	1139114
	WTF4SD-32162220A00	1136373

Connection type	Type	Part no.
Cable, 4-wire, 2 m	WTF4SD-1H161220A00	1136375
	WTF4SD-1H162220A00	1139084
Male connector M8, 4-pin	WTF4SD-22162220A00	1132089

- **Sensing range min. / max.:** 0 m / 4 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** Without reflector minimum distance (autocollimation/coaxial optics)
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Connection type	Type	Part no.
Dark switching	Cable with M12 male connector, 4-pin, 190 mm	WLA4SP-8416A100A00	1139765
	Cable with connector M8, 3-pin, 110 mm	WLA4SP-31311100ZZZ	1139129
	Cable, 3-wire, 2 m	WLA4SP-1G311100ZZZ	1139133
	Cable, 4-wire, 2 m	WLA4SP-1H163100A00	1140051
	Connector M8, 3-pin	WLA4SP-21311100ZZZ	1139131
	Male connector M8, 4-pin	WLA4SP-22163100A00	1140052
Light switching	Cable with connector M8, 3-pin, 110 mm	WLA4SP-31312100ZZZ	1139138
	Cable, 3-wire, 2 m	WLA4SP-1G312100ZZZ	1139137
	Cable, 4-wire, 2 m	WLA4SP-1H165100A00	1140053
	Connector M8, 3-pin	WLA4SP-21312100ZZZ	1139135
Light/dark switching	Cable with M12 male connector, 4-pin, 190 mm	WLA4SP-84162100A00	1139756
	Cable with M8 male connector, 4-pin, 114 mm	WLA4SP-32162100A00	1136376
	Cable, 4-wire, 2 m	WLA4SP-1H161100A00	1136378
		WLA4SP-1H162100A00	1136377
	Male connector M8, 4-pin	WLA4SP-22162100A00	1132091
			1140452

- **Sensing range min. / max.:** 0 m / 7.1 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** Without reflector minimum distance (autocollimation/coaxial optics)
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Connection type	Type	Part no.
Dark switching	Cable with connector M8, 3-pin, 110 mm	WLA4SP-31311130ZZZ	1139134
	Cable, 4-wire, 2 m	WLA4SP-1H163130A00	1140054
	Connector M8, 3-pin	WLA4SP-21311130ZZZ	1139136
	Male connector M8, 4-pin	WLA4SP-22163130A00	1141246



Switching mode	Connection type	Type	Part no.
Light switching	Cable with connector M8, 3-pin, 110 mm	WLA4SP-31312130ZZZ	1139130
	Cable, 4-wire, 2 m	WLA4SP-1H165130A00	1140055
	Connector M8, 3-pin	WLA4SP-21312130ZZZ	1139132
	Male connector M8, 4-pin	WLA4SP-22165130A00	1140056
Light/dark switching	Cable with M12 male connector, 4-pin, 190 mm	WLA4SP-84162130A00	1139759
	Cable with M8 male connector, 4-pin, 114 mm	WLA4SP-32162130A00	1136388
	Cable with connector M8, 4-pin, with knurled nuts, 220 mm	WLA4SP-88162130A00	1140451
	Cable, 4-wire, 2 m	WLA4SP-1H161130A00	1136386
		WLA4SP-1H162130A00	1136387
	Male connector M8, 4-pin	WLA4SP-22161130A00	1139755
		WLA4SP-22162130A00	1136389

- **Sensing range min. / max.:** 0 m / 7.1 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** Without reflector minimum distance (autocollimation/coaxial optics), ClearSens
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Dark switching	Push-pull: PNP/NPN	Cable with connector M8, 3-pin, 110 mm	WLG4SP-31311130ZZZ	1140091
		Cable, 3-wire, 2 m	WLG4SP-1G311130ZZZ	1140050
		Connector M8, 3-pin	WLG4SP-21311130ZZZ	1141248
Light switching	NPN	Cable with Tyco male connector, 3-pin, 440 mm	WLG4SP-XXE12130ZZZ	1141349
	Push-pull: PNP/NPN	Cable with connector M8, 3-pin, 110 mm	WLG4SP-31312130ZZZ	1140102
		Connector M8, 3-pin	WLG4SP-21312130ZZZ	1141247

- **Sensing range min. / max.:** 0 m / 7.1 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** Without reflector minimum distance (autocollimation/coaxial optics), ClearSens, MultiMode
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Connection type	Type	Part no.
Dark switching	Cable with M12 male connector, 4-pin, 190 mm	WLG4SP-8416A130A00	1139766
	Cable with M8 male connector, 4-pin, 114 mm	WLG4SP-32167130A00	1139761
	Cable with connector M8, 4-pin, with knurled nut, 220 mm	WLG4SP-88167130A00	1143644
	Cable, 4-wire, 2 m	WLG4SP-1H163130A00	1140057
	Male connector M8, 4-pin	WLG4SP-22163130A00	1140058
		WLG4SP-22167130A00	1139760

Switching mode	Connection type	Type	Part no.
Light switching	Cable with MOLEX-connector, 4-pin, 295 mm	WLG4SP-XX56K130A00	1141316
	Cable with MOLEX-connector, 5-pin, 175 mm	WLG4SP-XX56K130A00	1141317
	Cable, 4-wire, 2 m	WLG4SP-1H165130A00	1140060
WLG4SP-1H56K130A00		1140059	
Light/dark switching	Cable with M12 male connector, 4-pin, 190 mm	WLG4SP-84161130A00	1139754
		WLG4SP-84162120A00	1136380
		WLG4SP-84162130A00	1139758
		WLG4SP-8416K130A00	1139764
	Cable with M8 male connector, 4-pin, 114 mm	WLG4SP-32162120A00	1136379
		WLG4SP-32162130A00	1136638
		WLG4SP-3216K130A00	1139763
	Cable, 4-wire, 2 m	WLG4SP-1H161120A00	1139757
		WLG4SP-1H162120A00	1136381
		WLG4SP-1H162130A00	1136639
	Male connector M8, 4-pin	WLG4SP-22161130A00	1139753
		WLG4SP-22162120A00	1132092
		WLG4SP-22162130A00	1136637
		WLG4SP-2216K130A00	1139762

- **Sensing range min. / max.:** 0 m / 12 m
- **Functional principle:** Through-beam photoelectric sensor
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Connection type	Type	Part no.
-	Cable with M12 male connector, 4-pin, 190 mm	WSE4SP-8416A100A00	1140391
	Male connector M8, 4-pin	WSE4SP-22112100ZZZ	1142679
Dark switching	Cable with M12 male connector, 4-pin, 190 mm	WSE4SP-84161100A00	1140390
	Cable with M8 male connector, 4-pin, 114 mm	WSE4SP-32161100A00	1140395
	Cable with connector M8, 3-pin, 110 mm	WSE4SP-31311100ZZZ	1140393
	Cable, 3-wire, 2 m	WSE4SP-1G311100ZZZ	1140384
	Connector M8, 3-pin	WSE4SP-21311100ZZZ	1140382
	Male connector M8, 4-pin	WSE4SP-22161100A00	1140392
	Light switching	Cable with connector M8, 3-pin, 110 mm	WSE4SP-31312100ZZZ
Light/dark switching	Cable, 3-wire, 2 m	WSE4SP-1G312100ZZZ	1140383
	Connector M8, 3-pin	WSE4SP-21312100ZZZ	1140381
	Male connector M8, 4-pin	WSE4SP-22162100A00	1138377

- **Sensing range min. / max.:** 0 m / 2.5 m
- **Functional principle:** Through-beam photoelectric sensor
- **Switching mode:** Light/dark switching
- **Switching output:** push-pull: PNP/NPN

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Male connector M8, 4-pin	Rectangular	WSE4SP-22162800A00	1142680

- **Sensing range min. / max.:** 0.035 m / 4.8 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** With minimum distance to reflector (dual lens system)
- **Switching output:** push-pull: PNP/NPN
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Connection type	Type	Part no.
Light switching	Connector M8, 3-pin	WLD4SP-213121A0ZZZ	1142555
Light/dark switching	Male connector M8, 4-pin	WLD4SP-221121A0ZZZ	1142556

- **Sensing range max.:** 4 mm ... 150 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Light source:** PinPoint LED
- **Housing:** rectangular

Switching mode	Switching output	Type of light	Connection type	Type	Part no.	
Dark switching	NPN	Visible red light	Cable with connector M8, 3-pin <sup>1)</sup>	WTB4-3E3161	1028109	
			Cable, 3-wire, 2 m <sup>1)</sup>	WTB4-3E1361	1028108	
				WTB4-3E1371	1066656	
			Cable, 4-wire, 2 m <sup>1)</sup>	WTB4-3E1164S01	1029111	
		Connector M8, 3-pin	WTB4-3E2161	1028110		
	PNP	Visible red light	Cable with connector M8, 3-pin <sup>1)</sup>	WTB4-3F3161	1028106	
				WTB4-3F3162	1084429	
			Cable, 3-wire, 2 m <sup>1)</sup>	WTB4-3F1361	1028105	
			Connector M8, 3-pin	WTB4-3F2161	1028107	
				WTB4-3F2162	1051228	
Light switching	NPN	Visible red light	–	WTB4-3N1061S31	1044345	
			Cable with connector M8, 3-pin <sup>1)</sup>	WTB4-3N3161	1028103	
					WTB4-3N3162	1028089
					WTB4-3N3171	1041717
			Cable with connector Microfit, 4-pin <sup>1)</sup>	WTB4-3N3064S76	1058336	
			Cable, 3-wire, 2 m <sup>1)</sup>	WTB4-3N1361	1028101	
					WTB4-3N1361S16	1029877
					WTB4-3N1362	1028087
					WTB4-3N1371	1028125
			Cable, 3-wire, 5 m <sup>1)</sup>	WTB4-3N1461	1057301	
			Cable, 4-wire, 2 m <sup>1)</sup>	WTB4-3N1160S53	1044783	
					WTB4-3N1164	1028090
					WTB4S-3N1164	1042036
	Connector M8, 3-pin	WTB4-3N2161	1028104			
		WTB4-3N2171	1028126			
	Cable with special connector, 3-wire <sup>1)</sup>	WTB4-3N1164S86	1077100			
	PNP	Infrared light	Cable with M8 male connector, 4-pin <sup>1)</sup>	WTB4-3P3214S59	1052261	
	Light switching	PNP	Visible red light	Cable with M12 male connector, 4-pin <sup>1)</sup>	WTB4-3P3464	1044013
Cable with M8 male connector, 4-pin <sup>1)</sup>				WTB4-3P3261S27	1029884	
					WTB4-3P3264	1047193
					WTB4-3P3264S03	1029467

<sup>1)</sup> Do not bend below 0 °C.

Switching mode	Switching output	Type of light	Connection type	Type	Part no.	
				WTB4-3P3264S30	1040628	
				WTB4-3P3271S07	1083881	
				WTB4S-3P3264	1042035	
			Cable with connector M8, 3-pin	WTB4-3P3061S15	1029876	
				WTB4S-3P3162	1042038	
			Cable with connector M8, 3-pin <sup>1)</sup>	WTB4-3P3161	1028097	
				WTB4-3P3161S11	1029873	
				WTB4-3P3162	1028082	
				WTB4-3P3162S04	1029917	
		Visible red light	Cable with connector M8, 3-pin <sup>1)</sup>	WTB4-3P3162S45	1042104	
				WTB4-3P3171	1028122	
			Cable, 3-wire, 2 m <sup>1)</sup>	WTB4-3P1361	1028094	
				WTB4-3P1362	1028081	
				WTB4-3P1371	1028121	
			Cable, 4-wire, 5 m <sup>1)</sup>	WTB4-3P1264	1041890	
			Connector M8, 3-pin	WTB4-3P2161	1028099	
					WTB4-3P2161S28	1040445
					WTB4-3P2162	1028084
					WTB4-3P2171	1028123
					WTB4S-3P2162	1042037
			Male connector M8, 4-pin	WTB4-3P2261S25	1029883	
					WTB4-3P2262S41	1041242
					WTB4-3P2264	1028086
					WTB4-3P2264S32	1045858
				WTB4S-3P2264	1042034	
				WTB4S-3P2264S01	1043652	

<sup>1)</sup> Do not bend below 0 °C.

Switching mode	Switching output	Type of light	Connection type	Type	Part no.
Light/dark switching	NPN	Visible red light	Cable with M8 male connector, 4-pin <sup>1)</sup>	WTB4-3N3262	1075083
			Cable, 4-wire, 2 m <sup>1)</sup>	WTB4-3N1161	1028102
	PNP	Visible red light	Cable with M12 male connector, 4-pin	WTB4C-3P3462A00	1099420
			Cable with M12 male connector, 4-pin <sup>1)</sup>	WTB4-3P3461	1029949
			Cable with M8 male connector, 4-pin <sup>1)</sup>	WTB4-3P3261	1028098
			Cable, 4-wire, 2 m <sup>1)</sup>	WTB4-3P1161	1028096
			Cable, 4-wire, 5 m <sup>1)</sup>	WTB4-3P1261	1092244
			Male connector M8, 4-pin	WTB4-3P2261	1028100
				WTB4-3P2262	1028085
				WTB4-3P2271	1042190
				WTB4C-3P2262A70	1080928
				WTB4C-3P2262A71	9243603
				1080929	

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 3 mm ... 150 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching output:** PNP
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Connection type	Type	Part no.
Light switching	Cable with M8 male connector, 4-pin <sup>1)</sup>	WTB4-3P3261S51	1043518
Light/dark switching	Male connector M8, 4-pin	WTB4-3P2261S44	1041937

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 4 mm ... 140 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Cable with connector M8, 3-pin <sup>1)</sup>	Rectangular	WTB4-3P3161S02	1029261

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 28 mm ... 165 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Cable with connector M8, 3-pin	Rectangular	WTB4-3P2100S78	1059594

- **Sensing range max.:** 4 mm ... 55 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Dark switching	NPN	Cable with male connector <sup>1)</sup>	WTB4-3E1360S46	1042154
Light switching	PNP	Cable with connector M8, 3-pin <sup>1)</sup>	WTV4-3P3041S12	1029874
		Cable, 3-wire, 2 m <sup>1)</sup>	WTV4-3P1341S77	1059327

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 15 mm ... 150 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Cable with M8 male connector, 4-pin <sup>1)</sup>	Rectangular	WTB4-3P3264S75	1057266

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 3 mm ... 200 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** PNP
- **Light source:** LED
- **Type of light:** Infrared light
- **Connection type:** Cable with M8 male connector, 4-pin (Do not bend below 0 °C.)
- **Housing:** rectangular

Type	Part no.
WTB4-3P3212S54	1046786
WTB4-3P3212S61	1052910

- **Sensing range max.:** ≤ 150 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
LED	Infrared light	Cable with connector RJ10, 4-pin <sup>1)</sup>	Rectangular	WTB4-3P3241S74	1057156

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 3 mm ... 250 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** NPN

Light source	Type of light	Connection type	Housing	Type	Part no.
LED	Infrared light	Cable with M8 male connector, 4-pin <sup>1)</sup>	Rectangular	WTB4-3N3212S55	1046787

<sup>1)</sup> Do not bend below 0 °C.



- **Sensing range max.:** 4 mm ... 50 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Light source:** PinPoint LED
- **Housing:** rectangular

Switching mode	Switching output	Type of light	Connection type	Type	Part no.
Dark switching	NPN	Visible red light	Cable, 4-wire, 2 m <sup>1)</sup>	WTV4-3N1141	1084396
	PNP	Visible red light	Cable with connector M8, 3-pin <sup>1)</sup>	WTV4-3F3141S48	1042161
Light switching	NPN	Infrared light	Cable, 3-wire, 2 m <sup>1)</sup>	WTV4-3N1321	1029885
				WTV4-3N1322P07	1104149
				WTV4-3N1322S01	1085155
				WTV4-3N1322S88	1100125
				WTV4-3N1322S89	1088289
				WTV4-3N1322S90	1093901
	Visible red light	Cable, 3-wire, 2 m <sup>1)</sup>	WTV4-3N1341	1028115	
			Connector M8, 3-pin	WTV4-3N2141	1028116
	PNP	Infrared light	Cable with connector M8, 3-pin <sup>1)</sup>	WTV4-3P3021S64	1054543
				WTV4-3P3121	1042191
				WTV4-3P3122	1046411
				Cable, 3-wire, 2 m <sup>1)</sup>	WTV4-3P1321
		Visible red light	-	WTV4-3P1040S42	1041689
			Cable with M12 male connector, 4-pin <sup>1)</sup>	WTV4-3P3441S38	1040696
			Cable with connector M8, 3-pin <sup>1)</sup>	WTV4-3P3141	1028112
			Cable, 3-wire, 2 m <sup>1)</sup>	WTV4-3P1341	1028111
			Connector M8, 3-pin	WTV4-3P2140S32	1040689
				WTV4-3P2140S33	1029887
	WTV4-3P2140S43	1041693			
	WTV4-3P2141	1028113			
Light/dark switching	NPN	Infrared light	Male connector M8, 4-pin	WTV4-3N2221	1048995
	PNP	Visible red light	Cable with M12 male connector, 4-pin <sup>1)</sup>	WTV4-3P3441	1029582
			Cable, 4-wire, 2 m <sup>1)</sup>	WTV4-3P1141	1084397
			Male connector M8, 4-pin	WTV4-3P2241	1028114

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 22 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Cable, 3-wire, 3 m	Rectangular	WTV4-3P1040S17	1029879

- **Sensing range max.:** 2 mm ... 50 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Light source:** PinPoint LED
- **Type of light:** Infrared light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Light switching	NPN	Cable, 3-wire, 2 m <sup>1)</sup>	WTV4-3N1321S49	1043721
	PNP	Cable, 3-wire, 2 m <sup>1)</sup>	WTV4-3P1321S54	1045365
Light/dark switching	NPN	Male connector M8, 4-pin	WTV4-3N2221P04	1051481

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 3 mm ... 50 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Light source:** PinPoint LED
- **Type of light:** Infrared light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Light switching	NPN	Male connector M8, 4-pin	WTV4-3N2201S68	1055055
	PNP	Cable with M8 male connector, 4-pin <sup>1)</sup>	WTV4-3P3222S57	1050786
Light/dark switching	PNP	Cable with M8 male connector, 4-pin <sup>1)</sup>	WTV4-3P3222S60	1052426

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 10 mm ... 60 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Foreground suppression
- **Switching mode:** Light switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Connector M8, 3-pin	Rectangular	WTF4-3F2161S49	1042432

- **Sensing range max.:** 0.01 m ... 4.5 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** With minimum distance to reflector (dual lens system)
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Dark switching	NPN	-	WL4-3E3030S21	1029891
		Cable with connector M8, 3-pin <sup>1)</sup>	WL4-3E3130	1028157
		Cable with special male connector, 4-pin <sup>1)</sup>	WL4-3E3034S34	1064934
		Cable, 3-wire, 2 m <sup>1)</sup>	WL4-3E1330	1028156
		Connector M8, 3-pin	WL4-3E2130	1028158
	PNP	-	WL4-3F3030S35	1068099
		Cable with M12 male connector, 4-pin <sup>1)</sup>	WL4-3F3430S29	1043682
		Cable with connector M8, 3-pin <sup>1)</sup>	WL4-3F3130	1028153
		Cable, 3-wire, 2 m <sup>1)</sup>	WL4-3F1330	1028152
		Connector M8, 3-pin	WL4-3F2130	1028155
Light switching	NPN	-	WL4-3N3031S02	1042990
		-	WL4-3N3031S03	1042991
		Cable with connector M8, 3-pin <sup>1)</sup>	WL4-3N3130	1028150
		Cable, 3-wire, 2 m <sup>1)</sup>	WL4-3N1330	1028148
		Connector M8, 3-pin	WL4-3N2130	1028151
	PNP	Cable with M12 male connector, 4-pin <sup>1)</sup>	WL4-3P3430	1044347
		Cable with Tyco connector <sup>1)</sup>	WL4-3P3030S32	1058696
			WL4-3P3030S33	1058697
		Cable with connector M8, 3-pin <sup>1)</sup>	WL4-3P3130	1028144
		Cable, 3-wire, 2 m <sup>1)</sup>	WL4-3P1330	1028143
		Cable, 3-wire, 5 m <sup>1)</sup>	WL4-3P1430	1050558
		Connector M8, 3-pin	WL4-3P2130	1028146

<sup>1)</sup> Do not bend below 0 °C.

Switching mode	Switching output	Connection type	Type	Part no.
Light/dark switching	PNP	Cable with M12 male connector, 4-pin	WL4C-3P3432A00	1099421
		Cable with M12 male connector, 4-pin <sup>1)</sup>	WL4-3K3430	1106886
		Cable with M8 male connector, 4-pin <sup>1)</sup>	WL4-3P3230	1028145
		Male connector M8, 4-pin	WL4-3P2230	1028147
			WL4C-3P2232A00	1080930
			WL4C-3P2232A70	1080931
			WL4C-3P2232A71	1080932

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 0.01 m ... 4.5 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Dark switching	NPN	Cable, 3-wire, 2 m <sup>1)</sup>	WLG4-3E1332	1028131
		Cable, 4-wire, 2 m <sup>1)</sup>	WLG4-3E1134	1028133
		Connector M8, 3-pin	WLG4-3E2132	1028132
	PNP	Cable with M12 male connector, 4-pin <sup>1)</sup>	WLG4-3F3434	1043683
		Cable with M8 male connector, 4-pin <sup>1)</sup>	WLG4-3F3234	1028129
		Cable with connector M8, 3-pin <sup>1)</sup>	WLG4-3F3132	1028128
		Connector M8, 3-pin	WLG4-3F2132	1028127
		Male connector M8, 4-pin	WL4-3F2260S28	1042430
			WLG4-3F2234	1028130
Light switching	PNP	Cable, 3-wire, 2 m <sup>1)</sup>	WLG4-3P1332	1042844
		Connector M8, 3-pin	WLG4-3P2132	1029567
		Male connector M8, 4-pin	WL4-3P2260S27	1042429
Light/dark switching	PNP	Male connector M8, 4-pin	WLG4-3K2232	1070194
			WLG4C-3P2232A00	1080933
			WLG4C-3P2232A70	1080934
			WLG4C-3P2232A71	1080935

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 0.4 m ... 3.5 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Switching mode:** Light switching
- **Light source:** LED
- **Type of light:** Infrared light
- **Housing:** rectangular

Switching output	Connection type	Type	Part no.
NPN	Cable, 3-wire <sup>1)</sup>	WL4-3N1310S25	1029959
PNP	Cable with M12 male connector, 4-pin <sup>1)</sup>	WL4-3P3410S19	1029889
	Cable, 3-wire, 2 m <sup>1)</sup>	WL4-3P1310S31	1044668
	Cable with male connector <sup>1)</sup>	WL4-3P3010S22	1042455

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 0.4 m ... 9 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** With minimum distance to reflector (dual lens system)
- **Switching mode:** Light/dark switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
LED	Infrared light	Cable with male connector <sup>1)</sup>	Rectangular	WL4-3P3010S23	1029892

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 0 m ... 4 m
- **Functional principle:** Through-beam photoelectric sensor
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.		
Dark switching	NPN	Cable with connector M8, 3-pin <sup>1)</sup>	WSE4-3E3130	1028174		
		Cable, 3-wire, 2 m <sup>1)</sup>	WSE4-3E1330	1028172		
		Connector M8, 3-pin	WSE4-3E2130	1028175		
	PNP	Cable with M12 male connector, 4-pin <sup>1)</sup>	WSE4-3F3430	1044346		
		Cable with connector M8, 3-pin <sup>1)</sup>	WSE4-3F3130	1028170		
		Cable, 3-wire, 2 m <sup>1)</sup>	WSE4-3F1330	1028168		
		Connector M8, 3-pin	WSE4-3F2130	1028171		
			WSE4-3F2131	1041132		
		Light switching	NPN	Cable with connector M8, 3-pin <sup>1)</sup>	WSE4-3N3130	1028166
				Cable, 3-wire, 2 m <sup>1)</sup>	WSE4-3N1330	1028164
Connector M8, 3-pin	WSE4-3N2130			1028167		
PNP	Cable with connector M8, 3-pin <sup>1)</sup>		WSE4-3P3130	1028161		
			WSE4-3P3131	1029898		
	Cable, 3-wire, 2 m <sup>1)</sup>		WSE4-3P1330	1028159		
	Cable, 3-wire, 5 m <sup>1)</sup>		WSE4-3P1430	1029645		
Light/dark switching	PNP	Connector M8, 3-pin	WSE4-3P2130	1028163		
		Male connector M8, 4-pin	WSE4-3P2230	1028160		
			WSE4C-3P2230A00	1080936		
			WSE4C-3P2230A70	1080937		
			WSE4C-3P2230A71	1080938		

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 0 m ... 1.5 m
- **Functional principle:** Through-beam photoelectric sensor
- **Switching mode:** Light switching
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching output	Connection type	Type	Part no.
NPN	Cable, 3-wire, 2 m <sup>1)</sup>	WSE4S-3P1330HS01	1054973
PNP	Connector M8, 3-pin	WSE4-3P2130S03	1066598

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 0 m ... 0.9 m
- **Functional principle:** Through-beam photoelectric sensor
- **Switching mode:** Light/dark switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Male connector M8, 4-pin	Rectangular	WSE4-3P2230S02	1043260

- **Sensing range max.:** 4 mm ... 180 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Dark switching	NPN	Cable, 3-wire, 2 m <sup>1)</sup>	WTB4S-3E1361	1042047
	PNP	Connector M8, 3-pin	WTB4S-3F2161	1042044
Light switching	NPN	Cable, 3-wire, 2 m <sup>1)</sup>	WTB4S-3N1361	1042046
			WTB4S-3N1361P01	1103888
	PNP	Connector M8, 3-pin	WTB4S-3N2161	1042045
		Cable with connector M8, 3-pin <sup>1)</sup>	WTB4S-3P3161	1042042
		Cable, 3-wire, 2 m <sup>1)</sup>	WTB4S-3P1361	1042043
		Connector M8, 3-pin	WTB4S-3P2161	1042040

<sup>1)</sup> Do not bend below 0 °C.

<sup>2)</sup> Max. tightening torque: 0.7 Nm.

<sup>3)</sup> Max. tightening torque: 0.6 Nm.

Switching mode	Switching output	Connection type	Type	Part no.
Light/dark switching	PNP	Cable with M12 male connector, 4-pin, 150 mm	WTB4SC-3P3462A00	1117403
		Cable with M12 male connector, 4-pin <sup>1)</sup>	WTB4S-3P3461	1044809
			WTB4S-3P3462	1051374
		Cable with M12 male connector, 4-pin <sup>1) 2)</sup>	WTB4SC-3P3462VA00	1097823
		Cable with M8 male connector, 4-pin	WTB4S-3P3261	1064142
		Male connector M12, 4-pin <sup>2)</sup>	WTB4SC-3P2462VA00	1097825
		Male connector M8, 4-pin	WTB4S-3K2261	1047804
			WTB4S-3P2261	1042041
			WTB4S-3P2262	1070222
			WTB4SC-3P2262A00	1042033
			WTB4SC-3P2262A70	1067756
			WTB4SC-3P2262A71	1067757
			WTB4SC-3P2262A73	1093610
		Male connector M8, 4-pin <sup>3)</sup>	WTB4SC-3P2262A91	1067758
			WTB4SC-3P2262B03	1099918
WTB4SC-3P2262VA00	1097824			
WTB4SC-3P5232HA00	1097836			

<sup>1)</sup> Do not bend below 0 °C.

<sup>2)</sup> Max. tightening torque: 0.7 Nm.

<sup>3)</sup> Max. tightening torque: 0.6 Nm.

- **Sensing range max.:** 4 mm ... 120 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Dark switching	NPN	Cable, 3-wire, 2 m <sup>1)</sup>	WTB4S-3E1331	1042064
		PNP	Cable with connector M8, 3-pin <sup>1) 2)</sup>	WTB4S-3F3132V
	Connector M8, 3-pin		WTB4S-3F2131	1042060
	Connector M8, 3-pin <sup>2)</sup>	WTB4S-3F2132V	1046404	
Light switching	NPN	Cable with connector M8, 3-pin <sup>1)</sup>	WTB4S-3N3132	1074980
		Cable, 3-wire, 2 m <sup>1)</sup>	WTB4S-3N1331	1042062
			WTB4S-3N1332	1042055
Cable, 4-wire, 2 m <sup>1)</sup>	WTB4S-3N1132	1051563		

<sup>1)</sup> Do not bend below 0 °C.

<sup>2)</sup> Max. tightening torque: 0.6 Nm.

<sup>3)</sup> Max. tightening torque: 0.7 Nm.



Switching mode	Switching output	Connection type	Type	Part no.	
			WTB4S-3N1134	1042052	
		Cable, 4-wire, 5 m <sup>1)</sup>	WTB4T-3N1264	1028092	
		Connector M8, 3-pin	WTB4S-3N2131	1042061	
		Connector M8, 3-pin <sup>2)</sup>	WTB4S-3N2132V	1046405	
	PNP	Cable with M12 male connector, 4-pin <sup>1) 3)</sup>		WTB4S-3P3434V	1048016
				WTB4S-3P3435V	1046407
		Cable with M8 male connector, 4-pin <sup>1)</sup>		WTB4S-3P3234	1042051
		Cable with M8 male connector, 4-pin <sup>1) 2)</sup>		WTB4S-3P3234H	1048097
				WTB4S-3P3235H	1048100
		Cable with connector M8, 3-pin <sup>1)</sup>		WTB4S-3P3131	1042058
				WTB4S-3P3132	1042054
		Cable with connector M8, 3-pin <sup>1) 2)</sup>		WTB4S-3P3132V	1046400
		Cable, 3-wire, 2 m <sup>1)</sup>		WTB4S-3P1331	1042059
				WTB4S-3P1332	1052284
		Cable, 4-wire, 10 m <sup>1)</sup>		WTB4S-3P1035VS06	1051749
		Cable, 4-wire, 5 m <sup>1)</sup>		WTB4T-3P1264	1028091
		Connector M8, 3-pin		WTB4S-3P2131	1042056
				WTB4S-3P2132	1042053
		Connector M8, 3-pin <sup>2)</sup>		WTB4S-3P2132V	1046397
		Male connector M12, 4-pin <sup>3)</sup>		WTB4S-3P2432V	1054672
		Male connector M8, 4-pin		WTB4S-3P2234	1042050
				WTB4S-3P2234S07	1058763
		Male connector M8, 4-pin <sup>2)</sup>		WTB4S-3P2234VS10	1058488
				WTB4S-3P2235V	1045093
				WTB4S-3P2235VS07	1053760

<sup>1)</sup> Do not bend below 0 °C.

<sup>2)</sup> Max. tightening torque: 0.6 Nm.

<sup>3)</sup> Max. tightening torque: 0.7 Nm.

Switching mode	Switching output	Connection type	Type	Part no.	
Light/dark switching	NPN	Cable, 4-wire, 2 m <sup>1)</sup>	WTB4S-3N1131	1042063	
			WTB4S-3N1132H	1048098	
			WTB4S-3N1132V	1046403	
		Male connector M12, 4-pin <sup>3)</sup>	WTB4S-3N2432V	1054674	
			Male connector M8, 4-pin	WTB4S-3N2232	1051872
				PNP	Cable with M12 male connector, 4-pin <sup>1)</sup>
	WTB4S-3P3432	1051373			
	Cable with M12 male connector, 4-pin <sup>1) 3)</sup>	WTB4S-3P3432V	1046399		
		Cable with M8 male connector, 4-pin <sup>1) 2)</sup>	WTB4S-3P3232H		1048096
	WTB4S-3P3232V		1046398		
	WTB4SC-3P3232H		1048099		
	Cable, 4-wire, 2 m <sup>1)</sup>	WTB4S-3P1132V	1046402		
		Cable, 4-wire, 5 m <sup>1)</sup>	WTB4S-3P1232V		1052411
	Male connector M8, 4-pin	WTB4S-3P2231	1042057		
		WTB4S-3P2232	1054282		
		WTB4SC-3P2232A00	1042049		
	Male connector M8, 4-pin <sup>2)</sup>	WTB4S-3P2232V	1046396		
		WTB4S-3P5232H	1054864		

<sup>1)</sup> Do not bend below 0 °C.

<sup>2)</sup> Max. tightening torque: 0.6 Nm.

<sup>3)</sup> Max. tightening torque: 0.7 Nm.

- **Sensing range max.:** 4 mm ... 500 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Dark switching	PNP	Cable with connector M8, 3-pin <sup>1) 2)</sup>	WTB4S-3F3162V	1046390
		Connector M8, 3-pin <sup>1)</sup>	WTB4S-3F2162V	1046389
		Male connector M8, 4-pin <sup>1)</sup>	WTB4S-3F2265V	1048208

<sup>1)</sup> Max. tightening torque: 0.6 Nm.

<sup>2)</sup> Do not bend below 0 °C.

<sup>3)</sup> Max. tightening torque: 0.7 Nm.

Switching mode	Switching output	Connection type	Type	Part no.
Light switching	NPN	Cable, 3-wire, 2 m <sup>2)</sup>	WTB4S-3N1362V	1046393
		Connector M8, 3-pin <sup>1)</sup>	WTB4S-3N2162V	1046392
		Male connector M8, 4-pin <sup>1)</sup>	WTB4S-3N2265V	1047620
	PNP	Cable with M12 male connector, 4-pin <sup>2) 3)</sup>	WTB4S-3P3464V	1048015
			WTB4S-3P3465V	1046394
		Cable with M8 male connector, 4-pin <sup>2)</sup>	WTB4S-3P3264S13	1123076
		Cable with M8 male connector, 4-pin <sup>1) 2)</sup>	WTB4S-3P3264H	1048047
			WTB4S-3P3265H	1048102
		Cable with connector M8, 3-pin <sup>1) 2)</sup>	WTB4S-3P3162V	1046387
		Cable, 4-wire, 2 m <sup>2)</sup>	WTB4S-3P1165H	1086062
		Connector M8, 3-pin <sup>1)</sup>	WTB4S-3P2162V	1046384
		Male connector M12, 4-pin <sup>3)</sup>	WTB4S-3P2465V	1096885
		Male connector M8, 4-pin <sup>1)</sup>	WTB4S-3P2264V	1047651
			WTB4S-3P2265V	1045091
		Light/dark switching	NPN	Cable, 4-wire, 2 m <sup>2)</sup>
WTB4S-3N1162V	1046391			
Male connector M12, 4-pin <sup>3)</sup>	WTB4S-3N2462V			1054703
PNP	Cable with M12 male connector, 4-pin <sup>2) 3)</sup>		WTB4S-3P3462V	1046386
			WTB4S-3P3462VS15	1098603
	Cable with M8 male connector, 4-pin <sup>1) 2)</sup>		WTB4S-3P3262H	1048094
			WTB4S-3P3262V	1046385
	Cable, 4-wire, 2 m <sup>2)</sup>		WTB4S-3P1162H	1051983
			WTB4S-3P1162V	1046388
	Cable, 4-wire, 5 m <sup>2)</sup>		WTB4S-3P1262H	1117988
			WTB4S-3P1262V	1100117
	Male connector M12, 4-pin <sup>1)</sup>		WTB4SC-3P2462VB02	1134582
	Male connector M12, 4-pin <sup>3)</sup>		WTB4S-3P2462V	1054675
	Male connector M8, 4-pin <sup>1)</sup>		WTB4S-3P2262V	1046383
			WTB4S-3P5262H	1099888
			WTB4SC-3P2262VB01	1115584

<sup>1)</sup> Max. tightening torque: 0.6 Nm.

<sup>2)</sup> Do not bend below 0 °C.

<sup>3)</sup> Max. tightening torque: 0.7 Nm.

- **Sensing range max.:** 100 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Dark switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Cable with connector M8, 3-pin	Rectangular	WTB4S-3F3160S12	1062834

- **Sensing range max.:** 4 mm ... 280 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching output:** PNP
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Connection type	Type	Part no.
Dark switching	Male connector M8, 4-pin <sup>1)</sup>	WTB4S-3F2234VS08	1053075
Light switching	Cable with M8 male connector, 4-pin <sup>2)</sup>	WTB4S-3P3234S04	1050600
	Cable with M8 male connector, 4-pin <sup>1) 2)</sup>	WTB4S-3P3204HS01	1048532
	Male connector M8, 4-pin <sup>1)</sup>	WTB4S-3P2204VS02	1047652
		WTB4S-3P2205VS01	1046214
Light/dark switching	Cable with M8 male connector, 4-pin	WTB4S-3P2234VS05	1050833
		WTB4S-3P5204HS02	1054865
	Male connector M12, 4-pin <sup>3)</sup>	WTB4SC-3P3232S10	1079436
		WTB4S-3P2402VS09	1054706

<sup>1)</sup> Max. tightening torque: 0.6 Nm.

<sup>2)</sup> Do not bend below 0 °C.

<sup>3)</sup> Max. tightening torque: 0.7 Nm.

- **Sensing range max.:** 8 mm ... 120 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Male connector M8, 4-pin	Rectangular	WTB4SC-3P2232B02	1088195

- **Sensing range max.:** 4 mm ... 100 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** PNP
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with M8 male connector, 4-pin <sup>1)</sup>	WTB4S-3P3231S09	1063276
Male connector M8, 4-pin	WTB4S-3P2264S03	1046255

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 3 mm ... 280 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Cable with M12 male connector, 4-pin <sup>1)</sup>	Rectangular	WTB4S-3P3432S05	1051765

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 3 mm ... 120 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Cable with M8 male connector, 4-pin <sup>1)</sup>	Rectangular	WTB4S-3P3260S02	1044275

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 30 mm ... 100 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light switching
- **Switching output:** NPN

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Cable, 4-wire, 2.5 m <sup>1)</sup>	Rectangular	WTB4S-3N1061S14	1095761

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 3 mm ... 100 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Foreground suppression
- **Switching mode:** Light/dark switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Cable with M8 male connector, 4-pin <sup>1)</sup>	Rectangular	WTF4S-3P3231S08	1061140

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 0 m ... 4 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** Without reflector minimum distance (autocollimation/coaxial optics)
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Dark switching	NPN	Cable, 3-wire, 2 m <sup>1)</sup>	WL4S-3E1330	1042072
			WL4S-3E1330V	1046420
		Connector M8, 3-pin	WL4S-3E2130	1042071
		Connector M8, 3-pin <sup>2)</sup>	WL4S-3E2130V	1045097
	PNP	Cable with M12 male connector, 4-pin <sup>1)</sup>	WL4S-3F3430S01	1053409
			Cable with connector M8, 3-pin <sup>1)</sup>	WL4S-3F3130
			WL4S-3F3130S04	1056053
		Cable with connector M8, 3-pin <sup>1) 2)</sup>	WL4S-3F3130V	1046416
		Cable, 3-wire, 2 m <sup>1)</sup>	WL4S-3F1330V	1046417
		Connector M8, 3-pin	WL4S-3F2130	1042065
Light switching	NPN	Cable, 3-wire, 2 m <sup>1)</sup>	WL4S-3N1330	1042073
			WLG4S-3N1332S12	1129078
	PNP	Cable with connector M8, 3-pin <sup>1)</sup>	WL4S-3P3130	1042070
			Cable with connector M8, 3-pin <sup>1) 2)</sup>	WL4S-3P3130V
		Cable, 3-wire, 2 m <sup>1)</sup>	WL4S-3P1330V	1048044
		Connector M8, 3-pin	WL4S-3P2130	1042069
		Connector M8, 3-pin <sup>2)</sup>	WL4S-3P2130V	1046413

<sup>1)</sup> Do not bend below 0 °C.

<sup>2)</sup> Max. tightening torque: 0.6 Nm.

<sup>3)</sup> Max. tightening torque: 0.7 Nm.

Switching mode	Switching output	Connection type	Type	Part no.
Light/dark switching	NPN	Cable, 4-wire, 2 m <sup>1)</sup>	WL4S-3N1130H	1048116
			WL4S-3N1130V	1046418
	PNP	Male connector M12, 4-pin <sup>3)</sup>	WL4S-3N2430V	1054712
			WL4S-3P3430V	1046415
			WL4S-3P3230	1073200
			WL4S-3P3230H	1048115
			WL4S-3P2430V	1054707
			WL4S-3P2230	1042066
			WL4S-3P2230S02	1054695
			WL4S-3P2230V	1045095
			WL4S-3P5230H	1057052

<sup>1)</sup> Do not bend below 0 °C.

<sup>2)</sup> Max. tightening torque: 0.6 Nm.

<sup>3)</sup> Max. tightening torque: 0.7 Nm.

- **Sensing range max.:** 0 m ... 5 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** Without reflector minimum distance (autocollimation/coaxial optics)
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.	
Dark switching	NPN	Cable with connector M8, 3-pin <sup>1)</sup>	WL4S-3E3132	1074981	
			WL4S-3E1332	1042081	
		Cable, 3-wire, 2 m <sup>1)</sup>	WL4S-3E1332V	1046437	
			Cable, 4-wire, 2 m <sup>1)</sup>	WL4S-3W1132	1042083
				WLG4S-3E1134H	1048124
				WLG4S-3E1134V	1048027
			WLG4S-3E1135V	1046438	
		Connector M8, 3-pin	WL4S-3E2132	1042080	

<sup>1)</sup> Do not bend below 0 °C.

<sup>2)</sup> Max. tightening torque: 0.6 Nm.

<sup>3)</sup> Max. tightening torque: 0.7 Nm.

Switching mode	Switching output	Connection type	Type	Part no.
	PNP	Connector M8, 3-pin <sup>2)</sup>	WL4S-3E2132V	1046435
		Cable with M12 male connector, 4-pin <sup>1) 3)</sup>	WLG4S-3F3434V	1048024
			WLG4S-3F3435V	1062552
		Cable with M8 male connector, 4-pin <sup>1) 2)</sup>	WLG4S-3F3234H	1048121
			WLG4S-3P3232HS03	1053364
			WLG4S-3V3232H	1048122
		Cable with connector M8, 3-pin <sup>1)</sup>	WL4S-3F3132	1042075
		Cable with connector M8, 3-pin <sup>1) 2)</sup>	WL4S-3F3132V	1046429
		Cable, 3-wire, 2 m <sup>1)</sup>	WL4S-3F1332V	1046430
		Cable, 3-wire, 5 m <sup>1)</sup>	WL4S-3F1432V	1055380
		Cable, 4-wire, 2 m <sup>1)</sup>	WL4S-3V1132	1069132
		Connector M8, 3-pin <sup>2)</sup>	WL4S-3F2132V	1046428
		Male connector M12, 4-pin <sup>1) 3)</sup>	WLG4S-3F2434V	1054727
		Male connector M8, 4-pin	WL4S-3V2232	1042079
			WLG4SC-3P2232S12	1080804
		Male connector M8, 4-pin <sup>2)</sup>	WL4S-3V2232V	1046422
			WLG4S-3F2234V	1047653
			WLG4S-3F2234VS04	1050832
			WLG4S-3F2235V	1045098
			WLG4S-3V2232V	1046447
Light switching	NPN	Cable, 3-wire, 2 m <sup>1)</sup>	WL4S-3N1332	1042082
		Connector M8, 3-pin <sup>2)</sup>	WL4S-3N2132V	1046432
	PNP	Cable with M8 male connector, 4-pin	WLG4SC-3P3235HS05	1070621
		Cable with connector M8, 3-pin <sup>1)</sup>	WL4S-3P3132	1044802
		Cable with connector M8, 3-pin <sup>1) 2)</sup>	WL4S-3P3132V	1046425
		Cable, 3-wire, 2 m <sup>1)</sup>	WL4S-3P1332V	1046427
		Connector M8, 3-pin	WL4S-3P2132	1042077
		Connector M8, 3-pin <sup>2)</sup>	WL4S-3P2132V	1046424
		Male connector M8, 4-pin <sup>2)</sup>	WLG4S-3P2234V	1051456
			WLG4S-3P2234VS05	1058027
WLG4S-3P2235V	1069744			
		WLG4S-3P5234HS06	1102183	

<sup>1)</sup> Do not bend below 0 °C.

<sup>2)</sup> Max. tightening torque: 0.6 Nm.

<sup>3)</sup> Max. tightening torque: 0.7 Nm.



Switching mode	Switching output	Connection type	Type	Part no.
Light/dark switching	NPN	Cable, 4-wire, 2 m <sup>1)</sup>	WL4S-3N1132H	1048119
			WL4S-3N1132V	1046431
			WLG4S-3N1132V	1046450
		Male connector M12, 4-pin <sup>3)</sup>	WL4S-3N2432V	1054722
		Male connector M12, 4-pin <sup>1) 3)</sup>	WLG4S-3N2432V	1054728
	PNP	Cable with M12 male connector, 4-pin <sup>1) 3)</sup>	WL4S-3P3432V	1046426
			WLG4S-3P3432V	1046449
			WLG4SC-3P3432VA00	1097829
		Cable with M8 male connector, 4-pin	WLG4SC-3P3232A00	1131816
		Cable with M8 male connector, 4-pin <sup>1)</sup>	WLG4SC-3P3232B01	1070334
Light/dark switching	PNP	Cable with M8 male connector, 4-pin <sup>1) 2)</sup>	WL4S-3P3232H	1048117
			WLG4S-3P3232H	1048120
			WLG4S-3P3232HS02	1050665
			WLG4S-3P3232V	1046448
		Cable, 4-wire, 2 m <sup>1)</sup>	WLG4S-3P1132V	1055044
		Cable, 4-wire, 5 m <sup>1)</sup>	WL4S-3P1032HS01	1050684
			WL4S-3P1032HS02	1089545
			WLG4S-3P1232V	1088867
		Connector M8, 3-pin <sup>2)</sup>	WLG4S-3P5132HS04	1058974
		Male connector M12, 4-pin <sup>3)</sup>	WL4S-3P2432V	1054715

<sup>1)</sup> Do not bend below 0 °C.

<sup>2)</sup> Max. tightening torque: 0.6 Nm.

<sup>3)</sup> Max. tightening torque: 0.7 Nm.

Switching mode	Switching output	Connection type	Type	Part no.
		Male connector M12, 4-pin <sup>1) 3)</sup>	WLG4S-3P2432V	1054725
			WLG4SC-3P2432VA00	1090947
		Male connector M8, 4-pin	WL4S-3P2232	1042078
			WL4SC-3P2232A00	1065315
			WL4SC-3P2232A70	1067760
			WL4SC-3P2232A71	1067761
			WL4SC-3P2232A72	1088640
			WL4SC-3P2232A91	1067762
			WLG4SC-3P2232A00	1057177
			WLG4SC-3P2232A70	1067763
			WLG4SC-3P2232A71	1067765
			WLG4SC-3P2232A91	1067766
			Male connector M8, 4-pin <sup>2)</sup>	WL4S-3P2232V
		WLG4S-3P2232V		1046446
		WLG4S-3P2232VS03		1050831
		WLG4S-3P2232VS07		1051943
		WLG4S-3P2234VS06		1069434
		WLG4S-3P5232H		1057053
		WLG4SC-3P2232VA00		1097830
		WLG4SC-3P5232HA00	1090378	

<sup>1)</sup> Do not bend below 0 °C.

<sup>2)</sup> Max. tightening torque: 0.6 Nm.

<sup>3)</sup> Max. tightening torque: 0.7 Nm.

- **Sensing range max.:** 0 m ... 5 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Switching mode:** Light/dark switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Cable with M8 male connector, 4-pin <sup>1)</sup>	Rectangular	WL4SC-3P3232B02	1104554

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 0 m ... 5 m
- **Functional principle:** Through-beam photoelectric sensor
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.	
Dark switching	NPN	Cable with connector M8, 3-pin <sup>1)</sup>	WSE4S-3E3130H	1048131	
		Cable, 3-wire, 2 m <sup>1)</sup>	WSE4S-3E1330	1042093	
			WSE4S-3E1330H	1052867	
			WSE4S-3E1330H	1052868	
			WSE4S-3E1330V	1048130	
		Connector M8, 3-pin	WSE4S-3E2130	1052869	
		Connector M8, 3-pin <sup>2)</sup>	WSE4S-3E2130	1042092	
			WSE4S-3E2130V	1052876	
		PNP	Cable with M12 male connector, 4-pin <sup>1)</sup>	WSE4S-3F3430	1052877
			Cable with M12 male connector, 4-pin <sup>1) 3)</sup>	WSE4S-3F3430	1051883
	WSE4S-3F3430V			1052884	
	Cable with connector M8, 3-pin <sup>1)</sup>		WSE4S-3F3430V	1052885	
			WSE4SC-3P3430VA00	1097831	
	Cable with connector M8, 3-pin <sup>1) 2)</sup>		WSE4S-3F3130	1042089	
			WSE4S-3F3130H	1052881	
	Cable with connector M8, 3-pin <sup>1) 2)</sup>		WSE4S-3F3130H	1048128	
			WSE4S-3F3130V	1052882	
	Cable, 3-wire, 2 m <sup>1)</sup>		WSE4S-3F3130V	1052883	
		WSE4S-3F1330	1042090		
	Connector M8, 3-pin	WSE4S-3F1330V	1052879		
WSE4S-3F2130		1052880			
Connector M8, 3-pin <sup>2)</sup>	WSE4S-3F2130	1042088			
	WSE4S-3F2130V	1052890			
		WSE4S-3F2130V	1052891		

<sup>1)</sup> Do not bend below 0 °C.

<sup>2)</sup> Max. tightening torque: 0.6 Nm.

<sup>3)</sup> Max. tightening torque: 0.7 Nm.

Switching mode	Switching output	Connection type	Type	Part no.	
Light switching	NPN	Cable, 3-wire, 2 m <sup>1)</sup>	WSE4S-3N1330	1042094 1052872	
			WSE4S-3N1330H	1048129	
			WSE4S-3N1330V	1052874	
		Connector M8, 3-pin <sup>2)</sup>	WSE4S-3N2130V	1052878	
		PNP	Cable with M8 male connector, 4-pin <sup>1) 2)</sup>	WSE4S-3P3230V	1061108
				WSE4S-3P3130H	1048127
	Cable with connector M8, 3-pin <sup>1)</sup>		WSE4S-3P3130H	1052888	
			WSE4S-3P3130V	1052889	
	Cable, 3-wire, 2 m <sup>1)</sup>		WSE4S-3P1330H	1052886 1051980	
			WSE4S-3P1330V	1052887	
			WSE4S-3P1430V	1058184	
	Cable, 3-wire, 5 m <sup>1)</sup>		WSE4S-3P1430V	1058184	
	Cable, 4-wire, 10 m <sup>1)</sup>		WSE4S-3P1030VS02	1059404	
	Connector M8, 3-pin		WSE4S-3P2130	1042091 1052892	
			WSE4S-3P2130V	1052893	
	Male connector M8, 4-pin <sup>2)</sup>		WSE4S-3P2230V	1061815	
	Light/dark switching	NPN	Male connector M12, 4-pin	WSE4S-3N2430V	1054786
		PNP	Male connector M12, 4-pin <sup>3)</sup>	WSE4S-3P2430V	1054784
WSE4S-3K2236				1074138	
Male connector M8, 4-pin			WSE4S-3P2230	1067843	
			WSE4SC-3P2230A00	1067767	
			WSE4SC-3P2230A70	1067768	
			WSE4SC-3P2230A91	1067770	
			WSE4SC-3P2230S03	1078552	
Male connector M8, 4-pin <sup>1) 2)</sup>			WSE4S-3P5230H	1054896	

<sup>1)</sup> Do not bend below 0 °C.

<sup>2)</sup> Max. tightening torque: 0.6 Nm.

<sup>3)</sup> Max. tightening torque: 0.7 Nm.

- **Sensing range max.:** 0 m ... 2 m
- **Functional principle:** Through-beam photoelectric sensor
- **Switching mode:** Light/dark switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
PinPoint LED	Visible red light	Male connector M8, 4-pin	Rectangular	WSE4SC-3P2230S04	1079435

- **Sensing range max.:** 0 m ... 3 m
- **Functional principle:** Through-beam photoelectric sensor
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Connection type:** Cable, 3-wire, 5 m (Do not bend below 0 °C.)
- **Housing:** rectangular

Switching mode	Switching output	Type	Part no.
Dark switching	NPN	WSE4T-3E1430	1029648
	PNP	WSE4T-3F1430	1029647
Light switching	NPN	WSE4T-3N1430	1102467
	PNP	WSE4T-3P1430	1029646

- **Sensing range max.:** 0.01 m ... 1.6 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Dark switching	NPN	Cable, 3-wire, 2 m <sup>1)</sup>	WLG4-3E1382	1028138
		Cable, 4-wire, 2 m <sup>1)</sup>	WLG4-3E1184	1028140
	PNP	Cable with connector M8, 3-pin <sup>1)</sup>	WLG4-3F3182	1028135
		Connector M8, 3-pin	WLG4-3F2182	1028134
		Male connector M8, 4-pin	WLG4-3F2284	1028137
Light switching	NPN	Cable, 3-wire, 2 m <sup>1)</sup>	WLG4-3N1382	1040493
	PNP	Cable, 3-wire, 5 m <sup>1)</sup>	WLG4-3P1482	1029897
		Connector M8, 3-pin	WLG4-3P2182	1044179

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 0.01 m ... 4 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Switching output:** PNP
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Connection type	Type	Part no.
Dark switching	Cable with M8 male connector, 4-pin <sup>1)</sup>	WLG4-3F3234S05	1043538
Light switching	Connector M8, 3-pin	WLG4-3P2132S07	1060007

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 0.01 m ... 1.5 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Switching mode:** Dark switching
- **Switching output:** PNP
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Connection type	Type	Part no.
Cable with connector M8, 3-pin <sup>1)</sup>	WLG4-3F3182S06	1044190
Cable, 3-wire, 5 m <sup>1)</sup>	WLG4-3F1482S04	1042291

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 0.01 m ... 5 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** Without reflector minimum distance (autocollimation/coaxial optics)
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Dark switching	NPN	Cable with MOLEX-connector <sup>1)</sup>	WLG4S-3W3032S13	1091964
		Cable, 4-wire, 2 m <sup>1)</sup>	WLG4S-3E1134	1042085
			WLG4S-3W1132	1042086
	Cable with special connector, 3-wire <sup>1)</sup>	WLG4S-3E1334S03	1055060	
	PNP	Cable with M8 male connector, 4-pin <sup>1)</sup>	WLG4S-3F3234	1043840
		Cable with connector M12, 3-pin <sup>1)</sup>	WLG4S-3F3332	1059718
		Cable with connector M8, 3-pin <sup>1)</sup>	WLG4S-3F3132	1043838
		Cable, 4-wire, 2 m <sup>1)</sup>	WLG4S-3V1132	1055895
		Male connector M8, 4-pin	WLG4S-3F2234	1042084
	WLG4S-3V2232		1042087	

<sup>1)</sup> Do not bend below 0 °C.

Switching mode	Switching output	Connection type	Type	Part no.
Light switching	NPN	Cable with special connector <sup>1)</sup>	WLG4S-3N1332A01	1047821
		Cable, 3-wire, 2 m <sup>1)</sup>	WLG4S-3N1332	1046111
	PNP	Cable with M12 male connector, 4-pin <sup>1)</sup>	WLG4S-3P3434	1046819
		Cable with M8 male connector, 4-pin <sup>1)</sup>	WLG4S-3P3234	1054098
		Cable with connector M8, 3-pin <sup>1)</sup>	WLG4S-3P3132	1043839
		Male connector M8, 4-pin	WLG4S-3P2234	1052999
Light/dark switching	NPN	Cable with M12 male connector, 4-pin <sup>1)</sup>	WLG4S-3N3432	1052210
	PNP	Cable with M12 male connector, 4-pin <sup>1)</sup>	WLG4S-3K3432	1106887
			WLG4S-3P3432	1051097
		Cable with M8 male connector, 4-pin <sup>1)</sup>	WLG4S-3P3232	1052963
		Male connector M8, 4-pin	WLG4S-3K2232	1069998
	WLG4S-3P2232		1044186	

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 25 mm ... 300 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Light source:** laser
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Light switching	PNP	Cable with connector M8, 3-pin <sup>1)</sup>	WTB4SL-3P3161	1075216
		Male connector M8, 4-pin <sup>2)</sup>	WTB4SL-3P5264H	1103456
Light/dark switching	NPN	Cable with M8 male connector, 4-pin <sup>1)</sup>	WTB4SL-3N3261	1058241
		Cable, 4-wire, 2 m <sup>1)</sup>	WTB4SL-3N1161	1058242
			WTB4SL-3N1162V	1058257

<sup>1)</sup> Do not bend below 0 °C.

<sup>2)</sup> Max. tightening torque: 0.6 Nm.

<sup>3)</sup> Max. tightening torque: 0.7 Nm.

Switching mode	Switching output	Connection type	Type	Part no.
			WTB4SL-3N4162H	1058275
		Male connector M12, 4-pin	WTB4SL-3N2462V	1058254
		Male connector M8, 4-pin	WTB4SL-3N2261	1058240
		Male connector M8, 4-pin <sup>2)</sup>	WTB4SL-3N2262V	1058252
	PNP	Cable with M12 male connector, 4-pin <sup>1) 3)</sup>	WTB4SL-3P3462V	1058255
		Cable with M8 male connector, 4-pin <sup>1)</sup>	WTB4SL-3P3261	1058238
			WTB4SL-3P3262H	1096530
		Cable with M8 male connector, 4-pin <sup>1) 2)</sup>	WTB4SL-3P7262H	1058272
		Cable, 4-wire, 2 m <sup>1)</sup>	WTB4SL-3P1161	1058239
			WTB4SL-3P1162V	1058256
			WTB4SL-3P4162H	1058274
		Cable, 4-wire, 5 m <sup>1)</sup>	WTB4SL-3P4262H	1127818
		Male connector M12, 4-pin	WTB4SL-3P2462V	1058253
		Male connector M8, 4-pin	WTB4SL-3P2261	1058237
			WTB4SLC-3P2262A00	1080939
			WTB4SLC-3P2262A70	1080940
			WTB4SLC-3P2262A71	1080941
		Male connector M8, 4-pin <sup>2)</sup>	WTB4SL-3P2262V	1058251
			WTB4SL-3P2264VS01	1070085
			WTB4SL-3P5262H	1058271

<sup>1)</sup> Do not bend below 0 °C.

<sup>2)</sup> Max. tightening torque: 0.6 Nm.

<sup>3)</sup> Max. tightening torque: 0.7 Nm.



- **Sensing range max.:** 0 m ... 12 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** Without reflector minimum distance (autocollimation/coaxial optics)
- **Light source:** laser
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Dark switching	NPN	Cable, 4-wire, 2 m <sup>1)</sup>	WL4SL-3E1134	1061566
	PNP	Cable with M8 male connector, 4-pin <sup>1)</sup>	WL4SL-3F3234	1061564
		Male connector M8, 4-pin	WL4SL-3F2234	1061562
Light switching	NPN	Cable with connector M8, 3-pin <sup>1)</sup>	WL4SL-3N3132S03	1092001
Light/dark switching	NPN	Cable, 4-wire, 2 m <sup>1)</sup>	WL4SL-3N1132	1061565
	PNP	Cable with M12 male connector, 4-pin <sup>1)</sup>	WL4SL-3P3432	1147975
			WL4SL-3F3232	1106888
		Male connector M8, 4-pin	WL4SL-3P3232	1061563
			WL4SLC-3P3232A00	1144712
			WL4SL-3F2232	1076420
			WL4SL-3P2232	1061561
			WL4SLC-3P2232A00	1080945
			WL4SLC-3P2232A70	1080947
			WL4SLC-3P2232A71	1080949
			WL4SLC-3P2232A72	1098509

<sup>1)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 0 m ... 60 m
- **Functional principle:** Through-beam photoelectric sensor
- **Switching mode:** Light/dark switching
- **Light source:** laser
- **Type of light:** visible red light
- **Housing:** rectangular

Switching output	Connection type	Type	Part no.
NPN	Cable, 4-wire, 2 m <sup>1)</sup>	WSE4SL-3N1137	1058250
		WSE4SL-3N1137V	1058270

<sup>1)</sup> Do not bend below 0 °C.

<sup>2)</sup> Max. tightening torque: 0.7 Nm.

<sup>3)</sup> Max. tightening torque: 0.6 Nm.

Switching output	Connection type	Type	Part no.
PNP	Cable with M8 male connector, 4-pin	WSE4SLC-3P3236A00	1144713
	Cable with M8 male connector, 4-pin <sup>1)</sup>	WSE4SL-3P3237	1095976
	Cable, 4-wire, 2 m <sup>1)</sup>	WSE4SL-3P1137V	1115139
	Male connector M12, 4-pin <sup>2)</sup>	WSE4SL-3P2437V	1058269
	Male connector M8, 4-pin	WSE4SL-3P2237	1058249
		WSE4SLC-3P2236A00	1080957
		WSE4SLC-3P2236A70	1080959
		WSE4SLC-3P2236A71	1080961
	Male connector M8, 4-pin <sup>3)</sup>	WSE4SLC-3P2236B01	1147214
		WSE4SL-3P2237V	1058267
	WSE4SL-3P5237H	1092532	

<sup>1)</sup> Do not bend below 0 °C.

<sup>2)</sup> Max. tightening torque: 0.7 Nm.

<sup>3)</sup> Max. tightening torque: 0.6 Nm.

- **Sensing range max.:** 0 m ... 4.5 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** Without reflector minimum distance (autocollimation/coaxial optics)
- **Switching mode:** Light/dark switching
- **Light source:** laser
- **Type of light:** visible red light
- **Housing:** rectangular

Switching output	Connection type	Type	Part no.
NPN	Cable, 4-wire, 2 m <sup>1)</sup>	WL4SLG-3N1132	1058247
		WL4SLG-3N1162P01	1101033
PNP	Cable with M8 male connector, 4-pin <sup>1) 2)</sup>	WL4SLG-3P3232H	1068109
	Male connector M12, 4-pin <sup>3)</sup>	WL4SLG-3K2432VS01	1065697
	Male connector M8, 4-pin	WL4SLG-3F2232	1132822
		WL4SLG-3P2232	1058243
	Male connector M8, 4-pin <sup>2)</sup>	WL4SLG-3P5234HS03	1110468

<sup>1)</sup> Do not bend below 0 °C.

<sup>2)</sup> Max. tightening torque: 0.6 Nm.

<sup>3)</sup> Max. tightening torque: 0.7 Nm.

- **Sensing range max.:** 0 m ... 3.5 m
- **Functional principle:** Photoelectric retro-reflective sensor
- **Functional principle detail:** Without reflector minimum distance (autocollimation/coaxial optics)
- **Light source:** laser
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Switching output	Connection type	Type	Part no.
Dark switching	PNP	Cable with M8 male connector, 4-pin <sup>1) 2)</sup>	WL4SLG-3F7254H	1076066
		Male connector M8, 4-pin <sup>1)</sup>	WL4SLG-3F2254V	1076059
			WL4SLG-3F5254H	1076064
Light switching	PNP	Male connector M8, 4-pin <sup>1)</sup>	WL4SLG-3P2254V	1076061
			WL4SLG-3P5254H	1109333
Light/dark switching	NPN	Cable, 4-wire, 2 m	WL4SLG-3N1152	1076053
	PNP	Cable with M12 male connector, 4-pin <sup>1)</sup>	WL4SLG-3P3452V	1076057
		Cable with M8 male connector, 4-pin	WL4SLGC-3P3052B01	1119068
		Male connector M8, 4-pin	WL4SLG-3P2252	1076046
			WL4SLGC-3P2252A00	1080951
			WL4SLGC-3P2252A70	1080953
			WL4SLGC-3P2252A71	1080955
		Male connector M8, 4-pin <sup>1)</sup>	WL4SLG-3P5252H	1076062

<sup>1)</sup> Max. tightening torque: 0.6 Nm.

<sup>2)</sup> Do not bend below 0 °C.

- **Sensing range max.:** 20 mm ... 200 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Foreground suppression
- **Switching output:** PNP
- **Light source:** PinPoint LED
- **Type of light:** visible red light
- **Housing:** rectangular

Switching mode	Connection type	Type	Part no.
Light switching	Cable with M8 male connector, 4-pin <sup>1)</sup>	WTF4S-3P3264H	1048109
	Male connector M8, 4-pin <sup>2)</sup>	WTF4S-3P2205VS02	1046742
		WTF4S-3P2265V	1045094
Light/dark switching	Cable, 4-wire, 5 m <sup>1)</sup>	WTF4S-3P3232HS03	1050933
	Male connector M12, 4-pin <sup>2)</sup>	WTF4S-3P2462V	1072453
	Male connector M8, 4-pin <sup>2)</sup>	WTF4S-3P2262V	1046410

<sup>1)</sup> Do not bend below 0 °C.

<sup>2)</sup> Max. tightening torque: 0.6 Nm.

- **Sensing range max.:** 40 mm ... 200 mm
- **Functional principle:** Photoelectric proximity sensor
- **Functional principle detail:** Background suppression
- **Switching mode:** Light/dark switching
- **Switching output:** PNP

Light source	Type of light	Connection type	Housing	Type	Part no.
Laser	Visible red light	Male connector M8, 4-pin <sup>1)</sup>	Rectangular	WTB4SL-3P2264VS02	1095525

<sup>1)</sup> Max. tightening torque: 0.6 Nm.

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)