


LR205-X-2RSR

Galet de roulement

Yoke type track rollers LR2...-2RS/2RSR, single row self-retaining ball bearings with particularly thick-walled outer ring, ball and cage assembly and an inner ring, axial guidance of outer ring is provided by the balls, lip seal on both sides, with axial sealing action/with radial sealing action

Information technique



Votre alternative produit actuelle

joint	2RSR	Joint frottant des deux côtés
profile bague extérieure	X	Diamètre extérieur cylindrique
dispositif de lubrification	Without	Without

dimensions principale & données de performance

D	62 mm	Diamètre extérieur
d	25 mm	Alésage
C	15 mm	Hauteur
C _{r w}	13.300 N	Charge dyn. de base, radiale
C _{0r w}	7.300 N	Charge stat. de base, radiale
C _{ur w}	370 N	Limite à la fatigue, radiale
n _{D G}	7.000 1/min	Vitesse pour une lubrification à la graisse
≈m	0,23 kg	Poids

Dimensions

d ₂	33,5 mm	Diamètre rondèle de butée
r _{min}	1 mm	Dimension minimum de chanfrein
R	500 mm	Rayon bague extérieure profile externe



Caractéristiques



Effort radial



Effort axial uni directionnel



Effort axial dans les 2 directions



Lubrification à vie, sans entretien



Lubrification à la graisse



Etanche des 2 côtés