

2104 : Fast feed 6-65 mm plastic pipe cutter

Description

Max thickness: 8 mm.

For pipes in plastic, composite materials and multilayer.


Notched telescopic slide and release button for fast forward and reverse wheel adjustment.

Removable rotary hole deburrer with interchangeable blade.

Cutting wheel with 4 rollers for increased cutting precision.

Soft Touch® anti-slip knob.

Colour-coded end cap according to the material to be cut.



References

Sku	A mm	A " OD	L mm	H mm	E maxi mm	kg
210497	6 - 65	1/4 - 2.9/16	230	100	8	0,820

