

KERN DBS-A01.

KERN

Temperature calibration set consists of measuring sensor and display device



Environmental conditions

Storage temperature [Min]	-10 °C
Storage temperature [Max]	50 °C

Approval

CE mark	✓
---------	---

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	290×190×50 mm
Shipping method	Parcel service
Net weight approx.	0,25 kg
Gross weight approx.	0,25 kg
Shipping weight	0,6 kg
Shipping volume weight	0,6 kg

Product information

GTIN/EAN number	4045761188013
Trade number	90160090
REACH classification	no prohibited substances

Pictograms

STANDARD



Category

Brand	KERN
Product category	Balance
Product group	Temperature calibration set

Measuring System

Units	°C °F
Temperature [Min] (°C)	-50 °C
Temperature [Max] (°C)	300 °C
Readability temperature [d] (°C)	0,1 °C

Construction

Dimension (W×D×H)	115×75×18 mm
Material	plastic + metal
Material housing	ABS plastic
Cable length	0,9 m

Power Supply

Supplied power supply	Battery
Battery / accumulator type	Alkali(-Manganese)
Battery	2×1.5 V AAA
Battery connection	Pad + Spring
Battery operating time	400 h
Battery capacity	1.200 mAh
Battery voltage	3 V
Battery – Number of cells	2
Battery – Individual weight	22,6 g
Battery – Total weight	45,2 g
Battery capacity (Wh)	1,8 Wh