

# PROGRAMMATEUR UNIVERSEL DE PRODUCTION, 4 SUPPORTS ZIF48, PORT USB2.0 POUR EPROMs, EEPROMs, NANDs, FLASHs, PLDs, MICROCONTROLEURS

Supporte plus de 17.000 composants



## PROMAX-4G



### Présentation:

Le programmeur ProMax-4G offre la possibilité de programmer simultanément et indépendamment 4 composants. Livré avec 4 supports ZIF48 universels, il permet de programmer plus de 17.000 références de composants différents parmi les PROMs, EPROMs, EEPROMs, FLASHs, NAND, GAL, PEEL, EPLD, FPGA, PAL, GAL, EPLD et les Microcontrôleurs. Il gère également les composants basse tension en 1,8V / 2,0V / 2,5V / 2,7V / 3,3V / 5,0V. Le programme source peut être chargé à partir de la connexion USB, ou bien à partir d'un master à placer sur le premier support du programmeur. Le lancement de la programmation se fait directement à l'aide des touches start sur le programmeur. La vitesse de programmation est extrêmement rapide puisque la vitesse de transfert peut atteindre 2,5Mb/seconde. Les mises à jour sont disponibles gratuitement pour l'ajout de nouveaux composants. La nouvelle génération ProMax-4G offre la double fonction de programmeur universel de développement et de programmeur universel de production grâce à sa technologie multi support. Accepte les fichiers au format Binaire, ASCII, Intel, MotorolaS, Tektronik, JEDEC, POF. Fonctionne avec le logiciel MaxLoader pour Windows98/2000/XP/VISTA/Win7/Win8/Win10 (32/64bits).

### Caractéristiques:

Accepte tous les formats standards (POF et JEDEC, INTEL (Extended) HEX, Motorola S-Records, Tekhex, Straight Hex, Hex-Space, Extended TekHex. Gère les fichiers au format 16 bits et 32 bits.  
Teste les composants logiques TTL/CMOS ainsi que les RAM Dynamic/Static.  
Identifie automatiquement les fabricants des E(E)PROMs, auto identifie les composants logiques TTL/CMOS.  
Effectue les tests d'insertion du composant et les broches défectueuses.  
Gère les composants low-voltage jusqu'à 1,8V.  
Fonction de programmation en mode production à l'aide d'une touche "Start" sur le coffret du programmeur.  
Fonctions d'utilisation : Lecture, Test de virginité, Programme, Vérifie, CheckSum, Comparaison, Bit de sécurité, Options.  
Adaptateurs universels DIP, PLCC, QFP, TSOP, PSOP, SOIC, SSOP, SDIP, etc...  
Supporte Windows XP / VISTA / Windows 7 / Windows8 / Windows10 (32bits et 64bits).

### Specifications électriques et matériels:

Dimensions produit : 435 x 350 x 170mm.  
Poids : 7460g.  
Alimentation : prise CEE AC 100V à 240V, 50Hz/60Hz.  
Interface : port USB2.0  
Support : 4xZIF48, (supporte les composants de 8 broches à 48 broches)



### Inclus:

Un programmeur, (boîtier métallique).  
Un cordon d'alimentation CEE, (110V à 240Vac).  
Un câble USB de type A-B.  
Logiciel sur CD.  
Un mode d'emploi en Français et en Anglais.

Informations produits : [www.seeit.fr](http://www.seeit.fr)

↓ Liste des composants programmés ↓



**LISTE DES COMPOSANTS PROMAX-4G**

(Programmateur universel de production, 4 supports ZIF48)

Appuyer sur "CTRL + F" pour rechercher un composant

Programmateur universel ProMax-4G

Nombre de composants : 17349

Version : 5.0r

Fabricants	Composants	Boitiers	Adaptateurs
ALLIANCE	AS29F040	DIP 32	
ALLIANCE	AS29F040	TSOP 32	PA32TS20/PA32TS32D-20
ALLIANCE	AS29F040	PLCC 32	PA32PL32D
ALLIANCE	AS29F010	DIP 32	
ALLIANCE	AS29F010	TSOP 32	PA32TS20/PA32TS32D-20
ALLIANCE	AS29F010	PLCC 32	PA32PL32D
ALLIANCE	AS29F200T	SOP 44	PA44SO44D
ALLIANCE	AS29F200T	TSOP 48	PA48TS48D
ALLIANCE	AS29F200B	SOP 44	PA44SO44D
ALLIANCE	AS29F200B	TSOP 48	PA48TS48D
ALLIANCE	AS29LV400B	SOP 44	PA44SO44D
ALLIANCE	AS29LV400B	TSOP 48	PA48TS48D
ALLIANCE	AS29LV400T	SOP 44	PA44SO44D
ALLIANCE	AS29LV400T	TSOP 48	PA48TS48D
ALLIANCE	AS29LV800B	SOP 44	PA44SO44D
ALLIANCE	AS29LV800B	TSOP 48	PA48TS48D
ALLIANCE	AS29LV800T	SOP 44	PA44SO44D
ALLIANCE	AS29LV800T	TSOP 48	PA48TS48D
ASAHI KASEI(AKM)	AK93C85AM	SSOP 8	PA8TSS-OT
ASAHI KASEI(AKM)	AK93C95AF	SOIC 8	PA16SO16D-EO-150
ASAHI KASEI(AKM)	AK93C10AF	SOIC 8	PA16SO16D-EO-150
ASAHI KASEI(AKM)	AK6002A	SOIC 8	PA8SO8D-EO-150
ASAHI KASEI(AKM)	AK6002A	TSSOP 8	PA8TSS8D
ASAHI KASEI(AKM)	AK6002A	TSSOP 8	PA24TSS24D
ASAHI KASEI(AKM)	AK6003A	TSSOP 8	PA8TSS8D
ASAHI KASEI(AKM)	AK6003A	TSSOP 8	PA24TSS24D
ASAHI KASEI(AKM)	AK6004A	SOIC 8	PA8SO8D-EO-150
ASAHI KASEI(AKM)	AK6004A	SSOP 8	PA8SS8D
ASAHI KASEI(AKM)	AK6008A	SOIC 8	PA8SO8D-EO-150
ASAHI KASEI(AKM)	AK6010A	SOIC 8	PA8SO8D-EO-150
ASAHI KASEI(AKM)	AK6012A	SOIC 8	PA8SO8D-EO-150
ALTERA	EPC1	DIP 8	
ALTERA	EPC1	PLCC 20	PA20LC20D[Dead Bug]
ALTERA	EPC2	PLCC 20	PA20LC20D[Dead Bug]
ALTERA	EPC2	TQFP 32	PA32TQ32D
ALTERA	EPC1064	DIP 8	
ALTERA	EPC1213	DIP 8	
ALTERA	EPC1441	DIP 8	
ALTERA	EPC1441	PLCC 20	PA20LC20D[Dead Bug]
ALTERA	EPC1441	TQFP 32	PA32TQ32D-YC
ALTERA	EPCS1SI8	SOIC 8	PA16SO16D-EO-150
ALTERA	EPCS1SI8N	SOIC 8	PA16SO16D-EO-150
ALTERA	EPCS4SI8	SOIC 8	PA16SO16D-EO-150
ALTERA	EPCS4SI8N	SOIC 8	PA16SO16D-EO-150
ALTERA	EPCS16SI8N	SOIC 8	PA8SO8D-EO-150
ALTERA	EPCS16SI16N	SOIC 16	PA28SO28D-EO-300
ALTERA	EPCS64SI16N	SOIC 16	PA28SO28D-EO-300
ZEMPRO ELECTRONIC	TS25L010A	SOIC 8	PA8SO8D-EO-150
ZEMPRO ELECTRONIC	TS25L020A	SOIC 8	PA8SO8D-EO-150
ZEMPRO ELECTRONIC	TS25L512A	SOIC 8	PA8SO8D-EO-150
ZEMPRO ELECTRONIC	TS25L16AP	SOIC 8	PA8SO8D-210
ZEMPRO ELECTRONIC	ZP25L16P	SOIC 8	PA8SO8D-210
AMD	Am2716	DIP 24	
AMD	Am2716B	DIP 24	
AMD	Am2732	DIP 24	
AMD	Am2732A	DIP 24	
AMD	Am2732B	DIP 24	
AMD	Am2764	DIP 28	
AMD	Am2764	PLCC 32	PA32PL28D-YA
AMD	Am2764A	DIP 28	
AMD	Am2764A	PLCC 32	PA32PL28D-YA
AMD	Am27128	DIP 28	
AMD	Am27128	PLCC 32	PA32PL28D-YA

AMD	Am27128A	DIP 28	
AMD	Am27128A	PLCC 32	PA32PL28D-YA
AMD	Am27256	DIP 28	
AMD	Am27256	PLCC 32	PA32PL28D-YA
AMD	Am27512	DIP 28	
AMD	Am27512	PLCC 32	PA32PL28D-YA
AMD	Am27C64	DIP 28	
AMD	Am27C64	PLCC 32	PA32PL28D-YA
AMD	Am27C128	DIP 28	
AMD	Am27C128	PLCC 32	PA32PL28D-YA
AMD	Am27C256	DIP 28	
AMD	Am27C256	PLCC 32	PA32PL28D-YA
AMD	Am27C512	DIP 28	
AMD	Am27C512	PLCC 32	PA32PL28D-YA
AMD	Am27C010	DIP 32	
AMD	Am27C010	PLCC 32	PA32PL32D
AMD	Am27C020	DIP 32	
AMD	Am27C020	PLCC 32	PA32PL32D
AMD	Am27C040	DIP 32	
AMD	Am27C040	PLCC 32	PA32PL32D
AMD	Am27H256	DIP 28	
AMD	Am27H256	PLCC 32	PA32PL28D-YA
AMD	Am27H010	DIP 32	
AMD	Am27H010	PLCC 32	PA32PL32D
AMD	Am27HB010	DIP 32	
AMD	Am27HB010	PLCC 32	PA32PL32D
AMD	Am27LV010	PLCC 32	PA32PL32D
AMD	Am27LV010	TSOP 32	PA32TS20/PA32TS32D-20
AMD	Am27LV010B	DIP 32	
AMD	Am27LV010B	PLCC 32	PA32PL32D
AMD	Am27LV010B	TSOP 32	PA32TS20/PA32TS32D-20
AMD	Am27LV020	DIP 32	
AMD	Am27LV020	PLCC 32	PA32PL32D
AMD	Am27LV020	TSOP 32	PA32TS20/PA32TS32D-20
AMD	Am27LV020B	DIP 32	
AMD	Am27LV020B	PLCC 32	PA32PL32D
AMD	Am27LV020B	TSOP 32	PA32TS20/PA32TS32D-20
AMD	Am27C1024	DIP 40	
AMD	Am27C1024	PLCC 44	PA44-48U
AMD	Am27C2048	DIP 40	
AMD	Am27C2048	PLCC 44	PA44-48U
AMD	Am27C4096	DIP 40	
AMD	Am27C4096	PLCC 44	PA44-48U
AMD	Am27C400	DIP 40	
AMD	Am27C800	DIP 42	
AMD	Am27C800	PLCC 44	PA44-48U
AMD	Am2817A	DIP 28	
AMD	Am2864A	DIP 28	
AMD	Am2864AE	DIP 28	
AMD	Am2864B	DIP 28	
AMD	Am2864BE	DIP 28	
AMD	Am28F256	DIP 32	
AMD	Am28F256	PLCC 32	PA32PL32D
AMD	Am28F256	TSOP 32	PA32TS20/PA32TS32D-20
AMD	Am28F256A	DIP 32	
AMD	Am28F256A	TSOP 32	PA32TS20/PA32TS32D-20
AMD	Am28F256A	PLCC 32	PA32PL32D
AMD	Am28F512	DIP 32	
AMD	Am28F512	PLCC 32	PA32PL32D
AMD	Am28F512	TSOP 32	PA32TS20/PA32TS32D-20
AMD	Am28F512A	DIP 32	
AMD	Am28F512A	TSOP 32	PA32TS20/PA32TS32D-20
AMD	Am28F512A	PLCC 32	PA32PL32D
AMD	Am28F010	DIP 32	
AMD	Am28F010	PLCC 32	PA32PL32D
AMD	Am28F010	TSOP 32	PA32TS20/PA32TS32D-20
AMD	Am28F010A	DIP 32	
AMD	Am28F010A	TSOP 32	PA32TS20/PA32TS32D-20
AMD	Am28F010A	PLCC 32	PA32PL32D
AMD	Am28F020	DIP 32	
AMD	Am28F020	PLCC 32	PA32PL32D
AMD	Am28F020	TSOP 32	PA32TS20/PA32TS32D-20
AMD	Am28F020A	DIP 32	

AMD	Am28F020A	TSOP 32	PA32TS20/PA32TS32D-20
AMD	Am28F020A	PLCC 32	PA32PL32D
AMD	Am29BL802CB	SSOP 56	PA56SS48DA
AMD	Am29DL400BB	SOP 44	PA44SO44D
AMD	Am29DL400BB	TSOP 48	PA48TS48D
AMD	Am29DL400BT	SOP 44	PA44SO44D
AMD	Am29DL400BT	TSOP 48	PA48TS48D
AMD	Am29DL800BB	SOP 44	PA44SO44D
AMD	Am29DL800BB	TSOP 48	PA48TS48D
AMD	Am29DL800BT	SOP 44	PA44SO44D
AMD	Am29DL800BT	TSOP 48	PA48TS48D
AMD	Am29DL162CB	TSOP 48	PA48TS48D
AMD	Am29DL162CT	TSOP 48	PA48TS48D
AMD	Am29DL162DB	BGA 48	HA48BGA48DAO
AMD	Am29DL162DT	BGA 48	HA48BGA48DAO
AMD	Am29DL163CB	TSOP 48	PA48TS48D
AMD	Am29DL163CT	TSOP 48	PA48TS48D
AMD	Am29DL164DB	TSOP 48	PA48TS48D
AMD	Am29DL164DT	TSOP 48	PA48TS48D
AMD	Am29DL316CB	TSOP 40	PA40TS40D
AMD	Am29DL316CT	TSOP 40	PA40TS40D
AMD	Am29DL322CB	TSOP 48	PA48TS48D
AMD	Am29DL322CT	TSOP 48	PA48TS48D
AMD	Am29DL322DB	TSOP 48	PA48TS48D
AMD	Am29DL322DT	TSOP 48	PA48TS48D
AMD	Am29DL323CB	TSOP 48	PA48TS48D
AMD	Am29DL323CT	TSOP 48	PA48TS48D
AMD	Am29DL323DB	TSOP 48	PA48TS48D
AMD	Am29DL323DT	TSOP 48	PA48TS48D
AMD	Am29DL323GB	TSOP 48	PA48TS48D
AMD	Am29DL323GT	TSOP 48	PA48TS48D
AMD	Am29DL324DB	TSOP 48	PA48TS48D
AMD	Am29DL324DT	TSOP 48	PA48TS48D
AMD	Am29DL640D	TSOP 48	PA48TS48D
AMD	Am29DL640G	TSOP 48	PA48TS48D
AMD	Am29F002T	DIP 32	
AMD	Am29F002T	PLCC 32	PA32PL32D
AMD	Am29F002T	TSOP 32	PA32TS32D
AMD	Am29F002B	DIP 32	
AMD	Am29F002B	PLCC 32	PA32PL32D
AMD	Am29F002B	TSOP 32	PA32TS32D
AMD	Am29F002BT	DIP 32	
AMD	Am29F002BT	PLCC 32	PA32PL32D
AMD	Am29F002BT	TSOP 32	PA32TS32D
AMD	Am29F002BB	DIP 32	
AMD	Am29F002BB	PLCC 32	PA32PL32D
AMD	Am29F002BB	TSOP 32	PA32TS32D
AMD	Am29F002NT	DIP 32	
AMD	Am29F002NT	PLCC 32	PA32PL32D
AMD	Am29F002NT	TSOP 32	PA32TS32D
AMD	Am29F002NB	DIP 32	
AMD	Am29F002NB	PLCC 32	PA32PL32D
AMD	Am29F002NB	TSOP 32	PA32TS32D
AMD	Am29F002NBT	DIP 32	
AMD	Am29F002NBT	PLCC 32	PA32PL32D
AMD	Am29F002NBT	TSOP 32	PA32TS32D
AMD	Am29F002NBB	DIP 32	
AMD	Am29F002NBB	PLCC 32	PA32PL32D
AMD	Am29F002NBB	TSOP 32	PA32TS32D
AMD	Am29F004BB	DIP 32	
AMD	Am29F004BB	PLCC 32	PA32PL32D
AMD	Am29F004BB	TSOP 32	PA32TS32D
AMD	Am29F004BT	DIP 32	
AMD	Am29F004BT	PLCC 32	PA32PL32D
AMD	Am29F004BT	TSOP 32	PA32TS32D
AMD	Am29F010	DIP 32	
AMD	Am29F010	PLCC 32	PA32PL32D
AMD	Am29F010	TSOP 32	PA32TS32D
AMD	Am29F010A	DIP 32	
AMD	Am29F010A	PLCC 32	PA32PL32D
AMD	Am29F010A	TSOP 32	PA32TS32D
AMD	Am29F010B	DIP 32	
AMD	Am29F010B	PLCC 32	PA32PL32D

AMD	Am29F010B	TSOP 32	PA32TS32D
AMD	Am29F040	DIP 32	
AMD	Am29F040	PLCC 32	PA32PL32D
AMD	Am29F040	TSOP 32	PA32TS32D
AMD	Am29F040B	DIP 32	
AMD	Am29F040B	PLCC 32	PA32PL32D
AMD	Am29F040B	TSOP 32	PA32TS32D
AMD	Am29F080	SOP 44	PA44SO44D
AMD	Am29F080	TSOP 40	PA40TS40D
AMD	Am29F080B	SOP 44	PA44SO44D
AMD	Am29F080B	TSOP 40	PA40TS40D
AMD	Am29F016	TSOP 48	PA48TS48D
AMD	Am29F016	SOP 44	PA44SO44D
AMD	Am29F016B	TSOP 48	PA48TS48D
AMD	Am29F016B	TSOP 40	PA40TS40D
AMD	Am29F016B	SOP 44	PA44SO44D
AMD	Am29F016D	TSOP 48	PA48TS48D
AMD	Am29F016D	TSOP 40	PA40TS40D
AMD	Am29F016D	SOP 44	PA44SO44D
AMD	Am29F017B	TSOP 40	PA40TS40D
AMD	Am29F017B	TSOP 48	PA48TS48D
AMD	Am29F017D	TSOP 40	PA40TS40D
AMD	Am29F017D	TSOP 48	PA48TS48D
AMD	Am29F032B	TSOP 40	PA40TS40D
AMD	Am29F032B	DIP 40	R.F.53432101
AMD	Am29F032B	SOP 44	PA44SO44D
AMD	Am29F100B	SOP 44	PA44SO44D
AMD	Am29F100B	TSOP 48	PA48TS48D
AMD	Am29F100T	SOP 44	PA44SO44D
AMD	Am29F100T	TSOP 48	PA48TS48D
AMD	Am29F200B	SOP 44	PA44SO44D
AMD	Am29F200B	TSOP 48	PA48TS48D
AMD	Am29F200T	SOP 44	PA44SO44D
AMD	Am29F200T	TSOP 48	PA48TS48D
AMD	Am29F200AB	SOP 44	PA44SO44D
AMD	Am29F200AB	TSOP 48	PA48TS48D
AMD	Am29F200AT	SOP 44	PA44SO44D
AMD	Am29F200AT	TSOP 48	PA48TS48D
AMD	Am29F200BB	SOP 44	PA44SO44D
AMD	Am29F200BB	TSOP 48	PA48TS48D
AMD	Am29F200BT	SOP 44	PA44SO44D
AMD	Am29F200BT	TSOP 48	PA48TS48D
AMD	Am29F400B	SOP 44	PA44SO44D
AMD	Am29F400B	TSOP 48	PA48TS48D
AMD	Am29F400T	SOP 44	PA44SO44D
AMD	Am29F400T	TSOP 48	PA48TS48D
AMD	Am29F400AB	SOP 44	PA44SO44D
AMD	Am29F400AB	TSOP 48	PA48TS48D
AMD	Am29F400AT	SOP 44	PA44SO44D
AMD	Am29F400AT	TSOP 48	PA48TS48D
AMD	Am29F400BB	SOP 44	PA44SO44D
AMD	Am29F400BB	TSOP 48	PA48TS48D
AMD	Am29F400BT	SOP 44	PA44SO44D
AMD	Am29F400BT	TSOP 48	PA48TS48D
AMD	Am29F800B	SOP 44	PA44SO44D
AMD	Am29F800B	TSOP 48	PA48TS48D
AMD	Am29F800T	SOP 44	PA44SO44D
AMD	Am29F800T	TSOP 48	PA48TS48D
AMD	Am29F800AB	SOP 44	PA44SO44D
AMD	Am29F800AB	TSOP 48	PA48TS48D
AMD	Am29F800AT	SOP 44	PA44SO44D
AMD	Am29F800AT	TSOP 48	PA48TS48D
AMD	Am29F800BB	SOP 44	PA44SO44D
AMD	Am29F800BB	TSOP 48	PA48TS48D
AMD	Am29F800BT	SOP 44	PA44SO44D
AMD	Am29F800BT	TSOP 48	PA48TS48D
AMD	Am29F160DB	TSOP 48	PA48TS48D
AMD	Am29F160DT	TSOP 48	PA48TS48D
AMD	Am29LV010B	DIP 32	
AMD	Am29LV010B	TSOP 32	PA32TS20/PA32TS32D-20
AMD	Am29LV010B	PLCC 32	PA32PL32D
AMD	Am29LV040B	DIP 32	
AMD	Am29LV040B	TSOP 32	PA32TS20/PA32TS32D-20

AMD	Am29LV040B	PLCC 32	PA32PL32D
AMD	Am29LV001BT	DIP 32	
AMD	Am29LV001BT	TSOP 32	PA32TS20/PA32TS32D-20
AMD	Am29LV001BT	PLCC 32	PA32PL32D
AMD	Am29LV001BB	DIP 32	
AMD	Am29LV001BB	TSOP 32	PA32TS20/PA32TS32D-20
AMD	Am29LV001BB	PLCC 32	PA32PL32D
AMD	Am29LV002T	TSOP 40	PA40TS40D
AMD	Am29LV002B	TSOP 40	PA40TS40D
AMD	Am29LV002BT	TSOP 40	PA40TS40D
AMD	Am29LV002BB	TSOP 40	PA40TS40D
AMD	Am29LV004T	TSOP 40	PA40TS40D
AMD	Am29LV004B	TSOP 40	PA40TS40D
AMD	Am29LV004BT	TSOP 40	PA40TS40D
AMD	Am29LV004BB	TSOP 40	PA40TS40D
AMD	Am29LV008T	TSOP 40	PA40TS40D
AMD	Am29LV008B	TSOP 40	PA40TS40D
AMD	Am29LV008BT	TSOP 40	PA40TS40D
AMD	Am29LV008BB	TSOP 40	PA40TS40D
AMD	Am29LV081	TSOP 40	PA40TS40D
AMD	Am29LV081B	TSOP 40	PA40TS40D
AMD	Am29LV116BB	TSOP 40	PA40TS40D
AMD	Am29LV116BT	TSOP 40	PA40TS40D
AMD	Am29LV116DB	TSOP 40	PA40TS40D
AMD	Am29LV116DT	TSOP 40	PA40TS40D
AMD	Am29LV017B	TSOP 40	PA40TS40D
AMD	Am29LV017D	TSOP 40	PA40TS40D
AMD	Am29LV033C	TSOP 40	PA40TS40D
AMD	Am29LV065D	TSOP 48	PA48TS48D
AMD	Am29LV200B	SOP 44	PA44SO44D
AMD	Am29LV200B	TSOP 48	PA48TS48D
AMD	Am29LV200T	SOP 44	PA44SO44D
AMD	Am29LV200T	TSOP 48	PA48TS48D
AMD	Am29LV200BB	SOP 44	PA44SO44D
AMD	Am29LV200BB	TSOP 48	PA48TS48D
AMD	Am29LV200BT	SOP 44	PA44SO44D
AMD	Am29LV200BT	TSOP 48	PA48TS48D
AMD	Am29LV400B	SOP 44	PA44SO44D
AMD	Am29LV400B	TSOP 48	PA48TS48D
AMD	Am29LV400T	SOP 44	PA44SO44D
AMD	Am29LV400T	TSOP 48	PA48TS48D
AMD	Am29LV400BB	SOP 44	PA44SO44D
AMD	Am29LV400BB	TSOP 48	PA48TS48D
AMD	Am29LV400BB	BGA 48	PA48BG48DW
AMD	Am29LV400BB	BGA 48	HA48BG48DAI
AMD	Am29LV400BT	SOP 44	PA44SO44D
AMD	Am29LV400BT	TSOP 48	PA48TS48D
AMD	Am29LV400BT	BGA 48	PA48BG48DW
AMD	Am29LV400BT	BGA 48	HA48BG48DAI
AMD	Am29LV800B	SOP 44	PA44SO44D
AMD	Am29LV800B	TSOP 48	PA48TS48D
AMD	Am29LV800T	SOP 44	PA44SO44D
AMD	Am29LV800T	TSOP 48	PA48TS48D
AMD	Am29LV800BB	SOP 44	PA44SO44D
AMD	Am29LV800BB	TSOP 48	PA48TS48D
AMD	Am29LV800BB	BGA 48	HA48BG48DAP
AMD	Am29LV800BT	SOP 44	PA44SO44D
AMD	Am29LV800BT	TSOP 48	PA48TS48D
AMD	Am29LV800BT	BGA 48	HA48BG48DAP
AMD	Am29LV800DB	SOP 44	PA44SO44D
AMD	Am29LV800DB	TSOP 48	PA48TS48D
AMD	Am29LV800DB	BGA 48	HA48BG48DAP
AMD	Am29LV800DT	SOP 44	PA44SO44D
AMD	Am29LV800DT	TSOP 48	PA48TS48D
AMD	Am29LV800DT	BGA 48	HA48BG48DAP
AMD	Am29LV160BB	SOP 44	PA44SO44D
AMD	Am29LV160BB	TSOP 48	PA48TS48D
AMD	Am29LV160BT	SOP 44	PA44SO44D
AMD	Am29LV160BT	TSOP 48	PA48TS48D
AMD	Am29LV160DB	SOP 44	PA44SO44D
AMD	Am29LV160DB	TSOP 48	PA48TS48D
AMD	Am29LV160DT	SOP 44	PA44SO44D
AMD	Am29LV160DT	TSOP 48	PA48TS48D

AMD	Am29LV160MB	TSOP 48	PA48TS48D1
AMD	Am29LV160MT	TSOP 48	PA48TS48D1
AMD	Am29LV320DB	TSOP 48	PA48TS48D
AMD	Am29LV320DT	TSOP 48	PA48TS48D
AMD	Am29LV320MB	TSOP 48	PA48TS48D1
AMD	Am29LV320MT	TSOP 48	PA48TS48D1
AMD	Am29LV640DUxxPC	BGA 64	PA64BG48DK
AMD	Am29LV640MB	TSOP 48	PA48TS48D
AMD	Am29LV640MT	TSOP 48	PA48TS48D
AMD	Am29LV640MH	TSOP 56	PA56TS48DC
AMD	Am29LV640ML	TSOP 56	PA56TS48DC
AMD	Am29LV641DH	TSOP 48	PA48TS48D
AMD	Am29LV641DL	TSOP 48	PA48TS48D
AMD	Am29LV641MH	TSOP 48	PA48TS48D
AMD	Am29LV641ML	TSOP 48	PA48TS48D
AMD	Am29LV128MH	TSOP 56	PA56TS48DB
AMD	Am29LV128ML	TSOP 56	PA56TS48DB
AMD	Am29LV256MH	TSOP 56	PA56TS48DC
AMD	Am29LV256ML	TSOP 56	PA56TS48DC
AMD	Am29PL160CB	SOP 44	PA44SO44D
AMD	Am29PL160CB	TSOP 48	PA48TS48D
AMD	Am29PL160CT	SOP 44	PA44SO44D
AMD	Am29PL160CT	TSOP 48	PA48TS48D
AMD	Am29SL800CB	TSOP 48	PA48TS48D
AMD	Am29SL800CB	BGA 48	HA48BG48DBC
AMD	Am29SL800CT	TSOP 48	PA48TS48D
AMD	Am29SL800CT	BGA 48	HA48BG48DBC
AMD	Am29SL800DB	TSOP 48	PA48TS48D
AMD	Am29SL800DB	BGA 48	HA48BG48DBC
AMD	Am29SL800DT	TSOP 48	PA48TS48D
AMD	Am29SL800DT	BGA 48	HA48BG48DBC
AMD	Am29SL160BB	TSOP 48	PA48TS48D
AMD	Am29SL160BT	TSOP 48	PA48TS48D
AMD	Am29SL160CB	TSOP 48	PA48TS48D
AMD	Am29SL160CT	TSOP 48	PA48TS48D
AMD	Am42DL640AG	BGA 73	PA73BGA48DC-YO-8X11.6
AMD	Am45DL6408G	BGA 73	PA73BGA48DC-YO-8X11.6
AMD	Am49DL640BG	BGA 73	PA73BGA48DC-YO-8X11.6
AMD	Am50DL128BG	BGA 73	PA73BGA48DC-YO-8X11.6
AMD	Am50DL128CG	BGA 88	PA88BG48DB-WO-11.6X8
AMD	Am50DL128CH	BGA 88	PA88BG48DB-WO-11.6X8
AMD	Am50DL9608BG	BGA 73	PA73BGA48DC-YO-8X11.6
AMD	Am50PDL193BH	BGA 73	PA73BG48DG
AMD	Am50PDL193CH	BGA 73	PA73BG48DG
AMIC	A25L40PT	DIP 8	
AMIC	A25L05PUO	SOIC 8	PA16SO16D-EO-150
AMIC	A25L10PUO	SOIC 8	PA16SO16D-EO-150
AMIC	A25L20PUO	SOIC 8	PA16SO16D-EO-150
AMIC	A25L40PTO	SOIC 8	PA16SO16D-EO-150
AMIC	A25L40PTM	SOIC 8	PA20SO20D-EO-210
AMIC	A25L40PTN	SOIC 16	PA28SO28D-EO-300
AMIC	A25L40PTQ	MLP 8	PA8SON8D
AMIC	A25L40PU	DIP 8	
AMIC	A25L40PUO	SOIC 8	PA16SO16D-EO-150
AMIC	A25L40PUM	SOIC 8	PA20SO20D-EO-210
AMIC	A25L40PUN	SOIC 16	PA28SO28D-EO-300
AMIC	A25L40PUQ	MLP 8	PA8SON8D
AMIC	A25L80PM	SOIC 8	PA20SO20D-EO-210
AMIC	A25L80PN	SOIC 16	PA28SO28D-EO-300
AMIC	A25L010MO	SOIC 8	PA16SO16D-EO-150
AMIC	A25L020AO	SOIC 8	PA16SO16D-EO-150
AMIC	A25L020M	SOIC 8	PA20SO20D-EO-210
AMIC	A25L040M	SOIC 8	PA20SO20D-EO-210
AMIC	A25L040AO-F	SOIC 8	PA16SO16D-EO-150
AMIC	A25L080	DIP 8	
AMIC	A25L080M	SOIC 8	PA20SO20D-EO-210
AMIC	A25L016M	SOIC 8	PA20SO20D-EO-210
AMIC	A25LQ64M-FE	SOIC 8	PA20SO20D-EO-210
AMIC	A25L16PUM	SOIC 8	PA20SO20D-EO-210
AMIC	A25L16PTM	SOIC 8	PA20SO20D-EO-210
AMIC	A276308A	DIP 28	
AMIC	A276308AL	PLCC 32	PA32PL28D-YA
AMIC	A27020	DIP 32	

AMIC	A27020	PLCC 32	PA32PL32D
AMIC	A27020	TSOP 32	PA32TS20/PA32TS32D-20
AMIC	A27020L	DIP 32	
AMIC	A27020L	PLCC 32	PA32PL32D
AMIC	A27020L	TSOP 32	PA32TS20/PA32TS32D-20
AMIC	A29001U	DIP 32	
AMIC	A29001U	TSOP 32	PA32TS20/PA32TS32D-20
AMIC	A29001U	PLCC 32	PA32PL32D
AMIC	A29001T	DIP 32	
AMIC	A29001T	TSOP 32	PA32TS20/PA32TS32D-20
AMIC	A29001T	PLCC 32	PA32PL32D
AMIC	A290011U	DIP 32	
AMIC	A290011U	TSOP 32	PA32TS20/PA32TS32D-20
AMIC	A290011U	PLCC 32	PA32PL32D
AMIC	A290011T	DIP 32	
AMIC	A290011T	TSOP 32	PA32TS20/PA32TS32D-20
AMIC	A290011T	PLCC 32	PA32PL32D
AMIC	A290011AULU	PLCC 32	PA32PL32D
AMIC	A29002U	DIP 32	
AMIC	A29002U	TSOP 32	PA32TS20/PA32TS32D-20
AMIC	A29002U	PLCC 32	PA32PL32D
AMIC	A29002T	DIP 32	
AMIC	A29002T	TSOP 32	PA32TS20/PA32TS32D-20
AMIC	A29002T	PLCC 32	PA32PL32D
AMIC	A290021U	DIP 32	
AMIC	A290021U	TSOP 32	PA32TS20/PA32TS32D-20
AMIC	A290021U	PLCC 32	PA32PL32D
AMIC	A290021T	DIP 32	
AMIC	A290021T	TSOP 32	PA32TS20/PA32TS32D-20
AMIC	A290021T	PLCC 32	PA32PL32D
AMIC	A29512	DIP 32	
AMIC	A29512L	PLCC 32	PA32PL32D
AMIC	A29512V	TSOP 32	PA32TS20/PA32TS32D-20
AMIC	A29512A	DIP 32	
AMIC	A29512A	PLCC 32	PA32PL32D
AMIC	A29512A	TSOP 32	PA32TS20/PA32TS32D-20
AMIC	A29010	DIP 32	
AMIC	A29010A	DIP 32	
AMIC	A29010L	PLCC 32	PA32PL32D
AMIC	A29010V	TSOP 32	PA32TS20/PA32TS32D-20
AMIC	A29040	DIP 32	
AMIC	A29040L	PLCC 32	PA32PL32D
AMIC	A29040V	TSOP 32	PA32TS20/PA32TS32D-20
AMIC	A29040A	DIP 32	
AMIC	A29040AL	PLCC 32	PA32PL32D
AMIC	A29040AV	TSOP 32	PA32TS20/PA32TS32D-20
AMIC	A29040B	DIP 32	
AMIC	A29040BL	PLCC 32	PA32PL32D
AMIC	A29040BV	TSOP 32	PA32TS20/PA32TS32D-20
AMIC	A29040CL	PLCC 32	PA32PL32D
AMIC	A29400U	TSOP 48	PA48TS48D
AMIC	A29400T	TSOP 48	PA48TS48D
AMIC	A29800ATV	TSOP 48	PA48TS48D
AMIC	A29800UV	TSOP 48	PA48TS48D
AMIC	A29800UM	SOP 44	PA44SO44D
AMIC	A29800TV	TSOP 48	PA48TS48D
AMIC	A29800TM	SOP 44	PA44SO44D
AMIC	A29801AUV	TSOP 48	PA48TS48D
AMIC	A29L040L	PLCC 32	PA32PL32D
AMIC	A29L040V	TSOP 32	PA32TS20/PA32TS32D-20
AMIC	A29L040X	TSOP 32	PA32TS32D
AMIC	A29L004TL	PLCC 32	PA32PL32D
AMIC	A29L004TX	TSOP 32	PA32TS32D
AMIC	A29L004TV	TSOP 32	PA32TS20/PA32TS32D-20
AMIC	A29L004TW	TSOP 40	PA40TS40D
AMIC	A29L004UL	PLCC 32	PA32PL32D
AMIC	A29L004UX	TSOP 32	PA32TS32D
AMIC	A29L004UV	TSOP 32	PA32TS20/PA32TS32D-20
AMIC	A29L004UW	TSOP 40	PA40TS40D
AMIC	A29L008TV	TSOP 40	PA40TS40D
AMIC	A29L008AUV	TSOP 40	PA40TS40D
AMIC	A29L008UV	TSOP 40	PA40TS40D
AMIC	A29L400UM	SOP 44	PA44SO44D



AMIC	A29L400UV	TSOP 48	PA48TS48D
AMIC	A29L400TM	SOP 44	PA44SO44D
AMIC	A29L400TV	TSOP 48	PA48TS48D
AMIC	A29L400AUM	SOP 44	PA44SO44D
AMIC	A29L400AUV	TSOP 48	PA48TS48D
AMIC	A29L400ATM	SOP 44	PA44SO44D
AMIC	A29L400ATV	TSOP 48	PA48TS48D
AMIC	A29L800UM	SOP 44	PA44SO44D
AMIC	A29L800MV	TSOP 48	PA48TS48D
AMIC	A29L800TM	SOP 44	PA44SO44D
AMIC	A29L800TV	TSOP 48	PA48TS48D
AMIC	A29L800AUM	SOP 44	PA44SO44D
AMIC	A29L800AUV	TSOP 48	PA48TS48D
AMIC	A29L800ATM	SOP 44	PA44SO44D
AMIC	A29L800ATV	TSOP 48	PA48TS48D
AMIC	A29L800HUM	SOP 44	PA44SO44D
AMIC	A29L800HUV	TSOP 48	PA48TS48D
AMIC	A29L800HTM	SOP 44	PA44SO44D
AMIC	A29L800HTV	TSOP 48	PA48TS48D
AMIC	A29L160UM	SOP 44	PA44SO44D
AMIC	A29L160UV	TSOP 48	PA48TS48D
AMIC	A29L160TM	SOP 44	PA44SO44D
AMIC	A29L160TV	TSOP 48	PA48TS48D
AMIC	A29L160HUM	SOP 44	PA44SO44D
AMIC	A29L160HUV	TSOP 48	PA48TS48D
AMIC	A29L160HTM	SOP 44	PA44SO44D
AMIC	A29L160HTV	TSOP 48	PA48TS48D
AMIC	A29L160FUV	TSOP 48	PA48TS48D
AMIC	A29L160FTV	TSOP 48	PA48TS48D
AMIC	A29L160AUM	SOP 44	PA44SO44D
AMIC	A29L160AUV	TSOP 48	PA48TS48D1
AMIC	A29L160ATM	SOP 44	PA44SO44D
AMIC	A29L160ATV	TSOP 48	PA48TS48D1
AMIC	A29L160BTM	SOP 44	PA44SO44D
AMIC	A29L160BTV	TSOP 48	PA48TS48D1
AMIC	A29L160BUM	SOP 44	PA44SO44D
AMIC	A29L160BUV	TSOP 48	PA48TS48D1
AMIC	A29160ATV	TSOP 48	PA48TS48D
AMIC	A29160AUV	TSOP 48	PA48TS48D
AMIC	A29160TV	TSOP 48	PA48TS48D1
AMIC	A29160UV	TSOP 48	PA48TS48D1
AMIC	A29L801TV	TSOP 48	PA48TS48D1
AMIC	A29L801UV	TSOP 48	PA48TS48D1
AMIC	A29DL162UV	TSOP 48	PA48TS48D1
AMIC	A29DL162TV	TSOP 48	PA48TS48D1
AMIC	A29DL163UV	TSOP 48	PA48TS48D1
AMIC	A29DL163TV	TSOP 48	PA48TS48D1
AMIC	A29DL164UV	TSOP 48	PA48TS48D1
AMIC	A29DL164TV	TSOP 48	PA48TS48D1
AMIC	A29DL320FUV	TSOP 48	PA48TS48D1
AMIC	A29DL320FTV	TSOP 48	PA48TS48D1
AMIC	A29DL324UV	TSOP 48	PA48TS48D1
AMIC	A29DL324TV	TSOP 48	PA48TS48D1
AMIC	A29L320AUV	TSOP 48	PA48TS48D1
AMIC	A29L320ATV	TSOP 48	PA48TS48D1
AMIC	A29DL322UV	TSOP 48	PA48TS48D1
AMIC	A29DL322TV	TSOP 48	PA48TS48D1
AMIC	A29DL323UV	TSOP 48	PA48TS48D1
AMIC	A29DL323TV	TSOP 48	PA48TS48D1
AMIC	A49LF004TL	PLCC 32	PA32PL32D
AMIC	A49LF004MTL	PLCC 32	PA32PL32D
AMIC	A49LF040TL	PLCC 32	PA32PL32D
AMIC	A49LF040ATL	PLCC 32	PA32PL32D
AMIC	A49LF040ATL	TSOP 32	PA32TS32D
AMIC	A50FW040TL	PLCC 32	PA32PL32D
AMIC	A50FW040MTL	PLCC 32	PA32PL32D
AMIC	A50LPW040TL	PLCC 32	PA32PL32D
ATMEL	AT17C65	DIP 8	
ATMEL	AT17C65	SOIC 20	PA28SO28D-EO-300
ATMEL	AT17C65	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17C65A	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17C128	DIP 8	
ATMEL	AT17C128	PLCC 20	PA20LC20D[Dead Bug]

ATMEL	AT17C128A	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17C256	DIP 8	
ATMEL	AT17C256	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17C256A	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17C512	DIP 8	
ATMEL	AT17C512	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17C512A	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17C010	DIP 8	
ATMEL	AT17C010	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17C010A	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17C020	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17C020A	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17C002	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17C002	PLCC 44	PA44-48U
ATMEL	AT17C002	QFP 44	PA44QF44D
ATMEL	AT17C002A	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17C002A	PLCC 44	PA44-48U
ATMEL	AT17C002A	QFP 44	PA44QF44D
ATMEL	AT17C040	PLCC 44	PA44-48U
ATMEL	AT17C040	QFP 44	PA44QF44D
ATMEL	AT17C040A	PLCC 44	PA44-48U
ATMEL	AT17C040A	QFP 44	PA44QF44D
ATMEL	AT17F040	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17F080	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17F080	PLCC 44	PA44-48U
ATMEL	AT17F080	QFP 44	PA44QF44D
ATMEL	AT17F040A	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17F080A	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17LV65	DIP 8	
ATMEL	AT17LV65	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17LV65	SOIC 20	PA28SO28D-EO-300
ATMEL	AT17LV128	DIP 8	
ATMEL	AT17LV128	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17LV128	SOIC 20	PA28SO28D-EO-300
ATMEL	AT17LV256	DIP 8	
ATMEL	AT17LV256	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17LV256	SOIC 20	PA28SO28D-EO-300
ATMEL	AT17LV512	DIP 8	
ATMEL	AT17LV512	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17LV512	SOIC 20	PA28SO28D-EO-300
ATMEL	AT17LV010	DIP 8	
ATMEL	AT17LV010	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17LV010	SOIC 20	PA28SO28D-EO-300
ATMEL	AT17LV002	LAP 8	PA8SON8DB
ATMEL	AT17LV002A	LAP 8	PA8SON8DB
ATMEL	AT17LV002	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17LV002	PLCC 44	PA44-48U
ATMEL	AT17LV002	QFP 44	PA44QF44D
ATMEL	AT17LV002	SOIC 20	PA28SO28D-EO-300
ATMEL	AT17LV65A	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17LV128A	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17LV256A	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17LV010A	DIP 8	
ATMEL	AT17LV010A	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17LV512A	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17LV002A	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17LV002A	PLCC 44	PA44-48U
ATMEL	AT17LV002A	QFP 44	PA44QF44D
ATMEL	AT17LV040	PLCC 44	PA44-48U
ATMEL	AT17LV040	QFP 44	PA44QF44D
ATMEL	AT17LV040A	PLCC 44	PA44-48U
ATMEL	AT17LV040A	QFP 44	PA44QF44D
ATMEL	AT17LV020	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17LV020A	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	AT17N256	DIP 8	
ATMEL	AT17N256	SOIC 8	PA16SO16D-EO-150
ATMEL	AT17N256	SOIC 20	PA28SO28D-EO-300
ATMEL	AT17N512	DIP 8	
ATMEL	AT17N512	LAP 8	PA8LAP8D-EO-230
ATMEL	AT17N512	SOIC 20	PA28SO28D-EO-300
ATMEL	AT17N010	DIP 8	
ATMEL	AT17N010	LAP 8	PA8LAP8D-EO-230
ATMEL	AT17N010	SOIC 20	PA28SO28D-EO-300

ATMEL	AT17N002	LAP 8	PA8LAP8D-EO-230
ATMEL	AT17N002	SOIC 20	PA28SO28D-EO-300
ATMEL	AT17N002	QFP 44	PA44QF44D
ATMEL	AT17N040	QFP 44	PA44QF44D
ATMEL	AT24C01	DIP 8	
ATMEL	AT24C01	TSSOP 8	PA8TSS8D
ATMEL	AT24C01	TSSOP 8	PA24TSS24D
ATMEL	AT24C01	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24C01A	DIP 8	
ATMEL	AT24C01A	TSSOP 8	PA8TSS8D
ATMEL	AT24C01A	TSSOP 8	PA24TSS24D
ATMEL	AT24C01A	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24C01A	dBGA 8	PA8DBGA8D
ATMEL	AT24C01A	MAP 8	PA8MAP8
ATMEL	AT24C01A	SCM 8	PA5SOT5D
ATMEL	AT24C02	DIP 8	
ATMEL	AT24C02	TSSOP 8	PA8TSS8D
ATMEL	AT24C02	TSSOP 8	PA24TSS24D
ATMEL	AT24C02	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24C02	dBGA 8	PA8DBGA8D
ATMEL	AT24C02	MAP 8	PA8MAP8
ATMEL	AT24C02	SOT23- 5	PA5SOT5D
ATMEL	AT24C02A	DIP 8	
ATMEL	AT24C02A	TSSOP 8	PA8TSS8D
ATMEL	AT24C02A	TSSOP 8	PA24TSS24D
ATMEL	AT24C02A	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24C02A	MAP 8	PA8MAP8
ATMEL	AT24C04	DIP 8	
ATMEL	AT24C04	TSSOP 8	PA8TSS8D
ATMEL	AT24C04	TSSOP 8	PA24TSS24D
ATMEL	AT24C04	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24C04	dBGA 8	PA8DBGA8D
ATMEL	AT24C04	MAP 8	PA8MAP8
ATMEL	AT24C04	SOT23- 5	PA5SOT5D
ATMEL	AT24C04A	DIP 8	
ATMEL	AT24C04A	TSSOP 8	PA8TSS8D
ATMEL	AT24C04A	TSSOP 8	PA24TSS24D
ATMEL	AT24C04A	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24C04A	MAP 8	PA8MAP8
ATMEL	AT24C08	DIP 8	
ATMEL	AT24C08	TSSOP 8	PA8TSS8D
ATMEL	AT24C08	TSSOP 8	PA24TSS24D
ATMEL	AT24C08	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24C08	dBGA 8	PA8DBGA8D
ATMEL	AT24C08	MAP 8	PA8MAP8
ATMEL	AT24C08	SOT23- 5	PA5SOT5D
ATMEL	AT24C08A	DIP 8	
ATMEL	AT24C08A	TSSOP 8	PA8TSS8D
ATMEL	AT24C08A	TSSOP 8	PA24TSS24D
ATMEL	AT24C08A	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24C08A	MAP 8	PA8MAP8
ATMEL	AT24C16	DIP 8	
ATMEL	AT24C16	TSSOP 8	PA8TSS8D
ATMEL	AT24C16	TSSOP 8	PA24TSS24D
ATMEL	AT24C16	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24C16	dBGA 8	PA8DBGA8D
ATMEL	AT24C16	MAP 8	PA8MAP8
ATMEL	AT24C16	SOT23- 5	PA5SOT5D
ATMEL	AT24C16A	DIP 8	
ATMEL	AT24C16A	TSSOP 8	PA8TSS8D
ATMEL	AT24C16A	TSSOP 8	PA24TSS24D
ATMEL	AT24C16A	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24C16A	MAP 8	PA8MAP8
ATMEL	AT24C16C-SSHM-T	SOIC 8	PA16SO16D-EO-150
ATMEL	AT24C16C-PUM	DIP 8	
ATMEL	AT24C164	DIP 8	
ATMEL	AT24C164	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24C32	DIP 8	
ATMEL	AT24C32	TSSOP 8	PA8TSS8D
ATMEL	AT24C32	TSSOP 8	PA24TSS24D
ATMEL	AT24C32	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24C32A	DIP 8	
ATMEL	AT24C32A	SOIC 8	PA8SO8D-EO-150

ATMEL	AT24C32A	SOIC 8	PA16SO16D-EO-150
ATMEL	AT24C32A	TSSOP 8	PA8TSS8D
ATMEL	AT24C32A	TSSOP 8	PA24TSS24D
ATMEL	AT24C32A	MAP 8	PA8MAP8
ATMEL	AT24C32B	DIP 8	
ATMEL	AT24C32B	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24C32B	TSSOP 8	PA8TSS8D
ATMEL	AT24C32B	TSSOP 8	PA24TSS24D
ATMEL	AT24C64	DIP 8	
ATMEL	AT24C64	TSSOP 8	PA8TSS8D
ATMEL	AT24C64	TSSOP 8	PA24TSS24D
ATMEL	AT24C64	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24C64A	DIP 8	
ATMEL	AT24C64A	SOIC 8	PA16SO16D-EO-150
ATMEL	AT24C64A	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24C64A	TSSOP 8	PA8TSS8D
ATMEL	AT24C64A	TSSOP 8	PA24TSS24D
ATMEL	AT24C64A	MAP 8	PA8MAP8
ATMEL	AT24C64B	DIP 8	
ATMEL	AT24C64B	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24C64B	TSSOP 8	PA8TSS8D
ATMEL	AT24C64B	TSSOP 8	PA24TSS24D
ATMEL	AT24C128	DIP 8	
ATMEL	AT24C128	TSSOP 8	PA24TSS24D
ATMEL	AT24C128-1.8V	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24C128-1.8V	dBGA 8	PA8DBG8D
ATMEL	AT24C128-1.8V	TSSOP 14	PA28TSS28D-EO
ATMEL	AT24C128-5V	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24C128-5V	dBGA 8	PA8DBG8D
ATMEL	AT24C128-5V	TSSOP 14	PA28TSS28D-EO
ATMEL	AT24C256	DIP 8	
ATMEL	AT24C256	TSSOP 8	PA24TSS24D
ATMEL	AT24C256N	SOIC 8	PA16SO16D-EO-150
ATMEL	AT24C256-1.8V	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24C256-1.8V	dBGA 8	PA8DBG8D
ATMEL	AT24C256-1.8V	TSSOP 14	PA28TSS28D-EO
ATMEL	AT24C256-5V	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24C256-5V	dBGA 8	PA8DBG8D
ATMEL	AT24C256-5V	TSSOP 14	PA28TSS28D-EO
ATMEL	AT24C256B	DIP 8	
ATMEL	AT24C256B	TSSOP 8	PA24TSS24D
ATMEL	AT24C256BN	SOIC 8	PA16SO16D-EO-150
ATMEL	AT24C512	DIP 8	
ATMEL	AT24C512	TSSOP 8	PA24TSS24D
ATMEL	AT24C512-1.8V	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24C512-1.8V	LAP 8	PA8LAP8D-EO-230
ATMEL	AT24C512-1.8V	dBGA 8	PA8DBG8D
ATMEL	AT24C512-5V	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24C512-5V	LAP 8	PA8LAP8D-EO-230
ATMEL	AT24C512-5V	dBGA 8	PA8DBG8D
ATMEL	AT24C1024	DIP 8	
ATMEL	AT24C1024	SOIC 8	PA16SO16D-EO-150
ATMEL	AT24C1024W	SOIC 8	PA20SO20D-EO-210
ATMEL	AT24C1024	LAP 8	PA8MAP8
ATMEL	AT24C1024	LAP 8	PA8LAP8D-EO-300
ATMEL	AT24C1024	LAP 8	PA8LAP8D-EO-230
ATMEL	AT24C1024	dBGA 8	PA8DBG8D
ATMEL	AT24CS128	DIP 8	
ATMEL	AT24CS128-1.8V	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24CS128-1.8V	SOIC 8	PA16SO16D-EO-150
ATMEL	AT24CS128-2.7:5V	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24CS128-2.7:5V	SOIC 8	PA16SO16D-EO-150
ATMEL	AT24CS256	DIP 8	
ATMEL	AT24CS256-1.8V	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24CS256-1.8V	SOIC 8	PA16SO16D-EO-150
ATMEL	AT24CS256-2.7:5V	SOIC 8	PA8SO8D-EO-150
ATMEL	AT24CS256-2.7:5V	SOIC 8	PA16SO16D-EO-150
ATMEL	AT24C01ASC-E	SCM 8	PA8SCM8D
ATMEL	AT24C01ASC-G	SCM 8	PA8SCM8D
ATMEL	AT24C01ASC-H	SCM 8	PA8SCM8D
ATMEL	AT24C01ASC-P	SCM 8	PA8SCM8D
ATMEL	AT24C01ASC-W	SCM 8	PA8SCM8D
ATMEL	AT24C02SC-E	SCM 8	PA8SCM8D

ATMEL	AT24C02SC-P	SCM 8	PA8SCM8D
ATMEL	AT24C02SC-W	SCM 8	PA8SCM8D
ATMEL	AT24C04SC-E	SCM 8	PA8SCM8D
ATMEL	AT24C04SC-P	SCM 8	PA8SCM8D
ATMEL	AT24C04SC-W	SCM 8	PA8SCM8D
ATMEL	AT24C08SC-E	SCM 8	PA8SCM8D
ATMEL	AT24C08SC-P	SCM 8	PA8SCM8D
ATMEL	AT24C08SC-W	SCM 8	PA8SCM8D
ATMEL	AT24C16SC-E	SCM 8	PA8SCM8D
ATMEL	AT24C16SC-P	SCM 8	PA8SCM8D
ATMEL	AT24C16SC-W	SCM 8	PA8SCM8D
ATMEL	AT24RF08CN	SOIC 8	PA16SO16D-EO-150
ATMEL	AT24RF08CT	TSSOP 14	PA24TSS24D
ATMEL	AT24HC02C	SOIC 8	PA16SO16D-EO-150
ATMEL	AT24CM01	SOIC 8	PA16SO16D-EO-150
ATMEL	AT34C02	DIP 8	
ATMEL	AT34C02	TSSOP 8	PA8TSS-OT
ATMEL	AT34C02	SOIC 8	PA8SO8D-EO-150
ATMEL	AT34C02	TSSOP 8	PA8TSS8D
ATMEL	AT34C02	TSSOP 8	PA24TSS24D
ATMEL	AT34C02B	SOIC 8	PA8SO8D-EO-150
ATMEL	AT34C02B	TSSOP 8	PA8TSS8D
ATMEL	AT34C02B	TSSOP 8	PA24TSS24D
ATMEL	AT34C02C	SOIC 8	PA8SO8D-EO-150
ATMEL	AT34C02C	TSSOP 8	PA8TSS8D
ATMEL	AT34C02C	TSSOP 8	PA24TSS24D
ATMEL	AT30TSE004A	DFN 8	PA8QFN8D
ON SEMICONDUCTOR	CAT34T504	DFN 8	PA8QFN8D
IDT	TSE2004G	DFN 8	PA8QFN8D
MICROCHIP	MCP98244	DFN 8	PA8QFN8D
ST	STTS2004	DFN 8	PA8QFN8D
MICROCHIP	34AA04	DFN 8	PA8QFN8D
ATMEL	AT25010	DIP 8	
ATMEL	AT25010	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25010A	DIP 8	
ATMEL	AT25010A	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25010A	MAP 8	PA8MAP8
ATMEL	AT25010A	TSSOP 8	PA24TSS24D
ATMEL	AT25020	DIP 8	
ATMEL	AT25020	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25020A	DIP 8	
ATMEL	AT25020A	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25020A	MAP 8	PA8MAP8
ATMEL	AT25020A	TSSOP 8	PA24TSS24D
ATMEL	AT25040	DIP 8	
ATMEL	AT25040	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25040A	DIP 8	
ATMEL	AT25040A	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25040A	MAP 8	PA8MAP8
ATMEL	AT25040A	TSSOP 8	PA24TSS24D
ATMEL	AT25080	DIP 8	
ATMEL	AT25080	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25080	TSSOP 14	PA14TSS14D
ATMEL	AT25080	TSSOP 20	PA20TSS20D
ATMEL	AT25080A	DIP 8	
ATMEL	AT25080A	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25080A	MAP 8	PA8MAP8
ATMEL	AT25080A	TSSOP 8	PA24TSS24D
ATMEL	AT25160	DIP 8	
ATMEL	AT25160	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25160	TSSOP 14	PA14TSS14D
ATMEL	AT25160	TSSOP 20	PA20TSS20D
ATMEL	AT25160A	DIP 8	
ATMEL	AT25160A	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25160A	MAP 8	PA8MAP8
ATMEL	AT25160A	TSSOP 8	PA24TSS24D
ATMEL	AT25320	DIP 8	
ATMEL	AT25320	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25320	TSSOP 14	PA14TSS14D
ATMEL	AT25320	TSSOP 20	PA20TSS20D
ATMEL	AT25320A(QF4A512)	LQFP 32	HA32LQ48DA
ATMEL	AT25320A	DIP 8	
ATMEL	AT25320A	SOIC 8	PA16SO16D-EO-150

ATMEL	AT25320A	MAP 8	PA8MAP8
ATMEL	AT25320A	TSSOP 8	PA24TSS24D
ATMEL	AT25640	DIP 8	
ATMEL	AT25640	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25640	TSSOP 14	PA14TSS14D
ATMEL	AT25640	TSSOP 20	PA20TSS20D
ATMEL	AT25640A	DIP 8	
ATMEL	AT25640A	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25640A	MAP 8	PA8MAP8
ATMEL	AT25640A	TSSOP 8	PA24TSS24D
ATMEL	AT25128	DIP 8	
ATMEL	AT25128	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25128	LAP 8	PA8MAP8
ATMEL	AT25128	TSSOP 14	PA14TSS14D
ATMEL	AT25128	SOIC 16	PA16SO16D-1
ATMEL	AT25128	TSSOP 20	PA20TSS20D
ATMEL	AT25128A	DIP 8	
ATMEL	AT25128A	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25128A	MAP 8	PA8MAP8
ATMEL	AT25128A	TSSOP 8	PA24TSS24D
ATMEL	AT25128A	BGA 8	HA8BG48D
ATMEL	AT25256	DIP 8	
ATMEL	AT25256	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25256	LAP 8	PA8MAP8
ATMEL	AT25256	TSSOP 14	PA14TSS14D
ATMEL	AT25256	SOIC 16	PA16SO16D-1
ATMEL	AT25256	TSSOP 20	PA20TSS20D
ATMEL	AT25256A	DIP 8	
ATMEL	AT25256A	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25256A	MAP 8	PA8MAP8
ATMEL	AT25256A	TSSOP 8	PA24TSS24D
ATMEL	AT25256A	BGA 8	HA8BG48D
ATMEL	AT25HP256	DIP 8	
ATMEL	AT25HP256	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25HP256	LAP 8	PA8MAP8
ATMEL	AT25HP512	DIP 8	
ATMEL	AT25HP512	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25HP512	LAP 8	PA8MAP8
ATMEL	AT25P1024	SOIC 20	PA28SO28D-EO-300
ATMEL	AT25P1024	LAP 8	PA8MAP8
ATMEL	AT25F512A	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25F512A	QFN 8	PA8SON8D
ATMEL	AT25F512B	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25F512B	QFN 8	PA8SON8D
ATMEL	AT25FS010	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25F1024	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25F2048	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25F4096	SOIC 8	PA20SO20D-EO-210
ATMEL	AT25080(1.8)	DIP 8	
ATMEL	AT25080(1.8)	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25080(1.8)	TSSOP 14	PA14TSS14D
ATMEL	AT25080(1.8)	TSSOP 20	PA20TSS20D
ATMEL	AT25160(1.8)	DIP 8	
ATMEL	AT25160(1.8)	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25160(1.8)	TSSOP 14	PA14TSS14D
ATMEL	AT25160(1.8)	TSSOP 20	PA20TSS20D
ATMEL	AT25320(1.8)	DIP 8	
ATMEL	AT25320(1.8)	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25320(1.8)	TSSOP 14	PA14TSS14D
ATMEL	AT25320(1.8)	TSSOP 20	PA20TSS20D
ATMEL	AT25640(1.8)	DIP 8	
ATMEL	AT25640(1.8)	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25640(1.8)	TSSOP 14	PA14TSS14D
ATMEL	AT25640(1.8)	TSSOP 20	PA20TSS20D
ATMEL	AT25128(1.8)	DIP 8	
ATMEL	AT25128(1.8)	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25128(1.8)	LAP 8	PA8MAP8
ATMEL	AT25128(1.8)	TSSOP 14	PA14TSS14D
ATMEL	AT25128(1.8)	SOIC 16	PA16SO16D-1
ATMEL	AT25128(1.8)	TSSOP 20	PA20TSS20D
ATMEL	AT25256(1.8)	DIP 8	
ATMEL	AT25256(1.8)	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25256(1.8)	LAP 8	PA8MAP8

ATMEL	AT25256(1.8)	TSSOP 14	PA14TSS14D
ATMEL	AT25256(1.8)	SOIC 16	PA16SO16D-1
ATMEL	AT25256(1.8)	TSSOP 20	PA20TSS20D
ATMEL	AT25HP256(1.8)	DIP 8	
ATMEL	AT25HP256(1.8)	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25HP256(1.8)	LAP 8	PA8MAP8
ATMEL	AT25HP512(1.8)	DIP 8	
ATMEL	AT25HP512(1.8)	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25HP512(1.8)	LAP 8	PA8MAP8
ATMEL	AT25P1024(1.8)	SOIC 20	PA28SO28D-EO-300
ATMEL	AT25P1024(1.8)	LAP 8	PA8MAP8
ATMEL	AT25DF021	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25DF021	CASON 8	PA8SON8D
ATMEL	AT25DF041A	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25DF041A	CASON 8	PA8SON8D
ATMEL	AT25DF081	SOP 8	PA16SO16D-EO-150
ATMEL	AT25DF161	SOIC 8	PA16SO16D-EO-150
ATMEL	AT25DF161	SOIC 8	PA20SO20D-EO-210
ATMEL	AT25DF161	CASON 8	PA8SON8D
ATMEL	AT26DF081	SOP 8	PA16SO16D-EO-150
ATMEL	AT26DF081	SOP 8	PA20SO20D-EO-210
ATMEL	AT26DF081A	SOP 8	PA16SO16D-EO-150
ATMEL	AT26DF081A	SOP 8	PA20SO20D-EO-210
ATMEL	AT26DF161	MLP 8	PA8SON8D
ATMEL	AT26DF161	SOP 8	PA20SO20D-EO-210
ATMEL	AT26DF161A	MLP 8	PA8SON8D
ATMEL	AT26DF161A	SOP 8	PA20SO20D-EO-210
ATMEL	AT26DF321	SOIC 8	PA20SO20D-EO-210
ATMEL	AT26DF321	SOIC 16	PA28SO28D-EO-300
ATMEL	AT25DF321	SOIC 8	PA20SO20D-EO-210
ATMEL	AT25DF321	SOIC 16	PA28SO28D-EO-300
ATMEL	AT25DF641	SOIC 16	PA28SO28D-EO-300
ATMEL	AT26F004	SOP 8	PA16SO16D-EO-150
ATMEL	AT26F004	SOP 8	PA20SO20D-EO-210
ATMEL	AT26F004	MLP 8	PA8SON8D
ATMEL	AT27BV256	DIP 28	
ATMEL	AT27BV256	TSOP 28	PA28TS28D-EO
ATMEL	AT27BV256	PLCC 32	PA32PL28D-YA
ATMEL	AT27BV256	SOIC 28	PA28SO28D-EO-300
ATMEL	AT27BV512	DIP 28	
ATMEL	AT27BV512	PLCC 32	PA32PL28D-YA
ATMEL	AT27BV512	SOIC 28	PA28SO28D-EO-300
ATMEL	AT27BV512	TSOP 28	PA28TS28D-EO
ATMEL	AT27BV010	DIP 32	
ATMEL	AT27BV010	PLCC 32	PA32PL32D
ATMEL	AT27BV010	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT27BV010	sTSOP 32	PA32TS32D
ATMEL	AT27BV020	DIP 32	
ATMEL	AT27BV020	PLCC 32	PA32PL32D
ATMEL	AT27BV020	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT27BV020	sTSOP 32	PA32TS32D
ATMEL	AT27BV040	DIP 32	
ATMEL	AT27BV1024	DIP 40	
ATMEL	AT27BV1024	PLCC 44	PA44-48U
ATMEL	AT27BV1024	TSOP 40	PA40TS40D
ATMEL	AT27BV4096	DIP 40	
ATMEL	AT27BV4096	PLCC 44	PA44-48U
ATMEL	AT27BV4096	TSOP 40	PA40TS40D
ATMEL	AT27BV800	PLCC 44	PA44-48U
ATMEL	AT27BV800	SOP 44	PA44SO44D
ATMEL	AT27C64	DIP 28	
ATMEL	AT27C64	PLCC 32	PA32PL28D-YA
ATMEL	AT27C128	DIP 28	
ATMEL	AT27C128	PLCC 32	PA32PL28D-YA
ATMEL	AT27C256	DIP 28	
ATMEL	AT27C256	PLCC 32	PA32PL28D-YA
ATMEL	AT27C256R	DIP 28	
ATMEL	AT27C256R	TSOP 28	PA28TS28D-EO
ATMEL	AT27C256R	PLCC 32	PA32PL28D-YA
ATMEL	AT27C256R	SOIC 28	PA28SO28DB-EC-350
ATMEL	AT27C512	DIP 28	
ATMEL	AT27C512	PLCC 32	PA32PL28D-YA
ATMEL	AT27C512	SOIC 28	PA28SO28D-EO-300

ATMEL	AT27C512	TSOP 28	PA28TS28D-EO
ATMEL	AT27C512R	DIP 28	
ATMEL	AT27C512R	PLCC 32	PA32PL28D-YA
ATMEL	AT27C512R	SOIC 28	PA28SO28D-EO-300
ATMEL	AT27C512R	TSOP 28	PA28TS28D-EO
ATMEL	AT27C513	DIP 28	
ATMEL	AT27C513R	DIP 28	
ATMEL	AT27C520	SOIC 20	PA28SO-08(C)
ATMEL	AT27C520	TSOP 20	PA24TSS24D
ATMEL	AT27C010	DIP 32	
ATMEL	AT27C010	PLCC 32	PA32PL32D
ATMEL	AT27C010	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT27C010L	DIP 32	
ATMEL	AT27C010L	PLCC 32	PA32PL32D
ATMEL	AT27C010L	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT27C020	DIP 32	
ATMEL	AT27C020	PLCC 32	PA32PL32D
ATMEL	AT27C020	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT27C040	DIP 32	
ATMEL	AT27C040	PLCC 32	PA32PL32D
ATMEL	AT27C040	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT27C040	SOIC 32	PA32SO32D-EO-450
ATMEL	AT27C080	DIP 32	
ATMEL	AT27C080	PLCC 32	PA32PL32D
ATMEL	AT27C080	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT27C080	SOIC 32	PA32SO32D-EO-450
ATMEL	AT32C16	DIP 40	
ATMEL	AT27C516	DIP 40	
ATMEL	AT27C516	PLCC 44	PA44-48U
ATMEL	AT27C516	TSOP 40	PA40TS40D
ATMEL	AT27C1024	DIP 40	
ATMEL	AT27C1024	PLCC 44	PA44-48U
ATMEL	AT27C1024	TSOP 40	PA40TS40D
ATMEL	AT27C1024L	DIP 40	
ATMEL	AT27C1024L	PLCC 44	PA44-48U
ATMEL	AT27C1024L	TSOP 40	PA40TS40D
ATMEL	AT27C2048	DIP 40	
ATMEL	AT27C2048	PLCC 44	PA44-48U
ATMEL	AT27C2048	TSOP 40	PA40TS40D
ATMEL	AT27C4096	DIP 40	
ATMEL	AT27C4096	PLCC 44	PA44-48U
ATMEL	AT27C4096	TSOP 40	PA40TS40D
ATMEL	AT27C400	DIP 40	
ATMEL	AT27C400	TSOP 48	PA48TS48D
ATMEL	AT27C400	SOP 40	PA40SO40D-EO-450
ATMEL	AT27C800	DIP 42	
ATMEL	AT27C800	PLCC 44	PA44-48U
ATMEL	AT27C800	SOP 44	PA44SO44D
ATMEL	AT27C8192	DIP 42	
ATMEL	AT27C8192	SOP 44	PA44SO44D
ATMEL	AT27HC1024	DIP 40	
ATMEL	AT27HC1024	PLCC 44	PA44-48U
ATMEL	AT27HC64	DIP 28	
ATMEL	AT27HC64	PLCC 32	PA32PL28D-YA
ATMEL	AT27HC64L	DIP 28	
ATMEL	AT27HC64L	PLCC 32	PA32PL28D-YA
ATMEL	AT27HC256	DIP 28	
ATMEL	AT27HC256	PLCC 32	PA32PL28D-YA
ATMEL	AT27HC256R	DIP 28	
ATMEL	AT27HC256R	PLCC 32	PA32PL28D-YA
ATMEL	AT27LV256A	DIP 28	
ATMEL	AT27LV256R	DIP 28	
ATMEL	AT27LV256A/R	PLCC 32	PA32PL28D-YA
ATMEL	AT27LV256A/R	SOIC 28	PA28SO28D-EO-300
ATMEL	AT27LV256A/R	TSOP 28	PA28TS28D-EO
ATMEL	AT27LV512A	DIP 28	
ATMEL	AT27LV512A	PLCC 32	PA32PL28D-YA
ATMEL	AT27LV512A	SOIC 28	PA28SO28D-EO-300
ATMEL	AT27LV512A	TSOP 28	PA28TS28D-EO
ATMEL	AT27LV512R	DIP 28	
ATMEL	AT27LV512R	PLCC 32	PA32PL28D-YA
ATMEL	AT27LV512R	SOIC 28	PA28SO28D-EO-300
ATMEL	AT27LV512R	TSOP 28	PA28TS28D-EO



ATMEL	AT27LV520	SOIC 20	PA28SO-08(C)
ATMEL	AT27LV520	TSOP 20	PA24TSS24D
ATMEL	AT27LV010	DIP 32	
ATMEL	AT27LV010	PLCC 32	PA32PL32D
ATMEL	AT27LV010	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT27LV010	sTSOP 32	PA32TS32D
ATMEL	AT27LV010A	DIP 32	
ATMEL	AT27LV010A	PLCC 32	PA32PL32D
ATMEL	AT27LV010A	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT27LV010A	sTSOP 32	PA32TS32D
ATMEL	AT27LV010AL	DIP 32	
ATMEL	AT27LV010AL	PLCC 32	PA32PL32D
ATMEL	AT27LV010AL	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT27LV010AL	sTSOP 32	PA32TS32D
ATMEL	AT27LV020	DIP 32	
ATMEL	AT27LV020	PLCC 32	PA32PL32D
ATMEL	AT27LV020	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT27LV020	sTSOP 32	PA32TS32D
ATMEL	AT27LV020A	DIP 32	
ATMEL	AT27LV020A	PLCC 32	PA32PL32D
ATMEL	AT27LV020A	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT27LV020A	sTSOP 32	PA32TS32D
ATMEL	AT27LV040	DIP 32	
ATMEL	AT27LV040	PLCC 32	PA32PL32D
ATMEL	AT27LV040	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT27LV040	sTSOP 32	PA32TS32D
ATMEL	AT27LV040A	DIP 32	
ATMEL	AT27LV040A	PLCC 32	PA32PL32D
ATMEL	AT27LV040A	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT27LV040A	sTSOP 32	PA32TS32D
ATMEL	AT27LV080	DIP 32	
ATMEL	AT27LV080	PLCC 32	PA32PL32D
ATMEL	AT27LV080	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT27LV080	SOIC 32	PA32SO32D-EO-450
ATMEL	AT27LV1024	DIP 40	
ATMEL	AT27LV1024	PLCC 44	PA44-48U
ATMEL	AT27LV1024	TSOP 40	PA40TS40D
ATMEL	AT27LV4096	DIP 40	
ATMEL	AT27LV4096	PLCC 44	PA44-48U
ATMEL	AT27LV4096	TSOP 40	PA40TS40D
ATMEL	AT27RW1024	PLCC 44	PA44-48U
ATMEL	AT28BV16	DIP 24	
ATMEL	AT28BV16	SOIC 24	PA28SO28D-EO-300
ATMEL	AT28BV16	PLCC 32	PA32PL32D
ATMEL	AT28BV16	TSOP 28	PA28TS28D-EO
ATMEL	AT28BV64	DIP 28	
ATMEL	AT28BV64	SOIC 28	PA28SO28D-EO-300
ATMEL	AT28BV64	PLCC 32	PA32PL28D-YA
ATMEL	AT28BV64	TSOP 28	PA28TS28D-EO
ATMEL	AT28BV64B	DIP 28	
ATMEL	AT28BV64B	SOIC 28	PA28SO28D-EO-300
ATMEL	AT28BV64B	PLCC 32	PA32PL28D-YA
ATMEL	AT28BV64B	TSOP 28	PA28TS28D-EO
ATMEL	AT28C16	DIP 24	
ATMEL	AT28C16	SOIC 24	PA28SO28D-EO-300
ATMEL	AT28C16	PLCC 32	PA32PL24D
ATMEL	AT28C16	TSOP 28	PA28TS28D-EO
ATMEL	AT28C16E	DIP 24	
ATMEL	AT28C16E	SOIC 24	PA28SO28D-EO-300
ATMEL	AT28C16E	PLCC 32	PA32PL24D
ATMEL	AT28C16E	TSOP 28	PA28TS28D-EO
ATMEL	AT28C17	DIP 28	
ATMEL	AT28C17	SOIC 24	PA28SO28D-EO-300
ATMEL	AT28C17	PLCC 32	PA32PL28D-YA
ATMEL	AT28C17	TSOP 28	PA28TS28D-EO
ATMEL	AT28C17E	DIP 28	
ATMEL	AT28C17E	SOIC 24	PA28SO28D-EO-300
ATMEL	AT28C17E	PLCC 32	PA32PL28D-YA
ATMEL	AT28C17E	TSOP 28	PA28TS28D-EO
ATMEL	AT28C64	DIP 28	
ATMEL	AT28C64	SOIC 24	PA28SO28D-EO-300
ATMEL	AT28C64	PLCC 32	PA32PL28D-YA
ATMEL	AT28C64	TSOP 28	PA28TS28D-EO

ATMEL	AT28C64B	DIP 28	
ATMEL	AT28C64B	SOIC 24	PA28SO28D-EO-300
ATMEL	AT28C64B	PLCC 32	PA32PL28D-YA
ATMEL	AT28C64B	TSOP 28	PA28TS28D-EO
ATMEL	AT28C64E	DIP 28	
ATMEL	AT28C64E	SOIC 24	PA28SO28D-EO-300
ATMEL	AT28C64E	PLCC 32	PA32PL28D-YA
ATMEL	AT28C64E	TSOP 28	PA28TS28D-EO
ATMEL	AT28C64X	DIP 28	
ATMEL	AT28C64X	SOIC 24	PA28SO28D-EO-300
ATMEL	AT28C64X	PLCC 32	PA32PL28D-YA
ATMEL	AT28C64X	TSOP 28	PA28TS28D-EO
ATMEL	AT28C256	DIP 28	
ATMEL	AT28C256	TSOP 28	PA28TS28D-EO
ATMEL	AT28C256	PLCC 32	PA32PL28D-YA
ATMEL	AT28C256	SOIC 28	PA28SO28D-EO-300
ATMEL	AT28C256E	DIP 28	
ATMEL	AT28C256E	TSOP 28	PA28TS28D-EO
ATMEL	AT28C256E	PLCC 32	PA32PL28D-YA
ATMEL	AT28C256E	SOIC 28	PA28SO28D-EO-300
ATMEL	AT28C256F	DIP 28	
ATMEL	AT28C256F	TSOP 28	PA28TS28D-EO
ATMEL	AT28C256F	PLCC 32	PA32PL28D-YA
ATMEL	AT28C256F	SOIC 28	PA28SO28D-EO-300
ATMEL	AT28C010	DIP 32	
ATMEL	AT28C010	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT28C010	PLCC 32	PA32PL28D-YA
ATMEL	AT28C010E	DIP 32	
ATMEL	AT28C010E	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT28C010E	PLCC 32	PA32PL28D-YA
ATMEL	AT28C020	DIP 32	
ATMEL	AT28C040	DIP 32	
ATMEL	AT28HC16	DIP 24	
ATMEL	AT28HC16L	DIP 24	
ATMEL	AT28HC64	DIP 28	
ATMEL	AT28HC64	SOIC 24	PA28SO28D-EO-300
ATMEL	AT28HC64	PLCC 32	PA32PL28D-YA
ATMEL	AT28HC64	TSOP 28	PA28TS28D-EO
ATMEL	AT28HC64B	DIP 28	
ATMEL	AT28HC64B	SOIC 24	PA28SO28D-EO-300
ATMEL	AT28HC64B	PLCC 32	PA32PL28D-YA
ATMEL	AT28HC64B	TSOP 28	PA28TS28D-EO
ATMEL	AT28HC256	DIP 28	
ATMEL	AT28HC256	TSOP 28	PA28TS28D-EO
ATMEL	AT28HC256	PLCC 32	PA32PL28D-YA
ATMEL	AT28HC256	SOIC 28	PA28SO28D-EO-300
ATMEL	AT28HC256E	DIP 28	
ATMEL	AT28HC256E-normalWrite	DIP 28	
ATMEL	AT28HC256E	TSOP 28	PA28TS28D-EO
ATMEL	AT28HC256E	PLCC 32	PA32PL28D-YA
ATMEL	AT28HC256E	SOIC 28	PA28SO28D-EO-300
ATMEL	AT28HC256F	DIP 28	
ATMEL	AT28HC256F	TSOP 28	PA28TS28D-EO
ATMEL	AT28HC256F	PLCC 32	PA32PL28D-YA
ATMEL	AT28HC256F	SOIC 28	PA28SO28D-EO-300
ATMEL	AT28HC256N	PLCC 32	PA32PL28D-YA
ATMEL	AT28MC010	DIP 32	
ATMEL	AT28MC040	DIP 32	
ATMEL	AT28PC64	DIP 28	
ATMEL	AT28PC64	SOIC 24	PA28SO28D-EO-300
ATMEL	AT28PC64	PLCC 32	PA32PL28D-YA
ATMEL	AT28PC64	TSOP 28	PA28TS28D-EO
ATMEL	AT28PC64E	DIP 28	
ATMEL	AT28BV256	DIP 28	
ATMEL	AT28BV256	SOIC 28	PA28SO28D-EO-300
ATMEL	AT28BV256	PLCC 32	PA32PL28D-YA
ATMEL	AT28BV256	TSOP 28	PA28TS28D-EO
ATMEL	AT28LV64	DIP 28	
ATMEL	AT28LV64	SOIC 24	PA28SO28D-EO-300
ATMEL	AT28LV64	PLCC 32	PA32PL28D-YA
ATMEL	AT28LV64	TSOP 28	PA28TS28D-EO
ATMEL	AT28LV64B	DIP 28	
ATMEL	AT28LV64B	SOIC 24	PA28SO28D-EO-300

ATMEL	AT28LV64B	PLCC 32	PA32PL28D-YA
ATMEL	AT28LV64B	TSOP 28	PA28TS28D-EO
ATMEL	AT28LV256	DIP 28	
ATMEL	AT28LV256	TSOP 28	PA28TS28D-EO
ATMEL	AT28LV256	PLCC 32	PA32PL28D-YA
ATMEL	AT28LV256	SOIC 28	PA28SO28D-EO-300
ATMEL	AT28LV010	DIP 32	
ATMEL	AT28LV010	PLCC 32	PA32PL32D
ATMEL	AT28LV010	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT29BV256	DIP 28	
ATMEL	AT29BV010A	DIP 32	
ATMEL	AT29BV010A	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT29BV010A	PLCC 32	PA32PL32D
ATMEL	AT29BV020	DIP 32	
ATMEL	AT29BV020	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT29BV020	PLCC 32	PA32PL32D
ATMEL	AT29BV040A	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT29C256	DIP 28	
ATMEL	AT29C256	PLCC 32	PA32PL28D-YA
ATMEL	AT29C257	DIP 32	
ATMEL	AT29C257	PLCC 32	PA32PL32D
ATMEL	AT29C512	DIP 32	
ATMEL	AT29C512	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT29C512	PLCC 32	PA32PL32D
ATMEL	AT29C010	DIP 32	
ATMEL	AT29C010	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT29C010	PLCC 32	PA32PL32D
ATMEL	AT29C010A	DIP 32	
ATMEL	AT29C010A	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT29C010A	PLCC 32	PA32PL32D
ATMEL	AT29C020	DIP 32	
ATMEL	AT29C020	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT29C020	PLCC 32	PA32PL32D
ATMEL	AT29C040	DIP 32	
ATMEL	AT29C040	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT29C040	PLCC 32	PA32PL32D
ATMEL	AT29C040A	DIP 32	
ATMEL	AT29C040A	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT29C040A	PLCC 32	PA32PL32D
ATMEL	AT29LV256	DIP 28	
ATMEL	AT29LV256	PLCC 32	PA32PL28D-YA
ATMEL	AT29LV512	DIP 32	
ATMEL	AT29LV512	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT29LV512	PLCC 32	PA32PL32D
ATMEL	AT29LV010	DIP 32	
ATMEL	AT29LV010	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT29LV010	PLCC 32	PA32PL32D
ATMEL	AT29LV010A	DIP 32	
ATMEL	AT29LV010A	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT29LV010A	PLCC 32	PA32PL32D
ATMEL	AT29LV020	DIP 32	
ATMEL	AT29LV020	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT29LV020	PLCC 32	PA32PL32D
ATMEL	AT29LV040A	DIP 32	
ATMEL	AT29LV040A	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT29LV040A	PLCC 32	PA32PL32D
ATMEL	AT28C1024	DIP 40	
ATMEL	AT28C1024	PLCC 44	PA44-48U
ATMEL	AT29C1024	DIP 40	
ATMEL	AT29C1024	PLCC 44	PA44-48U
ATMEL	AT29C1024	TSOP 48	PA48TS48D
ATMEL	AT29LV1024	DIP 40	
ATMEL	AT29LV1024	PLCC 44	PA44-48U
ATMEL	AT29LV1024	TSOP 48	PA48TS48D
ATMEL	AT29BV1024	DIP 40	
ATMEL	AT29BV1024	PLCC 44	PA44-48U
ATMEL	AT45D011	SOP 8	PA20SO20D-EO-210
ATMEL	AT45D011	PLCC 32	PA32PL32D
ATMEL	AT45DB011	SOP 8	PA20SO20D-EO-210
ATMEL	AT45DB011	PLCC 32	PA32PL32D
ATMEL	AT45DB011B	SOP 8	PA20SO20D-EO-210
ATMEL	AT45DB011B	PLCC 32	PA32PL32D
ATMEL	AT45DB011B	TSSOP 14	PA24TSS24D

ATMEL	AT45DB011D	SOIC 8	PA16SO16D-EO-150
ATMEL	AT45DB011D	SOIC 8	PA20SO20D-EO-210
ATMEL	AT45DB011D	CASON 8	PA8SON8D
ATMEL	AT45D021	PLCC 32	PA32PL32D
ATMEL	AT45D021	SOP 28	PA28SO28DB-EC-350
ATMEL	AT45D021	TSOP 28	PA28TS28D-EO
ATMEL	AT45DB021	PLCC 32	PA32PL32D
ATMEL	AT45DB021	SOP 28	PA28SO28DB-EC-350
ATMEL	AT45DB021	TSOP 28	PA28TS28D-EO
ATMEL	AT45DB021B	SOP 28	PA28SO28DB-EC-350
ATMEL	AT45DB021B	TSOP 28	PA28TS28D-EO
ATMEL	AT45DB021B	SOIC 8	PA20SO20D-EO-210
ATMEL	AT45DB021D	SOIC 8	PA16SO16D-EO-150
ATMEL	AT45DB021D	SOIC 8	PA20SO20D-EO-210
ATMEL	AT45D041	PLCC 32	PA32PL32D
ATMEL	AT45D041	SOP 28	PA28SO28DB-EC-350
ATMEL	AT45D041	TSOP 28	PA28TS28D-EO
ATMEL	AT45DB041	PLCC 32	PA32PL32D
ATMEL	AT45DB041	SOP 28	PA28SO28DB-EC-350
ATMEL	AT45DB041	TSOP 28	PA28TS28D-EO
ATMEL	AT45DB041B	CASON 8	PA8SON20D
ATMEL	AT45DB041B	SOP 8	PA20SO20D-EO-210
ATMEL	AT45DB041B	SOP 28	PA28SO28DB-EC-350
ATMEL	AT45DB041B	TSOP 28	PA28TS28D-EO
ATMEL	AT45DB041D	SOIC 8	PA20SO20D-EO-210
ATMEL	AT45DB041D	SOIC 8	PA16SO16D-EO-150
ATMEL	AT45D081	SOP 28	PA28SO28DB-EC-350
ATMEL	AT45D081	TSOP 32	PA48TS48D
ATMEL	AT45D081	TSOP 32	PA48TS48D
ATMEL	AT45DB081	SOP 28	PA28SO28DB-EC-350
ATMEL	AT45DB081	TSOP 32	PA48TS48D
ATMEL	AT45DB081B	CASON 8	PA8SON20D
ATMEL	AT45DB081B	TSOP 32	PA48TS48D
ATMEL	AT45DB081B	TSOP 28	PA28TS28D-EO
ATMEL	AT45DB081D	SOP 8	PA20SO20D-EO-210
ATMEL	AT45DB081D	MLF 8	PA8SON8D
ATMEL	AT45D161	PLCC 32	PA32PL32D
ATMEL	AT45D161	SOP 28	PA28SO28DB-EC-350
ATMEL	AT45D161	TSOP 28	PA28TS28D-EO
ATMEL	AT45DB161	PLCC 32	PA32PL32D
ATMEL	AT45DB161	SOP 28	PA28SO28DB-EC-350
ATMEL	AT45DB161	TSOP 28	PA28TS28D-EO
ATMEL	AT45DB161D	SOIC 8	PA20SO20D-EO-210
ATMEL	AT45DB161D	TSOP 28	PA28TS28D-EO
ATMEL	AT45DB161B	CASON 8	PA8SON20D
ATMEL	AT45DB161B	SOP 28	PA28SO28DB-EC-350
ATMEL	AT45DB161B	TSOP 28	PA28TS28D-EO
ATMEL	AT45DB321	SOP 28	PA28SO28DB-EC-350
ATMEL	AT45DB321	TSOP 32	PA48TS48D
ATMEL	AT45DB321	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT45DB321B	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT45DB321C	TSOP 28	PA28TS28D-EO
ATMEL	AT45DB321D	SOIC 8	PA20SO20D-EO-210
ATMEL	AT45DB642D	TSOP 28	PA28TS28D-EO
ATMEL	AT45DCB002	CASON 8	HA8SON48DB
ATMEL	AT45DCB004	SOP 28	PAAT02-04A
ATMEL	AT45DCB008	SOP 28	PAAT02-04A
ATMEL	AT49BV512	DIP 32	
ATMEL	AT49BV512	PLCC 32	PA32PL32D
ATMEL	AT49BV512	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV512	SSOP 32	PA32TS32D
ATMEL	AT49BV010	DIP 32	
ATMEL	AT49BV010	PLCC 32	PA32PL32D
ATMEL	AT49BV010	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV020	DIP 32	
ATMEL	AT49BV020	PLCC 32	PA32PL32D
ATMEL	AT49BV020	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV020	SSOP 32	PA32TS32D
ATMEL	AT49BV040	DIP 32	
ATMEL	AT49BV040	PLCC 32	PA32PL32D
ATMEL	AT49BV040	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV040	SSOP 32	PA32TS32D

ATMEL	AT49BV040B	PLCC 32	PA32PL32D
ATMEL	AT49BV040T	DIP 32	
ATMEL	AT49BV040T	PLCC 32	PA32PL32D
ATMEL	AT49BV040T	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV040T	SSOP 32	PA32TS32D
ATMEL	AT49BV080	SOP 44	PA44SO44D
ATMEL	AT49BV080	TSOP 40	PA40TS40D
ATMEL	AT49BV080T	SOP 44	PA44SO44D
ATMEL	AT49BV080T	TSOP 40	PA40TS40D
ATMEL	AT49BV1024A	SOP 40	PA44SO44D
ATMEL	AT49BV2048	SOP 44	PA44SO44D
ATMEL	AT49BV2048	TSOP 48	PA48TS48D
ATMEL	AT49BV2048A	SOP 44	PA44SO44D
ATMEL	AT49BV2048A	TSOP 48	PA48TS48D
ATMEL	AT49BV4096	SOP 44	PA44SO44D
ATMEL	AT49BV4096	TSOP 48	PA48TS48D
ATMEL	AT49BV4096A	SOP 44	PA44SO44D
ATMEL	AT49BV4096A	TSOP 48	PA48TS48D
ATMEL	AT49BV4096AT	SOP 44	PA44SO44D
ATMEL	AT49BV4096AT	TSOP 48	PA48TS48D
ATMEL	AT49BV802A	TSOP 48	PA48TS48D
ATMEL	AT49SV802A	TSOP 48	HA48TS48DJ
ATMEL	AT49SV802A	BGA 48	HA48BG48DAY
ATMEL	AT49BV802AT	TSOP 48	PA48TS48D
ATMEL	AT49SV802AT	TSOP 48	HA48TS48DJ
ATMEL	AT49SV802AT	BGA 48	HA48BG48DAY
ATMEL	AT49BV8004	TSOP 48	PA48TS48D
ATMEL	AT49BV8004T	TSOP 48	PA48TS48D
ATMEL	AT49BV8011	TSOP 48	PA48TS48D
ATMEL	AT49BV8011T	TSOP 48	PA48TS48D
ATMEL	AT49BV8192	SOP 44	PA44SO44D
ATMEL	AT49BV8192	TSOP 48	PA48TS48D
ATMEL	AT49BV8192T	TSOP 48	PA48TS48D
ATMEL	AT49BV8192A	TSOP 48	PA48TS48D
ATMEL	AT49BV8192AT	TSOP 48	PA48TS48D
ATMEL	AT49BV160C	TSOP 48	PA48TS48D
ATMEL	AT49BV160CT	TSOP 48	PA48TS48D
ATMEL	AT49BV163A	TSOP 48	PA48TS48D
ATMEL	AT49BV320C	TSOP 48	PA48TS48D
ATMEL	AT49BV320CT	TSOP 48	PA48TS48D
ATMEL	AT49BV320D	TSOP 48	PA48TS48D
ATMEL	AT49BV320DT	TSOP 48	PA48TS48D
ATMEL	AT49BV001	DIP 32	
ATMEL	AT49BV001	PLCC 32	PA32PL32D
ATMEL	AT49BV001	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV001	SSOP 32	PA32TS32D
ATMEL	AT49BV001N	DIP 32	
ATMEL	AT49BV001N	PLCC 32	PA32PL32D
ATMEL	AT49BV001N	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV001N	SSOP 32	PA32TS32D
ATMEL	AT49BV001T	DIP 32	
ATMEL	AT49BV001T	PLCC 32	PA32PL32D
ATMEL	AT49BV001T	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV001T	SSOP 32	PA32TS32D
ATMEL	AT49BV001NT	DIP 32	
ATMEL	AT49BV001NT	PLCC 32	PA32PL32D
ATMEL	AT49BV001NT	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV001NT	SSOP 32	PA32TS32D
ATMEL	AT49BV001A	PLCC 32	PA32PL32D
ATMEL	AT49BV001A	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV001A	SSOP 32	PA32TS32D
ATMEL	AT49BV001AN	PLCC 32	PA32PL32D
ATMEL	AT49BV001AN	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV001AN	SSOP 32	PA32TS32D
ATMEL	AT49BV001AT	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV001AT	SSOP 32	PA32TS32D
ATMEL	AT49BV001AT	PLCC 32	PA32PL32D
ATMEL	AT49BV001ANT	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV001ANT	SSOP 32	PA32TS32D
ATMEL	AT49BV001ANT	PLCC 32	PA32PL32D
ATMEL	AT49BV002	DIP 32	
ATMEL	AT49BV002	PLCC 32	PA32PL32D
ATMEL	AT49BV002	TSOP 32	PA32TS20/PA32TS32D-20

ATMEL	AT49BV002	SSOP 32	PA32TS32D
ATMEL	AT49BV002N	DIP 32	
ATMEL	AT49BV002N	PLCC 32	PA32PL32D
ATMEL	AT49BV002N	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV002N	SSOP 32	PA32TS32D
ATMEL	AT49BV002T	DIP 32	
ATMEL	AT49BV002T	PLCC 32	PA32PL32D
ATMEL	AT49BV002T	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV002T	SSOP 32	PA32TS32D
ATMEL	AT49BV002NT	DIP 32	
ATMEL	AT49BV002NT	PLCC 32	PA32PL32D
ATMEL	AT49BV002NT	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV002NT	SSOP 32	PA32TS32D
ATMEL	AT49BV002A	DIP 32	
ATMEL	AT49BV002A	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV002A	PLCC 32	PA32PL32D
ATMEL	AT49BV002A	SSOP 32	PA32TS32D
ATMEL	AT49BV002AT	DIP 32	
ATMEL	AT49BV002AT	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV002AT	PLCC 32	PA32PL32D
ATMEL	AT49BV002AT	SSOP 32	PA32TS32D
ATMEL	AT49BV002ANT	DIP 32	
ATMEL	AT49BV002ANT	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV002ANT	PLCC 32	PA32PL32D
ATMEL	AT49BV002ANT	SSOP 32	PA32TS32D
ATMEL	AT49BV002AN	DIP 32	
ATMEL	AT49BV002AN	PLCC 32	PA32PL32D
ATMEL	AT49BV002AN	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV002AN	SSOP 32	PA32TS32D
ATMEL	AT49BV008A	TSOP 40	PA40TS40D
ATMEL	AT49BV008AT	TSOP 40	PA40TS40D
ATMEL	AT49BV040A	PLCC 32	PA32PL32D
ATMEL	AT49BV040A	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV040A	SSOP 32	PA32TS32D
ATMEL	AT49BV160	TSOP 48	PA48TS48D
ATMEL	AT49BV160T	TSOP 48	PA48TS48D
ATMEL	AT49BV160C	TSOP 48	PA48TS48D
ATMEL	AT49BV160CT	TSOP 48	PA48TS48D
ATMEL	AT49BV161	TSOP 48	PA48TS48D
ATMEL	AT49BV161T	TSOP 48	PA48TS48D
ATMEL	AT49BV162A	TSOP 48	PA48TS48D
ATMEL	AT49BV162AT	TSOP 48	PA48TS48D
ATMEL	AT49BV1604	TSOP 48	PA48TS48D
ATMEL	AT49BV1604T	TSOP 48	PA48TS48D
ATMEL	AT49BV1614	TSOP 48	PA48TS48D
ATMEL	AT49BV1614T	TSOP 48	PA48TS48D
ATMEL	AT49BV1604A	TSOP 48	PA48TS48D
ATMEL	AT49BV1604AT	TSOP 48	PA48TS48D
ATMEL	AT49BV1614A	TSOP 48	PA48TS48D
ATMEL	AT49BV1614AT	TSOP 48	PA48TS48D
ATMEL	AT49BV1618	TSOP 48	PA48TS48D
ATMEL	AT49BV1618T	TSOP 48	PA48TS48D
ATMEL	AT49BV320	TSOP 48	PA48TS48D
ATMEL	AT49BV320T	TSOP 48	PA48TS48D
ATMEL	AT49BV321	TSOP 48	PA48TS48D
ATMEL	AT49BV321T	TSOP 48	PA48TS48D
ATMEL	AT49BV320A	TSOP 48	PA48TS48D
ATMEL	AT49BV320AT	TSOP 48	PA48TS48D
ATMEL	AT49BV322A	TSOP 48	PA48TS48D
ATMEL	AT49BV322A	BGA 48	HA48BG48DAR
ATMEL	AT49BV322AT	TSOP 48	PA48TS48D
ATMEL	AT49BV322AT	BGA 48	HA48BG48DAR
ATMEL	AT49BV322D	TSOP 48	PA48TS48D
ATMEL	AT49BV322DT	TSOP 48	PA48TS48D
ATMEL	AT49SV322A	TSOP 48	HA48TS48DJ
ATMEL	AT49SV322AT	TSOP 48	HA48TS48DJ
ATMEL	AT49SV322D	TSOP 48	HA48TS48DJ
ATMEL	AT49SV322DT	TSOP 48	HA48TS48DJ
ATMEL	AT49BV6416	TSOP 48	PA48TS48D
ATMEL	AT49BV6416T	TSOP 48	PA48TS48D
ATMEL	AT49LL040	PLCC 32	PA32PL32D
ATMEL	AT49LW040	PLCC 32	PA32PL32D
ATMEL	AT49LW040	TSOP 40	PA40TS40D

ATMEL	AT49LW080	PLCC 32	PA32PL32D
ATMEL	AT49LW080	TSOP 40	PA40TS40D
ATMEL	AT49F001	DIP 32	
ATMEL	AT49F001	PLCC 32	PA32PL32D
ATMEL	AT49F001	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49F001N	DIP 32	
ATMEL	AT49F001N	PLCC 32	PA32PL32D
ATMEL	AT49F001N	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49F001T	DIP 32	
ATMEL	AT49F001T	PLCC 32	PA32PL32D
ATMEL	AT49F001T	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49F001NT	DIP 32	
ATMEL	AT49F001NT	PLCC 32	PA32PL32D
ATMEL	AT49F001NT	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49F001A	PLCC 32	PA32PL32D
ATMEL	AT49F001AN	PLCC 32	PA32PL32D
ATMEL	AT49F001A	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49F001AN	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49F001AT	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49F001ANT	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49F001A	SSOP 32	PA32TS32D
ATMEL	AT49F001AN	SSOP 32	PA32TS32D
ATMEL	AT49F001AT	SSOP 32	PA32TS32D
ATMEL	AT49F001ANT	SSOP 32	PA32TS32D
ATMEL	AT49F001A	PLCC 32	PA32PL32D
ATMEL	AT49F001AN	PLCC 32	PA32PL32D
ATMEL	AT49F001AT	PLCC 32	PA32PL32D
ATMEL	AT49F001ANT	PLCC 32	PA32PL32D
ATMEL	AT49F002	DIP 32	
ATMEL	AT49F002	PLCC 32	PA32PL32D
ATMEL	AT49F002	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49F002	SSOP 32	PA32TS32D
ATMEL	AT49F002N	DIP 32	
ATMEL	AT49F002N	PLCC 32	PA32PL32D
ATMEL	AT49F002N	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49F002N	SSOP 32	PA32TS32D
ATMEL	AT49F002T	DIP 32	
ATMEL	AT49F002T	PLCC 32	PA32PL32D
ATMEL	AT49F002T	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49F002T	SSOP 32	PA32TS32D
ATMEL	AT49F002NT	DIP 32	
ATMEL	AT49F002NT	PLCC 32	PA32PL32D
ATMEL	AT49F002NT	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49F002NT	SSOP 32	PA32TS32D
ATMEL	AT49F002A	PLCC 32	PA32PL32D
ATMEL	AT49F002A	DIP 32	
ATMEL	AT49F002A	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49F002A	SSOP 32	PA32TS32D
ATMEL	AT49F002AN	SSOP 32	PA32TS32D
ATMEL	AT49F002AN	DIP 32	
ATMEL	AT49F002AN	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49F002AN	PLCC 32	PA32PL32D
ATMEL	AT49F002AT	SSOP 32	PA32TS32D
ATMEL	AT49F002AT	DIP 32	
ATMEL	AT49F002AT	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49F002AT	PLCC 32	PA32PL32D
ATMEL	AT49F002ANT	DIP 32	
ATMEL	AT49F002ANT	SSOP 32	PA32TS32D
ATMEL	AT49F002ANT	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49F002ANT	PLCC 32	PA32PL32D
ATMEL	AT49F512	DIP 32	
ATMEL	AT49F512	PLCC 32	PA32PL32D
ATMEL	AT49F512	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49F512	SSOP 32	PA32TS32D
ATMEL	AT49F010	DIP 32	
ATMEL	AT49F010	PLCC 32	PA32PL32D
ATMEL	AT49F010	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49F020	DIP 32	
ATMEL	AT49F020	PLCC 32	PA32PL32D
ATMEL	AT49F020	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49F040	DIP 32	
ATMEL	AT49F040	PLCC 32	PA32PL32D
ATMEL	AT49F040	TSOP 32	PA32TS20/PA32TS32D-20

ATMEL	AT49F040T	DIP 32	
ATMEL	AT49F040T	PLCC 32	PA32PL32D
ATMEL	AT49F040T	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49F040A	DIP 32	
ATMEL	AT49F040A	PLCC 32	PA32PL32D
ATMEL	AT49F040A	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49F040B	PLCC 32	PA32PL32D
ATMEL	AT49F040B	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49F040B	SSOP 32	PA32TS32D
ATMEL	AT49F080	TSOP 40	PA40TS40D
ATMEL	AT49F080T	TSOP 40	PA40TS40D
ATMEL	AT49F1024	TSOP 40	PA40TS14-OT
ATMEL	AT49F1024	PLCC 44	PA44-48U
ATMEL	AT49F1024	TSOP 40	PA40TS40D
ATMEL	AT49F1024A	TSOP 40	PA40TS40D
ATMEL	AT49F1025	PLCC 44	PA44-48U
ATMEL	AT49F1025	SOP 40	PA44SO44D
ATMEL	AT49F2048	SOP 44	PA44SO44D
ATMEL	AT49F2048	TSOP 48	PA48TS48D
ATMEL	AT49F2048A	SOP 44	PA44SO44D
ATMEL	AT49F2048A	TSOP 48	PA48TS48D
ATMEL	AT49F4096	SOP 44	PA44SO44D
ATMEL	AT49F4096	TSOP 48	PA48TS48D
ATMEL	AT49F4096A	SOP 44	PA44SO44D
ATMEL	AT49F4096A	TSOP 48	PA48TS48D
ATMEL	AT49F4096AT	SOP 44	PA44SO44D
ATMEL	AT49F4096AT	TSOP 48	PA48TS48D
ATMEL	AT49F8004	TSOP 48	PA48TS48D
ATMEL	AT49F8004T	TSOP 48	PA48TS48D
ATMEL	AT49F8011	TSOP 48	PA48TS48D
ATMEL	AT49F8011T	TSOP 48	PA48TS48D
ATMEL	AT49F8192	SOP 44	PA44SO44D
ATMEL	AT49F8192	TSOP 48	PA48TS48D
ATMEL	AT49F8192T	SOP 44	PA44SO44D
ATMEL	AT49F8192T	TSOP 48	PA48TS48D
ATMEL	AT49F8192A	SOP 44	PA44SO44D
ATMEL	AT49F8192A	TSOP 48	PA48TS48D
ATMEL	AT49F8192AT	SOP 44	PA44SO44D
ATMEL	AT49F8192AT	TSOP 48	PA48TS48D
ATMEL	AT49F1604	TSOP 48	PA48TS48D
ATMEL	AT49F1604T	TSOP 48	PA48TS48D
ATMEL	AT49F1614	TSOP 48	PA48TS48D
ATMEL	AT49F1614T	TSOP 48	PA48TS48D
ATMEL	AT49F1618	TSOP 48	PA48TS48D
ATMEL	AT49F1618T	TSOP 48	PA48TS48D
ATMEL	AT49HF010	DIP 32	
ATMEL	AT49HF010	PLCC 32	PA32PL32D
ATMEL	AT49HF010	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49HBV010	PLCC 32	PA32PL32D
ATMEL	AT49HBV010	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49HLV010	PLCC 32	PA32PL32D
ATMEL	AT49HLV010	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49LH002-xxTC	TSOP 40	PA40TS40D
ATMEL	AT49LH004-xxTC	TSOP 40	PA40TS40D
ATMEL	AT49LH002-xxJC	PLCC 32	PA32PL32D
ATMEL	AT49LH004-xxJC	PLCC 32	PA32PL32D
ATMEL	AT49LH004-xxJC	PLCC 32	PA32PL32D
ATMEL	AT49LV001	DIP 32	
ATMEL	AT49LV001	PLCC 32	PA32PL32D
ATMEL	AT49LV001	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49LV001	SSOP 32	PA32TS32D
ATMEL	AT49LV001N	DIP 32	
ATMEL	AT49LV001N	PLCC 32	PA32PL32D
ATMEL	AT49LV001N	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49LV001N	SSOP 32	PA32TS32D
ATMEL	AT49LV001T	DIP 32	
ATMEL	AT49LV001T	PLCC 32	PA32PL32D
ATMEL	AT49LV001T	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49LV001T	SSOP 32	PA32TS32D
ATMEL	AT49LV001NT	DIP 32	
ATMEL	AT49LV001NT	PLCC 32	PA32PL32D
ATMEL	AT49LV001NT	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49LV001NT	SSOP 32	PA32TS32D



ATMEL	AT49LV002	DIP 32	
ATMEL	AT49LV002	PLCC 32	PA32PL32D
ATMEL	AT49LV002	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49LV002	SSOP 32	PA32TS32D
ATMEL	AT49LV002N	DIP 32	
ATMEL	AT49LV002N	PLCC 32	PA32PL32D
ATMEL	AT49LV002N	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49LV002N	SSOP 32	PA32TS32D
ATMEL	AT49LV002T	DIP 32	
ATMEL	AT49LV002T	PLCC 32	PA32PL32D
ATMEL	AT49LV002T	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49LV002T	SSOP 32	PA32TS32D
ATMEL	AT49LV002NT	DIP 32	
ATMEL	AT49LV002NT	PLCC 32	PA32PL32D
ATMEL	AT49LV002NT	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49LV002NT	SSOP 32	PA32TS32D
ATMEL	AT49LV010	DIP 32	
ATMEL	AT49LV010	PLCC 32	PA32PL32D
ATMEL	AT49LV010	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49LV020	DIP 32	
ATMEL	AT49LV020	PLCC 32	PA32PL32D
ATMEL	AT49LV020	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49LV020	SSOP 32	PA32TS32D
ATMEL	AT49LV040	DIP 32	
ATMEL	AT49LV040	PLCC 32	PA32PL32D
ATMEL	AT49LV040	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49LV040	SSOP 32	PA32TS32D
ATMEL	AT49LV040T	DIP 32	
ATMEL	AT49LV040T	PLCC 32	PA32PL32D
ATMEL	AT49LV040T	TSOP 32	PA32TS20/PA32TS32D-20
ATMEL	AT49LV080	SOP 44	PA44SO44D
ATMEL	AT49LV080T	SOP 44	PA44SO44D
ATMEL	AT49LV080	TSOP 40	PA40TS40D
ATMEL	AT49LV080T	TSOP 40	PA40TS40D
ATMEL	AT49LV1025	PLCC 44	PA44-48U
ATMEL	AT49LV2048	SOP 44	PA44SO44D
ATMEL	AT49LV2048	TSOP 48	PA48TS48D
ATMEL	AT49LV4096A	SOP 44	PA44SO44D
ATMEL	AT49LV4096A	TSOP 48	PA48TS48D
ATMEL	AT49LV8192A	TSOP 48	PA48TS48D
ATMEL	AT49LV1614	TSOP 48	PA48TS48D
ATMEL	AT49LV1614T	TSOP 48	PA48TS48D
ATMEL	AT49LV1614A	TSOP 48	PA48TS48D
ATMEL	AT49LV1614AT	TSOP 48	PA48TS48D
ATMEL	AT59C11	DIP 8	
ATMEL	AT59C22	DIP 8	
ATMEL	AT59C13	DIP 8	
ATMEL	AT93C46	DIP 8	
ATMEL	AT93C46	TSSOP 8	PA8TSS-OT
ATMEL	AT93C46	SOIC 8	PA16SO16D-EO-150
ATMEL	AT93C46R	SOIC 8	PA8SO8D-EO-150
ATMEL	AT93C46A	DIP 8	
ATMEL	AT93C46A	TSSOP 8	PA8TSS-OT
ATMEL	AT93C46A	SOIC 8	PA16SO16D-EO-150
ATMEL	AT93C56	DIP 8	
ATMEL	AT93C56	TSSOP 8	PA8TSS-OT
ATMEL	AT93C56	SOIC 8	PA16SO16D-EO-150
ATMEL	AT93C56R	SOIC 8	PA8SO8D-EO-150
ATMEL	AT93C56A	DIP 8	
ATMEL	AT93C56A	TSSOP 8	PA8TSS-OT
ATMEL	AT93C56A	SOIC 8	PA16SO16D-EO-150
ATMEL	AT93C57	DIP 8	
ATMEL	AT93C57	SOIC 8	PA16SO16D-EO-150
ATMEL	AT93C66	DIP 8	
ATMEL	AT93C66	TSSOP 8	PA8TSS-OT
ATMEL	AT93C66	SOIC 8	PA16SO16D-EO-150
ATMEL	AT93C66R	SOIC 8	PA8SO8D-EO-150
ATMEL	AT93C66A	DIP 8	
ATMEL	AT93C66A	TSSOP 8	PA8TSS-OT
ATMEL	AT93C66A	SOIC 8	PA16SO16D-EO-150
ATMEL	AT93C66B-XHM	TSSOP 8	PA8TSS8D
ATMEL	AT93C86	DIP 8	
ATMEL	AT93C86	TSSOP 8	PA8TSS-OT

ATMEL	AT93C86	SOIC 8	PA16SO16D-EO-150
ATMEL	AT93C86A	DIP 8	
ATMEL	AT93C86A	TSSOP 8	PA8TSS-OT
ATMEL	AT93C86A	SOIC 8	PA16SO16D-EO-150
BMT	BM29LV160B	TSOP 48	PA48TS48D
BMT	BM29LV160T	TSOP 48	PA48TS48D
BENCHMARK	BQ4011	EDIP 28	
BENCHMARK	BQ4011Y	EDIP 28	
BENCHMARK	BQ4013	EDIP 32	
BENCHMARK	BQ4013Y	EDIP 32	
BRIGHT	BM29F040	DIP 32	
BRIGHT	BM29F040	PLCC 32	PA32PL32D
BRIGHT	BM29F040	TSOP 32	PA32TS20/PA32TS32D-20
BRIGHT	BM29F400B	SOP 44	PA44SO44D
BRIGHT	BM29F400B	TSOP 48	PA48TS48D
BRIGHT	BM29F400T	SOP 44	PA44SO44D
BRIGHT	BM29F400T	TSOP 48	PA48TS48D
CATALYST	CAT24AC128	DIP 8	
CATALYST	CAT24AC128-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24AC128-K	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT24AC128-U14	TSSOP 14	PA28TSS28D-EO
CATALYST	CAT24AC128-L	DIP 8	
CATALYST	CAT24AC128-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24AC128-X	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT24AC128-Y14	TSSOP 14	PA28TSS28D-EO
CATALYST	CAT24C00	DIP 8	
CATALYST	CAT24C00-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C00-U	TSSOP 8	PA8TSS8D
CATALYST	CAT24C00-U	TSSOP 8	PA24TSS24D
CATALYST	CAT24C00-TP	SOT23- 5	PA5SOT5D
CATALYST	CAT24C00-L	DIP 8	
CATALYST	CAT24C00-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C00-Y	TSSOP 8	PA8TSS8D
CATALYST	CAT24C00-Y	TSSOP 8	PA24TSS24D
CATALYST	CAT24C00-TB	SOT23- 5	PA5SOT5D
CATALYST	CAT24C01	DIP 8	
CATALYST	CAT24C01-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C01-J14	SOIC 14	PA16SO16D-EO-150
CATALYST	CAT24C01-U	TSSOP 8	PA8TSS8D
CATALYST	CAT24C01-U	TSSOP 8	PA24TSS24D
CATALYST	CAT24C01B	DIP 8	
CATALYST	CAT24C01B-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C01B-R	MSOP 8	PA8MSOP8D
CATALYST	CAT24C01B-U	TSSOP 8	PA8TSS8D
CATALYST	CAT24C01B-U	TSSOP 8	PA24TSS24D
CATALYST	CAT24C01B-L	DIP 8	
CATALYST	CAT24C01B-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C01B-Z	MSOP 8	PA8MSOP8D
CATALYST	CAT24C01B-Y	TSSOP 8	PA8TSS8D
CATALYST	CAT24C01B-Y	TSSOP 8	PA24TSS24D
CATALYST	CAT24C21B	DIP 8	
CATALYST	CAT24C21B-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C21B-R	MSOP 8	PA8MSOP8D
CATALYST	CAT24C21B-U	TSSOP 8	PA8TSS8D
CATALYST	CAT24C21B-U	TSSOP 8	PA24TSS24D
CATALYST	CAT24C21B-L	DIP 8	
CATALYST	CAT24C21B-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C21B-Z	MSOP 8	PA8MSOP8D
CATALYST	CAT24C21B-Y	TSSOP 8	PA8TSS8D
CATALYST	CAT24C21B-Y	TSSOP 8	PA24TSS24D
CATALYST	CAT24C02	DIP 8	
CATALYST	CAT24C02-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C02-J14	SOIC 14	PA16SO16D-EO-150
CATALYST	CAT24C02-U	TSSOP 8	PA8TSS8D
CATALYST	CAT24C02-U	TSSOP 8	PA24TSS24D
CATALYST	CAT24C021	DIP 8	
CATALYST	CAT24C021-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C022	DIP 8	
CATALYST	CAT24C022-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C023	DIP 8	
CATALYST	CAT24C023-J	SOIC 8	PA8SO8D-EO-150
ON SEMICONDUCTOR	CAT24C03WI	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C04	DIP 8	

CATALYST	CAT24C04-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C04-J14	SOIC 14	PA16SO16D-EO-150
CATALYST	CAT24C04-U	TSSOP 8	PA8TSS8D
CATALYST	CAT24C04-U	TSSOP 8	PA24TSS24D
CATALYST	CAT24C041	DIP 8	
CATALYST	CAT24C041-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C042	DIP 8	
CATALYST	CAT24C042-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C043	DIP 8	
CATALYST	CAT24C043-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C08	DIP 8	
CATALYST	CAT24C08-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C08-J14	SOIC 14	PA16SO16D-EO-150
CATALYST	CAT24C08-U	TSSOP 8	PA8TSS8D
CATALYST	CAT24C08-U	TSSOP 8	PA24TSS24D
CATALYST	CAT24C081	DIP 8	
CATALYST	CAT24C081-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C082	DIP 8	
CATALYST	CAT24C082-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C083	DIP 8	
CATALYST	CAT24C083-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C16	DIP 8	
CATALYST	CAT24C16-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C16-J14	SOIC 14	PA16SO16D-EO-150
CATALYST	CAT24C16-U	TSSOP 8	PA8TSS8D
CATALYST	CAT24C16-U	TSSOP 8	PA24TSS24D
CATALYST	CAT24C161	DIP 8	
CATALYST	CAT24C161-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C162	DIP 8	
CATALYST	CAT24C162-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C163	DIP 8	
CATALYST	CAT24C163-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C32-L	DIP 8	
CATALYST	CAT24C32-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C32-Y	TSSOP 8	PA8TSS8D
CATALYST	CAT24C32-Y	TSSOP 8	PA24TSS24D
CATALYST	CAT24C321	DIP 8	
CATALYST	CAT24C321-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C322	DIP 8	
CATALYST	CAT24C322-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C323	DIP 8	
CATALYST	CAT24C323-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C64-L	DIP 8	
CATALYST	CAT24C64-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C64-Y	TSSOP 8	PA8TSS8D
CATALYST	CAT24C64-Y	TSSOP 8	PA24TSS24D
CATALYST	CAT24C641	DIP 8	
CATALYST	CAT24C641-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C642	DIP 8	
CATALYST	CAT24C642-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C643	DIP 8	
CATALYST	CAT24C643-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24C256-L	DIP 8	
CATALYST	CAT24C256-W	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT24C256-X	SOIC 8	PA20SO20D-EO-210
CATALYST	CAT24FC01	DIP 8	
CATALYST	CAT24FC01-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24FC01-R	MSOP 8	PA8MSOP8D
CATALYST	CAT24FC01-U	TSSOP 8	PA8TSS8D
CATALYST	CAT24FC01-U	TSSOP 8	PA24TSS24D
CATALYST	CAT24FC01-L	DIP 8	
CATALYST	CAT24FC01-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24FC01-Z	MSOP 8	PA8MSOP8D
CATALYST	CAT24FC01-Y	TSSOP 8	PA8TSS8D
CATALYST	CAT24FC01-Y	TSSOP 8	PA24TSS24D
CATALYST	CAT24FC02	DIP 8	
CATALYST	CAT24FC02-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24FC02-R	MSOP 8	PA8MSOP8D
CATALYST	CAT24FC02-U	TSSOP 8	PA8TSS8D
CATALYST	CAT24FC02-U	TSSOP 8	PA24TSS24D
CATALYST	CAT24FC02-L	DIP 8	
CATALYST	CAT24FC02-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24FC02-Z	MSOP 8	PA8MSOP8D

CATALYST	CAT24FC02-Y	TSSOP 8	PA8TSS8D
CATALYST	CAT24FC02-Y	TSSOP 8	PA24TSS24D
CATALYST	CAT24FC02-GL	DIP 8	
CATALYST	CAT24FC02-GW	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24FC02-GZ	MSOP 8	PA8MSOP8D
CATALYST	CAT24FC02-GY	TSSOP 8	PA8TSS8D
CATALYST	CAT24FC02-GY	TSSOP 8	PA24TSS24D
CATALYST	CAT24FC16	DIP 8	
CATALYST	CAT24FC16-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24FC16-R	MSOP 8	PA8MSOP8D
CATALYST	CAT24FC16-U	TSSOP 8	PA8TSS8D
CATALYST	CAT24FC16-U	TSSOP 8	PA24TSS24D
CATALYST	CAT24FC16-RD4	TDFN 8	PA8TDFN8D
CATALYST	CAT24FC16-L	DIP 8	
CATALYST	CAT24FC16-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24FC16-Z	MSOP 8	PA8MSOP8D
CATALYST	CAT24FC16-Y	TSSOP 8	PA8TSS8D
CATALYST	CAT24FC16-Y	TSSOP 8	PA24TSS24D
CATALYST	CAT24FC16-ZD4	TDFN 8	PA8TDFN8D
CATALYST	CAT24FC17	DIP 8	
CATALYST	CAT24FC17-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24FC17-R	MSOP 8	PA8MSOP8D
CATALYST	CAT24FC17-U	TSSOP 8	PA8TSS8D
CATALYST	CAT24FC17-U	TSSOP 8	PA24TSS24D
CATALYST	CAT24FC17-RD4	TDFN 8	PA8TDFN8D
CATALYST	CAT24FC17-L	DIP 8	
CATALYST	CAT24FC17-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24FC17-Z	MSOP 8	PA8MSOP8D
CATALYST	CAT24FC17-Y	TSSOP 8	PA8TSS8D
CATALYST	CAT24FC17-Y	TSSOP 8	PA24TSS24D
CATALYST	CAT24FC17-ZD4	TDFN 8	PA8TDFN8D
CATALYST	CAT24FC17-GL	DIP 8	
CATALYST	CAT24FC17-GW	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24FC17-GZ	MSOP 8	PA8MSOP8D
CATALYST	CAT24FC17-GY	TSSOP 8	PA8TSS8D
CATALYST	CAT24FC17-GY	TSSOP 8	PA24TSS24D
CATALYST	CAT24FC17-GD4	TDFN 8	PA8TDFN8D
CATALYST	CAT24FC32	DIP 8	
CATALYST	CAT24FC32-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24FC32-K	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT24FC32-U	TSSOP 8	PA8TSS8D
CATALYST	CAT24FC32-U	TSSOP 8	PA24TSS24D
CATALYST	CAT24FC32-RD2	TDFN 8	PA8TDFN8D
CATALYST	CAT24FC32-L	DIP 8	
CATALYST	CAT24FC32-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24FC32-X	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT24FC32-Y	TSSOP 8	PA8TSS8D
CATALYST	CAT24FC32-Y	TSSOP 8	PA24TSS24D
CATALYST	CAT24FC32-ZD2	TDFN 8	PA8TDFN8D
CATALYST	CAT24FC32-GL	DIP 8	
CATALYST	CAT24FC32-GW	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24FC32-GX	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT24FC32-GY	TSSOP 8	PA8TSS8D
CATALYST	CAT24FC32-GY	TSSOP 8	PA24TSS24D
CATALYST	CAT24FC32A	DIP 8	
CATALYST	CAT24FC32A-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24FC32A-K	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT24FC32A-U	TSSOP 8	PA8TSS8D
CATALYST	CAT24FC32A-U	TSSOP 8	PA24TSS24D
CATALYST	CAT24FC32A-L	DIP 8	
CATALYST	CAT24FC32A-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24FC32A-X	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT24FC32A-Y	TSSOP 8	PA8TSS8D
CATALYST	CAT24FC32A-Y	TSSOP 8	PA24TSS24D
CATALYST	CAT24FC64	DIP 8	
CATALYST	CAT24FC64-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24FC64-K	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT24FC64-U	TSSOP 8	PA8TSS8D
CATALYST	CAT24FC64-U	TSSOP 8	PA24TSS24D
CATALYST	CAT24FC64-RD2	TDFN 8	PA8TDFN8D
CATALYST	CAT24FC64-L	DIP 8	
CATALYST	CAT24FC64-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24FC64-X	SOIC 8	PA16SO16D-EO-150

CATALYST	CAT24FC64-Y	TSSOP 8	PA8TSS8D
CATALYST	CAT24FC64-Y	TSSOP 8	PA24TSS24D
CATALYST	CAT24FC64-ZD2	TDFN 8	PA8TDFN8D
CATALYST	CAT24FC256	DIP 8	
CATALYST	CAT24FC256-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24FC256-K	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT24FC256-L	DIP 8	
CATALYST	CAT24FC256-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24FC256-X	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT24WC01	DIP 8	
CATALYST	CAT24WC01-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC01-R	MSOP 8	PA8MSOP8D
CATALYST	CAT24WC01-U	TSSOP 8	PA8TSS8D
CATALYST	CAT24WC01-U	TSSOP 8	PA24TSS24D
CATALYST	CAT24WC01-L	DIP 8	
CATALYST	CAT24WC01-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC01-Z	MSOP 8	PA8MSOP8D
CATALYST	CAT24WC01-Y	TSSOP 8	PA8TSS8D
CATALYST	CAT24WC01-Y	TSSOP 8	PA24TSS24D
CATALYST	CAT24WC02	DIP 8	
CATALYST	CAT24WC02-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC02-R	MSOP 8	PA8MSOP8D
CATALYST	CAT24WC02-U	TSSOP 8	PA8TSS8D
CATALYST	CAT24WC02-U	TSSOP 8	PA24TSS24D
CATALYST	CAT24WC02-L	DIP 8	
CATALYST	CAT24WC02-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC02-Z	MSOP 8	PA8MSOP8D
CATALYST	CAT24WC02-Y	TSSOP 8	PA8TSS8D
CATALYST	CAT24WC02-Y	TSSOP 8	PA24TSS24D
CATALYST	CAT24WC03	DIP 8	
CATALYST	CAT24WC03-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC03-U	TSSOP 8	PA8TSS8D
CATALYST	CAT24WC03-U	TSSOP 8	PA24TSS24D
CATALYST	CAT24WC04	DIP 8	
CATALYST	CAT24WC04-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC04-R	MSOP 8	PA8MSOP8D
CATALYST	CAT24WC04-U	TSSOP 8	PA8TSS8D
CATALYST	CAT24WC04-U	TSSOP 8	PA24TSS24D
CATALYST	CAT24WC04-L	DIP 8	
CATALYST	CAT24WC04-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC04-Z	MSOP 8	PA8MSOP8D
CATALYST	CAT24WC04-Y	TSSOP 8	PA8TSS8D
CATALYST	CAT24WC04-Y	TSSOP 8	PA24TSS24D
CATALYST	CAT24WC05	DIP 8	
CATALYST	CAT24WC05-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC08	DIP 8	
CATALYST	CAT24WC08-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC08-L	DIP 8	
CATALYST	CAT24WC08-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC09	DIP 8	
CATALYST	CAT24WC09-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC16	DIP 8	
CATALYST	CAT24WC16-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC16-P	DIP 8	
CATALYST	CAT24WC16-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC164	DIP 8	
CATALYST	CAT24WC164-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC164-R	MSOP 8	PA8MSOP8D
CATALYST	CAT24WC164-U	TSSOP 8	PA8TSS8D
CATALYST	CAT24WC164-U	TSSOP 8	PA24TSS24D
CATALYST	CAT24WC164-L	DIP 8	
CATALYST	CAT24WC164-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC164-Z	MSOP 8	PA8MSOP8D
CATALYST	CAT24WC164-Y	TSSOP 8	PA8TSS8D
CATALYST	CAT24WC164-Y	TSSOP 8	PA24TSS24D
CATALYST	CAT24WC17	DIP 8	
CATALYST	CAT24WC17-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC32	DIP 8	
CATALYST	CAT24WC32-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC32-K	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT24WC32-L	DIP 8	
CATALYST	CAT24WC32-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC32-X	SOIC 8	PA16SO16D-EO-150

CATALYST	CAT24WC33	DIP 8	
CATALYST	CAT24WC33-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC33-K	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT24WC33-L	DIP 8	
CATALYST	CAT24WC33-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC33-X	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT24WC64	DIP 8	
CATALYST	CAT24WC64-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC64-K	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT24WC64-L	DIP 8	
CATALYST	CAT24WC64-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC64-X	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT24WC65	DIP 8	
CATALYST	CAT24WC65-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC65-K	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT24WC65-L	DIP 8	
CATALYST	CAT24WC65-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC65-X	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT24WC66	DIP 8	
CATALYST	CAT24WC66-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC66-K	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT24WC66-L	DIP 8	
CATALYST	CAT24WC66-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC128	DIP 8	
CATALYST	CAT24WC128-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC128-K	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT24WC128-U14	TSSOP 14	PA28TSS28D-EO
CATALYST	CAT24WC129	DIP 8	
CATALYST	CAT24WC129-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT24WC129-K	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT24WC256	DIP 8	
CATALYST	CAT24WC256-K	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT24WC257	DIP 8	
CATALYST	CAT24WC257-K	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT34WC02-Y	TSSOP 8	PA8TSS8D
CATALYST	CAT34WC02-Y	TSSOP 8	PA24TSS24D
CATALYST	CAT34WC02-VP2	TDFN 8	PA8TDFN8D
CATALYST	CAT34C02-Y	TSSOP 8	PA8TSS8D
CATALYST	CAT34C02-Y	TSSOP 8	PA24TSS24D
CATALYST	CAT34C02-VP2	TDFN 8	PA8TDFN8D
CATALYST	CAT34FC02	DIP 8	
CATALYST	CAT34FC02-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT34FC02-U	TSSOP 8	PA8TSS8D
CATALYST	CAT34FC02-U	TSSOP 8	PA24TSS24D
CATALYST	CAT34FC02-RD7	TDFN 8	PA8TDFN8D
CATALYST	CAT34FC02-L	DIP 8	
CATALYST	CAT34FC02-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT34FC02-Y	TSSOP 8	PA8TSS8D
CATALYST	CAT34FC02-Y	TSSOP 8	PA24TSS24D
CATALYST	CAT34FC02-ZD7	TDFN 8	PA8TDFN8D
CATALYST	CAT34RC02	DIP 8	
CATALYST	CAT34RC02-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT34RC02-U	TSSOP 8	PA8TSS8D
CATALYST	CAT34RC02-U	TSSOP 8	PA24TSS24D
CATALYST	CAT34RC02-SP2	TDFN 8	PA8TDFN8D
CATALYST	CAT34RC02-L	DIP 8	
CATALYST	CAT34RC02-W	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT34RC02-Y	TSSOP 8	PA8TSS8D
CATALYST	CAT34RC02-Y	TSSOP 8	PA24TSS24D
CATALYST	CAT34RC02-VP2	TDFN 8	PA8TDFN8D
CATALYST	CAT25C01	DIP 8	
CATALYST	CAT25C01	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT25C01	MSOP 8	PA8MSOP8D
CATALYST	CAT25C01	TSSOP 8	PA8TSS8D
CATALYST	CAT25C01	TSSOP 8	PA24TSS24D
CATALYST	CAT25C01	TSSOP 14	PA14TSS14D
CATALYST	CAT25C11	DIP 8	
CATALYST	CAT25C11	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT25C11	MSOP 8	PA8MSOP8D
CATALYST	CAT25C11	TSSOP 8	PA8TSS8D
CATALYST	CAT25C11	TSSOP 8	PA24TSS24D
CATALYST	CAT25C11	TSSOP 14	PA14TSS14D
CATALYST	CAT25C02	DIP 8	

CATALYST	CAT25C02	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT25C02	MSOP 8	PA8MSOP8D
CATALYST	CAT25C02	TSSOP 8	PA8TSS8D
CATALYST	CAT25C02	TSSOP 8	PA24TSS24D
CATALYST	CAT25C02	TSSOP 14	PA14TSS14D
CATALYST	CAT25C03	DIP 8	
CATALYST	CAT25C03	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT25C03	MSOP 8	PA8MSOP8D
CATALYST	CAT25C03	TSSOP 8	PA8TSS8D
CATALYST	CAT25C03	TSSOP 8	PA24TSS24D
CATALYST	CAT25C03	TSSOP 14	PA14TSS14D
CATALYST	CAT25C04	DIP 8	
CATALYST	CAT25C04	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT25C04	TSSOP 8	PA8TSS8D
CATALYST	CAT25C04	TSSOP 8	PA24TSS24D
CATALYST	CAT25C04	TSSOP 14	PA14TSS14D
CATALYST	CAT25C05	DIP 8	
CATALYST	CAT25C05	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT25C05	TSSOP 8	PA8TSS8D
CATALYST	CAT25C05	TSSOP 8	PA24TSS24D
CATALYST	CAT25C05	TSSOP 14	PA14TSS14D
CATALYST	CAT25C08	DIP 8	
CATALYST	CAT25C08	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT25C08	TSSOP 8	PA8TSS8D
CATALYST	CAT25C08	TSSOP 8	PA24TSS24D
CATALYST	CAT25C08	TSSOP 14	PA14TSS14D
CATALYST	CAT25C09	DIP 8	
CATALYST	CAT25C09	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT25C09	TSSOP 8	PA8TSS8D
CATALYST	CAT25C09	TSSOP 8	PA24TSS24D
CATALYST	CAT25C09	TSSOP 14	PA14TSS14D
CATALYST	CAT25C16	DIP 8	
CATALYST	CAT25C16	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT25C16	TSSOP 8	PA8TSS8D
CATALYST	CAT25C16	TSSOP 8	PA24TSS24D
CATALYST	CAT25C16	TSSOP 14	PA14TSS14D
CATALYST	CAT25C17	DIP 8	
CATALYST	CAT25C17	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT25C17	TSSOP 8	PA8TSS8D
CATALYST	CAT25C17	TSSOP 8	PA24TSS24D
CATALYST	CAT25C17	TSSOP 14	PA14TSS14D
CATALYST	CAT25C32	DIP 8	
CATALYST	CAT25C32	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT25C32	TSSOP 14	PA14TSS14D
CATALYST	CAT25C32	TSSOP 20	PA20TSS20D
CATALYST	CAT25C32S	DIP 8	
CATALYST	CAT25C64	DIP 8	
CATALYST	CAT25C64	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT25C64	TSSOP 14	PA14TSS14D
CATALYST	CAT25C64	TSSOP 20	PA20TSS20D
CATALYST	CAT25640	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT25C128	DIP 8	
CATALYST	CAT25C128	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT25C128	TSSOP 14	PA14TSS14D
CATALYST	CAT25C128	SOIC 16	PA16SO16D-1
CATALYST	CAT25C128	TSSOP 20	PA20TSS20D
CATALYST	CAT25C256	DIP 8	
CATALYST	CAT25C256	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT25C256	TSSOP 14	PA14TSS14D
CATALYST	CAT25C256	SOIC 16	PA16SO16D-1
CATALYST	CAT25C256	TSSOP 20	PA20TSS20D
CATALYST	CAT27010	DIP 32	
CATALYST	CAT27010	PLCC 32	PA32PL32D
CATALYST	CAT27010	TSOP 32	PA32TS20/PA32TS32D-20
CATALYST	CAT27128A	DIP 28	
CATALYST	CAT27128A	PLCC 32	PA32PL28D-YA
CATALYST	CAT27256	DIP 28	
CATALYST	CAT27512	DIP 28	
CATALYST	CAT27512	PLCC 32	PA32PL28D-YA
CATALYST	CAT2764A	DIP 28	
CATALYST	CAT27C210	DIP 40	
CATALYST	CAT27C210	PLCC 44	PA44-48U
CATALYST	CAT27HC256	DIP 28	

CATALYST	CAT27HC256	PLCC 32	PA32PL28D-YA
CATALYST	CAT27HC256L	DIP 28	
CATALYST	CAT27HC256L	PLCC 32	PA32PL28D-YA
CATALYST	CAT28C16A	DIP 24	
CATALYST	CAT28C16A	PLCC 32	PA32PL32D
CATALYST	CAT28C16A	SOIC 24	PA28SO28D-EO-300
CATALYST	CAT28C17A	DIP 28	
CATALYST	CAT28C17A	PLCC 32	PA32PL28D-YA
CATALYST	CAT28C17A	SOIC 24	PA28SO28D-EO-300
CATALYST	CAT28C256	DIP 28	
CATALYST	CAT28C256	PLCC 32	PA32PL28D-YA
CATALYST	CAT28C256	TSOP 28	PA28TS28D-EO
CATALYST	CAT28C64A	DIP 28	
CATALYST	CAT28C64A	PLCC 32	PA32PL28D-YA
CATALYST	CAT28C64A	SOIC 28	PA28SO28D-EO-300
CATALYST	CAT28C64B	DIP 28	
CATALYST	CAT28C64B	PLCC 32	PA32PL28D-YA
CATALYST	CAT28C64B	SOIC 28	PA28SO28D-EO-300
CATALYST	CAT28C64B	TSOP 28	PA28TS28D-EO
CATALYST	CAT28C65BJ	SOIC 28	PA28SO28D-EO-300
CATALYST	CAT28C65A	DIP 28	
CATALYST	CAT28C65A	PLCC 32	PA32PL28D-YA
CATALYST	CAT28C65A	SOIC 28	PA28SO28D-EO-300
CATALYST	CAT28C65B	DIP 28	
CATALYST	CAT28C65B	PLCC 32	PA32PL28D-YA
CATALYST	CAT28C65B	TSOP 28	PA28TS28D-EO
CATALYST	CAT28C512	DIP 32	
CATALYST	CAT28C512	PLCC 32	PA32PL32D
CATALYST	CAT28C512	TSOP 32	PA32TS20/PA32TS32D-20
CATALYST	CAT28C513	PLCC 32	PA32PL32D
CATALYST	CAT28F010	DIP 32	
CATALYST	CAT28F010	PLCC 32	PA32PL32D
CATALYST	CAT28F010	TSOP 32	PA32TS20/PA32TS32D-20
CATALYST	CAT28F020	DIP 32	
CATALYST	CAT28F020	PLCC 32	PA32PL32D
CATALYST	CAT28F020	TSOP 32	PA32TS20/PA32TS32D-20
CATALYST	CAT28F512	DIP 32	
CATALYST	CAT28F512	PLCC 32	PA32PL32D
CATALYST	CAT28F512	TSOP 32	PA32TS20/PA32TS32D-20
CATALYST	CAT28F001B	DIP 32	
CATALYST	CAT28F001B	PLCC 32	PA32PL32D
CATALYST	CAT28F001B	TSOP 32	PA32TS20/PA32TS32D-20
CATALYST	CAT28F001T	DIP 32	
CATALYST	CAT28F001T	PLCC 32	PA32PL32D
CATALYST	CAT28F001T	TSOP 32	PA32TS20/PA32TS32D-20
CATALYST	CAT28LV64	DIP 28	
CATALYST	CAT28LV64	PLCC 32	PA32PL28D-YA
CATALYST	CAT28LV64	SOIC 28	PA28SO28D-EO-300
CATALYST	CAT28LV64	TSOP 28	PA28TS28D-EO
CATALYST	CAT28LV65	DIP 28	
CATALYST	CAT28LV65	PLCC 32	PA32PL28D-YA
CATALYST	CAT28LV65	SOIC 28	PA28SO28D-EO-300
CATALYST	CAT28LV65	TSOP 28	PA28TS28D-EO
CATALYST	CAT28LV256	DIP 28	
CATALYST	CAT28LV256	PLCC 32	PA32PL28D-YA
CATALYST	CAT28LV256	TSOP 28	PA28TS28D-EO
CATALYST	CAT33C101	DIP 8	
CATALYST	CAT33C104	DIP 8	
CATALYST	CAT33C116	DIP 8	
CATALYST	CAT33C116I	DIP 8	
CATALYST	CAT33C204	DIP 8	
CATALYST	CAT35C102	DIP 8	
CATALYST	CAT35C104	DIP 8	
CATALYST	CAT35C116	DIP 8	
CATALYST	CAT35C116I	DIP 8	
CATALYST	CAT35C202	DIP 8	
CATALYST	CAT35C204	DIP 8	
CATALYST	CAT59C11	DIP 8	
CATALYST	CAT93C46	DIP 8	
CATALYST	CAT93C46	TSSOP 8	PA8TSS-OT
CATALYST	CAT93C46	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT93C46-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT93C46A	DIP 8	



CATALYST	CAT93C46A	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT93C46A-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT93C56	DIP 8	
CATALYST	CAT93C56	TSSOP 8	PA8TSS-OT
CATALYST	CAT93C56	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT93C56-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT93C57	DIP 8	
CATALYST	CAT93C57	TSSOP 8	PA8TSS-OT
CATALYST	CAT93C57	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT93C57-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT93C66	DIP 8	
CATALYST	CAT93C66	TSSOP 8	PA8TSS-OT
CATALYST	CAT93C66	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT93C66-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT93C66A	DIP 8	
CATALYST	CAT93C66A	TSSOP 8	PA8TSS-OT
CATALYST	CAT93C66A	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT93C66A-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT93C86	DIP 8	
CATALYST	CAT93C86	TSSOP 8	PA8TSS-OT
CATALYST	CAT93C86	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT93C86-J	SOIC 8	PA8SO8D-EO-150
CATALYST	CAT93C86A	DIP 8	
CATALYST	CAT93C86A	TSSOP 8	PA8TSS-OT
CATALYST	CAT93C86A	SOIC 8	PA16SO16D-EO-150
CATALYST	CAT93C86A-J	SOIC 8	PA8SO8D-EO-150
CYPRESS	CY27C128	DIP 28	
CYPRESS	CY27C256	DIP 28	
CYPRESS	CY27C256	PLCC 32	PA32PL28D-YA
CYPRESS	CY27C256	TSOP 28	PA28TS28D-EO
CYPRESS	CY27C256A	DIP 28	
CYPRESS	CY27C256A	PLCC 32	PA32PL28D-YA
CYPRESS	CY27C256A	TSOP 28	PA28TS28D-EO
CYPRESS	CY27C512	DIP 28	
CYPRESS	CY27C512	PLCC 32	PA32PL28D-YA
CYPRESS	CY27C512	TSOP 28	PA28TS28D-EO
CYPRESS	CY27H256	DIP 28	
CYPRESS	CY27H256	PLCC 32	PA32PL28D-YA
CYPRESS	CY27H512	DIP 20	
CYPRESS	CY27H512	PLCC 32	PA32PL28D-YA
CYPRESS	CY27H512	TSOP 28	PA28TS28D-EO
CYPRESS	CY27C010	DIP 32	
CYPRESS	CY27C010	PLCC 32	PA32PL32D
CYPRESS	CY27C010	TSOP 32	PA32TS20/PA32TS32D-20
CYPRESS	CY27C020	DIP 32	
CYPRESS	CY27C020	PLCC 32	PA32PL32D
CYPRESS	CY27C020	TSOP 32	PA32TS20/PA32TS32D-20
CYPRESS	CY27C040	DIP 32	
CYPRESS	CY27C040	PLCC 32	PA32PL32D
CYPRESS	CY27C040	TSOP 32	PA32TS20/PA32TS32D-20
CYPRESS	CY27H010	DIP 32	
CYPRESS	CY27H010	PLCC 32	PA32PL32D
CYPRESS	CY27H010	TSOP 32	PA32TS20/PA32TS32D-20
DALLAS	DS1220AB	EDIP 24	
DALLAS	DS1220AD	EDIP 24	
DALLAS	DS1220Y	EDIP 24	
DALLAS	DS1225AB	EDIP 28	
DALLAS	DS1225AD	EDIP 28	
DALLAS	DS1225Y	EDIP 28	
DALLAS	DS1230AB	EDIP 28	
DALLAS	DS1230Y	EDIP 28	
DALLAS	DS1235AB	EDIP 28	
DALLAS	DS1235YW	EDIP 28	
DALLAS	DS1243Y	EDIP 28	
DALLAS	DS1244Y	EDIP 28	
DALLAS	DS1244W	EDIP 28	
DALLAS	DS1244WP	EDIP 28	
DALLAS	DS1245AB	EDIP 32	
DALLAS	DS1245Y	EDIP 32	
DALLAS	DS1248Y	EDIP 32	
DALLAS	DS1250AB	EDIP 32	
DALLAS	DS1250Y	EDIP 32	
DALLAS	DS1642	EDIP 24	

DALLAS	DS1643	EDIP 28	
DALLAS	DS1643Y	EDIP 28	
DALLAS	DS1644	EDIP 28	
DALLAS	DS1645AB	EDIP 32	
DALLAS	DS1645Y	EDIP 32	
DALLAS	DS1650AB	EDIP 32	
DALLAS	DS1650Y	EDIP 32	
DALLAS	DS1386(8K)	EDIP 32	
DALLAS	DS1386(32K)	EDIP 32	
DALLAS	DS1486	EDIP 32	
DALLAS	DS1658AB	DIP 40	
DALLAS	DS1658Y	DIP 40	
DALLAS	DS12887	EDIP 24	
DALLAS	DS12C887	EDIP 24	
DALLAS	DS1086	SOP 8	PA16SO16D-EO-150
DALLAS	DS1624	DIP 8	
DALLAS	DS1624S	SOIC 8	PA20SO20D-EO-210
DENSE PAC	DPV27C101	DIP 32	
DENSE PAC	DPV27C256	DIP 28	
DENSE PAC	DPV27C512	DIP 28	
DENSE PAC	DPV27C512	PLCC 32	PA32PL28D-YA
EON	EN25B10T-G	SOIC 8	PA16SO16D-EO-150
EON	EN25B10T-V	VDFN 8	PA8SON8D
EON	EN25B10-G	SOIC 8	PA16SO16D-EO-150
EON	EN25B10-V	VDFN 8	PA8SON8D
EON	EN25B20T-G	SOIC 8	PA16SO16D-EO-150
EON	EN25B20T-V	VDFN 8	PA8SON8D
EON	EN25B20-G	SOIC 8	PA16SO16D-EO-150
EON	EN25B20-V	VDFN 8	PA8SON8D
EON	EN25B40T-G	SOIC 8	PA16SO16D-EO-150
EON	EN25B40T-H	SOIC 8	PA20SO20D-EO-210
EON	EN25B40T-V	VDFN 8	PA8SON8D
EON	EN25B40-G	SOIC 8	PA16SO16D-EO-150
EON	EN25B40-H	SOIC 8	PA20SO20D-EO-210
EON	EN25B40-V	VDFN 8	PA8SON8D
EON	EN25P80-H	SOIC 8	PA20SO20D-EO-210
EON	EN25P80-V	VDFN 8	PA8SON8D
EON	EN25B80T-H	SOIC 8	PA20SO20D-EO-210
EON	EN25B80T-V	VDFN 8	PA8SON8D
EON	EN25B80-H	SOIC 8	PA20SO20D-EO-210
EON	EN25B80-V	VDFN 8	PA8SON8D
EON	EN25B16T-H	SOIC 8	PA20SO20D-EO-210
EON	EN25B16T-V	VDFN 8	PA8SON8D
EON	EN25B16-H	SOIC 8	PA20SO20D-EO-210
EON	EN25B16-V	VDFN 8	PA8SON8D
EON	EN25B32-H	SOIC 8	PA20SO20D-EO-210
EON	EN25B32-F	SOIC 16	PA28SO28D-EO-300
EON	EN25B32-Q	DIP 8	
EON	EN25B32T-H	SOIC 8	PA20SO20D-EO-210
EON	EN25B64	SOIC 16	PA28SO28D-EO-300
EON	EN25P05-G	SOIC 8	PA16SO16D-EO-150
EON	EN25P05-V	VDFN 8	PA8SON8D
EON	EN25P10-G	SOIC 8	PA16SO16D-EO-150
EON	EN25P10-V	VDFN 8	PA8SON8D
EON	EN25P20-G	SOIC 8	PA16SO16D-EO-150
EON	EN25P20-V	VDFN 8	PA8SON8D
EON	EN25P40-G	SOIC 8	PA16SO16D-EO-150
EON	EN25P40-H	SOIC 8	PA20SO20D-EO-210
EON	EN25P40-V	VDFN 8	PA8SON8D
EON	EN25P16-H	SOIC 8	PA20SO20D-EO-210
EON	EN25P16-V	VDFN 8	PA8SON8D
EON	EN25T16-H	SOIC 8	PA20SO20D-EO-210
EON	EN25T16-75HIP	SOIC 8	PA8SO8D-210
EON	EN25P32-V	VDFN 8	PA8SON8D
EON	EN25P32-H	SOIC 8	PA20SO20D-EO-210
EON	EN25P32-F	SOIC 16	PA28SO28D-EO-300
EON	EN25LF05-G	SOIC 8	PA8SO8D-EO-150
EON	EN25LF10-G	SOIC 8	PA16SO16D-EO-150
EON	EN25F10-G	SOIC 8	PA16SO16D-EO-150
EON	EN25F10-100GIP	SOIC 8	PA8SO8D-EO-150
EON	EN25F20-G	SOIC 8	PA16SO16D-EO-150
EON	EN25F20-V	VDFN 8	PA8SON8D
EON	EN25F40-G	SOIC 8	PA16SO16D-EO-150

EON	EN25F40-H	SOIC 8	PA20SO20D-EO-210
EON	EN25F40-V	VDFN 8	PA8SON8D
EON	EN25F80-H	SOIC 8	PA20SO20D-EO-210
EON	EN25F80A-H	SOIC 8	PA20SO20D-EO-210
EON	EN25F80A-75HIP	SOIC 8	PA8SO8D-210
EON	EN25F80-V	VDFN 8	PA8SON8D
EON	EN25F80-Q	DIP 8	
EON	EN25Q80A-G	SOIC 8	PA16SO16D-EO-150
EON	EN25Q80A-H	SOIC 8	PA20SO20D-EO-210
EON	EN25Q80A-W	VDFN 8	PA8SON8D
EON	EN25Q80A-Q	DIP 8	
EON	EN25S80A-R	SOIC 8	PA20SO20D-EO-210
EON	EN25S16-R	SOIC 8	PA20SO20D-EO-210
EON	EN25S16-W	VDFN 8	PA8SON8D
EON	EN25S32-R	SOIC 8	PA20SO20D-EO-210
EON	EN25Q32B-BB	BGA 24	HA24BG48D
MICRON	N25Q008A11EF6	WSON 8	HA8SON48DG
MICRON	N25Q008A11ESC	SOIC 8	HA8SO48DAD
MICRON	N25Q016A11ESC	SOIC 8	HA8SO48DAD
EON	EN25Q16-G	SOIC 8	PA16SO16D-EO-150
EON	EN25Q16-H	SOIC 8	PA20SO20D-EO-210
EON	EN25Q16-W	VDFN 8	PA8SON8D
EON	EN25Q16-Q	DIP 8	
EON	EN25F16-H	SOIC 8	PA20SO20D-EO-210
EON	EN25Q32B	SOIC 8	PA8SO8D-210
NUMONYX	N25Q032A	MLP 8	PA8SON8D
NUMONYX	N25Q032A	SOIC 8	PA8SO8D-EO-150
NUMONYX	N25Q032A	SOIC 8	PA8SO8D-210
NUMONYX	N25Q032A	BGA 24	HA32LQ48DA
NUMONYX	N25Q064A	SOIC 8	PA8SO8D-210
NUMONYX	N25Q064A	MLP 8	PA8SON8D
MICRON	N25Q064A11EF640E	VDFN 8	PA8SON8D
NUMONYX	N25Q064A	MLP 8	PA8SON8DA
NUMONYX	N25Q064A	BGA 24	HA32LQ48DA
NUMONYX	N25Q064A	SOIC 16	PA28SO28D-EO-300
NUMONYX	N25Q128A	SOIC 8	PA8SO8D-210
NUMONYX	N25Q128A	MLP 8	PA8SON8DA
NUMONYX	N25Q128A13BSF	SOIC 16	PA28SO28D-EO-300
MICRON	N25Q064A13ESE	SOIC 8	PA20SO20D-EO-210
MICRON	N25Q064A13ESF	SOIC 16	PA28SO28D-EO-300
MICRON	N25Q064A13EF6	WSON 8	PA8SON8D
MICRON	N25Q064A13EF8	WSON 8	PA8SON8DA
MICRON	N25Q064A13E12	BGA 24	NA24BG48DA
MICRON	N25Q032A13ESF	SOIC 16	PA28SO28D-EO-300
MICRON	N25Q128A11ESE	SOIC 8	PA20SO20D-EO-210
MICRON	N25Q032A11EF6	MLP 8	PA8SON8D
MICRON	N25Q128A11EF7	MLP 8	PA8SON8D
MICRON	N25Q128A13EF7	MLP 8	PA8SON8D
MICRON	N25Q128A11E12	BGA 24	NA24BG48DA
MICRON	N25Q032A13EF4	MLP 8	HBP8USON48D
MICRON	N25Q256A83ESF	SOIC 16	PA28SO28D-EO-300
MICRON	N25Q512A83GSF	SOIC 16	PA28SO28D-EO-300
MICRON	N25Q256A73ESF	SOIC 16	PA28SO28D-EO-300
MICRON	N25Q256A13EF8	MLP 8	PA8SON8DA
MICRON	N25Q00AA11G12	BGA 24	NA24BG48DA
MICRON	MT25QU512ABB8ESF	SOIC 16	HA16SO48DP
FIDELIX	FM25M04A-B1	SOIC 8	HA8SO48DAC
FIDELIX	FM25M04A-B4	WSON 8	HA8SON48DG
FIDELIX	FM25M04A-B5	SOIC 8	HA8SO48DAD
FIDELIX	FM25M04A-B7	SOIC 8	HA8SO48DAC
FIDELIX	FM25M04A-B	USON 8	HBP8USON48DC
FIDELIX	FM25M08A-B1	SOIC 8	HA8SO48DAC
FIDELIX	FM25M08A-B4	WSON 8	HA8SON48DG
FIDELIX	FM25M08A-B5	SOIC 8	HA8SO48DAD
FIDELIX	FM25M08A-B7	SOIC 8	HA8SO48DAC
FIDELIX	FM25M16A-B1	SOIC 8	HA8SO48DAC
FIDELIX	FM25M16A-B4	WSON 8	HA8SON48DG
FIDELIX	FM25M16A-B5	SOIC 8	HA8SO48DAD
FIDELIX	FM25M16A-B7	SOIC 8	HA8SO48DAC
FIDELIX	FM25Q16A-A1	SOIC 8	PA20SO20D-EO-210
FIDELIX	FM25Q16A-A2	SOIC 16	PA28SO28D-EO-300
FIDELIX	FM25Q16A-A3	DIP 8	
FIDELIX	FM25Q16A-A4	WSON 8	PA8SON8D

FIDELIX	FM25Q16A-A5	SOIC 8	PA16SO16D-EO-150
FIDELIX	FM25Q16A-A6	WSON 8	PA8SON8DA
FIDELIX	FM25Q16A-A7	SOIC 8	PA20SO20D-EO-210
FIDELIX	FM25Q16A-A8	BGA 24	NA24BG48D-D
FIDELIX	FM25Q16B-A1	SOIC 8	PA20SO20D-EO-210
FIDELIX	FM25Q16B-A2	SOIC 16	PA28SO28D-EO-300
FIDELIX	FM25Q16B-A3	DIP 8	
FIDELIX	FM25Q16B-A4	WSON 8	PA8SON8D
FIDELIX	FM25Q16B-A5	SOIC 8	PA16SO16D-EO-150
FIDELIX	FM25Q16B-A6	WSON 8	PA8SON8DA
FIDELIX	FM25Q16B-A7	SOIC 8	PA20SO20D-EO-210
FIDELIX	FM25Q16B-A8	BGA 24	NA24BG48D-D
FIDELIX	FM25Q32A	SOIC 8	PA20SO20D-EO-210
FIDELIX	FM25M32A-B1	SOIC 8	HA8SO48DAC
FIDELIX	FM25M32A-B4	WSON 8	HA8SON48DG
FIDELIX	FM25M32A-B5	SOIC 8	HA8SO48DAD
FIDELIX	FM25M32A-B7	SOIC 8	HA8SO48DAC
FIDELIX	FM25M64A-B1	SOIC 8	HA8SO48DAC
FIDELIX	FM25M64A-B4	WSON 8	HA8SON48DG
FIDELIX	FM25M64A-B5	SOIC 8	HA8SO48DAD
FIDELIX	FM25M64A-B7	SOIC 8	HA8SO48DAC
FIDELIX	FM25M4AA-B1	SOIC 8	HA8SO48DAC
FIDELIX	FM25M4AA-B4	WSON 8	HA8SON48DG
FIDELIX	FM25M4AA-B7	SOIC 8	HA8SO48DAC
EON	EN25F32-H	SOIC 8	PA20SO20D-EO-210
EON	EN25F32-100HIP	SOIC 8	PA8SO8D-210
EON	EN25F32-W	VDFN 8	PA8SON8D
EON	EN25F32-Q	DIP 8	
EON	EN25F32-F	SOIC 16	PA28SO28D-EO-300
EON	EN27C512	DIP 28	
EON	EN27C512	PLCC 32	PA32PL28D-YA
EON	EN27C512	TSOP 28	PA28TS28D-EO
EON	EN27C010	DIP 32	
EON	EN27C010	PLCC 32	PA32PL32D
EON	EN27C010	TSOP 32	PA32TS20/PA32TS32D-20
EON	EN27C020	DIP 32	
EON	EN27C020	PLCC 32	PA32PL32D
EON	EN27C020	TSOP 32	PA32TS20/PA32TS32D-20
EON	EN27LV512	DIP 28	
EON	EN27LV512	PLCC 32	PA32PL28D-YA
EON	EN27LV512	TSOP 28	PA28TS28D-EO
EON	EN27LV512B	DIP 28	
EON	EN27LV512B	PLCC 32	PA32PL28D-YA
EON	EN27LV512B	TSOP 28	PA28TS28D-EO
EON	EN27LV010	DIP 32	
EON	EN27LV010	PLCC 32	PA32PL32D
EON	EN27LV010	TSOP 32	PA32TS20/PA32TS32D-20
EON	EN27LV010B	DIP 32	
EON	EN27LV010B	PLCC 32	PA32PL32D
EON	EN27LV010B	TSOP 32	PA32TS20/PA32TS32D-20
EON	EN27LV020	DIP 32	
EON	EN27LV020	PLCC 32	PA32PL32D
EON	EN27LV020	TSOP 32	PA32TS20/PA32TS32D-20
EON	EN27LV020B	DIP 32	
EON	EN27LV020B	PLCC 32	PA32PL32D
EON	EN27LV020B	TSOP 32	PA32TS20/PA32TS32D-20
EON	EN29F512	DIP 32	
EON	EN29F512	PLCC 32	PA32PL32D
EON	EN29F512	TSOP 32	PA32TS20/PA32TS32D-20
EON	EN29F010	DIP 32	
EON	EN29F010	PLCC 32	PA32PL32D
EON	EN29F010	TSOP 32	PA32TS20/PA32TS32D-20
EON	EN29F002B	DIP 32	
EON	EN29F002B	PLCC 32	PA32PL32D
EON	EN29F002B	TSOP 32	PA32TS20/PA32TS32D-20
EON	EN29F002T	DIP 32	
EON	EN29F002T	PLCC 32	PA32PL32D
EON	EN29F002T	TSOP 32	PA32TS20/PA32TS32D-20
EON	EN29F002AT	DIP 32	
EON	EN29F002AT	PLCC 32	PA32PL32D
EON	EN29F002AT	TSOP 32	PA32TS20/PA32TS32D-20
EON	EN29F002AB	DIP 32	
EON	EN29F002AB	PLCC 32	PA32PL32D

EON	EN29F002AB	TSOP 32	PA32TS20/PA32TS32D-20
EON	EN29F002ANT	DIP 32	
EON	EN29F002ANT	PLCC 32	PA32PL32D
EON	EN29F002ANT	TSOP 32	PA32TS20/PA32TS32D-20
EON	EN29F002ANB	DIP 32	
EON	EN29F002ANB	PLCC 32	PA32PL32D
EON	EN29F002ANB	TSOP 32	PA32TS20/PA32TS32D-20
EON	EN29F002NB	DIP 32	
EON	EN29F002NB	PLCC 32	PA32PL32D
EON	EN29F002NB	TSOP 32	PA32TS20/PA32TS32D-20
EON	EN29F002NT	DIP 32	
EON	EN29F002NT	PLCC 32	PA32PL32D
EON	EN29F002NT	TSOP 32	PA32TS20/PA32TS32D-20
EON	EN29F040	DIP 32	
EON	EN29F040	PLCC 32	PA32PL32D
EON	EN29F040	TSOP 32	PA32TS20/PA32TS32D-20
EON	EN29F040A	DIP 32	
EON	EN29F040A	PLCC 32	PA32PL32D
EON	EN29F040A	TSOP 32	PA32TS20/PA32TS32D-20
EON	EN29F800B	TSOP 48	PA48TS48D
EON	EN29F800T	TSOP 48	PA48TS48D
EON	EN29LV512	PLCC 32	PA32PL32D
EON	EN29LV512	TSOP 32	PA32TS20/PA32TS32D-20
EON	EN29LV010	PLCC 32	PA32PL32D
EON	EN29LV010	TSOP 32	PA32TS20/PA32TS32D-20
EON	EN29LV040	PLCC 32	PA32PL32D
EON	EN29LV040	TSOP 32	PA32TS20/PA32TS32D-20
EON	EN29LV040	sTSOP 32	PA32TS32D
EON	EN29LV040A	PLCC 32	PA32PL32D
EON	EN29LV040A	TSOP 32	PA32TS20/PA32TS32D-20
EON	EN29LV040A	sTSOP 32	PA32TS32D
EON	EN29LV040J	PLCC 32	PA32PL32D
EON	EN29LV040J	TSOP 32	PA32TS20/PA32TS32D-20
EON	EN29LV040J	sTSOP 32	PA32TS32D
EON	EN29LV400B	TSOP 48	PA48TS48D
EON	EN29LV400T	TSOP 48	PA48TS48D
EON	EN29LV400AB	TSOP 48	PA48TS48D
EON	EN29LV400AT	TSOP 48	PA48TS48D
EON	EN29LV400JB	TSOP 48	PA48TS48D
EON	EN29LV400JT	TSOP 48	PA48TS48D
EON	EN29LV800B	TSOP 48	PA48TS48D
EON	EN29LV800T	TSOP 48	PA48TS48D
EON	EN29LV800AB	TSOP 48	PA48TS48D
EON	EN29LV800AT	TSOP 48	PA48TS48D
EON	EN29LV800BB	TSOP 48	PA48TS48D1
EON	EN29LV800BT	TSOP 48	PA48TS48D1
EON	EN29LV800CB-T	TSOP 48	PA48TS48D1
EON	EN29LV800CT-T	TSOP 48	PA48TS48D1
EON	EN29LV800CT-70TIP	TSOP 48	PA48TS48D1
EON	EN29LV800CB-B	BGA 48	HA48BG48DAI
EON	EN29LV800CB-70TIP	TSOP 48	PA48TS48D1
EON	EN29LV800CT-B	BGA 48	HA48BG48DAI
EON	EN29LV800JB	TSOP 48	PA48TS48D
EON	EN29LV800JT	TSOP 48	PA48TS48D
EON	EN29LV160AB	TSOP 48	PA48TS48D1
EON	EN29LV160AT	TSOP 48	PA48TS48D1
EON	EN29LV160AT	BGA 48	PA48BG48DAI
EON	EN29LV160BB	TSOP 48	PA48TS48D1
EON	EN29LV160BB-70TIP	TSOP 48	PA48TS48D1
EON	EN29LV160BT	TSOP 48	PA48TS48D1
EON	EN29LV160BT-70TIP	TSOP 48	PA48TS48D1
EON	EN29LV160BB-B	BGA 48	HA48BG48DAI
EON	EN29LV160BT-B	BGA 48	HA48BG48DAI
EON	EN29LV160BB-70BIP	BGA 48	HA48BG48DAI
EON	EN29LV160BT-70BIP	BGA 48	HA48BG48DAI
EON	EN29LV320B	TSOP 48	PA48TS48D1
EON	EN29LV320T	TSOP 48	PA48TS48D1
EON	EN29LV320AB	BGA 48	PA48BG48DW
EON	EN29LV320AB	BGA 48	HA48BG48DAI
EON	EN29LV320AB	TSOP 48	PA48TS48D1
EON	EN29LV320AT	TSOP 48	PA48TS48D1
EON	EN29LV320AT	BGA 48	PA48BG48DAI
EON	EN29LV320BT	TSOP 48	PA48TS48D1

EON	EN29LV320BB	TSOP 48	PA48TS48D1
EON	EN29LV320BT-B	BGA 48	HA48BG48DAI
EON	EN29LV320BB-B	BGA 48	HA48BG48DAI
EON	EN29LV640H	TSOP 48	PA48TS48D1
EON	EN29LV640L	TSOP 48	PA48TS48D1
EON	EN29LV640B	TSOP 48	PA48TS48D1
EON	EN29LV640T	TSOP 48	PA48TS48D1
EON	EN29LV641H	TSOP 48	PA48TS48D
EON	EN29LV641L	TSOP 48	PA48TS48D
EON	EN29SL400T	TSOP 48	HA48TS48DJ
EON	EN29SL400B	TSOP 48	HA48TS48DJ
EON	EN29SL800T	TSOP 48	HA48TS48DJ
EON	EN29SL800B	TSOP 48	HA48TS48DJ
EON	EN29GL128H	TSOP 56	PA56TS48DB
EON	EN29GL128H	TSOP 56	PA56TS48DC
EON	EN29GL128H	TSOP 56	PA56TS48DD
EON	EN29GL128L	TSOP 56	PA56TS48DB
EON	EN29GL128L	TSOP 56	PA56TS48DC
EON	EN29GL128L	TSOP 56	PA56TS48DD
EON	EN39LV010	PLCC 32	PA32PL32D
EXEL	XLS2804A	DIP 24	
EXEL	XL2816A	DIP 24	
EXEL	XL2816A	PLCC 32	PA32PL32D
EXEL	XL2816A	SOIC 28	PA28SO28D-EO-300
EXEL	XL28C16A	DIP 24	
EXEL	XL28C16A	PLCC 32	PA32PL32D
EXEL	XL28C16A	SOIC 28	PA28SO28D-EO-300
EXEL	XLE2816A	DIP 24	
EXEL	XLE2816A	PLCC 32	PA32PL32D
EXEL	XLE2816A	SOIC 28	PA28SO28D-EO-300
EXEL	XLE28C16A	DIP 24	
EXEL	XLE28C16A	PLCC 32	PA32PL32D
EXEL	XLE28C16A	SOIC 28	PA28SO28D-EO-300
EXEL	XLS2816A	DIP 24	
EXEL	XLS2816A	PLCC 32	PA32PL32D
EXEL	XLS2816A	SOIC 28	PA28SO28D-EO-300
EXEL	XLS28C16A	DIP 24	
EXEL	XLS28C16A	PLCC 32	PA32PL32D
EXEL	XLS28C16A	SOIC 28	PA28SO28D-EO-300
EXEL	XL2817A	DIP 28	
EXEL	XLM2817A	DIP 28	
EXEL	XLS2817A	DIP 28	
EXEL	XL2864A	DIP 28	
EXEL	XL2864A	PLCC 32	PA32PL28D-YA
EXEL	XL2864A	SOIC 28	PA28SO28D-EO-300
EXEL	XL28C64	DIP 28	
EXEL	XL28C64	PLCC 32	PA32PL28D-YA
EXEL	XL28C64	SOIC 28	PA28SO28D-EO-300
EXEL	XL28C64B	DIP 28	
EXEL	XL28C64B	PLCC 32	PA32PL28D-YA
EXEL	XL28C64B	SOIC 28	PA28SO28D-EO-300
EXEL	XLE2864A	DIP 28	
EXEL	XLE2864A	PLCC 32	PA32PL28D-YA
EXEL	XLE2864A	SOIC 28	PA28SO28D-EO-300
EXEL	XLE28C64	DIP 28	
EXEL	XLE28C64	PLCC 32	PA32PL28D-YA
EXEL	XLE28C64	SOIC 28	PA28SO28D-EO-300
EXEL	XLE28C64B	DIP 28	
EXEL	XLE28C64B	PLCC 32	PA32PL28D-YA
EXEL	XLE28C64B	SOIC 28	PA28SO28D-EO-300
EXEL	XLS2864A	DIP 28	
EXEL	XLS2864A	PLCC 32	PA32PL28D-YA
EXEL	XLS2864A	SOIC 28	PA28SO28D-EO-300
EXEL	XLS28C64	DIP 28	
EXEL	XLS28C64	PLCC 32	PA32PL28D-YA
EXEL	XLS28C64	SOIC 28	PA28SO28D-EO-300
EXEL	XLS28C64B	DIP 28	
EXEL	XLS28C64B	PLCC 32	PA32PL28D-YA
EXEL	XLS28C64B	SOIC 28	PA28SO28D-EO-300
EXEL	XL2865A	DIP 28	
EXEL	XL2865A	PLCC 32	PA32PL28D-YA
EXEL	XL28C65A	DIP 28	
EXEL	XL28C65A	PLCC 32	PA32PL32D

EXEL	XL28C65A	SOIC 28	PA28SO28D-EO-300
EXEL	XLE2865A	DIP 28	
EXEL	XLE2865A	PLCC 32	PA32PL28D-YA
EXEL	XLE28C65A	DIP 28	
EXEL	XLE28C65A	PLCC 32	PA32PL28D-YA
EXEL	XLE28C65A	SOIC 28	PA28SO28D-EO-300
EXEL	XLM28C65A	DIP 28	
EXEL	XLM28C65A	PLCC 32	PA32PL28D-YA
EXEL	XLM28C65A	SOIC 28	PA28SO28D-EO-300
EXEL	XLS2865A	DIP 28	
EXEL	XLS2865A	PLCC 32	PA32PL28D-YA
EXEL	XLS28C65A	DIP 28	
EXEL	XLS28C65A	PLCC 32	PA32PL28D-YA
EXEL	XLS28C65A	SOIC 28	PA28SO28D-EO-300
EXEL	XL28C256	DIP 28	
EXEL	XL28C256	PLCC 32	PA32PL28D-YA
EXEL	XLE28C256	DIP 28	
EXEL	XLE28C256	PLCC 32	PA32PL28D-YA
EXEL	XLS28C256	DIP 28	
EXEL	XLS28C256	PLCC 32	PA32PL28D-YA
EXEL	XL93C06	DIP 8	
EXEL	XL93C06	SOIC 8	PA16SO16D-EO-150
EXEL	XL93C46	DIP 8	
EXEL	XL93C46	SOIC 8	PA16SO16D-EO-150
EXEL	XL93CS46	DIP 8	
EXEL	XL93C46A	DIP 8	
EXEL	XL93C46A	SOIC 8	PA16SO16D-EO-150
EXEL	XL93C56	DIP 8	
EXEL	XL93C56	SOIC 8	PA16SO16D-EO-150
EXEL	XL93C56A	DIP 8	
EXEL	XL93C56A	SOIC 8	PA16SO16D-EO-150
EXEL	XL93C66	DIP 8	
EXEL	XL93C66	SOIC 8	PA16SO16D-EO-150
EXEL	XL93C66A	DIP 8	
EXEL	XL93C66A	SOIC 8	PA16SO16D-EO-150
EXEL	XL93LC46	DIP 8	
EXEL	XL93LC46	SOIC 8	PA16SO16D-EO-150
EXEL	XL93LC56	DIP 8	
EXEL	XL93LC56	SOIC 8	PA16SO16D-EO-150
EXEL	XL93LC66	DIP 8	
EXEL	XL93LC66	SOIC 8	PA16SO16D-EO-150
EXEL	XL93LL46	DIP 8	
EXEL	XL93LL56	DIP 8	
EXEL	XL93LL66	DIP 8	
EXEL	XLE93C46	DIP 8	
EXEL	XLE93CS46	DIP 8	
EXEL	XLE93C56	DIP 8	
EXEL	XLE93C66	DIP 8	
EXEL	XLS93C46	DIP 8	
EXEL	XLS93C46	SOIC 8	PA16SO16D-EO-150
EXEL	XLS93C56	DIP 8	
EXEL	XLS93C56	SOIC 8	PA16SO16D-EO-150
EXEL	XLS93C66	DIP 8	
EXEL	XLS93C66	SOIC 8	PA16SO16D-EO-150
EXEL	XLS93CS46	DIP 8	
EXEL	XLS93LC46	DIP 8	
EXEL	XLS93LC56	DIP 8	
EXEL	XLS93LC66	DIP 8	
EXCELSEMI	ES25M80A-1	SOIC 8	PA16SO16D-EO-150
EXCELSEMI	ES25M80A-2	SOIC 8	PA20SO20D-EO-210
EXCELSEMI	ES25M80A-3	SOIC 16	PA28SO28D-EO-300
EXCELSEMI	ES25M80A-4	DIP 8	
EXCELSEMI	ES25M80A-5	CASON 8	PA8SON8D
EXCELSEMI	ES25P16-CG2	SOP 8	PA20SO20D-EO-210
EXCELSEMI	ES25P16	SOP 8	PA8SO8D-210
EXCELSEMI	ES29LV800DB	TSOP 48	PA48TS48D1
EXCELSEMI	ES29LV800DT	TSOP 48	PA48TS48D1
EXCELSEMI	ES29LV160DB	TSOP 48	PA48TS48D1
EXCELSEMI	ES29LV160DT	TSOP 48	PA48TS48D1
EXCELSEMI	ES29LV320DB	TSOP 48	PA48TS48D1
EXCELSEMI	ES29LV320DB	BGA 48	HA48BG48DBC
EXCELSEMI	ES29LV320DT	TSOP 48	PA48TS48D1
EXCELSEMI	ES29LV320DT	BGA 48	HA48BG48DBC

EXCELSEMI	ES29LV400DB	TSOP 48	PA48TS48D1
EXCELSEMI	ES29LV400DB	BGA 48	HA48BG48DBC
EXCELSEMI	ES29LV400DT	TSOP 48	PA48TS48D1
EXCELSEMI	ES29LV400DT	BGA 48	HA48BG48DBC
EXCELSEMI	ES29LV400EB	TSOP 48	PA48TS48D1
EXCELSEMI	ES29LV400EB	BGA 48	HA48BG48DBC
EXCELSEMI	ES29LV400ET	TSOP 48	PA48TS48D1
EXCELSEMI	ES29LV400ET	BGA 48	HA48BG48DBC
EXCELSEMI	ES29LV800DB	SOP 44	PA44SO44D
EXCELSEMI	ES29LV800DB	BGA 48	HA48BG48DBC
EXCELSEMI	ES29LV800DT	SOP 44	PA44SO44D
EXCELSEMI	ES29LV800DT	BGA 48	HA48BG48DBC
EXCELSEMI	ES29LV800ET	TSOP 48	PA48TS48D1
EXCELSEMI	ES29LV800ET	BGA 48	HA48BG48DBC
EXCELSEMI	ES29LV800EB	TSOP 48	PA48TS48D1
EXCELSEMI	ES29LV800EB	BGA 48	HA48BG48DBC
EXCELSEMI	ES29LV160DB	SOP 44	PA44SO44D
EXCELSEMI	ES29LV160DT	SOP 44	PA44SO44D
EXCELSEMI	ES29LV160EB	SOP 44	PA44SO44D
EXCELSEMI	ES29LV160EB	TSOP 48	PA48TS48D1
EXCELSEMI	ES29LV160ET	SOP 44	PA44SO44D
EXCELSEMI	ES29LV160ET	TSOP 48	PA48TS48D1
EXCELSEMI	ES29LV160FB	BGA 48	HA48BG48DBC
EXCELSEMI	ES29LV160FB	TSOP 48	PA48TS48D1
EXCELSEMI	ES29LV160FT	BGA 48	HA48BG48DBC
EXCELSEMI	ES29LV160FT	TSOP 48	PA48TS48D1
EXCELSEMI	ES29LV320EB	TSOP 48	PA48TS48D1
EXCELSEMI	ES29LV320ET	TSOP 48	PA48TS48D1
FAIRCHILD	NM93C06	DIP 8	
FAIRCHILD	NM93C06	TSSOP 8	PA8TSS-OT
FAIRCHILD	NM93C06	SOIC 8	PA16SO16D-EO-150
FAIRCHILD	NM93C46	DIP 8	
FAIRCHILD	NM93C46	TSSOP 8	PA8TSS-OT
FAIRCHILD	NM93C46	SOIC 8	PA16SO16D-EO-150
FAIRCHILD	NM93C56	DIP 8	
FAIRCHILD	NM93C56	TSSOP 8	PA8TSS-OT
FAIRCHILD	NM93C56	SOIC 8	PA16SO16D-EO-150
FAIRCHILD	NM93C66	DIP 8	
FAIRCHILD	NM93C66	TSSOP 8	PA8TSS-OT
FAIRCHILD	NM93C66	SOIC 8	PA16SO16D-EO-150
FAIRCHILD	NM93C86	DIP 8	
FAIRCHILD	NM93C86	TSSOP 8	PA8TSS-OT
FAIRCHILD	NM93C86	SOIC 8	PA16SO16D-EO-150
FAIRCHILD	NM93CS06	TSSOP 8	PA8TSS-OT
FAIRCHILD	NM93CS06	SOIC 8	PA16SO16D-EO-150
FAIRCHILD	NM93CS46	DIP 8	
FAIRCHILD	NM93CS46	TSSOP 8	PA8TSS-OT
FAIRCHILD	NM93CS46	SOIC 8	PA16SO16D-EO-150
FAIRCHILD	NM93CS56	DIP 8	
FAIRCHILD	NM93CS56	TSSOP 8	PA8TSS-OT
FAIRCHILD	NM93CS56	SOIC 8	PA16SO16D-EO-150
FAIRCHILD	NM93CS66	DIP 8	
FAIRCHILD	NM93CS66	TSSOP 8	PA8TSS-OT
FAIRCHILD	NM93CS66	SOIC 8	PA16SO16D-EO-150
FAIRCHILD	FM24C02U-N	DIP 8	
FAIRCHILD	FM24C02U-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM24C02U-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	FM24C02U-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	FM24C02UF-N	DIP 8	
FAIRCHILD	FM24C02UF-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM24C02UF-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	FM24C02UF-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	FM24C03U-N	DIP 8	
FAIRCHILD	FM24C03U-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM24C03U-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	FM24C03U-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	FM24C03UF-N	DIP 8	
FAIRCHILD	FM24C03UF-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM24C03UF-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	FM24C03UF-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	FM24C04U-N	DIP 8	
FAIRCHILD	FM24C04U-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM24C04U-MT8	TSSOP 8	PA8TSS8D



FAIRCHILD	FM24C04U-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	FM24C04UF-N	DIP 8	
FAIRCHILD	FM24C04UF-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM24C04UF-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	FM24C04UF-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	FM24C05U-N	DIP 8	
FAIRCHILD	FM24C05U-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM24C05U-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	FM24C05U-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	FM24C05UF-N	DIP 8	
FAIRCHILD	FM24C05UF-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM24C05UF-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	FM24C05UF-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	FM24C08U-N	DIP 8	
FAIRCHILD	FM24C08U-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM24C08U-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	FM24C08U-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	FM24C08UF-N	DIP 8	
FAIRCHILD	FM24C08UF-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM24C08UF-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	FM24C08UF-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	FM24C09U-N	DIP 8	
FAIRCHILD	FM24C09U-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM24C09U-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	FM24C09U-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	FM24C09UF-N	DIP 8	
FAIRCHILD	FM24C09UF-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM24C09UF-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	FM24C09UF-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	FM24C16U-N	DIP 8	
FAIRCHILD	FM24C16U-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM24C16U-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	FM24C16U-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	FM24C16UF-N	DIP 8	
FAIRCHILD	FM24C16UF-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM24C16UF-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	FM24C16UF-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	FM24C17U-N	DIP 8	
FAIRCHILD	FM24C17U-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM24C17U-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	FM24C17U-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	FM24C17UF-N	DIP 8	
FAIRCHILD	FM24C17UF-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM24C17UF-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	FM24C17UF-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	FM24C32U-N	DIP 8	
FAIRCHILD	FM24C32U-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM24C32UF-N	DIP 8	
FAIRCHILD	FM24C32UF-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM24C64-N	DIP 8	
FAIRCHILD	FM24C64-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM24C64-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	FM24C64-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	FM24C64F-N	DIP 8	
FAIRCHILD	FM24C64F-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM24C64F-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	FM24C64F-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	FM24C128-N	DIP 8	
FAIRCHILD	FM24C128-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM24C128-MT8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM24C128F-N	DIP 8	
FAIRCHILD	FM24C128F-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM24C128F-MT8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM34C02U-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	FM34C02U-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	FM34C02U-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	NM24C02U-N	DIP 8	
FAIRCHILD	NM24C02U-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM24C02U-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	NM24C02U-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	NM24C02UF-N	DIP 8	
FAIRCHILD	NM24C02UF-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM24C02UF-MT8	TSSOP 8	PA8TSS8D

FAIRCHILD	NM24C02UF-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	NM24C03U-N	DIP 8	
FAIRCHILD	NM24C03U-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM24C03U-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	NM24C03U-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	NM24C03UF-N	DIP 8	
FAIRCHILD	NM24C03UF-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM24C03UF-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	NM24C03UF-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	NM24C04U-N	DIP 8	
FAIRCHILD	NM24C04U-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM24C04U-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	NM24C04U-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	NM24C04UF-N	DIP 8	
FAIRCHILD	NM24C04UF-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM24C04UF-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	NM24C04UF-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	NM24C05U-N	DIP 8	
FAIRCHILD	NM24C05U-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM24C05U-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	NM24C05U-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	NM24C05UF-N	DIP 8	
FAIRCHILD	NM24C05UF-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM24C05UF-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	NM24C05UF-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	NM24C08U-N	DIP 8	
FAIRCHILD	NM24C08U-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM24C08U-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	NM24C08U-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	NM24C08UF-N	DIP 8	
FAIRCHILD	NM24C08UF-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM24C08UF-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	NM24C08UF-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	NM24C09U-N	DIP 8	
FAIRCHILD	NM24C09U-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM24C09U-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	NM24C09U-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	NM24C09UF-N	DIP 8	
FAIRCHILD	NM24C09UF-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM24C09UF-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	NM24C09UF-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	NM24C16U-N	DIP 8	
FAIRCHILD	NM24C16U-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM24C16U-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	NM24C16U-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	NM24C16UF-N	DIP 8	
FAIRCHILD	NM24C16UF-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM24C16UF-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	NM24C16UF-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	NM24C17U-N	DIP 8	
FAIRCHILD	NM24C17U-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM24C17U-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	NM24C17U-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	NM24C17UF-N	DIP 8	
FAIRCHILD	NM24C17UF-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM24C17UF-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	NM24C17UF-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	NM24C32U-N	DIP 8	
FAIRCHILD	NM24C32U-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM24C32UF-N	DIP 8	
FAIRCHILD	NM24C32UF-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM24C64-N	DIP 8	
FAIRCHILD	NM24C64-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM24C64-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	NM24C64-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	NM24C64F-N	DIP 8	
FAIRCHILD	NM24C64F-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM24C64F-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	NM24C64F-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	NM24C128-N	DIP 8	
FAIRCHILD	NM24C128-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM24C128-MT8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM24C128F-N	DIP 8	

FAIRCHILD	NM24C128F-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM24C128F-MT8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM34C02U-M8	SOIC 8	PA8SO8D-EO-150
FAIRCHILD	NM34C02U-MT8	TSSOP 8	PA8TSS8D
FAIRCHILD	NM34C02U-MT8	TSSOP 8	PA24TSS24D
FAIRCHILD	NM25C020	DIP 8	
FAIRCHILD	NM25C020	SOIC 8	PA16SO16D-EO-150
FAIRCHILD	NM25C020	TSSOP 8	PA8TSS8D
FAIRCHILD	NM25C020	TSSOP 8	PA24TSS24D
FAIRCHILD	NM25C040	DIP 8	
FAIRCHILD	NM25C040	SOIC 8	PA16SO16D-EO-150
FAIRCHILD	NM25C040	TSSOP 8	PA8TSS8D
FAIRCHILD	NM25C040	TSSOP 8	PA24TSS24D
FAIRCHILD	NM25C160	DIP 8	
FAIRCHILD	NM25C160	SOIC 8	PA16SO16D-EO-150
FAIRCHILD	NM25C160	TSSOP 8	PA8TSS8D
FAIRCHILD	NM25C160	TSSOP 8	PA24TSS24D
FAIRCHILD	NM25C640	DIP 8	
FAIRCHILD	NM25C640	SOIC 8	PA16SO16D-EO-150
FAIRCHILD	NM25C640	TSSOP 8	PA8TSS8D
FAIRCHILD	NM25C640	TSSOP 8	PA24TSS24D
FAIRCHILD	FM27C040Q	DIP 32	
FAIRCHILD	F2716	DIP 24	
FAIRCHILD	F2732	DIP 24	
FAIRCHILD	NMC27C64	DIP 28	
FAIRCHILD	NMC27LC64	DIP 28	
FAIRCHILD	NM27C128	DIP 28	
FAIRCHILD	NM27C128	PLCC 32	PA32PL28D-YA
FAIRCHILD	FM27C256	DIP 28	
FAIRCHILD	FM27C256	PLCC 32	PA32PL28D-YA
FAIRCHILD	NM27C256	DIP 28	
FAIRCHILD	NM27C256	PLCC 32	PA32PL28D-YA
FAIRCHILD	NM27C256B	DIP 28	
FAIRCHILD	NM27C256B	PLCC 32	PA32PL28D-YA
FAIRCHILD	FM27C512	DIP 28	
FAIRCHILD	FM27C512	PLCC 32	PA32PL28D-YA
FAIRCHILD	NM27C512	DIP 28	
FAIRCHILD	NM27C512	PLCC 32	PA32PL28D-YA
FAIRCHILD	NM27LC256	DIP 28	
FAIRCHILD	NM27LC256	PLCC 32	PA32PL28D-YA
FAIRCHILD	NM27LC512	DIP 28	
FAIRCHILD	NM27LC512	PLCC 32	PA32PL28D-YA
FAIRCHILD	NM27LV512	DIP 28	
FAIRCHILD	NM27LV512	PLCC 32	PA32PL28D-YA
FAIRCHILD	NM27P512	DIP 28	
FAIRCHILD	NM27P512	PLCC 32	PA32PL28D-YA
FAIRCHILD	FM27C010	DIP 32	
FAIRCHILD	FM27C010	PLCC 32	PA32PL32D
FAIRCHILD	FM27LV010	DIP 32	
FAIRCHILD	FM27LV010	PLCC 32	PA32PL32D
FAIRCHILD	NM27C010	DIP 32	
FAIRCHILD	NM27C010	PLCC 32	PA32PL32D
FAIRCHILD	NM27C010	TSOP 32	PA32TS20/PA32TS32D-20
FAIRCHILD	NM27LV010	DIP 32	
FAIRCHILD	NM27LV010	PLCC 32	PA32PL32D
FAIRCHILD	NM27LV010	TSOP 32	PA32TS20/PA32TS32D-20
FAIRCHILD	NM27LV010B	DIP 32	
FAIRCHILD	NM27LV010B	PLCC 32	PA32PL32D
FAIRCHILD	NM27LV010B	TSOP 32	PA32TS20/PA32TS32D-20
FAIRCHILD	NM27C020	DIP 32	
FAIRCHILD	NM27C020	PLCC 32	PA32PL32D
FAIRCHILD	NM27C020	TSOP 32	PA32TS20/PA32TS32D-20
FAIRCHILD	FM27C040	DIP 32	
FAIRCHILD	FM27C040	PLCC 32	PA32PL32D
FAIRCHILD	NM27C040	DIP 32	
FAIRCHILD	NM27C040	PLCC 32	PA32PL32D
FAIRCHILD	NM27P040	DIP 32	
FAIRCHILD	NM27P040	PLCC 32	PA32PL32D
FAIRCHILD	NM27C210	DIP 40	
FAIRCHILD	NM27C210	PLCC 44	PA44-48U
FAIRCHILD	NM27LV210	PLCC 44	PA44-48U
FAIRCHILD	NM27C240	DIP 40	
FAIRCHILD	NM27C240	PLCC 44	PA44-48U

FUJITSU	MB8541P	DIP 8	
FUJITSU	MB84VD23280FA	BGA 65	PA65BGA48DA
FUJITSU	MB84VD23381FJ	BGA 65	PA65BGA48DA
FUJITSU	MB84VD23381HJ	BGA 56	PA56BG48DG
FUJITSU	MB84VF5F5F5J2	BGA 107	PA107BG48DA
FUJITSU	MB84VF5F5F4J2	BGA 107	PA107BG48DA
FUJITSU	MB89P625	DIP 64	HA64ZF48D
FUJITSU	MB89P625	DIP 64	64SD-28DP-8L
FUJITSU	MBM27128	DIP 28	
FUJITSU	MBM27128	PLCC 32	PA32PL28D-YA
FUJITSU	MBM2716	DIP 24	
FUJITSU	MBM2716H	DIP 24	
FUJITSU	MBM27256	DIP 28	
FUJITSU	MBM27256	PLCC 32	PA32PL28D-YA
FUJITSU	MBM2732	DIP 24	
FUJITSU	MBM2732A	DIP 24	
FUJITSU	MBM2764	DIP 28	
FUJITSU	MBM27C1000	DIP 32	
FUJITSU	MBM27C1001	DIP 32	
FUJITSU	MBM27C1001A	DIP 32	
FUJITSU	MBM27C128	DIP 28	
FUJITSU	MBM27C128P	DIP 28	
FUJITSU	MBM27C128P	PLCC 32	PA32PL28D-YA
FUJITSU	MBM27C256	DIP 28	
FUJITSU	MBM27C256	PLCC 32	PA32PL28D-YA
FUJITSU	MBM27C256A	DIP 28	
FUJITSU	MBM27C256A	PLCC 32	PA32PL28D-YA
FUJITSU	MBM27C256A-##-W	DIP 28	
FUJITSU	MBM27C256AP	DIP 28	
FUJITSU	MBM27C256AP	PLCC 32	PA32PL28D-YA
FUJITSU	MBM27C256AP	SOIC 28	PA28SO28D-EO-300
FUJITSU	MBM27C256H	DIP 28	
FUJITSU	MBM27C256H	PLCC 32	PA32PL28D-YA
FUJITSU	MBM27C512	DIP 28	
FUJITSU	MBM27C512	PLCC 32	PA32PL28D-YA
FUJITSU	MBM27C512P	DIP 28	
FUJITSU	MBM27C512P	PLCC 32	PA32PL28D-YA
FUJITSU	MBM27C64	DIP 28	
FUJITSU	MBM27C4001	DIP 32	
FUJITSU	MBM28C64	DIP 28	
FUJITSU	MBM28C65	DIP 28	
FUJITSU	MBM28C256	DIP 28	
FUJITSU	MBM27C1024	DIP 40	
FUJITSU	MBM27C1024	PLCC 44	PA44-48U
FUJITSU	MBM27C2048	DIP 40	
FUJITSU	MBM27C2048	PLCC 44	PA44-48U
FUJITSU	MBM27C4096	DIP 40	
FUJITSU	MBM27C4096	PLCC 44	PA44-48U
FUJITSU	MBM28F010	DIP 32	
FUJITSU	MBM28F010	PLCC 32	PA32PL32D
FUJITSU	MBM28F010	TSOP 32	PA32TS20/PA32TS32D-20
FUJITSU	MBM29F002T	DIP 32	
FUJITSU	MBM29F002T	PLCC 32	PA32PL32D
FUJITSU	MBM29F002T	TSOP 32	PA32TS20/PA32TS32D-20
FUJITSU	MBM29F002B	DIP 32	
FUJITSU	MBM29F002B	PLCC 32	PA32PL32D
FUJITSU	MBM29F002B	TSOP 32	PA32TS20/PA32TS32D-20
FUJITSU	MBM29F002TC	PLCC 32	PA32PL32D
FUJITSU	MBM29F002TC	TSOP 32	PA32TS20/PA32TS32D-20
FUJITSU	MBM29F002BC	PLCC 32	PA32PL32D
FUJITSU	MBM29F002BC	TSOP 32	PA32TS20/PA32TS32D-20
FUJITSU	MBM29F002SB	TSOP 40	PA40TS40D
FUJITSU	MBM29F002ST	TSOP 40	PA40TS40D
FUJITSU	MBM29F004TC	PLCC 32	PA32PL32D
FUJITSU	MBM29F004TC	TSOP 32	PA32TS20/PA32TS32D-20
FUJITSU	MBM29F004BC	PLCC 32	PA32PL32D
FUJITSU	MBM29F004BC	TSOP 32	PA32TS20/PA32TS32D-20
FUJITSU	MBM29F040	DIP 32	
FUJITSU	MBM29F040A	PLCC 32	PA32PL32D
FUJITSU	MBM29F040A	TSOP 32	PA32TS20/PA32TS32D-20
FUJITSU	MBM29F040B	DIP 32	
FUJITSU	MBM29F040C	DIP 32	
FUJITSU	MBM29F040C	PLCC 32	PA32PL32D

FUJITSU	MBM29F040C	TSOP 32	PA32TS20/PA32TS32D-20
FUJITSU	MBM29F080	SOP 44	PA44SO44D
FUJITSU	MBM29F080	TSOP 48	PA48TS48D
FUJITSU	MBM29F080	TSOP 40	PA40TS40D
FUJITSU	MBM29F080A	SOP 44	PA44SO44D
FUJITSU	MBM29F080A	TSOP 48	PA48TS48D
FUJITSU	MBM29F080A	TSOP 40	PA40TS40D
FUJITSU	MBM29F016	TSOP 48	PA48TS48D
FUJITSU	MBM29F016A	TSOP 48	PA48TS48D
FUJITSU	MBM29F017A	TSOP 48	PA48TS48D
FUJITSU	MBM29LV001TC	PLCC 32	PA32PL32D
FUJITSU	MBM29LV001TC	TSOP 32	PA32TS20/PA32TS32D-20
FUJITSU	MBM29LV001BC	PLCC 32	PA32PL32D
FUJITSU	MBM29LV001BC	TSOP 32	PA32TS20/PA32TS32D-20
FUJITSU	MBM29LV002T	TSOP 40	PA40TS40D
FUJITSU	MBM29LV002B	TSOP 40	PA40TS40D
FUJITSU	MBM29LV002TC	TSOP 40	PA40TS40D
FUJITSU	MBM29LV002BC	TSOP 40	PA40TS40D
FUJITSU	MBM29LV004T	TSOP 40	PA40TS40D
FUJITSU	MBM29LV004B	TSOP 40	PA40TS40D
FUJITSU	MBM29LV004TC	TSOP 40	PA40TS40D
FUJITSU	MBM29LV004BC	TSOP 40	PA40TS40D
FUJITSU	MBM29LV008T	TSOP 40	PA40TS40D
FUJITSU	MBM29LV008B	TSOP 40	PA40TS40D
FUJITSU	MBM29LV008TA	TSOP 40	PA40TS40D
FUJITSU	MBM29LV008BA	TSOP 40	PA40TS40D
FUJITSU	MBM29LV008BT	TSOP 40	PA40TS40D
FUJITSU	MBM29LV008BB	TSOP 40	PA40TS40D
FUJITSU	MBM29LV080	TSOP 40	PA40TS40D
FUJITSU	MBM29LV080A	TSOP 40	PA40TS40D
FUJITSU	MBM29F200BA	SOP 44	PA44SO44D
FUJITSU	MBM29F200BA	TSOP 48	PA48TS48D
FUJITSU	MBM29F200TA	SOP 44	PA44SO44D
FUJITSU	MBM29F200TA	TSOP 48	PA48TS48D
FUJITSU	MBM29F200BB	SOP 44	PA44SO44D
FUJITSU	MBM29F200BB	TSOP 48	PA48TS48D
FUJITSU	MBM29F200BT	SOP 44	PA44SO44D
FUJITSU	MBM29F200BT	TSOP 48	PA48TS48D
FUJITSU	MBM29F200BC	SOP 44	PA44SO44D
FUJITSU	MBM29F200BC	TSOP 48	PA48TS48D
FUJITSU	MBM29F200TC	SOP 44	PA44SO44D
FUJITSU	MBM29F200TC	TSOP 48	PA48TS48D
FUJITSU	MBM29F400BB	SOP 44	PA44SO44D
FUJITSU	MBM29F400BB	TSOP 48	PA48TS48D
FUJITSU	MBM29F400BT	SOP 44	PA44SO44D
FUJITSU	MBM29F400BT	TSOP 48	PA48TS48D
FUJITSU	MBM29F400BA	SOP 44	PA44SO44D
FUJITSU	MBM29F400BA	TSOP 48	PA48TS48D
FUJITSU	MBM29F400TA	SOP 44	PA44SO44D
FUJITSU	MBM29F400TA	TSOP 48	PA48TS48D
FUJITSU	MBM29F400BC	SOP 44	PA44SO44D
FUJITSU	MBM29F400BC	TSOP 48	PA48TS48D
FUJITSU	MBM29F400TC	SOP 44	PA44SO44D
FUJITSU	MBM29F400TC	TSOP 48	PA48TS48D
FUJITSU	MBM29F800B	TSOP 48	PA48TS48D
FUJITSU	MBM29F800T	TSOP 48	PA48TS48D
FUJITSU	MBM29F800BA	TSOP 48	PA48TS48D
FUJITSU	MBM29F800TA	TSOP 48	PA48TS48D
FUJITSU	MBM29F800BA	SOP 44	PA44SO44D
FUJITSU	MBM29F800TA	SOP 44	PA44SO44D
FUJITSU	MBM29F160BE	TSOP 48	PA48TS48D
FUJITSU	MBM29F160TE	TSOP 48	PA48TS48D
FUJITSU	MBM29LV200BB	SOP 44	PA44SO44D
FUJITSU	MBM29LV200BB	TSOP 48	PA48TS48D
FUJITSU	MBM29LV200BT	SOP 44	PA44SO44D
FUJITSU	MBM29LV200BT	TSOP 48	PA48TS48D
FUJITSU	MBM29LV200BC	SOP 44	PA44SO44D
FUJITSU	MBM29LV200BC	TSOP 48	PA48TS48D
FUJITSU	MBM29LV200TC	SOP 44	PA44SO44D
FUJITSU	MBM29LV200TC	TSOP 48	PA48TS48D
FUJITSU	MBM29LV400B	SOP 44	PA44SO44D
FUJITSU	MBM29LV400B	TSOP 48	PA48TS48D
FUJITSU	MBM29LV400T	SOP 44	PA44SO44D

FUJITSU	MBM29LV400T	TSOP 48	PA48TS48D
FUJITSU	MBM29LV400BB	SOP 44	PA44SO44D
FUJITSU	MBM29LV400BB	TSOP 48	PA48TS48D
FUJITSU	MBM29LV400BT	SOP 44	PA44SO44D
FUJITSU	MBM29LV400BT	TSOP 48	PA48TS48D
FUJITSU	MBM29LV400BC	SOP 44	PA44SO44D
FUJITSU	MBM29LV400BC	TSOP 48	PA48TS48D
FUJITSU	MBM29LV400BC	BGA 48	HA48BG48DBC
FUJITSU	MBM29LV400TC	SOP 44	PA44SO44D
FUJITSU	MBM29LV400TC	TSOP 48	PA48TS48D
FUJITSU	MBM29LV400TC	BGA 48	HA48BG48DBC
FUJITSU	MBM29LV800BA	SOP 44	PA44SO44D
FUJITSU	MBM29LV800BA	TSOP 48	PA48TS48D
FUJITSU	MBM29LV800BA	BGA 48	HA48BG48DBC
FUJITSU	MBM29LV800TA	SOP 44	PA44SO44D
FUJITSU	MBM29LV800TA	TSOP 48	PA48TS48D
FUJITSU	MBM29LV800TA	BGA 48	HA48BG48DBC
FUJITSU	MBM29LV800BB	SOP 44	PA44SO44D
FUJITSU	MBM29LV800BB	TSOP 48	PA48TS48D
FUJITSU	MBM29LV800BT	SOP 44	PA44SO44D
FUJITSU	MBM29LV800BT	TSOP 48	PA48TS48D
FUJITSU	MBM29LV800BE	TSOP 48	PA48TS48D
FUJITSU	MBM29LV800TE	TSOP 48	PA48TS48D
FUJITSU	MBM29LV160B	TSOP 48	PA48TS48D
FUJITSU	MBM29LV160T	TSOP 48	PA48TS48D
FUJITSU	MBM29LV160BB	SOP 44	PA44SO44D
FUJITSU	MBM29LV160BB	TSOP 48	PA48TS48D
FUJITSU	MBM29LV160BT	SOP 44	PA44SO44D
FUJITSU	MBM29LV160BT	TSOP 48	PA48TS48D
FUJITSU	MBM29LV160DB	SOP 44	PA44SO44D
FUJITSU	MBM29LV160DB	TSOP 48	PA48TS48D
FUJITSU	MBM29LV160DT	SOP 44	PA44SO44D
FUJITSU	MBM29LV160DT	TSOP 48	PA48TS48D
FUJITSU	MBM29LV160BE	TSOP 48	PA48TS48D
FUJITSU	MBM29LV160TE	TSOP 48	PA48TS48D
FUJITSU	MBM29LV160BE	BGA 48	PA48BG48DAG
FUJITSU	MBM29LV160TE	BGA 48	PA48BG48DAG
FUJITSU	MBM29LV320BE	TSOP 48	PA48TS48D
FUJITSU	MBM29LV320TE	TSOP 48	PA48TS48D
FUJITSU	MBM29LV650UE	TSOP 48	PA48TS48D
FUJITSU	MBM29LV651UE	TSOP 48	PA48TS48D
FUJITSU	MBM29DL316CB	TSOP 40	PA40TS40D
FUJITSU	MBM29DL316CT	TSOP 40	PA40TS40D
FUJITSU	MBM29DL400BB	SOP 44	PA44SO44D
FUJITSU	MBM29DL400BB	TSOP 48	PA48TS48D
FUJITSU	MBM29DL400BT	SOP 44	PA44SO44D
FUJITSU	MBM29DL400BT	TSOP 48	PA48TS48D
FUJITSU	MBM29DL400BC	TSOP 48	PA48TS48D
FUJITSU	MBM29DL400BC	BGA 48	HA48BG48DBC
FUJITSU	MBM29DL400TC	TSOP 48	PA48TS48D
FUJITSU	MBM29DL400TC	BGA 48	HA48BG48DBC
FUJITSU	MBM29DL800BB	SOP 44	PA44SO44D
FUJITSU	MBM29DL800BB	TSOP 48	PA48TS48D
FUJITSU	MBM29DL800BT	SOP 44	PA44SO44D
FUJITSU	MBM29DL800BT	TSOP 48	PA48TS48D
FUJITSU	MBM29DL800BA	TSOP 48	PA48TS48D
FUJITSU	MBM29DL800BA	BGA 48	HA48BG48DBC
FUJITSU	MBM29DL800TA	TSOP 48	PA48TS48D
FUJITSU	MBM29DL800TA	BGA 48	HA48BG48DBC
FUJITSU	MBM29DL161BD	BGA 48	PA48BG48DAH
FUJITSU	MBM29DL161TD	BGA 48	PA48BG48DAH
FUJITSU	MBM29DL162CB	TSOP 48	PA48TS48D
FUJITSU	MBM29DL162CT	TSOP 48	PA48TS48D
FUJITSU	MBM29DL163CB	TSOP 48	PA48TS48D
FUJITSU	MBM29DL163CT	TSOP 48	PA48TS48D
FUJITSU	MBM29DL32BF	TSOP 48	PA48TS48D
FUJITSU	MBM29DL32TF	TSOP 48	PA48TS48D
FUJITSU	MBM29DL34BF	TSOP 48	PA48TS48D
FUJITSU	MBM29DL34TF	TSOP 48	PA48TS48D
FUJITSU	MBM29DL322CB	TSOP 48	PA48TS48D
FUJITSU	MBM29DL322CT	TSOP 48	PA48TS48D
FUJITSU	MBM29DL323CB	TSOP 48	PA48TS48D
FUJITSU	MBM29DL323CT	TSOP 48	PA48TS48D

FUJITSU	MBM29DL322BE		TSOP 48	PA48TS48D
FUJITSU	MBM29DL322TE		TSOP 48	PA48TS48D
FUJITSU	MBM29PL160CB		SOP 44	PA44SO44D
FUJITSU	MBM29PL160CB		TSOP 48	PA48TS48D
FUJITSU	MBM29PL160CT		SOP 44	PA44SO44D
FUJITSU	MBM29PL160CT		TSOP 48	PA48TS48D
FUJITSU	MBM29PL160BD		SOP 44	PA44SO44D
FUJITSU	MBM29PL160TD		TSOP 48	PA48TS48D
FUJITSU	MBM29PL32BM		TSOP 48	PA48TS48D
FUJITSU	MBM29PL32TM		TSOP 48	PA48TS48D
FUJITSU	MBM29SL800BD		TSOP 48	PA48TS48D
FUJITSU	MBM29SL800BD		BGA 48	HA48BG48DBC
FUJITSU	MBM29SL800TD		TSOP 48	PA48TS48D
FUJITSU	MBM29SL800TD		BGA 48	HA48BG48DBC
FUJITSU	MBM29SL800BE		TSOP 48	PA48TS48D
FUJITSU	MBM29SL800TE		TSOP 48	PA48TS48D
FUJITSU	MBM29SL800CB		TSOP 48	PA48TS48D
FUJITSU	MBM29SL800CT		TSOP 48	PA48TS48D
FUJITSU	MBM29SL160CB		TSOP 48	PA48TS48D
FUJITSU	MBM29SL160CT		TSOP 48	PA48TS48D
FUJITSU	MSP55LV128		SOP 44	PA44SO44D
FUJITSU	MSP55LV256		SOP 44	PA44SO44D
GENERAL INSTRUMENT		27256	DIP 28	
GENERAL INSTRUMENT	27C64		DIP 28	
GENERAL INSTRUMENT	27C128		DIP 28	
GENERAL INSTRUMENT	27C128		PLCC 32	PA32PL28D-YA
GENERAL INSTRUMENT	27C256		DIP 28	
GENERAL INSTRUMENT	27C256		PLCC 32	PA32PL28D-YA
GENERAL INSTRUMENT	27C512		DIP 28	
GENERAL INSTRUMENT	27C512		PLCC 32	PA32PL28D-YA
GENERAL INSTRUMENT	27HC64		DIP 28	
GENERAL INSTRUMENT	27HC64L		PLCC 32	PA32PL28D-YA
GENERAL INSTRUMENT	28C04		DIP 24	
GENERAL INSTRUMENT	28C04F		DIP 24	
GENERAL INSTRUMENT	28C16		DIP 24	
GENERAL INSTRUMENT	28C17		DIP 28	
GENERAL INSTRUMENT	28C17F		DIP 28	
GENERAL INSTRUMENT	28C64		DIP 28	
GENERAL INSTRUMENT	28C64A		DIP 28	
GENERAL INSTRUMENT	28C64AX		DIP 28	
GENERIC ALGORITHM	27128<21V>		DIP 28	
GENERIC ALGORITHM	27128A<12.5V>		DIP 28	
GENERIC ALGORITHM	2716<25V>		DIP 24	
GENERIC ALGORITHM	27256<12.5>		DIP 28	
GENERIC ALGORITHM	27512<12.5V>		PLCC 32	PA32PL28D-YA
GENERIC ALGORITHM	27C512<12.5V>		PLCC 32	PA32PL28D-YA
GENERIC ALGORITHM	2732<25V>		DIP 24	
GENERIC ALGORITHM	2732A<21V>		DIP 24	
GENERIC ALGORITHM	2732B<12.5V>		DIP 24	
GENERIC ALGORITHM	27512<12.5V>		DIP 28	
GENERIC ALGORITHM	2764<21V>		DIP 28	
GENERIC ALGORITHM	2764A<12.5V>		DIP 28	
GENERIC ALGORITHM	27C128<12.5V>		DIP 28	
GENERIC ALGORITHM	27C128<21V>		DIP 28	
GENERIC ALGORITHM	27C16<25V>		DIP 24	
GENERIC ALGORITHM	27C256<12.5V>		DIP 28	
GENERIC ALGORITHM	27C32<25V>		DIP 24	
GENERIC ALGORITHM	27C512<12.5V>		DIP 28	
GENERIC ALGORITHM	27C64<12.5V>		DIP 28	
GENERIC ALGORITHM	27C64<21V>		DIP 28	
GREENWICH	GR281		EDIP 24	
GREENWICH	GR881		EDIP 28	
GREENWICH	GR3281		EDIP 28	
GREENWICH	GR12882		EDIP 32	
GREENWICH	GR12883		EDIP 32	
GREENWICH	GR27128		DIP 28	
GREENWICH	GR27256		DIP 28	
GREENWICH	GR27512		DIP 28	
GREENWICH	GR2764		DIP 28	
HOLTEK	HT27C512		DIP 28	
HOLTEK	HT27C512		PLCC 32	PA32PL28D-YA
HOLTEK	HT27C010		DIP 32	
HOLTEK	HT27C010		PLCC 32	PA32PL32D

HOLTEK	HT27C010	SOP 32	PA32SO32D-EO-450
HOLTEK	HT27C020	DIP 32	
HOLTEK	HT27C020	PLCC 32	PA32PL32D
HOLTEK	HT27C020	SOP 32	PA32SO32D-EO-450
HOLTEK	HT27C040	DIP 32	
HOLTEK	HT27C040	PLCC 32	PA32PL32D
HOLTEK	HT27C040	SOP 32	PA32SO32D-EO-450
HOLTEK	HT27LC512	DIP 28	
HOLTEK	HT27LC512	PLCC 32	PA32PL28D-YA
HOLTEK	HT27LC010	DIP 32	
HOLTEK	HT27LC010	PLCC 32	PA32PL32D
HOLTEK	HT27LC010	TSOP 32	PA32TS20/PA32TS32D-20
HOLTEK	HT27LC010	SOP 32	PA32SO32D-EO-450
HOLTEK	HT27LC020	DIP 32	
HOLTEK	HT27LC020	PLCC 32	PA32PL32D
HOLTEK	HT27LC020	TSOP 32	PA32TS20/PA32TS32D-20
HOLTEK	HT27LC020	SOP 32	PA32SO32D-EO-450
HOLTEK	HT27LC040	DIP 32	
HOLTEK	HT27LC040	PLCC 32	PA32PL32D
HOLTEK	HT27LC040	TSOP 32	PA32TS20/PA32TS32D-20
HOLTEK	HT27LC040	SOP 32	PA32SO32D-EO-450
HOLTEK	HT93C46	DIP 8	
HOLTEK	HT93C46	SOIC 8	PA16SO16D-EO-150
HOLTEK	HT93C56	DIP 8	
HOLTEK	HT93C56	SOIC 8	PA16SO16D-EO-150
HOLTEK	HT93C66	DIP 8	
HOLTEK	HT93C66	SOIC 8	PA16SO16D-EO-150
HOLTEK	HT93LC46	DIP 8	
HOLTEK	HT93LC46	TSSOP 8	PA8TSS-OT
HOLTEK	HT93LC46	SOIC 8	PA16SO16D-EO-150
HOLTEK	HT93LC56	DIP 8	
HOLTEK	HT93LC56	SOIC 8	PA16SO16D-EO-150
HOLTEK	HT93LC66	DIP 8	
HOLTEK	HT93LC66	TSSOP 8	PA8TSS-OT
HOLTEK	HT93LC66	SOIC 8	PA16SO16D-EO-150
HOLTEK	HT93LC86	DIP 8	
HOLTEK	HT93LC86	TSSOP 8	PA8TSS-OT
HOLTEK	HT93LC86	SOIC 8	PA16SO16D-EO-150
HITACHI	HN2764	DIP 28	
HITACHI	HN2764AG	DIP 28	
HITACHI	HN27128A	DIP 28	
HITACHI	HN27128AG	DIP 28	
HITACHI	HN27128AP	DIP 28	
HITACHI	HN27256	DIP 28	
HITACHI	HN27256G	DIP 28	
HITACHI	HN27256P	DIP 28	
HITACHI	HN27512	DIP 28	
HITACHI	HN27512G	DIP 28	
HITACHI	HN27512P	DIP 28	
HITACHI	HN27C101AG	DIP 32	
HITACHI	HN27C101AP	DIP 32	
HITACHI	HN27C101G	DIP 32	
HITACHI	HN27C101G	SOP 32	PA32SO32D-EO-450
HITACHI	HN27C101GP	SOP 32	PA32SO32D-EO-450
HITACHI	HN27C101P	DIP 32	
HITACHI	HN27C256	DIP 28	
HITACHI	HN27C256A	PLCC 32	PA32PL28D-YA
HITACHI	HN27C256A	SOIC 28	PA28SO28D-EO-300
HITACHI	HN27C256AG	DIP 28	
HITACHI	HN27C256H	PLCC 32	PA32PL28D-YA
HITACHI	HN27C256H	SOIC 28	PA28SO28D-EO-300
HITACHI	HN27C256HG	DIP 28	
HITACHI	HN27C256G	DIP 28	
HITACHI	HN27C301G	DIP 32	
HITACHI	HN27C301P	DIP 32	
HITACHI	HN27C4000G	DIP 40	
HITACHI	HN27C4001G	DIP 32	
HITACHI	HN27C512AG	DIP 28	
HITACHI	HN27C64	DIP 28	
HITACHI	HN27C64G	DIP 28	
HITACHI	HN462716	DIP 24	
HITACHI	HN462716G	DIP 24	
HITACHI	HN462732	DIP 24	



HITACHI	HN462732G	DIP 24	
HITACHI	HN48016P	DIP 24	
HITACHI	HN4827128G	DIP 28	
HITACHI	HN4827128P	DIP 28	
HITACHI	HN482732A	DIP 24	
HITACHI	HN482732AG	DIP 24	
HITACHI	HN482764G	DIP 28	
HITACHI	HN482764P	DIP 28	
HITACHI	HN58064	DIP 28	
HITACHI	HN58C65P	DIP 28	
RENESAS	HN58V65A	SOP 28	PA28SO28DB-EC-350
HITACHI	HN58C256P(Page)	DIP 28	
HITACHI	HN58C256P(Single)	DIP 28	
HITACHI	HN58C1001	DIP 32	
HITACHI	HN58C1001	SOP 32	PA32PS-32D-450
HITACHI	HN27C1024HG	DIP 40	
HITACHI	HN27C1024HG	PLCC 44	PA44-48U
HITACHI	HN27C4096	DIP 40	
HITACHI	HN27C4096	PLCC 44	PA44-48U
HITACHI	HN27C4096G	DIP 40	
HITACHI	HN27C4096G	PLCC 44	PA44-48U
HITACHI	HN27C4096HG	DIP 40	
HITACHI	HN27C4096HCC	PLCC 44	PA44-48U
HITACHI	HN27C4096AHG	DIP 40	
HITACHI	HN27C4096AHCC	PLCC 44	PA44-48U
HITACHI	HN28F101	DIP 32	
HITACHI	HN28F101	PLCC 32	PA32PL32D
HYNIX	HY2764	DIP 28	
HYNIX	HY27C64A	DIP 28	
HYNIX	HY27US08281A	TSOP 48	PA48TS48D
HYNIX	HY27US08281A(+Spare)	TSOP 48	PA48TS48D
HYNIX	HY27US08561A	TSOP 48	PA48TS48D
HYNIX	HY27US08561A(+Spare)	TSOP 48	PA48TS48D
HYNIX	HY27US08561A	BGA 63	HA63BG48DN
HYNIX	HY27US08561A(+Spare)	BGA 63	HA63BG48DN
HYNIX	HY27US08121A	TSOP 48	PA48TS48D
HYNIX	HY27US08121A(+Spare)	TSOP 48	PA48TS48D
HYNIX	HY27US08121A	BGA 63	HA63BG48DN
HYNIX	HY27US08121A(+Spare)	BGA 63	HA63BG48DN
HYNIX	HY27UF081G2M	TSOP 48	PA48TS48D
HYNIX	HY27UF081G2M(+Spare)	TSOP 48	PA48TS48D
HYNIX	HY27UF082G2M	TSOP 48	PA48TS48D
HYNIX	HY27UF082G2M(+Spare)	TSOP 48	PA48TS48D
HYNIX	HY27UF084G2M	TSOP 48	PA48TS48D
HYNIX	HY27UF084G2M(+Spare)	TSOP 48	PA48TS48D
HYNIX	HY29F002T	DIP 32	
HYNIX	HY29F002T	PLCC 32	PA32PL32D
HYNIX	HY29F002T	TSOP 32	PA32TS20/PA32TS32D-20
HYNIX	HY29F002B	DIP 32	
HYNIX	HY29F002B	PLCC 32	PA32PL32D
HYNIX	HY29F002B	TSOP 32	PA32TS20/PA32TS32D-20
HYNIX	HY29F002CT	PLCC 32	PA32PL32D
HYNIX	HY29F002TT	TSOP 32	PA32TS20/PA32TS32D-20
HYNIX	HY29F040	DIP 32	
HYNIX	HY29F040	PLCC 32	PA32PL32D
HYNIX	HY29F040	TSOP 32	PA32TS20/PA32TS32D-20
HYNIX	HY29F040A	DIP 32	
HYNIX	HY29F040A	PLCC 32	PA32PL32D
HYNIX	HY29F040A	TSOP 32	PA32TS20/PA32TS32D-20
HYNIX	HY29F080T	SOP 44	PA44SO44D
HYNIX	HY29F080T	TSOP 40	PA40TS40D
HYNIX	HY29F400BT	TSOP 48	PA48TS48D
HYNIX	HY29F400TT	TSOP 48	PA48TS48D
HYNIX	HY29F400BG	SOP 44	PA44SO44D
HYNIX	HY29F400TG	SOP 44	PA44SO44D
HYNIX	HY29F800BT	TSOP 48	PA48TS48D
HYNIX	HY29F800TT	TSOP 48	PA48TS48D
HYNIX	HY29F800BG	SOP 44	PA44SO44D
HYNIX	HY29F800TG	SOP 44	PA44SO44D
HYNIX	HY29LV400BT	SOP 44	PA44SO44D
HYNIX	HY29LV400BT	TSOP 48	PA48TS48D
HYNIX	HY29LV400TT	SOP 44	PA44SO44D
HYNIX	HY29LV400TT	TSOP 48	PA48TS48D

HYNIX	HY29LV800BT	SOP 44	PA44SO44D
HYNIX	HY29LV800BT	TSOP 48	PA48TS48D
HYNIX	HY29LV800TT	SOP 44	PA44SO44D
HYNIX	HY29LV800TT	TSOP 48	PA48TS48D
HYNIX	HY29LV160BT	TSOP 48	PA48TS48D
HYNIX	HY29LV160TT	TSOP 48	PA48TS48D
HYNIX	HY29DL162BT	TSOP 48	PA48TS48D
HYNIX	HY29DL162TT	TSOP 48	PA48TS48D
HYNIX	HY29DL163BT	TSOP 48	PA48TS48D
HYNIX	HY29DL163TT	TSOP 48	PA48TS48D
HYNIX	HY29DS162BT	TSOP 48	PA48TS48D
HYNIX	HY29DS162TT	TSOP 48	PA48TS48D
HYNIX	HY29DS163BT	TSOP 48	PA48TS48D
HYNIX	HY29DS163TT	TSOP 48	PA48TS48D
HYNIX	HY29LV320BT	TSOP 48	PA48TS48D
HYNIX	HY29LV320TT	TSOP 48	PA48TS48D
HYNIX	HY91U3204AD	BGA 72	PA72BGA48D-B11
HYNIX	HY91U3208AD	BGA 72	PA72BGA48D-B11
HYNIX	HY96U1604M	BGA 69	PA69BGA48DH
HYNIX	HY93C46	DIP 8	
ICT	27CX010	DIP 32	
ICT	93C46	DIP 8	
ICT	93C46	SOIC 8	PA16SO16D-EO-150
ICT	93C56	DIP 8	
ICT	93C56	SOIC 8	PA16SO16D-EO-150
ICT	93C66	DIP 8	
ICT	93C66	SOIC 8	PA16SO16D-EO-150
ICT	93C46A	DIP 8	
ICT	93C46A	SOIC 8	PA16SO16D-EO-150
ICT	93C56A	DIP 8	
ICT	93C56A	SOIC 8	PA16SO16D-EO-150
ICT	93C66A	DIP 8	
ICT	93C66A	SOIC 8	PA16SO16D-EO-150
ICT	93CX46	DIP 8	
ICT	93CX46	SOIC 8	PA16SO16D-EO-150
ICT	93CX56	DIP 8	
ICT	93CX56	SOIC 8	PA16SO16D-EO-150
ICT	93CX66	DIP 8	
ICT	93CX66	SOIC 8	PA16SO16D-EO-150
IMT	IM29F001B	DIP 32	
IMT	IM29F001B	PLCC 32	PA32PL32D
IMT	IM29F001B	TSOP 32	PA32TS20/PA32TS32D-20
IMT	IM29F001T	DIP 32	
IMT	IM29F001T	PLCC 32	PA32PL32D
IMT	IM29F001T	TSOP 32	PA32TS20/PA32TS32D-20
IMT	IM29F002B	DIP 32	
IMT	IM29F002B	PLCC 32	PA32PL32D
IMT	IM29F002B	TSOP 32	PA32TS20/PA32TS32D-20
IMT	IM29F002T	DIP 32	
IMT	IM29F002T	PLCC 32	PA32PL32D
IMT	IM29F002T	TSOP 32	PA32TS20/PA32TS32D-20
IMT	IM29F004B	DIP 32	
IMT	IM29F004B	PLCC 32	PA32PL32D
IMT	IM29F004B	TSOP 32	PA32TS20/PA32TS32D-20
IMT	IM29F004T	DIP 32	
IMT	IM29F004T	PLCC 32	PA32PL32D
IMT	IM29F004T	TSOP 32	PA32TS20/PA32TS32D-20
IMT	IM29LV004B	DIP 32	
IMT	IM29LV004B	PLCC 32	PA32PL32D
IMT	IM29LV004B	TSOP 32	PA32TS20/PA32TS32D-20
IMT	IM29LV004T	DIP 32	
IMT	IM29LV004T	PLCC 32	PA32PL32D
IMT	IM29LV004T	TSOP 32	PA32TS20/PA32TS32D-20
INTEL	I2716	DIP 24	
INTEL	ID2716	DIP 24	
INTEL	M2716	DIP 24	
INTEL		2716	DIP 24
INTEL		2732	DIP 24
INTEL	2732A	DIP 24	
INTEL		2764	DIP 28
INTEL	2764A	DIP 28	
INTEL		27128	DIP 28
INTEL	27128A	DIP 28	

INTEL	27128B		DIP 28	
INTEL		27256	DIP 28	
INTEL		27512	DIP 28	
INTEL	27512J		DIP 28	
INTEL		27010	DIP 32	
INTEL		27010	PLCC 32	PA32PL32D
INTEL		27010	TSOP 32	PA32TS20/PA32TS32D-20
INTEL	27C010		DIP 32	
INTEL	27C010		PLCC 32	PA32PL32D
INTEL	27C010		TSOP 32	PA32TS20/PA32TS32D-20
INTEL	27C010A		DIP 32	
INTEL	27C010A		PLCC 32	PA32PL32D
INTEL	27C010A		TSOP 32	PA32TS20/PA32TS32D-20
INTEL		27011	DIP 28	
INTEL	27C011		DIP 28	
INTEL	27C020		DIP 32	
INTEL	27C020		PLCC 32	PA32PL32D
INTEL	27C020		TSOP 32	PA32TS20/PA32TS32D-20
INTEL	27C040		DIP 32	
INTEL	27C040		PLCC 32	PA32PL32D
INTEL	27C100		DIP 32	
INTEL	27C128		DIP 28	
INTEL	27C128		PLCC 32	PA32PL28D-YA
INTEL	27C256		DIP 28	
INTEL	27C256		PLCC 32	PA32PL28D-YA
INTEL	27C400		DIP 40	
INTEL	27C512		DIP 28	
INTEL	27C512		PLCC 32	PA32PL28D-YA
INTEL	27C513		DIP 28	
INTEL	27C64		DIP 28	
INTEL	27C64		PLCC 32	PA32PL28D-YA
INTEL	87C64		DIP 28	
INTEL	P27128A		DIP 28	
INTEL	P27128B		DIP 28	
INTEL	P27256		DIP 28	
INTEL	P27512		DIP 28	
INTEL	P2764A		DIP 28	
INTEL	P27C128		DIP 28	
INTEL	P27C256		DIP 28	
INTEL	P27C256		PLCC 32	PA32PL28D-YA
INTEL	P27C64		DIP 28	
INTEL		27210	DIP 40	
INTEL		27210	PLCC 44	PA44-48U
INTEL	27C210		DIP 40	
INTEL	27C210		PLCC 44	PA44-48U
INTEL	27C220		DIP 40	
INTEL	27C220		PLCC 44	PA44-48U
INTEL	27C240		DIP 40	
INTEL	27C240		PLCC 44	PA44-48U
INTEL	2816A		DIP 24	
INTEL	2817A		DIP 28	
INTEL		2864	DIP 28	
INTEL	2864A		DIP 28	
INTEL	28F256-###P1C2		DIP 32	
INTEL	28F256-###P2C2		DIP 32	
INTEL	28F256A		DIP 32	
INTEL	28F512		DIP 32	
INTEL	P28F010		DIP 32	
INTEL	N28F010		PLCC 32	PA32PL32D
INTEL	P28F020		DIP 32	
INTEL	N28F020		PLCC 32	PA32PL32D
INTEL	P28F001BX-B		DIP 32	
INTEL	N28F001BX-B		PLCC 32	PA32PL32D
INTEL	P28F001BX-T		DIP 32	
INTEL	N28F001BX-T		PLCC 32	PA32PL32D
INTEL	N82802AB		PLCC 32	PA32PL32D
INTEL	E82802AB		TSOP 40	PA40TS40D
INTEL	N82802AC		PLCC 32	PA32PL32D
INTEL	E82802AC		TSOP 40	PA40TS40D
INTEL	DD28F032SA		TSOP 56	PA56TS48DK
INTEL	DT28F800F3-B		SSOP 56	CIC-56SS-48D-C6-TI
INTEL	DT28F800F3-T		SSOP 56	CIC-56SS-48D-C6-TI
INTEL	DT28F160F3-B		SSOP 56	CIC-56SS-48D-C6-TI

INTEL	DT28F160F3-T	SSOP 56	CIC-56SS-48D-C6-TI
INTEL	E28F002BC-T	TSOP 40	PA40TS40D
INTEL	E28F002BX/L-B	TSOP 40	PA40TS40D
INTEL	E28F002BX/L-T	TSOP 40	PA40TS40D
INTEL	E28F002BV/E-B	TSOP 40	PA40TS40D
INTEL	E28F002BV/E-T	TSOP 40	PA40TS40D
INTEL	E28F004B5-B	TSOP 40	PA40TS40D
INTEL	E28F004B5-T	TSOP 40	PA40TS40D
INTEL	E28F004BX/L-B	TSOP 40	PA40TS40D
INTEL	E28F004BX/L-T	TSOP 40	PA40TS40D
INTEL	E28F004BV-B	TSOP 40	PA40TS40D
INTEL	E28F004BV-T	TSOP 40	PA40TS40D
INTEL	E28F004BE-B	TSOP 40	PA40TS40D
INTEL	E28F004BE-T	TSOP 40	PA40TS40D
INTEL	E28F004S3	TSOP 40	PA40TS40D
INTEL	E28F004S5	TSOP 40	PA40TS40D
INTEL	E28F008BE-B	TSOP 40	PA40TS40D
INTEL	E28F008BE-T	TSOP 40	PA40TS40D
INTEL	E28F008BV-B	TSOP 40	PA40TS40D
INTEL	E28F008BV-T	TSOP 40	PA40TS40D
INTEL	E28F008S3	TSOP 40	PA40TS40D
INTEL	E28F008S5	TSOP 40	PA40TS40D
INTEL	E28F008SA	TSOP 40	PA40TS40D
INTEL	E28F016S3	TSOP 40	PA40TS40D
INTEL	E28F016S5	TSOP 40	PA40TS40D
INTEL	E28F400B3-B	TSOP 48	PA48TS48D
INTEL	E28F400B3-T	TSOP 48	PA48TS48D
INTEL	E28F400C3-B	TSOP 48	PA48TS48D
INTEL	E28F400C3-T	TSOP 48	PA48TS48D
INTEL	E28F800CV-B	TSOP 48	PA48TS48D
INTEL	E28F800CV-T	TSOP 48	PA48TS48D
INTEL	E28F800B5-B	TSOP 48	PA48TS48D
INTEL	E28F800B5-T	TSOP 48	PA48TS48D
INTEL	E28F004B3-B	TSOP 40	PA40TS40D
INTEL	E28F004B3-T	TSOP 40	PA40TS40D
INTEL	E28F008B3-B	TSOP 40	PA40TS40D
INTEL	E28F008B3-T	TSOP 40	PA40TS40D
INTEL	E28F016B3-B	TSOP 40	PA40TS40D
INTEL	E28F016B3-T	TSOP 40	PA40TS40D
INTEL	E28F800B3-B	TSOP 48	PA48TS48D
INTEL	E28F800B3-T	TSOP 48	PA48TS48D
INTEL	E28F160B3-B	TSOP 48	PA48TS48D
INTEL	E28F160B3-T	TSOP 48	PA48TS48D
INTEL	E28F320B3-B	TSOP 48	PA48TS48D
INTEL	E28F320B3-T	TSOP 48	PA48TS48D
INTEL	E28F800C2-BA	TSOP 48	PA48TS48D
INTEL	E28F800C2-TA	TSOP 48	PA48TS48D
INTEL	E28F160C2-BA	TSOP 48	PA48TS48D
INTEL	E28F160C2-TA	TSOP 48	PA48TS48D
INTEL	E28F008C3-B	TSOP 40	PA40TS40D
INTEL	E28F008C3-T	TSOP 40	PA40TS40D
INTEL	E28F016C3-B	TSOP 40	PA40TS40D
INTEL	E28F016C3-T	TSOP 40	PA40TS40D
INTEL	E28F800C3-B	TSOP 48	PA48TS48D
INTEL	E28F800C3-T	TSOP 48	PA48TS48D
INTEL	E28F160C3-B	TSOP 48	PA48TS48D
INTEL	E28F160C3-T	TSOP 48	PA48TS48D
INTEL	E28F320C3-B	TSOP 48	PA48TS48D
INTEL	E28F320C3-T	TSOP 48	PA48TS48D
INTEL	GE28F320W30-B	BGA 56	PA56BGA48D-TO
INTEL	GE28F320W30-T	BGA 56	PA56BGA48D-TO
INTEL	GE28F3204W30-B	BGA 56	PA56BGA48D-TO
INTEL	GE28F3204W30-T	BGA 56	PA56BGA48D-TO
INTEL	GE28F3208W30-B	BGA 56	PA56BGA48D-TO
INTEL	GE28F3208W30-T	BGA 56	PA56BGA48D-TO
INTEL	GE28F6408W30-B	BGA 56	PA56BGA48D-TO
INTEL	GE28F6408W30-T	BGA 56	PA56BGA48D-TO
INTEL	GE28F6408W18-B	BGA 56	PA56BGA48DE
INTEL	GE28F6408W18-T	BGA 56	PA56BGA48DE
INTEL	GT28F004B3-B	BGA 48	CIC-48uBGA-40D-B6-TI
INTEL	GT28F004B3-T	BGA 48	CIC-48uBGA-40D-B6-TI
INTEL	GT28F008B3-B	BGA 48	CIC-48uBGA-40D-B6-TI
INTEL	GT28F008B3-T	BGA 48	CIC-48uBGA-40D-B6-TI

INTEL	GT28F016B3-B	BGA 48	CIC-48uBGA-40D-B6-TI
INTEL	GT28F016B3-T	BGA 48	CIC-48uBGA-40D-B6-TI
INTEL	GT28F400B3-B	BGA 48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F400B3-T	BGA 48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F800B3-B	BGA 48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F800B3-T	BGA 48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F160B3-B	BGA 48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F160B3-T	BGA 48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F320B3-B	BGA 48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F320B3-T	BGA 48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F800C2-BA	BGA 48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F800C2-TA	BGA 48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F160C2-BA	BGA 48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F160C2-TA	BGA 48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F008C3-B	BGA 48	CIC-48uBGA-40D-B6-TI
INTEL	GT28F008C3-T	BGA 48	CIC-48uBGA-40D-B6-TI
INTEL	GT28F016C3-B	BGA 48	CIC-48uBGA-40D-B6-TI
INTEL	GT28F016C3-T	BGA 48	CIC-48uBGA-40D-B6-TI
INTEL	GT28F400C3-B	BGA 48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F400C3-T	BGA 48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F800C3-B	BGA 48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F800C3-T	BGA 48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F160C3-B	BGA 48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F160C3-T	BGA 48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F320C3-B	BGA 48	CIC-48uBGA-48D-A6-TI
INTEL	GT28F320C3-T	BGA 48	CIC-48uBGA-48D-A6-TI
INTEL	GT28F800F3-B	BGA 56	CIC-56uBGA-48D-B6-TI
INTEL	GT28F800F3-T	BGA 56	CIC-56uBGA-48D-B6-TI
INTEL	GT28F160F3-B	BGA 56	CIC-56uBGA-48D-B6-TI
INTEL	GT28F160F3-T	BGA 56	CIC-56uBGA-48D-B6-TI
INTEL	RD28F1602C3-B	BGA 72	PA72BGA48D-B
INTEL	RD28F1602C3-T	BGA 72	PA72BGA48D-B
INTEL	RD28F1604C3-B	BGA 72	PA72BGA48D-B
INTEL	RD28F1604C3-T	BGA 72	PA72BGA48D-B
INTEL	RD28F3202C3-B	BGA 72	PA72BGA48D-B
INTEL	RD28F3202C3-T	BGA 72	PA72BGA48D-B
INTEL	RD28F3204C3-B	BGA 72	PA72BGA48D-B
INTEL	RD28F3204C3-T	BGA 72	PA72BGA48D-B
INTEL	RD28F320W30-B	BGA 80	PA80BGA48D
INTEL	RD28F320W30-T	BGA 80	PA80BGA48D
INTEL	RD28F3208W30-B	BGA 80	PA80BGA48D
INTEL	RD28F3208W30-T	BGA 80	PA80BGA48D
INTEL	RD28F640W30-B	BGA 80	PA80BGA48D
INTEL	RD28F640W30-T	BGA 80	PA80BGA48D
INTEL	RD28F6408W30-B	BGA 80	PA80BGA48D
INTEL	RD28F6408W30-T	BGA 80	PA80BGA48D
INTEL	RD38F1010C0ZBL0	BGA 66	PA66BGA48DB
INTEL	RD38F1010C0ZTL0	BGA 66	PA66BGA48DB
INTEL	RD38F1020C0ZBL0	BGA 66	PA66BGA48DB
INTEL	RD38F1020C0ZTL0	BGA 66	PA66BGA48DB
INTEL	RD38F1030W0ZBQ0	BGA 88	PA88BGA48DA-YO-8X10
INTEL	RD38F2030W0ZBQ1	BGA 88	PA88BGA48DA-YO-8X10
INTEL	RD38F2040W0YBQ0	BGA 88	HA88BGA48DA7
INTEL	RD38F2040W0ZBQ0	BGA 88	PA88BGA48DA-YO-8X10
INTEL	RD38F2230WWZBQ0	BGA 88	PA88BGA48DA-YO-8X10
INTEL	RD38F2240WWZBQ0	BGA 88	PA88BGA48DA-YO-8X10
INTEL	RD38F2240WWZDQ0	BGA 88	PA88BGA48DA-YO-8X10
INTEL	RD38F3350WWZDQ1	BGA 88	PA88BGA48DA-YO-8X10
INTEL	RD38F3350LLZDQ0	BGA 88	PA88BGA48DA-YO-8X10
INTEL	RD38F3040L0ZBQ0	BGA 88	PA88BGA48DA-YO-8X10
INTEL	RD38F3040L0ZTQ0	BGA 88	PA88BGA48DA-YO-8X10
INTEL	PA28F200BX/L-B	SOP 44	PA44SO44D
INTEL	PA28F200BX/L-T	SOP 44	PA44SO44D
INTEL	PA28F200BV/E-B	SOP 44	PA44SO44D
INTEL	PA28F200BV/E-T	SOP 44	PA44SO44D
INTEL	PA28F200B5-B	SOP 44	PA44SO44D
INTEL	PA28F200B5-T	SOP 44	PA44SO44D
INTEL	PA28F400BX/L-B	SOP 44	PA44SO44D
INTEL	PA28F400BX/L-T	SOP 44	PA44SO44D
INTEL	PA28F400BV/E-B	SOP 44	PA44SO44D
INTEL	PA28F400BV/E-T	SOP 44	PA44SO44D
INTEL	PA28F400B5-B	SOP 44	PA44SO44D
INTEL	PA28F400B5-T	SOP 44	PA44SO44D

INTEL	AB28F200BRB	SOP 44	PA44SO44D
INTEL	AB28F200BRT	SOP 44	PA44SO44D
INTEL	AB28F200BXB	SOP 44	PA44SO44D
INTEL	AB28F200BXT	SOP 44	PA44SO44D
INTEL	AB28F200B5B	SOP 44	PA44SO44D
INTEL	AB28F200B5T	SOP 44	PA44SO44D
INTEL	AB28F400BRB	SOP 44	PA44SO44D
INTEL	AB28F400BRT	SOP 44	PA44SO44D
INTEL	PA28F004S3	SOP 44	PA44SO44D
INTEL	PA28F004S5	SOP 44	PA44SO44D
INTEL	PA28F008S3	SOP 44	PA44SO44D
INTEL	PA28F008S5	SOP 44	PA44SO44D
INTEL	PA28F008SA	SOP 44	PA44SO44D
INTEL	PA28F008SA-L	SOP 44	PA44SO44D
INTEL	RC28F640P30B	EBGA 64	PA64BGA48DI
INTEL	RC28F640P30T	EBGA 64	PA64BGA48DI
INTEL	RC28F128P30T	EBGA 64	PA64BGA48DI
INTEL	RC28F256P30B	EBGA 64	PA64BGA48DI
INTEL	RC28F256P30T	EBGA 64	PA64BGA48DI
INTEL	TE28F640C3-B	TSOP 48	PA48TS48D
INTEL	TE28F640C3-T	TSOP 48	PA48TS48D
INTEL	TE28F640P30B	TSOP 56	HA56TS48DJ
INTEL	TE28F640P30T	TSOP 56	HA56TS48DJ
INTEL	TE28F128P30B	TSOP 56	HA56TS48DJ
INTEL	TE28F128P30T	TSOP 56	HA56TS48DJ
INTEL	TE28F256P30B	TSOP 56	HA56TS48DJ
INTEL	TE28F256P30T	TSOP 56	HA56TS48DJ
INTEL	JS28F640P30B	TSOP 56	HA56TS48DJ
INTEL	JS28F640P30T	TSOP 56	HA56TS48DJ
INTEL	JS28F128P30B	TSOP 56	HA56TS48DJ
INTEL	JS28F128P30T	TSOP 56	HA56TS48DJ
INTEL	JS28F256P30B	TSOP 56	HA56TS48DJ
INTEL	JS28F256P30T	TSOP 56	HA56TS48DJ
INTEL	TE28F640P33B	TSOP 56	HA56TS48DF
INTEL	TE28F640P33T	TSOP 56	HA56TS48DF
INTEL	TE28F128P33B	TSOP 56	HA56TS48DF
INTEL	TE28F128P33T	TSOP 56	HA56TS48DF
INTEL	TE28F256P33B	TSOP 56	HA56TS48DF
INTEL	TE28F256P33T	TSOP 56	HA56TS48DF
INTEL	JS28F640P33B	TSOP 56	HA56TS48DF
INTEL	JS28F640P33T	TSOP 56	HA56TS48DF
INTEL	JS28F128P33B	TSOP 56	HA56TS48DF
INTEL	JS28F128P33T	TSOP 56	HA56TS48DF
INTEL	JS28F256P33B	TSOP 56	HA56TS48DF
INTEL	JS28F256P33T	TSOP 56	HA56TS48DF
INTEL	JS28F256P3G	TSOP 56	PA56TS48DC
INTEL	QH25F160S33B	SOIC 16	PA28SO28D-EO-300
INTEL	QH25F160S33T	SOIC 16	PA28SO28D-EO-300
INTEL	QH25F320S33B	SOIC 16	PA28SO28D-EO-300
INTEL	QH25F320S33T	SOIC 16	PA28SO28D-EO-300
INTEL	QH25F640S33B	SOIC 16	PA28SO28D-EO-300
INTEL	QH25F640S33T	SOIC 16	PA28SO28D-EO-300
INTEL	QB25F016S33T	SOIC 8	PA20SO20D-EO-210
INTEL	QB25F016S33B	SOIC 8	PA20SO20D-EO-210
INTEL	QB25F160S33B	SOIC 16	PA28SO28D-EO-300
INTEL	QB25F160S33T	SOIC 16	PA28SO28D-EO-300
INTEL	QB25F320S33B	SOIC 16	PA28SO28D-EO-300
INTEL	QB25F320S33T	SOIC 16	PA28SO28D-EO-300
INTEL	QB25F640S33B	SOIC 16	PA28SO28D-EO-300
INTEL	QB25F640S33T	SOIC 16	PA28SO28D-EO-300
ISSI	IS24C64A	TSSOP 8	PA8TSS8D
ISSI	IS24C64A	TSSOP 8	PA24TSS24D
ISSI	IS27C256	DIP 28	
ISSI	IS27C256	PLCC 32	PA32PL28D-YA
ISSI	IS27C512	DIP 28	
ISSI	IS27C512	PLCC 32	PA32PL28D-YA
ISSI	IS27C512	TSOP 28	PA28TS28D-EO
ISSI	IS27C010	DIP 32	
ISSI	IS27C010	PLCC 32	PA32PL32D
ISSI	IS27C010	TSOP 32	PA32TS20/PA32TS32D-20
ISSI	IS27C020	DIP 32	
ISSI	IS27C020	PLCC 32	PA32PL32D
ISSI	IS27C020	TSOP 32	PA32TS20/PA32TS32D-20

ISSI	IS27DV256	DIP 28	
ISSI	IS27DV256	PLCC 32	PA32PL28D-YA
ISSI	IS27DV256	TSOP 28	PA28TS28D-EO
ISSI	IS27HC256	DIP 28	
ISSI	IS27HC256	PLCC 32	PA32PL28D-YA
ISSI	IS27HC256	TSOP 28	PA28TS28D-EO
ISSI	IS27HC512	DIP 28	
ISSI	IS27HC512	PLCC 32	PA32PL28D-YA
ISSI	IS27HC512	TSOP 28	PA28TS28D-EO
ISSI	IS27HC010	DIP 32	
ISSI	IS27HC010	PLCC 32	PA32PL32D
ISSI	IS27HC010	TSOP 32	PA32TS20/PA32TS32D-20
ISSI	IS27HC020	DIP 32	
ISSI	IS27HC020	PLCC 32	PA32PL32D
ISSI	IS27HC020	TSOP 32	PA32TS20/PA32TS32D-20
ISSI	IS27LV256	DIP 28	
ISSI	IS27LV256	PLCC 32	PA32PL28D-YA
ISSI	IS27LV256	TSOP 28	PA28TS28D-EO
ISSI	IS27LV512	DIP 28	
ISSI	IS27LV512	PLCC 32	PA32PL28D-YA
ISSI	IS27LV512	TSOP 28	PA28TS28D-EO
ISSI	IS27LV010	DIP 32	
ISSI	IS27LV010	PLCC 32	PA32PL32D
ISSI	IS27LV010	TSOP 32	PA32TS20/PA32TS32D-20
ISSI	IS27LV020	DIP 32	
ISSI	IS27LV020	PLCC 32	PA32PL32D
ISSI	IS27LV020	TSOP 32	PA32TS20/PA32TS32D-20
ISSI	IS28F010	DIP 32	
ISSI	IS28F010	PLCC 32	PA32PL32D
ISSI	IS28F010	TSOP 32	PA32TS20/PA32TS32D-20
ISSI	IS28F020	DIP 32	
ISSI	IS28F020	PLCC 32	PA32PL32D
ISSI	IS28F020	TSOP 32	PA32TS20/PA32TS32D-20
ISSI	IS93C46	DIP 8	
ISSI	IS93C56	DIP 8	
ISSI	IS93C66	DIP 8	
ISSI	IS93C46-3P	DIP 8	
ISSI	IS93C46-3G	SOIC 8	PA8SO8D-EO-150
ISSI	IS93C46-3GR	SOIC 8	PA16SO16D-EO-150
ISSI	IS93C56-3P	DIP 8	
ISSI	IS93C56-3G	SOIC 8	PA8SO8D-EO-150
ISSI	IS93C56-3GR	SOIC 8	PA16SO16D-EO-150
ISSI	IS93C66-3P	DIP 8	
ISSI	IS93C66-3G	SOIC 8	PA8SO8D-EO-150
ISSI	IS93C66-3GR	SOIC 8	PA16SO16D-EO-150
ISSI	IS93C46A-3P	DIP 8	
ISSI	IS93C46A-3G	SOIC 8	PA8SO8D-EO-150
ISSI	IS93C46A-3GR	SOIC 8	PA16SO16D-EO-150
ISSI	IS93C56A-3P	DIP 8	
ISSI	IS93C56A-3G	SOIC 8	PA8SO8D-EO-150
ISSI	IS93C56A-3GR	SOIC 8	PA16SO16D-EO-150
ISSI	IS93C66A-3P	DIP 8	
ISSI	IS93C66A-3G	SOIC 8	PA8SO8D-EO-150
ISSI	IS93C66A-3GR	SOIC 8	PA16SO16D-EO-150
ISSI	IS93C76A-3P	DIP 8	
ISSI	IS93C76A-3G	SOIC 8	PA8SO8D-EO-150
ISSI	IS93C76A-3GR	SOIC 8	PA16SO16D-EO-150
ISSI	IS93C86A-3P	DIP 8	
ISSI	IS93C86A-3G	SOIC 8	PA8SO8D-EO-150
ISSI	IS93C86A-3GR	SOIC 8	PA16SO16D-EO-150
ISSI	IS93C46D-2P	DIP 8	
ISSI	IS93C46D-2G	SOIC 8	PA8SO8D-EO-150
ISSI	IS93C46D-2GR	SOIC 8	PA16SO16D-EO-150
ISSI	IS93C46D-3P	DIP 8	
ISSI	IS93C46D-3GR	SOIC 8	PA16SO16D-EO-150
LINVEX TECHNOLOGY	LX59CF2010	TSOP 32	PA32TS20/PA32TS32D-20
LINVEX TECHNOLOGY	LX59CF2128	TSOP 32	PA32TS20/PA32TS32D-20
LINVEX TECHNOLOGY	LX59CF4010	TSOP 40	PA40TS40D
LINVEX TECHNOLOGY	LX59CF4128	TSOP 32	PA32TS20/PA32TS32D-20
LINVEX TECHNOLOGY	LX59CF432	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX23C1000PC	DIP 28	
MACRONIX	MX23C1010PC	DIP 32	
MACRONIX	MX23C1010MC	SOP 32	PA44SO44D

MACRONIX	MX23C1010QC	PLCC 32	PA32PL32D
MACRONIX	MX23C2000PC	DIP 32	
MACRONIX	MX23C2000MC	SOP 32	PA44SO44D
MACRONIX	MX23C2000QC	PLCC 32	PA32PL32D
MACRONIX	MX23C4000PC	DIP 32	
MACRONIX	MX23C4000MC	SOP 32	PA44SO44D
MACRONIX	MX23C4000QC	PLCC 32	PA32PL32D
MACRONIX	MX23C8000PC	DIP 32	
MACRONIX	MX23C8000MC	SOP 32	PA44SO44D
MACRONIX	MX23C8000QC	PLCC 32	PA32PL32D
MACRONIX	MX25L802MC	SOP 28	PA28SO28DA-EC-330
MACRONIX	MX25L1602MC	SOP 28	PA28SO28DA-EC-330
MACRONIX	MX25L3202MC	SOP 32	PA32SO32D-1
MACRONIX	MX25L6402MC	SOP 32	PA32SO32D-1
MACRONIX	MX25L6402AMC	SOP 28	PA28SO28DA-EC-330
MACRONIX	MX25L512MC	SOP 8	PA16SO16D-EO-150
MACRONIX	MX25L512ZMC	CASON 8	PA8SON8D
MACRONIX	MX25L512CM	SOP 8	PA16SO16D-EO-150
MACRONIX	MX25L5121EMI	SOIC 8	PA16SO16D-EO-150
MACRONIX	MX25U5121EM	SOIC 8	HA8SO48DAD
MACRONIX	MX25U5121EZU	USON 8	HBP8USON48DC
MACRONIX	MX25U1001EM	SOIC 8	HA8SO48DAD
MACRONIX	MX25U1001EZU	USON 8	HBP8USON48DC
MACRONIX	MX25L1005MC	SOP 8	PA16SO16D-EO-150
MACRONIX	MX25L1005CM	SOP 8	PA16SO16D-EO-150
MACRONIX	MX25L1025CM	SOP 8	PA16SO16D-EO-150
MACRONIX	MX25L1026EM1	SOP 8	PA8SO8D-EO-150
MACRONIX	MX25L1021EMI	SOIC 8	PA16SO16D-EO-150
MACRONIX	MX25L1005ZMC	CASON 8	PA8SON8D
MACRONIX	MX25L1005AMC	SOP 8	PA16SO16D-EO-150
MACRONIX	MX25L2005MC	SOP 8	PA16SO16D-EO-150
MACRONIX	MX25L2005ZMC	CASON 8	PA8SON8D
MACRONIX	MX25L2005CMI	SOIC 8	PA16SO16D-EO-150
MACRONIX	MX25L2006E	SOP 8	PA8SO8D-EO-150
MACRONIX	MX25L2025MC	SOP 8	PA16SO16D-EO-150
MACRONIX	MX25L2025ZMC	CASON 8	PA8SON8D
MACRONIX	MX25L4005MC	SOP 8	PA16SO16D-EO-150
MACRONIX	MX25L4006E	SOP 8	PA8SO8D-EO-150
MACRONIX	MX25L4006E	SOP 8	PA8SO8D-210
MACRONIX	MX25L4006EM1	SOP 8	PA16SO16D-EO-150
MACRONIX	MX25L4006EM2	SOP 8	PA20SO20D-EO-210
MACRONIX	MX25L4006EZN	WSON 8	PA8SON8D
MACRONIX	MX25L4006EP	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX25L2025CM	SOP 8	PA16SO16D-EO-150
MACRONIX	MX25L4005CP	DIP 8	
MACRONIX	MX25L4005CM	SOP 8	PA16SO16D-EO-150
MACRONIX	MX25L4005CM2	SOP 8	PA20SO20D-EO-210
MACRONIX	MX25L4005CZN	CASON 8	PA8SON8D
MACRONIX	MX25L4025CM	SOP 8	PA16SO16D-EO-150
MACRONIX	MX25L4005M2C	SOP 8	PA20SO20D-EO-210
MACRONIX	MX25L4005ZMC	CASON 8	PA8SON8D
MACRONIX	MX25L4005APC	DIP 8	
MACRONIX	MX25L4005AMC	SOP 8	PA16SO16D-EO-150
MACRONIX	MX25L4005AZMC	CASON 8	PA8SON8D
MACRONIX	MX25L4025MC	SOP 8	PA16SO16D-EO-150
MACRONIX	MX25L4025ZMC	CASON 8	PA8SON8D
MACRONIX	MX25L8005PC	DIP 8	
MACRONIX	MX25L8005MC	SOP 8	PA16SO16D-EO-150
MACRONIX	MX25L8005M2C	SOP 8	PA20SO20D-EO-210
MACRONIX	MX25L8005ZMC	CASON 8	PA8SON8D
MACRONIX	MX25L8005ZU	USON 8	PA8USON8D
MACRONIX	MX25L8025MC	SOP 8	PA16SO16D-EO-150
MACRONIX	MX25L8025ZMC	CASON 8	PA8SON8D
MACRONIX	MX25L1605MC	SOP 8	PA16SO16D-EO-150
MACRONIX	MX25L1605MC	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX25L1605A	SOP 8	PA16SO16D-EO-150
MACRONIX	MX25L1605A	SOP 8	PA20SO20D-EO-210
MACRONIX	MX25L1605A	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX25L1605D	DIP 8	
MACRONIX	MX25L1605D	SOP 8	PA16SO16D-EO-150
MACRONIX	MX25L1605D	SOP 8	PA20SO20D-EO-210
MACRONIX	MX25L1605D	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX25L1605D	CASON 8	PA8SON8D



MACRONIX	MX25L1606EM2I	SOIC 8	PA20SO20D-EO-210
MACRONIX	MX25L1606EM1I	SOP 8	PA16SO16D-EO-150
MACRONIX	MX25L1673EZN	WSON 8	PA8SON8D
MACRONIX	MX25L3291FM2	SOP 8	PA20SO20D-EO-210
MACRONIX	MX25L1635D	SOIC 8	PA20SO20D-EO-210
MACRONIX	MX25L1635D	CASON 8	PA8SON8D
MACRONIX	MX25L3205MC	SOP 8	PA16SO16D-EO-150
MACRONIX	MX25L3205MC	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX25L3205AZMC	CASON 8	PA8SON8DA
MACRONIX	MX25L3205D	SOP 8	PA16SO16D-EO-150
MACRONIX	MX25L3205D	SOP 8	PA20SO20D-EO-210
MACRONIX	MX25L3205D	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX25L3205D	CASON 8	PA8SON8D
MACRONIX	MX25L3206EPI	DIP 8	
MACRONIX	MX25L3206EM2I	SOIC 8	PA20SO20D-EO-210
MACRONIX	MX25L3235D	SOIC 8	PA20SO20D-EO-210
MACRONIX	MX25L3235D	CASON 8	PA8SON8D
MACRONIX	MX25L3235D	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX25L3237D	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX25L3237D	CASON 8	PA8SON8D
MACRONIX	MX25L3255DXCI	BGA 24	HA24BG48D(A)
MACRONIX	MX25L3255DXCI	BGA 24	HA24BG48D
MACRONIX	MX25L6405D	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX25L6405D	WSON 8	PA8SON8DA
MACRONIX	MX25L6406EMI	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX25L6406EM2I	SOIC 8	PA20SO20D-EO-210
MACRONIX	MX25L6445D	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX25L12805D	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX25L6405MC	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX25L12845EM	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX25L12845EZN	USON 8	PA8SON8DA
MACRONIX	MX25L12835FMI	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX25L12835FM2I	SOP 8	PA20SO20D-EO-210
MACRONIX	MX25L12835FZNI	WSON 8	PA8SON8D
MACRONIX	MX25L12835FZ2I	WSON 8	PA8SON8DA
MACRONIX	MX25L12873FP	DIP 8	
MACRONIX	MX25L12873FM	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX25L12873FM2	SOP 8	PA20SO20D-EO-210
MACRONIX	MX25L12873FZN	WSON 8	PA8SON8D
MACRONIX	MX25L25635EMI(Serial)	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX25L25835EMI	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX25L25635EMI(Parallel)	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX25L25635FZ2I	USON 8	PA8SON8DA
MACRONIX	MX25L25735EMI	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX25L51245GZ2	WSON 8	PA8SON8DA
MACRONIX	MX25L51245GM	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX25L51245GXD	BGA 24	NA24BG48DA
MACRONIX	MX66L1G45GM	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX66L1G45GXD	BGA 24	NA24BG48DA
MACRONIX	MX25L6436EM2I	SOP 8	PA20SO20D-EO-210
MACRONIX	MX25L6445EZN	USON 8	PA8SON8DA
MACRONIX	MX25L6445EM2	SOP 8	PA20SO20D-EO-210
MACRONIX	MX25L6445EMI	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX25L12805NMC(Old)	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX25L12805NMC	SOIC 16	PA28SO28D-EO-300
MACRONIX	MX25V512EM	SOIC 8	PA16SO16D-EO-150
MACRONIX	MX25V512EZU	USON 8	HBP8USON48DB
MACRONIX	MX25V512EO	TSSOP 8	PA8TSS8D
MACRONIX	MX25V1006EM	SOIC 8	PA16SO16D-EO-150
MACRONIX	MX25V1006EZU	USON 8	HBP8USON48DB
MACRONIX	MX25V1006EO	TSSOP 8	PA8TSS8D
MACRONIX	MX25V2006EM1	SOIC 8	PA16SO16D-EO-150
MACRONIX	MX25V2006EMD	SOIC 8	PA16SO16D-EO-150
MACRONIX	MX25V2006EZN	WSON 8	PA8SON8D
MACRONIX	MX25V2006EZU	USON 8	HBP8USON48DB
MACRONIX	MX25V4005	SOIC 8	PA16SO16D-EO-150
MACRONIX	MX25V4005	CASON 8	PA8SON8D
MACRONIX	MX25V4035-ZN	CASON 8	PA8SON8D
MACRONIX	MX25V8005	SOIC 8	PA16SO16D-EO-150
MACRONIX	MX25V8005	CASON 8	PA8SON8D
MACRONIX	MX25L8006EM1I	SOIC 8	PA16SO16D-EO-150
MACRONIX	MX25L8006EM2I	SOIC 8	PA20SO20D-EO-210
MACRONIX	MX25L8006EZNI	WSON 8	PA8SON8D

MACRONIX	MX25V8035-M	SOIC 8	PA16SO16D-EO-150
MACRONIX	MX25V8035-ZN	CASON 8	PA8SON8D
MACRONIX	MX25U2032EMD	SOIC 8	HA8SO48DAD
MACRONIX	MX25U2032EM	SOIC 8	HA8SO48DAD
MACRONIX	MX25U2032EZN	WSON 8	HA8SON48DG
MACRONIX	MX25U2033EM1	SOIC 8	HA8SO48DAD
MACRONIX	MX25U2033EZN	WSON 8	HA8SON48DG
MACRONIX	MX25U4032EMD	SOIC 8	HA8SO48DAD
MACRONIX	MX25U4032EM1	SOIC 8	HA8SO48DAD
MACRONIX	MX25U4032EZN	WSON 8	HA8SON48DG
MACRONIX	MX25U4033EM1	SOIC 8	HA8SO48DAD
MACRONIX	MX25U4033EZN	WSON 8	HA8SON48DG
MACRONIX	MX25U8032EM1	SOIC 8	HA8SO48DAD
MACRONIX	MX25U8032EMD	SOIC 8	HA8SO48DAD
MACRONIX	MX25U8032EZN	WSON 8	HA8SON48DG
MACRONIX	MX25U8035EM1I	SOIC 8	PA16SO16D-EO-150
MACRONIX	MX25U8035EM2I	SOIC 8	PA20SO20D-EO-210
MACRONIX	MX25U8035EZN1	WSON 8	PA8SON8D
MACRONIX	MX25U8035EM1	SOIC 8	HA8SO48DAD
MACRONIX	MX25U8035EM2	SOIC 8	HA8SO48DAC
MACRONIX	MX25U8035EZN	WSON 8	HA8SON48DG
MACRONIX	MX25U1635EM1I	SOIC 8	PA16SO16D-EO-150
MACRONIX	MX25U1635EM1	SOIC 8	HA8SO48DAD
MACRONIX	MX25U1635EM2	SOIC 8	HA8SO48DAC
MACRONIX	MX25U1635EZN	WSON 8	HA8SON48DG
MACRONIX	MX25U3235FM2	SOIC 8	HA8SO48DAC
MACRONIX	MX25U6435FM2	SOIC 8	HA8SO48DAC
MACRONIX	MX25U6435FZN	WSON 8	HA8SON48DG
MACRONIX	MX25U12835FZN	WSON 8	HA8SON48DG
MACRONIX	MX25R1035FM1	SOIC 8	PA16SO16D-EO-150
MACRONIX	MX25R1035FM2	SOIC 8	PA20SO20D-EO-210
MACRONIX	MX25R1035FZU	USON 8	HBP8USON48DB
MACRONIX	MX25R2035FM1	SOIC 8	PA16SO16D-EO-150
MACRONIX	MX25R2035FZU	USON 8	HBP8USON48DB
MACRONIX	MX25R2035FO	TSSOP 8	PA8TSS8D
MACRONIX	MX25R4035FM1	SOIC 8	PA16SO16D-EO-150
MACRONIX	MX25R4035FM2	SOIC 8	PA20SO20D-EO-210
MACRONIX	MX25R4035FZU	USON 8	HBP8USON48DB
MACRONIX	MX25R8035FM1	SOIC 8	PA16SO16D-EO-150
MACRONIX	MX25R8035FM2	SOIC 8	PA20SO20D-EO-210
MACRONIX	MX25R8035FZN	WSON 8	PA8SON8D
MACRONIX	MX25R8035FZU	USON 8	HBP8USON48DB
MACRONIX	MX25R1635FM1	SOIC 8	PA16SO16D-EO-150
MACRONIX	MX25R1635FM2	SOIC 8	PA20SO20D-EO-210
MACRONIX	MX25R1635FZN	WSON 8	PA8SON8D
MACRONIX	MX25R1635FZU	USON 8	HBP8USON48DB
MACRONIX	MX25R3235FM1	SOIC 8	PA16SO16D-EO-150
MACRONIX	MX25R3235FM2	SOIC 8	PA20SO20D-EO-210
MACRONIX	MX25R3235FZN	WSON 8	PA8SON8D
MACRONIX	MX25R3235FZB	USON 8	HBP8USON48D
MACRONIX	MX25R6435FM2	SOIC 8	PA16SO16D-EO-150
MACRONIX	MX25R6435FZN	WSON 8	PA8SON8D
MACRONIX	MX25R6435FZA	USON 8	HA8MLF48D
MACRONIX	MX26C512A	DIP 28	
MACRONIX	MX26C1000A	DIP 32	
MACRONIX	MX26C1000A	PLCC 32	PA32PL32D
MACRONIX	MX26C1000B	DIP 32	
MACRONIX	MX26C1000B	PLCC 32	PA32PL32D
MACRONIX	MX26C2000B	DIP 32	
MACRONIX	MX26C2000B	PLCC 32	PA32PL32D
MACRONIX	MX26L3220	TSOP 48	PA48TS48D
MACRONIX	MX26L6420MC	SOP 44	PA44SO44D
MACRONIX	MX26L6420TC	TSOP 48	PA48TS48D
MACRONIX	MX26LV004BQC	PLCC 32	PA32PL32D
MACRONIX	MX26LV004TQC	PLCC 32	PA32PL32D
MACRONIX	MX26LV004BTC	TSOP 40	PA40TS40D
MACRONIX	MX26LV004TTC	TSOP 40	PA40TS40D
MACRONIX	MX26LV008BTC	TSOP 40	PA40TS40D
MACRONIX	MX26LV008TTC	TSOP 40	PA40TS40D
MACRONIX	MX26LV400BTC	TSOP 48	PA48TS48D1
MACRONIX	MX26LV400TTC	TSOP 48	PA48TS48D1
MACRONIX	MX26LV800BTC	TSOP 48	PA48TS48D1
MACRONIX	MX26LV800TTC	TSOP 48	PA48TS48D1

MACRONIX	MX26LV160BTC	TSOP 48	PA48TS48D1
MACRONIX	MX26LV160TTC	TSOP 48	PA48TS48D1
MACRONIX	MX26LV160ABTC	TSOP 48	PA48TS48D1
MACRONIX	MX26LV160ATTC	TSOP 48	PA48TS48D1
MACRONIX	MX27C64	DIP 28	
MACRONIX	MX27C256	DIP 28	
MACRONIX	MX27C256	PLCC 32	PA32PL28D-YA
MACRONIX	MX27C256	TSOP 28	PA28TS28D-EO
MACRONIX	MX27C512	DIP 28	
MACRONIX	MX27C512	PLCC 32	PA32PL28D-YA
MACRONIX	MX27C512	TSOP 28	PA28TS28D-EO
MACRONIX	MX27C516	PLCC 44	PA44-48U
MACRONIX	MX27C516	DIP 40	
MACRONIX	MX27C516	TSOP 40	PA40TS40D
MACRONIX	MX27C1000	DIP 32	
MACRONIX	MX27C1000	PLCC 32	PA32PL32D
MACRONIX	MX27C1000	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX27C1000	SOP 32	PA32SO32D-EO-450
MACRONIX	MX27C1000A	DIP 32	
MACRONIX	MX27C1000A	PLCC 32	PA32PL32D
MACRONIX	MX27C1000A	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX27C1000A	SOP 32	PA32SO32D-EO-450
MACRONIX	MX27C1001	DIP 32	
MACRONIX	MX27C1001	SOP 32	PA32SO32D-EO-450
MACRONIX	MX27C2000	DIP 32	
MACRONIX	MX27C2000	PLCC 32	PA32PL32D
MACRONIX	MX27C2000	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX27C2000	SOP 32	PA32SO32D-EO-450
MACRONIX	MX27C2000A	PLCC 32	PA32PL32D
MACRONIX	MX27C2000A	DIP 32	
MACRONIX	MX27C2000A	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX27C2000A	SOP 32	PA32SO32D-EO-450
MACRONIX	MX27C4000	DIP 32	
MACRONIX	MX27C4000	PLCC 32	PA32PL32D
MACRONIX	MX27C4000	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX27C4000	SOIC 32	PA32SO32D-EO-450
MACRONIX	MX27C4000A	DIP 32	
MACRONIX	MX27C4000A	PLCC 32	PA32PL32D
MACRONIX	MX27C4000A	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX27C4000A	SOIC 32	PA32SO32D-EO-450
MACRONIX	MX27C8000	DIP 32	
MACRONIX	MX27C8000	PLCC 32	PA32PL32D
MACRONIX	MX27C8000	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX27C8000	SOP 32	PA32SO32D-EO-450
MACRONIX	MX27C8000A	DIP 32	
MACRONIX	MX27C8000A	PLCC 32	PA32PL32D
MACRONIX	MX27C8000A	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX27C8000A	SOP 32	PA32SO32D-EO-450
MACRONIX	MX27C1024	DIP 40	
MACRONIX	MX27C1024	PLCC 44	PA44-48U
MACRONIX	MX27C1024	TSOP 40	PA40TS40D
MACRONIX	MX27C1024	SOP 40	PA40SO40D-EO-450
MACRONIX	MX27C2048	DIP 40	
MACRONIX	MX27C2048	PLCC 44	PA44-48U
MACRONIX	MX27C2048	TSOP 40	PA40TS40D
MACRONIX	MX27C4096	DIP 40	
MACRONIX	MX27C4096	PLCC 44	PA44-48U
MACRONIX	MX27C1100	DIP 40	
MACRONIX	MX27C2100	DIP 40	
MACRONIX	MX27C4100	DIP 40	
MACRONIX	MX27C4100	SOP 40	PA40SO40D-EO-450
MACRONIX	MX27C4111	SOP 40	PA40SO40D-EO-450
MACRONIX	MX27C4111	DIP 40	
MACRONIX	MX27C8100	DIP 42	
MACRONIX	MX27C8100	SOP 44	PA44SO44D
MACRONIX	MX27C8111	DIP 42	
MACRONIX	MX27C8111	SOP 44	PA44SO44D
MACRONIX	MX27L256	DIP 28	
MACRONIX	MX27L256	PLCC 32	PA32PL28D-YA
MACRONIX	MX27L256	TSOP 28	PA28TS28D-EO
MACRONIX	MX27L512	DIP 28	
MACRONIX	MX27L512	PLCC 32	PA32PL28D-YA
MACRONIX	MX27L512	TSOP 28	PA28TS28D-EO

MACRONIX	MX27L1000	DIP 32	
MACRONIX	MX27L1000	PLCC 32	PA32PL32D
MACRONIX	MX27L1000	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX27L1000	SOP 32	PA32SO32D-EO-450
MACRONIX	MX27L2000	DIP 32	
MACRONIX	MX27L2000	PLCC 32	PA32PL32D
MACRONIX	MX27L2000	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX27L2000	SOP 32	PA32SO32D-EO-450
MACRONIX	MX27L4000	DIP 32	
MACRONIX	MX27L4000	PLCC 32	PA32PL32D
MACRONIX	MX27L4000	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX27L4000	SOIC 32	PA32SO32D-EO-450
MACRONIX	MX27L4100	DIP 40	
MACRONIX	MX27L4100	SOP 40	PA40SO40D-EO-450
MACRONIX	MX27L1024	DIP 40	
MACRONIX	MX27L1024	PLCC 44	PA44-48U
MACRONIX	MX27L1024	TSOP 40	PA40TS40D
MACRONIX	MX27L1024	SOP 40	PA40SO40D-EO-450
MACRONIX	MX27L4096	DIP 40	
MACRONIX	MX27L4096	PLCC 44	PA44-48U
MACRONIX	MX27L4096	TSOP 40	PA40TS40D
MACRONIX	MX28F1000	DIP 32	
MACRONIX	MX28F1000	PLCC 32	PA32PL32D
MACRONIX	MX28F2000	DIP 32	
MACRONIX	MX28F2000	PLCC 32	PA32PL32D
MACRONIX	MX28F160C3BTC	TSOP 48	PA48TS48D
MACRONIX	MX28F160C3TTC	TSOP 48	PA48TS48D
MACRONIX	MX29F001B	DIP 32	
MACRONIX	MX29F001B	PLCC 32	PA32PL32D
MACRONIX	MX29F001B	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F001T	DIP 32	
MACRONIX	MX29F001T	PLCC 32	PA32PL32D
MACRONIX	MX29F001T	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F002B	DIP 32	
MACRONIX	MX29F002B	PLCC 32	PA32PL32D
MACRONIX	MX29F002B	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F002T	DIP 32	
MACRONIX	MX29F002T	PLCC 32	PA32PL32D
MACRONIX	MX29F002T	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F002NB	DIP 32	
MACRONIX	MX29F002NB	PLCC 32	PA32PL32D
MACRONIX	MX29F002NB	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F002NT	DIP 32	
MACRONIX	MX29F002NT	PLCC 32	PA32PL32D
MACRONIX	MX29F002NT	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F022B	DIP 32	
MACRONIX	MX29F022B	PLCC 32	PA32PL32D
MACRONIX	MX29F022B	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F022T	DIP 32	
MACRONIX	MX29F022T	PLCC 32	PA32PL32D
MACRONIX	MX29F022T	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F022NB	DIP 32	
MACRONIX	MX29F022NB	PLCC 32	PA32PL32D
MACRONIX	MX29F022NB	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F022NT	DIP 32	
MACRONIX	MX29F022NT	PLCC 32	PA32PL32D
MACRONIX	MX29F022NT	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F004B	DIP 32	
MACRONIX	MX29F004B	PLCC 32	PA32PL32D
MACRONIX	MX29F004B	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F004T	DIP 32	
MACRONIX	MX29F004T	PLCC 32	PA32PL32D
MACRONIX	MX29F004T	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F040PC	DIP 32	
MACRONIX	MX29F040QC	PLCC 32	PA32PL32D
MACRONIX	MX29F040TC	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F040CPC	DIP 32	
MACRONIX	MX29F040CTC	PLCC 32	PA32PL32D
MACRONIX	MX29F040CTC	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F016	SOP 44	PA44SO44D
MACRONIX	MX29F016	TSOP 48	PA48TS48D
MACRONIX	MX29F016	TSOP 40	PA40TS40D
MACRONIX	MX29F100BMC	SOP 44	PA44SO44D

MACRONIX	MX29F100BTC	TSOP 48	PA48TS48D
MACRONIX	MX29F100TMC	SOP 44	PA44SO44D
MACRONIX	MX29F100TTC	TSOP 48	PA48TS48D
MACRONIX	MX29F200B	SOP 44	PA44SO44D
MACRONIX	MX29F200B	TSOP 48	PA48TS48D
MACRONIX	MX29F200T	SOP 44	PA44SO44D
MACRONIX	MX29F200T	TSOP 48	PA48TS48D
MACRONIX	MX29F200CBMI	SOP 44	PA44SO44D
MACRONIX	MX29F200CBTI	TSOP 48	PA48TS48D
MACRONIX	MX29F200CTMI	SOP 44	PA44SO44D
MACRONIX	MX29F200CTTI	TSOP 48	PA48TS48D
MACRONIX	MX29F400BMC	SOP 44	PA44SO44D
MACRONIX	MX29F400BTC	TSOP 48	PA48TS48D
MACRONIX	MX29F400TMC	SOP 44	PA44SO44D
MACRONIX	MX29F400TTC	TSOP 48	PA48TS48D
MACRONIX	MX29F400CBMC	SOP 44	PA44SO44D
MACRONIX	MX29F400CBTC	TSOP 48	PA48TS48D
MACRONIX	MX29F400CTMC	SOP 44	PA44SO44D
MACRONIX	MX29F400CTTC	TSOP 48	PA48TS48D
MACRONIX	MX29F800CBT	TSOP 48	PA48TS48D
MACRONIX	MX29F800CTT	TSOP 48	PA48TS48D
MACRONIX	MX29F800B	SOP 44	PA44SO44D
MACRONIX	MX29F800B	TSOP 48	PA48TS48D
MACRONIX	MX29F800T	SOP 44	PA44SO44D
MACRONIX	MX29F800T	TSOP 48	PA48TS48D
MACRONIX	MX29F8100MC(USB2.0only)	SOP 44	PA44SO44D
MACRONIX	MX29F8100TC(USB2.0only)	TSOP 48	PA48TS48D
MACRONIX	MX29F1610MC(USB2.0only)	SOP 44	PA44SO44D
MACRONIX	MX29F1610TC(USB2.0only)	TSOP 48	PA48TS48D
MACRONIX	MX29F1610AMC(USB2.0only)	SOP 44	PA44SO44D
MACRONIX	MX29F1610ATC(USB2.0only)	TSOP 48	PA48TS48D
MACRONIX	MX29F1610BTC(USB2.0only)	TSOP 48	PA48TS48D
MACRONIX	MX29F1611MC(USB2.0only)	SOP 44	PA44SO44D
MACRONIX	MX29F1611TC(USB2.0only)	TSOP 48	PA48TS48D
MACRONIX	MX29L8000BTC(USB2.0only)	TSOP 40	PA40TS40D
MACRONIX	MX29L8000TTC(USB2.0only)	TSOP 40	PA40TS40D
MACRONIX	MX29L8100BTC(USB2.0only)	TSOP 48	PA48TS48D
MACRONIX	MX29L8100TTC(USB2.0only)	TSOP 48	PA48TS48D
MACRONIX	MX29L1611MC(USB2.0only)	SOP 44	PA44SO44D
MACRONIX	MX29L1611TC(USB2.0only)	TSOP 48	PA48TS48D
MACRONIX	MX29L3211MC(USB2.0only)	SOP 44	PA44SO44D
MACRONIX	MX29L3211TC(USB2.0only)	TSOP 48	PA48TS48D
MACRONIX	MX29L3211AMC(USB2.0only)	SOP 44	PA44SO44D
MACRONIX	MX29L3211ATC(USB2.0only)	TSOP 48	PA48TS48D
MACRONIX	MX29F1615	DIP 42	
MACRONIX	MX29L1611G	DIP 42	
MACRONIX	MX29LA320MBTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LA320MTTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LA320MBXBC	BGA 48	PA48BG48DW
MACRONIX	MX29LA320MBXEC	BGA 48	PA48BG48DW
MACRONIX	MX29LA320MTXBC	BGA 48	PA48BG48DW
MACRONIX	MX29LA320MTXEC	BGA 48	PA48BG48DW
MACRONIX	MX29LV400BXBC	BGA 48	PA48BG48DW
MACRONIX	MX29LV400BXEC	BGA 48	PA48BG48DW
MACRONIX	MX29LV400TXBC	BGA 48	PA48BG48DW
MACRONIX	MX29LV400TXEC	BGA 48	PA48BG48DW
MACRONIX	MX29LV400CBXBC	BGA 48	PA48BG48DW
MACRONIX	MX29LV400CBXEC	BGA 48	PA48BG48DW
MACRONIX	MX29LV400CTXBC	BGA 48	PA48BG48DW
MACRONIX	MX29LV400CTXEC	BGA 48	PA48BG48DW
MACRONIX	MX29LV800BXBC	BGA 48	PA48BG48DW
MACRONIX	MX29LV800BXEC	BGA 48	PA48BG48DW
MACRONIX	MX29LV800TXBC	BGA 48	PA48BG48DW
MACRONIX	MX29LV800TXEC	BGA 48	PA48BG48DW
MACRONIX	MX29LV800ABXBC	BGA 48	PA48BG48DW
MACRONIX	MX29LV800ABXEC	BGA 48	PA48BG48DW
MACRONIX	MX29LV800ATXBC	BGA 48	PA48BG48DW
MACRONIX	MX29LV800ATXEC	BGA 48	PA48BG48DW
MACRONIX	MX29LV800BBXBC	BGA 48	PA48BG48DW
MACRONIX	MX29LV800BBXEC	BGA 48	PA48BG48DW
MACRONIX	MX29LV800BTXBC	BGA 48	PA48BG48DW
MACRONIX	MX29LV800BTXEC	BGA 48	PA48BG48DW
MACRONIX	MX29LV800CBXBC	BGA 48	PA48BG48DW

MACRONIX	MX29LV800CBXEC	BGA 48	PA48BG48DW
MACRONIX	MX29LV800CTXBC	BGA 48	PA48BG48DW
MACRONIX	MX29LV800CTXEC	BGA 48	PA48BG48DW
MACRONIX	MX29LV160CBXBC	BGA 48	PA48BG48DW
MACRONIX	MX29LV160CBXEC	BGA 48	PA48BG48DW
MACRONIX	MX29LV160CTXBC	BGA 48	PA48BG48DW
MACRONIX	MX29LV160CTXEC	BGA 48	PA48BG48DW
MACRONIX	MX29LV320TXBC	BGA 48	PA48BG48DW
MACRONIX	MX29LV320TXEC	BGA 48	PA48BG48DW
MACRONIX	MX29LV320BXBC	BGA 48	PA48BG48DW
MACRONIX	MX29LV320BXEC	BGA 48	PA48BG48DW
MACRONIX	MX29LV320CTXBC	BGA 48	PA48BG48DW
MACRONIX	MX29LV320CTXEC	BGA 48	PA48BG48DW
MACRONIX	MX29LV320CBXBC	BGA 48	PA48BG48DW
MACRONIX	MX29LV320CBXEC	BGA 48	PA48BG48DW
MACRONIX	MX29LV320DB	BGA 48	PA48BG48DW
MACRONIX	MX29LV320DT	BGA 48	PA48BG48DW
MACRONIX	MX29LV640DB	BGA 48	PA48BG48DW
MACRONIX	MX29LV640DT	BGA 48	PA48BG48DW
MACRONIX	MX29LV640EB	BGA 48	PA48BG48DW
MACRONIX	MX29LV640ET	BGA 48	PA48BG48DW
MACRONIX	MX29LV320MBXBC	BGA 48	PA48BG48DW
MACRONIX	MX29LV320MBXEC	BGA 48	PA48BG48DW
MACRONIX	MX29LV320MTXBC	BGA 48	PA48BG48DW
MACRONIX	MX29LV320MTXEC	BGA 48	PA48BG48DW
MACRONIX	MX29LA320MBXBC	BGA 48	HA48BG48DAI
MACRONIX	MX29LA320MBXEC	BGA 48	HA48BG48DAI
MACRONIX	MX29LA320MTXBC	BGA 48	HA48BG48DAI
MACRONIX	MX29LA320MTXEC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV400BXBC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV400BXEC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV400TXBC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV400TXEC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV400CBXBC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV400CBXEC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV400CTXBC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV400CTXEC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV800BXBC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV800BXEC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV800TXBC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV800TXEC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV800ABXBC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV800ABXEC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV800ATXBC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV800ATXEC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV800BBXBC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV800BBXEC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV800BTXBC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV800BTXEC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV800CBXBC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV800CBXEC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV800CTXBC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV800CTXEC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV160CBXBC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV160CBXEC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV160CTXBC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV160CTXEC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV320TXBC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV320TXEC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV320BXBC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV320BXEC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV320CTXBC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV320CTXEC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV320CBXBC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV320CBXEC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV320DB	BGA 48	HA48BG48DAI
MACRONIX	MX29LV320DT	BGA 48	HA48BG48DAI
MACRONIX	MX29LV320EB	BGA 48	HA48BG48DAI
MACRONIX	MX29LV320ET	BGA 48	HA48BG48DAI
MACRONIX	MX29LV640DB	BGA 48	HA48BG48DAI
MACRONIX	MX29LV640DT	BGA 48	HA48BG48DAI
MACRONIX	MX29LV640EB	BGA 48	HA48BG48DAI
MACRONIX	MX29LV640ET	BGA 48	HA48BG48DAI

MACRONIX	MX29LV320MBXBC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV320MBXEC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV320MTXBC	BGA 48	HA48BG48DAI
MACRONIX	MX29LV320MTXEC	BGA 48	HA48BG48DAI
MACRONIX	MX29LA321MBTC	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
MACRONIX	MX29LA321MTTC	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
MACRONIX	MX29LA321MHTC	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
MACRONIX	MX29LA321MLTC	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
MACRONIX	MX29LA128MBTC	TSOP 56	PA56TS48DB
MACRONIX	MX29LA128MTTC	TSOP 56	PA56TS48DB
MACRONIX	MX29LV040QC	PLCC 32	PA32PL32D
MACRONIX	MX29LV040TC	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX29LV040CQC	PLCC 32	PA32PL32D
MACRONIX	MX29LV040CTC	TSOP 32	PA32TS20/PA32TS32D-20
MACRONIX	MX29LV002BPC	DIP 32	
MACRONIX	MX29LV002BQC	PLCC 32	PA32PL32D
MACRONIX	MX29LV002BTC	TSOP 32	PA32TS32D
MACRONIX	MX29LV002TPC	DIP 32	
MACRONIX	MX29LV002TQC	PLCC 32	PA32PL32D
MACRONIX	MX29LV002TTC	TSOP 32	PA32TS32D
MACRONIX	MX29LV002NBPC	DIP 32	
MACRONIX	MX29LV002NBQC	PLCC 32	PA32PL32D
MACRONIX	MX29LV002NBTC	TSOP 32	PA32TS32D
MACRONIX	MX29LV002NTPC	DIP 32	
MACRONIX	MX29LV002NTQC	PLCC 32	PA32PL32D
MACRONIX	MX29LV002NTTC	TSOP 32	PA32TS32D
MACRONIX	MX29LV002CBQC	PLCC 32	PA32PL32D
MACRONIX	MX29LV002CBTC	TSOP 32	PA32TS32D
MACRONIX	MX29LV002CTQC	PLCC 32	PA32PL32D
MACRONIX	MX29LV002CTTC	TSOP 32	PA32TS32D
MACRONIX	MX29LV002NCBQC	PLCC 32	PA32PL32D
MACRONIX	MX29LV002NCBTC	TSOP 32	PA32TS32D
MACRONIX	MX29LV002NCTQC	PLCC 32	PA32PL32D
MACRONIX	MX29LV002NCTTC	TSOP 32	PA32TS32D
MACRONIX	MX29LV004B	DIP 32	
MACRONIX	MX29LV004T	DIP 32	
MACRONIX	MX29LV004BTC	TSOP 40	PA40TS40D
MACRONIX	MX29LV004TTC	TSOP 40	PA40TS40D
MACRONIX	MX29LV004CBQC	PLCC 32	PA32PL32D
MACRONIX	MX29LV004CTQC	PLCC 32	PA32PL32D
MACRONIX	MX29LV004CBTC	TSOP 40	PA40TS40D
MACRONIX	MX29LV004CTTC	TSOP 40	PA40TS40D
MACRONIX	MX29LV008BTC	TSOP 40	PA40TS40D
MACRONIX	MX29LV008TTC	TSOP 40	PA40TS40D
MACRONIX	MX29LV008BBTC	TSOP 40	PA40TS40D
MACRONIX	MX29LV008BTTC	TSOP 40	PA40TS40D
MACRONIX	MX29LV008CBTC	TSOP 40	PA40TS40D
MACRONIX	MX29LV008CTTC	TSOP 40	PA40TS40D
MACRONIX	MX29LV081	TSOP 40	PA40TS40D
MACRONIX	MX29LV017A	TSOP 40	PA40TS40D
MACRONIX	MX29LV033	TSOP 40	PA40TS40D
MACRONIX	MX29LV033A	TSOP 40	PA40TS40D
MACRONIX	MX29LV033C	TSOP 40	PA40TS40D
MACRONIX	MX29LV033M	TSOP 40	PA40TS40D
MACRONIX	MX29LV033TC	TSOP 40	PA40TS40D
MACRONIX	MX29LV033MTC	TSOP 40	PA40TS40D
MACRONIX	MX29LV065BTC	TSOP 48	PA48TS48D
MACRONIX	MX29LV065MTC	TSOP 48	PA48TS48D
MACRONIX	MX29LV400BMC	SOP 44	PA44SO44D1
MACRONIX	MX29LV400BTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV400TMC	SOP 44	PA44SO44D1
MACRONIX	MX29LV400TTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV400CBMC	SOP 44	PA44SO44D1
MACRONIX	MX29LV400CBTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV400CTMC	SOP 44	PA44SO44D1
MACRONIX	MX29LV400CTTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV401B	SOP 44	PA44SO44D1
MACRONIX	MX29LV401B	TSOP 48	PA48TS48D1
MACRONIX	MX29LV401T	SOP 44	PA44SO44D1
MACRONIX	MX29LV401T	TSOP 48	PA48TS48D1
MACRONIX	MX29LV800BMC	SOP 44	PA44SO44D1
MACRONIX	MX29LV800BTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV800TMC	SOP 44	PA44SO44D1

MACRONIX	MX29LV800TTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV800ABMC	SOP 44	PA44SO44D1
MACRONIX	MX29LV800ABTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV800ATMC	SOP 44	PA44SO44D1
MACRONIX	MX29LV800ATTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV800BBMC	SOP 44	PA44SO44D1
MACRONIX	MX29LV800BBTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV800BBI	TSOP 48	PA48TS48D1
MACRONIX	MX29LV800BTMC	SOP 44	PA44SO44D1
MACRONIX	MX29LV800BTTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV800BTI	TSOP 48	PA48TS48D1
MACRONIX	MX29LV800CBMC	SOP 44	PA44SO44D1
MACRONIX	MX29LV800CBTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV800CBTI	TSOP 48	PA48TS48D1
MACRONIX	MX29LV800CTMC	SOP 44	PA44SO44D1
MACRONIX	MX29LV800CTTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV160BMC	SOP 44	PA44SO44D1
MACRONIX	MX29LV160BTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV160TMC	SOP 44	PA44SO44D1
MACRONIX	MX29LV160TTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV160ABMC	SOP 44	PA44SO44D1
MACRONIX	MX29LV160ABTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV160ATMC	SOP 44	PA44SO44D1
MACRONIX	MX29LV160ATTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV160BTTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV160BBTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV160CBMC	SOP 44	PA44SO44D1
MACRONIX	MX29LV160CBTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV160CTMC	SOP 44	PA44SO44D1
MACRONIX	MX29LV160CTTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV160DB	TSOP 48	PA48TS48D1
MACRONIX	MX29LV160DB	BGA 48	PA48BG48DAI
MACRONIX	MX29LV160DT	TSOP 48	PA48TS48D1
MACRONIX	MX29LV160DT	BGA 48	PA48BG48DAI
MACRONIX	MX29LV161DBT	TSOP 48	PA48TS48D1
MACRONIX	MX29LV161DTT	TSOP 48	PA48TS48D1
MACRONIX	MX29LV320TTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV320ATTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV320ABTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV320BTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV320CTTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV320CBTC	TSOP 48	PA48TS48D
MACRONIX	MX29LV320DB	TSOP 48	PA48TS48D1
MACRONIX	MX29LV320DT	TSOP 48	PA48TS48D1
MACRONIX	MX29LV320EB	TSOP 48	PA48TS48D1
MACRONIX	MX29LV320ET	TSOP 48	PA48TS48D1
MACRONIX	MX29LV321DT	TSOP 48	PA48TS48D1
MACRONIX	MX29LV321DB	TSOP 48	PA48TS48D1
MACRONIX	MX29LV320MBTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV320MTTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV320MHTC	TSOP 56	PA56TS48DB
MACRONIX	MX29LV320MLTC	TSOP 56	PA56TS48DB
MACRONIX	MX29LV640TTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV640BTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV640BTTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV640BBTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV640BUTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV640DTTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV640DBTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV640DTTI	TSOP 48	PA48TS48D1
MACRONIX	MX29LV640DBTI	TSOP 48	PA48TS48D1
MACRONIX	MX29LV640ET	TSOP 48	PA48TS48D1
MACRONIX	MX29LV640EB	TSOP 48	PA48TS48D1
MACRONIX	MX29LV640MBTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV640MTTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV640MHTC	TSOP 56	PA56TS48DC
MACRONIX	MX29LV640MLTC	TSOP 56	PA56TS48DC
MACRONIX	MX29LV641MHTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV641MLTC	TSOP 48	PA48TS48D1
MACRONIX	MX29LV128MHTC	TSOP 56	PA56TS48DB
MACRONIX	MX29LV128MLTC	TSOP 56	PA56TS48DB
MACRONIX	MX29LV128MBTC	TSOP 56	PA56TS48DB
MACRONIX	MX29LV128MTTC	TSOP 56	PA56TS48DB



MACRONIX	MX29LV128DBT2C	TSOP 56	PA56TS48DB
MACRONIX	MX29LV128DBT2C	TSOP 56	PA56TS48DC
MACRONIX	MX29LV128DBT2C	TSOP 56	PA56TS48DD
MACRONIX	MX29LV128DTT2C	TSOP 56	PA56TS48DB
MACRONIX	MX29LV128DTT2C	TSOP 56	PA56TS48DC
MACRONIX	MX29LV128DTT2C	TSOP 56	PA56TS48DD
MACRONIX	MX29LV128DBTC	TSOP 48	PA48TS48D
MACRONIX	MX29LV128DTTC	TSOP 48	PA48TS48D
MACRONIX	MX29GL320ELT2	TSOP 56	PA56TS48DB
MACRONIX	MX29GL320ELT2	TSOP 56	PA56TS48DC
MACRONIX	MX29GL320ELT2	TSOP 56	PA56TS48DD
MACRONIX	MX29GL320EHT2	TSOP 56	PA56TS48DB
MACRONIX	MX29GL320EHT2	TSOP 56	PA56TS48DC
MACRONIX	MX29GL320EHT2	TSOP 56	PA56TS48DD
MACRONIX	MX29GL640ELT2	TSOP 56	PA56TS48DB
MACRONIX	MX29GL640ELT2	TSOP 56	PA56TS48DC
MACRONIX	MX29GL640ELT2	TSOP 56	PA56TS48DD
MACRONIX	MX29GL640EHT2	TSOP 56	PA56TS48DB
MACRONIX	MX29GL640EHT2	TSOP 56	PA56TS48DC
MACRONIX	MX29GL640EHT2	TSOP 56	PA56TS48DD
MACRONIX	MX29GL640ETTI	TSOP 48	PA48TS48D1
MACRONIX	MX29GL128ELT2	TSOP 56	PA56TS48DB
MACRONIX	MX29GL128ELT2	TSOP 56	PA56TS48DC
MACRONIX	MX29GL128ELT2	TSOP 56	PA56TS48DD
MACRONIX	MX29GL128FDT2	TSOP 56	HA56TS48DI
MACRONIX	MX29GL128FUT2	TSOP 56	HA56TS48DI
MACRONIX	MX29GL128EHT2	TSOP 56	PA56TS48DB
MACRONIX	MX29GL128EHT2	TSOP 56	PA56TS48DC
MACRONIX	MX29GL128EHT2	TSOP 56	PA56TS48DD
MACRONIX	MX29GL256ELT2	TSOP 56	PA56TS48DC
MACRONIX	MX29GL256ELT2	TSOP 56	PA56TS48DD
MACRONIX	MX29GL256EHT2	TSOP 56	PA56TS48DC
MACRONIX	MX29GL256EHT2	TSOP 56	PA56TS48DD
MACRONIX	MX29GL128FLT2	TSOP 56	PA56TS48DD
MACRONIX	MX29GL128FHT2	TSOP 56	PA56TS48DD
MACRONIX	MX29GL512FHT2	TSOP 56	PA56TS48DD
MACRONIX	MX29GL512FHT2	TSOP 56	HA56TS48DI
MACRONIX	MX29GL512GHT2	TSOP 56	HA56TS48DI
MACRONIX	MX29GL512GLT2	TSOP 56	HA56TS48DI
MACRONIX	MX29GL512GHXF	BGA 64	PA64BG48DR
MACRONIX	MX29GL512GLXF	BGA 64	PA64BG48DR
MACRONIX	MX68GL1G0FHT2I	TSOP 56	HA56TS48DI
MACRONIX	MX29GA120ELXF	BGA 64	PA64BG48DK
MACRONIX	MX29GA120EHXF	BGA 64	PA64BG48DK
MACRONIX	MX29GA128ELXF	BGA 64	PA64BG48DK
MACRONIX	MX29GA128EHXF	BGA 64	PA64BG48DK
MACRONIX	MX29GA250ELXF	BGA 64	PA64BG48DK
MACRONIX	MX29GA250EHXF	BGA 64	PA64BG48DK
MACRONIX	MX29GA256ELXF	BGA 64	PA64BG48DK
MACRONIX	MX29GA256EHXF	BGA 64	PA64BG48DK
MACRONIX	MX29GL320ELXF	BGA 64	PA64BG48DK
MACRONIX	MX29GL320EHXF	BGA 64	PA64BG48DK
MACRONIX	MX29GL640ELXF	BGA 64	PA64BG48DK
MACRONIX	MX29GL640EHXF	BGA 64	PA64BG48DK
MACRONIX	MX29GL128ELXF	BGA 64	PA64BG48DK
MACRONIX	MX29GL128EHXF	BGA 64	PA64BG48DK
MACRONIX	MX29GL256ELXF	BGA 64	PA64BG48DK
MACRONIX	MX29GL256EHXF	BGA 64	PA64BG48DK
MACRONIX	MX29GL256FUXF	BGA 64	PA64BG48DK
MACRONIX	MX29GL256FLXF	BGA 64	PA64BG48DK
MACRONIX	MX29GL256FHXF	BGA 64	PA64BG48DK
MACRONIX	MX29GL256FLXG	BGA 56	NA56BG48DU
MACRONIX	MX29GL256FHXG	BGA 56	NA56BG48DU
MACRONIX	MX29GL128FLXF	BGA 64	PA64BG48DK
MACRONIX	MX29GL128FHXF	BGA 64	PA64BG48DK
MACRONIX	MX29GL128FLXG	BGA 56	NA56BG48DU
MACRONIX	MX29GL128FHXG	BGA 56	NA56BG48DU
MACRONIX	MX29GL128FUXG	BGA 56	NA56BG48DU
MACRONIX	MX29GL128FDXG	BGA 56	NA56BG48DU
MACRONIX	MX29GL128FUXF	BGA 64	PA64BG48DR
MACRONIX	MX29GL128FDXF	BGA 64	PA64BG48DR
MACRONIX	MX29GL320DHXC	BGA 64	NA64BG48DT
MACRONIX	MX29GL320DLXC	BGA 64	NA64BG48DT

MACRONIX	MX29GL128EHXC	BGA 64	NA64BG48DT
MACRONIX	MX29GL128ELXC	BGA 64	NA64BG48DT
MACRONIX	MX29GL256EHXC	BGA 64	NA64BG48DT
MACRONIX	MX29GL256ELXC	BGA 64	NA64BG48DT
MACRONIX	MX29GA128EHXC	BGA 64	NA64BG48DT
MACRONIX	MX29GA128ELXC	BGA 64	NA64BG48DT
MACRONIX	MX29GA256EHXC	BGA 64	NA64BG48DT
MACRONIX	MX29GA256ELXC	BGA 64	NA64BG48DT
MACRONIX	MX29LA321DHXC	BGA 64	NA64BG48DU
MACRONIX	MX29LA321DLXC	BGA 64	NA64BG48DU
MACRONIX	MX29LA641DHXC	BGA 64	NA64BG48DU
MACRONIX	MX29LA641DLXC	BGA 64	NA64BG48DU
MACRONIX	MX29GA129EHXC	BGA 64	NA64BG48DU
MACRONIX	MX29GA129ELXC	BGA 64	NA64BG48DU
MACRONIX	MX29GA257EHXC	BGA 64	NA64BG48DU
MACRONIX	MX29GA257ELXC	BGA 64	NA64BG48DU
MACRONIX	MX29SL402C-T-T	TSOP 48	PA48TS48D1
MACRONIX	MX29SL402C-B-T	TSOP 48	PA48TS48D1
MACRONIX	MX29SL800CTTI	TSOP 48	HA48TS48DJ
MACRONIX	MX29SL800CBTI	TSOP 48	HA48TS48DJ
MACRONIX	MX29SL800CTXB	BGA 48	HA48BG48DAY
MACRONIX	MX30LF1G08AA	BGA 63	HA63BG48DN
MACRONIX	MX30LF1G08AA(+Spare)	BGA 63	HA63BG48DN
MACRONIX	MX30LF1G08AA	TSOP 48	PA48TS48D
MACRONIX	MX30LF1G08AA(+Spare)	TSOP 48	PA48TS48D
MACRONIX	MX30LF1G18AC_TI	TSOP 48	PA48TS48D
MACRONIX	MX30LF1G18_T(+Spare)	TSOP 48	PA48TS48D
MACRONIX	MX30LF1G18AC_XK	BGA 63	HA63BG48DN
MACRONIX	MX30LF1G18_X(+Spare)	BGA 63	HA63BG48DN
MACRONIX	MX30LF1GE8AB_TI	TSOP 48	PA48TS48D
MACRONIX	MX30LF1GE8_T(+Spare)	TSOP 48	PA48TS48D
MACRONIX	MX30LF2G18AC_TI	TSOP 48	PA48TS48D
MACRONIX	MX30LF2G18_T(+Spare)	TSOP 48	PA48TS48D
MACRONIX	MX30LF2GE8AB_TI	TSOP 48	PA48TS48D
MACRONIX	MX30LF2GE8_T(+Spare)	TSOP 48	PA48TS48D
MACRONIX	MX30LF2G18AC_XK	BGA 63	HA63BG48DN
MACRONIX	MX30LF2G18_X(+Spare)	BGA 63	HA63BG48DN
MACRONIX	MX30LF4G18AC_TI	TSOP 48	PA48TS48D
MACRONIX	MX30LF4G18_T(+Spare)	TSOP 48	PA48TS48D
MACRONIX	MX30LF4GE8AB_TI	TSOP 48	PA48TS48D
MACRONIX	MX30LF4GE8_T(+Spare)	TSOP 48	PA48TS48D
MACRONIX	MX30LF4G18AC_XK	BGA 63	HA63BG48DN
MACRONIX	MX30LF4G18_X(+Spare)	BGA 63	HA63BG48DN
MICRON	MT28C64432W30A-T	BGA 88	PA88BGA48DA-YO-8X10
MICRON	MT28C128532W30D-TB	BGA 88	PA88BGA48DA-YO-8X10
MICRON	MT28C128564W30D-TB	BGA 88	PA88BGA48DA-YO-8X10
MICRON	MT28F800B3-B	TSOP 48	PA48TS48D
MICRON	MT28F800B3-T	TSOP 48	PA48TS48D
MICRON	MT28F800B5-B	TSOP 48	PA48TS48D
MICRON	MT28F800B5-T	TSOP 48	PA48TS48D
MICROCHIP	24AA00	DIP 8	
MICROCHIP	24AA00	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24AA00	TSSOP 8	PA8TSS8D
MICROCHIP	24AA00	SOT23- 5	PA5SOT5D
MICROCHIP	24AA00-I/P	DIP 8	
MICROCHIP	24AA00-I/SN	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24AA00-I/ST	TSSOP 8	PA8TSS8D
MICROCHIP	24AA01	DIP 8	
MICROCHIP	24AA01	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24AA01	TSSOP 8	PA8TSS8D
MICROCHIP	24AA01	MSOP 8	PA8MSOP8D
MICROCHIP	24AA01	SOT23- 5	PA5SOT5D
MICROCHIP	24AA014	DIP 8	
MICROCHIP	24AA014	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24AA014	TSSOP 8	PA8TSS8D
MICROCHIP	24AA014	MSOP 8	PA8MSOP8D
MICROCHIP	24AA02	DIP 8	
MICROCHIP	24AA02	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24AA02	TSSOP 8	PA8TSS8D
MICROCHIP	24AA02	MSOP 8	PA8MSOP8D
MICROCHIP	24AA02	SOT23- 5	PA5SOT5D
MICROCHIP	24AA024	DIP 8	
MICROCHIP	24AA024	SOIC 8	PA8SO8D-EO-150

MICROCHIP	24AA024	TSSOP 8	PA8TSS8D
MICROCHIP	24AA024	MSOP 8	PA8MSOP8D
MICROCHIP	24AA025E64-I/SN	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24AA02UID-I/SN	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24AA04	DIP 8	
MICROCHIP	24AA04	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24AA04	TSSOP 8	PA8TSS8D
MICROCHIP	24AA04	MSOP 8	PA8MSOP8D
MICROCHIP	24AA04	SOT23- 5	PA5SOT5D
MICROCHIP	24AA08	DIP 8	
MICROCHIP	24AA08	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24AA08	TSSOP 8	PA8TSS8D
MICROCHIP	24AA08	TSSOP 8	PA24TSS24D
MICROCHIP	24AA08	MSOP 8	PA8MSOP8D
MICROCHIP	24AA08	SOT23- 5	PA5SOT5D
MICROCHIP	24AA16	DIP 8	
MICROCHIP	24AA16	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24AA16	TSSOP 8	PA8TSS8D
MICROCHIP	24AA16	TSSOP 8	PA24TSS24D
MICROCHIP	24AA16	MSOP 8	PA8MSOP8D
MICROCHIP	24AA16	SOT23- 5	PA5SOT5D
MICROCHIP	24AA16-I/P	DIP 8	
MICROCHIP	24AA16-I/SN	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24AA16-I/ST	TSSOP 8	PA8TSS8D
MICROCHIP	24AA16-I-MS	MSOP 8	HA8MSOP48D
MICROCHIP	24AA164	DIP 8	
MICROCHIP	24AA164	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24AA174	DIP 8	
MICROCHIP	24AA174	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24AA32	DIP 8	
MICROCHIP	24AA32	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24AA32A	DIP 8	
MICROCHIP	24AA32A	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24AA32A	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24AA32A	TSSOP 8	PA8TSS8D
MICROCHIP	24AA32A	TSSOP 8	PA24TSS24D
MICROCHIP	24AA32A	MSOP 8	PA8MSOP8D
MICROCHIP	24AA32AX	TSSOP 8	PA8RTSS8D
MICROCHIP	24AA32A-I/P	DIP 8	
MICROCHIP	24AA32A-I/SN	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24AA32A-I/SM	SOIC 8	PA20SO20D-EO-210
MICROCHIP	24AA32A-I/ST	TSSOP 8	PA8TSS8D
MICROCHIP	24AA32A-I/MS	MSOP 8	HA8MSOP48D
MICROCHIP	24AA64	DIP 8	
MICROCHIP	24AA64	DFN 8	PA8QFN8D
MICROCHIP	24AA64	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24AA64	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24AA64	TSSOP 8	PA8TSS8D
MICROCHIP	24AA64	TSSOP 8	PA24TSS24D
MICROCHIP	24AA64	MSOP 8	PA8MSOP8D
MICROCHIP	24AA64X	TSSOP 8	PA8RTSS8D
MICROCHIP	24AA64-I/P	DIP 8	
MICROCHIP	24AA64-I/SN	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24AA64-I/MS	MSOP 8	HA8MSOP48D
MICROCHIP	24AA64-I/ST	TSSOP 8	PA8TSS8D
MICROCHIP	24AA64-I/SM	SOIC 8	PA20SO20D-EO-210
MICROCHIP	24AA65	DIP 8	
MICROCHIP	24AA65	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24AA128	DIP 8	
MICROCHIP	24AA128	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24AA128	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24AA128	TSSOP 8	PA8TSS8D
MICROCHIP	24AA128	TSSOP 8	PA24TSS24D
MICROCHIP	24AA128	TSSOP 14	PA28TSS28D-EO
MICROCHIP	24AA128	MSOP 8	PA8MSOP8D
MICROCHIP	24AA128	DFN 8	PA8SON8D
MICROCHIP	24AA256	DIP 8	
MICROCHIP	24AA256	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24AA256	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24AA256	TSSOP 8	PA8TSS8D
MICROCHIP	24AA256	TSSOP 8	PA24TSS24D
MICROCHIP	24AA256	TSSOP 14	PA28TSS28D-EO
MICROCHIP	24AA256	MSOP 8	PA8MSOP8D

MICROCHIP	24AA256	DFN 8	PA8SON8D
MICROCHIP	24AA512	DIP 8	
MICROCHIP	24AA512	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24AA512	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24AA512	TSSOP 8	PA8TSS8D
MICROCHIP	24AA512	TSSOP 8	PA24TSS24D
MICROCHIP	24AA512	TSSOP 14	PA28TSS28D-EO
MICROCHIP	24AA512	MSOP 8	PA8MSOP8D
MICROCHIP	24AA512	DFN 8	PA8SON8D
MICROCHIP	24AA515	DIP 8	
MICROCHIP	24AA515	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24AA515	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24AA1025	DIP 8	
MICROCHIP	24AA1025	SOIC 8	PA20SO20D-EO-210
MICROCHIP	24AA52	DIP 8	
MICROCHIP	24AA52	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24AA52	TSSOP 8	PA8TSS8D
MICROCHIP	24AA52	TSSOP 8	PA24TSS24D
MICROCHIP	24AA52	MSOP 8	PA8MSOP8D
MICROCHIP	24AA64T-I/MNY	DFN 8	PA8QFN8D
MICROCHIP	24C00	DIP 8	
MICROCHIP	24C00	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24C00	TSSOP 8	PA8TSS8D
MICROCHIP	24C00	TSSOP 8	PA24TSS24D
MICROCHIP	24C00	SOT23- 5	PA5SOT5D
MICROCHIP	24C01A	DIP 8	
MICROCHIP	24C01A	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24C01A	SOIC 14	PA16SO16D-EO-150
MICROCHIP	24C01B	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24C01B	SOIC 14	PA16SO16D-EO-150
MICROCHIP	24C01C	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24C01C	TSSOP 8	PA8TSS8D
MICROCHIP	24C01C	TSSOP 8	PA24TSS24D
MICROCHIP	24C02A	DIP 8	
MICROCHIP	24C02A	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24C02A	SOIC 14	PA16SO16D-EO-150
MICROCHIP	24C02B	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24C02B	SOIC 14	PA16SO16D-EO-150
MICROCHIP	24C04A	DIP 8	
MICROCHIP	24C04A	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24C04A	SOIC 14	PA16SO16D-EO-150
MICROCHIP	24C08A	DIP 8	
MICROCHIP	24C08A	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24C08A	SOIC 14	PA16SO16D-EO-150
MICROCHIP	24C08B	DIP 8	
MICROCHIP	24C08B	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24C08B	SOIC 14	PA16SO16D-EO-150
MICROCHIP	24C16A	DIP 8	
MICROCHIP	24C16A	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24C16A	SOIC 14	PA16SO16D-EO-150
MICROCHIP	24C16B	DIP 8	
MICROCHIP	24C16B	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24C16B	SOIC 14	PA16SO16D-EO-150
MICROCHIP	24C32	DIP 8	
MICROCHIP	24C32	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24C32	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24C32A	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24C32A	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24C64	DIP 8	
MICROCHIP	24C65	DIP 8	
MICROCHIP	24C65	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24C65	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24C128	DIP 8	
MICROCHIP	24C256	DIP 8	
MICROCHIP	24LC00	DIP 8	
MICROCHIP	24LC00	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LC00	TSSOP 8	PA8TSS8D
MICROCHIP	24LC00	TSSOP 8	PA24TSS24D
MICROCHIP	24LC00	SOT23- 5	PA5SOT5D
MICROCHIP	24LC00-I/P	DIP 8	
MICROCHIP	24LC00-I/SN	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LC014	DIP 8	
MICROCHIP	24LC014	SOIC 8	PA8SO8D-EO-150

MICROCHIP	24LC014	TSSOP 8	PA8TSS8D
MICROCHIP	24LC014	TSSOP 8	PA24TSS24D
MICROCHIP	24LC014	MSOP 8	PA8MSOP8D
MICROCHIP	24LC01B	DIP 8	
MICROCHIP	24LC02B	DIP 8	
MICROCHIP	24LC04B	DIP 8	
MICROCHIP	24LC08B	DIP 8	
MICROCHIP	24LC01B	TSSOP 8	PA8TSS8D
MICROCHIP	24LC01B	TSSOP 8	PA24TSS24D
MICROCHIP	24LC02B	TSSOP 8	PA8TSS8D
MICROCHIP	24LC02B	TSSOP 8	PA24TSS24D
MICROCHIP	24LC04B	TSSOP 8	PA8TSS8D
MICROCHIP	24LC04B	TSSOP 8	PA24TSS24D
MICROCHIP	24LC08B	TSSOP 8	PA8TSS8D
MICROCHIP	24LC08B	TSSOP 8	PA24TSS24D
MICROCHIP	24LC01B	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LC04B	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LC08B	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LC01B	MSOP 8	PA8MSOP8D
MICROCHIP	24LC02B	MSOP 8	PA8MSOP8D
MICROCHIP	24LC04B	MSOP 8	PA8MSOP8D
MICROCHIP	24LC08B	MSOP 8	PA8MSOP8D
MICROCHIP	24LC01B	SOT23- 5	PA5SOT5D
MICROCHIP	24LC02B	SOT23- 5	PA5SOT5D
MICROCHIP	24LC04B	SOT23- 5	PA5SOT5D
MICROCHIP	24LC08B	SOT23- 5	PA5SOT5D
MICROCHIP	24LC08B-I/P	DIP 8	
MICROCHIP	24LC08B-I/ST	TSSOP 8	PA8TSS8D
MICROCHIP	24LC08B-I/SN	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24LC08B-I/MS	MSOP 8	HA8MSOP48D
MICROCHIP	24LC09	DIP 8	
MICROCHIP	24LC09	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LC21	DIP 8	
MICROCHIP	24LC21	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LC21A	DIP 8	
MICROCHIP	24LC21A	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LC21A-I/P	DIP 8	
MICROCHIP	24LC21A-I/SN	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LC211	DIP 8	
MICROCHIP	24LC211	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LC22A	DIP 8	
MICROCHIP	24LC22A	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LC22A-I/P	DIP 8	
MICROCHIP	24LC22A-I/SN	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LC41	DIP 8	
MICROCHIP	24LC41	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LC41A	DIP 8	
MICROCHIP	24LC41A	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LC024	DIP 8	
MICROCHIP	24LC024	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LC024	TSSOP 8	PA8TSS8D
MICROCHIP	24LC024	TSSOP 8	PA24TSS24D
MICROCHIP	24LC024	MSOP 8	PA8MSOP8D
MICROCHIP	24LC025	DIP 8	
MICROCHIP	24LC025	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LC025	TSSOP 8	PA8TSS8D
MICROCHIP	24LC025	TSSOP 8	PA24TSS24D
MICROCHIP	24LC025	MSOP 8	PA8MSOP8D
MICROCHIP	24LC16B	DIP 8	
MICROCHIP	24LC16B	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LC16B	TSSOP 8	PA8TSS8D
MICROCHIP	24LC16B	TSSOP 8	PA24TSS24D
MICROCHIP	24LC16B	MSOP 8	PA8MSOP8D
MICROCHIP	24LC16B	SOT23- 5	PA5SOT5D
MICROCHIP	24LC16B	SOIC 14	PA16SO16D-EO-150
MICROCHIP	24LC16B-I/ST	TSSOP 8	PA8TSS8D
MICROCHIP	24LC16B-I/SN	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LC16B-I/P	DIP 8	
MICROCHIP	24LC16B-I/MS	MSOP 8	PA8MSOP8D
MICROCHIP	24LC164	DIP 8	
MICROCHIP	24LC164	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LC174	DIP 8	
MICROCHIP	24LC174	SOIC 8	PA8SO8D-EO-150

MICROCHIP	24LC32	DIP 8	
MICROCHIP	24LC32	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LC32A	DIP 8	
MICROCHIP	24LC32A	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LC32A	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24LC32A	TSSOP 8	PA8TSS8D
MICROCHIP	24LC32A	TSSOP 8	PA24TSS24D
MICROCHIP	24LC32A	MSOP 8	PA8MSOP8D
MICROCHIP	24LC32AX	TSSOP 8	PA8RTSS8D
MICROCHIP	24LC32A-I/P	DIP 8	
MICROCHIP	24LC32A-I/SN	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24LC32A-I/SM	SOIC 8	PA20SO20D-EO-210
MICROCHIP	24LC32A-I/ST	TSSOP 8	PA8TSS8D
MICROCHIP	24LC32A-I/MS	MSOP 8	HA8MSOP48D
MICROCHIP	24LC64	DIP 8	
MICROCHIP	24LC64	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24LC64	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LC64	TSSOP 8	PA8TSS8D
MICROCHIP	24LC64	TSSOP 8	PA24TSS24D
MICROCHIP	24LC64	MSOP 8	PA8MSOP8D
MICROCHIP	24LC64X	TSSOP 8	PA8RTSS8D
MICROCHIP	24LC65	DIP 8	
MICROCHIP	24LC65	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LC65	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24LC128	DIP 8	
MICROCHIP	24LC128	SOIC 8	PA20SO20D-EO-210
MICROCHIP	24LC128	TSSOP 8	PA24TSS24D
MICROCHIP	24LC128	TSSOP 14	PA28TSS28D-EO
MICROCHIP	24LC128	DFN 8	PA8SON8D
MICROCHIP	24LC256	DIP 8	
MICROCHIP	24LC256	SOIC 8	PA20SO20D-EO-210
MICROCHIP	24LC256	TSSOP 8	PA24TSS24D
MICROCHIP	24LC256	TSSOP 14	PA28TSS28D-EO
MICROCHIP	24LC256	DFN 8	PA8SON8D
MICROCHIP	24LC512	DIP 8	
MICROCHIP	24LC512	SOIC 8	PA20SO20D-EO-210
MICROCHIP	24LC512	TSSOP 8	PA24TSS24D
MICROCHIP	24LC512	TSSOP 14	PA28TSS28D-EO
MICROCHIP	24LC512	DFN 8	PA8SON8D
MICROCHIP	24LC515	DIP 8	
MICROCHIP	24LC515	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LC515	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24LC1025	DIP 8	
MICROCHIP	24LC1025	SOIC 8	PA20SO20D-EO-210
MICROCHIP	24LCS21	DIP 8	
MICROCHIP	24LCS21	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LCS21A	DIP 8	
MICROCHIP	24LCS21A	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LCS22A	DIP 8	
MICROCHIP	24LCS22A	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LCS41	DIP 8	
MICROCHIP	24LCS41A	DIP 8	
MICROCHIP	24LCS52	DIP 8	
MICROCHIP	24LCS52	TSSOP 8	PA8TSS-OT
MICROCHIP	24LCS52	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LCS52	TSSOP 8	PA8TSS8D
MICROCHIP	24LCS52	TSSOP 8	PA24TSS24D
MICROCHIP	24LCS52	MSOP 8	PA8MSOP8D
MICROCHIP	24LCS61	DIP 8	
MICROCHIP	24LCS61	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LCS61	TSSOP 14	PA28TSS28D-EO
MICROCHIP	24LCS62	DIP 8	
MICROCHIP	24LCS62	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24LCS62	TSSOP 14	PA28TSS28D-EO
MICROCHIP	24FC16	DIP 8	
MICROCHIP	24FC16	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24FC32	DIP 8	
MICROCHIP	24FC32	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24FC64	DIP 8	
MICROCHIP	24FC64	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24FC65	DIP 8	
MICROCHIP	24FC65	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24FC128	DIP 8	

MICROCHIP	24FC128	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24FC128	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24FC128	TSSOP 8	PA8TSS8D
MICROCHIP	24FC128	TSSOP 8	PA24TSS24D
MICROCHIP	24FC128	TSSOP 14	PA28TSS28D-EO
MICROCHIP	24FC128	MSOP 8	PA8MSOP8D
MICROCHIP	24FC128	DFN 8	PA8SON8D
MICROCHIP	24FC256	DIP 8	
MICROCHIP	24FC256	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24FC256	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24FC256	TSSOP 8	PA8TSS8D
MICROCHIP	24FC256	TSSOP 8	PA24TSS24D
MICROCHIP	24FC256	TSSOP 14	PA28TSS28D-EO
MICROCHIP	24FC256	MSOP 8	PA8MSOP8D
MICROCHIP	24FC256	DFN 8	PA8SON8D
MICROCHIP	24FC512	DIP 8	
MICROCHIP	24FC512	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24FC512	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24FC512	TSSOP 8	PA8TSS8D
MICROCHIP	24FC512	TSSOP 8	PA24TSS24D
MICROCHIP	24FC512	TSSOP 14	PA28TSS28D-EO
MICROCHIP	24FC512	MSOP 8	PA8MSOP8D
MICROCHIP	24FC512	DFN 8	PA8SON8D
MICROCHIP	24FC515	DIP 8	
MICROCHIP	24FC515	SOIC 8	PA8SO8D-EO-150
MICROCHIP	24FC515	SOIC 8	PA16SO16D-EO-150
MICROCHIP	24FC1025	DIP 8	
MICROCHIP	24FC1025	SOIC 8	PA20SO20D-EO-210
MICROCHIP	25AA02UID-I/SN	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25AA040	DIP 8	
MICROCHIP	25AA040	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25AA040	TSSOP 8	PA8TSS8D
MICROCHIP	25AA040	TSSOP 8	PA24TSS24D
MICROCHIP	25AA080	DIP 8	
MICROCHIP	25AA080	MSOP 8	PA8MSOP8D
MICROCHIP	25AA080	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25AA080A	DIP 8	
MICROCHIP	25AA080A	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25AA080A	TSSOP 8	PA8TSS8D
MICROCHIP	25AA080A	TSSOP 8	PA24TSS24D
MICROCHIP	25AA080A	MSOP 8	PA8MSOP8D
MICROCHIP	25AA080B	DIP 8	
MICROCHIP	25AA080B	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25AA080B	TSSOP 8	PA8TSS8D
MICROCHIP	25AA080B	TSSOP 8	PA24TSS24D
MICROCHIP	25AA080B	MSOP 8	PA8MSOP8D
MICROCHIP	25AA160	DIP 8	
MICROCHIP	25AA160	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25AA160A	DIP 8	
MICROCHIP	25AA160A	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25AA160A	TSSOP 8	PA8TSS8D
MICROCHIP	25AA160A	TSSOP 8	PA24TSS24D
MICROCHIP	25AA160A	MSOP 8	PA8MSOP8D
MICROCHIP	25AA160B	DIP 8	
MICROCHIP	25AA160B	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25AA160B	TSSOP 8	PA8TSS8D
MICROCHIP	25AA160B	TSSOP 8	PA24TSS24D
MICROCHIP	25AA160B	MSOP 8	PA8MSOP8D
MICROCHIP	25AA320	DIP 8	
MICROCHIP	25AA320	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25AA320X	TSSOP 8	PA8TSS8D
MICROCHIP	25AA320X	TSSOP 8	PA24TSS24D
MICROCHIP	25AA640	DIP 8	
MICROCHIP	25AA640	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25AA640X	TSSOP 8	PA8TSS8D
MICROCHIP	25AA640X	TSSOP 8	PA24TSS24D
MICROCHIP	25AA256	DIP 8	
MICROCHIP	25AA256	DFN 8	PA8SON8D
MICROCHIP	25AA256	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25AA256X	TSSOP 8	PA8TSS8D
MICROCHIP	25AA256X	TSSOP 8	PA24TSS24D
MICROCHIP	25AA512	DIP 8	
MICROCHIP	25AA512	DFN 8	PA8SON8D

MICROCHIP	25AA512	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25AA512X	TSSOP 8	PA8TSS8D
MICROCHIP	25AA512X	TSSOP 8	PA24TSS24D
MICROCHIP	25AA1024	DIP 8	
MICROCHIP	25AA1024	SOIC 8	PA20SO20D-EO-210
MICROCHIP	25AA1024	DFN 8	PA8SON8D
MICROCHIP	25LC040	DIP 8	
MICROCHIP	25LC040	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25LC040	TSSOP 8	PA8TSS8D
MICROCHIP	25LC040	TSSOP 8	PA24TSS24D
MICROCHIP	25LC080	DIP 8	
MICROCHIP	25LC080	MSOP 8	PA8MSOP8D
MICROCHIP	25LC080	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25LC080A	DIP 8	
MICROCHIP	25LC080A	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25LC080A	TSSOP 8	PA8TSS8D
MICROCHIP	25LC080A	TSSOP 8	PA24TSS24D
MICROCHIP	25LC080A	MSOP 8	PA8MSOP8D
MICROCHIP	25LC080B	DIP 8	
MICROCHIP	25LC080B	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25LC080B	TSSOP 8	PA8TSS8D
MICROCHIP	25LC080B	TSSOP 8	PA24TSS24D
MICROCHIP	25LC080B	MSOP 8	PA8MSOP8D
MICROCHIP	25LC160	DIP 8	
MICROCHIP	25LC160	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25LC160A	DIP 8	
MICROCHIP	25LC160A	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25LC160A	TSSOP 8	PA8TSS8D
MICROCHIP	25LC160A	TSSOP 8	PA24TSS24D
MICROCHIP	25LC160A	MSOP 8	PA8MSOP8D
MICROCHIP	25LC160B	DIP 8	
MICROCHIP	25LC160B	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25LC160B	TSSOP 8	PA8TSS8D
MICROCHIP	25LC160B	TSSOP 8	PA24TSS24D
MICROCHIP	25LC160B	MSOP 8	PA8MSOP8D
MICROCHIP	25LC320	DIP 8	
MICROCHIP	25LC320	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25LC320	TSSOP 14	PA14TSS14D
MICROCHIP	25LC320X	TSSOP 8	PA8TSS8D
MICROCHIP	25LC320X	TSSOP 8	PA24TSS24D
MICROCHIP	25LC640	DIP 8	
MICROCHIP	25LC640	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25LC640X	TSSOP 8	PA8TSS8D
MICROCHIP	25LC640X	TSSOP 8	PA24TSS24D
MICROCHIP	25LC256	DIP 8	
MICROCHIP	25LC256	DFN 8	PA8SON8D
MICROCHIP	25LC256	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25LC256X	TSSOP 8	PA8TSS8D
MICROCHIP	25LC256X	TSSOP 8	PA24TSS24D
MICROCHIP	25LC512	DIP 8	
MICROCHIP	25LC512	DFN 8	PA8SON8D
MICROCHIP	25LC512	SOIC 8	PA20SO20D-EO-210
MICROCHIP	25LC512	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25LC1024	DIP 8	
MICROCHIP	25LC1024	DFN 8	PA8SON8D
MICROCHIP	25LC1024	SOIC 8	PA20SO20D-EO-210
MICROCHIP	25C040	DIP 8	
MICROCHIP	25C040	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25C040	TSSOP 8	PA8TSS8D
MICROCHIP	25C040	TSSOP 8	PA24TSS24D
MICROCHIP	25C080	DIP 8	
MICROCHIP	25C080	MSOP 8	PA8MSOP8D
MICROCHIP	25C080	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25C160	DIP 8	
MICROCHIP	25C160	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25C320	DIP 8	
MICROCHIP	25C320	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25C320	TSSOP 14	PA14TSS14D
MICROCHIP	25C320X	TSSOP 8	PA8TSS8D
MICROCHIP	25C320X	TSSOP 8	PA24TSS24D
MICROCHIP	25C640	DIP 8	
MICROCHIP	25C640	SOIC 8	PA16SO16D-EO-150
MICROCHIP	25C640X	TSSOP 8	PA8TSS8D



MICROCHIP	25C640X		TSSOP 8	PA24TSS24D
MICROCHIP		27256	DIP 28	
MICROCHIP		27256	PLCC 32	PA32PL28D-YA
MICROCHIP	27C128		DIP 28	
MICROCHIP	27C128		PLCC 32	PA32PL28D-YA
MICROCHIP	27C128		SOIC 28	PA28SO28D-EO-300
MICROCHIP	27C256		DIP 28	
MICROCHIP	27C256		PLCC 32	PA32PL28D-YA
MICROCHIP	27C256		SOIC 28	PA28SO28D-EO-300
MICROCHIP	27C256		TSOP 28	PA28TS28D-EO
MICROCHIP	27C512		DIP 28	
MICROCHIP	27C512		PLCC 32	PA32PL28D-YA
MICROCHIP	27C512		SOIC 28	PA28SO28D-EO-300
MICROCHIP	27C512A		DIP 28	
MICROCHIP	27C512A		PLCC 32	PA32PL28D-YA
MICROCHIP	27C512A		SOIC 28	PA28SO28D-EO-300
MICROCHIP	27C512A		TSOP 28	PA28TS28D-EO
MICROCHIP	27C64		DIP 28	
MICROCHIP	27C64		PLCC 32	PA32PL28D-YA
MICROCHIP	27C64		SOIC 28	PA28SO28D-EO-300
MICROCHIP	27HC128		DIP 28	
MICROCHIP	27HC128		PLCC 32	PA32PL28D-YA
MICROCHIP	27HC128		SOIC 28	PA28SO28D-EO-300
MICROCHIP	27HC256		DIP 28	
MICROCHIP	27HC256		PLCC 32	PA32PL28D-YA
MICROCHIP	27HC256		SOIC 28	PA28SO28D-EO-300
MICROCHIP	27HC256L		DIP 28	
MICROCHIP	27HC256L		PLCC 32	PA32PL28D-YA
MICROCHIP	27HC256L		SOIC 28	PA28SO28D-EO-300
MICROCHIP	27HC64		DIP 28	
MICROCHIP	27HC64		SOIC 28	PA28SO28D-EO-300
MICROCHIP	27HC64		PLCC 32	PA32PL28D-YA
MICROCHIP	27HC64L		DIP 28	
MICROCHIP	27LV64		DIP 28	
MICROCHIP	27LV64		PLCC 32	PA32PL28D-YA
MICROCHIP	27LV64		SOIC 28	PA28SO28D-EO-300
MICROCHIP	27LV256		DIP 28	
MICROCHIP	27LV256		PLCC 32	PA32PL28D-YA
MICROCHIP	27LV256		SOIC 28	PA28SO28D-EO-300
MICROCHIP	27LV256		TSOP 28	PA28TS28D-EO
MICROCHIP	27LV512		DIP 28	
MICROCHIP	27LV512		PLCC 32	PA32PL28D-YA
MICROCHIP	27LV512		SOIC 28	PA28SO28D-EO-300
MICROCHIP	27LV512		TSOP 28	PA28TS28D-EO
MICROCHIP	28C04		DIP 24	
MICROCHIP	28C04A		DIP 24	
MICROCHIP	28C04A		PLCC 32	PA32PL32D
MICROCHIP	28C04AF		DIP 24	
MICROCHIP	28C04AF		PLCC 32	PA32PL32D
MICROCHIP	28C04F		DIP 24	
MICROCHIP	28C16		DIP 24	
MICROCHIP	28C16A		DIP 24	
MICROCHIP	28C16A		PLCC 32	PA32PL32D
MICROCHIP	28C16AF		DIP 24	
MICROCHIP	28C16AF		PLCC 32	PA32PL32D
MICROCHIP	28C16F		DIP 24	
MICROCHIP	28C17		DIP 28	
MICROCHIP	28C17A		DIP 28	
MICROCHIP	28C17A		PLCC 32	PA32PL28D-YA
MICROCHIP	28C17AF		DIP 28	
MICROCHIP	28C17AF		PLCC 32	PA32PL28D-YA
MICROCHIP	28C17F		DIP 28	
MICROCHIP	28C64		DIP 28	
MICROCHIP	28C64A		DIP 28	
MICROCHIP	28C64AX		DIP 28	
MICROCHIP	28C64AF		DIP 28	
MICROCHIP	37LV36		DIP 8	
MICROCHIP	37LV65		DIP 8	
MICROCHIP	37LV128		DIP 8	
MICROCHIP	85C72		DIP 8	
MICROCHIP	85C72		SOP 8	PA20SO20D-EO-210
MICROCHIP	85C82		DIP 8	
MICROCHIP	85C82		SOP 8	PA20SO20D-EO-210

MICROCHIP	85C92	DIP 8	
MICROCHIP	85C92	SOP 8	PA20SO20D-EO-210
MICROCHIP	85C92	SOIC 14	PA16SO16D-EO-150
MICROCHIP	93AA46	DIP 8	
MICROCHIP	93AA46	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93AA46X	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93AA46A	DIP 8	
MICROCHIP	93AA46A	TSSOP 8	PA8TSS-OT
MICROCHIP	93AA46A	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93AA46AX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93AA46B	DIP 8	
MICROCHIP	93AA46B	TSSOP 8	PA8TSS-OT
MICROCHIP	93AA46B	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93AA46BX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93AA46C	DIP 8	
MICROCHIP	93AA46C	TSSOP 8	PA8TSS-OT
MICROCHIP	93AA46C	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93AA46CX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93AA56	DIP 8	
MICROCHIP	93AA56	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93AA56X	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93AA56A	DIP 8	
MICROCHIP	93AA56A	TSSOP 8	PA8TSS-OT
MICROCHIP	93AA56A	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93AA56AX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93AA56B	DIP 8	
MICROCHIP	93AA56B	TSSOP 8	PA8TSS-OT
MICROCHIP	93AA56B	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93AA56BX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93AA56C	DIP 8	
MICROCHIP	93AA56C	TSSOP 8	PA8TSS-OT
MICROCHIP	93AA56C	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93AA56CX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93AA66	DIP 8	
MICROCHIP	93AA66	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93AA66X	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93AA66A	DIP 8	
MICROCHIP	93AA66A	TSSOP 8	PA8TSS-OT
MICROCHIP	93AA66A	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93AA66AX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93AA66B	DIP 8	
MICROCHIP	93AA66B	TSSOP 8	PA8TSS-OT
MICROCHIP	93AA66B	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93AA66BX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93AA66C	DIP 8	
MICROCHIP	93AA66C	TSSOP 8	PA8TSS-OT
MICROCHIP	93AA66C	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93AA66CX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93AA76	DIP 8	
MICROCHIP	93AA76	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93AA76X	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93AA76B	DIP 8	
MICROCHIP	93AA76B	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93AA76C	DIP 8	
MICROCHIP	93AA76C	TSSOP 8	PA8TSS-OT
MICROCHIP	93AA76C	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93AA86	DIP 8	
MICROCHIP	93AA86	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93AA86X	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93AA86B	DIP 8	
MICROCHIP	93AA86B	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93AA86C	DIP 8	
MICROCHIP	93AA86C	TSSOP 8	PA8TSS-OT
MICROCHIP	93AA86C	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93C06	DIP 8	
MICROCHIP	93C06	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93C46	DIP 8	
MICROCHIP	93C46	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93C46X	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93C46A	DIP 8	
MICROCHIP	93C46A	TSSOP 8	PA8TSS-OT
MICROCHIP	93C46A	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93C46AX	SOIC 8	PA8SO8D-EO-150

MICROCHIP	93C46B	DIP 8	
MICROCHIP	93C46B	TSSOP 8	PA8TSS-OT
MICROCHIP	93C46B	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93C46BX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93C46C	DIP 8	
MICROCHIP	93C46C	TSSOP 8	PA8TSS-OT
MICROCHIP	93C46C	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93C46CX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93C56	DIP 8	
MICROCHIP	93C56	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93C56X	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93C56A	DIP 8	
MICROCHIP	93C56A	TSSOP 8	PA8TSS-OT
MICROCHIP	93C56A	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93C56AX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93C56B	DIP 8	
MICROCHIP	93C56B	TSSOP 8	PA8TSS-OT
MICROCHIP	93C56B	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93C56BX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93C56C	DIP 8	
MICROCHIP	93C56C	TSSOP 8	PA8TSS-OT
MICROCHIP	93C56C	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93C56CX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93C66	DIP 8	
MICROCHIP	93C66	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93C66A	DIP 8	
MICROCHIP	93C66A	TSSOP 8	PA8TSS-OT
MICROCHIP	93C66A	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93C66AX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93C66B	DIP 8	
MICROCHIP	93C66B	TSSOP 8	PA8TSS-OT
MICROCHIP	93C66B	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93C66BX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93C66C	DIP 8	
MICROCHIP	93C66C	TSSOP 8	PA8TSS-OT
MICROCHIP	93C66C	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93C66CX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93C76	DIP 8	
MICROCHIP	93C76	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93C76A	DIP 8	
MICROCHIP	93C76A	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93C76B	DIP 8	
MICROCHIP	93C76B	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93C76C	DIP 8	
MICROCHIP	93C76C	TSSOP 8	PA8TSS-OT
MICROCHIP	93C76C	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93C76C-I/P	DIP 8	
MICROCHIP	93C76C-I/ST	TSSOP 8	PA8TSS8D
MICROCHIP	93C76C-I/SN	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93C76C-I/MS	MSOP 8	HA8MSOP48D
MICROCHIP	93C86	DIP 8	
MICROCHIP	93C86	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93C86A	DIP 8	
MICROCHIP	93C86A	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93C86B	DIP 8	
MICROCHIP	93C86B	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93C86C	DIP 8	
MICROCHIP	93C86C	TSSOP 8	PA8TSS-OT
MICROCHIP	93C86C	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93C86C-I/P	DIP 8	
MICROCHIP	93C86C-I/ST	TSSOP 8	PA8TSS8D
MICROCHIP	93C86C-I/SN	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93C86C-I/MS	MSOP 8	HA8MSOP48D
MICROCHIP	93LC46	DIP 8	
MICROCHIP	93LC46	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LC46X	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93LC46A	DIP 8	
MICROCHIP	93LC46A	TSSOP 8	PA8TSS-OT
MICROCHIP	93LC46A	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LC46AX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93LC46B	DIP 8	
MICROCHIP	93LC46B	TSSOP 8	PA8TSS-OT
MICROCHIP	93LC46B	SOIC 8	PA16SO16D-EO-150

MICROCHIP	93LC46BX	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LC46C	DIP 8	
MICROCHIP	93LC46C	TSSOP 8	PA8TSS-OT
MICROCHIP	93LC46C	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LC46C-I/P	DIP 8	
MICROCHIP	93LC46C-I/ST	TSSOP 8	PA8TSS8D
MICROCHIP	93LC46C-I/SN	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LC46C-I/MS	MSOP 8	HA8MSOP48D
MICROCHIP	93LC46CX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93LC56	DIP 8	
MICROCHIP	93LC56	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LC56X	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93LC56A	DIP 8	
MICROCHIP	93LC56A	TSSOP 8	PA8TSS-OT
MICROCHIP	93LC56A	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LC56A-I/P	DIP 8	
MICROCHIP	93LC56A-I/ST	TSSOP 8	PA8TSS8D
MICROCHIP	93LC56A-I/SN	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LC56A-I/MS	MSOP 8	HA8MSOP48D
MICROCHIP	93LC56AX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93LC56B	DIP 8	
MICROCHIP	93LC56B	TSSOP 8	PA8TSS-OT
MICROCHIP	93LC56B	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LC56B-I/P	DIP 8	
MICROCHIP	93LC56B-I/ST	TSSOP 8	PA8TSS8D
MICROCHIP	93LC56B-I/SN	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LC56B-I/MS	MSOP 8	HA8MSOP48D
MICROCHIP	93LC56BX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93LC56C	DIP 8	
MICROCHIP	93LC56C	TSSOP 8	PA8TSS-OT
MICROCHIP	93LC56C	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LC56CX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93LC66	DIP 8	
MICROCHIP	93LC66	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LC66X	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93LC66A	DIP 8	
MICROCHIP	93LC66A	TSSOP 8	PA8TSS-OT
MICROCHIP	93LC66A	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LC66AX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93LC66B	DIP 8	
MICROCHIP	93LC66B	TSSOP 8	PA8TSS-OT
MICROCHIP	93LC66B	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LC66BX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93LC66C	DIP 8	
MICROCHIP	93LC66C	TSSOP 8	PA8TSS-OT
MICROCHIP	93LC66C	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LC66CX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93LC76	DIP 8	
MICROCHIP	93LC76	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LC76X	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93LC76A	DIP 8	
MICROCHIP	93LC76A	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LC76AX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93LC76B	DIP 8	
MICROCHIP	93LC76B	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LC76C	DIP 8	
MICROCHIP	93LC76C	TSSOP 8	PA8TSS-OT
MICROCHIP	93LC76C	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LC86	DIP 8	
MICROCHIP	93LC86	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LC86X	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93LC86A	DIP 8	
MICROCHIP	93LC86A	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LC86AX	SOIC 8	PA8SO8D-EO-150
MICROCHIP	93LC86B	DIP 8	
MICROCHIP	93LC86B	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LC86C	DIP 8	
MICROCHIP	93LC86C	TSSOP 8	PA8TSS-OT
MICROCHIP	93LC86C	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LC86C-I/P	DIP 8	
MICROCHIP	93LC86C-I/ST	TSSOP 8	PA8TSS8D
MICROCHIP	93LC86C-I/SN	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LC86C-I/MS	MSOP 8	HA8MSOP48D

MICROCHIP	93LCS56	DIP 8	
MICROCHIP	93LCS56	SOIC 8	PA16SO16D-EO-150
MICROCHIP	93LCS66	DIP 8	
MICROCHIP	93LCS66	SOIC 8	PA16SO16D-EO-150
MICROCHIP	HCS200	DIP 8	
MICROCHIP	HCS200	SOIC 8	PA16SO16D-EO-150
MICROCHIP	HCS201	DIP 8	
MICROCHIP	HCS201	SOIC 8	PA16SO16D-EO-150
MICROCHIP	HCS300	DIP 8	
MICROCHIP	HCS300	SOIC 8	PA16SO16D-EO-150
MICROCHIP	HCS301	DIP 8	
MICROCHIP	HCS301	SOIC 8	PA16SO16D-EO-150
MICROCHIP	HCS320	DIP 8	
MICROCHIP	HCS320	SOIC 8	PA16SO16D-EO-150
MICROCHIP	HCS360	DIP 8	
MICROCHIP	HCS360	SOIC 8	PA16SO16D-EO-150
MICROCHIP	HCS361	DIP 8	
MICROCHIP	HCS361	SOIC 8	PA16SO16D-EO-150
MICROCHIP	HCS362	DIP 8	
MICROCHIP	HCS362	SOIC 8	PA16SO16D-EO-150
MICROCHIP	HCS362	TSSOP 8	PA8TSS-OT
MICROCHIP	HCS410	DIP 8	
MICROCHIP	HCS410	SOIC 8	PA16SO16D-EO-150
MICROCHIP	HCS410	TSSOP 8	PA8TSS-OT
MICROCHIP	HCS412	DIP 8	
MICROCHIP	HCS412	SOIC 8	PA16SO16D-EO-150
MICRON	29F2G08AAC	TSOP 48	PA48TS48D
MICRON	29F2G08AAC(+Spare)	TSOP 48	PA48TS48D
MICRON	29F4G08AA	TSOP 48	HA48TS48DET
MICRON	29F4G08AA(+Spare)	TSOP 48	HA48TS48DET
MICRON	29F8G08AA-size4G	TSOP 48	HA48TS48DET
MICRON	29F8G08AA(+Spare)-size4G	TSOP 48	HA48TS48DET
MICRON	M29F160FT	TSOP 48	PA48TS48D
MICRON	M29F160FB	TSOP 48	PA48TS48D
MITSUBISHI	M5L2732	DIP 24	
MITSUBISHI	M5L2764K	DIP 28	
MITSUBISHI	M5L27128K	DIP 28	
MITSUBISHI	M5L27256K	DIP 28	
MITSUBISHI	M5L27512K	DIP 28	
MITSUBISHI	M5M2764P	DIP 28	
MITSUBISHI	M5M27128P	DIP 28	
MITSUBISHI	M5M27256P	DIP 28	
MITSUBISHI	M5M27512P	DIP 28	
MITSUBISHI	M5M27C128K	DIP 28	
MITSUBISHI	M5M27C201K	DIP 32	
MITSUBISHI	M5M27C201K	PLCC 32	PA32PL32D
MITSUBISHI	M5M27C256AK	DIP 28	
MITSUBISHI	M5M27C256AK	SOIC 28	PA28SO28D-EO-300
MITSUBISHI	M5M27C256AK	TSOP 28	PA28TS28D-EO
MITSUBISHI	M5M27C256K	DIP 28	
MITSUBISHI	M5M27C256P	DIP 28	
MITSUBISHI	M5M27C401K	DIP 32	
MITSUBISHI	M5M27C401K	PLCC 32	PA32PL32D
MITSUBISHI	M5M27C401K	TSOP 32	PA32TS20/PA32TS32D-20
MITSUBISHI	M5M27C512AK	DIP 28	
MITSUBISHI	M5M27C512AP	DIP 28	
MITSUBISHI	M5M27C100K	DIP 32	
MITSUBISHI	M5M27C100P	DIP 32	
MITSUBISHI	M5M27C101K	DIP 32	
MITSUBISHI	M5M27C101P	DIP 32	
MITSUBISHI	M5M27C102K	DIP 40	
MITSUBISHI	M5M27C102K	PLCC 44	PA44-48U
MITSUBISHI	M5M27C102K	SOP 40	PA40SO40D-EO-450
MITSUBISHI	M5M27C102K	TSOP 40	PA40TS40D
MITSUBISHI	M5M27C102P	DIP 40	
MITSUBISHI	M5M27C102P	PLCC 44	PA44-48U
MITSUBISHI	M5M27C102P	SOP 40	PA40SO40D-EO-450
MITSUBISHI	M5M27C102P	TSOP 40	PA40TS40D
MITSUBISHI	M5M27C202K	DIP 40	
MITSUBISHI	M5M27C202K	PLCC 44	PA44-48U
MITSUBISHI	M5M27C202K	TSOP 40	PA40TS40D
MITSUBISHI	M5M27C202K	SOP 40	PA40SO40D-EO-450
MITSUBISHI	M5M27C402K	DIP 40	

mitsubishi	M5M28C64AP	DIP 28	
mitsubishi	M5M28C64P	DIP 28	
MOSEL VITELIC	V29C31004B	PLCC 32	PA32PL32D
MOSEL VITELIC	V29C31004B	TSOP 32	PA32TS20/PA32TS32D-20
MOSEL VITELIC	V29C31004T	PLCC 32	PA32PL32D
MOSEL VITELIC	V29C31004T	TSOP 32	PA32TS20/PA32TS32D-20
MOSEL VITELIC	V29C51000B	DIP 32	
MOSEL VITELIC	V29C51000B	PLCC 32	PA32PL32D
MOSEL VITELIC	V29C51000B	TSOP 32	PA32TS20/PA32TS32D-20
MOSEL VITELIC	V29C51000T	DIP 32	
MOSEL VITELIC	V29C51000T	PLCC 32	PA32PL32D
MOSEL VITELIC	V29C51000T	TSOP 32	PA32TS20/PA32TS32D-20
MOSEL VITELIC	V29C51001B	DIP 32	
MOSEL VITELIC	V29C51001B	PLCC 32	PA32PL32D
MOSEL VITELIC	V29C51001B	TSOP 32	PA32TS20/PA32TS32D-20
MOSEL VITELIC	V29C51001T	DIP 32	
MOSEL VITELIC	V29C51001T	PLCC 32	PA32PL32D
MOSEL VITELIC	V29C51001T	TSOP 32	PA32TS20/PA32TS32D-20
MOSEL VITELIC	V29C51002B	DIP 32	
MOSEL VITELIC	V29C51002B	PLCC 32	PA32PL32D
MOSEL VITELIC	V29C51002B	TSOP 32	PA32TS20/PA32TS32D-20
MOSEL VITELIC	V29C51002T	DIP 32	
MOSEL VITELIC	V29C51002T	PLCC 32	PA32PL32D
MOSEL VITELIC	V29C51002T	TSOP 32	PA32TS20/PA32TS32D-20
MOSEL VITELIC	V29C51004B	PLCC 32	PA32PL32D
MOSEL VITELIC	V29C51004B	TSOP 32	PA32TS20/PA32TS32D-20
MOSEL VITELIC	V29C51004T	PLCC 32	PA32PL32D
MOSEL VITELIC	V29C51004T	TSOP 32	PA32TS20/PA32TS32D-20
MOSTEK	ET2716	DIP 24	
MOSTEK	ETC2716	DIP 24	
MOSTEK	ETC2732	DIP 24	
MOSTEK	MK2716	DIP 24	
MOSTEK	MKM2716	DIP 24	
MOSTEK	MKB2716	DIP 24	
MOSTEK	MK2764	DIP 28	
MOTOROLA	MCM2716	DIP 24	
MOTOROLA	MCM2814	DIP 8	
MOTOROLA	MCM68764	DIP 24	
MOTOROLA	MCM68766	DIP 24	
NATIONAL	NM24C02	DIP 8	
NATIONAL	NM24C04	DIP 8	
NATIONAL	NM24C08	DIP 8	
NATIONAL	NM24C16	DIP 8	
NATIONAL	NM25C020	DIP 8	
NATIONAL	NM25C020	SOIC 8	PA16SO16D-EO-150
NATIONAL	NM25C020	TSSOP 8	PA8TSS8D
NATIONAL	NM25C020	TSSOP 8	PA24TSS24D
NATIONAL	NM25C04	DIP 8	
NATIONAL	NM25C04	SOIC 8	PA16SO16D-EO-150
NATIONAL	NM25C040	DIP 8	
NATIONAL	NM25C040	SOIC 8	PA16SO16D-EO-150
NATIONAL	NM25C040	TSSOP 8	PA8TSS8D
NATIONAL	NM25C040	TSSOP 8	PA24TSS24D
NATIONAL	NM25C160	DIP 8	
NATIONAL	NM25C160	SOIC 8	PA16SO16D-EO-150
NATIONAL	NM25C160	TSSOP 8	PA8TSS8D
NATIONAL	NM25C160	TSSOP 8	PA24TSS24D
NATIONAL	NM25C640	DIP 8	
NATIONAL	NM25C640	SOIC 8	PA16SO16D-EO-150
NATIONAL	NM25C640	TSSOP 8	PA8TSS8D
NATIONAL	NM25C640	TSSOP 8	PA24TSS24D
NATIONAL	MM2716	DIP 24	
NATIONAL	MM2716E	DIP 24	
NATIONAL	MM2716Q	DIP 24	
NATIONAL	NM27C010	DIP 32	
NATIONAL	NM27C010	PLCC 32	PA32PL32D
NATIONAL	NM27C010	TSOP 32	PA32TS20/PA32TS32D-20
NATIONAL	NM27LV010	DIP 32	
NATIONAL	NM27LV010	PLCC 32	PA32PL32D
NATIONAL	NM27LV010	TSOP 32	PA32TS20/PA32TS32D-20
NATIONAL	NM27LV010B	DIP 32	
NATIONAL	NM27LV010B	PLCC 32	PA32PL32D
NATIONAL	NM27LV010B	TSOP 32	PA32TS20/PA32TS32D-20

NATIONAL	NM27C020	DIP 32	
NATIONAL	NM27C020	PLCC 32	PA32PL32D
NATIONAL	NM27C020	TSOP 32	PA32TS20/PA32TS32D-20
NATIONAL	NM27C040	DIP 32	
NATIONAL	NM27C040	PLCC 32	PA32PL32D
NATIONAL	NM27C040Q	DIP 32	
NATIONAL	NM27C040Q	PLCC 32	PA32PL32D
NATIONAL	NM27P040	DIP 32	
NATIONAL	NM27P040	PLCC 32	PA32PL32D
NATIONAL	NM27C64	DIP 28	
NATIONAL	NM27C128	DIP 28	
NATIONAL	NM27C128	PLCC 32	PA32PL28D-YA
NATIONAL	NM27C256	DIP 28	
NATIONAL	NM27C256	PLCC 32	PA32PL28D-YA
NATIONAL	NM27LC256	DIP 28	
NATIONAL	NM27LC256	PLCC 32	PA32PL28D-YA
NATIONAL	NM27C512	DIP 28	
NATIONAL	NM27C512	PLCC 32	PA32PL28D-YA
NATIONAL	NM27LC512	DIP 28	
NATIONAL	NM27LC512	PLCC 32	PA32PL28D-YA
NATIONAL	NM27LV512	DIP 28	
NATIONAL	NM27LV512	PLCC 32	PA32PL28D-YA
NATIONAL	NM27P512	DIP 28	
NATIONAL	NM27P512	PLCC 32	PA32PL28D-YA
NATIONAL	NMC27C16	DIP 24	
NATIONAL	NMC27C16B	DIP 24	
NATIONAL	NMC27C16Q	DIP 24	
NATIONAL	NMC27C16BQ	DIP 24	
NATIONAL	NMC27C16H	DIP 24	
NATIONAL	NMC27C16HQ	DIP 24	
NATIONAL	NMC2732	DIP 24	
NATIONAL	NMC27C32	DIP 24	
NATIONAL	NMC27C32E	DIP 24	
NATIONAL	NMC27C32Q	DIP 24	
NATIONAL	NMC27C32B	DIP 24	
NATIONAL	NMC27C32H	DIP 24	
NATIONAL	NMC27C32EH	DIP 24	
NATIONAL	NMC27C64	DIP 28	
NATIONAL	NMC27C64N	DIP 28	
NATIONAL	NMC27C64B	DIP 28	
NATIONAL	NMC27C64BN	DIP 28	
NATIONAL	NMC27C64Q	DIP 28	
NATIONAL	NMC27C128B	DIP 28	
NATIONAL	NMC27C128BN	DIP 28	
NATIONAL	NMC27C128Q	DIP 28	
NATIONAL	NMC27C128BQ	DIP 28	
NATIONAL	NMC27C128C	DIP 28	
NATIONAL	NMC27C128CQ	DIP 28	
NATIONAL	NMC27CP128	DIP 28	
NATIONAL	NMC27C256	DIP 28	
NATIONAL	NMC27C256	PLCC 32	PA32PL28D-YA
NATIONAL	NMC27C256B	DIP 28	
NATIONAL	NMC27C256B	PLCC 32	PA32PL28D-YA
NATIONAL	NMC27C256BN	DIP 28	
NATIONAL	NMC27C256C	DIP 28	
NATIONAL	NMC27C256Q	DIP 28	
NATIONAL	NMC27C512	DIP 28	
NATIONAL	NMC27C512	PLCC 32	PA32PL28D-YA
NATIONAL	NMC27C512A	DIP 28	
NATIONAL	NMC27C512A	PLCC 32	PA32PL28D-YA
NATIONAL	NMC27C512AN	DIP 28	
NATIONAL	NMC27C512AN	PLCC 32	PA32PL28D-YA
NATIONAL	NMC27C010	DIP 32	
NATIONAL	NMC27C010	PLCC 32	PA32PL32D
NATIONAL	NMC27C020	DIP 32	
NATIONAL	NMC27C020	PLCC 32	PA32PL32D
NATIONAL	NMC27C020	TSOP 32	PA32TS20/PA32TS32D-20
NATIONAL	NM27C240Q	DIP 40	
NATIONAL	NM27C240Q	PLCC 44	PA44-48U
NATIONAL	NMC9306	DIP 8	
NATIONAL	NMC9307	DIP 8	
NATIONAL	NMC9313B	DIP 8	
NATIONAL	NMC9314B	DIP 8	

NATIONAL	NMC9346	DIP 8	
NATIONAL	NMC93C06	DIP 8	
NATIONAL	NMC93C06	TSSOP 8	PA8TSS-OT
NATIONAL	NMC93C06	SOIC 8	PA16SO16D-EO-150
NATIONAL	NMC93C13	DIP 8	
NATIONAL	NMC93C13	SOIC 8	PA16SO16D-EO-150
NATIONAL	NMC93C14	DIP 8	
NATIONAL	NMC93C14	SOIC 8	PA16SO16D-EO-150
NATIONAL	NMC93C46	DIP 8	
NATIONAL	NMC93C46	DIP 8	
NATIONAL	NMC93C46	TSSOP 8	PA8TSS-OT
NATIONAL	NMC93C46	SOIC 8	PA16SO16D-EO-150
NATIONAL	NMC93C56	DIP 8	
NATIONAL	NMC93C56	TSSOP 8	PA8TSS-OT
NATIONAL	NMC93C56	SOIC 8	PA16SO16D-EO-150
NATIONAL	NMC93C66	DIP 8	
NATIONAL	NMC93C66	TSSOP 8	PA8TSS-OT
NATIONAL	NMC93C66	SOIC 8	PA16SO16D-EO-150
NATIONAL	NMC93C86	DIP 8	
NATIONAL	NMC93C86	TSSOP 8	PA8TSS-OT
NATIONAL	NMC93C86	SOIC 8	PA16SO16D-EO-150
FAIRCHILD	NM93CS06	DIP 8	
NATIONAL	NMC93CS06	DIP 8	
NATIONAL	NMC93CS06	TSSOP 8	PA8TSS-OT
NATIONAL	NMC93CS06	SOIC 8	PA16SO16D-EO-150
NATIONAL	NMC93CS46	DIP 8	
NATIONAL	NMC93CS46	TSSOP 8	PA8TSS-OT
NATIONAL	NMC93CS46	SOIC 8	PA16SO16D-EO-150
NATIONAL	NMC93CS56	DIP 8	
NATIONAL	NMC93CS56	TSSOP 8	PA8TSS-OT
NATIONAL	NMC93CS56	SOIC 8	PA16SO16D-EO-150
NATIONAL	NMC93CS66	DIP 8	
NATIONAL	NMC93CS66	TSSOP 8	PA8TSS-OT
NATIONAL	NMC93CS66	SOIC 8	PA16SO16D-EO-150
NATIONAL	NMC27C1024	DIP 40	
NATIONAL	NMC27C1024	PLCC 44	PA44-48U
NATIONAL	NMC27C2048	DIP 40	
NATIONAL	NMC27C2048	PLCC 44	PA44-48U
NEC	uPD27128	DIP 28	
NEC	uPD2716	DIP 24	
NEC	uPD27256	DIP 28	
NEC	uPD2732	DIP 24	
NEC	uPD2732A	DIP 24	
NEC	uPD2764	DIP 28	
NEC	uPD27C1000	DIP 32	
NEC	uPD27C1000A	DIP 32	
NEC	uPD27C1001A	DIP 32	
NEC	uPD27C1001A	SOP 32	PA32SO32D-EO-450
NEC	uPD27C1001D	DIP 32	
NEC	uPD27C2001	DIP 32	
NEC	uPD27C2001	PLCC 32	PA32PL32D
NEC	uPD27C2001	SOP 32	PA32SO32D-EO-450
NEC	uPD27C256	DIP 28	
NEC	uPD27C256A	DIP 28	
NEC	uPD27C256A	SOIC 28	PA28SO28D-EO-300
NEC	uPD27C4001	DIP 32	
NEC	uPD27C512	DIP 28	
NEC	uPD27C512	PLCC 32	PA32PL28D-YA
NEC	uPD27C64	DIP 28	
NEC	uPD27C8001	DIP 32	
NEC	uPD27C8000	DIP 42	
NEC	uPD27C1024	DIP 40	
NEC	uPD27C1024	PLCC 44	PA44-48U
NEC	uPD27C1024A	DIP 40	
NEC	uPD27C1024A	PLCC 44	PA44-48U
NEC	uPD27C4096	DIP 40	
NEC	uPD27C4096	PLCC 44	PA44-48U
NEC	uPD28C64	DIP 28	
NEC	uPD28C64	SOIC 28	PA28SO28D-EO-300
NEC	uPD28C64C	DIP 28	
NEC	uPD28C64C	SOIC 28	PA28SO28D-EO-300
NEXFLASH	NX29F010	DIP 32	
NEXFLASH	NX29F010	PLCC 32	PA32PL32D



NEXFLASH	NX29F010	TSOP 32	PA32TS20/PA32TS32D-20
NEXFLASH	NX25P10VNIG	SOIC 8	PA16SO16D-EO-150
NEXFLASH	NX25P20VNIG	SOIC 8	PA16SO16D-EO-150
NEXFLASH	NX25P40VNIG	SOIC 8	PA16SO16D-EO-150
NEXFLASH	NX25P80VSIG	SOIC 8	PA20SO20D-EO-210
NEXFLASH	NX25P16VSIG	SOIC 8	PA20SO20D-EO-210
NEXFLASH	NX25P16VFIG	SOIC 16	PA28SO28D-EO-300
NEXFLASH	NX25P32VFIG	SOIC 16	PA28SO28D-EO-300
OKI	MR27V401D	DIP 32	
OKI	MR27V401D	TSOP 32	PA32TS20/PA32TS32D-20
OKI	MR27V401D	SOP 32	PA32SO32D-EO-450
OKI	MR27V402D	SOP 40	PA40SO40D-EO-450
OKI	MR27V402E	SOP 40	PA40SO40D-EO-450
OKI	MR27V452D	SOP 40	PA40SO40D-EO-450
OKI	MR27V452D	DIP 40	
OKI	MR27V452D	TSOP 44	PA44TS44D
OKI	MR27V402D	DIP 40	
OKI	MR27V402D	TSOP 44	PA44TS44D
OKI	MR27V402E	DIP 40	
OKI	MR27V402E	TSOP 44	PA44TS44D
OKI	MR27V801D	DIP 32	
OKI	MR27V801D	PLCC 32	PA32PL32D
OKI	MR27V801D	TSOP 32	PA32TS20/PA32TS32D-20
OKI	MR27V801D	SOP 32	PA32SO32D-EO-450
OKI	MR27V802D	DIP 42	
OKI	MR27V802D	SOP 44	PA44SO44D
OKI	MR27V802D	TSOP 44	PA44TS44D
OKI	MR27V802F	SOP 44	PA44SO44D
OKI	MR27V852D	DIP 42	
OKI	MR27V852D	SOP 44	PA44SO44D
OKI	MR27V852D	TSOP 44	PA44TS44D
OKI	MR27V1602D	DIP 42	
OKI	MR27V1602D	SOP 44	PA44SO44D
OKI	MR27V1602E	SOP 44	PA44SO44D
OKI	MR27V1602F	DIP 42	
OKI	MR27V1602F	SOP 44	PA44SO44D
OKI	MR27V1652D	DIP 42	
OKI	MR27V1652D	SOP 44	PA44SO44D
OKI	MR27V1652E	DIP 42	
OKI	MR27V1652E	SOP 44	PA44SO44D
OKI	MR27V3202D	SOP 44	PA44SO44D
OKI	MR27V3202D	TSOP 48	PA48TS48D
OKI	MR27V3202E	SOP 44	PA44SO44D
OKI	MR27V3202E	TSOP 44	PA44TS44D
OKI	MR27V3202F	TSOP 48	PA48TS48D
OKI	MR27V3202F	SOP 44	PA44SO44D
OKI	MR27V3252D	SOP 44	PA44SO44D
OKI	MR27V3252D	TSOP 48	PA48TS48D
OKI	MR27V6402D	SOP 44	PA44SO44D
OKI	MR27V6402G	SOP 44	PA44SO44D
OKI	MR27V6466F	TSOP 86	PA6466R
OKI	MSM2716	DIP 24	
OKI	MSM2716AS	DIP 24	
OKI	MSM2732	DIP 24	
OKI	MSM2732A	DIP 24	
OKI	MSM2764	DIP 28	
OKI	MSM2764A	DIP 28	
OKI	MSM2764AZB	DIP 28	
OKI	MSM2764AS	DIP 28	
OKI	MSM2764RS	DIP 28	
OKI	MSM27128A	DIP 28	
OKI	MSM27128AS	DIP 28	
OKI	MSM27128AZB-RS	DIP 28	
OKI	MSM27256	DIP 28	
OKI	MSM27256AS	DIP 28	
OKI	MSM27256ZB-RS	DIP 28	
OKI	MSM27512	DIP 28	
OKI	MSM27512ZB-RS	DIP 28	
OKI	MSM27512AS	DIP 28	
OKI	MSM271000	DIP 32	
OKI	MSM271000AS	DIP 32	
OKI	MSM271000ZB	DIP 32	
OKI	MSM27C128AS	DIP 28	

OKI	MSM27C64AS	DIP 28	
OKI	MSM27C256	DIP 28	
OKI	MSM27C256	PLCC 32	PA32PL28D-YA
OKI	MSM27C256H	DIP 28	
OKI	MSM27C256H	PLCC 32	PA32PL28D-YA
OKI	MSM27C256HQB	DIP 28	
OKI	MSM27C256HQB	PLCC 32	PA32PL28D-YA
OKI	MSM27C256ZB	DIP 28	
OKI	MSM27C256ZB	PLCC 32	PA32PL28D-YA
OKI	MSM27C101ZB	DIP 32	
OKI	MSM27C101ZB	PLCC 32	PA32PL32D
OKI	MSM27C101ZB	TSOP 32	PA32TS20/PA32TS32D-20
OKI	MSM27C2000	DIP 32	
OKI	MSM27C401CZ	DIP 32	
OKI	MSM27C401CZ	TSOP 32	PA32TS20/PA32TS32D-20
OKI	MSM27C401CZ	SOP 32	PA32SO32D-EO-450
OKI	MSM27C402ZB	SOP 44	PA44SO44D
OKI	MSM27C452CZ	DIP 40	
OKI	MSM27C452CZ	TSOP 44	PA44TS44D
OKI	MSM27C802CZ	DIP 42	
OKI	MSM27C802CZ	SOP 44	PA44SO44D
OKI	MSM27C802CZ	TSOP 44	PA44TS44D
OKI	MSM27C852CZ	DIP 42	
OKI	MSM27C852CZ	SOP 44	PA44SO44D
OKI	MSM27C852CZ	TSOP 44	PA44TS44D
OKI	MSM2816ARS	DIP 24	
OKI	MSM271024	DIP 40	
OKI	MSM271024	PLCC 44	PA44-48U
OKI	MSM271024AS	DIP 40	
OKI	MSM271024AS	PLCC 44	PA44-48U
OKI	MSM271024ZB	DIP 40	
OKI	MSM271024ZB	PLCC 44	PA44-48U
OKI	MSM27C1024	DIP 40	
OKI	MSM27C1024	PLCC 44	PA44-48U
OKI	MSM27C1024AS	DIP 40	
OKI	MSM27C1024AS	PLCC 44	PA44-48U
OKI	MSM27C2048	DIP 40	
OKI	MSM27C2048	PLCC 44	PA44-48U
OKI	MSM27C1602CZ	DIP 42	
OKI	MSM27C1602CZ	SOP 44	PA44SO44D
OKI	MSM27C1652CZ	DIP 42	
OKI	MSM27C1652CZ	SOP 44	PA44SO44D
OKI	MSM27C3202CZ	SOP 44	PA44SO44D
OKI	MSM27C3252CZ	SOP 44	PA44SO44D
PHILIPS	PCF8582C	DIP 8	
PHILIPS	PCF8582D	DIP 8	
PHILIPS	PCF8582E	DIP 8	
PHILIPS	PCF8592C	DIP 8	
PHILIPS	PCF8594C	DIP 8	
PHILIPS	PCF8598C	DIP 8	
PHILIPS	PCF8582C	SOIC 8	PA16SO16D-EO-150
PHILIPS	PCF8582D	SOIC 8	PA16SO16D-EO-150
PHILIPS	PCF8582E	SOIC 8	PA16SO16D-EO-150
PHILIPS	PCF8592C	SOIC 8	PA16SO16D-EO-150
PHILIPS	PCF8594C	SOIC 8	PA16SO16D-EO-150
PHILIPS	PCF8598C	SOIC 8	PA16SO16D-EO-150
PHILIPS	27C64A	DIP 28	
PHILIPS	27C64A	PLCC 32	PA32PL28D-YA
PHILIPS	27C256	DIP 28	
PHILIPS	27C256	PLCC 32	PA32PL28D-YA
PHILIPS	27C512	DIP 28	
PHILIPS	27C512	PLCC 32	PA32PL28D-YA
PHILIPS	27C010	DIP 32	
PHILIPS	27C010	PLCC 32	PA32PL32D
PHILIPS	27C010	TSOP 32	PA32TS20/PA32TS32D-20
PHILIPS	27C040	DIP 32	
PHILIPS	27C210	DIP 40	
PHILIPS	27C210	PLCC 44	PA44-48U
PHILIPS	27C240	DIP 40	
PHILIPS	27C240	PLCC 44	PA44-48U
SIGNETICS(PHILIPS)	27C256	DIP 28	
SIGNETICS(PHILIPS)	27C256	PLCC 32	PA32PL28D-YA
SIGNETICS(PHILIPS)	27C010	DIP 32	

SIGNETICS(PHILIPS)	27C010		PLCC 32	PA32PL32D
SIGNETICS(PHILIPS)	27C010		TSOP 32	PA32TS20/PA32TS32D-20
PMC	PM25LD040-P		DIP 8	
PMC	PM25LD040-S		SOIC 8	PA16SO16D-EO-150
PMC	PM25LD040-B		SOIC 8	PA20SO20D-EO-210
PMC	PM25LD040-K		WSON 8	PA8SON8D
PMC	PM25LV010		SOIC 8	PA16SO16D-EO-150
PMC	PM25LV512		SOIC 8	PA16SO16D-EO-150
PMC	Pm29F002B		DIP 32	
PMC	Pm29F002B		PLCC 32	PA32PL32D
PMC	Pm29F002T		DIP 32	
PMC	Pm29F002T		PLCC 32	PA32PL32D
PMC	Pm29F004B		DIP 32	
PMC	Pm29F004B		PLCC 32	PA32PL32D
PMC	Pm29F004B		TSOP 32	PA32TS20/PA32TS32D-20
PMC	Pm29F004T		DIP 32	
PMC	Pm29F004T		PLCC 32	PA32PL32D
PMC	Pm29F004T		TSOP 32	PA32TS20/PA32TS32D-20
PMC	Pm29LV002B		DIP 32	
PMC	Pm29LV002T		DIP 32	
PMC	Pm29LV104RB		PLCC 32	PA32PL32D
PMC	Pm29LV104RB		TSOP 32	PA32TS20/PA32TS32D-20
PMC	Pm29LV104RT		PLCC 32	PA32PL32D
PMC	Pm29LV104RT		TSOP 32	PA32TS20/PA32TS32D-20
PMC	Pm39F010-xxJC		PLCC 32	PA32PL32D
PMC	Pm39F020-xxJC		PLCC 32	PA32PL32D
PMC	Pm39F040-xxJC		PLCC 32	PA32PL32D
PMC	Pm39LV512-xxVC		sTSOP 32	PA32TS32D
PMC	Pm39LV512-xxJC		PLCC 32	PA32PL32D
PMC	Pm39LV512R		DIP 32	PA32PL32D
PMC	Pm39LV010-xxVC		sTSOP 32	PA32TS32D
PMC	Pm39LV010-xxJC		PLCC 32	PA32PL32D
PMC	Pm39LV020-xxJC		PLCC 32	PA32PL32D
PMC	Pm39LV040-xxJC		PLCC 32	PA32PL32D
PMC	Pm49FL002T-xxJC		PLCC 32	PA32PL32D
PMC	Pm49FL004T-xxJC		PLCC 32	PA32PL32D
PMC	Pm49FL008T-xxJC		PLCC 32	PA32PL32D
PMC	Pm49FL002T-xxJV		sTSOP 32	PA32TS32D
PMC	Pm49FL004T-xxJV		sTSOP 32	PA32TS32D
PMC	Pm49FL008T-xxJV		sTSOP 32	PA32TS32D
QUICK PULSE ALGORITHM	2764A		DIP 28	
QUICK PULSE ALGORITHM	27128A		DIP 28	
QUICK PULSE ALGORITHM		27256	DIP 28	
QUICK PULSE ALGORITHM		27512	DIP 28	
QUICK PULSE ALGORITHM		27010	DIP 32	
QUICK PULSE ALGORITHM		27040	DIP 32	
QUICK PULSE ALGORITHM		27210	DIP 40	
QUICK PULSE ALGORITHM		27210	PLCC 44	PA44-48U
RAMTRON	FM18L08-P		DIP 28	
RAMTRON	FM18L08-PG		DIP 28	
RAMTRON	FM18L08-S		SOIC 28	PA28SO28D-EO-300
RAMTRON	FM18L08-SG		SOIC 28	PA28SO28D-EO-300
ROCKWELL	R2764		DIP 28	
ROCKWELL	R2764C		DIP 28	
ROCKWELL	R2764P		DIP 28	
ROCKWELL	R27C64		DIP 28	
RICOH	27C64		DIP 28	
RICOH	27C64		PLCC 32	PA32PL28D-YA
RICOH	RD27C64		DIP 28	
RICOH	RD27C256		DIP 28	
RICOH	RD27C256		PLCC 32	PA32PL28D-YA
ROCKWELL	R2816		DIP 24	
ROHM	BR24C01A		DIP 8	
ROHM	BR24C01-MN		SOIC 8	PA8SO8D-EO-150
ROHM	BR24C01-DW		TSSOP 8	PA8TSS8D
ROHM	BR24C01-DW		TSSOP 8	PA24TSS24D
ROHM	BR24C01-DS		TSSOP 8	PA8TSS8D
ROHM	BR24C01-DS		TSSOP 8	PA24TSS24D
ROHM	BR24C01A-W		DIP 8	
ROHM	BR24C01AF-W		SOIC 8	PA8SO8D-EO-150
ROHM	BR24C01AFJ-W		SOIC 8	PA8SO8D-EO-150
ROHM	BR24C01AFV-W		SSOP 8	PA8SS8D
ROHM	BR24C01AF		SOIC 8	PA8SO8D-EO-150

ROHM	BR24C01AFJ	SOIC 8	PA8SO8D-EO-150
ROHM	BR24C01AFV	SSOP 8	PA8SS8D
ROHM	BR24C21-W	DIP 8	
ROHM	BR24C21F-W	SOIC 8	PA8SO8D-EO-150
ROHM	BR24C21FJ-W	SOIC 8	PA8SO8D-EO-150
ROHM	BR24C21FV-W	SSOP 8	PA8SS8D
ROHM	BR24C02	DIP 8	
ROHM	BR24C02-MN	SOIC 8	PA8SO8D-EO-150
ROHM	BR24C02-DW	TSSOP 8	PA8TSS8D
ROHM	BR24C02-DW	TSSOP 8	PA24TSS24D
ROHM	BR24C02-DS	TSSOP 8	PA8TSS8D
ROHM	BR24C02-DS	TSSOP 8	PA24TSS24D
ROHM	BR24C02A-W	DIP 8	
ROHM	BR24C02AF-W	SOIC 8	PA8SO8D-EO-150
ROHM	BR24C02AFJ-W	SOIC 8	PA8SO8D-EO-150
ROHM	BR24C02AFV-W	SSOP 8	PA8SS8D
ROHM	BR24C02AF	SOIC 8	PA8SO8D-EO-150
ROHM	BR24C02AFJ	SOIC 8	PA8SO8D-EO-150
ROHM	BR24C02AFV	SSOP 8	PA8SS8D
ROHM	BR24C04	DIP 8	
ROHM	BR24C04-MN	SOIC 8	PA8SO8D-EO-150
ROHM	BR24C04-DW	TSSOP 8	PA8TSS8D
ROHM	BR24C04-DW	TSSOP 8	PA24TSS24D
ROHM	BR24C04-DS	TSSOP 8	PA8TSS8D
ROHM	BR24C04-DS	TSSOP 8	PA24TSS24D
ROHM	BR24C04A-W	DIP 8	
ROHM	BR24C04AF-W	SOIC 8	PA8SO8D-EO-150
ROHM	BR24C04AFJ-W	SOIC 8	PA8SO8D-EO-150
ROHM	BR24C04AFV-W	SSOP 8	PA8SS8D
ROHM	BR24C04AF	SOIC 8	PA8SO8D-EO-150
ROHM	BR24C04AFJ	SOIC 8	PA8SO8D-EO-150
ROHM	BR24C04AFV	SSOP 8	PA8SS8D
ROHM	BR24C08	DIP 8	
ROHM	BR24C08-MN	SOIC 8	PA8SO8D-EO-150
ROHM	BR24C08-DW	TSSOP 8	PA8TSS8D
ROHM	BR24C08-DW	TSSOP 8	PA24TSS24D
ROHM	BR24C08-DS	TSSOP 8	PA8TSS8D
ROHM	BR24C08-DS	TSSOP 8	PA24TSS24D
ROHM	BR24C08F	SOIC 8	PA8SO8D-EO-150
ROHM	BR24C08FJ	SOIC 8	PA8SO8D-EO-150
ROHM	BR24C08FV	SSOP 8	PA8SS8D
ROHM	BR24C16	DIP 8	
ROHM	BR24C16-MN	SOIC 8	PA8SO8D-EO-150
ROHM	BR24C16-DW	TSSOP 8	PA8TSS8D
ROHM	BR24C16-DW	TSSOP 8	PA24TSS24D
ROHM	BR24C16-DS	TSSOP 8	PA8TSS8D
ROHM	BR24C16-DS	TSSOP 8	PA24TSS24D
ROHM	BR24C16F	SOIC 8	PA8SO8D-EO-150
ROHM	BR24C16FJ	SOIC 8	PA8SO8D-EO-150
ROHM	BR24C16FV	SSOP 8	PA8SS8D
ROHM	BR24E16	DIP 8	
ROHM	BR24E16F	SOIC 8	PA8SO8D-EO-150
ROHM	BR24E16FJ	SOIC 8	PA8SO8D-EO-150
ROHM	BR24E16FV	SSOP 8	PA8SS8D
ROHM	BR24C32-MN	SOIC 8	PA8SO8D-EO-150
ROHM	BR24C32-DW	TSSOP 8	PA8TSS8D
ROHM	BR24C32-DW	TSSOP 8	PA24TSS24D
ROHM	BR24C64-MN	SOIC 8	PA8SO8D-EO-150
ROHM	BR24L01A-W	DIP 8	
ROHM	BR24L01AF-W	SOIC 8	PA8SO8D-EO-150
ROHM	BR24L01AFJ-W	SOIC 8	PA8SO8D-EO-150
ROHM	BR24L01AFV-W	SSOP 8	PA8SS8D
ROHM	BR24L01AFVM-W	MSOP 8	PA8MSOP8D
ROHM	BR24L02-W	DIP 8	
ROHM	BR24L02F-W	SOIC 8	PA8SO8D-EO-150
ROHM	BR24L02FJ-W	SOIC 8	PA8SO8D-EO-150
ROHM	BR24L02FV-W	SSOP 8	PA8SS8D
ROHM	BR24L02FVM-W	MSOP 8	PA8MSOP8D
ROHM	BR24L04-W	DIP 8	
ROHM	BR24L04F-W	SOIC 8	PA8SO8D-EO-150
ROHM	BR24L04FJ-W	SOIC 8	PA8SO8D-EO-150
ROHM	BR24L04FV-W	SSOP 8	PA8SS8D
ROHM	BR24L04FVM-W	MSOP 8	PA8MSOP8D

ROHM	BR24L08-W	DIP 8	
ROHM	BR24L08F-W	SOIC 8	PA8SO8D-EO-150
ROHM	BR24L08FJ-W	SOIC 8	PA8SO8D-EO-150
ROHM	BR24L08FV-W	SSOP 8	PA8SS8D
ROHM	BR24L08FVM-W	MSOP 8	PA8MSOP8D
ROHM	BR24L16-W	DIP 8	
ROHM	BR24L16F-W	SOIC 8	PA8SO8D-EO-150
ROHM	BR24L16FJ-W	SOIC 8	PA8SO8D-EO-150
ROHM	BR24L16FV-W	SSOP 8	PA8SS8D
ROHM	BR24L16FVM-W	MSOP 8	PA8MSOP8D
ROHM	BR24L32-W	DIP 8	
ROHM	BR24L32F-W	SOIC 8	PA8SO8D-EO-150
ROHM	BR24L32FJ-W	SOIC 8	PA8SO8D-EO-150
ROHM	BR24L32FV-W	SSOP 8	PA8SS8D
ROHM	BR24L64-W	DIP 8	
ROHM	BR24L64F-W	SOIC 8	PA8SO8D-EO-150
ROHM	BR24L64FJ-W	SOIC 8	PA8SO8D-EO-150
ROHM	BR93LC46	DIP 8	
ROHM	BR93LC46F	SOIC 8	PA16SO16D-EO-150
ROHM	BR93LC46RF	SOP 8	PA8SO8D-EO-150
ROHM	BR93LC46FJ	SOP 8	PA16SO16D-EO-150
ROHM	BR93LC46RFJ	SOP 8	PA8SO8D-EO-150
ROHM	BR93LC46FV	SOP 8	PA8TSS8D
ROHM	BR93LC46FV	SOP 8	PA24TSS24D
ROHM	BR93LC56	DIP 8	
ROHM	BR93LC56F	SOIC 8	PA16SO16D-EO-150
ROHM	BR93LC66	DIP 8	
ROHM	BR93LC66F	SOIC 8	PA16SO16D-EO-150
ROHM	BR93LL46	DIP 8	
ROHM	BR93LL46F	SOIC 8	PA16SO16D-EO-150
ROHM	BR9010	DIP 8	
ROHM	BR9010F	DIP 8	
ROHM	BR9010F	SOIC 8	PA16SO16D-EO-150
ROHM	BR9010F	SSOP 8	PA8TSS-OT
ROHM	BR9020	DIP 8	
ROHM	BR9020	SOIC 8	PA16SO16D-EO-150
ROHM	BR9020	SSOP 8	PA8TSS-OT
ROHM	BR9020F	DIP 8	
ROHM	BR9020F	SOIC 8	PA16SO16D-EO-150
ROHM	BR9020F	SSOP 8	PA8TSS-OT
ROHM	BR9040	DIP 8	
ROHM	BR9040F	DIP 8	
ROHM	BR9040F	SOIC 8	PA16SO16D-EO-150
ROHM	BR9040F	SSOP 8	PA8TSS-OT
ROHM	BR9080	DIP 8	
ROHM	BR9080F	DIP 8	
ROHM	BR9080F	SOIC 8	PA16SO16D-EO-150
ROHM	BR9080F	SSOP 8	PA8TSS-OT
ROHM	BR9016	DIP 8	
ROHM	BR9016F	DIP 8	
ROHM	BR9016F	SOIC 8	PA16SO16D-EO-150
ROHM	BR9016F	SSOP 8	PA8TSS-OT
RUSSIAN	573RF2/5	DIP 24	
RUSSIAN	57RF4-21	DIP 28	
RUSSIAN	573RF4-21.5	DIP 28	
RUSSIAN	573RF4-23	DIP 28	
SAMSUNG	KS24L161	DIP 8	
SAMSUNG	KS24L321	DIP 8	
SAMSUNG	KS24L641	DIP 8	
SAMSUNG	KS24C010	DIP 8	
SAMSUNG	KS24C011	DIP 8	
SAMSUNG	KS24C020	DIP 8	
SAMSUNG	KS24C021	DIP 8	
SAMSUNG	KS24C040	DIP 8	
SAMSUNG	KS24C041	DIP 8	
SAMSUNG	KS24C080	DIP 8	
SAMSUNG	KS24C081	DIP 8	
SAMSUNG	KM2816A	DIP 24	
SAMSUNG	KM2816AI	DIP 24	
SAMSUNG	KM2817A	DIP 28	
SAMSUNG	KM2817AI	DIP 28	
SAMSUNG	KM2864A	DIP 28	
SAMSUNG	KM2864AH	DIP 28	

SAMSUNG	KM2865A	DIP 28	
SAMSUNG	KM2865AH	DIP 28	
SAMSUNG	KM28C16	DIP 24	
SAMSUNG	KM28C17	DIP 28	
SAMSUNG	KM28C17	PLCC 32	PA32PL28D-YA
SAMSUNG	KM28C64	DIP 28	
SAMSUNG	KM28C64	PLCC 32	PA32PL28D-YA
SAMSUNG	KM28C64A	DIP 28	
SAMSUNG	KM28C64A	PLCC 32	PA32PL28D-YA
SAMSUNG	KM28C65	DIP 28	
SAMSUNG	KM28C65	PLCC 32	PA32PL28D-YA
SAMSUNG	KM28C65A	DIP 28	
SAMSUNG	KM28C65A	PLCC 32	PA32PL28D-YA
SAMSUNG	KM28C256	DIP 28	
SAMSUNG	KM28C256	PLCC 32	PA32PL28D-YA
SAMSUNG	KM28C256A	DIP 28	
SAMSUNG	KM28C256A	PLCC 32	PA32PL28D-YA
SAMSUNG	KM28U800T-B	TSOP 48	PA48TS48D
SAMSUNG	KM28U800T-T	TSOP 48	PA48TS48D
SAMSUNG	KM28U160T-B	TSOP 48	PA48TS48D
SAMSUNG	KM28U160T-T	TSOP 48	PA48TS48D
SAMSUNG	K5L2963CAM	BGA 64	HA64BG48DF
SAMSUNG	K5J6332CBM	BGA 69	PA69BGA48DJ-YO-8X11.6
SAMSUNG	K5J6332CTM	BGA 69	PA69BGA48DJ-YO-8X11.6
SAMSUNG	K8D1616UBM-Y	TSOP 48	PA48TS48D
SAMSUNG	K8D1616UTM-Y	TSOP 48	PA48TS48D
SAMSUNG	K8D1616UBM-T	BGA 48	PA48BGA48DA
SAMSUNG	K8D1616UTM-T	BGA 48	PA48BGA48DA
SAMSUNG	K8D1616UBA-Y	TSOP 48	PA48TS48D
SAMSUNG	K8D1616UTA-Y	TSOP 48	PA48TS48D
SAMSUNG	K8D1616UBA-T	BGA 48	PA48BGA48DA
SAMSUNG	K8D1616UTA-T	BGA 48	PA48BGA48DA
SAMSUNG	K8D1716UBA-Y	TSOP 48	PA48TS48D
SAMSUNG	K8D1716UTA-Y	TSOP 48	PA48TS48D
SAMSUNG	K8D1716UBA-T	BGA 48	PA48BGA48DA
SAMSUNG	K8D1716UTA-T	BGA 48	PA48BGA48DA
SAMSUNG	K8D1716UBC-Y	TSOP 48	PA48TS48D
SAMSUNG	K8D1716UTC-Y	TSOP 48	PA48TS48D
SAMSUNG	K8D3216UBM-Y	TSOP 48	PA48TS48D
SAMSUNG	K8D3216UTM-Y	TSOP 48	PA48TS48D
SAMSUNG	K8D3216UBA-Y	TSOP 48	PA48TS48D
SAMSUNG	K8D3216UTA-Y	TSOP 48	PA48TS48D
SAMSUNG	K8D3216UBB-Y	TSOP 48	PA48TS48D
SAMSUNG	K8D3216UTB-Y	TSOP 48	PA48TS48D
SAMSUNG	K8D3216UBA-T	BGA 48	PA48BGA48DA
SAMSUNG	K8D3216UBB-T	BGA 48	PA48BGA48DA
SAMSUNG	K8D3216UBM-T	BGA 48	PA48BGA48DA
SAMSUNG	K8D3216UTM-T	BGA 48	PA48BGA48DA
SAMSUNG	K8D3216UTA-T	BGA 48	PA48BGA48DA
SAMSUNG	K8D3216UTB-T	BGA 48	PA48BGA48DA
SAMSUNG	K8D3216UBC-Y	TSOP 48	PA48TS48D
SAMSUNG	K8D3216UTC-Y	TSOP 48	PA48TS48D
SAMSUNG	K8D3216UBC-T	BGA 48	PA48BG48DAD
SAMSUNG	K8D3216UTC-T	BGA 48	PA48BG48DAD
SAMSUNG	K8D3316UBA-Y	TSOP 48	PA48TS48D
SAMSUNG	K8D3316UBM-Y	TSOP 48	PA48TS48D
SAMSUNG	K8D3316UTA-Y	TSOP 48	PA48TS48D
SAMSUNG	K8D3316UTM-Y	TSOP 48	PA48TS48D
SAMSUNG	K8D3316UBA-T	BGA 48	PA48BGA48DA
SAMSUNG	K8D3316UBC-T	BGA 48	PA48BG48DAD
SAMSUNG	K8D3316UBM-T	BGA 48	PA48BGA48DA
SAMSUNG	K8D3316UTA-T	BGA 48	PA48BGA48DA
SAMSUNG	K8D3316UTC-T	BGA 48	PA48BG48DAD
SAMSUNG	K8D3316UTM-T	BGA 48	PA48BGA48DA
SAMSUNG	K8D6316UBM-Y	TSOP 48	PA48TS48D
SAMSUNG	K8D6316UTM-Y	TSOP 48	PA48TS48D
SAMSUNG	K8D6316UBM-T	BGA 48	PA48BGA48DL
SAMSUNG	K8D6316UTM-T	BGA 48	PA48BGA48DL
SAMSUNG	K8D6316UBM-P	TSOP 48	PA48TS48D
SAMSUNG	K8D6316UTM-P	TSOP 48	PA48TS48D
SAMSUNG	K8P1615UQB	TSOP 48	PA48TS48D
SAMSUNG	K8P3215UQB	TSOP 48	PA48TS48D
SAMSUNG	K8P3215UQB	BGA 48	HA48BG48DAI

SAMSUNG	K8P6415UQB	TSOP 48	PA48TS48D
SAMSUNG	K8P6415UQB	BGA 48	HA48BG48DAI
SAMSUNG	K8Q2815UQB	TSOP 56	PA56TS48DB
SAMSUNG	K8P5615UQA	TSOP 56	PA56TS48DC
SAMSUNG	K8P2815UQB	BGA 80	HA80BG48DF
SAMSUNG	KM29C010	DIP 32	
SAMSUNG	KM29C010	PLCC 32	PA32PL32D
SAMSUNG	KM29C010	TSOP 32	PA32TS20/PA32TS32D-20
SAMSUNG	KM29W32000	TSOP 44	PA44TS44D
SAMSUNG	K9F2808U0M	TSOP 48	PA48TS48D
SAMSUNG	K9F2808U0M(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F2808U0A	TSOP 48	PA48TS48D
SAMSUNG	K9F2808U0A(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F2808U0B	TSOP 48	PA48TS48D
SAMSUNG	K9F2808U0B(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F2808U0C	TSOP 48	PA48TS48D
SAMSUNG	K9F2808U0C(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F5608U0M	TSOP 48	PA48TS48D
SAMSUNG	K9F5608U0M(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F5608U0A	TSOP 48	PA48TS48D
SAMSUNG	K9F5608U0A(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F5608U0B	TSOP 48	PA48TS48D
SAMSUNG	K9F5608U0B(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F5608U0C	TSOP 48	PA48TS48D
SAMSUNG	K9F5608U0C(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F5608U0D	TSOP 48	PA48TS48D
SAMSUNG	K9F5608U0D(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F5608U0D	BGA 63	HA63BG48DO
SAMSUNG	K9F5608U0D(+Spare)	BGA 63	HA63BG48DO
SAMSUNG	K9F5616U0M	TSOP 48	PA48TS48D
SAMSUNG	K9F5616U0M(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F5616U0B	TSOP 48	PA48TS48D
SAMSUNG	K9F5616U0B(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F5616U0C	TSOP 48	PA48TS48D
SAMSUNG	K9F5616U0C(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F1208U0M	TSOP 48	PA48TS48D
SAMSUNG	K9F1208U0M(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F1208U0A	TSOP 48	PA48TS48D
SAMSUNG	K9F1208U0A(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F1208U0B	TSOP 48	PA48TS48D
SAMSUNG	K9F1208U0B(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F1208U0C	TSOP 48	PA48TS48D
SAMSUNG	K9F1208U0C(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F1216U0A	TSOP 48	PA48TS48D
SAMSUNG	K9F1216U0A(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F1216U0A	BGA 63	PA63BGA48DD
SAMSUNG	K9F1216U0A(+Spare)	BGA 63	PA63BGA48DD
SAMSUNG	K9F1G08U0M	TSOP 48	PA48TS48D
SAMSUNG	K9F1G08U0M(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F1G08U0A	TSOP 48	PA48TS48D
SAMSUNG	K9F1G08U0A(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F1G08U0B	TSOP 48	PA48TS48D
SAMSUNG	K9F1G08U0B(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F1G08U0C	TSOP 48	PA48TS48D
SAMSUNG	K9F1G08U0C(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F1G08U0D	TSOP 48	PA48TS48D
SAMSUNG	K9F1G08U0D(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F2G08U0M	TSOP 48	PA48TS48D
SAMSUNG	K9F2G08U0M(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F2G08U0A	TSOP 48	PA48TS48D
SAMSUNG	K9F2G08U0A(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F2G08U0B	TSOP 48	PA48TS48D
SAMSUNG	K9F2G08U0B(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F4G08U0M	TSOP 48	PA48TS48D
SAMSUNG	K9F4G08U0M(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F4G08U0A	TSOP 48	PA48TS48D
SAMSUNG	K9F4G08U0A(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9F4G08U0B	TSOP 48	PA48TS48D
SAMSUNG	K9F4G08U0B(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9K8G08U0A	TSOP 48	PA48TS48D
SAMSUNG	K9K8G08U0A(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9K1208U0A	TSOP 48	PA48TS48D
SAMSUNG	K9K1208U0A(+Spare)	TSOP 48	PA48TS48D

SAMSUNG	K9K1216D0C	BGA 63	PA63BGA48DD
SAMSUNG	K9K1216D0C(+Spare)	BGA 63	PA63BGA48DD
SAMSUNG	K9K1G08U0M	TSOP 48	PA48TS48D
SAMSUNG	K9K1G08U0M(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9K1G08U0B	BGA 63	HA63BG48DH
SAMSUNG	K9K1G08U0B(+Spare)	BGA 63	HA63BG48DH
SAMSUNG	K9K4G08U0M	TSOP 48	PA48TS48D
SAMSUNG	K9K4G08U0M(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	K9K8G08U0M	TSOP 48	PA48TS48D
SAMSUNG	K9K8G08U0M(+Spare)	TSOP 48	PA48TS48D
SAMSUNG	KBE00F003M	BGA 107	HA107BG48DG
SAMSUNG	KBE00F003M(+Spare)	BGA 107	HA107BG48DG
SAMSUNG	KBE00F003A	BGA 107	HA107BGA48DH
SAMSUNG	KBE00F003A(+Spare)	BGA 107	HA107BGA48DH
SAMSUNG	KBE00F005M	BGA 137	HA137BG48DB
SAMSUNG	KBE00F005M(+Spare)	BGA 137	HA137BG48DB
SAMSUNG	KBE00F005A	BGA 137	HA137BG48DC
SAMSUNG	KBE00F005A(+Spare)	BGA 137	HA137BG48DC
SAMSUNG	KBE00M005M	BGA 137	HA137BG48DC
SAMSUNG	KBE00M005M(+Spare)	BGA 137	HA137BG48DC
SAMSUNG	KBE00S003M	BGA 107	HA107BG48DG
SAMSUNG	KBE00S003M(+Spare)	BGA 107	HA107BG48DG
SAMSUNG	KBE00S005M	BGA 137	HA137BGA48DE
SAMSUNG	KBE00S005M(+Spare)	BGA 137	HA137BGA48DE
SAMSUNG	KBE00S009M	BGA 137	HA137BGA48DE
SAMSUNG	KBE00S009M(+Spare)	BGA 137	HA137BGA48DE
SAMSUNG	K5F3264YBM(NOR)	BGA 69	PA69BGA48DB
SAMSUNG	K5F3264YTM(NOR)	BGA 69	PA69BGA48DB
SAMSUNG	KAB01D100M	BGA 80	PA80BGA48DB
SAMSUNG	KAB01D100M-A	BGA 80	PA80BGA48DB-A
SAMSUNG	KBB05A300M	BGA 80	PA80BGA48DC
SAMSUNG	KBB05A500M	BGA 80	PA80BGA48DD
SAMSUNG	KAC070010M	BGA 69	PA69BGA48DG-YO-8X13
SAMSUNG	KAD070300M	BGA 69	PA69BGA48DJ-YO-8X11.6
SAMSUNG	KAD070300A	BGA 69	PA69BGA48DJ-YO-8X11.6
SAMSUNG	K5A3240YBM	BGA 56	PA56BGA48-YO
SAMSUNG	K5A3240YTM	BGA 56	PA56BGA48-YO
SAMSUNG	K5D3241YBA	BGA 66	PA66BGA48DA-TO-8X11
SAMSUNG	K5D3241YTA	BGA 66	PA66BGA48DA-TO-8X11
SAMSUNG	K5A3280YBM	BGA 56	PA56BGA48-YO
SAMSUNG	K5A3280YTM	BGA 56	PA56BGA48-YO
SAMSUNG	K5A3280YBC	BGA 69	PA69BGA48DE
SAMSUNG	K5A3280YTC	BGA 69	PA69BGA48DE
SAMSUNG	K5A3281CBM	BGA 69	PA69BGA48DE
SAMSUNG	K5A3281CTM	BGA 69	PA69BGA48DE
SAMSUNG	K5A3340YBM	BGA 56	PA56BGA48-YO
SAMSUNG	K5A3340YTM	BGA 56	PA56BGA48-YO
SAMSUNG	K5A3380YBM	BGA 56	PA56BGA48-YO
SAMSUNG	K5A3380YTM	BGA 56	PA56BGA48-YO
SAMSUNG	K5A3240YBA	BGA 56	PA56BGA48-YO
SAMSUNG	K5A3240YTA	BGA 56	PA56BGA48-YO
SAMSUNG	K5A3280YBA	BGA 56	PA56BGA48-YO
SAMSUNG	K5A3280YTA	BGA 56	PA56BGA48-YO
SAMSUNG	K5A3340YBA	BGA 56	PA56BGA48-YO
SAMSUNG	K5A3340YTA	BGA 56	PA56BGA48-YO
SAMSUNG	K5A3380YBA	BGA 56	PA56BGA48-YO
SAMSUNG	K5A3380YTA	BGA 56	PA56BGA48-YO
SAMSUNG	K5A3240YBB	BGA 56	PA56BGA48-YO
SAMSUNG	K5A3240YTB	BGA 56	PA56BGA48-YO
SAMSUNG	K5A3280YBB	BGA 56	PA56BGA48-YO
SAMSUNG	K5A3280YTB	BGA 56	PA56BGA48-YO
SAMSUNG	K5A3340YBB	BGA 56	PA56BGA48-YO
SAMSUNG	K5A3340YTB	BGA 56	PA56BGA48-YO
SAMSUNG	K5A3380YBB	BGA 56	PA56BGA48-YO
SAMSUNG	K5A3380YTB	BGA 56	PA56BGA48-YO
SAMSUNG	KM5AU1620-B	BGA 56	PA56FBGA48D
SAMSUNG	KM5AU1620-T	BGA 56	PA56FBGA48D
SAMSUNG	KM5AU1621-B	BGA 56	PA56FBGA48D
SAMSUNG	KM5AU1621-T	BGA 56	PA56FBGA48D
SAMSUNG	KM5MU0820T-B	sTSOP 48	PA48TS48D-A
SAMSUNG	KM5MU0820T-T	sTSOP 48	PA48TS48D-A
SAMSUNG	KM5MU1620T-B	sTSOP 48	PA48TS48D-A
SAMSUNG	KM5MU1620T-T	sTSOP 48	PA48TS48D-A



SAMSUNG	KM93C06		DIP 8	
SAMSUNG	KM93C07		DIP 8	
SAMSUNG	KM93C46		DIP 8	
SAMSUNG	KM93C56		DIP 8	
SAMSUNG	KM93C66		DIP 8	
SEEQ		27128	DIP 28	
SEEQ		27256	DIP 28	
SEEQ		2764	DIP 28	
SEEQ	27C256		DIP 28	
SEEQ	2804A		DIP 24	
SEEQ	2816A		DIP 24	
SEEQ	2816A		PLCC 32	PA32PL28D-YA
SEEQ	2816AH		DIP 24	
SEEQ	2816AH		PLCC 32	PA32PL28D-YA
SEEQ	2817A		DIP 28	
SEEQ	2817A		PLCC 32	PA32PL28D-YA
SEEQ	2817AH		DIP 28	
SEEQ		2864	DIP 28	
SEEQ		2864	PLCC 32	PA32PL28D-YA
SEEQ	2864H		DIP 28	
SEEQ	2864H		PLCC 32	PA32PL28D-YA
SEEQ	28C010		DIP 32	
SEEQ	28C010		PLCC 32	PA32PL28D-YA
SEEQ	28C256		DIP 28	
SEEQ	28C256		PLCC 32	PA32PL28D-YA
SEEQ	28C256A		DIP 28	
SEEQ	28C256A		PLCC 32	PA32PL28D-YA
SEEQ	28C256AH		DIP 28	
SEEQ	28C256AH		PLCC 32	PA32PL28D-YA
SEEQ	28C64		DIP 28	
SEEQ	28C64A		DIP 28	
SEEQ	28C65		DIP 28	
SEEQ	28HC256		DIP 28	
SEEQ	28HC256H		DIP 28	
SEEQ	28HC64		DIP 28	
SEEQ	52B13		DIP 24	
SEEQ	52B13H		DIP 24	
SEEQ	52B33		DIP 28	
SEEQ	52B33H		DIP 28	
SEEQ	E28C64		DIP 28	
SEEQ	M28C64		DIP 28	
SEEQ	M28C010		DIP 32	
SEEQ	M28C010A		DIP 32	
SEIKO	S24C01A		DIP 8	
SEIKO	S24C02A		DIP 8	
SEIKO	S24CS02A		DIP 8	
SEIKO	S24CS02A		SOIC 8	PA16SO16D-EO-150
SEIKO	S24C04A		DIP 8	
SEIKO	S24C08ADPA		DIP 8	
SEIKO	S24C16ADPA		DIP 8	
SEIKO	S24C08AFJA		SOP 8	PA16SO16D-EO-150
SEIKO	S24C16AFJA		SOP 8	PA16SO16D-EO-150
SEIKO	S-2812A		DIP 28	
SEIKO	S-2812A		SOP 28	PA28SO28DA-EC-330
SEIKO	S-2817A		DIP 28	
SEIKO	S-2817A		SOP 28	PA28SO28DA-EC-330
SEIKO	S-2860B		DIP 28	
SEIKO	S-2860B		SOP 28	PA28SO28DA-EC-330
SEIKO	S-2864B		DIP 28	
SEIKO	S-2864B		SOP 28	PA28SO28DA-EC-330
SEIKO	S-29430A		DIP 8	
SEIKO	S-29430A		SOIC 8	PA16SO16D-EO-150
SEIKO	S-93C46ADP		DIP 8	
SEIKO	S-93C46AFT		TSSOP 8	PA8TSS-OT
SEIKO	S-93C46ADFJ		SOIC 8	PA16SO16D-EO-150
SEIKO	S-93C46AFJ		SOIC 8	PA8SO8D-EO-150
SEIKO	S-93C56ADP		DIP 8	
SEIKO	S-93C56AFT		TSSOP 8	PA8TSS-OT
SEIKO	S-93C56ADFJ		SOIC 8	PA16SO16D-EO-150
SEIKO	S-93C56AFJ		SOIC 8	PA8SO8D-EO-150
SEIKO	S-93C66ADP		DIP 8	
SEIKO	S-93C66AFT		TSSOP 8	PA8TSS-OT
SEIKO	S-93C66ADFJ		SOIC 8	PA16SO16D-EO-150

SEIKO	S-93C66AFJ	SOIC 8	PA8SO8D-EO-150
SEIKO	S-93C46BD	DIP 8	
SEIKO	S-93C46BD	TSSOP 8	PA8TSS-OT
SEIKO	S-93C46BD	SOIC 8	PA16SO16D-EO-150
SEIKO	S-93C46BR	SOIC 8	PA8SO8D-EO-150
SEIKO	S-93C56BD	DIP 8	
SEIKO	S-93C56BD	TSSOP 8	PA8TSS-OT
SEIKO	S-93C56BD	SOIC 8	PA16SO16D-EO-150
SEIKO	S-93C56BR	SOIC 8	PA8SO8D-EO-150
SEIKO	S-93C66BD	DIP 8	
SEIKO	S-93C66BD	TSSOP 8	PA8TSS-OT
SEIKO	S-93C66BD	SOIC 8	PA16SO16D-EO-150
SEIKO	S-93C66BR	SOIC 8	PA8SO8D-EO-150
SEIKO	S-93C76ADP	DIP 8	
SEIKO	S-93C76AFT	TSSOP 8	PA8TSS-OT
SEIKO	S-93C76ADFJ	SOIC 8	PA16SO16D-EO-150
SEIKO	S-93C86BD	TSSOP 8	PA8TSS-OT
SEIKO	S-93C86BD	SOIC 8	PA16SO16D-EO-150
ST	M24C01	DIP 8	
ST	M24C01	SOIC 8	PA16SO16D-EO-150
ST	M24C01	TSSOP 8	PA24TSS24D
ST	M24C02	DIP 8	
ST	M24C02	SOIC 8	PA16SO16D-EO-150
ST	M24C02	TSSOP 8	PA24TSS24D
ST	M24C04	DIP 8	
ST	M24C04	SOIC 8	PA16SO16D-EO-150
ST	M24C04	TSSOP 8	PA24TSS24D
ST	M24C08	DIP 8	
ST	M24C08	TSSOP 8	PA24TSS24D
ST	M24C08	SOIC 8	PA16SO16D-EO-150
ST	M24C08	MSOP 8	HA8MSOP48D
ST	M24C16	DIP 8	
ST	M24C16	SOIC 8	PA16SO16D-EO-150
ST	M24C16	TSSOP 8	PA24TSS24D
ST	M24C16W	DIP 8	
ST	M24C16W	SOIC 8	PA16SO16D-EO-150
ST	M24C16W	TSSOP 8	PA24TSS24D
ST	M24C32	DIP 8	
ST	M24C32	SOIC 8	PA16SO16D-EO-150
ST	M24C32	TSSOP 8	PA24TSS24D
ST	M24C32	QFN 8	PA8QFN8D
ST	M24C64	DIP 8	
ST	M24C64	SOIC 8	PA16SO16D-EO-150
ST	M24C64	TSSOP 8	PA24TSS24D
ST	M24128	DIP 8	
ST	M24128	SOIC 8	PA16SO16D-EO-150
ST	M24128	TSSOP 8	PA24TSS24D
ST	M24256	DIP 8	
ST	M24256	SOIC 8	PA16SO16D-EO-150
ST	M24512	SOIC 8	PA20SO20D-EO-210
ST	M24512	SOIC 8	PA16SO16D-EO-150
ST	M24512	TSSOP 8	PA8TSS8D
ST	M24512	TSSOP 8	PA24TSS24D
ST	M24512	QFN 8	PA8QFN8D
ST	M24LC21B	DIP 8	
ST	M24LC21B	SOIC 8	PA16SO16D-EO-150
ST	M24LC21B	TSSOP 8	PA24TSS24D
ST	M24M01-MN	SOIC 8	PA16SO16D-EO-150
ST	M24M01-DW	TSSOP 8	PA8TSS8D
ST	M34C02WBN	DIP 8	
ST	M34C02WMN	SOIC 8	PA8SO8D-EO-150
ST	M34C02WDW	TSSOP 8	PA8TSS8D
ST	M34C02WDW	TSSOP 8	PA24TSS24D
ST	M34C02LBN	DIP 8	
ST	M34C02LMN	SOIC 8	PA8SO8D-EO-150
ST	M34C02LDW	TSSOP 8	PA8TSS8D
ST	M34C02LDW	TSSOP 8	PA24TSS24D
ST	M34C02RBN	DIP 8	
ST	M34C02RMN	SOIC 8	PA8SO8D-EO-150
ST	M34C02RDW	TSSOP 8	PA8TSS8D
ST	M34C02RDW	TSSOP 8	PA24TSS24D
ST	M25P05VMN	SOIC 8	PA16SO16D-EO-150
ST	M25P05AVMP	MLP 8	PA8SON8D

ST	M25P05AVMN	SOIC 8	PA16SO16D-EO-150
ST	M25P05AVDW	TSSOP 8	PA28TSS28D-EO
ST	M25P10VMN	SOIC 8	PA16SO16D-EO-150
ST	M25P10VMW	SOIC 8	PA20SO20D-EO-210
ST	M25P10AVMP	MLP 8	PA8SON8D
ST	M25P10AVMN	SOIC 8	PA16SO16D-EO-150
ST	M25P20VMP	MLP 8	PA8SON8D
ST	M25P20VMN	SOIC 8	PA16SO16D-EO-150
ST	M25P20VMW	SOIC 8	PA16SO16D-EO-150
ST	M25P40VMN	SOIC 8	PA16SO16D-EO-150
ST	M25P40VMP	MLP 8	PA8SON8D
ST	M25P80VMW	SOIC 8	PA20SO20D-EO-210
ST	M25P80VMN	SOIC 8	PA16SO16D-EO-150
ST	M25P80VMF	SOIC 16	PA28SO28D-EO-300
ST	M25P16VMJ	SOIC 16	PA28SO28D-EO-300
ST	M25P16VMP	MLP 8	PA8SON8D
ST	M25P16VME	MLP 8	PA8SON8DA
ST	M25P16VMW	SOIC 8	PA20SO20D-EO-210
ST	M25P16VMF	SOIC 16	PA28SO28D-EO-300
ST	M25P16VMN	SOIC 8	PA16SO16D-EO-150
ST	M25P32VME	MLP 8	PA8SON8DA
ST	M25P32VML	MLP 8	PA8SON8D
ST	M25P32VMF	SOIC 16	PA28SO28D-EO-300
ST	M25P32VMJ	SOIC 16	PA28SO28D-EO-300
ST	M25P32VMW	SOIC 8	PA20SO20D-EO-210
MICRON	M25P32-VME	WSON 8	PA8SON8DA
MICRON	M25P32-VMP	WSON 8	PA8SON8D
MICRON	M25P32-VMF	SOIC 16	PA28SO28D-EO-300
MICRON	M25P32-VMW	SOIC 8	PA20SO20D-EO-210
ST	M25P32V6G	SOIC 8	PA20SO20D-EO-210
ST	M25P64VME	MLP 8	PA8SON8DA
ST	M25P64VME	MLP 8	PA8SON20D
ST	M25P64VMF	SOIC 16	PA28SO28D-EO-300
ST	M25P64VMJ	SOIC 16	PA28SO28D-EO-300
ST	M25P64V6P	SOIC 16	PA28SO28D-EO-300
ST	M25P128VME	MLP 8	PA8SON8DA
ST	M25P128VMF	SOIC 16	PA28SO28D-EO-300
ST	M25PE10VMN	SOIC 8	PA16SO16D-EO-150
ST	M25PE20VMN	SOIC 8	PA16SO16D-EO-150
ST	M25PE40VMP	MLP 8	PA8SON8D
ST	M25PE40VMW	SOIC 8	PA20SO20D-EO-210
ST	M25PE80VMW	SOIC 8	PA16SO16D-EO-150
ST	M25PE80VMP	MLP 8	PA8SON8D
ST	M25PE16VMW	SOIC 8	PA20SO20D-EO-210
ST	M25PE16VMP	MLP 8	PA8SON8D
ST	M25PF32VMW	SOIC 8	PA20SO20D-EO-210
ST	M25PF32VE	SOIC 8	PA20SO20D-EO-210
ST	M25PX16VMN	SOIC 8	PA16SO16D-EO-150
ST	M25PX64VME	MLP 8	PA8SON20D
ST	M25PX64VMD	MLP 8	PA8SON20D
ST	M25PX64VMP	SOIC 16	PA28SO28D-EO-300
NUMONYX	M25P128VMF	SOIC 16	PA28SO28D-EO-300
ST	M27128A	DIP 28	
ST	M2716	DIP 24	
ST	M2732A	DIP 24	
ST	M2764	DIP 28	
ST	M2764A	DIP 28	
ST	M27256	DIP 28	
ST	M27512	DIP 28	
ST	M27C516	DIP 40	
ST	M27C516	PLCC 44	PA44-48U
ST	M27C516	TSOP 40	PA40TS40D
ST	M27C1000	DIP 32	
ST	M27C1000	PLCC 32	PA32PL32D
ST	M27C1001	DIP 32	
ST	M27C1001	PLCC 32	PA32PL32D
ST	M27C1001	TSOP 32	PA32TS20/PA32TS32D-20
ST	M27C2001	DIP 32	
ST	M27C2001	TSOP 32	PA32TS20/PA32TS32D-20
ST	M27C2001	PLCC 32	PA32PL32D
ST	M27C256B	DIP 28	
ST	M27C256B	PLCC 32	PA32PL28D-YA
ST	M27C256B	TSOP 28	PA28TS28D-EO

ST	M27C4001	DIP 32	
ST	M27C4001	PLCC 32	PA32PL32D
ST	M27C4001	TSOP 32	PA32TS20/PA32TS32D-20
ST	M27C405	DIP 32	
ST	M27C512	DIP 28	
ST	M27C512	PLCC 32	PA32PL28D-YA
ST	M27C512	TSOP 28	PA28TS28D-EO
ST	M27C64A	DIP 28	
ST	M27C64A	PLCC 32	PA32PL28D-YA
ST	M27C801	DIP 32	
ST	M27C801	PLCC 32	PA32PL32D
ST	M27C801	TSOP 32	PA32TS20/PA32TS32D-20
ST	M27C1024	DIP 40	
ST	M27C1024	PLCC 44	PA44-48U
ST	M27C1024	TSOP 40	PA40TS40D
ST	M27C202	DIP 40	
ST	M27C202	PLCC 44	PA44-48U
ST	M27C202	TSOP 40	PA40TS40D
ST	M27C4002	DIP 40	
ST	M27C4002	PLCC 44	PA44-48U
ST	M27C4002	TSOP 40	PA40TS40D
ST	M27C400	DIP 40	
ST	M27C400	PLCC 44	PA44-48U
ST	M27C800	DIP 42	
ST	M27C800	PLCC 44	PA44-48U
ST	M27C800	SOP 44	PA44SO44D
ST	M27C160	DIP 42	
ST	M27C160	PLCC 44	PA44-48U
ST	M27C160	SOP 44	PA44SO44D
ST	M27C320	TSOP 48	PA48TS48D
ST	M27C320	SOP 44	PA44SO44D
ST	M27C322	DIP 42	
ST	M27V256	DIP 28	
ST	M27V256	PLCC 32	PA32PL28D-YA
ST	M27V256	TSOP 28	PA28TS28D-EO
ST	M27V512	DIP 28	
ST	M27V512	PLCC 32	PA32PL28D-YA
ST	M27V512	TSOP 28	PA28TS28D-EO
ST	M27V101	DIP 32	
ST	M27V101	PLCC 32	PA32PL32D
ST	M27V101	TSOP 32	PA32TS20/PA32TS32D-20
ST	M27V102	TSOP 40	PA40TS40D
ST	M27V201	DIP 32	
ST	M27V201	PLCC 32	PA32PL32D
ST	M27V201	TSOP 32	PA32TS20/PA32TS32D-20
ST	M27V401	DIP 32	
ST	M27V401	PLCC 32	PA32PL32D
ST	M27V401	TSOP 32	PA32TS20/PA32TS32D-20
ST	M27V402	DIP 40	
ST	M27V402	PLCC 44	PA44-48U
ST	M27V402	TSOP 40	PA40TS40D
ST	M27V801	DIP 32	
ST	M27V801	PLCC 32	PA32PL32D
ST	M27V801	TSOP 32	PA32TS20/PA32TS32D-20
ST	M27V800	DIP 42	
ST	M27V800	PLCC 44	PA44-48U
ST	M27V800	SOP 44	PA44SO44D
ST	M27V160	DIP 42	
ST	M27V160	PLCC 44	PA44-48U
ST	M27V160	SOP 44	PA44SO44D
ST	M27V322	DIP 42	
ST	M27W256	DIP 28	
ST	M27W256	PLCC 32	PA32PL28D-YA
ST	M27W256	TSOP 28	PA28TS28D-EO
ST	M27W256B	DIP 28	
ST	M27W512	DIP 28	
ST	M27W512	PLCC 32	PA32PL28D-YA
ST	M27W512	TSOP 28	PA28TS28D-EO
ST	M27W101	DIP 32	
ST	M27W101	PLCC 32	PA32PL32D
ST	M27W101	TSOP 32	PA32TS20/PA32TS32D-20
ST	M27W201	DIP 32	
ST	M27W201	PLCC 32	PA32PL32D

ST	M27W201	TSOP 32	PA32TS20/PA32TS32D-20
ST	M27W401	DIP 32	
ST	M27W401	PLCC 32	PA32PL32D
ST	M27W401	TSOP 32	PA32TS20/PA32TS32D-20
ST	M27W801	DIP 32	
ST	M27W801	PLCC 32	PA32PL32D
ST	M27W801	TSOP 32	PA32TS20/PA32TS32D-20
ST	M27W102	DIP 40	
ST	M27W102	PLCC 44	PA44-48U
ST	M27W102	TSOP 40	PA40TS40D
ST	M27W202	DIP 40	
ST	M27W202	PLCC 44	PA44-48U
ST	M27W202	TSOP 40	PA40TS40D
ST	M27W400	DIP 40	
ST	M27W400	PLCC 44	PA44-48U
ST	M27W402	DIP 40	
ST	M27W402	PLCC 44	PA44-48U
ST	M27W402	TSOP 40	PA40TS40D
ST	M27W800	DIP 42	
ST	M27W800	PLCC 44	PA44-48U
ST	M27W800	SOP 44	PA44SO44D
ST	M27W160	DIP 42	
ST	M27W160	SOP 44	PA44SO44D
ST	M27W322	DIP 42	
ST	TS27C64A	PLCC 32	PA32PL28D-YA
ST	ST27C256	PLCC 32	PA32PL28D-YA
ST	M28256	DIP 28	
ST	M28256	PLCC 32	PA32PL28D-YA
ST	M28256	SOIC 28	PA28SO28D-EO-300
ST	M28256	TSOP 28	PA28TS28D-EO
ST	M28256-xxW	DIP 28	
ST	M28256-xxW	PLCC 32	PA32PL28D-YA
ST	M28256-xxW	SOIC 28	PA28SO28D-EO-300
ST	M28256-xxW	TSOP 28	PA28TS28D-EO
ST	M28010	DIP 32	
ST	M28010	PLCC 32	PA32PL32D
ST	M28010	TSOP 32	PA32TS20/PA32TS32D-20
ST	M28010-xxW	DIP 32	
ST	M28010-xxW	PLCC 32	PA32PL32D
ST	M28010-xxW	TSOP 32	PA32TS20/PA32TS32D-20
ST	M28C17	DIP 28	
ST	M28C17	PLCC 32	PA32PL28D-YA
ST	M28C17	SOIC 28	PA28SO28D-EO-300
ST	M28C64	DIP 28	
ST	M28C64	PLCC 32	PA32PL28D-YA
ST	M28C64	SOIC 28	PA28SO28D-EO-300
ST	M28C64	TSOP 28	PA28TS28D-EO
ST	M28C64C	DIP 28	
ST	M28C64C	PLCC 32	PA32PL28D-YA
ST	M28C64C	SOIC 28	PA28SO28D-EO-300
ST	M28C64C	TSOP 28	PA28TS28D-EO
ST	M28C64X	DIP 28	
ST	M28C64X	PLCC 32	PA32PL28D-YA
ST	M28C64X	SOIC 28	PA28SO28D-EO-300
ST	M28C64X	TSOP 28	PA28TS28D-EO
ST	M28F256	DIP 32	
ST	M28F256	PLCC 32	PA32PL32D
ST	M28F256A	DIP 32	
ST	M28F256A	PLCC 32	PA32PL32D
ST	M28F512	DIP 32	
ST	M28F512	PLCC 32	PA32PL32D
ST	M28F101	DIP 32	
ST	M28F101	PLCC 32	PA32PL32D
ST	M28F101	TSOP 32	PA32TS20/PA32TS32D-20
ST	M28F201	DIP 32	
ST	M28F201	PLCC 32	PA32PL32D
ST	M28F201	TSOP 32	PA32TS20/PA32TS32D-20
ST	M28W800CB	TSOP 48	PA48TS48D
ST	M28W800CT	TSOP 48	PA48TS48D
ST	M28W160B	TSOP 48	PA48TS48D
ST	M28W160T	TSOP 48	PA48TS48D
ST	M28W160BB	TSOP 48	PA48TS48D
ST	M28W160BT	TSOP 48	PA48TS48D

ST	M28W160CB	TSOP 48	PA48TS48D
ST	M28W160CT	TSOP 48	PA48TS48D
ST	M28W320BB	TSOP 48	PA48TS48D
ST	M28W320BT	TSOP 48	PA48TS48D
ST	M28W320CB	TSOP 48	PA48TS48D
ST	M28W320CT	TSOP 48	PA48TS48D
ST	M28W320FCB	TSOP 48	PA48TS48D
ST	M28W320FCT	TSOP 48	PA48TS48D
ST	M28W640ECB	TSOP 48	PA48TS48D
ST	M28W640ECT	TSOP 48	PA48TS48D
ST	M28W640FCB	TSOP 48	PA48TS48D
ST	M28W640FCT	TSOP 48	PA48TS48D
ST	M28W640HCT	TSOP 48	PA48TS48D
ST	M28W640FST-ZA	EBGA 64	PA64BGA48D
ST	M28W640FST-ZA	EBGA 64	HA64BGA48D
ST	M28W640FSB-ZA	EBGA 64	PA64BGA48D
ST	M28W640FSB-ZA	EBGA 64	HA64BGA48D
ST	M28W640FSU-ZA	EBGA 64	PA64BGA48D
ST	M28W640FSU-ZA	EBGA 64	HA64BGA48D
ST	M29DW323DB	TSOP 48	PA48TS48D
ST	M29DW323DT	TSOP 48	PA48TS48D
ST	M29DW640F	TSOP 48	PA48TS48D
ST	M29DW128G-NF	TSOP 56	PA56TS48DD
ST	M29DW256G	TSOP 56	PA56TS48DD
ST	M29DW256G	TSOP 56	PA56TS48DC
ST	M29DW256GH	TSOP 56	PA56TS48DC
ST	M29F512B	PLCC 32	PA32PL32D
ST	M29F512B	TSOP 32	PA32TS20/PA32TS32D-20
ST	M29F002T	DIP 32	
ST	M29F002T	PLCC 32	PA32PL32D
ST	M29F002T	TSOP 32	PA32TS20/PA32TS32D-20
ST	M29F002B	DIP 32	
ST	M29F002B	PLCC 32	PA32PL32D
ST	M29F002B	TSOP 32	PA32TS20/PA32TS32D-20
ST	M29F002BB	DIP 32	
ST	M29F002BB	PLCC 32	PA32PL32D
ST	M29F002BB	TSOP 32	PA32TS20/PA32TS32D-20
ST	M29F002BT	DIP 32	
ST	M29F002BT	PLCC 32	PA32PL32D
ST	M29F002BT	TSOP 32	PA32TS20/PA32TS32D-20
ST	M29F002BNT	DIP 32	
ST	M29F002BNT	PLCC 32	PA32PL32D
ST	M29F002BNT	TSOP 32	PA32TS20/PA32TS32D-20
ST	M29F002NT	DIP 32	
ST	M29F002NT	PLCC 32	PA32PL32D
ST	M29F002NT	TSOP 32	PA32TS20/PA32TS32D-20
ST	M29F010B	DIP 32	
ST	M29F010B	PLCC 32	PA32PL32D
ST	M29F010B	TSOP 32	PA32TS20/PA32TS32D-20
ST	M29F040	DIP 32	
ST	M29F040	PLCC 32	PA32PL32D
ST	M29F040	TSOP 32	PA32TS20/PA32TS32D-20
ST	M29F040B	DIP 32	
ST	M29F040B	PLCC 32	PA32PL32D
ST	M29F040B	TSOP 32	PA32TS20/PA32TS32D-20
ST	M29F080A	TSOP 40	PA40TS40D
ST	M29F080D	TSOP 40	PA40TS40D
ST	M29F016B	TSOP 40	PA40TS40D
ST	M29F016B	SOP 44	PA44SO44D
ST	M29F016D	TSOP 40	PA40TS40D
ST	M29F016D	SOP 44	PA44SO44D
ST	M29F032D	TSOP 40	PA40TS40D
ST	M29F100B	SOP 44	PA44SO44D
ST	M29F100B	TSOP 48	PA48TS48D
ST	M29F100T	SOP 44	PA44SO44D
ST	M29F100T	TSOP 48	PA48TS48D
ST	M29F100BB	SOP 44	PA44SO44D
ST	M29F100BB	TSOP 48	PA48TS48D
ST	M29F100BT	SOP 44	PA44SO44D
ST	M29F100BT	TSOP 48	PA48TS48D
ST	M29F200B	SOP 44	PA44SO44D
ST	M29F200B	TSOP 48	PA48TS48D
ST	M29F200T	SOP 44	PA44SO44D

ST	M29F200T	TSOP 48	PA48TS48D
ST	M29F200BB	SOP 44	PA44SO44D
ST	M29F200BB	TSOP 48	PA48TS48D
ST	M29F200BT	SOP 44	PA44SO44D
ST	M29F200BT	TSOP 48	PA48TS48D
ST	M29F400B	SOP 44	PA44SO44D
ST	M29F400B	TSOP 48	PA48TS48D
ST	M29F400T	SOP 44	PA44SO44D
ST	M29F400T	TSOP 48	PA48TS48D
ST	M29F400BB	SOP 44	PA44SO44D
ST	M29F400BB	TSOP 48	PA48TS48D
ST	M29F400BT	SOP 44	PA44SO44D
ST	M29F400BT	TSOP 48	PA48TS48D
NUMONYX	M29F400FT	SOP 44	PA44SO44D
NUMONYX	M29F400FT	TSOP 48	PA48TS48D
ST	M29F800AB	SOP 44	PA44SO44D
ST	M29F800AB	TSOP 48	PA48TS48D
ST	M29F800AT	SOP 44	PA44SO44D
ST	M29F800AT	TSOP 48	PA48TS48D
ST	M29F800DB	SOP 44	PA44SO44D
ST	M29F800DB	TSOP 48	PA48TS48D
ST	M29F800DT	SOP 44	PA44SO44D
ST	M29F800DT	TSOP 48	PA48TS48D
ST	M29F800FB	TSOP 48	PA48TS48D
ST	M29F160BB	TSOP 48	PA48TS48D
ST	M29F160BT	TSOP 48	PA48TS48D
ST	M29KW016E	TSOP 48	PA48TS48D1
ST	M29KW032E	TSOP 48	PA48TS48D1
ST	M29KW064E	TSOP 48	PA48TS48D1
ST	M29W512B	PLCC 32	PA32PL32D
ST	M29W512B	TSOP 32	PA32TS20/PA32TS32D-20
ST	M29W010B	DIP 32	
ST	M29W010B	PLCC 32	PA32PL32D
ST	M29W010B	TSOP 32	PA32TS20/PA32TS32D-20
ST	M29W022BB	PLCC 32	PA32PL32D
ST	M29W022BB	TSOP 32	PA32TS20/PA32TS32D-20
ST	M29W022BT	PLCC 32	PA32PL32D
ST	M29W022BT	TSOP 32	PA32TS20/PA32TS32D-20
ST	M29W040	DIP 32	
ST	M29W040	PLCC 32	PA32PL32D
ST	M29W040	TSOP 32	PA32TS20/PA32TS32D-20
ST	M29W040	TSOP 32	PA32TS32D
ST	M29W040B	DIP 32	
ST	M29W040B	PLCC 32	PA32PL32D
ST	M29W040B	TSOP 32	PA32TS20/PA32TS32D-20
ST	M29W040B	TSOP 32	PA32TS32D
ST	M29W017D	TSOP 40	PA40TS40D
ST	M29W004BB	TSOP 40	PA40TS40D
ST	M29W004BT	TSOP 40	PA40TS40D
ST	M29W008AB	TSOP 40	PA40TS40D
ST	M29W008AT	TSOP 40	PA40TS40D
ST	M29W200BB	SOP 44	PA44SO44D
ST	M29W200BB	TSOP 48	PA48TS48D
ST	M29W200BT	SOP 44	PA44SO44D
ST	M29W200BT	TSOP 48	PA48TS48D
ST	M29W400B	SOP 44	PA44SO44D
ST	M29W400B	TSOP 48	PA48TS48D
ST	M29W400T	SOP 44	PA44SO44D
ST	M29W400T	TSOP 48	PA48TS48D
ST	M29W400FT	TSOP 48	PA48TS48D
ST	M29W800B	SOP 44	PA44SO44D
ST	M29W800B	TSOP 48	PA48TS48D
ST	M29W800T	SOP 44	PA44SO44D
ST	M29W800T	TSOP 48	PA48TS48D
ST	M29W400BB	SOP 44	PA44SO44D
ST	M29W400BB	TSOP 48	PA48TS48D
ST	M29W400BT	SOP 44	PA44SO44D
ST	M29W400BT	TSOP 48	PA48TS48D
ST	M29W400DB	SOP 44	PA44SO44D
ST	M29W400DB	TSOP 48	PA48TS48D
ST	M29W400DT	SOP 44	PA44SO44D
ST	M29W400DT	TSOP 48	PA48TS48D
ST	M29W800AB	SOP 44	PA44SO44D

ST	M29W800AB	TSOP 48	PA48TS48D
ST	M29W800AT	SOP 44	PA44SO44D
ST	M29W800AT	TSOP 48	PA48TS48D
ST	M29W800DB	SOP 44	PA44SO44D
ST	M29W800DB	TSOP 48	PA48TS48D
ST	M29W800DT	SOP 44	PA44SO44D
ST	M29W800DT	TSOP 48	PA48TS48D
ST	M29W160DB	TSOP 48	PA48TS48D
ST	M29W160DT	TSOP 48	PA48TS48D
ST	M29W160EB	TSOP 48	PA48TS48D
ST	M29W160ET	TSOP 48	PA48TS48D
ST	M29W320DB	TSOP 48	PA48TS48D
ST	M28W320FSB-ZA	EBGA 64	PA64BGA48D
ST	M28W320FSB-ZA	EBGA 64	HA64BGA48D
ST	M28W320FST-ZA	EBGA 64	PA64BGA48D
ST	M28W320FST-ZA	EBGA 64	HA64BGA48D
ST	M29W320DT	TSOP 48	PA48TS48D
ST	M29W320EB	TSOP 48	PA48TS48D
ST	M29W320ET	TSOP 48	PA48TS48D
ST	M29W640DB	TSOP 48	PA48TS48D
ST	M29W640DT	TSOP 48	PA48TS48D
ST	M29W640FB	TSOP 48	PA48TS48D
ST	M29W640FT	TSOP 48	PA48TS48D
ST	M29W640GB	TSOP 48	PA48TS48D
ST	M29W640GB	TSOP 56	PA56TS48DB
ST	M29W640GH	TSOP 48	PA48TS48D
ST	M29W640GH	BGA 48	HA48BG48DAI
ST	M29W640GH	TSOP 56	PA56TS48DB
ST	M29W640GT	TSOP 48	PA48TS48D
ST	M29W640GT	TSOP 56	PA56TS48DB
ST	M29W160EB	BGA 64	PA64BG48DK
ST	M29W160ET	BGA 64	PA64BG48DK
ST	M29W320EB	BGA 64	PA64BG48DK
ST	M29W320ET	BGA 64	PA64BG48DK
ST	M29W640GT-ZF	BGA 64	NA64BG48DT
ST	M29W640GB-ZF	BGA 64	NA64BG48DT
ST	M29W640GH-ZF	BGA 64	NA64BG48DT
ST	M29W640GL-ZF	BGA 64	NA64BG48DT
ST	M29W256GH-ZA	BGA 64	NA64BG48DT
ST	M29W256GL-ZA	BGA 64	NA64BG48DT
NUMONYX	M29W256GL-ZA	BGA 64	PA64BG48DK
NUMONYX	M29W256GL-ZS	BGA 64	PA64BG48DK
ST	M29W641D	TSOP 48	PA48TS48D
ST	M29W128FL	TSOP 56	PA56TS48DB
ST	M29W128FH	TSOP 56	PA56TS48DB
ST	M29W128GH	TSOP 56	PA56TS48DB
ST	M29W128GL	TSOP 56	PA56TS48DB
MICRON	M29W256GH-N	TSOP 56	HA56TS48DI
MICRON	M29W256GH-ZS	BGA 64	PA64BG48DR
MICRON	M29W256GL-N	TSOP 56	HA56TS48DI
MICRON	M29W256GL-ZS	BGA 64	PA64BG48DR
ST	M36A0W5030T0	BGA 66	PA66BGA48DB
ST	M36A0W5030B0	BGA 66	PA66BGA48DB
ST	M36L0R8060B	BGA 88	HA88BGA48DA7
ST	M36L0R8060T	BGA 88	HA88BGA48DA7
ST	M36WWT6650D0	BGA 88	PA88BGA48DA-YO-8X10
ST	M36WWT6650T0	BGA 88	PA88BGA48DA-YO-8X10
ST	M36WWT6650B0	BGA 88	PA88BGA48DA-YO-8X10
ST	M50FW020	PLCC 32	PA32PL32D
ST	M50FW040	PLCC 32	PA32PL32D
ST	M50FW040	TSOP 40	PA40TS40D
ST	M50FW080	PLCC 32	PA32PL32D
ST	M50FW080	TSOP 40	PA40TS40D
ST	M50FW080	TSOP 32	PA32TS32D
ST	M50FW016	TSOP 40	PA40TS40D
ST	M50FLW040A	PLCC 32	PA32PL32D
ST	M50FLW040A	TSOP 32	PA32TS32D
ST	M50FLW040A	TSOP 40	PA40TS40D
ST	M50FLW040B	PLCC 32	PA32PL32D
ST	M50FLW040B	TSOP 32	PA32TS32D
ST	M50FLW040B	TSOP 40	PA40TS40D
ST	M50FLW080A	PLCC 32	PA32PL32D
ST	M50FLW080A	TSOP 32	PA32TS32D



ST	M50FLW080A	TSOP 40	PA40TS40D
ST	M50FLW080B	PLCC 32	PA32PL32D
ST	M50FLW080B	TSOP 32	PA32TS32D
ST	M50FLW080B	TSOP 40	PA40TS40D
ST	M50LPW020	PLCC 32	PA32PL32D
ST	M50LPW040	PLCC 32	PA32PL32D
ST	M50LPW040	TSOP 40	PA40TS40D
ST	M50LPW080	PLCC 32	PA32PL32D
ST	M50LPW080	TSOP 40	PA40TS40D
ST	M50LPW116	TSOP 40	PA40TS40D
ST	M45PE10VMN	SOP 8	PA16SO16D-EO-150
ST	M45PE10VMP	MLP 8	PA8SON8D
ST	M45PE16VMW	SOP 8	PA20SO20D-EO-210
ST	M45PE16VMP	MLP 8	PA8SON8D
ST	M45PE20VMN	SOP 8	PA16SO16D-EO-150
ST	M45PE20VMP	MLP 8	PA8SON8D
ST	M45PE40VMN	SOP 8	PA20SO20D-EO-210
ST	M45PE40VMP	MLP 8	PA8SON8D
ST	M45PE80VMN	SOP 8	PA20SO20D-EO-210
ST	M45PE80VMP	MLP 8	PA8SON8D
ST	M72DW54003TB	BGA 73	PA73BGA48DC-YO-8X11.6
ST	M72DW54003BB	BGA 73	PA73BGA48DC-YO-8X11.6
ST	M72DW64000B	BGA 73	PA73BGA48DC-YO-8X11.6
ST	M87C257	DIP 28	
ST	M9306	DIP 8	
ST	M9346	DIP 8	
ST	M93C06	DIP 8	
ST	M93C06	TSSOP 8	PA8TSS-OT
ST	M93C06	SOIC 8	PA16SO16D-EO-150
ST	M93C06-W	DIP 8	
ST	M93C06-W	TSSOP 8	PA8TSS-OT
ST	M93C06-W	SOIC 8	PA16SO16D-EO-150
ST	M93C06-R	DIP 8	
ST	M93C06-R	TSSOP 8	PA8TSS-OT
ST	M93C06-R	SOIC 8	PA16SO16D-EO-150
ST	M93C06-T	SOIC 8	PA8SO8D-EO-150
ST	M93C46	DIP 8	
ST	M93C46	TSSOP 8	PA8TSS-OT
ST	M93C46	SOIC 8	PA16SO16D-EO-150
ST	M93C46-W	DIP 8	
ST	M93C46-W	TSSOP 8	PA8TSS-OT
ST	M93C46-W	SOIC 8	PA16SO16D-EO-150
ST	M93C46-R	DIP 8	
ST	M93C46-R	TSSOP 8	PA8TSS-OT
ST	M93C46-R	SOIC 8	PA16SO16D-EO-150
ST	M93C46-T	SOIC 8	PA8SO8D-EO-150
ST	M93C56	DIP 8	
ST	M93C56	TSSOP 8	PA8TSS-OT
ST	M93C56	SOIC 8	PA16SO16D-EO-150
ST	M93C56-W	DIP 8	
ST	M93C56-W	TSSOP 8	PA8TSS-OT
ST	M93C56-W	SOIC 8	PA16SO16D-EO-150
ST	M93C56-R	DIP 8	
ST	M93C56-R	TSSOP 8	PA8TSS-OT
ST	M93C56-R	SOIC 8	PA16SO16D-EO-150
ST	M93C56-T	SOIC 8	PA8SO8D-EO-150
ST	M93C66	DIP 8	
ST	M93C66	TSSOP 8	PA8TSS-OT
ST	M93C66	SOIC 8	PA16SO16D-EO-150
ST	M93C66-W	DIP 8	
ST	M93C66-W	TSSOP 8	PA8TSS-OT
ST	M93C66-W	SOIC 8	PA16SO16D-EO-150
ST	M93C66-R	DIP 8	
ST	M93C66-R	TSSOP 8	PA8TSS-OT
ST	M93C66-R	SOIC 8	PA16SO16D-EO-150
ST	M93C66-T	SOIC 8	PA8SO8D-EO-150
ST	M93C76	DIP 8	
ST	M93C76	TSSOP 8	PA8TSS-OT
ST	M93C76	SOIC 8	PA16SO16D-EO-150
ST	M93C76-W	DIP 8	
ST	M93C76-W	TSSOP 8	PA8TSS-OT
ST	M93C76-W	SOIC 8	PA16SO16D-EO-150
ST	M93C76-R	DIP 8	

ST	M93C76-R	TSSOP 8	PA8TSS-OT
ST	M93C76-R	SOIC 8	PA16SO16D-EO-150
ST	M93C76-T	SOIC 8	PA8SO8D-EO-150
ST	M93C86	DIP 8	
ST	M93C86	TSSOP 8	PA8TSS-OT
ST	M93C86	SOIC 8	PA16SO16D-EO-150
ST	M93C86-W	DIP 8	
ST	M93C86-W	TSSOP 8	PA8TSS-OT
ST	M93C86-W	SOIC 8	PA16SO16D-EO-150
ST	M93C86-R	DIP 8	
ST	M93C86-R	TSSOP 8	PA8TSS-OT
ST	M93C86-R	SOIC 8	PA16SO16D-EO-150
ST	M93C86-T	SOIC 8	PA8SO8D-EO-150
ST	M93S46	DIP 8	
ST	M93S46	TSSOP 8	PA8TSS-OT
ST	M93S46	SOIC 8	PA16SO16D-EO-150
ST	M93S46-R	DIP 8	
ST	M93S46-R	TSSOP 8	PA8TSS-OT
ST	M93S46-R	SOIC 8	PA16SO16D-EO-150
ST	M93S46-W	DIP 8	
ST	M93S46-W	TSSOP 8	PA8TSS-OT
ST	M93S46-W	SOIC 8	PA16SO16D-EO-150
ST	M93S56	DIP 8	
ST	M93S56	TSSOP 8	PA8TSS-OT
ST	M93S56	SOIC 8	PA16SO16D-EO-150
ST	M93S56-R	DIP 8	
ST	M93S56-R	TSSOP 8	PA8TSS-OT
ST	M93S56-R	SOIC 8	PA16SO16D-EO-150
ST	M93S56-W	DIP 8	
ST	M93S56-W	TSSOP 8	PA8TSS-OT
ST	M93S56-W	SOIC 8	PA16SO16D-EO-150
ST	M93S66	DIP 8	
ST	M93S66	TSSOP 8	PA8TSS-OT
ST	M93S66	SOIC 8	PA16SO16D-EO-150
ST	M93S66-R	DIP 8	
ST	M93S66-R	TSSOP 8	PA8TSS-OT
ST	M93S66-R	SOIC 8	PA16SO16D-EO-150
ST	M93S66-W	DIP 8	
ST	M93S66-W	TSSOP 8	PA8TSS-OT
ST	M93S66-W	SOIC 8	PA16SO16D-EO-150
ST	M95010-R	DIP 8	
ST	M95010-R	SOIC 8	PA16SO16D-EO-150
ST	M95010-R	TSSOP 8	PA8TSS8D
ST	M95010-R	TSSOP 8	PA24TSS24D
ST	M95010	DIP 8	
ST	M95010	SOIC 8	PA16SO16D-EO-150
ST	M95010	TSSOP 8	PA8TSS8D
ST	M95010	TSSOP 8	PA24TSS24D
ST	M95010-W	DIP 8	
ST	M95010-W	SOIC 8	PA16SO16D-EO-150
ST	M95010-W	TSSOP 8	PA8TSS8D
ST	M95010-W	TSSOP 8	PA24TSS24D
ST	M95020-R	DIP 8	
ST	M95020-R	SOIC 8	PA16SO16D-EO-150
ST	M95020-R	TSSOP 8	PA8TSS8D
ST	M95020-R	TSSOP 8	PA24TSS24D
ST	M95020	DIP 8	
ST	M95020	SOIC 8	PA16SO16D-EO-150
ST	M95020	TSSOP 8	PA8TSS8D
ST	M95020	TSSOP 8	PA24TSS24D
ST	M95020-W	DIP 8	
ST	M95020-W	SOIC 8	PA16SO16D-EO-150
ST	M95020-W	TSSOP 8	PA8TSS8D
ST	M95020-W	TSSOP 8	PA24TSS24D
ST	M95040-R	DIP 8	
ST	M95040-R	SOIC 8	PA16SO16D-EO-150
ST	M95040-R	TSSOP 8	PA8TSS8D
ST	M95040-R	TSSOP 8	PA24TSS24D
ST	M95040	DIP 8	
ST	M95040	SOIC 8	PA16SO16D-EO-150
ST	M95040	TSSOP 8	PA8TSS8D
ST	M95040	TSSOP 8	PA24TSS24D
ST	M95040-W	DIP 8	

ST	M95040-W	SOIC 8	PA16SO16D-EO-150
ST	M95040-W	TSSOP 8	PA8TSS8D
ST	M95040-W	TSSOP 8	PA24TSS24D
ST	M95080-R	DIP 8	
ST	M95080-R	SOIC 8	PA16SO16D-EO-150
ST	M95080-R	TSSOP 8	PA8TSS8D
ST	M95080-R	TSSOP 8	PA24TSS24D
ST	M95080-R	MSOP 8	PA8MSOP8D
ST	M95080-R	MLP 8	PA8SON8D
ST	M95080-R	QFN 8	PA8QFN8D
ST	M95080	DIP 8	
ST	M95080	SOIC 8	PA16SO16D-EO-150
ST	M95080	TSSOP 8	PA8TSS8D
ST	M95080	TSSOP 8	PA24TSS24D
ST	M95080	MSOP 8	PA8MSOP8D
ST	M95080	MLP 8	PA8SON8D
ST	M95080-V	DIP 8	
ST	M95080-V	SOIC 8	PA16SO16D-EO-150
ST	M95080-V	TSSOP 8	PA8TSS8D
ST	M95080-V	TSSOP 8	PA24TSS24D
ST	M95080-V	MSOP 8	PA8MSOP8D
ST	M95080-V	MLP 8	PA8SON8D
ST	M95080-W	DIP 8	
ST	M95080-W	SOIC 8	PA16SO16D-EO-150
ST	M95080-W	TSSOP 8	PA8TSS8D
ST	M95080-W	TSSOP 8	PA24TSS24D
ST	M95080-W	MSOP 8	PA8MSOP8D
ST	M95080-W	MLP 8	PA8SON8D
ST	M95160-R	DIP 8	
ST	M95160-R	SOIC 8	PA16SO16D-EO-150
ST	M95160-R	TSSOP 8	PA8TSS8D
ST	M95160-R	TSSOP 8	PA24TSS24D
ST	M95160-R	MSOP 8	PA8MSOP8D
ST	M95160-R	MLP 8	PA8SON8D
ST	M95160	DIP 8	
ST	M95160	SOIC 8	PA16SO16D-EO-150
ST	M95160	TSSOP 8	PA8TSS8D
ST	M95160	TSSOP 8	PA24TSS24D
ST	M95160	MSOP 8	PA8MSOP8D
ST	M95160	MLP 8	PA8SON8D
ST	M95160-V	DIP 8	
ST	M95160-V	SOIC 8	PA16SO16D-EO-150
ST	M95160-V	TSSOP 8	PA8TSS8D
ST	M95160-V	TSSOP 8	PA24TSS24D
ST	M95160-V	MSOP 8	PA8MSOP8D
ST	M95160-V	MLP 8	PA8SON8D
ST	M95160-W	DIP 8	
ST	M95160-W	SOIC 8	PA16SO16D-EO-150
ST	M95160-W	TSSOP 8	PA8TSS8D
ST	M95160-W	TSSOP 8	PA24TSS24D
ST	M95160-W	MSOP 8	PA8MSOP8D
ST	M95160-W	MLP 8	PA8SON8D
ST	M95320-R	DIP 8	
ST	M95320-R	SOIC 8	PA16SO16D-EO-150
ST	M95320-R	TSSOP 8	PA8TSS8D
ST	M95320-R	TSSOP 8	PA24TSS24D
ST	M95320-R	TSSOP 14	PA14TSS14D
ST	M95320	DIP 8	
ST	M95320	SOIC 8	PA16SO16D-EO-150
ST	M95320	TSSOP 8	PA8TSS8D
ST	M95320	TSSOP 8	PA24TSS24D
ST	M95320	TSSOP 14	PA14TSS14D
ST	M95320-V	DIP 8	
ST	M95320-V	SOIC 8	PA16SO16D-EO-150
ST	M95320-V	TSSOP 8	PA8TSS8D
ST	M95320-V	TSSOP 8	PA24TSS24D
ST	M95320-V	TSSOP 14	PA14TSS14D
ST	M95320-W	DIP 8	
ST	M95320-W	SOIC 8	PA16SO16D-EO-150
ST	M95320-W	TSSOP 8	PA8TSS8D
ST	M95320-W	TSSOP 8	PA24TSS24D
ST	M95320-W	TSSOP 14	PA14TSS14D
ST	M95640-R	DIP 8	

ST	M95640-R	SOIC 8	PA16SO16D-EO-150
ST	M95640-R	TSSOP 8	PA8TSS8D
ST	M95640-R	TSSOP 8	PA24TSS24D
ST	M95640-R	TSSOP 14	PA14TSS14D
ST	M95640	DIP 8	
ST	M95640	SOIC 8	PA16SO16D-EO-150
ST	M95640	TSSOP 8	PA8TSS8D
ST	M95640	TSSOP 8	PA24TSS24D
ST	M95640	TSSOP 14	PA14TSS14D
ST	M95640-V	DIP 8	
ST	M95640-V	SOIC 8	PA16SO16D-EO-150
ST	M95640-V	TSSOP 8	PA8TSS8D
ST	M95640-V	TSSOP 8	PA24TSS24D
ST	M95640-V	TSSOP 14	PA14TSS14D
ST	M95640-W	DIP 8	
ST	M95640-W	SOIC 8	PA16SO16D-EO-150
ST	M95640-W	TSSOP 8	PA8TSS8D
ST	M95640-W	TSSOP 8	PA24TSS24D
ST	M95640-W	TSSOP 14	PA14TSS14D
ST	M95128	DIP 8	
ST	M95128(150)	SOIC 8	PA16SO16D-EO-150
ST	M95128(200)	SOIC 8	PA8SO8D-200
ST	M95128	TSSOP 8	PA8TSS8D
ST	M95128	TSSOP 8	PA24TSS24D
ST	M95128-V	DIP 8	
ST	M95128-V(150)	SOIC 8	PA16SO16D-EO-150
ST	M95128-V(200)	SOIC 8	PA8SO8D-200
ST	M95128-V	TSSOP 8	PA8TSS8D
ST	M95128-V	TSSOP 8	PA24TSS24D
ST	M95128-W	DIP 8	
ST	M95128-W(150)	SOIC 8	PA16SO16D-EO-150
ST	M95128-W(200)	SOIC 8	PA8SO8D-200
ST	M95128-W	TSSOP 8	PA8TSS8D
ST	M95128-W	TSSOP 8	PA24TSS24D
ST	M95128-R	DIP 8	
ST	M95128-R(150)	SOIC 8	PA16SO16D-EO-150
ST	M95128-R(200)	SOIC 8	PA8SO8D-200
ST	M95128-R	TSSOP 8	PA8TSS8D
ST	M95128-R	TSSOP 8	PA24TSS24D
ST	M95256	DIP 8	
ST	M95256(150)	SOIC 8	PA16SO16D-EO-150
ST	M95256(200)	SOIC 8	PA8SO8D-200
ST	M95256	TSSOP 8	PA8TSS8D
ST	M95256	TSSOP 8	PA24TSS24D
ST	M95256-V	DIP 8	
ST	M95256-V(150)	SOIC 8	PA16SO16D-EO-150
ST	M95256-V(200)	SOIC 8	PA8SO8D-200
ST	M95256-V	TSSOP 8	PA8TSS8D
ST	M95256-V	TSSOP 8	PA24TSS24D
ST	M95256-W	DIP 8	
ST	M95256-W(150)	SOIC 8	PA16SO16D-EO-150
ST	M95256-W(200)	SOIC 8	PA8SO8D-200
ST	M95256-W	TSSOP 8	PA8TSS8D
ST	M95256-W	TSSOP 8	PA24TSS24D
ST	M95256-R	DIP 8	
ST	M95256-R(150)	SOIC 8	PA16SO16D-EO-150
ST	M95256-R(200)	SOIC 8	PA8SO8D-200
ST	M95256-R	TSSOP 8	PA8TSS8D
ST	M95256-R	TSSOP 8	PA24TSS24D
ST	MK48T02	EDIP 24	
ST	MK48T12	EDIP 24	
ST	MK48T02B	EDIP 24	
ST	MK48T12B	EDIP 24	
ST	MK48Z02	EDIP 24	
ST	MK48Z12	EDIP 24	
ST	MK48Z02B	EDIP 24	
ST	MK48Z12B	EDIP 24	
ST	M48T12	EDIP 24	
ST	MK48T08	EDIP 28	
ST	MK48T18	EDIP 28	
ST	MK48T08B	EDIP 28	
ST	MK48T18B	EDIP 28	
ST	MK48Z08	EDIP 28	

ST	MK48Z18	EDIP 28	
ST	MK48Z08B	EDIP 28	
ST	MK48Z18B	EDIP 28	
ST	MK48Z09	EDIP 28	
ST	MK48Z19	EDIP 28	
ST	M48T58	EDIP 28	
ST	M48T58Y	EDIP 28	
ST	M48T35AY	EDIP 28	
ST	M48T35AV	EDIP 28	
ST	M48T35Y	EDIP 28	
ST	M48T35V	EDIP 28	
ST	M48Z128	EDIP 32	
ST	M48Z128V	EDIP 32	
ST	M48Z128Y	EDIP 32	
ST	M48Z129	EDIP 32	
ST	M48Z129V	EDIP 32	
ST	M48Z129Y	EDIP 32	
ST	M48Z35	EDIP 28	
ST	M48Z35Y	EDIP 28	
ST	M48Z256	EDIP 32	
ST	M48Z256Y	EDIP 32	
ST	NAND128W3A	TSOP 48	PA48TS48D
ST	NAND128W3A(+Spare)	TSOP 48	PA48TS48D
ST	NAND256W3A	TSOP 48	PA48TS48D
ST	NAND256W3A(+Spare)	TSOP 48	PA48TS48D
ST	NAND512W3A	TSOP 48	PA48TS48D
ST	NAND512W3A(+Spare)	TSOP 48	PA48TS48D
ST	NAND01GW3A	TSOP 48	PA48TS48D
ST	NAND01GW3A(+Spare)	TSOP 48	PA48TS48D
ST	NAND01GW3B	TSOP 48	PA48TS48D
ST	NAND01GW3B(+Spare)	TSOP 48	PA48TS48D
ST	NAND01GW3M2A	BGA 137	HA137BGA48DI
ST	NAND01GW3M2A(+Spare)	BGA 137	HA137BGA48DI
ST	NAND02GW3B	TSOP 48	PA48TS48D
ST	NAND02GW3B(+Spare)	TSOP 48	PA48TS48D
ST	NAND04GW3B	TSOP 48	PA48TS48D
ST	NAND04GW3B(+Spare)	TSOP 48	PA48TS48D
ST	NAND08GW3B-size4G	TSOP 48	PA48TS48D
ST	NAND08GW3B(+Spare)-size4G	TSOP 48	PA48TS48D
ST	ST24C02	DIP 8	
ST	ST24C02R	DIP 8	
ST	ST24W02	DIP 8	
ST	ST25C02	DIP 8	
ST	ST25W02	DIP 8	
ST	ST27128A	DIP 28	
ST	ST27256	DIP 28	
ST	ST2764A	DIP 28	
ST	ST27C256	DIP 28	
ST	ST93C46A	DIP 8	
ST	ST93C46A	SOIC 8	PA16SO16D-EO-150
ST	ST93C46C	DIP 8	
ST	ST93C46C	SOIC 8	PA16SO16D-EO-150
ST	ST93C46T	SOIC 8	PA16SO16D-EO-150
ST	ST93C47C	DIP 8	
ST	ST93C47C	SOIC 8	PA16SO16D-EO-150
ST	ST93C47T	SOIC 8	PA16SO16D-EO-150
ST	ST93C56	DIP 8	
ST	ST93C56	SOIC 8	PA16SO16D-EO-150
ST	ST93C56C	DIP 8	
ST	ST93C56C	SOIC 8	PA16SO16D-EO-150
ST	ST93C57C	DIP 8	
ST	ST93C57C	SOIC 8	PA16SO16D-EO-150
ST	ST93C66	DIP 8	
ST	ST93C66	SOIC 8	PA16SO16D-EO-150
ST	ST93C67	DIP 8	
ST	ST93C67	SOIC 8	PA16SO16D-EO-150
ST	ST93CS46	DIP 8	
ST	ST93CS46	SOIC 8	PA16SO16D-EO-150
ST	ST93CS47	DIP 8	
ST	ST93CS47	SOIC 8	PA16SO16D-EO-150
ST	ST93CS56	DIP 8	
ST	ST93CS56	SOIC 8	PA16SO16D-EO-150
ST	ST93CS57	DIP 8	

ST	ST93CS57	SOIC 8	PA16SO16D-EO-150
ST	ST93CS66	DIP 8	
ST	ST93CS66	SOIC 8	PA16SO16D-EO-150
ST	ST93CS67	DIP 8	
ST	ST93CS67	SOIC 8	PA16SO16D-EO-150
ST	TS27C256	DIP 28	
ST	TS27C64	DIP 28	
ST	TS27C64A	DIP 28	
ST	TS28C16A	DIP 24	
ST	TS28C17A	DIP 28	
ST	TS28C64	DIP 28	
SHARP	LH28F004SUT	TSOP 40	PA40TS40D
SHARP	LH28F008SAT	TSOP 40	PA40TS40D
SHARP	LH28F400BVE-BL	TSOP 48	PA48TS48D
SHARP	LH28F400BVE-TL	TSOP 48	PA48TS48D
SHARP	LH28F400SUE	TSOP 48	PA48TS48D
SHARP	LH28F800BJE	TSOP 48	PA48TS48D
SHARP	LH28F800BJHE-PTTLT6	TSOP 48	PA48TS48D
SHARP	LH28F800BJHE-PBTLT9	TSOP 48	PA48TS48D
SHARP	LH28F800BGHE	TSOP 48	PA48TS48D
SHARP	LH28F800BVHE	TSOP 48	PA48TS48D
SHARP	LH28F800SGE	TSOP 48	PA48TS48D
SHARP	LH28F160BJE	TSOP 48	PA48TS48D
SHARP	LH28F160BJE	TSOP 48	PA48TS48D
SHARP	LH28F160BJE-TTL	TSOP 48	PA48TS48D
SHARP	LH28F160BJE-BTL	TSOP 48	PA48TS48D
SHARP	LH28F160BJD-TTL	DIP 42	
SHARP	LH28F320BJE-PBTL	TSOP 48	PA48TS48D
SHARP	LH28F320BJHE-PTTL	TSOP 48	PA48TS48D
SHARP	LH28F320BFHE-PBTL	TSOP 48	PA48TS48D
SHARP	LH28F320BFHE-PTTL	TSOP 48	PA48TS48D
SHARP	LH5764	DIP 28	
SHARP	LH57128	DIP 28	
SHARP	LH57256	DIP 28	
SHARP	LH28F800B	BGA 48	CIC-48uBGA-44D-A6-YAM
SHARP	LH28F160B	BGA 48	CIC-48uBGA-44D-A6-YAM
SHARP	LHF00L09	BGA 48	HA48BG48DBG
SHARP	LHF00L35	PLCC 32	PA32PL32D
SHARP	LHF00L47	TSOP 40	PA40TS40D
SHARP	LRS1311	BGA 72	PA72BGA48D-A
SHARP	LRS1316A	BGA 72	PA72BGA48D-C
SHARP	LRS1337	BGA 72	PA72BGA48D-B
SHARP	LRS1349	BGA 72	PA72BGA48D-A
SHARP	LRS1331	BGA 72	PA72BGA48D-B
SHARP	LRS1342	BGA 72	PA72BGA48D-B
SHARP	LRS1325A	BGA 72	PA72BGA48D-A
SHARP	LRS1329	BGA 72	PA72BGA48D-A
SHARP	LRS1350	BGA 72	PA72BGA48D-A
SHARP	LRS1360	BGA 72	PA72BGA48D-B
SHARP	LRS1370	BGA 72	PA72BGA48D-B
SHARP	LRS1381A	BGA 72	PA72BGA48D-B
SHARP	LRS1383	BGA 72	PA72BGA48D-B
SHARP	LRS1386	BGA 72	PA72BGA48D-B
SHARP	LRS1387	BGA 72	PA72BGA48D-B
SHARP	LRS1805A	BGA 72	PA72BGA48D-B
SHARP	LRS1806A	BGA 72	PA72BGA48D-B
SHARP	LRS1815	BGA 72	PA72BGA48D-B
SHARP	LRS1816	BGA 72	PA72BGA48D-B
SHARP	LRS1825	BGA 72	PA72BGA48D-B
SHARP	LRS1826	BGA 72	PA72BGA48D-B
SHARP	LRS1828	BGA 72	PA72BGA48D-BB
SHARP	LRS1863	BGA 72	PA72BGA48D-BC
SHARP	LRS1850	BGA 72	PA72BGA48D-B
SHARP	LRS1864	BGA 72	PA72BGA48D-BC
SHARP	LRS1876	BGA 72	PA72BGA48D-BC
SIEMENS	SDA2506	DIP 8	
SIEMENS	SDE2506	DIP 8	
SIMTEK	STK20C04	DIP 28	
SANYO	LE25FS406	SOIC 8	PA16SO16D-EO-150
SILICON7	SV5C3238UBA	BGA 72	PA72BGA48DD-TO-8X11
SILICON7	SV5C3238UTA	BGA 72	PA72BGA48DD-TO-8X11
SILICON7	SV5C6416UDA	BGA 72	PA72BGA48DD-TO-8X11
SILICON7	SV5C2832UCA	BGA 72	PA72BGA48DE

SILICON7	SV5C2832UCR	BGA 72	PA72BGA48DE
SILICON7	SV5C2832UDR	BGA 72	PA72BGA48DE
SILICON7	SV5D2832UDA	BGA 88	PA88BGA48DA-YO-8X10
SILICON7	SV5D6416UBA	BGA 88	PA88BGA48DA-YO-8X10
SILICON7	SV5D6416UTA	BGA 88	PA88BGA48DA-YO-8X10
SILICON7	SV6C6416UTA	BGA 72	PA72BG48DK
SILICON7	SV6C6416UBA	BGA 72	PA72BG48DK
SILICON7	SV6C6432UTA	BGA 72	PA72BG48DK
SILICON7	SV6C6432UBA	BGA 72	PA72BG48DK
SILICON7	SV6C2832UTA	BGA 72	PA72BG48DK
SILICON7	SV6C2832UBA	BGA 72	PA72BG48DK
SILICON7	SV6C2864UTA	BGA 72	PA72BG48DK
SILICON7	SV6C2864UBA	BGA 72	PA72BG48DK
SMOS	SPM27C64	DIP 28	
SMOS	SPM27C64H	DIP 28	
SMOS	SPM27128	DIP 28	
SMOS	SPM27128C	DIP 28	
SMOS	SPM27C256	DIP 28	
SMOS	SPM2864C	DIP 28	
SPANSION	S25FL004A-M	SOP 8	PA20SO20D-EO-210
SPANSION	S25FL004A-N	CASON 8	PA8SON8D
SPANSION	S25FL040A-V-I	SOP 8	PA16SO16D-EO-150
SPANSION	S25FL040A-V-T	SOP 8	PA16SO16D-EO-150
SPANSION	S25FL040A-V-B	SOP 8	PA16SO16D-EO-150
SPANSION	S25FL040A-M-I	SOP 8	PA20SO20D-EO-210
SPANSION	S25FL040A-M-T	SOP 8	PA20SO20D-EO-210
SPANSION	S25FL040A-M-B	SOP 8	PA20SO20D-EO-210
SPANSION	S25FL040A-N-I	CASON 8	PA8SON8D
SPANSION	S25FL040A-N-T	CASON 8	PA8SON8D
SPANSION	S25FL040A-N-B	CASON 8	PA8SON8D
SPANSION	S25FL008A-M	SOP 8	PA20SO20D-EO-210
SPANSION	S25FL008A-N	CASON 8	PA8SON8D
SPANSION	S25FL008K-M	SOP 8	PA20SO20D-EO-210
SPANSION	S25FL016A-M	SOP 8	PA20SO20D-EO-210
SPANSION	S25FL016A-M	SOIC 16	PA28SO28D-EO-300
SPANSION	S25FL016A-N	CASON 8	PA8SON8D
SPANSION	S25FL016K-M	SOP 8	PA8SO8D-EO-150
SPANSION	S25FL032A-M	SOIC 16	PA28SO28D-EO-300
SPANSION	S25FL064A-M	SOIC 16	PA28SO28D-EO-300
SPANSION	S25FL164K-MF-00	SOIC 16	PA28SO28D-EO-300
SPANSION	S25FL164K-MF-01	SOIC 8	PA20SO20D-EO-210
SPANSION	S25FL164K-MF-Q1	SOIC 8	PA20SO20D-EO-210
SPANSION	S25FL164K-NF-01	WSON 8	PA8SON8D
SPANSION	S25FL164K-NF-Q1	WSON 8	PA8SON8D
SPANSION	S25FL164K-BH-02	BGA 24	NA24BG48DA
SPANSION	S25FL164K-BH-S3	BGA 24	NA24BG48D-D
SPANSION	S25FL164K-BH-03	BGA 24	NA24BG48D-D
SPANSION	S25FL208K-MF-01	SOIC 8	PA20SO20D-EO-210
SPANSION	S25FL208K-MF-04	SOIC 8	PA16SO16D-EO-150
SPANSION	S25FL216K-MF-01	SOIC 8	PA20SO20D-EO-210
SPANSION	S25FL216K-MF-04	SOIC 8	PA16SO16D-EO-150
SPANSION	S25FL204K	SOP 8	PA16SO16D-EO-150
SPANSION	S25FL204K	SOP 8	PA20SO20D-EO-210
SPANSION	S25FL204K-MF-01	SOP 8	PA20SO20D-EO-210
SPANSION	S25FL204K-MF-04	SOP 8	PA16SO16D-EO-150
SPANSION	S25FL116K	WSON 8	PA8SON8D
SPANSION	S25FL116K	SOIC 8	PA16SO16D-EO-150
SPANSION	S25FL132K	SOIC 8	PA20SO20D-EO-210
SPANSION	S25FL132K	SOIC 8	PA16SO16D-EO-150
SPANSION	S25FL116K-BH-02	BGA 24	NA24BG48DA
SPANSION	S25FL116K-BH-S2	BGA 24	NA24BG48DA
SPANSION	S25FL116K-NF-01	WSON 8	PA8SON8D
SPANSION	S25FL132K-BH-S2	BGA 24	NA24BG48DA
SPANSION	S25FL132K-BH-02	BGA 24	NA24BG48DA
SPANSION	S25FL132K-BH-S3	BGA 24	NA24BG48D-D
SPANSION	S25FL132K-BH-03	BGA 24	NA24BG48D-D
SPANSION	S25FL032PIF	SOIC 16	PA28SO28D-EO-300
SPANSION	S25FL032PIF	SOIC 8	PA20SO20D-EO-210
SPANSION	S25FL032PIF	USON 8	PA8SON8D
SPANSION	S25FL032PIF	BGA 24	NA24BG48DA
SPANSION	S25FL032P-BH-S2	BGA 24	NA24BG48DA
SPANSION	S25FL064PIF	USON 8	PA8SON8DA
SPANSION	S25FL064PIF	SOIC 16	PA28SO28D-EO-300

SPANSION	S25FL127S-MF-10	SOIC 8	PA20SO20D-EO-210
SPANSION	S25FL127S-NF-10	WSON 8	PA8SON8D
SPANSION	S25FL127S-BH-00	BGA 24	NA24BG48DA
SPANSION	S25FL128PxxMFI00(FL128PIF)	DIP 24	HA48BGA48DAO
SPANSION	S25FL128PxxMFI01(FL128PIFL)	DIP 24	HA48BGA48DAO
SPANSION	S25FL128PxxNFI00(FL128PIF)	DIP 24	HA48BGA48DAO
SPANSION	S25FL128PxxNFI01(FL128PIFL)	DIP 24	HA48BGA48DAO
SPANSION	S25FL128PxxNFI00(FL128PIF)	DIP 24	HA48BGA48DAO
SPANSION	S25FL128PxxNFI01(FL128PIFL)	DIP 24	HA48BGA48DAO
SPANSION	S25FL128SxxMFI00	SOIC 16	PA28SO28D-EO-300
SPANSION	S25FL128SxxMFI01	SOIC 16	PA28SO28D-EO-300
SPANSION	S25FL128SxxNFI00	WSON 8	PA8SON20D
SPANSION	S25FL128SxxNFI01	WSON 8	PA8SON20D
SPANSION	S25FL128SxxNFI00	WSON 8	PA8SON8DA
SPANSION	S25FL128SxxNFI01	WSON 8	PA8SON8DA
SPANSION	S25FL129PxxMFI00(FL129PIF)	DIP 24	HA48BGA48DAO
SPANSION	S25FL129PxxMFI01(FL129PIF)	DIP 24	HA48BGA48DAO
SPANSION	S25FL129PIF	WSON 8	PA8SON8DA
SPANSION	S25FL256S-MF-00	SOIC 16	PA28SO28D-EO-300
SPANSION	S25FL256S-MF-01	SOIC 16	PA28SO28D-EO-300
SPANSION	S25FL128S-BH-A0	BGA 24	NA24BG48DA
SPANSION	S25FL128S-BH-20	BGA 24	NA24BG48DA
SPANSION	S25FL256S-BH-20	BGA 24	NA24BG48DA
SPANSION	S25FL256S-BH-21	BGA 24	NA24BG48DA
SPANSION	S25FL256S-BH-A0	BGA 24	NA24BG48DA
SPANSION	S25FS128SA1	BGA 24	NA24BG48DA
SPANSION	S25FL128S-MF-00	SOIC 16	PA28SO28D-EO-300
SPANSION	S25FL128S-MF-G0	SOIC 16	PA28SO28D-EO-300
SPANSION	S25FL128S-MF-G1	SOIC 16	PA28SO28D-EO-300
SPANSION	S25FL256S-MF-G0	SOIC 16	PA28SO28D-EO-300
SPANSION	S25FL256S-MF-G1	SOIC 16	PA28SO28D-EO-300
SPANSION	S25FS128S-MF-10	SOIC 8	HA8SO48DAC
SPANSION	S25FS128S-MF-1D	SOIC 8	HA8SO48DAC
SPANSION	S25FS128S-NF-01	WSON 8	HA8SON48DG
SPANSION	S25FL132K-NF-01	WSON 8	PA8SON8D
SPANSION	S25FL132K-MF-01	SOIC 8	PA20SO20D-EO-210
SPANSION	S25FL132K-MF-04	SOIC 8	PA16SO16D-EO-150
SPANSION	S25FL132K-MF-Q1	SOIC 8	PA20SO20D-EO-210
SPANSION	S25FL512S-BH-31	BGA 24	NA24BG48D-D
SPANSION	S25FL512S-BH-C1	BGA 24	NA24BG48DA
SPANSION	S25FL512S-MF-01	SOIC 16	PA28SO28D-EO-300
SPANSION	S25FL512S-BH-D1	BGA 24	NA24BG48D-D
SPANSION	S25FL512S-BH-21	BGA 24	NA24BG48DA
SPANSION	S29AL002-S-02	SOP 44	PA44SO44D
SPANSION	S29AL002-T-02	TSOP 48	PA48TS48D
SPANSION	S29AL002-B-02	BGA 48	PA48BG48DW
SPANSION	S29AL002-B-02	BGA 48	HA48BG48DAI
SPANSION	S29AL002-S-01	SOP 44	PA44SO44D
SPANSION	S29AL002-T-01	TSOP 48	PA48TS48D
SPANSION	S29AL002-B-01	BGA 48	PA48BG48DW
SPANSION	S29AL002-B-01	BGA 48	HA48BG48DAI
SPANSION	S29AL004-S-02	SOP 44	PA44SO44D
SPANSION	S29AL004-T-02	TSOP 48	PA48TS48D
SPANSION	S29AL004-B-02	BGA 48	PA48BG48DW
SPANSION	S29AL004-B-02	BGA 48	HA48BG48DAI
SPANSION	S29AL004-S-01	SOP 44	PA44SO44D
SPANSION	S29AL004-T-01	TSOP 48	PA48TS48D
SPANSION	S29AL004-B-01	BGA 48	PA48BG48DW
SPANSION	S29AL004-B-01	BGA 48	HA48BG48DAI
SPANSION	S29AL008-S-02	SOP 44	PA44SO44D
SPANSION	S29AL008-T-02	TSOP 48	PA48TS48D
SPANSION	S29AL008-B-02	BGA 48	PA48BG48DW
SPANSION	S29AL008-B-02	BGA 48	HA48BG48DAI
SPANSION	S29AL008-S-01	SOP 44	PA44SO44D
SPANSION	S29AL008-T-01	TSOP 48	PA48TS48D
SPANSION	S29AL008-B-01	BGA 48	PA48BG48DW
SPANSION	S29AL008-B-01	BGA 48	HA48BG48DAI
SPANSION	S29AL008D-M-02	SOP 44	PA44SO44D
SPANSION	S29AL008D-T-02	TSOP 48	PA48TS48D
SPANSION	S29AL008D-B-02	BGA 48	PA48BG48DAI
SPANSION	S29AL008D-M-01	SOP 44	PA44SO44D
SPANSION	S29AL008D-T-01	TSOP 48	PA48TS48D
SPANSION	S29AL008D-B-01	BGA 48	PA48BG48DAI



SPANSION	S29AL008D-M-R2	SOP 44	PA44SO44D
SPANSION	S29AL008D-T-R2	TSOP 48	PA48TS48D
SPANSION	S29AL008D-B-R2	BGA 48	PA48BG48DAI
SPANSION	S29AL008D-M-R1	SOP 44	PA44SO44D
SPANSION	S29AL008D-T-R1	TSOP 48	PA48TS48D
SPANSION	S29AL008D-B-R1	BGA 48	PA48BG48DAI
SPANSION	S29AL016-S-02	SOP 44	PA44SO44D
SPANSION	S29AL016-T-02	TSOP 48	PA48TS48D
SPANSION	S29AL016-S-01	SOP 44	PA44SO44D
SPANSION	S29AL016-T-01	TSOP 48	PA48TS48D
SPANSION	S29AL016M-T-01	TSOP 48	PA48TS48D
SPANSION	S29AL016M-T-02	TSOP 48	PA48TS48D
SPANSION	S29AL016M-T-R1	TSOP 48	PA48TS48D
SPANSION	S29AL016M-T-R2	TSOP 48	PA48TS48D
SPANSION	S29AL016MB	TSOP 48	PA48TS48D
SPANSION	S29AL016DB	TSOP 48	PA48TS48D
SPANSION	S29AL016DT	TSOP 48	PA48TS48D
SPANSION	S29AL016D-M-02	SOP 44	PA44SO44D
SPANSION	S29AL032D	TSOP 40	PA40TS40D
SPANSION	S29AL032D-T-03	TSOP 48	PA48TS48D1
SPANSION	S29AL032D-T-04	TSOP 48	PA48TS48D1
SPANSION	S29AL008J-T-01	TSOP 48	PA48TS48D1
SPANSION	S29AL008J-T-02	TSOP 48	PA48TS48D1
SPANSION	S29AL008J-T-03	TSOP 48	PA48TS48D1
SPANSION	S29AL008J-T-04	TSOP 48	PA48TS48D1
SPANSION	S29AL016J-T-01	TSOP 48	PA48TS48D1
SPANSION	S29AL016J-T-02	TSOP 48	PA48TS48D1
SPANSION	S29AL016J-T-03	TSOP 48	PA48TS48D1
SPANSION	S29AL016J-T-04	TSOP 48	PA48TS48D1
SPANSION	S29AL008J-B-01	BGA 48	PA48BG48DW
SPANSION	S29AL008J-B-02	BGA 48	PA48BG48DW
SPANSION	S29AL008J-B-03	BGA 48	PA48BG48DW
SPANSION	S29AL008J-B-04	BGA 48	PA48BG48DW
SPANSION	S29AL016J-B-01	BGA 48	PA48BG48DW
SPANSION	S29AL016J-B-02	BGA 48	PA48BG48DW
SPANSION	S29AL016J-B-03	BGA 48	PA48BG48DW
SPANSION	S29AL016J-B-04	BGA 48	PA48BG48DW
SPANSION	S29AS016J-B-01	BGA 48	PA48BG48DW
SPANSION	S29AS016J-B-02	BGA 48	PA48BG48DW
SPANSION	S29AS008J-B-01	BGA 48	PA48BG48DW
SPANSION	S29AS008J-B-02	BGA 48	PA48BG48DW
SPANSION	S29AL008J-B-01	BGA 48	HA48BG48DAI
SPANSION	S29AL008J-B-02	BGA 48	HA48BG48DAI
SPANSION	S29AL008J-B-03	BGA 48	HA48BG48DAI
SPANSION	S29AL008J-B-04	BGA 48	HA48BG48DAI
SPANSION	S29AL016J-B-01	BGA 48	HA48BG48DAI
SPANSION	S29AL016J-B-02	BGA 48	HA48BG48DAI
SPANSION	S29AL016J-B-03	BGA 48	HA48BG48DAI
SPANSION	S29AL016J-B-04	BGA 48	HA48BG48DAI
SPANSION	S29AS016J-B-01	BGA 48	HA48BG48DAI
SPANSION	S29AS016J-B-02	BGA 48	HA48BG48DAI
SPANSION	S29AS008J-B-01	BGA 48	HA48BG48DAI
SPANSION	S29AS008J-B-02	BGA 48	HA48BG48DAI
SPANSION	S29AS016J-T-01	TSOP 48	PA48TS48D1
SPANSION	S29AS016J-T-02	TSOP 48	PA48TS48D1
SPANSION	S29AS008J-T-01	TSOP 48	PA48TS48D1
SPANSION	S29AS008J-T-02	TSOP 48	PA48TS48D1
SPANSION	S29GL016A-TF-R1	TSOP 48	PA48TS48D1
SPANSION	S29GL016A-TF-R2	TSOP 48	PA48TS48D1
SPANSION	S29GL032A-TF-R1	TSOP 56	PA56TS48DB
SPANSION	S29GL032A-TF-R2	TSOP 56	PA56TS48DB
SPANSION	S29GL032A-TF-R3	TSOP 48	PA48TS48D1
SPANSION	S29GL032A-TF-R4	TSOP 48	PA48TS48D1
SPANSION	S29GL032A-FF-S1	BGA 64	PA64BG48DG
SPANSION	S29GL032A-FF-S2	BGA 64	PA64BG48DG
SPANSION	S29GL032A-FF-S3	BGA 64	PA64BG48DH
SPANSION	S29GL032A-FF-S4	BGA 64	PA64BG48DH
SPANSION	S29GL064A-TF-R1	TSOP 56	PA56TS48DB
SPANSION	S29GL064A-TF-R2	TSOP 56	PA56TS48DB
SPANSION	S29GL064A-TF-R3	TSOP 48	PA48TS48D1
SPANSION	S29GL064A-TF-R4	TSOP 48	PA48TS48D1
SPANSION	S29GL064A-TF-R6	TSOP 48	PA48TS48D1
SPANSION	S29GL064A-TF-R7	TSOP 48	PA48TS48D1

SPANSION	S29GL064A-FF-S1	BGA 64	PA64BG48DG
SPANSION	S29GL064A-FF-S2	BGA 64	PA64BG48DG
SPANSION	S29GL064A-FF-S3	BGA 64	PA64BG48DH
SPANSION	S29GL064A-FF-S4	BGA 64	PA64BG48DH
SPANSION	S29GL032M-R0	TSOP 40	PA40TS40D
SPANSION	S29GL032M-R3	TSOP 48	PA48TS48D
SPANSION	S29GL032M-R3	BGA 48	PA48BG48DAO/DAO1
SPANSION	S29GL032M-R4(+SecSi)	TSOP 48	PA48TS48D
SPANSION	S29GL032M-R4	TSOP 48	PA48TS48D
SPANSION	S29GL032M-R4	BGA 48	PA48BG48DAO/DAO1
SPANSION	S29GL032M-R5	TSOP 48	PA48TS48D
SPANSION	S29GL032M-R5	BGA 48	PA48BG48DAO/DAO1
SPANSION	S29GL032M-R6	TSOP 48	PA48TS48D
SPANSION	S29GL032M-R6	BGA 48	PA48BG48DAO/DAO1
SPANSION	S29GL032M-FA-S1	BGA 64	PA64BG48DG
SPANSION	S29GL032M-FA-S2	BGA 64	PA64BG48DG
SPANSION	S29GL032M-FA-S3	BGA 64	PA64BG48DH
SPANSION	S29GL032M-FA-S4	BGA 64	PA64BG48DH
SPANSION	S29GL032M-FF-S1	BGA 64	PA64BG48DG
SPANSION	S29GL032M-FF-S2	BGA 64	PA64BG48DG
SPANSION	S29GL032M-FF-S3	BGA 64	PA64BG48DH
SPANSION	S29GL032M-FF-S4	BGA 64	PA64BG48DH
SPANSION	S29GL064M-R1	TSOP 56	PA56TS48DB
SPANSION	S29GL064M-R2	TSOP 56	PA56TS48DB
SPANSION	S29GL064M-R3	TSOP 48	PA48TS48D
SPANSION	S29GL064M-R4	TSOP 48	PA48TS48D
SPANSION	S29GL064M-R6	TSOP 48	PA48TS48D
SPANSION	S29GL064M-R7	TSOP 48	PA48TS48D
SPANSION	S29GL064M-FA-S1	BGA 64	PA64BG48DG
SPANSION	S29GL064M-FA-S2	BGA 64	PA64BG48DG
SPANSION	S29GL064M-FA-S3	BGA 64	PA64BG48DH
SPANSION	S29GL064M-FA-S4	BGA 64	PA64BG48DH
SPANSION	S29GL064M-FF-S1	BGA 64	PA64BG48DG
SPANSION	S29GL064M-FF-S2	BGA 64	PA64BG48DG
SPANSION	S29GL064M-FF-S3	BGA 64	PA64BG48DH
SPANSION	S29GL064M-FF-S4	BGA 64	PA64BG48DH
SPANSION	S29GL032N-FF-01	BGA 64	PA64BG48DG
SPANSION	S29GL032N-FF-02	BGA 64	PA64BG48DG
SPANSION	S29GL032N-FF-03	BGA 64	PA64BG48DG
SPANSION	S29GL032N-FF-04	BGA 64	PA64BG48DG
SPANSION	S29GL032N-FF-S1	BGA 64	PA64BG48DG
SPANSION	S29GL032N-FF-S2	BGA 64	PA64BG48DG
SPANSION	S29GL032N-FF-S3	BGA 64	PA64BG48DH
SPANSION	S29GL032N-FF-S4	BGA 64	PA64BG48DH
SPANSION	S29GL064N-FF-01	BGA 64	PA64BG48DG
SPANSION	S29GL064N-FF-01	BGA 64	PA64BG48DK
SPANSION	S29GL064N-FF-02	BGA 64	PA64BG48DG
SPANSION	S29GL064N-FF-03	BGA 64	PA64BG48DG
SPANSION	S29GL064N-FF-04	BGA 64	PA64BG48DG
SPANSION	S29GL064N-FF-S1	BGA 64	PA64BG48DG
SPANSION	S29GL064N-FF-S2	BGA 64	PA64BG48DG
SPANSION	S29GL064N-FF-S3	BGA 64	PA64BG48DH
SPANSION	S29GL064N-FF-S4	BGA 64	PA64BG48DH
SPANSION	S29GL064N-FF-R2	BGA 64	PA64BG48DG
SPANSION	S29GL032N-TF-01	TSOP 56	PA56TS48DB
SPANSION	S29GL032N-TF-02	TSOP 56	PA56TS48DB
SPANSION	S29GL032N-TF-03	TSOP 48	PA48TS48D1
SPANSION	S29GL032N-TF-04	TSOP 48	PA48TS48D1
SPANSION	S29GL032N-B-03	BGA 48	PA48BG48DW
SPANSION	S29GL032N-B-04	BGA 48	PA48BG48DW
SPANSION	S29GL032N-B-03	BGA 48	HA48BG48DAI
SPANSION	S29GL032N-B-04	BGA 48	HA48BG48DAI
SPANSION	S29GL064N-TF-V1	TSOP 56	PA56TS48DB
SPANSION	S29GL064N-TF-02	TSOP 56	PA56TS48DB
SPANSION	S29GL064N-TF-03	TSOP 48	PA48TS48D1
SPANSION	S29GL064N-TF-04	TSOP 48	PA48TS48D1
SPANSION	S29GL064N-B-03	BGA 48	PA48BG48DW
SPANSION	S29GL064N-B-04	BGA 48	PA48BG48DW
SPANSION	S29GL064N-B-03	BGA 48	HA48BG48DAI
SPANSION	S29GL064N-B-04	BGA 48	HA48BG48DAI
SPANSION	S29GL064N-TF-R3	TSOP 48	PA48TS48D1
SPANSION	S29GL064N-TF-R3(+SecSi)	TSOP 48	PA48TS48D1
SPANSION	S29GL064N-TF-R4	TSOP 48	PA48TS48D1

SPANSION	S29GL064N-TF-06	TSOP 48	PA48TS48D1
SPANSION	S29GL064N-TF-07	TSOP 48	PA48TS48D1
SPANSION	S29GL064S-BH-03	BGA 48	HA48BG48DAI
SPANSION	S29GL064S-BH-04	BGA 48	HA48BG48DAI
SPANSION	S29GL064S-FH-01	BGA 64	PA64BG48DG
SPANSION	S29GL064S-FH-02	BGA 64	PA64BG48DG
SPANSION	S29GL064S-FH-03	BGA 64	PA64BG48DG
SPANSION	S29GL064S-FH-04	BGA 64	PA64BG48DG
SPANSION	S29GL128M-R1	TSOP 56	PA56TS48DB
SPANSION	S29GL128M-R2	TSOP 56	PA56TS48DB
SPANSION	S29GL256M-R1	TSOP 56	PA56TS48DC
SPANSION	S29GL256M-R2	TSOP 56	PA56TS48DC
SPANSION	S29GL128NxxTxxR2	TSOP 56	PA56TS48DB
SPANSION	S29GL256NxxTxxR2	TSOP 56	PA56TS48DC
SPANSION	S29GL128NxxTxx01	TSOP 56	PA56TS48DB
SPANSION	S29GL256NxxTxx01	TSOP 56	PA56TS48DC
SPANSION	S29GL512NxxTxx01	TSOP 56	PA56TS48DD
SPANSION	S29GL128NxxTxx02	TSOP 56	PA56TS48DB
SPANSION	S29GL256NxxTxx02	TSOP 56	PA56TS48DC
SPANSION	S29GL512NxxTxx02	TSOP 56	PA56TS48DD
SPANSION	S29GL128NxxTxxV1	TSOP 56	PA56TS48DB
SPANSION	S29GL256NxxTxxV1	TSOP 56	PA56TS48DC
SPANSION	S29GL512NxxTxxV1	TSOP 56	PA56TS48DD
SPANSION	S29GL128NxxTxxV2	TSOP 56	PA56TS48DB
SPANSION	S29GL256NxxTxxV2	TSOP 56	PA56TS48DC
SPANSION	S29GL512NxxTxxV2	TSOP 56	PA56TS48DD
SPANSION	S29GL128NxxFxx01	BGA 64	PA64BG48DK
SPANSION	S29GL256NxxFxx01	BGA 64	PA64BG48DK
SPANSION	S29GL512NxxFxx01	BGA 64	PA64BG48DK
SPANSION	S29GL128NxxFxx02	BGA 64	PA64BG48DK
SPANSION	S29GL256NxxFxx02	BGA 64	PA64BG48DK
SPANSION	S29GL512NxxFxx02	BGA 64	PA64BG48DK
SPANSION	S29GL128NxxFxxV1	BGA 64	PA64BG48DK
SPANSION	S29GL256NxxFxxV1	BGA 64	PA64BG48DK
SPANSION	S29GL512NxxFxxV1	BGA 64	PA64BG48DK
SPANSION	S29GL128NxxFxxV2	BGA 64	PA64BG48DK
SPANSION	S29GL256NxxFxxV2	BGA 64	PA64BG48DK
SPANSION	S29GL512NxxFxxV2	BGA 64	PA64BG48DK
SPANSION	S29GL128PxxTxx01	TSOP 56	PA56TS48DD
SPANSION	S29GL128PxxTxxR1	TSOP 56	PA56TS48DB
SPANSION	S29GL128PxxTxxR1	TSOP 56	PA56TS48DC
SPANSION	S29GL128PxxTxxR1	TSOP 56	PA56TS48DD
SPANSION	S29GL128PxxTxxR2	TSOP 56	PA56TS48DB
SPANSION	S29GL128PxxTxxR2	TSOP 56	PA56TS48DC
SPANSION	S29GL128PxxTxxR2	TSOP 56	PA56TS48DD
SPANSION	S29GL256PxxTxx01	TSOP 56	PA56TS48DD
SPANSION	S29GL256PxxTxx02	TSOP 56	PA56TS48DD
SPANSION	S29GL256PxxTxxR1	TSOP 56	PA56TS48DD
SPANSION	S29GL256PxxTxxR2	TSOP 56	PA56TS48DD
SPANSION	S29GL256PxxTxxV1	TSOP 56	PA56TS48DD
SPANSION	S29GL256PxxTxxV2	TSOP 56	PA56TS48DD
SPANSION	S29GL512PxxTxx01	TSOP 56	HA56TS48DI
SPANSION	S29GL128PxxFxx01	BGA 64	PA64BG48DK
SPANSION	S29GL128PxxFxx02	BGA 64	PA64BG48DK
SPANSION	S29GL128PxxFxxV1	BGA 64	PA64BG48DK
SPANSION	S29GL128PxxFxxV2	BGA 64	PA64BG48DK
SPANSION	S29GL128PxxFxxR1	BGA 64	PA64BG48DK
SPANSION	S29GL128PxxFxxR2	BGA 64	PA64BG48DK
SPANSION	S29GL256PxxFxx01	BGA 64	PA64BG48DK
SPANSION	S29GL256PxxFxx02	BGA 64	PA64BG48DK
SPANSION	S29GL256PxxFxxV1	BGA 64	PA64BG48DK
SPANSION	S29GL256PxxFxxV2	BGA 64	PA64BG48DK
SPANSION	S29GL128P-FF-S0	BGA 64	HA64BG48DQ
SPANSION	S29GL128P-FF-S1	BGA 64	PA64BG48DK
SPANSION	S29GL128P-FF-S2	BGA 64	PA64BG48DK
SPANSION	S29GL128P-FF-S3	BGA 64	HA64BG48DQ
SPANSION	S29GL128P-FF-S4	BGA 64	HA64BG48DQ
SPANSION	S29GL128P-FF-S7	BGA 64	PA64BG48DK
SPANSION	S29GL128P-FF-S9	BGA 64	HA64BG48DQ
SPANSION	S29GL256P-FF-S0	BGA 64	HA64BG48DQ
SPANSION	S29GL256P-FF-S1	BGA 64	PA64BG48DK
SPANSION	S29GL256P-FF-S2	BGA 64	PA64BG48DK
SPANSION	S29GL256P-FF-S3	BGA 64	HA64BG48DQ

SPANSION	S29GL256P-FF-S4	BGA 64	HA64BG48DQ
SPANSION	S29GL256P-FF-S7	BGA 64	PA64BG48DK
SPANSION	S29GL256P-FF-S8	BGA 64	PA64BG48DK
SPANSION	S29GL256P-FF-S9	BGA 64	HA64BG48DQ
SPANSION	S29GL512PxxFxx01	BGA 64	PA64BG48DK
SPANSION	S29GL512PxxFxx02	BGA 64	PA64BG48DK
SPANSION	S29GL512PxxFxxV1	BGA 64	PA64BG48DK
SPANSION	S29GL512PxxFxxV2	BGA 64	PA64BG48DK
SPANSION	S29GL512P-FF-S1	BGA 64	PA64BG48DK
SPANSION	S29GL512P-FF-S2	BGA 64	PA64BG48DK
SPANSION	S29GL512P-FF-S7	BGA 64	PA64BG48DK
SPANSION	S29GL512P-FF-S8	BGA 64	PA64BG48DK
SPANSION	S29GL512P-TF-R1	TSOP 56	PA56TS48DD
SPANSION	S29GL512RxxTxxR1	TSOP 56	PA56TS48DD
SPANSION	S29GL512RxxTxx01	TSOP 56	PA56TS48DD
SPANSION	S29GL512RxxTxx02	TSOP 56	PA56TS48DD
SPANSION	S29GL128S-TF-01	TSOP 56	PA56TS48DD
SPANSION	S29GL128S-TF-02	TSOP 56	PA56TS48DD
SPANSION	S29GL128S-TF-V1	TSOP 56	PA56TS48DD
SPANSION	S29GL128S-TF-V2	TSOP 56	PA56TS48DD
SPANSION	S29GL128S-GH-01	BGA 56	NA56BG48DU
SPANSION	S29GL128S-GH-02	BGA 56	NA56BG48DU
SPANSION	S29GL256S-TF-01	TSOP 56	PA56TS48DD
SPANSION	S29GL256S-TF-02	TSOP 56	PA56TS48DD
SPANSION	S29GL256S-TF-V1	TSOP 56	PA56TS48DD
SPANSION	S29GL256S-TF-V2	TSOP 56	PA56TS48DD
SPANSION	S29GL256S-FH-S6	BGA 64	PA64BG48DR
SPANSION	S29GL256S-DH-S6	BGA 64	NA64BG48DY
SPANSION	S29GL256S-GH-01	BGA 56	NA56BG48DU
SPANSION	S29GL256S-GH-02	BGA 56	NA56BG48DU
SPANSION	S29GL512S-TF-01	TSOP 56	PA56TS48DD
SPANSION	S29GL512S-TF-02	TSOP 56	PA56TS48DD
SPANSION	S29GL512S-TF-V1	TSOP 56	PA56TS48DD
SPANSION	S29GL512S-TF-V2	TSOP 56	PA56TS48DD
SPANSION	S29GL512S-FH-S6	BGA 64	PA64BG48DR
SPANSION	S29GL01GS-DH-S5	BGA 64	NA64BG48DY
SPANSION	S29GL01GS-DH-S6	BGA 64	NA64BG48DY
SPANSION	S29GL512PxxFxx01	BGA 64	PA64BG48DR
SPANSION	S29JL032H-01	TSOP 48	PA48TS48D1
SPANSION	S29JL032H-02	TSOP 48	PA48TS48D1
SPANSION	S29JL032H-21	TSOP 48	PA48TS48D1
SPANSION	S29JL032H-22	TSOP 48	PA48TS48D1
SPANSION	S29JL032H-31	TSOP 48	PA48TS48D1
SPANSION	S29JL032H-32	TSOP 48	PA48TS48D1
SPANSION	S29JL032H-41	TSOP 48	PA48TS48D1
SPANSION	S29JL032H-42	TSOP 48	PA48TS48D1
SPANSION	S29JL064H	TSOP 48	PA48TS48D1
SPANSION	S29PL032J12	BGA 48	HA48BG48DAS
SPANSION	S71JL064HB0	BGA 73	PA73BGA48DC-YO-8X11.6
SPANSION	S71JL128HB0	BGA 73	PA73BGA48DC-YO-8X11.6
SPANSION	S71PL032JA0	BGA 56	HA56BG48DH
SPANSION	S71GL032N	BGA 56	HA56BG48DH
SPANSION	S71PL064JA0	BGA 56	HA56BG48DH
SPANSION	S71GL064N	BGA 56	HA56BG48DH
SPANSION	S71PL127NB0	BGA 64	HA64BG48DF
SPANSION	S71PL127NC0	BGA 64	HA64BG48DF
SPANSION	S71PL129JA0	BGA 73	PA73BGA48DC-YO-8X11.6
SPANSION	S71PL129JB0	BGA 64	HA64BG48DF
SPANSION	S71PL129JC0	BGA 64	HA64BG48DF
SPANSION	S99PL193JC0	BGA 73	PA73BG48DG
SPANSION	S34ML02G100TFI00	TSOP 48	PA48TS48D
SPANSION	S34ML02G100T(+Spare)	TSOP 48	PA48TS48D
SPANSION	S34ML04G100TFI00	TSOP 48	PA48TS48D
SPANSION	S34ML04G100T(+Spare)	TSOP 48	PA48TS48D
MICROCHIP	SST28LF040	DIP 32	
MICROCHIP	SST28LF040	PLCC 32	PA32PL32D
MICROCHIP	SST28LF040	TSOP 32	PA32TS20/PA32TS32D-20
MICROCHIP	SST28SF040	DIP 32	
MICROCHIP	SST28SF040	PLCC 32	PA32PL32D
MICROCHIP	SST28SF040	TSOP 32	PA32TS20/PA32TS32D-20
MICROCHIP	SST28SF040A	DIP 32	
MICROCHIP	SST28SF040A	PLCC 32	PA32PL32D
MICROCHIP	SST28SF040A	TSOP 32	PA32TS20/PA32TS32D-20

MICROCHIP	SST28VF040	DIP 32	
MICROCHIP	SST28VF040	PLCC 32	PA32PL32D
MICROCHIP	SST28VF040	TSOP 32	PA32TS20/PA32TS32D-20
MICROCHIP	SST28VF040A	DIP 32	
MICROCHIP	SST28VF040A	PLCC 32	PA32PL32D
MICROCHIP	SST28VF040A	TSOP 32	PA32TS20/PA32TS32D-20
MICROCHIP	PH28EE011	DIP 32	
MICROCHIP	SST25WF512	SOIC 8	PA16SO16D-EO-150
MICROCHIP	SST25WF010	SOIC 8	PA16SO16D-EO-150
MICROCHIP	SST25WF020	SOIC 8	PA16SO16D-EO-150
MICROCHIP	SST25WF040	SOIC 8	PA20SO20D-EO-210
MICROCHIP	SST25WF040	SOIC 8	PA16SO16D-EO-150
MICROCHIP	SST25WF080	SOIC 8	PA20SO20D-EO-210
MICROCHIP	SST25WF080	SOIC 8	PA16SO16D-EO-150
MICROCHIP	SST25VF512	SOIC 8	PA16SO16D-EO-150
MICROCHIP	SST25VF512	WSON 8	PA8SON8D
MICROCHIP	SST25VF512A	SOIC 8	PA16SO16D-EO-150
MICROCHIP	SST25VF512A	WSON 8	PA8SON8D
MICROCHIP	SST25VF010	SOIC 8	PA16SO16D-EO-150
MICROCHIP	SST25VF010A	WSON 8	PA8SON8D
MICROCHIP	SST25VF010A	SOIC 8	PA16SO16D-EO-150
MICROCHIP	SST25VF020	WSON 8	PA8SON8D
MICROCHIP	SST25VF020	SOIC 8	PA16SO16D-EO-150
MICROCHIP	SST25VF040	WSON 8	PA8SON8D
MICROCHIP	SST25VF040	SOIC 8	PA20SO20D-EO-210
MICROCHIP	SST25VF040B	WSON 8	PA8SON8D
MICROCHIP	SST25VF040B	SOIC 8	PA16SO16D-EO-150
MICROCHIP	SST25PF040C-SN	WSON 8	PA8SON8D
MICROCHIP	SST25PF040C-MF	USON 8	HBP8USON48DB
MICROCHIP	SST25PF040C-NP	SOIC 8	PA20SO20D-EO-210
MICROCHIP	SST25VF080B	WSON 8	PA8SON8D
MICROCHIP	SST25VF080B	SOIC 8	PA20SO20D-EO-210
MICROCHIP	SST25VF016B	WSON 8	PA8SON8D
MICROCHIP	SST25VF016B	SOIC 8	PA20SO20D-EO-210
MICROCHIP	SST25VF032B	SOIC 16	PA20SO20D-EO-210
MICROCHIP	SST25VF032B	SOIC 16	PA28SO28D-EO-300
MICROCHIP	SST25VF064C	SOIC 8	PA16SO16D-EO-150
MICROCHIP	SST25LF020A	SOIC 8	PA20SO20D-EO-210
MICROCHIP	SST25LF040A	SOIC 8	PA20SO20D-EO-210
MICROCHIP	SST25LF080A	SOIC 8	PA16SO16D-EO-150
MICROCHIP	SST25PF020B-SAE	WSON 8	PA8SON8D
MICROCHIP	SST25PF020B-QAE	USON 8	HBP8USON48DB
MICROCHIP	SST25PF020B-Q3AE	DIP 28	
MICROCHIP	SST27SF256	DIP 28	
MICROCHIP	SST27VF256	DIP 28	
MICROCHIP	SST27SF512	PLCC 32	PA32PL28D-YA
MICROCHIP	SST27SF512	sTSOP 28	PA28TS28D-EO
MICROCHIP	SST27SF010	DIP 32	
MICROCHIP	SST27SF010	PLCC 32	PA32PL32D
MICROCHIP	SST27SF010	TSOP 32	PA32TS20/PA32TS32D-20
MICROCHIP	SST27SF020	DIP 32	
MICROCHIP	SST27SF020	PLCC 32	PA32PL32D
MICROCHIP	SST27SF020	TSOP 32	PA32TS20/PA32TS32D-20
MICROCHIP	SST27VF512	DIP 28	
MICROCHIP	SST27VF512	PLCC 32	PA32PL28D-YA
MICROCHIP	SST27VF512	sTSOP 28	PA28TS28D-EO
MICROCHIP	SST27VF010	DIP 32	
MICROCHIP	SST27VF010	PLCC 32	PA32PL32D
MICROCHIP	SST27VF010	TSOP 32	PA32TS20/PA32TS32D-20
MICROCHIP	SST27VF020	DIP 32	
MICROCHIP	SST27VF020	PLCC 32	PA32PL32D
MICROCHIP	SST27VF020	TSOP 32	PA32TS20/PA32TS32D-20
MICROCHIP	SST29EE512	DIP 32	
MICROCHIP	SST29EE512	PLCC 32	PA32PL32D
MICROCHIP	SST29EE512	TSOP 32	PA32TS20/PA32TS32D-20
MICROCHIP	SST29EE512A	DIP 32	
MICROCHIP	SST29EE512A	PLCC 32	PA32PL32D
MICROCHIP	SST29EE512A	TSOP 32	PA32TS20/PA32TS32D-20
MICROCHIP	SST29EE010	DIP 32	
MICROCHIP	SST29EE010	PLCC 32	PA32PL32D
MICROCHIP	SST29EE010	TSOP 32	PA32TS32D

MICROCHIP	SST29EE010A	DIP 32	
MICROCHIP	SST29EE010A	PLCC 32	PA32PL32D
MICROCHIP	SST29EE010A	TSOP 32	PA32TS32D
MICROCHIP	SST29EE020	DIP 32	
MICROCHIP	SST29EE020	PLCC 32	PA32PL32D
MICROCHIP	SST29EE020	TSOP 32	PA32TS32D
MICROCHIP	SST29EE020A	DIP 32	
MICROCHIP	SST29EE020A	PLCC 32	PA32PL32D
MICROCHIP	SST29EE020A	TSOP 32	PA32TS32D
MICROCHIP	SST29LE512	DIP 32	
MICROCHIP	SST29LE512	PLCC 32	PA32PL32D
MICROCHIP	SST29LE512	TSOP 32	PA32TS32D
MICROCHIP	SST29LE512A	DIP 32	
MICROCHIP	SST29LE512A	PLCC 32	PA32PL32D
MICROCHIP	SST29LE512A	TSOP 32	PA32TS32D
MICROCHIP	SST29LE010	DIP 32	
MICROCHIP	SST29LE010	PLCC 32	PA32PL32D
MICROCHIP	SST29LE010	TSOP 32	PA32TS32D
MICROCHIP	SST29LE010A	DIP 32	
MICROCHIP	SST29LE010A	PLCC 32	PA32PL32D
MICROCHIP	SST29LE010A	TSOP 32	PA32TS32D
MICROCHIP	SST29LE020	DIP 32	
MICROCHIP	SST29LE020	PLCC 32	PA32PL32D
MICROCHIP	SST29LE020	TSOP 32	PA32TS32D
MICROCHIP	SST29LE020A	DIP 32	
MICROCHIP	SST29LE020A	PLCC 32	PA32PL32D
MICROCHIP	SST29LE020A	TSOP 32	PA32TS32D
MICROCHIP	SST29SF512	DIP 32	
MICROCHIP	SST29SF512	PLCC 32	PA32PL32D
MICROCHIP	SST29SF512	TSOP 32	PA32TS32D
MICROCHIP	SST29SF010	DIP 32	
MICROCHIP	SST29SF010	PLCC 32	PA32PL32D
MICROCHIP	SST29SF010	TSOP 32	PA32TS32D
MICROCHIP	SST29SF020	DIP 32	
MICROCHIP	SST29SF020	PLCC 32	PA32PL32D
MICROCHIP	SST29SF020	TSOP 32	PA32TS32D
MICROCHIP	SST29SF040	DIP 32	
MICROCHIP	SST29SF040	PLCC 32	PA32PL32D
MICROCHIP	SST29SF040	TSOP 32	PA32TS32D
MICROCHIP	SST29VE512	DIP 32	
MICROCHIP	SST29VE512	PLCC 32	PA32PL32D
MICROCHIP	SST29VE512	TSOP 32	PA32TS32D
MICROCHIP	SST29VE512A	DIP 32	
MICROCHIP	SST29VE512A	PLCC 32	PA32PL32D
MICROCHIP	SST29VE512A	TSOP 32	PA32TS32D
MICROCHIP	SST29VE010	DIP 32	
MICROCHIP	SST29VE010	PLCC 32	PA32PL32D
MICROCHIP	SST29VE010	TSOP 32	PA32TS32D
MICROCHIP	SST29VE010A	DIP 32	
MICROCHIP	SST29VE010A	PLCC 32	PA32PL32D
MICROCHIP	SST29VE010A	TSOP 32	PA32TS32D
MICROCHIP	SST29VE020	DIP 32	
MICROCHIP	SST29VE020	PLCC 32	PA32PL32D
MICROCHIP	SST29VE020	TSOP 32	PA32TS32D
MICROCHIP	SST29VE020A	DIP 32	
MICROCHIP	SST29VE020A	PLCC 32	PA32PL32D
MICROCHIP	SST29VE020A	TSOP 32	PA32TS32D
MICROCHIP	SST29VF512	DIP 32	
MICROCHIP	SST29VF512	PLCC 32	PA32PL32D
MICROCHIP	SST29VF512	TSOP 32	PA32TS32D
MICROCHIP	SST29VF010	DIP 32	
MICROCHIP	SST29VF010	PLCC 32	PA32PL32D
MICROCHIP	SST29VF010	TSOP 32	PA32TS32D
MICROCHIP	SST29VF020	DIP 32	
MICROCHIP	SST29VF020	PLCC 32	PA32PL32D
MICROCHIP	SST29VF020	TSOP 32	PA32TS32D
MICROCHIP	SST29VF040	DIP 32	
MICROCHIP	SST29VF040	PLCC 32	PA32PL32D
MICROCHIP	SST29VF040	TSOP 32	PA32TS32D
MICROCHIP	SST31LF021	TSOP 40	PA40TS14-OT
MICROCHIP	SST31LF021	TSOP 32	PA32TS32D
MICROCHIP	SST31LF021E	TSOP 32	PA32TS32D
MICROCHIP	SST31LF041	TSOP 40	PA40TS14-OT

MICROCHIP	SST31LF041A	TSOP 32	PA32TS32D
MICROCHIP	SST32VF201	BGA 48	PA48BGA48-SST
MICROCHIP	SST32HF402	BGA 48	PA48BG48D
MICROCHIP	SST32HF402	BGA 48	PA48BG48DAI
MICROCHIP	SST32HF1622C	BGA 62	PA62BGA48D
MICROCHIP	SST32HF1642	BGA 62	PA62BGA48D
MICROCHIP	SST32HF1642C	BGA 62	PA62BGA48D
MICROCHIP	SST32HF1682C	BGA 62	PA62BGA48D
MICROCHIP	SST34HF162G	BGA 48	PA48BG48DAI
MICROCHIP	SST34HF164G	BGA 48	PA48BG48DAI
MICROCHIP	SST34HF1621/Polling	BGA 56	PA56BGA48D
MICROCHIP	SST34HF1621/Toggle	BGA 56	PA56BGA48D
MICROCHIP	SST34HF1621/Single	BGA 56	PA56BGA48D
MICROCHIP	SST34HF1621A/Polling	BGA 56	PA56BGA48D
MICROCHIP	SST34HF1621A/Toggle	BGA 56	PA56BGA48D
MICROCHIP	SST34HF1621A	BGA 62	PA62BGA48D
MICROCHIP	SST34HF1621C/Polling	BGA 56	PA56BGA48D-1
MICROCHIP	SST34HF1621C/Toggle	BGA 56	PA56BGA48D-1
MICROCHIP	SST34HF1621C/Single	BGA 56	PA56BGA48D-1
MICROCHIP	SST34HF1621S/Polling	BGA 56	PA56BGA48D-1
MICROCHIP	SST34HF1621S/Toggle	BGA 56	PA56BGA48D-1
MICROCHIP	SST34HF1641	BGA 56	PA56BGA48D
MICROCHIP	SST34HF1641	BGA 62	PA62BGA48D
MICROCHIP	SST34HF1641A	BGA 56	PA56BGA48D
MICROCHIP	SST34HF1641A	BGA 62	PA62BGA48D
MICROCHIP	SST34HF1641C	BGA 56	PA56BGA48D
MICROCHIP	SST34HF1641C	BGA 62	PA62BGA48D
MICROCHIP	SST34HF1641D	BGA 56	PA56BGA48D
MICROCHIP	SST34HF1641D	BGA 62	PA62BGA48D
MICROCHIP	SST34HF1641S	BGA 56	PA56BGA48D
MICROCHIP	SST34HF1641S	BGA 62	PA62BGA48D
MICROCHIP	SST34HF1681C	BGA 56	PA56BGA48D
MICROCHIP	SST34HF1681C	BGA 62	PA62BGA48D
MICROCHIP	SST34HF1681D	BGA 56	PA56BGA48D
MICROCHIP	SST34HF1681D	BGA 62	PA62BGA48D
MICROCHIP	SST34HF1681J	BGA 56	PA56BGA48D-1
MICROCHIP	SST34HF1642	BGA 56	PA56BGA48D
MICROCHIP	SST34HF1622	BGA 56	PA56BGA48D
MICROCHIP	SST34HF1622C	BGA 56	PA56BGA48D
MICROCHIP	SST34HF1642C	BGA 56	PA56BGA48D1
MICROCHIP	SST34HF1642D	BGA 56	PA56BGA48D
MICROCHIP	SST34HF1682D	BGA 56	PA56BGA48D
MICROCHIP	SST34HF1622S	BGA 56	PA56BGA48D
MICROCHIP	SST34HF1642S	BGA 56	PA56BGA48D
MICROCHIP	SST34HF1622C	BGA 62	PA62BGA48D
MICROCHIP	SST34HF1642C	BGA 62	PA62BGA48D1
MICROCHIP	SST34HF1642D	BGA 62	PA62BGA48D
MICROCHIP	SST34HF1682D	BGA 62	PA62BGA48D
MICROCHIP	SST34HF1622S	BGA 62	PA62BGA48D
MICROCHIP	SST34HF1642S	BGA 62	PA62BGA48D
MICROCHIP	SST34HF3223A	BGA 56	PA56BGA48D
MICROCHIP	SST34HF3243A	BGA 56	PA56BGA48D
MICROCHIP	SST34HF3244C	BGA 56	PA56BGA48D1
MICROCHIP	SST34HF3244C	BGA 62	PA62BGA48D1
MICROCHIP	SST34HF3284	BGA 56	PA56BGA48D1
MICROCHIP	SST34HF3284	BGA 62	PA62BGA48D1
MICROCHIP	SST34HF32A4	BGA 56	HA56BGA48D-2
MICROCHIP	SST34VF1621	BGA 56	PA56BGA48D
MICROCHIP	SST34VF1622	BGA 56	PA56BGA48D
MICROCHIP	SST34VF1641	BGA 56	PA56BGA48D
MICROCHIP	SST34VF1642	BGA 56	PA56BGA48D
MICROCHIP	SST36VF1601	TSOP 48	PA48TS48D
MICROCHIP	SST36VF1601C	TSOP 48	PA48TS48D
MICROCHIP	SST36VF1601C	BGA 48	PA48BG48DAI
MICROCHIP	SST36VF1601C/PA5	TSOP 48	PA48TS48D
MICROCHIP	SST36VF1601C/PA5	BGA 48	PA48BG48DAI
MICROCHIP	SST36VF1601E	TSOP 48	PA48TS48D
MICROCHIP	SST36VF1601E	BGA 48	PA48BG48DAI
MICROCHIP	SST36VF1602E	TSOP 48	PA48TS48D
MICROCHIP	SST36VF1602E	BGA 48	PA48BG48DAI
MICROCHIP	SST36VF1602	TSOP 48	PA48TS48D
MICROCHIP	SST36VF1602C	TSOP 48	PA48TS48D
MICROCHIP	SST36VF1601H	TSOP 48	PA48TS48D

MICROCHIP	SST36VF1602H	TSOP 48	PA48TS48D
MICROCHIP	SST36VF1601G	TSOP 48	PA48TS48D1
MICROCHIP	SST36VF3203	TSOP 48	PA48TS48D1
MICROCHIP	SST36VF3203	BGA 48	PA48BG48DAI
MICROCHIP	SST36VF3204	TSOP 48	PA48TS48D1
MICROCHIP	SST36VF3204	BGA 48	PA48BG48DAI
MICROCHIP	SST37VF512	DIP 32	
MICROCHIP	SST37VF512	PLCC 32	PA32PL32D
MICROCHIP	SST37VF512	TSOP 32	PA32TS32D
MICROCHIP	SST37VF010	DIP 32	
MICROCHIP	SST37VF010	PLCC 32	PA32PL32D
MICROCHIP	SST37VF010	TSOP 32	PA32TS32D
MICROCHIP	SST37VF020	DIP 32	
MICROCHIP	SST37VF020	PLCC 32	PA32PL32D
MICROCHIP	SST37VF020	TSOP 32	PA32TS32D
MICROCHIP	SST37VF040	DIP 32	
MICROCHIP	SST37VF040	PLCC 32	PA32PL32D
MICROCHIP	SST37VF040	TSOP 32	PA32TS32D
MICROCHIP	SST37VF080	TSOP 48	PA48TS48D
MICROCHIP	SST39VF080B	TSOP 48	PA48TS48D
MICROCHIP	SST38VF6401	TSOP 48	PA48TS48D1
MICROCHIP	SST38VF6401	BGA 48	PA48BG48DW
MICROCHIP	SST38VF6401	BGA 48	HA48BG48DAI
MICROCHIP	SST38VF6401B	TSOP 48	PA48TS48D1
MICROCHIP	SST38VF6402	TSOP 48	PA48TS48D1
MICROCHIP	SST38VF6402	BGA 48	PA48BG48DW
MICROCHIP	SST38VF6402	BGA 48	HA48BG48DAI
MICROCHIP	SST38VF6403	TSOP 48	PA48TS48D1
MICROCHIP	SST38VF6403	BGA 48	PA48BG48DW
MICROCHIP	SST38VF6404	BGA 48	PA48BG48DW
MICROCHIP	SST38VF6403	BGA 48	HA48BG48DAI
MICROCHIP	SST38VF6404	BGA 48	HA48BG48DAI
MICROCHIP	SST38VF6404	TSOP 48	PA48TS48D1
MICROCHIP	SST39LH512	DIP 32	
MICROCHIP	SST39LH010	DIP 32	
MICROCHIP	SST39LH020	DIP 32	
MICROCHIP	SST39LH040	DIP 32	
MICROCHIP	SST39LF512	DIP 32	
MICROCHIP	SST39LF512	PLCC 32	PA32PL32D
MICROCHIP	SST39LF512	TSOP 32	PA32TS32D
MICROCHIP	SST39LF010	DIP 32	
MICROCHIP	SST39LF010	PLCC 32	PA32PL32D
MICROCHIP	SST39LF010	WFBGA 34	PA48WFB32D
MICROCHIP	SST39LF010	TSOP 32	PA32TS32D
MICROCHIP	SST39LF020	DIP 32	
MICROCHIP	SST39LF020	PLCC 32	PA32PL32D
MICROCHIP	SST39LF020	TSOP 32	PA32TS32D
MICROCHIP	SST39LF040	DIP 32	
MICROCHIP	SST39LF040	PLCC 32	PA32PL32D
MICROCHIP	SST39LF040	TSOP 32	PA32TS32D
MICROCHIP	SST39SF512	DIP 32	
MICROCHIP	SST39SF512	PLCC 32	PA32PL32D
MICROCHIP	SST39SF512	TSOP 32	PA32TS32D
MICROCHIP	SST39SF512A	DIP 32	
MICROCHIP	SST39SF512A	PLCC 32	PA32PL32D
MICROCHIP	SST39SF512A	TSOP 32	PA32TS32D
MICROCHIP	SST39SF010	DIP 32	
MICROCHIP	SST39SF010	PLCC 32	PA32PL32D
MICROCHIP	SST39SF010	TSOP 32	PA32TS32D
MICROCHIP	SST39SF010A	DIP 32	
MICROCHIP	SST39SF010A	PLCC 32	PA32PL32D
MICROCHIP	SST39SF010A	TSOP 32	PA32TS32D
MICROCHIP	SST39SF020	DIP 32	
MICROCHIP	SST39SF020	PLCC 32	PA32PL32D
MICROCHIP	SST39SF020	TSOP 32	PA32TS32D
MICROCHIP	SST39SF020A	DIP 32	
MICROCHIP	SST39SF020A	PLCC 32	PA32PL32D
MICROCHIP	SST39SF020A	TSOP 32	PA32TS32D
MICROCHIP	SST39SF020P	DIP 32	
MICROCHIP	SST39SF020P	PLCC 32	PA32PL32D
MICROCHIP	SST39SF020P	TSOP 32	PA32TS32D
MICROCHIP	SST39SF040	DIP 32	
MICROCHIP	SST39SF040	PLCC 32	PA32PL32D



MICROCHIP	SST39SF040	TSOP 32	PA32TS32D
MICROCHIP	SST39SF040P	DIP 32	
MICROCHIP	SST39SF040P	PLCC 32	PA32PL32D
MICROCHIP	SST39SF040P	TSOP 32	PA32TS32D
MICROCHIP	SST39VF512	DIP 32	
MICROCHIP	SST39VF512	PLCC 32	PA32PL32D
MICROCHIP	SST39VF512	TSOP 32	PA32TS32D
MICROCHIP	SST39VF010	DIP 32	
MICROCHIP	SST39VF010	PLCC 32	PA32PL32D
MICROCHIP	SST39VF010	TSOP 32	PA32TS32D
MICROCHIP	SST39VF020	DIP 32	
MICROCHIP	SST39VF020	PLCC 32	PA32PL32D
MICROCHIP	SST39VF020	TSOP 32	PA32TS32D
MICROCHIP	SST39VF020P	DIP 32	
MICROCHIP	SST39VF020P	PLCC 32	PA32PL32D
MICROCHIP	SST39VF020P	TSOP 32	PA32TS32D
MICROCHIP	SST39VF040	DIP 32	
MICROCHIP	SST39VF040	PLCC 32	PA32PL32D
MICROCHIP	SST39VF040	TSOP 32	PA32TS32D
MICROCHIP	SST39VF040P	DIP 32	
MICROCHIP	SST39VF040P	PLCC 32	PA32PL32D
MICROCHIP	SST39VF040P	TSOP 32	PA32TS32D
MICROCHIP	SST39VF512	BGA 48	PA48BGA32DN-3O-6X8
MICROCHIP	SST39VF010	BGA 48	PA48BGA32DN-3O-6X8
MICROCHIP	SST39VF020P	BGA 48	PA48BGA32DN-3O-6X8
MICROCHIP	SST39VF040P	BGA 48	PA48BGA32DN-3O-6X8
MICROCHIP	SST39VF080Q	TSOP 40	PA40TS40D
MICROCHIP	SST39VF080Q	TSOP 40	PA40TS40D
MICROCHIP	SST39VF088	TSOP 48	PA48TS48D
MICROCHIP	SST39VF016	TSOP 40	PA40TS40D
MICROCHIP	SST39VF016Q	TSOP 40	PA40TS40D
MICROCHIP	SST39LF100	TSOP 40	PA40TS14-OT
MICROCHIP	SST39LF200A	TSOP 48	PA48TS48D1
MICROCHIP	SST39LF400A	TSOP 48	PA48TS48D1
MICROCHIP	SST39LF800A	TSOP 48	PA48TS48D1
MICROCHIP	SST39LF800A	BGA 48	PA48BG48DAI
MICROCHIP	SST39LF800A	WFBGA 48	PA48WFB48D1
MICROCHIP	SST39VF100	TSOP 40	PA40TS14-OT
MICROCHIP	SST39VF200A	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF200A	BGA 48	PA48BG48DAI
MICROCHIP	SST39VF200A	WFBGA 48	PA48WFB48D1
MICROCHIP	SST39VF400A	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF400A	BGA 48	PA48BG48DAI
MICROCHIP	SST39VF400A	WFBGA 48	PA48WFB48D1
MICROCHIP	SST39VF401C	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF800A	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF800A	BGA 48	PA48BG48DAI
MICROCHIP	SST39VF800A	WFBGA 48	PA48WFB48D1
MICROCHIP	SST39VF801C	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF400	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF400Q	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF800	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF800Q	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF160	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF160(Single)	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF160Q	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF160Q(Single)	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF320	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF640	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF1601	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF1601	WFBGA 48	PA48BG48DAI
MICROCHIP	SST39VF1601C	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF1602	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF1681	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF1682	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF3201	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF3201	BGA 48	PA48BG48DAI
MICROCHIP	SST39VF3201B	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF3202	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF3202	BGA 48	PA48BG48DAI
MICROCHIP	SST39VF6401	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF6401	BGA 48	HA48BG48DG1
MICROCHIP	SST39VF6401B	TSOP 48	PA48TS48D1

MICROCHIP	SST39VF6401B	BGA 48	HA48BG48DG1
MICROCHIP	SST39VF6402	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF6402	BGA 48	HA48BG48DG1
MICROCHIP	SST39VF6402B	TSOP 48	PA48TS48D1
MICROCHIP	SST39VF6402B	BGA 48	HA48BG48DG1
MICROCHIP	SST39WF400A	WFBGA 48	PA48WFB48D
MICROCHIP	SST39WF400B	WFBGA 48	PA48BG48DW
MICROCHIP	SST39WF400B	WFBGA 48	HA48BG48DAI
MICROCHIP	SST39WF800A	WFBGA 48	PA48WFB48D1
MICROCHIP	SST39WF800B	WFBGA 48	PA48WFB48D1
MICROCHIP	SST39WF1601	WFBGA 48	PA48BG48DW
MICROCHIP	SST39WF1602	WFBGA 48	PA48BG48DW
MICROCHIP	SST39WF1601	WFBGA 48	HA48BG48DAI
MICROCHIP	SST39WF1602	WFBGA 48	HA48BG48DAI
MICROCHIP	SST45LF010	SOP 8	PA16SO16D-EO-150
MICROCHIP	SST45VF010	SOP 8	PA16SO16D-EO-150
MICROCHIP	SST49LF002	PLCC 32	PA32PL32D
MICROCHIP	SST49LF002	TSOP 32	PA32TS32D
MICROCHIP	SST49LF002A	PLCC 32	PA32PL32D
MICROCHIP	SST49LF002A	TSOP 40	PA40TS40D
MICROCHIP	SST49LF002A	TSOP 32	PA32TS32D
MICROCHIP	SST49LF002B	PLCC 32	PA32PL32D
MICROCHIP	SST49LF002B	TSOP 32	PA32TS32D
MICROCHIP	SST49LF002B	TSOP 40	PA40TS40D
MICROCHIP	SST49LF003A	PLCC 32	PA32PL32D
MICROCHIP	SST49LF003A	TSOP 32	PA32TS32D
MICROCHIP	SST49LF003A	TSOP 40	PA40TS40D
MICROCHIP	SST49LF003B	PLCC 32	PA32PL32D
MICROCHIP	SST49LF003B	TSOP 32	PA32TS32D
MICROCHIP	SST49LF003B	TSOP 40	PA40TS40D
MICROCHIP	SST49LF004	PLCC 32	PA32PL32D
MICROCHIP	SST49LF004	TSOP 32	PA32TS32D
MICROCHIP	SST49LF004A	PLCC 32	PA32PL32D
MICROCHIP	SST49LF004A	TSOP 32	PA32TS32D
MICROCHIP	SST49LF004A	TSOP 40	PA40TS40D
MICROCHIP	SST49LF004B	PLCC 32	PA32PL32D
MICROCHIP	SST49LF004B	TSOP 32	PA32TS32D
MICROCHIP	SST49LF004B	TSOP 40	PA40TS40D
MICROCHIP	SST49LF004C	PLCC 32	PA32PL32D
MICROCHIP	SST49LF004C	TSOP 32	PA32TS20/PA32TS32D-20
MICROCHIP	SST49LF008	PLCC 32	PA32PL32D
MICROCHIP	SST49LF008	TSOP 32	PA32TS32D
MICROCHIP	SST49LF008A	PLCC 32	PA32PL32D
MICROCHIP	SST49LF008A	TSOP 32	PA32TS32D
MICROCHIP	SST49LF008A	TSOP 40	PA40TS40D
MICROCHIP	SST49LF008B	PLCC 32	PA32PL32D
MICROCHIP	SST49LF008B	TSOP 32	PA32TS32D
MICROCHIP	SST49LF008B	TSOP 40	PA40TS40D
MICROCHIP	SST49LF008C	PLCC 32	PA32PL32D
MICROCHIP	SST49LF008C	TSOP 32	PA32TS20/PA32TS32D-20
MICROCHIP	SST49LF020	PLCC 32	PA32PL32D
MICROCHIP	SST49LF020	TSOP 32	PA32TS32D
MICROCHIP	SST49LF020A	PLCC 32	PA32PL32D
MICROCHIP	SST49LF020A	TSOP 32	PA32TS32D
MICROCHIP	SST49LF030A	PLCC 32	PA32PL32D
MICROCHIP	SST49LF040	PLCC 32	PA32PL32D
MICROCHIP	SST49LF040	TSOP 32	PA32TS32D
MICROCHIP	SST49LF040A	PLCC 32	PA32PL32D
MICROCHIP	SST49LF040A	TSOP 32	PA32TS32D
MICROCHIP	SST49LF040B	PLCC 32	PA32PL32D
MICROCHIP	SST49LF040B	TSOP 32	PA32TS32D
MICROCHIP	SST49LF080	PLCC 32	PA32PL32D
MICROCHIP	SST49LF080	TSOP 32	PA32TS32D
MICROCHIP	SST49LF080A	PLCC 32	PA32PL32D
MICROCHIP	SST49LF080A	TSOP 32	PA32TS32D
MICROCHIP	SST49LF016C(AAI)	PLCC 32	PA32PL32D
MICROCHIP	SST49LF016C(AAI)	TSOP 32	PA32TS20/PA32TS32D-20
MICROCHIP	SST49LF016C(AAI)	TSOP 32	PA32TS32D
MICROCHIP	SST49LF016C(AAI)	TSOP 40	PA40TS40D
MICROCHIP	SST49LF016C(LPC)	PLCC 32	PA32PL32D
MICROCHIP	SST49LF016C(LPC)	TSOP 32	PA32TS20/PA32TS32D-20
MICROCHIP	SST49LF016C(LPC)	TSOP 32	PA32TS32D
MICROCHIP	SST49LF016C(LPC)	TSOP 40	PA40TS40D

MICROCHIP	SST49LF016C(FWH)	PLCC 32	PA32PL32D
MICROCHIP	SST49LF016C(FWH)	TSOP 32	PA32TS20/PA32TS32D-20
MICROCHIP	SST49LF016C(FWH)	TSOP 32	PA32TS32D
MICROCHIP	SST49LF016C(FWH)	TSOP 40	PA40TS40D
MICROCHIP	SST49LF160C(AAI)	PLCC 32	PA32PL32D
MICROCHIP	SST49LF160C(AAI)	TSOP 32	PA32TS20/PA32TS32D-20
MICROCHIP	SST49LF160C(AAI)	TSOP 32	PA32TS32D
MICROCHIP	SST49LF160C(AAI)	TSOP 40	PA40TS40D
SST	SST28LF040	DIP 32	
SST	SST28LF040	PLCC 32	PA32PL32D
SST	SST28LF040	TSOP 32	PA32TS20/PA32TS32D-20
SST	SST28SF040	DIP 32	
SST	SST28SF040	PLCC 32	PA32PL32D
SST	SST28SF040	TSOP 32	PA32TS20/PA32TS32D-20
SST	SST28SF040A	DIP 32	
SST	SST28SF040A	PLCC 32	PA32PL32D
SST	SST28SF040A	TSOP 32	PA32TS20/PA32TS32D-20
SST	SST28VF040	DIP 32	
SST	SST28VF040	PLCC 32	PA32PL32D
SST	SST28VF040	TSOP 32	PA32TS20/PA32TS32D-20
SST	SST28VF040A	DIP 32	
SST	SST28VF040A	PLCC 32	PA32PL32D
SST	SST28VF040A	TSOP 32	PA32TS20/PA32TS32D-20
SST	PH28EE011	DIP 32	
SST	SST25WF512	SOIC 8	PA16SO16D-EO-150
SST	SST25WF010	SOIC 8	PA16SO16D-EO-150
SST	SST25WF020	SOIC 8	PA16SO16D-EO-150
SST	SST25WF040	SOIC 8	PA20SO20D-EO-210
SST	SST25WF040	SOIC 8	PA16SO16D-EO-150
SST	SST25WF080	SOIC 8	PA20SO20D-EO-210
SST	SST25WF080	SOIC 8	PA16SO16D-EO-150
SST	SST25VF512	SOIC 8	PA16SO16D-EO-150
SST	SST25VF512	WSO8 8	PA8SON8D
SST	SST25VF512A	SOIC 8	PA16SO16D-EO-150
SST	SST25VF512A	WSO8 8	PA8SON8D
SST	SST25VF010	SOIC 8	PA16SO16D-EO-150
SST	SST25VF010	WSO8 8	PA8SON8D
SST	SST25VF010A	SOIC 8	PA16SO16D-EO-150
SST	SST25VF010A	WSO8 8	PA8SON8D
SST	SST25VF020	SOIC 8	PA16SO16D-EO-150
SST	SST25VF020	WSO8 8	PA8SON8D
SST	SST25VF040	SOIC 8	PA20SO20D-EO-210
SST	SST25VF040	WSO8 8	PA8SON8D
PCT	PCT25VF040A	SOIC 8	PA8SO8D-EO-150
SST	SST25VF040B	SOIC 8	PA20SO20D-EO-210
SST	SST25VF040B	WSO8 8	PA8SON8D
SST	SST25VF080B	SOIC 8	PA20SO20D-EO-210
SST	SST25VF080B	WSO8 8	PA8SON8D
MICROCHIP	SST25VF080B-S2AE	SOIC 8	PA20SO20D-EO-210
MICROCHIP	SST25VF080B-QAE	WSO8 8	PA8SON8D
MICROCHIP	SST25VF080B-PAE	DIP 8	
SST	SST25VF016B	SOIC 8	PA20SO20D-EO-210
SST	SST25VF016B	WSO8 8	PA8SON8D
SST	SST25VF032B	SOIC 8	PA20SO20D-EO-210
SST	SST25VF032B	SOIC 16	PA20SO20D-EO-210
SST	SST25VF064C	SOIC 16	PA28SO28D-EO-300
SST	SST25LF020A	SOIC 8	PA16SO16D-EO-150
SST	SST25LF040A	SOIC 8	PA20SO20D-EO-210
SST	SST25LF080A	SOIC 8	PA20SO20D-EO-210
MICROCHIP	SST26VF016	SOIC 8	PA20SO20D-EO-210
SST	SST26VF016	SOIC 8	PA20SO20D-EO-210
MICROCHIP	SST26VF016-S2AE	SOIC 8	PA20SO20D-EO-210
MICROCHIP	SST26VF016-QAE	WSO8 8	PA8SON8D
MICROCHIP	SST26VF016B	SOIC 8	PA16SO16D-EO-150
MICROCHIP	SST26VF016B	SOIC 8	PA20SO20D-EO-210
MICROCHIP	SST26VF016B	WSO8 8	PA8SON8D
MICROCHIP	SST26VF016B	SOIC 8	PA20SO20D-EO-210
MICROCHIP	SST26VF032	SOIC 8	PA20SO20D-EO-210
SST	SST26VF032	SOIC 8	PA20SO20D-EO-210
MICROCHIP	SST26VF032-S2AE	SOIC 8	PA20SO20D-EO-210
MICROCHIP	SST26VF032-QAE	WSO8 8	PA8SON8D
MICROCHIP	SST26VF016BA	WSO8 8	PA8SON8D
MICROCHIP	SST26VF016BA	SOIC 8	PA16SO16D-EO-150
MICROCHIP	SST26VF016BA	SOIC 8	PA20SO20D-EO-210

MICROCHIP	SST26VF032B	WSON 8	PA8SON8D
MICROCHIP	SST26VF032B	SOIC 8	PA20SO20D-EO-210
MICROCHIP	SST26VF032B	BGA 24	NA24BG48DA
MICROCHIP	SST26VF032BA	WSON 8	PA8SON8D
MICROCHIP	SST26VF032BA	SOIC 8	PA20SO20D-EO-210
MICROCHIP	SST26VF032BA	BGA 24	NA24BG48DA
MICROCHIP	SST26VF064B	WSON 8	PA8SON8D
MICROCHIP	SST26VF064B	BGA 24	HA24BG48D
MICROCHIP	SST26VF064B	SOIC 16	PA28SO28D-EO-300
MICROCHIP	SST26VF064B	SOIC 8	PA20SO20D-EO-210
MICROCHIP	SST26VF064BA	WSON 8	PA8SON8D
MICROCHIP	SST26VF064BA	SOIC 16	PA28SO28D-EO-300
MICROCHIP	SST26VF064BA	BGA 24	HA24BG48D
MICROCHIP	SST26VF064BA	SOIC 8	PA20SO20D-EO-210
MICROCHIP	SST26VF064B-I/SO	SOIC 16	PA28SO28D-EO-300
MICROCHIP	SST26VF064B-I/SM	SOIC 8	PA20SO20D-EO-210
MICROCHIP	SST26VF064B-I/MF	WSON 8	PA8SON8D
MICROCHIP	SST26VF064B-I/TD	BGA 24	HA24BG48D
MICROCHIP	SST26VF064BA-I/SO	SOIC 16	PA28SO28D-EO-300
MICROCHIP	SST26VF064BA-I/SM	SOIC 8	PA20SO20D-EO-210
MICROCHIP	SST26VF064BA-I/MF	WSON 8	PA8SON8D
MICROCHIP	SST26VF064BA-I/TD	BGA 24	HA24BG48D
MICROCHIP	SST26WF040B	SOIC 8	HA8SO48DAD
MICROCHIP	SST26WF040B	WSON 8	HA8SON48DG
MICROCHIP	SST26WF040B	USON 8	HBP8USON48DC
MICROCHIP	SST26WF040BA	SOIC 8	HA8SO48DAD
MICROCHIP	SST26WF040BA	WSON 8	HA8SON48DG
MICROCHIP	SST26WF040BA	USON 8	HBP8USON48DC
MICROCHIP	SST26WF040B-I/SN	SOIC 8	HA8SO48DAD
MICROCHIP	SST26WF040B-I/MF	WSON 8	HA8SON48DG
MICROCHIP	SST26WF040B-I/NP	USON 8	HBP8USON48DC
MICROCHIP	SST26WF040BA-I/SN	SOIC 8	HA8SO48DAD
MICROCHIP	SST26WF040BA-I/MF	WSON 8	HA8SON48DG
MICROCHIP	SST26WF040BA-I/NP	USON 8	HBP8USON48DC
MICROCHIP	SST26WF080B	SOIC 8	HA8SO48DAD
MICROCHIP	SST26WF080B	WSON 8	HA8SON48DG
MICROCHIP	SST26WF080B	USON 8	HBP8USON48DC
MICROCHIP	SST26WF080BA	SOIC 8	HA8SO48DAD
MICROCHIP	SST26WF080BA	WSON 8	HA8SON48DG
MICROCHIP	SST26WF080BA	USON 8	HBP8USON48DC
MICROCHIP	SST26WF080B-I/SN	SOIC 8	HA8SO48DAD
MICROCHIP	SST26WF080B-I/MF	WSON 8	HA8SON48DG
MICROCHIP	SST26WF080B-I/NP	USON 8	HBP8USON48DC
MICROCHIP	SST26WF080BA-I/SN	SOIC 8	HA8SO48DAD
MICROCHIP	SST26WF080BA-I/MF	WSON 8	HA8SON48DG
MICROCHIP	SST26WF080BA-I/NP	USON 8	HBP8USON48DC
MICROCHIP	SST26WF016B	WSON 8	HA8SON48DG
MICROCHIP	SST26WF016B	USON 8	HBP8USON48DC
MICROCHIP	SST26WF016B	SOIC 8	HA8SO48DAD
MICROCHIP	SST26WF016BA	SOIC 8	HA8SO48DAD
MICROCHIP	SST26WF016BA	WSON 8	HA8SON48DG
MICROCHIP	SST26WF016BA	USON 8	HBP8USON48DC
MICROCHIP	SST26WF016B-I/SN	SOIC 8	HA8SO48DAD
MICROCHIP	SST26WF016B-I/MF	WSON 8	HA8SON48DG
MICROCHIP	SST26WF016B-I/NP	USON 8	HBP8USON48DC
MICROCHIP	SST26WF016BA-I/SN	SOIC 8	HA8SO48DAD
MICROCHIP	SST26WF016BA-I/MF	WSON 8	HA8SON48DG
MICROCHIP	SST26WF016BA-I/NP	USON 8	HBP8USON48DC
SST	SST27SF256	DIP 28	
SST	SST27VF256	DIP 28	
SST	SST27SF512	DIP 28	
SST	SST27SF512	PLCC 32	PA32PL28D-YA
SST	SST27SF512	sTSOP 28	PA28TS28D-EO
SST	SST27SF010	DIP 32	
SST	SST27SF010	PLCC 32	PA32PL32D
SST	SST27SF010	TSOP 32	PA32TS20/PA32TS32D-20
SST	SST27SF020	DIP 32	
SST	SST27SF020	PLCC 32	PA32PL32D
SST	SST27SF020	TSOP 32	PA32TS20/PA32TS32D-20
SST	SST27VF512	DIP 28	
SST	SST27VF512	PLCC 32	PA32PL28D-YA
SST	SST27VF512	sTSOP 28	PA28TS28D-EO
SST	SST27VF010	DIP 32	

SST	SST27VF010	PLCC 32	PA32PL32D
SST	SST27VF010	TSOP 32	PA32TS20/PA32TS32D-20
SST	SST27VF020	DIP 32	
SST	SST27VF020	PLCC 32	PA32PL32D
SST	SST27VF020	TSOP 32	PA32TS20/PA32TS32D-20
SST	SST29EE512	DIP 32	
SST	SST29EE512	PLCC 32	PA32PL32D
SST	SST29EE512	TSOP 32	PA32TS20/PA32TS32D-20
SST	SST29EE512A	DIP 32	
SST	SST29EE512A	PLCC 32	PA32PL32D
SST	SST29EE512A	TSOP 32	PA32TS20/PA32TS32D-20
SST	SST29EE010	DIP 32	
SST	SST29EE010	PLCC 32	PA32PL32D
SST	SST29EE010	TSOP 32	PA32TS32D
SST	SST29EE010A	DIP 32	
SST	SST29EE010A	PLCC 32	PA32PL32D
SST	SST29EE010A	TSOP 32	PA32TS32D
SST	SST29EE020	DIP 32	
SST	SST29EE020	PLCC 32	PA32PL32D
SST	SST29EE020	TSOP 32	PA32TS32D
SST	SST29EE020A	DIP 32	
SST	SST29EE020A	PLCC 32	PA32PL32D
SST	SST29EE020A	TSOP 32	PA32TS32D
SST	SST29LE512	DIP 32	
SST	SST29LE512	PLCC 32	PA32PL32D
SST	SST29LE512	TSOP 32	PA32TS32D
SST	SST29LE512A	DIP 32	
SST	SST29LE512A	PLCC 32	PA32PL32D
SST	SST29LE512A	TSOP 32	PA32TS32D
SST	SST29LE010	DIP 32	
SST	SST29LE010	PLCC 32	PA32PL32D
SST	SST29LE010	TSOP 32	PA32TS32D
SST	SST29LE010A	DIP 32	
SST	SST29LE010A	PLCC 32	PA32PL32D
SST	SST29LE010A	TSOP 32	PA32TS32D
SST	SST29LE020	DIP 32	
SST	SST29LE020	PLCC 32	PA32PL32D
SST	SST29LE020	TSOP 32	PA32TS32D
SST	SST29LE020A	DIP 32	
SST	SST29LE020A	PLCC 32	PA32PL32D
SST	SST29LE020A	TSOP 32	PA32TS32D
SST	SST29SF512	DIP 32	
SST	SST29SF512	PLCC 32	PA32PL32D
SST	SST29SF512	TSOP 32	PA32TS32D
SST	SST29SF010	DIP 32	
SST	SST29SF010	PLCC 32	PA32PL32D
SST	SST29SF010	TSOP 32	PA32TS32D
SST	SST29SF020	DIP 32	
SST	SST29SF020	PLCC 32	PA32PL32D
SST	SST29SF020	TSOP 32	PA32TS32D
SST	SST29SF040	DIP 32	
SST	SST29SF040	PLCC 32	PA32PL32D
SST	SST29SF040	TSOP 32	PA32TS32D
SST	SST29VE512	DIP 32	
SST	SST29VE512	PLCC 32	PA32PL32D
SST	SST29VE512	TSOP 32	PA32TS32D
SST	SST29VE512A	DIP 32	
SST	SST29VE512A	PLCC 32	PA32PL32D
SST	SST29VE512A	TSOP 32	PA32TS32D
SST	SST29VE010	DIP 32	
SST	SST29VE010	PLCC 32	PA32PL32D
SST	SST29VE010	TSOP 32	PA32TS32D
SST	SST29VE010A	DIP 32	
SST	SST29VE010A	PLCC 32	PA32PL32D
SST	SST29VE010A	TSOP 32	PA32TS32D
SST	SST29VE020	DIP 32	
SST	SST29VE020	PLCC 32	PA32PL32D
SST	SST29VE020	TSOP 32	PA32TS32D
SST	SST29VE020A	DIP 32	
SST	SST29VE020A	PLCC 32	PA32PL32D
SST	SST29VE020A	TSOP 32	PA32TS32D
SST	SST29VF512	DIP 32	
SST	SST29VF512	PLCC 32	PA32PL32D

SST	SST29VF512	TSOP 32	PA32TS32D
SST	SST29VF010	DIP 32	
SST	SST29VF010	PLCC 32	PA32PL32D
SST	SST29VF010	TSOP 32	PA32TS32D
SST	SST29VF020	DIP 32	
SST	SST29VF020	PLCC 32	PA32PL32D
SST	SST29VF020	TSOP 32	PA32TS32D
SST	SST29VF040	DIP 32	
SST	SST29VF040	PLCC 32	PA32PL32D
SST	SST29VF040	TSOP 32	PA32TS32D
SST	SST31LF021	TSOP 40	PA40TS14-OT
SST	SST31LF021	TSOP 32	PA32TS32D
SST	SST31LF021E	TSOP 32	PA32TS32D
SST	SST31LF041	TSOP 40	PA40TS14-OT
SST	SST31LF041A	TSOP 32	PA32TS32D
SST	SST32VF201	BGA 48	PA48BGA48-SST
SST	SST32HF402	BGA 48	PA48BG48D
SST	SST32HF402	BGA 48	PA48BG48DAI
SST	SST32HF1622C	BGA 62	PA62BGA48D
SST	SST32HF1642	BGA 62	PA62BGA48D
SST	SST32HF1642C	BGA 62	PA62BGA48D
SST	SST32HF1682C	BGA 62	PA62BGA48D
SST	SST34HF162G	BGA 48	PA48BG48DAI
SST	SST34HF164G	BGA 48	PA48BG48DAI
SST	SST34HF1621/Polling	BGA 56	PA56BGA48D
SST	SST34HF1621/Toggle	BGA 56	PA56BGA48D
SST	SST34HF1621/Single	BGA 56	PA56BGA48D
SST	SST34HF1621A/Polling	BGA 56	PA56BGA48D
SST	SST34HF1621A/Toggle	BGA 56	PA56BGA48D
SST	SST34HF1621A	BGA 62	PA62BGA48D
SST	SST34HF1621C/Polling	BGA 56	PA56BGA48D-1
SST	SST34HF1621C/Toggle	BGA 56	PA56BGA48D-1
SST	SST34HF1621C/Single	BGA 56	PA56BGA48D-1
SST	SST34HF1621S/Polling	BGA 56	PA56BGA48D-1
SST	SST34HF1621S/Toggle	BGA 56	PA56BGA48D-1
SST	SST34HF1641	BGA 56	PA56BGA48D
SST	SST34HF1641	BGA 62	PA62BGA48D
SST	SST34HF1641A	BGA 56	PA56BGA48D
SST	SST34HF1641A	BGA 62	PA62BGA48D
SST	SST34HF1641C	BGA 56	PA56BGA48D
SST	SST34HF1641C	BGA 62	PA62BGA48D
SST	SST34HF1641D	BGA 56	PA56BGA48D
SST	SST34HF1641D	BGA 62	PA62BGA48D
SST	SST34HF1641S	BGA 56	PA56BGA48D
SST	SST34HF1641S	BGA 62	PA62BGA48D
SST	SST34HF1681C	BGA 56	PA56BGA48D
SST	SST34HF1681C	BGA 62	PA62BGA48D
SST	SST34HF1681D	BGA 56	PA56BGA48D
SST	SST34HF1681D	BGA 62	PA62BGA48D
SST	SST34HF1681J	BGA 56	PA56BGA48D-1
SST	SST34HF1642	BGA 56	PA56BGA48D
SST	SST34HF1622	BGA 56	PA56BGA48D
SST	SST34HF1622C	BGA 56	PA56BGA48D
SST	SST34HF1642C	BGA 56	PA56BGA48D1
SST	SST34HF1642D	BGA 56	PA56BGA48D
SST	SST34HF1682D	BGA 56	PA56BGA48D
SST	SST34HF1622S	BGA 56	PA56BGA48D
SST	SST34HF1642S	BGA 56	PA56BGA48D
SST	SST34HF1622C	BGA 62	PA62BGA48D
SST	SST34HF1642C	BGA 62	PA62BGA48D1
SST	SST34HF1642D	BGA 62	PA62BGA48D
SST	SST34HF1682D	BGA 62	PA62BGA48D
SST	SST34HF1622S	BGA 62	PA62BGA48D
SST	SST34HF1642S	BGA 62	PA62BGA48D
SST	SST34HF3223A	BGA 56	PA56BGA48D
SST	SST34HF3243A	BGA 56	PA56BGA48D
SST	SST34HF3244C	BGA 56	PA56BGA48D1
SST	SST34HF3244C	BGA 62	PA62BGA48D1
SST	SST34HF3284	BGA 56	PA56BGA48D1
SST	SST34HF3284	BGA 62	PA62BGA48D1
SST	SST34HF32A4	BGA 56	HA56BGA48D-2
SST	SST34VF1621	BGA 56	PA56BGA48D
SST	SST34VF1622	BGA 56	PA56BGA48D

SST	SST34VF1641	BGA 56	PA56BGA48D
SST	SST34VF1642	BGA 56	PA56BGA48D
SST	SST36VF1601	TSOP 48	PA48TS48D
SST	SST36VF1601C	TSOP 48	PA48TS48D
SST	SST36VF1601C	BGA 48	PA48BG48DAI
SST	SST36VF1601C/PA5	TSOP 48	PA48TS48D
SST	SST36VF1601C/PA5	BGA 48	PA48BG48DAI
SST	SST36VF1601E	TSOP 48	PA48TS48D
SST	SST36VF1601E	BGA 48	PA48BG48DAI
SST	SST36VF1602E	TSOP 48	PA48TS48D
SST	SST36VF1602E	BGA 48	PA48BG48DAI
SST	SST36VF1602	TSOP 48	PA48TS48D
SST	SST36VF1602C	TSOP 48	PA48TS48D
SST	SST36VF1601H	TSOP 48	PA48TS48D
SST	SST36VF1602H	TSOP 48	PA48TS48D
SST	SST36VF1601G	TSOP 48	PA48TS48D1
SST	SST36VF3203	TSOP 48	PA48TS48D1
SST	SST36VF3203	BGA 48	PA48BG48DAI
SST	SST36VF3204	TSOP 48	PA48TS48D1
SST	SST36VF3204	BGA 48	PA48BG48DAI
SST	SST37VF512	DIP 32	
SST	SST37VF512	PLCC 32	PA32PL32D
SST	SST37VF512	TSOP 32	PA32TS32D
SST	SST37VF010	DIP 32	
SST	SST37VF010	PLCC 32	PA32PL32D
SST	SST37VF010	TSOP 32	PA32TS32D
SST	SST37VF020	DIP 32	
SST	SST37VF020	PLCC 32	PA32PL32D
SST	SST37VF020	TSOP 32	PA32TS32D
SST	SST37VF040	DIP 32	
SST	SST37VF040	PLCC 32	PA32PL32D
SST	SST37VF040	TSOP 32	PA32TS32D
SST	SST37VF080	TSOP 48	PA48TS48D
SST	SST39VF080B	TSOP 48	PA48TS48D
SST	SST38VF6401	TSOP 48	PA48TS48D1
SST	SST38VF6401	BGA 48	PA48BG48DW
SST	SST38VF6401	BGA 48	HA48BG48DAI
SST	SST38VF6402	TSOP 48	PA48TS48D1
SST	SST38VF6402	BGA 48	PA48BG48DW
SST	SST38VF6402	BGA 48	HA48BG48DAI
SST	SST38VF6403	TSOP 48	PA48TS48D1
SST	SST38VF6403	BGA 48	PA48BG48DW
SST	SST38VF6403	BGA 48	PA48BG48DW
SST	SST38VF6403	BGA 48	HA48BG48DAI
SST	SST38VF6404	BGA 48	HA48BG48DAI
SST	SST38VF6404	TSOP 48	PA48TS48D1
SST	SST39LH512	DIP 32	
SST	SST39LH010	DIP 32	
SST	SST39LH020	DIP 32	
SST	SST39LH040	DIP 32	
SST	SST39LF512	DIP 32	
SST	SST39LF512	PLCC 32	PA32PL32D
SST	SST39LF512	TSOP 32	PA32TS32D
SST	SST39LF010	DIP 32	
SST	SST39LF010	PLCC 32	PA32PL32D
SST	SST39LF010	WFBGA 34	PA48WFB32D
SST	SST39LF010	TSOP 32	PA32TS32D
SST	SST39LF020	DIP 32	
SST	SST39LF020	PLCC 32	PA32PL32D
SST	SST39LF020	TSOP 32	PA32TS32D
SST	SST39LF040	DIP 32	
SST	SST39LF040	PLCC 32	PA32PL32D
SST	SST39LF040	TSOP 32	PA32TS32D
SST	SST39SF512	DIP 32	
SST	SST39SF512	PLCC 32	PA32PL32D
SST	SST39SF512	TSOP 32	PA32TS32D
SST	SST39SF512A	DIP 32	
SST	SST39SF512A	PLCC 32	PA32PL32D
SST	SST39SF512A	TSOP 32	PA32TS32D
SST	SST39SF010	DIP 32	
SST	SST39SF010	PLCC 32	PA32PL32D
SST	SST39SF010	TSOP 32	PA32TS32D
SST	SST39SF010A	DIP 32	

SST	SST39SF010A	PLCC 32	PA32PL32D
SST	SST39SF010A	TSOP 32	PA32TS32D
SST	SST39SF020	DIP 32	
SST	SST39SF020	PLCC 32	PA32PL32D
SST	SST39SF020	TSOP 32	PA32TS32D
SST	SST39SF020A	DIP 32	
SST	SST39SF020A	PLCC 32	PA32PL32D
SST	SST39SF020A	TSOP 32	PA32TS32D
SST	SST39SF020P	DIP 32	
SST	SST39SF020P	PLCC 32	PA32PL32D
SST	SST39SF020P	TSOP 32	PA32TS32D
SST	SST39SF040	DIP 32	
SST	SST39SF040	PLCC 32	PA32PL32D
SST	SST39SF040	TSOP 32	PA32TS32D
SST	SST39SF040P	DIP 32	
SST	SST39SF040P	PLCC 32	PA32PL32D
SST	SST39SF040P	TSOP 32	PA32TS32D
SST	SST39VF512	DIP 32	
SST	SST39VF512	PLCC 32	PA32PL32D
SST	SST39VF512	TSOP 32	PA32TS32D
SST	SST39VF010	DIP 32	
SST	SST39VF010	PLCC 32	PA32PL32D
SST	SST39VF010	TSOP 32	PA32TS32D
SST	SST39VF020	DIP 32	
SST	SST39VF020	PLCC 32	PA32PL32D
SST	SST39VF020	TSOP 32	PA32TS32D
SST	SST39VF020P	DIP 32	
SST	SST39VF020P	PLCC 32	PA32PL32D
SST	SST39VF020P	TSOP 32	PA32TS32D
SST	SST39VF040	DIP 32	
SST	SST39VF040	PLCC 32	PA32PL32D
SST	SST39VF040	TSOP 32	PA32TS32D
SST	SST39VF040P	DIP 32	
SST	SST39VF040P	PLCC 32	PA32PL32D
SST	SST39VF040P	TSOP 32	PA32TS32D
SST	SST39VF512	BGA 48	PA48BGA32DN-3O-6X8
SST	SST39VF010	BGA 48	PA48BGA32DN-3O-6X8
SST	SST39VF020P	BGA 48	PA48BGA32DN-3O-6X8
SST	SST39VF040P	BGA 48	PA48BGA32DN-3O-6X8
SST	SST39VF080	TSOP 40	PA40TS40D
SST	SST39VF080Q	TSOP 40	PA40TS40D
SST	SST39VF088	TSOP 48	PA48TS48D
SST	SST39VF016	TSOP 40	PA40TS40D
SST	SST39VF016Q	TSOP 40	PA40TS40D
SST	SST39LF100	TSOP 40	PA40TS14-OT
SST	SST39LF200A	TSOP 48	PA48TS48D1
SST	SST39LF400A	TSOP 48	PA48TS48D1
SST	SST39LF800A	TSOP 48	PA48TS48D1
SST	SST39LF800A	BGA 48	PA48BG48DAI
SST	SST39LF800A	WFBGA 48	PA48WFB48D1
SST	SST39VF100	TSOP 40	PA40TS14-OT
SST	SST39VF200A	TSOP 48	PA48TS48D1
SST	SST39VF200A	BGA 48	PA48BG48DAI
SST	SST39VF200A	WFBGA 48	PA48WFB48D1
SST	SST39VF400A	TSOP 48	PA48TS48D1
SST	SST39VF400A	BGA 48	PA48BG48DAI
SST	SST39VF400A	WFBGA 48	PA48WFB48D1
SST	SST39VF401C	TSOP 48	PA48TS48D1
SST	SST39VF800A	TSOP 48	PA48TS48D1
SST	SST39VF800A	BGA 48	PA48BG48DAI
SST	SST39VF800A	WFBGA 48	PA48WFB48D1
SST	SST39VF801C	TSOP 48	PA48TS48D1
SST	SST39VF400	TSOP 48	PA48TS48D1
SST	SST39VF400Q	TSOP 48	PA48TS48D1
SST	SST39VF800	TSOP 48	PA48TS48D1
SST	SST39VF800Q	TSOP 48	PA48TS48D1
SST	SST39VF160	TSOP 48	PA48TS48D1
SST	SST39VF160(Single)	TSOP 48	PA48TS48D1
SST	SST39VF160Q	TSOP 48	PA48TS48D1
SST	SST39VF160Q(Single)	TSOP 48	PA48TS48D1
SST	SST39VF320	TSOP 48	PA48TS48D1
SST	SST39VF640	TSOP 48	PA48TS48D1
SST	SST39VF1601	TSOP 48	PA48TS48D1



SST	SST39VF1601	WFBGA 48	PA48BG48DAI
SST	SST39VF1601C	TSOP 48	PA48TS48D1
SST	SST39VF1602	TSOP 48	PA48TS48D1
SST	SST39VF1681	TSOP 48	PA48TS48D1
SST	SST39VF1682	TSOP 48	PA48TS48D1
SST	SST39VF3201	TSOP 48	PA48TS48D1
SST	SST39VF3201	BGA 48	PA48BG48DAI
MICROCHIP	SST39VF3201C	TSOP 48	PA48TS48D1
SST	SST39VF3201B	TSOP 48	PA48TS48D1
SST	SST39VF3202	TSOP 48	PA48TS48D1
SST	SST39VF3202	BGA 48	PA48BG48DAI
SST	SST39VF6401	TSOP 48	PA48TS48D1
SST	SST39VF6401	BGA 48	HA48BG48DG1
SST	SST39VF6401B	TSOP 48	PA48TS48D1
SST	SST39VF6401B	BGA 48	HA48BG48DG1
SST	SST39VF6402	TSOP 48	PA48TS48D1
SST	SST39VF6402B	BGA 48	HA48BG48DG1
SST	SST39VF6402B	TSOP 48	PA48TS48D1
SST	SST39VF6402B	BGA 48	HA48BG48DG1
SST	SST39WF400A	WFBGA 48	PA48WFB48D
SST	SST39WF400B	WFBGA 48	PA48BG48DW
SST	SST39WF400B	WFBGA 48	HA48BG48DAI
SST	SST39WF800A	WFBGA 48	PA48WFB48D1
SST	SST39WF800B	WFBGA 48	PA48WFB48D1
SST	SST39WF1601	WFBGA 48	PA48BG48DW
SST	SST39WF1602	WFBGA 48	PA48BG48DW
SST	SST39WF1601	WFBGA 48	HA48BG48DAI
SST	SST39WF1602	WFBGA 48	HA48BG48DAI
SST	SST45LF010	SOP 8	PA16SO16D-EO-150
SST	SST45VF010	SOP 8	PA16SO16D-EO-150
SST	SST49LF002	PLCC 32	PA32PL32D
SST	SST49LF002	TSOP 32	PA32TS32D
SST	SST49LF002A	PLCC 32	PA32PL32D
SST	SST49LF002A	TSOP 40	PA40TS40D
SST	SST49LF002A	TSOP 32	PA32TS32D
SST	SST49LF002B	PLCC 32	PA32PL32D
SST	SST49LF002B	TSOP 32	PA32TS32D
SST	SST49LF002B	TSOP 40	PA40TS40D
SST	SST49LF003A	PLCC 32	PA32PL32D
SST	SST49LF003A	TSOP 32	PA32TS32D
SST	SST49LF003A	TSOP 40	PA40TS40D
SST	SST49LF003B	PLCC 32	PA32PL32D
SST	SST49LF003B	TSOP 32	PA32TS32D
SST	SST49LF003B	TSOP 40	PA40TS40D
SST	SST49LF004	PLCC 32	PA32PL32D
SST	SST49LF004	TSOP 32	PA32TS32D
SST	SST49LF004A	PLCC 32	PA32PL32D
SST	SST49LF004A	TSOP 32	PA32TS32D
SST	SST49LF004A	TSOP 40	PA40TS40D
SST	SST49LF004B	PLCC 32	PA32PL32D
SST	SST49LF004B	TSOP 32	PA32TS32D
SST	SST49LF004B	TSOP 40	PA40TS40D
SST	SST49LF004C	PLCC 32	PA32PL32D
SST	SST49LF004C	TSOP 32	PA32TS20/PA32TS32D-20
SST	SST49LF008	PLCC 32	PA32PL32D
SST	SST49LF008	TSOP 32	PA32TS32D
SST	SST49LF008A	PLCC 32	PA32PL32D
SST	SST49LF008A	TSOP 32	PA32TS32D
SST	SST49LF008A	TSOP 40	PA40TS40D
SST	SST49LF008B	PLCC 32	PA32PL32D
SST	SST49LF008B	TSOP 32	PA32TS32D
SST	SST49LF008B	TSOP 40	PA40TS40D
SST	SST49LF008C	PLCC 32	PA32PL32D
SST	SST49LF008C	TSOP 32	PA32TS20/PA32TS32D-20
SST	SST49LF020	PLCC 32	PA32PL32D
SST	SST49LF020	TSOP 32	PA32TS32D
SST	SST49LF020A	PLCC 32	PA32PL32D
SST	SST49LF020A	TSOP 32	PA32TS32D
SST	SST49LF030A	PLCC 32	PA32PL32D
SST	SST49LF040	PLCC 32	PA32PL32D
SST	SST49LF040	TSOP 32	PA32TS32D
SST	SST49LF040A	PLCC 32	PA32PL32D
SST	SST49LF040A	TSOP 32	PA32TS32D

SST	SST49LF040B	PLCC 32	PA32PL32D
SST	SST49LF040B	TSOP 32	PA32TS32D
SST	SST49LF080	PLCC 32	PA32PL32D
SST	SST49LF080	TSOP 32	PA32TS32D
SST	SST49LF080A	PLCC 32	PA32PL32D
SST	SST49LF080A	TSOP 32	PA32TS32D
SST	SST49LF016C(AAI)	PLCC 32	PA32PL32D
SST	SST49LF016C(AAI)	TSOP 32	PA32TS20/PA32TS32D-20
SST	SST49LF016C(AAI)	TSOP 32	PA32TS32D
SST	SST49LF016C(AAI)	TSOP 40	PA40TS40D
SST	SST49LF016C(LPC)	PLCC 32	PA32PL32D
SST	SST49LF016C(LPC)	TSOP 32	PA32TS20/PA32TS32D-20
SST	SST49LF016C(LPC)	TSOP 32	PA32TS32D
SST	SST49LF016C(LPC)	TSOP 40	PA40TS40D
SST	SST49LF016C(LPC)	PLCC 32	PA32PL32D
SST	SST49LF016C(FWH)	TSOP 32	PA32TS20/PA32TS32D-20
SST	SST49LF016C(FWH)	TSOP 32	PA32TS32D
SST	SST49LF016C(FWH)	TSOP 40	PA40TS40D
SST	SST49LF160C(AAI)	PLCC 32	PA32PL32D
SST	SST49LF160C(AAI)	TSOP 32	PA32TS20/PA32TS32D-20
SST	SST49LF160C(AAI)	TSOP 32	PA32TS32D
SST	SST49LF160C(AAI)	TSOP 40	PA40TS40D
SST	SST49LF160C(AAI)	PLCC 32	PA32PL28D-YA
GREENLIANT	GLS27SF512	DIP 32	
GREENLIANT	GLS27SF010	PLCC 32	PA32PL32D
GREENLIANT	GLS27SF010	DIP 32	
GREENLIANT	GLS27SF020	PLCC 32	PA32PL32D
SYNCMOS	F29C51001B	DIP 32	
SYNCMOS	F29C51001B	PLCC 32	PA32PL32D
SYNCMOS	F29C51001B	TSOP 32	PA32TS20/PA32TS32D-20
SYNCMOS	F29C51001T	DIP 32	
SYNCMOS	F29C51001T	PLCC 32	PA32PL32D
SYNCMOS	F29C51001T	TSOP 32	PA32TS20/PA32TS32D-20
SYNCMOS	S29C51001B	DIP 32	
SYNCMOS	S29C51001B	PLCC 32	PA32PL32D
SYNCMOS	S29C51001B	TSOP 32	PA32TS20/PA32TS32D-20
SYNCMOS	S29C51001T	DIP 32	
SYNCMOS	S29C51001T	PLCC 32	PA32PL32D
SYNCMOS	S29C51001T	TSOP 32	PA32TS20/PA32TS32D-20
SYNCMOS	F29C51002B	DIP 32	
SYNCMOS	F29C51002B	PLCC 32	PA32PL32D
SYNCMOS	F29C51002B	TSOP 32	PA32TS20/PA32TS32D-20
SYNCMOS	F29C51002T	DIP 32	
SYNCMOS	F29C51002T	PLCC 32	PA32PL32D
SYNCMOS	F29C51002T	TSOP 32	PA32TS20/PA32TS32D-20
SYNCMOS	S29C51002B	DIP 32	
SYNCMOS	S29C51002B	PLCC 32	PA32PL32D
SYNCMOS	S29C51002B	TSOP 32	PA32TS20/PA32TS32D-20
SYNCMOS	S29C51002T	DIP 32	
SYNCMOS	S29C51002T	PLCC 32	PA32PL32D
SYNCMOS	S29C51002T	TSOP 32	PA32TS20/PA32TS32D-20
SYNCMOS	F29C51004B	DIP 32	
SYNCMOS	F29C51004B	PLCC 32	PA32PL32D
SYNCMOS	F29C51004B	TSOP 32	PA32TS20/PA32TS32D-20
SYNCMOS	F29C51004T	DIP 32	
SYNCMOS	F29C51004T	PLCC 32	PA32PL32D
SYNCMOS	F29C51004T	TSOP 32	PA32TS20/PA32TS32D-20
SYNCMOS	S29C51004T	DIP 32	
SYNCMOS	S29C51004T	PLCC 32	PA32PL32D
SYNCMOS	S29C51004T	TSOP 32	PA32TS20/PA32TS32D-20
SYNCMOS	S29C31004B	DIP 32	
SYNCMOS	S29C31004B	PLCC 32	PA32PL32D
SYNCMOS	S29C31004B	TSOP 32	PA32TS20/PA32TS32D-20
SYNCMOS	S29C31004T	DIP 32	
SYNCMOS	S29C31004T	PLCC 32	PA32PL32D
SYNCMOS	S29C31004T	TSOP 32	PA32TS20/PA32TS32D-20
SYNERTEK	SY2716	DIP 24	
TEXAS INSTRUMENTS	SMJ2516	DIP 24	
TEXAS INSTRUMENTS	SMJ2764	DIP 28	
TEXAS INSTRUMENTS	SMJ27C64	DIP 28	
TEXAS INSTRUMENTS	SMJ27C256	DIP 28	
TEXAS INSTRUMENTS	SMJ27C256	PLCC 32	PA32PL28D-YA
TEXAS INSTRUMENTS	SMJ27C512	DIP 28	

TEXAS INSTRUMENTS	SMJ27C512	PLCC 32	PA32PL28D-YA
TEXAS INSTRUMENTS	TMS2516JL	DIP 24	
TEXAS INSTRUMENTS	TMS2532	DIP 24	
TEXAS INSTRUMENTS	TMS2532A	DIP 24	
TEXAS INSTRUMENTS	TMS2564	DIP 28	
TEXAS INSTRUMENTS	TMS2716JL	DIP 24	
TEXAS INSTRUMENTS	TMS2732A	DIP 24	
TEXAS INSTRUMENTS	TMS2764	DIP 28	
TEXAS INSTRUMENTS	TMS27128	DIP 28	
TEXAS INSTRUMENTS	TMS27C32	DIP 24	
TEXAS INSTRUMENTS	TMS27C64	DIP 28	
TEXAS INSTRUMENTS	TMS27C128	DIP 28	
TEXAS INSTRUMENTS	TMS27C128	PLCC 32	PA32PL28D-YA
TEXAS INSTRUMENTS	TMS27C256	DIP 28	
TEXAS INSTRUMENTS	TMS27C256	PLCC 32	PA32PL28D-YA
TEXAS INSTRUMENTS	TMS27C512	DIP 28	
TEXAS INSTRUMENTS	TMS27C512	PLCC 32	PA32PL28D-YA
TEXAS INSTRUMENTS	TMS27C010	DIP 32	
TEXAS INSTRUMENTS	TMS27C010	PLCC 32	PA32PL32D
TEXAS INSTRUMENTS	TMS27C010	TSOP 32	PA32TS20/PA32TS32D-20
TEXAS INSTRUMENTS	TMS27C010A	DIP 32	
TEXAS INSTRUMENTS	TMS27C010A	PLCC 32	PA32PL32D
TEXAS INSTRUMENTS	TMS27C010A	TSOP 32	PA32TS20/PA32TS32D-20
TEXAS INSTRUMENTS	TMS27C020	DIP 32	
TEXAS INSTRUMENTS	TMS27C020	PLCC 32	PA32PL32D
TEXAS INSTRUMENTS	TMS27C040	DIP 32	
TEXAS INSTRUMENTS	TMS27C040	PLCC 32	PA32PL32D
TEXAS INSTRUMENTS	TMS27P32A	DIP 24	
TEXAS INSTRUMENTS	TMS27P64	DIP 28	
TEXAS INSTRUMENTS	TMS27PC32	DIP 24	
TEXAS INSTRUMENTS	TMS27PC64	DIP 28	
TEXAS INSTRUMENTS	TMS27PC128	DIP 28	
TEXAS INSTRUMENTS	TMS27PC128	PLCC 32	PA32PL28D-YA
TEXAS INSTRUMENTS	TMS27PC256	DIP 28	
TEXAS INSTRUMENTS	TMS27PC256	PLCC 32	PA32PL28D-YA
TEXAS INSTRUMENTS	TMS27PC512	DIP 28	
TEXAS INSTRUMENTS	TMS27PC512	PLCC 32	PA32PL28D-YA
TEXAS INSTRUMENTS	TMS27LV010A	DIP 32	
TEXAS INSTRUMENTS	TMS27LV010A	PLCC 32	PA32PL32D
TEXAS INSTRUMENTS	TMS27LV010A	TSOP 32	PA32TS20/PA32TS32D-20
TEXAS INSTRUMENTS	TMS27PC010	DIP 32	
TEXAS INSTRUMENTS	TMS27PC010	PLCC 32	PA32PL32D
TEXAS INSTRUMENTS	TMS27PC010	TSOP 32	PA32TS20/PA32TS32D-20
TEXAS INSTRUMENTS	TMS27PC010A	PLCC 32	PA32PL32D
TEXAS INSTRUMENTS	TMS27PC010A	TSOP 32	PA32TS20/PA32TS32D-20
TEXAS INSTRUMENTS	TMS27PC020	DIP 32	
TEXAS INSTRUMENTS	TMS27PC020	PLCC 32	PA32PL32D
TEXAS INSTRUMENTS	TMS27PC040	DIP 32	
TEXAS INSTRUMENTS	TMS27PC040	PLCC 32	PA32PL32D
TEXAS INSTRUMENTS	TMS27C210	DIP 40	
TEXAS INSTRUMENTS	TMS27C210	PLCC 44	PA44-48U
TEXAS INSTRUMENTS	TMS27C210A	DIP 40	
TEXAS INSTRUMENTS	TMS27C210A	PLCC 44	PA44-48U
TEXAS INSTRUMENTS	TMS27C240	DIP 40	
TEXAS INSTRUMENTS	TMS27C240	PLCC 44	PA44-48U
TEXAS INSTRUMENTS	TMS27PC210	DIP 40	
TEXAS INSTRUMENTS	TMS27PC210	PLCC 44	PA44-48U
TEXAS INSTRUMENTS	TMS27PC210A	DIP 40	
TEXAS INSTRUMENTS	TMS27PC210A	PLCC 44	PA44-48U
TEXAS INSTRUMENTS	TMS27PC240	DIP 40	
TEXAS INSTRUMENTS	TMS27PC240	PLCC 44	PA44-48U
TEXAS INSTRUMENTS	TMS28C64	DIP 28	
TEXAS INSTRUMENTS	TMS28F020	DIP 32	
TEXAS INSTRUMENTS	TMS28F020	PLCC 32	PA32PL32D
TEXAS INSTRUMENTS	TMS28F020	TSOP 32	PA32TS20/PA32TS32D-20
TEXAS INSTRUMENTS	TMS28F512A	PLCC 32	PA32PL32D
TEXAS INSTRUMENTS	TMS29F010	DIP 32	
TEXAS INSTRUMENTS	TMS29F040	DIP 32	
TEXAS INSTRUMENTS	TMS29LF040	DIP 32	
TEXAS INSTRUMENTS	TMS29VF040	DIP 32	
TOSHIBA	TH50VSF2580A	BGA 69	PA69BGA48DF
TOSHIBA	TH50VSF2581A	BGA 69	PA69BGA48DF
TOSHIBA	TH50VSF3680A	BGA 69	PA69BGA48DF

TOSHIBA	TH50VSF3681A	BGA 69	PA69BGA48DF
TOSHIBA	TH50VSF3682A	BGA 69	PA69BGA48DF
TOSHIBA	TH50VSF3683A	BGA 69	PA69BGA48DF
TOSHIBA	TH50VSF4682AASB	BGA 69	PA69BGA48DI
TOSHIBA	TH50VSF4683AASB	BGA 69	PA69BGA48DI
TOSHIBA	TH50VSF4682BCSB	BGA 69	PA69BGA48DI
TOSHIBA	TH50VSF4683BCSB	BGA 69	PA69BGA48DI
TOSHIBA	TH50VPF5584ADSB	BGA 73	PA73BGA48DE-TO-7X10
TOSHIBA	TH50VPF5585ADSB	BGA 73	PA73BGA48DE-TO-7X10
TOSHIBA	TH50VPF6782AASB	BGA 69	PA69BGA48DK-TO-9X12
TOSHIBA	TH50VPF6783AASB	BGA 69	PA69BGA48DK-TO-9X12
TOSHIBA	TH50VPF6784AASB	BGA 69	PA69BGA48DK-TO-9X12
TOSHIBA	TH50VPF5682CDSB	BGA 73	PA73BGA48DE-TO-7X10
TOSHIBA	TH50VPF5683CDSB	BGA 73	PA73BGA48DE-TO-7X10
TOSHIBA	THPV357022BCBB	BGA 85	PA85BGA48DA-TO-7X10
TOSHIBA	THPV357023BCBB	BGA 85	PA85BGA48DA-TO-7X10
TOSHIBA	THPV057022BCBB	BGA 69	PA69BGA48DM
TOSHIBA	THPV068022AABB	BGA 69	PA69BGA48DM
TOSHIBA	THPV068023AABB	BGA 73	PA73BGA48DF
TOSHIBA	THPV068023AABB	BGA 73	PA73BGA48DF
TOSHIBA	TC531000CP	DIP 28	
TOSHIBA	TC531001CP	DIP 32	
TOSHIBA	TC531001CF	SOP 32	PA44SO44D
TOSHIBA	TC54256AF	DIP 28	
TOSHIBA	TC54256AP	DIP 28	
TOSHIBA	TC54512AP	DIP 28	
TOSHIBA	TC541000J	DIP 32	
TOSHIBA	TC541000P	DIP 32	
TOSHIBA	TC541001J	DIP 32	
TOSHIBA	TC541001P	DIP 32	
TOSHIBA	TC544000P	DIP 32	
TOSHIBA	TC54H1024P	DIP 40	
TOSHIBA	TC54H1024P	PLCC 44	PA44-48U
TOSHIBA	TC57256	DIP 28	
TOSHIBA	TC57256AD	DIP 28	
TOSHIBA	TC57256ADI	DIP 28	
TOSHIBA	TC57256D	DIP 28	
TOSHIBA	TC57512AD	DIP 28	
TOSHIBA	TC571000AD	DIP 32	
TOSHIBA	TC571000D	DIP 32	
TOSHIBA	TC571001AD	DIP 32	
TOSHIBA	TC571001D	DIP 32	
TOSHIBA	TC574000D	DIP 32	
TOSHIBA	TC574000DI	DIP 32	
TOSHIBA	TC571024D	DIP 40	
TOSHIBA	TC571024D	PLCC 44	PA44-48U
TOSHIBA	TC574096D	DIP 40	
TOSHIBA	TC574096D	PLCC 44	PA44-48U
TOSHIBA	TC574200D	DIP 40	
TOSHIBA	TC578200D	DIP 42	
TOSHIBA	TC57H1024AD	DIP 40	
TOSHIBA	TC57H1024AD	PLCC 44	PA44-48U
TOSHIBA	TC57H1024D	DIP 40	
TOSHIBA	TC57H1024D	PLCC 44	PA44-48U
TOSHIBA	TC57H1025AD	DIP 40	
TOSHIBA	TC57H1025AD	PLCC 44	PA44-48U
TOSHIBA	TC57H1000AD	DIP 32	
TOSHIBA	TC57H1001AD	DIP 32	
TOSHIBA	TC57H256D	DIP 28	
TOSHIBA	TC58DVG02A1FT00	TSOP 48	PA48TS48D
TOSHIBA	TC58DVG02A1FT00(+Spare)	TSOP 48	PA48TS48D
TOSHIBA	TC58FVB400FT	TSOP 48	PA48TS48D
TOSHIBA	TC58FVT400FT	TSOP 48	PA48TS48D
TOSHIBA	TC58FVB800FT	TSOP 48	PA48TS48D
TOSHIBA	TC58FVT800FT	TSOP 48	PA48TS48D
TOSHIBA	TC58FVB160FT	TSOP 48	PA48TS48D
TOSHIBA	TC58FVT160FT	TSOP 48	PA48TS48D
TOSHIBA	TC58FVB321FT	TSOP 48	PA48TS48D
TOSHIBA	TC58FVT321FT	TSOP 48	PA48TS48D
TOSHIBA	TC58FVB641FT	TSOP 48	PA48TS48D
TOSHIBA	TC58FVT641FT	TSOP 48	PA48TS48D
TOSHIBA	TC58FVM5B2A	TSOP 48	PA48TS48D
TOSHIBA	TC58FVM5B3A	TSOP 48	PA48TS48D

TOSHIBA	TC58FVM5T2A	TSOP 48	PA48TS48D
TOSHIBA	TC58FVM5T3A	TSOP 48	PA48TS48D
TOSHIBA	TC58FVM6B2AFT	TSOP 48	PA48TS48D
TOSHIBA	TC58FVM6T2AFT	TSOP 48	PA48TS48D
TOSHIBA	TMM24128A	DIP 28	
TOSHIBA	TMM24256A	DIP 28	
TOSHIBA	TMM24256B	DIP 28	
TOSHIBA	TMM24512	DIP 28	
TOSHIBA	TMM24512A	DIP 28	
TOSHIBA	TMM2464A	DIP 28	
TOSHIBA	TMM2732	DIP 24	
TOSHIBA	TMM2764	DIP 28	
TOSHIBA	TMM2764A	DIP 28	
TOSHIBA	TMM2764AD	DIP 28	
TOSHIBA	TMM2764ADI	DIP 28	
TOSHIBA	TMM2764D	DIP 28	
TOSHIBA	TMM2764DI	DIP 28	
TOSHIBA	TMM27128	DIP 28	
TOSHIBA	TMM27128A	DIP 28	
TOSHIBA	TMM27128AD	DIP 28	
TOSHIBA	TMM27128ADI	DIP 28	
TOSHIBA	TMM27128D	DIP 28	
TOSHIBA	TMM27128DI	DIP 28	
TOSHIBA	TMM27256	DIP 28	
TOSHIBA	TMM27256A	DIP 28	
TOSHIBA	TMM27256AD	DIP 28	
TOSHIBA	TMM27256ADI	DIP 28	
TOSHIBA	TMM27256BD	DIP 28	
TOSHIBA	TMM27256BDI	DIP 28	
TOSHIBA	TMM27256D	DIP 28	
TOSHIBA	TMM27256DI	DIP 28	
TOSHIBA	TMM27512	DIP 28	
TOSHIBA	TMM27512AD	DIP 28	
TOSHIBA	TMM27512ADI	DIP 28	
TOSHIBA	TMM27512D	DIP 28	
TOSHIBA	TMM27512DI	DIP 28	
TOSHIBA	TV00670002AABB	BGA 73	PA73BGA48DI
TOSHIBA	TV00678003AABB	BGA 107	HA107BG48DE
TOSHIBA	TV006C002SAABB	BGA 73	PA7064/96-84LC
TOSHIBA	THPV067Z03BABD	BGA 107	HA107BG48DF
TOSHIBA	TY9000A800E0GG	BGA 225	HA225BG48DA1
TOSHIBA	TY9000A800E0GG(+Spare)	BGA 225	HA225BG48DA1
VLSI	VT27C64	DIP 28	
VLSI	VT27C256	DIP 28	
VLSI	VT27C512	DIP 28	
WAFERSCALE INTEGRATION	WS27C010L	DIP 32	
WAFERSCALE INTEGRATION	WS27C040L	DIP 32	
WAFERSCALE INTEGRATION	WS27C128F	DIP 28	
WAFERSCALE INTEGRATION	WS27C128F	PLCC 32	PA32PL28D-YA
WAFERSCALE INTEGRATION	WS27C256F	DIP 28	
WAFERSCALE INTEGRATION	WS27C256F	PLCC 32	PA32PL28D-YA
WAFERSCALE INTEGRATION	WS27C256L	DIP 28	
WAFERSCALE INTEGRATION	WS27C512F	DIP 28	
WAFERSCALE INTEGRATION	WS27C512F	PLCC 32	PA32PL28D-YA
WAFERSCALE INTEGRATION	WS27C512L	DIP 28	
WAFERSCALE INTEGRATION	WS27C512L	PLCC 32	PA32PL28D-YA
WAFERSCALE INTEGRATION	WS27C64F	DIP 28	
WAFERSCALE INTEGRATION	WS27C64F	PLCC 32	PA32PL28D-YA
WAFERSCALE INTEGRATION	WS27C64L	DIP 28	
WAFERSCALE INTEGRATION	WS27C64L	PLCC 32	PA32PL28D-YA
WAFERSCALE INTEGRATION	WS57C128F	DIP 28	
WAFERSCALE INTEGRATION	WS57C256F	DIP 28	
WAFERSCALE INTEGRATION	WS57C512F	DIP 28	
WAFERSCALE INTEGRATION	WS57C64F	DIP 28	
WAFERSCALE INTEGRATION	WS27C210L	DIP 40	
WAFERSCALE INTEGRATION	WS27C210L	PLCC 44	PA44-48U
WHITE MICROELECTRONICS	WE128K8	DIP 32	
WHITE MICROELECTRONICS	WE256K8	DIP 32	
WHITE MICROELECTRONICS	WE512K8	DIP 32	
GIGADEVICE	GD25Q41BSIG	SOIC 8	PA20SO20D-EO-210
GIGADEVICE	GD25Q41BTIG	SOIC 8	PA16SO16D-EO-150
GIGADEVICE	GD25Q41BOIG	TSSOP 8	PA8TSS8D
GIGADEVICE	GD25Q41BUIG	USON 8	HBP8USON48DB

GIGADEVICE	GD25Q41BWIG	WSON 8	PA8SON8D
GIGADEVICE	GD25Q40BSIG	SOIC 8	PA20SO20D-EO-210
GIGADEVICE	GD25Q40BTIG	SOIC 8	PA16SO16D-EO-150
GIGADEVICE	GD25Q40BOIG	TSSOP 8	PA8TSS8D
GIGADEVICE	GD25Q40BUIG	USON 8	HBP8USON48DB
GIGADEVICE	GD25Q80BSIG	SOIC 8	PA20SO20D-EO-210
GIGADEVICE	GD25Q80BTIG	SOIC 8	PA16SO16D-EO-150
GIGADEVICE	GD25Q80BPIG	DIP 8	
GIGADEVICE	GD25Q80BUIG	USON 8	HBP8USON48DB
GIGADEVICE	GD25Q32SIG	SOIC 8	PA20SO20D-EO-210
GIGADEVICE	GD25Q32WIG	WSON 8	PA8SON8D
GIGADEVICE	GD25Q32PIG	DIP 8	
GIGADEVICE	GD25Q32ZIG	BGA 24	NA24BG48D-D
GIGADEVICE	GD25Q32FIG	SOIC 16	PA28SO28D-EO-300
GIGADEVICE	GD25Q32BSIG	SOIC 8	PA20SO20D-EO-210
GIGADEVICE	GD25Q32BWIG	WSON 8	PA8SON8D
GIGADEVICE	GD25Q32BPIG	DIP 8	
GIGADEVICE	GD25Q32BZIG	BGA 24	NA24BG48D-D
GIGADEVICE	GD25Q32CSIG	SOIC 8	PA20SO20D-EO-210
GIGADEVICE	GD25Q32CWIG	WSON 8	PA8SON8D
GIGADEVICE	GD25Q32CPIG	DIP 8	
GIGADEVICE	GD25Q32CZIG	BGA 24	NA24BG48D-D
GIGADEVICE	GD25Q64BSIG	SOIC 8	PA20SO20D-EO-210
GIGADEVICE	GD25Q64BFIG	SOIC 16	PA28SO28D-EO-300
GIGADEVICE	GD25Q64BWIG	WSON 8	PA8SON8D
GIGADEVICE	GD25Q64BZIG	BGA 24	NA24BG48D-D
GIGADEVICE	GD25Q64BPIG	DIP 8	
GIGADEVICE	GD25Q64CSIG	SOIC 8	PA20SO20D-EO-210
GIGADEVICE	GD25Q64CFIG	SOIC 16	PA28SO28D-EO-300
GIGADEVICE	GD25Q64CWIG	WSON 8	PA8SON8D
GIGADEVICE	GD25Q64CZIG	BGA 24	NA24BG48D-D
GIGADEVICE	GD25Q64CPIG	DIP 8	
GIGADEVICE	GD25B64BPIG	DIP 8	
GIGADEVICE	GD25B64BFIG	SOIC 16	PA28SO28D-EO-300
GIGADEVICE	GD25B64BWIG	WSON 8	PA8SON8D
GIGADEVICE	GD25B64BZIG	BGA 24	NA24BG48D-D
GIGADEVICE	GD25LQ64BWIG	WSON 8	HA8SON48DGD
GIGADEVICE	GD25LQ64BVI	SOIC 8	HA8SO48DAC
GIGADEVICE	GD25Q128BYIG	WSON 8	PA8SON8DA
GIGADEVICE	GD25Q128BFIG	SOIC 16	PA28SO28D-EO-300
GIGADEVICE	GD25Q128BZIG	BGA 24	NA24BG48D-D
GIGADEVICE	GD25Q128CFIG	SOIC 16	PA28SO28D-EO-300
GIGADEVICE	GD25Q128CSIG	SOIC 8	PA20SO20D-EO-210
GIGADEVICE	GD25Q128CWIG	WSON 8	PA8SON8D
GIGADEVICE	GD25Q128CYIG	WSON 8	PA8SON8DA
GIGADEVICE	GD25Q128CZIG	BGA 24	NA24BG48D-D
GIGADEVICE	GD25Q256CFIG	SOIC 16	PA28SO28D-EO-300
GIGADEVICE	GD25Q256CYIG	WSON 8	PA8SON8DA
GIGADEVICE	GD25Q256CWIG	WSON 8	PA8SON8D
GIGADEVICE	GD25Q256CZIG	BGA 24	NA24BG48D-D
GIGADEVICE	GD25Q256CBIG	BGA 24	NA24BG48DA
WINBOND	W25D10VSNIG	SOIC 8	PA16SO16D-EO-150
WINBOND	W25D20VSNIG	SOIC 8	PA16SO16D-EO-150
WINBOND	W25D40VSNIG	SOIC 8	PA16SO16D-EO-150
WINBOND	W25D40VSSIG	SOIC 8	PA20SO20D-EO-210
WINBOND	W25D80VSSIG	SOIC 8	PA20SO20D-EO-210
WINBOND	W25D80VSNIG	SOIC 8	PA16SO16D-EO-150
WINBOND	W25D80VDAIG	DIP 8	
WINBOND	W25D80VZPIG	WSON 8	PA8SON8D
WINBOND	W25P10VSNIG	SOIC 8	PA16SO16D-EO-150
WINBOND	W25P10VSNIG	SOIC 8	PA16SO16D-EO-150
WINBOND	W25P20VSNIG	SOIC 8	PA16SO16D-EO-150
WINBOND	W25P20VSNIG	SOIC 8	PA16SO16D-EO-150
WINBOND	W25P40VSNIG	SOIC 8	PA16SO16D-EO-150
WINBOND	W25P40VSNIG	SOIC 8	PA16SO16D-EO-150
WINBOND	W25P80VSSIG	SOIC 8	PA20SO20D-EO-210
WINBOND	W25P16VSSIG	SOIC 8	PA20SO20D-EO-210
WINBOND	W25P16VSFIG	SOIC 16	PA28SO28D-EO-300
WINBOND	W25P32VSFIG	SOIC 16	PA28SO28D-EO-300
WINBOND	W25X10BVSNIG	SOIC 8	PA16SO16D-EO-150
WINBOND	W25X20VSNIG	SOIC 8	PA16SO16D-EO-150
WINBOND	W25X40VSNIG	SOIC 8	PA16SO16D-EO-150
WINBOND	W25X40VSSIG	SOIC 8	PA20SO20D-EO-210

WINBOND	W25X40VZPIG	WSO8 8	PA8SON8D
WINBOND	W25X40VDAIG	DIP 8	
WINBOND	W25X40BVSNI	SOIC 8	PA16SO16D-EO-150
WINBOND	W25X40BVSSIG	SOIC 8	PA20SO20D-EO-210
WINBOND	W25X40BVZPIG	WSO8 8	PA8SON8D
WINBOND	W25X40BVDAIG	DIP 8	
WINBOND	W25X80VSSIG	SOIC 8	PA20SO20D-EO-210
WINBOND	W25X80VDAIZ	DIP 8	
WINBOND	W25X16VSSIG	SOIC 8	PA20SO20D-EO-210
WINBOND	W25X16VSFIG	SOIC 16	PA28SO28D-EO-300
WINBOND	W25X16VZPIG	WSO8 8	PA8SON8D
WINBOND	W25X16VZEIG	WSO8 8	PA8SON8DA
WINBOND	W25X16VDAIG	DIP 8	
WINBOND	W25X16AV	DIP 8	
WINBOND	W25X16AV	SOIC 8	PA20SO20D-EO-210
WINBOND	W25X16AV	SOIC 8	PA16SO16D-EO-150
WINBOND	W25X16AVZPIG	WSO8 8	PA8SON8DA
WINBOND	W25X16AVZEIG	WSO8 8	PA8SON8D
WINBOND	W25X16AVSFIG	SOIC 16	PA28SO28D-EO-300
WINBOND	W25X32VSSIG	SOIC 8	PA20SO20D-EO-210
WINBOND	W25X32VSFIG	SOIC 16	PA28SO28D-EO-300
WINBOND	W25X32VZPIG	WSO8 8	PA8SON8D
WINBOND	W25X32VZEIG	WSO8 8	PA8SON8DA
WINBOND	W25X32VDAIG	DIP 8	
WINBOND	W25X05CLSNIG	SOIC 8	PA16SO16D-EO-150
WINBOND	W25X05CLSDIG	TSSOP 8	PA8TSS8D
WINBOND	W25X05CLUXIG	USO8 8	HBP8USO48DB
WINBOND	W25X10AVSNI	SOIC 8	PA16SO16D-EO-150
WINBOND	W25X10AVSSIG	SOIC 8	PA20SO20D-EO-210
WINBOND	W25X10AVZPIG	WSO8 8	PA8SON8D
WINBOND	W25X10AVDAIG	DIP 8	
WINBOND	W25X10CLSNIG	SOIC 8	PA16SO16D-EO-150
WINBOND	W25X10CLUXIG	USO8 8	HBP8USO48DB
WINBOND	W25X20BVSNI	SOIC 8	PA16SO16D-EO-150
WINBOND	W25X20BVSSIG	SOIC 8	PA20SO20D-EO-210
WINBOND	W25X20BVZPIG	WSO8 8	PA8SON8D
WINBOND	W25X20BVDAIG	DIP 8	
WINBOND	W25X20CLSNIG	SOIC 8	PA16SO16D-EO-150
WINBOND	W25X20CLSDIG	TSSOP 8	PA8TSS8D
WINBOND	W25X20CLZPIG	WSO8 8	PA8SON8D
WINBOND	W25X20CLUXIG	USO8 8	HBP8USO48DB
WINBOND	W25X40CLSNIG	SOIC 8	PA16SO16D-EO-150
WINBOND	W25X40CLSSIG	SOIC 8	PA20SO20D-EO-210
WINBOND	W25X40CLUXIG	USO8 8	HBP8USO48DB
WINBOND	W25X40CLZPIG	WSO8 8	PA8SON8D
WINBOND	W25X40CLDAIG	DIP 8	
WINBOND	W25Q40CLSNIG	SOIC 8	PA16SO16D-EO-150
WINBOND	W25Q40CLSSIG	SOIC 8	PA20SO20D-EO-210
WINBOND	W25Q40CLUXIG	USO8 8	HBP8USO48DB
WINBOND	W25X80AVSNI	SOIC 8	PA16SO16D-EO-150
WINBOND	W25X80AVSSIG	SOIC 8	PA20SO20D-EO-210
WINBOND	W25X80AVZPIG	WSO8 8	PA8SON8D
WINBOND	W25X80AVDAIG	DIP 8	
WINBOND	W25X64VIG	WSO8 8	PA8SON20D
WINBOND	W25X64VFIG	SOIC 16	PA28SO28D-EO-300
WINBOND	W25X64VDAIG	DIP 8	
WINBOND	W25X64VZEIG	WSO8 8	PA8SON8DA
WINBOND	W25X64VZPIG	WSO8 8	PA8SON8D
WINBOND	W25X64VSSIG	WSO8 8	PA20SO20D-EO-210
WINBOND	W25Q64CVIG	WSO8 8	PA8SON8D
WINBOND	W25Q16DWZPIG	WSO8 8	PA8SON8D
WINBOND	W25Q40BWSNI	SOIC 8	HA8SO48DAD
WINBOND	W25Q40BWSSIG	SOIC 8	HA8SO48DAC
WINBOND	W25Q40BWUXIG	USO8 8	HBP8USO48DC
WINBOND	W25Q40BWZPIG	WSO8 8	HA8SON48DG
WINBOND	W25X80BVSNI	SOIC 8	PA16SO16D-EO-150
WINBOND	W25Q16DWSNI	SOIC 8	PA16SO16D-EO-150
WINBOND	W25X16BVSFIG	SOIC 16	PA28SO28D-EO-300
WINBOND	W25X32BVSFIG	SOIC 16	PA28SO28D-EO-300
WINBOND	W25X64BVSFIG	SOIC 16	PA28SO28D-EO-300
WINBOND	W25Q16DWSFIG	SOIC 16	PA28SO28D-EO-300
WINBOND	W25Q16BV	WSO8 8	PA8SON8D
WINBOND	W25Q16BVAIG	DIP 8	

WINBOND	W25Q16BVSF1G	SOIC 16	PA28SO28D-EO-300
WINBOND	W25Q16BVSS1G	SOIC 8	PA20SO20D-EO-210
WINBOND	W25Q16BVSN1G	SOIC 8	PA16SO16D-EO-150
WINBOND	W25Q16DVSN1G	SOIC 8	PA16SO16D-EO-150
WINBOND	W25Q16DVSS1G	SOIC 8	PA20SO20D-EO-210
WINBOND	W25Q16DVDA1G	DIP 8	
WINBOND	W25Q16DVSF1G	SOIC 16	PA28SO28D-EO-300
WINBOND	W25Q16DVTB1G	BGA 24	NA24BG48DA
WINBOND	W25Q16DVT1G	BGA 24	NA24BG48D-D
WINBOND	W25Q16DVZP1G	WSON 8	PA8SON8D
WINBOND	W25Q16DVUU1G	USON 8	HBP8USON48D
WINBOND	W25Q16DVUZ1G	USON 8	HA8MLF48D
WINBOND	W25Q32BVSS1G	SOIC 8	PA20SO20D-EO-210
WINBOND	W25Q32BVSF1G	SOIC 16	PA28SO28D-EO-300
WINBOND	W25Q32BVA1G	DIP 8	
WINBOND	W25Q32BVZP1G	WSON 8	PA8SON8D
WINBOND	W25Q32BVZE1G	WSON 8	PA8SON8DA
WINBOND	W25Q32BVTB1G	BGA 24	NA24BG48DA
WINBOND	W25Q32BVT1G	BGA 24	NA24BG48D-D
WINBOND	W25Q32FV1G	SOIC 16	PA28SO28D-EO-300
WINBOND	W25Q32FVSS1G	SOIC 8	PA20SO20D-EO-210
WINBOND	W25Q32FVZE1G	WSON 8	PA8SON8DA
WINBOND	W25Q32FVTB1G	BGA 24	NA24BG48DA
WINBOND	W25Q32FVT1G	BGA 24	NA24BG48D-D
WINBOND	W25Q32FVDA1G	DIP 8	
WINBOND	W25Q32FWSS1G	SOIC 8	HA8SO48DAC
WINBOND	W25Q32FWZP1G	WSON 8	HA8SON48DG
WINBOND	W25Q64BVSS1G	SOIC 8	PA20SO20D-EO-210
WINBOND	W25Q64BVSF1G	SOIC 16	PA28SO28D-EO-300
WINBOND	W25Q64BVDA1G	DIP 8	
WINBOND	W25Q64BVZE1G	WSON 8	PA8SON8DA
WINBOND	W25Q64CVSS1G	SOIC 8	PA20SO20D-EO-210
WINBOND	W25Q64CVSF1G	SOIC 16	PA28SO28D-EO-300
WINBOND	W25Q64CVZP1G	WSON 8	PA8SON8D
WINBOND	W25Q64CVZE1G	WSON 8	PA8SON8DA
WINBOND	W25Q64CVTB1G	BGA 24	NA24BG48DA
WINBOND	W25Q64CVT1G	BGA 24	NA24BG48D-D
WINBOND	W25Q64CVDA1G	DIP 8	
WINBOND	W25Q64FV1G	SOIC 16	PA28SO28D-EO-300
WINBOND	W25Q64FVSS1G	SOIC 8	PA20SO20D-EO-210
WINBOND	W25Q64FVDA1G	DIP 8	
WINBOND	W25Q64FVZP1G	WSON 8	PA8SON8D
WINBOND	W25Q64FVZE1G	WSON 8	PA8SON8DA
WINBOND	W25Q64FVTB1G	BGA 24	NA24BG48DA
WINBOND	W25Q64FVT1G	BGA 24	NA24BG48D-D
WINBOND	W25Q64FWSS1G	SOIC 8	PA20SO20D-EO-210
WINBOND	W25Q64FWSF1G	SOIC 16	PA28SO28D-EO-300
WINBOND	W25Q64FWZP1G	WSON 8	PA8SON8D
WINBOND	W25Q64FWZE1G	WSON 8	PA8SON8DA
WINBOND	W25Q64FWTB1G	BGA 24	NA24BG48DA
WINBOND	W25Q64FWT1G	BGA 24	NA24BG48D-D
WINBOND	W25Q256FV1G	SOIC 16	PA28SO28D-EO-300
WINBOND	W25Q256FVE1G	WSON 8	PA8SON8DA
WINBOND	W25Q256FVB1G	BGA 24	NA24BG48DA
WINBOND	W25Q256FVC1G	BGA 24	NA24BG48D-D
WINBOND	W25X16BVSS1G	SOIC 8	PA20SO20D-EO-210
WINBOND	W25X32BVSS1G	SOIC 8	PA20SO20D-EO-210
WINBOND	W25X64BVSS1G	SOIC 8	PA20SO20D-EO-210
WINBOND	W25Q16DWSS1G	SOIC 8	PA20SO20D-EO-210
WINBOND	W25Q80BVSS1G	SOIC 8	PA20SO20D-EO-210
WINBOND	W25Q80BVSN1G	SOIC 8	PA16SO16D-EO-150
WINBOND	W25Q80BVZP1G	WSON 8	PA8SON8D
WINBOND	W25Q80BVUX1G	USON 8	HBP8USON48DB
WINBOND	W25Q80BVDA1G	DIP 8	
WINBOND	W25Q80DVSS1G	SOIC 8	PA20SO20D-EO-210
WINBOND	W25Q80DVSN1G	SOIC 8	PA16SO16D-EO-150
WINBOND	W25Q80DVZP1G	WSON 8	PA8SON8D
WINBOND	W25Q80DVUX1G	USON 8	HBP8USON48DB
WINBOND	W25Q80DVDA1G	DIP 8	
WINBOND	W25Q128BV1G	SOIC 16	PA28SO28D-EO-300
WINBOND	W25Q128BVE1G	WSON 8	PA8SON8DA
WINBOND	W25Q128BVB1G	BGA 24	NA24BG48DA
WINBOND	W25Q128BVC1G	BGA 24	NA24BG48D-D



WINBOND	W25Q128FVSIQ	SOIC 8	PA20SO20D-EO-210
WINBOND	W25Q128FVSIQ	SOIC 8	PA20SO20D-EO-210
WINBOND	W25Q128FVAIG	DIP 8	
WINBOND	W25Q128FVPIG	WSON 8	PA8SON8D
WINBOND	W25Q128FVEIG	WSON 8	PA8SON8DA
WINBOND	W25Q128FVBIQ	BGA 24	NA24BG48DA
WINBOND	W25Q128FVCIG	BGA 24	NA24BG48D-D
WINBOND	W29GL032CB-S	TSOP 48	PA48TS48D1
WINBOND	W29GL032CT-S	TSOP 48	PA48TS48D1
WINBOND	W29GL128CL-T	TSOP 56	HA56TS48DI
WINBOND	W29GL128CH-T	TSOP 56	HA56TS48DI
WINBOND	W29GL128CL-B	BGA 64	PA64BG48DR
WINBOND	W29GL128CH-B	BGA 64	PA64BG48DR
WINBOND	W29GL128CL-C	BGA 56	NA56BG48DU
WINBOND	W29GL128CH-C	BGA 56	NA56BG48DU
WINBOND	W29GL256SL-T	TSOP 56	HA56TS48DI
WINBOND	W29GL256SH-T	TSOP 56	HA56TS48DI
WINBOND	W29GL256SL-B	BGA 64	PA64BG48DR
WINBOND	W29GL256SH-B	BGA 64	PA64BG48DR
WINBOND	W29GL256SL-C	BGA 56	NA56BG48DU
WINBOND	W29GL256SH-C	BGA 56	NA56BG48DU
WINBOND	W19L320SBT	TSOP 48	PA48TS48D
WINBOND	W19L320STT	TSOP 48	PA48TS48D
WINBOND	W19B320AB	TSOP 48	PA48TS48D
WINBOND	W19B320AT	TSOP 48	PA48TS48D
WINBOND	W19B320BBT	TSOP 48	PA48TS48D
WINBOND	W19B320BTT	TSOP 48	PA48TS48D
WINBOND	W27C512	DIP 28	
WINBOND	W27C512	PLCC 32	PA32PL28D-YA
WINBOND	W27C010	DIP 32	
WINBOND	W27C010	PLCC 32	PA32PL32D
WINBOND	W27C010	SOP 32	PA32SO32D-EO-450
WINBOND	W27C020	DIP 32	
WINBOND	W27C020	PLCC 32	PA32PL32D
WINBOND	W27C020M	DIP 32	
WINBOND	W27C020M	PLCC 32	PA32PL32D
WINBOND	W27E256	DIP 28	
WINBOND	W27E257	DIP 28	
WINBOND	W27E512	DIP 28	
WINBOND	W27E512	PLCC 32	PA32PL28D-YA
WINBOND	W27E512	TSOP 28	PA28TS28D-EO
WINBOND	W27E010	DIP 32	
WINBOND	W27E010	PLCC 32	PA32PL32D
WINBOND	W27E010	SOP 32	PA32SO32D-EO-450
WINBOND	W27E020	DIP 32	
WINBOND	W27E020	PLCC 32	PA32PL32D
WINBOND	W27E040	DIP 32	
WINBOND	W27E040	PLCC 32	PA32PL32D
WINBOND	W27E040	TSOP 32	PA32TS20/PA32TS32D-20
WINBOND	W27E040	SOP 32	PA32SO32D-EO-450
WINBOND	W27E4096	DIP 40	
WINBOND	W27E4096	PLCC 44	PA44-48U
WINBOND	W27F256	DIP 28	
WINBOND	W27F512	DIP 28	
WINBOND	W27F010	DIP 32	
WINBOND	W27L010	DIP 32	
WINBOND	W27L010	PLCC 32	PA32PL32D
WINBOND	W27L010	SOP 32	PA32SO32D-EO-450
WINBOND	W27L02	DIP 32	
WINBOND	W27L02P	PLCC 32	PA32PL32D
WINBOND	W27L02Q	TSOP 32	PA32TS20/PA32TS32D-20
WINBOND	W29C010	DIP 32	
WINBOND	W29C010	PLCC 32	PA32PL32D
WINBOND	W29C010	SOP 32	PA32SO32D-EO-450
WINBOND	W29C011	DIP 32	
WINBOND	W29C011	PLCC 32	PA32PL32D
WINBOND	W29C011	SOP 32	PA32SO32D-EO-450
WINBOND	W29C011A	DIP 32	
WINBOND	W29C011A	PLCC 32	PA32PL32D
WINBOND	W29C011A	SOP 32	PA32SO32D-EO-450
WINBOND	W29C020	DIP 32	
WINBOND	W29C020P	PLCC 32	PA32PL32D
WINBOND	W29C020T	TSOP 32	PA32TS20/PA32TS32D-20

WINBOND	W29C040	DIP 32	
WINBOND	W29C040P	PLCC 32	PA32PL32D
WINBOND	W29C040T	TSOP 32	PA32TS20/PA32TS32D-20
WINBOND	W29C101	DIP 40	
WINBOND	W29C101	PLCC 44	PA44-48U
WINBOND	W29C101	TSOP 40	PA40TS40D
WINBOND	W29C102	DIP 40	
WINBOND	W29C102	PLCC 44	PA44-48U
WINBOND	W29C102	TSOP 40	PA40TS40D
WINBOND	W29EE010	DIP 32	
WINBOND	W29EE010	PLCC 32	PA32PL32D
WINBOND	W29EE010	TSOP 32	PA32TS20/PA32TS32D-20
WINBOND	W29EE010	SOP 32	PA32SO32D-EO-450
WINBOND	W29EE011	DIP 32	
WINBOND	W29EE011	PLCC 32	PA32PL32D
WINBOND	W29EE011	TSOP 32	PA32TS20/PA32TS32D-20
WINBOND	W29EE011	SOP 32	PA32SO32D-EO-450
WINBOND	W29EE012	PLCC 32	PA32PL32D
WINBOND	W29EE012	TSOP 32	PA32TS20/PA32TS32D-20
WINBOND	W29EE021	DIP 32	
WINBOND	W29EE512	DIP 32	
WINBOND	W29EE512	PLCC 32	PA32PL32D
WINBOND	W29F102	PLCC 44	PA44-48U
WINBOND	W29F102	TSOP 40	PA40TS40D
WINBOND	W39L020P	PLCC 32	PA32PL32D
WINBOND	W39L040P	PLCC 32	PA32PL32D
WINBOND	W39L040T	TSOP 32	PA32TS20/PA32TS32D-20
WINBOND	W39L040Q	sTSOP 32	PA32TS32D-14
WINBOND	W39L040AP	PLCC 32	PA32PL32D
WINBOND	W39L040AT	TSOP 32	PA32TS20/PA32TS32D-20
WINBOND	W39L040AQ	sTSOP 32	PA32TS32D-14
WINBOND	W39V040FAP	PLCC 32	PA32PL32D
WINBOND	W39V040FAPZ	PLCC 32	PA32PL32D
WINBOND	W39V040AP	PLCC 32	PA32PL32D
WINBOND	W39V040APZ	PLCC 32	PA32PL32D
WINBOND	W39V040BP	PLCC 32	PA32PL32D
WINBOND	W39V040BPZ	PLCC 32	PA32PL32D
WINBOND	W39V040CP	PLCC 32	PA32PL32D
WINBOND	W39V040CPZ	PLCC 32	PA32PL32D
WINBOND	W39V080AP	PLCC 32	PA32PL32D
WINBOND	W39V080APZ	PLCC 32	PA32PL32D
WINBOND	W49L102	TSOP 40	PA40TS14-OT
WINBOND	W49L201S	SOP 44	PA44SO44D
WINBOND	W49L201T	TSOP 48	PA48TS48D
WINBOND	W49L401S	SOP 44	PA44SO44D
WINBOND	W49L401T	TSOP 48	PA48TS48D
WINBOND	W49L401TS	SOP 44	PA44SO44D
WINBOND	W49L401TT	TSOP 48	PA48TS48D
WINBOND	W49F020	DIP 32	
WINBOND	W49F020P	PLCC 32	PA32PL32D
WINBOND	W49F020T	TSOP 32	PA32TS20/PA32TS32D-20
WINBOND	W49F002A	DIP 32	
WINBOND	W49F002A	PLCC 32	PA32PL32D
WINBOND	W49F002U	DIP 32	
WINBOND	W49F002U	PLCC 32	PA32PL32D
WINBOND	W49F002U	TSOP 32	PA32TS20/PA32TS32D-20
WINBOND	W49F102	PLCC 44	PA44-48U
WINBOND	W49F102	TSOP 40	PA40TS14-OT
WINBOND	W49F201S	SOP 44	PA44SO44D
WINBOND	W49F201T	TSOP 48	PA48TS48D
WINBOND	W49V002	DIP 32	
WINBOND	W49V002	PLCC 32	PA32PL32D
WINBOND	W49V002Q	TSOP 32	PA32TS20/PA32TS32D-20
WINBOND	W49V002AP	PLCC 32	PA32PL32D
WINBOND	W49V002AQ	TSOP 32	PA32TS20/PA32TS32D-20
WINBOND	W49V002FP	PLCC 32	PA32PL32D
WINBOND	W49V002FQ	TSOP 32	PA32TS20/PA32TS32D-20
WINBOND	W49V002FAP	PLCC 32	PA32PL32D
WINBOND	W49V002FAP	TSOP 32	PA32TS20/PA32TS32D-20
WINBOND	W49V002FAQ	TSOP 32	PA32TS20/PA32TS32D-20
XICOR	X2004	DIP 28	
XICOR	X2016	DIP 28	
XICOR	X20C04	DIP 28	
XICOR	X20C04	PLCC 32	PA32PL32D

XICOR	X20C16	DIP 28	
XICOR	X20C16	PLCC 32	PA32PL32D
XICOR	X20C16	SOIC 28	PA28SO28D-EO-300
XICOR	X20C16	TSOP 32	PA32TS32D
XICOR	X2210	DIP 18	
XICOR	X2210A	DIP 18	
XICOR	X22C10	DIP 18	
XICOR	X22C10	SOIC 16	PA16SO16D-EO-150
XICOR	X2212	DIP 18	
XICOR	X2212A	DIP 18	
XICOR	X22C12	DIP 18	
XICOR	X22C12	SOIC 20	PA28SO28D-EO-300
XICOR	X2402	DIP 8	
XICOR	X2404	DIP 8	
XICOR	X24164	DIP 8	
XICOR	X24320	DIP 8	
XICOR	X24325	DIP 8	
XICOR	X24645	DIP 8	
XICOR	X24320	SOIC 8	PA16SO16D-EO-150
XICOR	X24325	SOIC 8	PA16SO16D-EO-150
XICOR	X24645	SOIC 8	PA16SO16D-EO-150
XICOR	X24320	TSSOP 14	PA14TSS14D
XICOR	X24325	TSSOP 14	PA14TSS14D
XICOR	X24645	TSSOP 14	PA14TSS14D
XICOR	X24645	TSSOP 20	PA20TSS20D
XICOR	X24001	DIP 8	
XICOR	X24C00	DIP 8	
XICOR	X24C00	SOIC 8	PA16SO16D-EO-150
XICOR	X24C01	DIP 8	
XICOR	X24C01A	DIP 8	
XICOR	X24C02	DIP 8	
XICOR	X24C04	DIP 8	
XICOR	X24C08	DIP 8	
XICOR	X24C16	DIP 8	
XICOR	X24C44	DIP 8	
XICOR	X24C44	SOIC 8	PA16SO16D-EO-150
XICOR	X24F016	DIP 8	
XICOR	X24F032	DIP 8	
XICOR	X24F064	DIP 8	
XICOR	X24F128	DIP 8	
XICOR	X24F016	SOIC 8	PA16SO16D-EO-150
XICOR	X24F032	SOIC 8	PA16SO16D-EO-150
XICOR	X24F064	SOIC 8	PA16SO16D-EO-150
XICOR	X24F128	SOIC 8	PA16SO16D-EO-150
XICOR	X24F016	TSSOP 14	PA14TSS14D
XICOR	X24F032	TSSOP 14	PA14TSS14D
XICOR	X24F064	TSSOP 20	PA20TSS20D
XICOR	X24F128	SOIC 16	PA16SO16D-EO-150
XICOR	X25043	DIP 8	
XICOR	X25043	SOIC 8	PA16SO16D-EO-150
XICOR	X25043	TSSOP 14	PA14TSS14D
XICOR	X25045	DIP 8	
XICOR	X25045	SOIC 8	PA16SO16D-EO-150
XICOR	X25045	TSSOP 14	PA14TSS14D
XICOR	X25163	DIP 8	
XICOR	X25163	SOIC 8	PA16SO16D-EO-150
XICOR	X25163	SOIC 14	PA16SO16D-EO-150
XICOR	X25163	TSSOP 14	PA14TSS14D
XICOR	X25163(1.8)	DIP 8	
XICOR	X25163(1.8)	SOIC 8	PA16SO16D-EO-150
XICOR	X25163(1.8)	SOIC 14	PA16SO16D-EO-150
XICOR	X25163(1.8)	TSSOP 14	PA14TSS14D
XICOR	X25165	DIP 8	
XICOR	X25165	SOIC 8	PA16SO16D-EO-150
XICOR	X25165	SOIC 14	PA16SO16D-EO-150
XICOR	X25165	TSSOP 14	PA14TSS14D
XICOR	X25165(1.8)	DIP 8	
XICOR	X25165(1.8)	SOIC 8	PA16SO16D-EO-150
XICOR	X25165(1.8)	SOIC 14	PA16SO16D-EO-150
XICOR	X25165(1.8)	TSSOP 14	PA14TSS14D
XICOR	X25168	DIP 8	
XICOR	X25168	SOIC 8	PA16SO16D-EO-150
XICOR	X25168	SOIC 14	PA16SO16D-EO-150

XICOR	X25168	TSSOP 14	PA14TSS14D
XICOR	X25168(1.8)	DIP 8	
XICOR	X25168(1.8)	SOIC 8	PA16SO16D-EO-150
XICOR	X25168(1.8)	SOIC 14	PA16SO16D-EO-150
XICOR	X25168(1.8)	TSSOP 14	PA14TSS14D
XICOR	X25169	DIP 8	
XICOR	X25169	SOIC 8	PA16SO16D-EO-150
XICOR	X25169	SOIC 14	PA16SO16D-EO-150
XICOR	X25169	TSSOP 14	PA14TSS14D
XICOR	X25169(1.8)	DIP 8	
XICOR	X25169(1.8)	SOIC 8	PA16SO16D-EO-150
XICOR	X25169(1.8)	SOIC 14	PA16SO16D-EO-150
XICOR	X25169(1.8)	TSSOP 14	PA14TSS14D
XICOR	X25323	DIP 8	
XICOR	X25323	SOIC 8	PA16SO16D-EO-150
XICOR	X25323	SOIC 14	PA16SO16D-EO-150
XICOR	X25323	TSSOP 14	PA14TSS14D
XICOR	X25323(1.8)	DIP 8	
XICOR	X25323(1.8)	SOIC 8	PA16SO16D-EO-150
XICOR	X25323(1.8)	SOIC 14	PA16SO16D-EO-150
XICOR	X25323(1.8)	TSSOP 14	PA14TSS14D
XICOR	X25325	DIP 8	
XICOR	X25325	SOIC 8	PA16SO16D-EO-150
XICOR	X25325	SOIC 14	PA16SO16D-EO-150
XICOR	X25325	TSSOP 14	PA14TSS14D
XICOR	X25325(1.8)	DIP 8	
XICOR	X25325(1.8)	SOIC 8	PA16SO16D-EO-150
XICOR	X25325(1.8)	SOIC 14	PA16SO16D-EO-150
XICOR	X25325(1.8)	TSSOP 14	PA14TSS14D
XICOR	X25328	DIP 8	
XICOR	X25328	SOIC 8	PA16SO16D-EO-150
XICOR	X25328	SOIC 14	PA16SO16D-EO-150
XICOR	X25328	TSSOP 14	PA14TSS14D
XICOR	X25328(1.8)	DIP 8	
XICOR	X25328(1.8)	SOIC 8	PA16SO16D-EO-150
XICOR	X25328(1.8)	SOIC 14	PA16SO16D-EO-150
XICOR	X25328(1.8)	TSSOP 14	PA14TSS14D
XICOR	X25329	DIP 8	
XICOR	X25329	SOIC 8	PA16SO16D-EO-150
XICOR	X25329	SOIC 14	PA16SO16D-EO-150
XICOR	X25329	TSSOP 14	PA14TSS14D
XICOR	X25329(1.8)	DIP 8	
XICOR	X25329(1.8)	SOIC 8	PA16SO16D-EO-150
XICOR	X25329(1.8)	SOIC 14	PA16SO16D-EO-150
XICOR	X25329(1.8)	TSSOP 14	PA14TSS14D
XICOR	X25643	DIP 8	
XICOR	X25643	SOIC 8	PA16SO16D-EO-150
XICOR	X25643	SOIC 14	PA16SO16D-EO-150
XICOR	X25643	TSSOP 14	PA14TSS14D
XICOR	X25643(1.8)	DIP 8	
XICOR	X25643(1.8)	SOIC 8	PA16SO16D-EO-150
XICOR	X25643(1.8)	SOIC 14	PA16SO16D-EO-150
XICOR	X25643(1.8)	TSSOP 14	PA14TSS14D
XICOR	X25645	DIP 8	
XICOR	X25645	SOIC 8	PA16SO16D-EO-150
XICOR	X25645	SOIC 14	PA16SO16D-EO-150
XICOR	X25645	TSSOP 14	PA14TSS14D
XICOR	X25645(1.8)	DIP 8	
XICOR	X25645(1.8)	SOIC 8	PA16SO16D-EO-150
XICOR	X25645(1.8)	SOIC 14	PA16SO16D-EO-150
XICOR	X25645(1.8)	TSSOP 14	PA14TSS14D
XICOR	X25648	DIP 8	
XICOR	X25648	SOIC 8	PA16SO16D-EO-150
XICOR	X25648	SOIC 14	PA16SO16D-EO-150
XICOR	X25648	TSSOP 14	PA14TSS14D
XICOR	X25648(1.8)	DIP 8	
XICOR	X25648(1.8)	SOIC 8	PA16SO16D-EO-150
XICOR	X25648(1.8)	SOIC 14	PA16SO16D-EO-150
XICOR	X25648(1.8)	TSSOP 14	PA14TSS14D
XICOR	X25649	DIP 8	
XICOR	X25649	SOIC 8	PA16SO16D-EO-150
XICOR	X25649	SOIC 14	PA16SO16D-EO-150
XICOR	X25649	TSSOP 14	PA14TSS14D

XICOR	X25649(1.8)	DIP 8	
XICOR	X25649(1.8)	SOIC 8	PA16SO16D-EO-150
XICOR	X25649(1.8)	SOIC 14	PA16SO16D-EO-150
XICOR	X25649(1.8)	TSSOP 14	PA14TSS14D
XICOR	X25020	DIP 8	
XICOR	X25020	SOIC 8	PA16SO16D-EO-150
XICOR	X25020	TSSOP 8	PA8TSS8D
XICOR	X25021	DIP 8	
XICOR	X25021	SOIC 8	PA16SO16D-EO-150
XICOR	X25021	TSSOP 8	PA8TSS8D
XICOR	X25040	DIP 8	
XICOR	X25040	SOIC 8	PA16SO16D-EO-150
XICOR	X25040	TSSOP 8	PA8TSS8D
XICOR	X25041	DIP 8	
XICOR	X25041	SOIC 8	PA16SO16D-EO-150
XICOR	X25080	DIP 8	
XICOR	X25080	SOIC 8	PA16SO16D-EO-150
XICOR	X25080	TSSOP 14	PA14TSS14D
XICOR	X25160	DIP 8	
XICOR	X25160	SOIC 8	PA16SO16D-EO-150
XICOR	X25160	SOIC 14	PA16SO16D-EO-150
XICOR	X25170	DIP 8	
XICOR	X25170	SOIC 8	PA16SO16D-EO-150
XICOR	X25170	TSSOP 14	PA14TSS14D
XICOR	X25320	DIP 8	
XICOR	X25320	SOIC 8	PA16SO16D-EO-150
XICOR	X25320	TSSOP 14	PA14TSS14D
XICOR	X25640	DIP 8	
XICOR	X25642	DIP 8	
XICOR	X25642	SOIC 8	PA16SO16D-EO-150
XICOR	X25128	DIP 8	
XICOR	X25128	SOIC 14	PA16SO16D-EO-150
XICOR	X25128	SOIC 16	PA16SO16D-EO-150
XICOR	X25138	DIP 8	
XICOR	X25138	SOIC 8	PA16SO16D-EO-150
XICOR	X25138	TSSOP 8	PA8TSS8D
XICOR	X25138	TSSOP 8	PA24TSS24D
XICOR	X25138	SOIC 16	PA16SO16D-EO-150
XICOR	X25057	DIP 8	
XICOR	X25057	SOIC 8	PA16SO16D-EO-150
XICOR	X25057	TSSOP 8	PA8TSS8D
XICOR	X25057	TSSOP 8	PA24TSS24D
XICOR	X25057	MSOP 8	PA8MSOP8D-1
XICOR	X25057(1.8)	DIP 8	
XICOR	X25057(1.8)	SOIC 8	PA16SO16D-EO-150
XICOR	X25057(1.8)	TSSOP 8	PA8TSS8D
XICOR	X25057(1.8)	TSSOP 8	PA24TSS24D
XICOR	X25057(1.8)	MSOP 8	PA8MSOP8D-1
XICOR	X25097	DIP 8	
XICOR	X25097	SOIC 8	PA16SO16D-EO-150
XICOR	X25097	TSSOP 8	PA8TSS8D
XICOR	X25097	TSSOP 8	PA24TSS24D
XICOR	X25097(1.8)	DIP 8	
XICOR	X25097(1.8)	SOIC 8	PA16SO16D-EO-150
XICOR	X25097(1.8)	TSSOP 8	PA8TSS8D
XICOR	X25097(1.8)	TSSOP 8	PA24TSS24D
XICOR	X25C02	DIP 8	
XICOR	X25C02	MSOP 8	PA8MSOP8D
XICOR	X25C02	SOIC 8	PA16SO16D-EO-150
XICOR	X25F008	DIP 8	
XICOR	X25F008	SOIC 8	PA16SO16D-EO-150
XICOR	X25F008	TSSOP 14	PA14TSS14D
XICOR	X25F008	TSSOP 20	PA20TSS20D
XICOR	X25F008(1.8)	DIP 8	
XICOR	X25F008(1.8)	SOIC 8	PA16SO16D-EO-150
XICOR	X25F008(1.8)	TSSOP 14	PA14TSS14D
XICOR	X25F008(1.8)	TSSOP 20	PA20TSS20D
XICOR	X25F016	DIP 8	
XICOR	X25F016	SOIC 8	PA16SO16D-EO-150
XICOR	X25F016	TSSOP 14	PA14TSS14D
XICOR	X25F016	TSSOP 20	PA20TSS20D
XICOR	X25F016(1.8)	DIP 8	
XICOR	X25F016(1.8)	SOIC 8	PA16SO16D-EO-150

XICOR	X25F016(1.8)	TSSOP 14	PA14TSS14D
XICOR	X25F016(1.8)	TSSOP 20	PA20TSS20D
XICOR	X25F032	DIP 8	
XICOR	X25F032	SOIC 8	PA16SO16D-EO-150
XICOR	X25F032	TSSOP 14	PA14TSS14D
XICOR	X25F032	TSSOP 20	PA20TSS20D
XICOR	X25F032(1.8)	DIP 8	
XICOR	X25F032(1.8)	SOIC 8	PA16SO16D-EO-150
XICOR	X25F032(1.8)	TSSOP 14	PA14TSS14D
XICOR	X25F032(1.8)	TSSOP 20	PA20TSS20D
XICOR	X25F064	DIP 8	
XICOR	X25F064	SOIC 8	PA16SO16D-EO-150
XICOR	X25F064	TSSOP 14	PA14TSS14D
XICOR	X25F064	TSSOP 20	PA20TSS20D
XICOR	X25F064(1.8)	DIP 8	
XICOR	X25F064(1.8)	SOIC 8	PA16SO16D-EO-150
XICOR	X25F064(1.8)	TSSOP 14	PA14TSS14D
XICOR	X25F064(1.8)	TSSOP 20	PA20TSS20D
XICOR	X25F128	DIP 8	
XICOR	X25F128	SOIC 16	PA16SO16D-EO-150
XICOR	X25F128(1.8)	DIP 8	
XICOR	X25F128(1.8)	SOIC 16	PA16SO16D-EO-150
XICOR	X25F047	DIP 8	
XICOR	X25F047	SOIC 8	PA16SO16D-EO-150
XICOR	X25F047	MSOP 8	PA8MSOP8D-1
XICOR	X25F047	TSSOP 8	PA8TSS8D
XICOR	X25F047	TSSOP 8	PA24TSS24D
XICOR	X25F047(1.8)	DIP 8	
XICOR	X25F047(1.8)	SOIC 8	PA16SO16D-EO-150
XICOR	X25F047(1.8)	MSOP 8	PA8MSOP8D-1
XICOR	X25F047(1.8)	TSSOP 8	PA8TSS8D
XICOR	X25F047(1.8)	TSSOP 8	PA24TSS24D
XICOR	X25F087	DIP 8	
XICOR	X25F087	SOIC 8	PA16SO16D-EO-150
XICOR	X25F087	TSSOP 8	PA8TSS8D
XICOR	X25F087	TSSOP 8	PA24TSS24D
XICOR	X25F087(1.8)	DIP 8	
XICOR	X25F087(1.8)	SOIC 8	PA16SO16D-EO-150
XICOR	X25F087(1.8)	TSSOP 8	PA8TSS8D
XICOR	X25F087(1.8)	TSSOP 8	PA24TSS24D
XICOR	X2804A	DIP 24	
XICOR	X2816A	DIP 24	
XICOR	X2816B	DIP 24	
XICOR	X2816C	DIP 24	
XICOR	X28256	DIP 28	
XICOR	X2864A	DIP 28	
XICOR	X2864B	DIP 28	
XICOR	X2864H	DIP 28	
XICOR	X28C010	DIP 32	
XICOR	X28C256	DIP 28	
XICOR	X28C512	DIP 32	
XICOR	X28C513	PLCC 32	PA32PL32D
XICOR	X28C64	DIP 28	
XICOR	X28HC64	DIP 28	
XICOR	X28HC256	DIP 28	
XICOR	X28HC256	PLCC 32	PA32PL28D-YA
XICOR	X28LC512	DIP 32	
XICOR	X28LC513	PLCC 32	PA32PL32D
XICOR	X5043	DIP 8	
XICOR	X5043	SOIC 8	PA16SO16D-EO-150
XICOR	X5043	MSOP 8	PA8MSOP8D
XICOR	X5043	TSSOP 14	PA14TSS14D
XICOR	X5045	DIP 8	
XICOR	X5045	SOIC 8	PA16SO16D-EO-150
XICOR	X5045	MSOP 8	PA8MSOP8D
XICOR	X5045	TSSOP 14	PA14TSS14D
XICOR	X5163	DIP 8	
XICOR	X5163	SOIC 8	PA16SO16D-EO-150
XICOR	X5163	TSSOP 14	PA14TSS14D
XICOR	X5163AG	DIP 8	
XICOR	X5163AG	SOIC 8	PA16SO16D-EO-150
XICOR	X5163AG	TSSOP 14	PA14TSS14D
XICOR	X5163AH	DIP 8	

XICOR	X5163AH	SOIC 8	PA16SO16D-EO-150
XICOR	X5163AH	TSSOP 14	PA14TSS14D
XICOR	X5165	DIP 8	
XICOR	X5165	SOIC 8	PA16SO16D-EO-150
XICOR	X5165	TSSOP 14	PA14TSS14D
XICOR	X5165AG	DIP 8	
XICOR	X5165AG	SOIC 8	PA16SO16D-EO-150
XICOR	X5165AG	TSSOP 14	PA14TSS14D
XICOR	X5165AH	DIP 8	
XICOR	X5165AH	SOIC 8	PA16SO16D-EO-150
XICOR	X5165AH	TSSOP 14	PA14TSS14D
XICOR	X5168	DIP 8	
XICOR	X5168	SOIC 8	PA16SO16D-EO-150
XICOR	X5168	TSSOP 14	PA14TSS14D
XICOR	X5169	DIP 8	
XICOR	X5169	SOIC 8	PA16SO16D-EO-150
XICOR	X5169	TSSOP 14	PA14TSS14D
XICOR	X68C64	DIP 24	
XICOR	X68257	DIP 28	
XICOR	X76F100	DIP 8	
XICOR	X76F041P	DIP 8	
XICOR	X76F041P-3	DIP 8	
XICOR	X76F041A	SOIC 8	PA20SO20D-EO-210
XICOR	X76F041A-3	SOIC 8	PA20SO20D-EO-210
XICOR	X76F640	DIP 8	
XICOR	X84161	DIP 8	
XICOR	X84641	DIP 8	
XICOR	X84129	DIP 8	
XICOR	X84041	DIP 8	
XICOR	X84161	DIP 8	
XICOR	X84641	DIP 8	
XICOR	X84129	DIP 8	
XICOR	X84041	SOIC 8	PA16SO16D-EO-150
XICOR	X84161	SOIC 8	PA16SO16D-EO-150
XICOR	X84641	SOIC 8	PA16SO16D-EO-150
XICOR	X84129	SOIC 8	PA16SO16D-EO-150
XICOR	X84161	TSSOP 8	PA8TSS-OT
XICOR	X84041	TSSOP 14	PA14TSS14D
XICOR	X84129	TSSOP 14	PA14TSS14D
XICOR	X84641	TSSOP 20	PA20TSS20D
XICOR	X84129	TSSOP 28	PA28TSS28D-EO
XICOR	X88C64	DIP 24	
XICOR	X88257	DIP 28	
XICOR	XM28C010	DIP 32	
XILINX	XC1718D	DIP 8	
XILINX	XC1718D	SOIC 8	PA28SO28D-EO-300
XILINX	XC1718D	VDFN 8	PA8VO8D
XILINX	XC1718D	PLCC 20	PA20PL8D
XILINX	XC1718D	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC1718L	DIP 8	
XILINX	XC1718L	SOIC 8	PA28SO28D-EO-300
XILINX	XC1718L	VDFN 8	PA8VO8D
XILINX	XC1718L	PLCC 20	PA20PL8D
XILINX	XC1718L	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC1736D	DIP 8	
XILINX	XC1736D	SOIC 8	PA28SO28D-EO-300
XILINX	XC1736D	VDFN 8	PA8VO8D
XILINX	XC1736D	PLCC 20	PA20PL8D
XILINX	XC1736D	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC1736E	DIP 8	
XILINX	XC1736E	SOIC 8	PA28SO28D-EO-300
XILINX	XC1736E	VDFN 8	PA8VO8D
XILINX	XC1736E	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC1765D	DIP 8	
XILINX	XC1765D	SOIC 8	PA28SO28D-EO-300
XILINX	XC1765D	VDFN 8	PA8VO8D
XILINX	XC1765D	PLCC 20	PA20PL8D
XILINX	XC1765D	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC1765E	DIP 8	
XILINX	XC1765E	SOIC 8	PA28SO28D-EO-300
XILINX	XC1765E	VDFN 8	PA8VO8D
XILINX	XC1765E	PLCC 20	PA20PL8D
XILINX	XC1765E	PLCC 20	PA20LC20D[Dead Bug]

XILINX	XC1765L	DIP 8	
XILINX	XC1765L	SOIC 8	PA28SO28D-EO-300
XILINX	XC1765L	VDFN 8	PA8VO8D
XILINX	XC1765L	PLCC 20	PA20PL8D
XILINX	XC1765L	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC1765EL	DIP 8	
XILINX	XC1765EL	SOIC 8	PA28SO28D-EO-300
XILINX	XC1765EL	VDFN 8	PA8VO8D
XILINX	XC1765EL	PLCC 20	PA20PL8D
XILINX	XC1765EL	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC1765EL(X)	DIP 8	
XILINX	XC1765X	DIP 8	
XILINX	XC1765X	SOIC 8	PA28SO28D-EO-300
XILINX	XC1765X	VDFN 8	PA8VO8D
XILINX	XC1765X	PLCC 20	PA20PL8D
XILINX	XC1765X	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC17128D	DIP 8	
XILINX	XC17128D	VDFN 8	PA8VO8D
XILINX	XC17128D	PLCC 20	PA20PL8D
XILINX	XC17128D	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC17128E	DIP 8	
XILINX	XC17128E	VDFN 8	PA8VO8D
XILINX	XC17128E	PLCC 20	PA20PL8D
XILINX	XC17128E	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC17128L	DIP 8	
XILINX	XC17128L	VDFN 8	PA8VO8D
XILINX	XC17128L	PLCC 20	PA20PL8D
XILINX	XC17128L	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC17128EL	DIP 8	
XILINX	XC17128EL	VDFN 8	PA8VO8D
XILINX	XC17128EL	PLCC 20	PA20PL8D
XILINX	XC17128EL	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC17128EL(X)	DIP 8	
XILINX	XC17128X	DIP 8	
XILINX	XC17128X	VDFN 8	PA8VO8D
XILINX	XC17128X	PLCC 20	PA20PL8D
XILINX	XC17128X	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC17256D	DIP 8	
XILINX	XC17256D	VDFN 8	PA8VO8D
XILINX	XC17256D	PLCC 20	PA20PL8D
XILINX	XC17256D	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC17256E	DIP 8	
XILINX	XC17256E	VDFN 8	PA8VO8D
XILINX	XC17256E	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC17256L	DIP 8	
XILINX	XC17256L	VDFN 8	PA8VO8D
XILINX	XC17256L	PLCC 20	PA20PL8D
XILINX	XC17256L	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC17256EL	DIP 8	
XILINX	XC17256EL	VDFN 8	PA8VO8D
XILINX	XC17256EL	PLCC 20	PA20PL8D
XILINX	XC17256EL	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC17256EL(X)	DIP 8	
XILINX	XC17256X	DIP 8	
XILINX	XC17256X	VDFN 8	PA8VO8D
XILINX	XC17256X	PLCC 20	PA20PL8D
XILINX	XC17256X	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC17512L	DIP 8	
XILINX	XC17512L	SOIC 20	PA28SO28D-EO-300
XILINX	XC17512L	PLCC 44	PA44-48U
XILINX	XC1701	DIP 8	
XILINX	XC1701	SOIC 20	PA28SO28D-EO-300
XILINX	XC1701	PLCC 44	PA44-48U
XILINX	XC1701L	DIP 8	
XILINX	XC1701L	SOIC 20	PA28SO28D-EO-300
XILINX	XC1701L	PLCC 44	PA44-48U
XILINX	XC1702L	DIP 8	
XILINX	XC1702L	PLCC 44	PA44-48U
XILINX	XC1702L	QFP 44	PA44QF44D-1
XILINX	XC1704L	DIP 8	
XILINX	XC1704L	PLCC 44	PA44-48U
XILINX	XC1704L	QFP 44	PA44QF44D-1
XILINX	XC17V01	DIP 8	



XILINX	XC17V01	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC17V01	SOIC 20	PA28SO28D-EO-300
XILINX	XC17V01	PLCC 44	PA44-48U
XILINX	XC17V01	QFP 44	PA44QF44D
XILINX	XC17V01	VDFN 8	PA8VO8D
XILINX	XC17V02	DIP 8	
XILINX	XC17V02	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC17V02	SOIC 20	PA28SO28D-EO-300
XILINX	XC17V02	PLCC 44	PA44-48U
XILINX	XC17V02	QFP 44	PA44QF44D
XILINX	XC17V02	VDFN 8	PA8VO8D
XILINX	XC17V04	DIP 8	
XILINX	XC17V04	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC17V04	SOIC 20	PA28SO28D-EO-300
XILINX	XC17V04	PLCC 44	PA44-48U
XILINX	XC17V04	QFP 44	PA44QF44D
XILINX	XC17V04	VDFN 8	PA8VO8D
XILINX	XC17V08	PLCC 44	PA44-48U
XILINX	XC17V08	QFP 44	PA44QF44D
XILINX	XC17V16	PLCC 44	PA44-48U
XILINX	XC17V16	QFP 44	PA44QF44D
XILINX	XC17S05	DIP 8	
XILINX	XC17S05	SOIC 8	PA16SO16D-EO-150
XILINX	XC17S05	VDFN 8	PA8VO8D
XILINX	XC17S05L	DIP 8	
XILINX	XC17S05L	SOIC 8	PA16SO16D-EO-150
XILINX	XC17S05L	VDFN 8	PA8VO8D
XILINX	XC17S05XL	DIP 8	
XILINX	XC17S05XL	SOIC 8	PA16SO16D-EO-150
XILINX	XC17S05XL	VDFN 8	PA8VO8D
XILINX	XC17S10	DIP 8	
XILINX	XC17S10	VDFN 8	PA8VO8D
XILINX	XC17S10L	DIP 8	
XILINX	XC17S10L	VDFN 8	PA8VO8D
XILINX	XC17S10XL	DIP 8	
XILINX	XC17S10XL	VDFN 8	PA8VO8D
XILINX	XC17S20	DIP 8	
XILINX	XC17S20	VDFN 8	PA8VO8D
XILINX	XC17S20L	DIP 8	
XILINX	XC17S20L	VDFN 8	PA8VO8D
XILINX	XC17S20XL	DIP 8	
XILINX	XC17S20XL	VDFN 8	PA8VO8D
XILINX	XC17S30	DIP 8	
XILINX	XC17S30	VDFN 8	PA8VO8D
XILINX	XC17S30L	DIP 8	
XILINX	XC17S30L	VDFN 8	PA8VO8D
XILINX	XC17S30XL	DIP 8	
XILINX	XC17S30XL	VDFN 8	PA8VO8D
XILINX	XC17S40	DIP 8	
XILINX	XC17S40	SOIC 20	PA28SO28D-EO-300
XILINX	XC17S40L	DIP 8	
XILINX	XC17S40L	SOIC 20	PA28SO28D-EO-300
XILINX	XC17S40XL	DIP 8	
XILINX	XC17S40XL	SOIC 20	PA28SO28D-EO-300
XILINX	XC17S50	DIP 8	
XILINX	XC17S50	SOIC 20	PA28SO28D-EO-300
XILINX	XC17S50L	DIP 8	
XILINX	XC17S50L	SOIC 20	PA28SO28D-EO-300
XILINX	XC17S50XL	DIP 8	
XILINX	XC17S50XL	SOIC 20	PA28SO28D-EO-300
XILINX	XC17S100L	DIP 8	
XILINX	XC17S100L	SOIC 20	PA28SO28D-EO-300
XILINX	XC17S100XL	DIP 8	
XILINX	XC17S100XL	SOIC 20	PA28SO28D-EO-300
XILINX	XC17S150L	DIP 8	
XILINX	XC17S150L	SOIC 20	PA28SO28D-EO-300
XILINX	XC17S150XL	DIP 8	
XILINX	XC17S150XL	SOIC 20	PA28SO28D-EO-300
XILINX	XC17S15A	DIP 8	
XILINX	XC17S15A	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC17S15A	SOIC 20	PA28SO28D-EO-300
XILINX	XC17S15A	PLCC 44	PA44-48U
XILINX	XC17S15A	QFP 44	PA44QF44D

XILINX	XC17S15A	VDFN 8	PA8VO8D
XILINX	XC17S30A	DIP 8	
XILINX	XC17S30A	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC17S30A	SOIC 20	PA28SO28D-EO-300
XILINX	XC17S30A	PLCC 44	PA44-48U
XILINX	XC17S30A	QFP 44	PA44QF44D
XILINX	XC17S30A	VDFN 8	PA8VO8D
XILINX	XC17S50A	DIP 8	
XILINX	XC17S50A	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC17S50A	SOIC 20	PA28SO28D-EO-300
XILINX	XC17S50A	PLCC 44	PA44-48U
XILINX	XC17S50A	QFP 44	PA44QF44D
XILINX	XC17S50A	VDFN 8	PA8VO8D
XILINX	XC17S100A	DIP 8	
XILINX	XC17S100A	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC17S100A	SOIC 20	PA28SO28D-EO-300
XILINX	XC17S100A	PLCC 44	PA44-48U
XILINX	XC17S100A	QFP 44	PA44QF44D
XILINX	XC17S100A	VDFN 8	PA8VO8D
XILINX	XC17S150A	DIP 8	
XILINX	XC17S150A	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC17S150A	SOIC 20	PA28SO28D-EO-300
XILINX	XC17S150A	PLCC 44	PA44-48U
XILINX	XC17S150A	QFP 44	PA44QF44D
XILINX	XC17S150A	VDFN 8	PA8VO8D
XILINX	XC17S200A	DIP 8	
XILINX	XC17S200A	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC17S200A	SOIC 20	PA28SO28D-EO-300
XILINX	XC17S200A	PLCC 44	PA44-48U
XILINX	XC17S200A	QFP 44	PA44QF44D
XILINX	XC17S200A	VDFN 8	PA8VO8D
XILINX	XC18V256PC20	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC18V256SO20	SOIC 20	PA68-40B
XILINX	XC18V256VQ44	VQFP 44	PA44QF44D
XILINX	XC18V512PC20	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC18V512SO20	SOIC 20	PA68-40B
XILINX	XC18V512VQ44	VQFP 44	PA44QF44D
XILINX	XC18V01PC20	PLCC 20	PA20LC20D[Dead Bug]
XILINX	XC18V01SO20	SOIC 20	PA68-40B
XILINX	XC18V01VQ44	VQFP 44	PA44QF44D
XILINX	XC18V02PC44	PLCC 44	PA44-48U
XILINX	XC18V02VQ44	VQFP 44	PA44QF44D
XILINX	XC18V04PC44	PLCC 44	PA44-48U
XILINX	XC18V04VQ44	VQFP 44	PA44QF44D
XILINX	XCF01SVO20	TSSOP 20	PA24TSS24D
XILINX	XCF01SVOG20	TSSOP 20	PA24TSS24D
XILINX	XCF02SVO20	TSSOP 20	PA24TSS24D
XILINX	XCF02SVOG20	TSSOP 20	PA24TSS24D
XILINX	XCF04SVO20	TSSOP 20	PA24TSS24D
XILINX	XCF04SVOG20	TSSOP 20	PA24TSS24D
XILINX	XCF08PVO48	TSOP 48	PA48TS48D
XILINX	XCF16PVO48	TSOP 48	PA48TS48D
XILINX	XCF32PVO48	TSOP 48	PA48TS48D
ANACHIP	AM24LC02	DIP 8	
ANACHIP	AM24LC02	SOIC 8	PA8SO8D-EO-150
ANACHIP	AM24LC02	TSSOP 8	PA8TSS8D
ANACHIP	AM24LC04	DIP 8	
ANACHIP	AM24LC04	SOIC 8	PA8SO8D-EO-150
ANACHIP	AM24LC04	TSSOP 8	PA8TSS8D
ANACHIP	AM24LC08	DIP 8	
ANACHIP	AM24LC08	SOIC 8	PA8SO8D-EO-150
ANACHIP	AM24LC16	DIP 8	
ANACHIP	AM24LC16	SOIC 8	PA8SO8D-EO-150
ANACHIP	AM24LC21	DIP 8	
ANACHIP	AM24LC21	SOIC 8	PA8SO8D-EO-150
ANACHIP	AM24LC21B	DIP 8	
ANACHIP	AM24LC21B	SOIC 8	PA8SO8D-EO-150
ICE	ICE27C512	DIP 28	
ICE	ICE27C512	PLCC 32	PA32PL28D-YA
ICE	ICE27C512	TSOP 28	PA28TS28D-EO
ICE	ICE27IC512	DIP 28	
ICE	ICE27IC512	PLCC 32	PA32PL28D-YA
ICE	ICE27IC512	TSOP 28	PA28TS28D-EO

ICE	ICE27C010	DIP 32	
ICE	ICE27C010	PLCC 32	PA32PL32D
ICE	ICE27C010	TSOP 32	PA32TS20/PA32TS32D-20
ICE	ICE27LC010	DIP 32	
ICE	ICE27LC010	PLCC 32	PA32PL32D
ICE	ICE27LC010	TSOP 32	PA32TS20/PA32TS32D-20
ICE	ICE25P05	DIP 8	
ICE	ICE25P05	SOIC 8	PA16SO16D-EO-150
AUSTIN-SEMICONDUCTOR	SMJ27C040	DIP 32	
NTE	NTE2716	DIP 24	
NTE	2732A	DIP 24	
CERAMATE	24LC02	DIP 8	
CERAMATE	24LC02	SOIC 8	PA8SO8D-EO-150
CERAMATE	24LC02	TSSOP 8	PA8TSS8D
CERAMATE	24LC02	TSSOP 8	PA24TSS24D
CERAMATE	24LC08	DIP 8	
CERAMATE	24LC08	SOIC 8	PA8SO8D-EO-150
CERAMATE	24LC08	TSSOP 8	PA8TSS8D
CERAMATE	24LC08	TSSOP 8	PA24TSS24D
CERAMATE	24LC16	DIP 8	
CERAMATE	24LC16	SOIC 8	PA8SO8D-EO-150
CERAMATE	24LC16	TSSOP 8	PA8TSS8D
CERAMATE	24LC16	TSSOP 8	PA24TSS24D
CERAMATE	24LLC02	DIP 8	
CERAMATE	24LLC02	SOIC 8	PA8SO8D-EO-150
CERAMATE	24LLC02	TSSOP 8	PA8TSS8D
CERAMATE	24LLC02	TSSOP 8	PA24TSS24D
CERAMATE	24LLC08	DIP 8	
CERAMATE	24LLC08	SOIC 8	PA8SO8D-EO-150
CERAMATE	24LLC08	TSSOP 8	PA8TSS8D
CERAMATE	24LLC08	TSSOP 8	PA24TSS24D
CERAMATE	24LLC16	DIP 8	
CERAMATE	24LLC16	SOIC 8	PA8SO8D-EO-150
CERAMATE	24LLC16	TSSOP 8	PA8TSS8D
CERAMATE	24LLC16	TSSOP 8	PA24TSS24D
APLUS FLASH TECH	24BC01	DIP 8	
APLUS FLASH TECH	24BC01	SOIC 8	PA8SO8D-EO-150
APLUS FLASH TECH	24BC01	TSSOP 8	PA8TSS8D
APLUS FLASH TECH	24BC01	TSSOP 8	PA24TSS24D
APLUS FLASH TECH	24BC02	DIP 8	
APLUS FLASH TECH	24BC02	SOIC 8	PA8SO8D-EO-150
APLUS FLASH TECH	24BC02	TSSOP 8	PA8TSS8D
APLUS FLASH TECH	24BC02	TSSOP 8	PA24TSS24D
APLUS FLASH TECH	24BC04	DIP 8	
APLUS FLASH TECH	24BC04	SOIC 8	PA8SO8D-EO-150
APLUS FLASH TECH	24BC04	TSSOP 8	PA8TSS8D
APLUS FLASH TECH	24BC04	TSSOP 8	PA24TSS24D
APLUS FLASH TECH	24BC08	DIP 8	
APLUS FLASH TECH	24BC08	SOIC 8	PA8SO8D-EO-150
APLUS FLASH TECH	24BC08	TSSOP 8	PA8TSS8D
APLUS FLASH TECH	24BC08	TSSOP 8	PA24TSS24D
APLUS FLASH TECH	24BC16	DIP 8	
APLUS FLASH TECH	24BC16	SOIC 8	PA8SO8D-EO-150
APLUS FLASH TECH	24BC16	TSSOP 8	PA8TSS8D
APLUS FLASH TECH	24BC16	TSSOP 8	PA24TSS24D
APLUS FLASH TECH	24BC32	DIP 8	
APLUS FLASH TECH	24BC32	TSSOP 8	PA8TSS8D
APLUS FLASH TECH	24BC32	TSSOP 8	PA24TSS24D
APLUS FLASH TECH	24BC32	SOIC 8	PA8SO8D-EO-150
APLUS FLASH TECH	24BC64	DIP 8	
APLUS FLASH TECH	24BC64	TSSOP 8	PA8TSS8D
APLUS FLASH TECH	24BC64	TSSOP 8	PA24TSS24D
APLUS FLASH TECH	24BC64	SOIC 8	PA8SO8D-EO-150
ATC	AM24LC02	DIP 8	
ATC	AM24LC02	SOIC 8	PA8SO8D-EO-150
ATC	AM24LC02	TSSOP 8	PA8TSS8D
ATC	AM24LC02	TSSOP 8	PA24TSS24D
ATC	AM24LC04	DIP 8	
ATC	AM24LC04	SOIC 8	PA8SO8D-EO-150
ATC	AM24LC04	TSSOP 8	PA8TSS8D
ATC	AM24LC04	TSSOP 8	PA24TSS24D
ATC	AM24LC08	DIP 8	
ATC	AM24LC08	SOIC 8	PA8SO8D-EO-150

ATC	AM24LC16	DIP 8	
ATC	AM24LC16	SOIC 8	PA8SO8D-EO-150
ATC	AM24LC21	DIP 8	
ATC	AM24LC21	SOIC 8	PA8SO8D-EO-150
ATC	AM24LC21B	DIP 8	
ATC	AM24LC21B	SOIC 8	PA8SO8D-EO-150
CYPRESS	CY37032	PLCC 44	PA44-48U
CYPRESS	CY37032	TQFP 44	PA44QF44D
CYPRESS	CY37032V	PLCC 44	PA44-48U
CYPRESS	CY37032V	TQFP 44	PA44QF44D
CYPRESS	CY37064	PLCC 44	PA44-48U
CYPRESS	CY37064	TQFP 44	PA44QF44D
CYPRESS	CY37064V	PLCC 44	PA44-48U
CYPRESS	CY37064V	TQFP 44	PA44QF44D
ALTERA	EP310	DIP 20	
ALTERA	EP320	DIP 20	
ALTERA	EP330	DIP 20	
ALTERA	EP310I	DIP 20	
ALTERA	EP320I	DIP 20	
ALTERA	EP330I	DIP 20	
ALTERA	EP310	PLCC 20	PA20LC20D[Dead Bug]
ALTERA	EP320	PLCC 20	PA20LC20D[Dead Bug]
ALTERA	EP330	PLCC 20	PA20LC20D[Dead Bug]
ALTERA	EP310I	PLCC 20	PA20LC20D[Dead Bug]
ALTERA	EP320I	PLCC 20	PA20LC20D[Dead Bug]
ALTERA	EP330I	PLCC 20	PA20LC20D[Dead Bug]
ALTERA	EP312	DIP 24	
ALTERA	EP312	PLCC 28	PA28PL24D7P6-YA
ALTERA	EP600	DIP 24	
ALTERA	EP600I	DIP 24	
ALTERA	EP610	DIP 24	
ALTERA	EP610I	DIP 24	
ALTERA	EP600	PLCC 28	PA28PL24D7P6-YA
ALTERA	EP600I	PLCC 28	PA28PL24D7P6-YA
ALTERA	EP610	PLCC 28	PA28PL24D7P6-YA
ALTERA	EP610I	PLCC 28	PA28PL24D7P6-YA
ALTERA	EP600	SOIC 24	PA28SO28D-EO-300
ALTERA	EP600I	SOIC 24	PA28SO28D-EO-300
ALTERA	EP610	SOIC 24	PA28SO28D-EO-300
ALTERA	EP610I	SOIC 24	PA28SO28D-EO-300
ALTERA	EP900	DIP 40	
ALTERA	EP900I	DIP 40	
ALTERA	EP910	DIP 40	
ALTERA	EP910I	DIP 40	
ALTERA	EP900	PLCC 44	PA900-44
ALTERA	EP900I	PLCC 44	PA900-44
ALTERA	EP910	PLCC 44	PA900-44
ALTERA	EP910I	PLCC 44	PA900-44
ALTERA	EP900	PLCC 44	PA44-48U
ALTERA	EP900I	PLCC 44	PA44-48U
ALTERA	EP910	PLCC 44	PA44-48U
ALTERA	EP910I	PLCC 44	PA44-48U
ALTERA	EP910A	DIP 40	
ALTERA	EP910A	PLCC 44	PA900-44
ALTERA	EP910A	PLCC 44	PA44-48U
ALTERA	EP1800	PLCC 68	PA-EP1800
ALTERA	EP1810	PLCC 68	PA-EP1800
ALTERA	EP1830	PLCC 68	PA-EP1800
ALTERA	EPM3032A	PLCC 44	PA44-48U
ALTERA	EPM3032A	TQFP 44	PA44QF44D
ALTERA	EPM3064A	PLCC 44	PA44-48U
ALTERA	EPM3064A	TQFP 44	PA44QF44D
ALTERA	EPM3064A	TQFP 100	PA100TQ48D
ALTERA	EPM3128A	TQFP 100	PA100TQ48D
ALTERA	EPM570	TQFP 100	PA100QF48DF
ALTERA	EPM7032	PLCC 44	PA44-48U
ALTERA	EPM7032V	PLCC 44	PA44-48U
ALTERA	EPM7032AE	PLCC 44	PA44-48U
ALTERA	EPM7032AE	TQFP 44	PA44VQ44D
ALTERA	EPM7032AEas7032	PLCC 44	PA44-48U
ALTERA	EPM7032AEas7032	TQFP 44	PA44VQ44D
ALTERA	EPM7032AEas7032S	PLCC 44	PA44-48U
ALTERA	EPM7032AEas7032S	TQFP 44	PA44VQ44D

ALTERA	EPM7032S	PLCC 44	PA44-48U
ALTERA	EPM7032S	TQFP 44	PA44VQ44D
ALTERA	EPM7032Sas7032	PLCC 44	PA44-48U
ALTERA	EPM7032Sas7032	TQFP 44	PA44VQ44D
ALTERA	EPM7064	PLCC 44	PA44-48U
ALTERA	EPM7064	PLCC 44	PA44-40F
ALTERA	EPM7064	PLCC 68	PA68-40A
ALTERA	EPM7064	PLCC 68	PA7064/96-68LC
ALTERA	EPM7064	PLCC 84	PA84-40A
ALTERA	EPM7064	PLCC 84	PA7064/96-84LC
ALTERA	EPM7064AE	PLCC 44	PA44-48U
ALTERA	EPM7064AE	TQFP 44	PA44QF44D
ALTERA	EPM7064AEas7064	PLCC 44	PA44-48U
ALTERA	EPM7064AEas7064	TQFP 44	PA44QF44D
ALTERA	EPM7064AEas7064S	PLCC 44	PA44-48U
ALTERA	EPM7064AEas7064S	TQFP 44	PA44QF44D
ALTERA	EPM7064S	TQFP 100	PA100TQ48DB
ALTERA	EPM7064S	PLCC 44	PA44-48U
ALTERA	EPM7064S	PLCC 68	PA7064/96-68LC
ALTERA	EPM7064S	PLCC 84	PA7064/96-84LC
ALTERA	EPM7064Sas7064	PLCC 44	PA44-48U
ALTERA	EPM7064Sas7064	PLCC 68	PA7064/96-68LC
ALTERA	EPM7064Sas7064	PLCC 84	PA7064/96-84LC
ALTERA	EPM7096	PLCC 68	PA68-40B
ALTERA	EPM7096	PLCC 68	PA7064/96-68LC
ALTERA	EPM7096	PLCC 84	PA84-40B
ALTERA	EPM7096	PLCC 84	PA7064/96-84LC
ALTERA	EPM7128E	PLCC 84	PA7128/E-84LC
ALTERA	EPM7128E	PLCC 84	HA7128/E-84LC
ALTERA	EPM7128S	PLCC 84	PA7128/E-84LC
ALTERA	EPM7128S	PLCC 84	HA7128/E-84LC
ALTERA	EPM7128S	PLCC 84	PA84PL48DE-YC
ALTERA	EPM7128Sas7128	PLCC 84	PA7128/E-84LC
ALTERA	EPM7128Sas7128	PLCC 84	HA7128/E-84LC
ALTERA	EPM7128S	TQFP 100	PA100TQ48DA
ALTERA	EPM7128Sas7128	TQFP 100	PA100TQ48DA
AMD	AmPAL20L10-20	DIP 24	
AMD	AmPAL20L10A	DIP 24	
AMD	AmPAL20L10B	DIP 24	
AMD	AmPAL20L10-20	PLCC 28	PA28PL24D2P6-YA
AMD	AmPAL20L10A	PLCC 28	PA28PL24D2P6-YA
AMD	AmPAL20L10B	PLCC 28	PA28PL24D2P6-YA
AMD	PAL20L8-5	DIP 24	
AMD	PAL20L8-7	DIP 24	
AMD	PAL20L8-10/2	DIP 24	
AMD	PAL20R4-5	DIP 24	
AMD	PAL20R4-7	DIP 24	
AMD	PAL20R4-10/2	DIP 24	
AMD	PAL20R6-5	DIP 24	
AMD	PAL20R6-7	DIP 24	
AMD	PAL20R6-10/2	DIP 24	
AMD	PAL20R8-5	DIP 24	
AMD	PAL20R8-7	DIP 24	
AMD	PAL20R8-10/2	DIP 24	
AMD	PAL20L8-5	PLCC 28	PA28PL24D2P6-YA
AMD	PAL20L8-7	PLCC 28	PA28PL24D2P6-YA
AMD	PAL20L8-10/2	PLCC 28	PA28PL24D2P6-YA
AMD	PAL20R4-5	PLCC 28	PA28PL24D2P6-YA
AMD	PAL20R4-7	PLCC 28	PA28PL24D2P6-YA
AMD	PAL20R4-10/2	PLCC 28	PA28PL24D2P6-YA
AMD	PAL20R6-5	PLCC 28	PA28PL24D2P6-YA
AMD	PAL20R6-7	PLCC 28	PA28PL24D2P6-YA
AMD	PAL20R6-10/2	PLCC 28	PA28PL24D2P6-YA
AMD	PAL20R8-5	PLCC 28	PA28PL24D2P6-YA
AMD	PAL20R8-7	PLCC 28	PA28PL24D2P6-YA
AMD	PAL20R8-10/2	PLCC 28	PA28PL24D2P6-YA
AMD	PALC16L8Q	DIP 20	
AMD	PALC16R4Q	DIP 20	
AMD	PALC16R6Q	DIP 20	
AMD	PALC16R8Q	DIP 20	
AMD	PALC16L8Z	DIP 20	
AMD	PALC16R4Z	DIP 20	
AMD	PALC16R6Z	DIP 20	

AMD	PALC16R8Z	DIP 20	
AMD	PALC16L8Q	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALC16R4Q	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALC16R6Q	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALC16R8Q	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALC16L8Z	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALC16R4Z	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALC16R6Z	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALC16R8Z	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALC20L8Z	DIP 24	
AMD	PALC20R4Z	DIP 24	
AMD	PALC20R6Z	DIP 24	
AMD	PALC20R8Z	DIP 24	
AMD	PALC20L8Z	PLCC 28	PA28PL24D2P6-YA
AMD	PALC20R4Z	PLCC 28	PA28PL24D2P6-YA
AMD	PALC20R6Z	PLCC 28	PA28PL24D2P6-YA
AMD	PALC20R8Z	PLCC 28	PA28PL24D2P6-YA
AMD	PALCE16V8H	DIP 20	
AMD	PALCE16V8Has10H8	DIP 20	
AMD	PALCE16V8Has10L8	DIP 20	
AMD	PALCE16V8Has10P8	DIP 20	
AMD	PALCE16V8Has12H6	DIP 20	
AMD	PALCE16V8Has12L6	DIP 20	
AMD	PALCE16V8Has12P6	DIP 20	
AMD	PALCE16V8Has14H4	DIP 20	
AMD	PALCE16V8Has14L4	DIP 20	
AMD	PALCE16V8Has14P4	DIP 20	
AMD	PALCE16V8Has16H2	DIP 20	
AMD	PALCE16V8Has16L2	DIP 20	
AMD	PALCE16V8Has16P2	DIP 20	
AMD	PALCE16V8Has16H8	DIP 20	
AMD	PALCE16V8Has16L8	DIP 20	
AMD	PALCE16V8Has16P8	DIP 20	
AMD	PALCE16V8Has16R4	DIP 20	
AMD	PALCE16V8Has16R6	DIP 20	
AMD	PALCE16V8Has16R8	DIP 20	
AMD	PALCE16V8Has16RP4	DIP 20	
AMD	PALCE16V8Has16RP6	DIP 20	
AMD	PALCE16V8Has16RP8	DIP 20	
AMD	PALCE16V8H	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has10H8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has10L8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has10P8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has12H6	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has12L6	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has12P6	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has14H4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has14L4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has14P4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has16H2	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has16L2	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has16P2	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has16H8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has16L8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has16P8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has16R4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has16R6	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has16R8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has16RP4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has16RP6	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has16RP8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8H	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Has10H8	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Has10L8	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Has10P8	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Has12H6	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Has12L6	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Has12P6	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Has14H4	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Has14L4	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Has14P4	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Has16H2	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Has16L2	SOIC 20	PA20SO20D-EO-210

AMD	PALCE16V8Has16P2	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Has16H8	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Has16L8	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Has16P8	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Has16R4	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Has16R6	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Has16R8	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Has16RP4	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Has16RP6	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Has16RP8	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Q	DIP 20	
AMD	PALCE16V8Qas10H8	DIP 20	
AMD	PALCE16V8Qas10L8	DIP 20	
AMD	PALCE16V8Qas10P8	DIP 20	
AMD	PALCE16V8Qas12H6	DIP 20	
AMD	PALCE16V8Qas12L6	DIP 20	
AMD	PALCE16V8Qas12P6	DIP 20	
AMD	PALCE16V8Qas14H4	DIP 20	
AMD	PALCE16V8Qas14L4	DIP 20	
AMD	PALCE16V8Qas14P4	DIP 20	
AMD	PALCE16V8Qas16H2	DIP 20	
AMD	PALCE16V8Qas16L2	DIP 20	
AMD	PALCE16V8Qas16P2	DIP 20	
AMD	PALCE16V8Qas16H8	DIP 20	
AMD	PALCE16V8Qas16L8	DIP 20	
AMD	PALCE16V8Qas16P8	DIP 20	
AMD	PALCE16V8Qas16R4	DIP 20	
AMD	PALCE16V8Qas16R6	DIP 20	
AMD	PALCE16V8Qas16R8	DIP 20	
AMD	PALCE16V8Qas16RP4	DIP 20	
AMD	PALCE16V8Qas16RP6	DIP 20	
AMD	PALCE16V8Qas16RP8	DIP 20	
AMD	PALCE16V8Q	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas10H8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas10L8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas10P8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas12H6	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas12L6	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas12P6	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas14H4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas14L4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas14P4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas16H2	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas16L2	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas16P2	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas16H8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas16L8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas16P8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas16R4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas16R6	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas16R8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas16RP4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas16RP6	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas16RP8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Q	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Qas10H8	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Qas10L8	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Qas10P8	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Qas12H6	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Qas12L6	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Qas12P6	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Qas14H4	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Qas14L4	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Qas14P4	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Qas16H2	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Qas16L2	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Qas16P2	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Qas16H8	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Qas16L8	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Qas16P8	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Qas16R4	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Qas16R6	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Qas16R8	SOIC 20	PA20SO20D-EO-210

AMD	PALCE16V8Qas16RP4	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Qas16RP6	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Qas16RP8	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Z	DIP 20	
AMD	PALCE16V8Zas10H8	DIP 20	
AMD	PALCE16V8Zas10L8	DIP 20	
AMD	PALCE16V8Zas10P8	DIP 20	
AMD	PALCE16V8Zas12H6	DIP 20	
AMD	PALCE16V8Zas12L6	DIP 20	
AMD	PALCE16V8Zas12P6	DIP 20	
AMD	PALCE16V8Zas14H4	DIP 20	
AMD	PALCE16V8Zas14L4	DIP 20	
AMD	PALCE16V8Zas14P4	DIP 20	
AMD	PALCE16V8Zas16H2	DIP 20	
AMD	PALCE16V8Zas16L2	DIP 20	
AMD	PALCE16V8Zas16P2	DIP 20	
AMD	PALCE16V8Zas16H8	DIP 20	
AMD	PALCE16V8Zas16L8	DIP 20	
AMD	PALCE16V8Zas16P8	DIP 20	
AMD	PALCE16V8Zas16R4	DIP 20	
AMD	PALCE16V8Zas16R6	DIP 20	
AMD	PALCE16V8Zas16R8	DIP 20	
AMD	PALCE16V8Zas16RP4	DIP 20	
AMD	PALCE16V8Zas16RP6	DIP 20	
AMD	PALCE16V8Zas16RP8	DIP 20	
AMD	PALCE16V8Z	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas10H8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas10L8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas10P8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas12H6	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas12L6	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas12P6	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas14H4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas14L4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas14P4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas16H2	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas16L2	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas16P2	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas16H8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas16L8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas16P8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas16R4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas16R6	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas16R8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas16RP4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas16RP6	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas16RP8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Z	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Zas10H8	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Zas10L8	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Zas10P8	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Zas12H6	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Zas12L6	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Zas12P6	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Zas14H4	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Zas14L4	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Zas14P4	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Zas16H2	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Zas16L2	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Zas16P2	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Zas16H8	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Zas16L8	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Zas16P8	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Zas16R4	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Zas16R6	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Zas16R8	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Zas16RP4	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Zas16RP6	SOIC 20	PA20SO20D-EO-210
AMD	PALCE16V8Zas16RP8	SOIC 20	PA20SO20D-EO-210
AMD	PALCE20V8H-25	DIP 24	
AMD	PALCE20V8H-25as14H8	DIP 24	
AMD	PALCE20V8H-25as14L8	DIP 24	
AMD	PALCE20V8H-25as14P8	DIP 24	



AMD	PALCE20V8H-25as16H6	DIP 24	
AMD	PALCE20V8H-25as16L6	DIP 24	
AMD	PALCE20V8H-25as16P6	DIP 24	
AMD	PALCE20V8H-25as18H4	DIP 24	
AMD	PALCE20V8H-25as18L4	DIP 24	
AMD	PALCE20V8H-25as18P4	DIP 24	
AMD	PALCE20V8H-25as20H2	DIP 24	
AMD	PALCE20V8H-25as20L2	DIP 24	
AMD	PALCE20V8H-25as20P2	DIP 24	
AMD	PALCE20V8H-25as20H8	DIP 24	
AMD	PALCE20V8H-25as20L8	DIP 24	
AMD	PALCE20V8H-25as20P8	DIP 24	
AMD	PALCE20V8H-25as20R4	DIP 24	
AMD	PALCE20V8H-25as20R6	DIP 24	
AMD	PALCE20V8H-25as20R8	DIP 24	
AMD	PALCE20V8H-25as20RP4	DIP 24	
AMD	PALCE20V8H-25as20RP6	DIP 24	
AMD	PALCE20V8H-25as20RP8	DIP 24	
AMD	PALCE20V8H-25	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25as14H8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25as14L8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25as14P8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25as16H6	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25as16L6	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25as16P6	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25as18H4	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25as18L4	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25as18P4	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25as20H2	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25as20L2	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25as20P2	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25as20H8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25as20L8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25as20P8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25as20R4	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25as20R6	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25as20R8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25as20RP4	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25as20RP6	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25as20RP8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-10/4	DIP 24	
AMD	PALCE20V8H-10/4as14H8	DIP 24	
AMD	PALCE20V8H-10/4as14L8	DIP 24	
AMD	PALCE20V8H-10/4as14P8	DIP 24	
AMD	PALCE20V8H-10/4as16H6	DIP 24	
AMD	PALCE20V8H-10/4as16L6	DIP 24	
AMD	PALCE20V8H-10/4as16P6	DIP 24	
AMD	PALCE20V8H-10/4as18H4	DIP 24	
AMD	PALCE20V8H-10/4as18L4	DIP 24	
AMD	PALCE20V8H-10/4as18P4	DIP 24	
AMD	PALCE20V8H-10/4as20H2	DIP 24	
AMD	PALCE20V8H-10/4as20L2	DIP 24	
AMD	PALCE20V8H-10/4as20P2	DIP 24	
AMD	PALCE20V8H-10/4as20H8	DIP 24	
AMD	PALCE20V8H-10/4as20L8	DIP 24	
AMD	PALCE20V8H-10/4as20P8	DIP 24	
AMD	PALCE20V8H-10/4as20R4	DIP 24	
AMD	PALCE20V8H-10/4as20R6	DIP 24	
AMD	PALCE20V8H-10/4as20R8	DIP 24	
AMD	PALCE20V8H-10/4as20RP4	DIP 24	
AMD	PALCE20V8H-10/4as20RP6	DIP 24	
AMD	PALCE20V8H-10/4as20RP8	DIP 24	
AMD	PALCE20V8H-10/4	PLCC 28	PA28PL28D
AMD	PALCE20V8H-10/4as14H8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-10/4as14L8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-10/4as14P8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-10/4as16H6	PLCC 28	PA28PL28D
AMD	PALCE20V8H-10/4as16L6	PLCC 28	PA28PL28D
AMD	PALCE20V8H-10/4as16P6	PLCC 28	PA28PL28D
AMD	PALCE20V8H-10/4as18H4	PLCC 28	PA28PL28D
AMD	PALCE20V8H-10/4as18L4	PLCC 28	PA28PL28D
AMD	PALCE20V8H-10/4as18P4	PLCC 28	PA28PL28D
AMD	PALCE20V8H-10/4as20H2	PLCC 28	PA28PL28D

AMD	PALCE20V8H-10/4as20L2	PLCC 28	PA28PL28D
AMD	PALCE20V8H-10/4as20P2	PLCC 28	PA28PL28D
AMD	PALCE20V8H-10/4as20H8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-10/4as20L8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-10/4as20P8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-10/4as20R4	PLCC 28	PA28PL28D
AMD	PALCE20V8H-10/4as20R6	PLCC 28	PA28PL28D
AMD	PALCE20V8H-10/4as20R8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-10/4as20RP4	PLCC 28	PA28PL28D
AMD	PALCE20V8H-10/4as20RP6	PLCC 28	PA28PL28D
AMD	PALCE20V8H-10/4as20RP8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-15/4	DIP 24	
AMD	PALCE20V8H-15/4as14H8	DIP 24	
AMD	PALCE20V8H-15/4as14L8	DIP 24	
AMD	PALCE20V8H-15/4as14P8	DIP 24	
AMD	PALCE20V8H-15/4as16H6	DIP 24	
AMD	PALCE20V8H-15/4as16L6	DIP 24	
AMD	PALCE20V8H-15/4as16P6	DIP 24	
AMD	PALCE20V8H-15/4as18H4	DIP 24	
AMD	PALCE20V8H-15/4as18L4	DIP 24	
AMD	PALCE20V8H-15/4as18P4	DIP 24	
AMD	PALCE20V8H-15/4as20H2	DIP 24	
AMD	PALCE20V8H-15/4as20L2	DIP 24	
AMD	PALCE20V8H-15/4as20P2	DIP 24	
AMD	PALCE20V8H-15/4as20H8	DIP 24	
AMD	PALCE20V8H-15/4as20L8	DIP 24	
AMD	PALCE20V8H-15/4as20P8	DIP 24	
AMD	PALCE20V8H-15/4as20R4	DIP 24	
AMD	PALCE20V8H-15/4as20R6	DIP 24	
AMD	PALCE20V8H-15/4as20R8	DIP 24	
AMD	PALCE20V8H-15/4as20RP4	DIP 24	
AMD	PALCE20V8H-15/4as20RP6	DIP 24	
AMD	PALCE20V8H-15/4as20RP8	DIP 24	
AMD	PALCE20V8H-15/4	PLCC 28	PA28PL28D
AMD	PALCE20V8H-15/4as14H8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-15/4as14L8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-15/4as14P8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-15/4as16H6	PLCC 28	PA28PL28D
AMD	PALCE20V8H-15/4as16L6	PLCC 28	PA28PL28D
AMD	PALCE20V8H-15/4as16P6	PLCC 28	PA28PL28D
AMD	PALCE20V8H-15/4as18H4	PLCC 28	PA28PL28D
AMD	PALCE20V8H-15/4as18L4	PLCC 28	PA28PL28D
AMD	PALCE20V8H-15/4as18P4	PLCC 28	PA28PL28D
AMD	PALCE20V8H-15/4as20H2	PLCC 28	PA28PL28D
AMD	PALCE20V8H-15/4as20L2	PLCC 28	PA28PL28D
AMD	PALCE20V8H-15/4as20P2	PLCC 28	PA28PL28D
AMD	PALCE20V8H-15/4as20H8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-15/4as20L8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-15/4as20P8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-15/4as20R4	PLCC 28	PA28PL28D
AMD	PALCE20V8H-15/4as20R6	PLCC 28	PA28PL28D
AMD	PALCE20V8H-15/4as20R8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-15/4as20RP4	PLCC 28	PA28PL28D
AMD	PALCE20V8H-15/4as20RP6	PLCC 28	PA28PL28D
AMD	PALCE20V8H-15/4as20RP8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25/4	DIP 24	
AMD	PALCE20V8H-25/4as14H8	DIP 24	
AMD	PALCE20V8H-25/4as14L8	DIP 24	
AMD	PALCE20V8H-25/4as14P8	DIP 24	
AMD	PALCE20V8H-25/4as16H6	DIP 24	
AMD	PALCE20V8H-25/4as16L6	DIP 24	
AMD	PALCE20V8H-25/4as16P6	DIP 24	
AMD	PALCE20V8H-25/4as18H4	DIP 24	
AMD	PALCE20V8H-25/4as18L4	DIP 24	
AMD	PALCE20V8H-25/4as18P4	DIP 24	
AMD	PALCE20V8H-25/4as20H2	DIP 24	
AMD	PALCE20V8H-25/4as20L2	DIP 24	
AMD	PALCE20V8H-25/4as20P2	DIP 24	
AMD	PALCE20V8H-25/4as20H8	DIP 24	
AMD	PALCE20V8H-25/4as20L8	DIP 24	
AMD	PALCE20V8H-25/4as20P8	DIP 24	
AMD	PALCE20V8H-25/4as20R4	DIP 24	
AMD	PALCE20V8H-25/4as20R6	DIP 24	

AMD	PALCE20V8H-25/4as20R8	DIP 24	
AMD	PALCE20V8H-25/4as20RP4	DIP 24	
AMD	PALCE20V8H-25/4as20RP6	DIP 24	
AMD	PALCE20V8H-25/4as20RP8	DIP 24	
AMD	PALCE20V8H-25/4	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25/4as14H8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25/4as14L8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25/4as14P8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25/4as16H6	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25/4as16L6	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25/4as16P6	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25/4as18H4	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25/4as18L4	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25/4as18P4	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25/4as20H2	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25/4as20L2	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25/4as20P2	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25/4as20H8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25/4as20L8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25/4as20P8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25/4as20R4	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25/4as20R6	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25/4as20R8	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25/4as20RP4	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25/4as20RP6	PLCC 28	PA28PL28D
AMD	PALCE20V8H-25/4as20RP8	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-15/4	DIP 24	
AMD	PALCE20V8Q-15/4as14H8	DIP 24	
AMD	PALCE20V8Q-15/4as14L8	DIP 24	
AMD	PALCE20V8Q-15/4as14P8	DIP 24	
AMD	PALCE20V8Q-15/4as16H6	DIP 24	
AMD	PALCE20V8Q-15/4as16L6	DIP 24	
AMD	PALCE20V8Q-15/4as16P6	DIP 24	
AMD	PALCE20V8Q-15/4as18H4	DIP 24	
AMD	PALCE20V8Q-15/4as18L4	DIP 24	
AMD	PALCE20V8Q-15/4as18P4	DIP 24	
AMD	PALCE20V8Q-15/4as20H2	DIP 24	
AMD	PALCE20V8Q-15/4as20L2	DIP 24	
AMD	PALCE20V8Q-15/4as20P2	DIP 24	
AMD	PALCE20V8Q-15/4as20H8	DIP 24	
AMD	PALCE20V8Q-15/4as20L8	DIP 24	
AMD	PALCE20V8Q-15/4as20P8	DIP 24	
AMD	PALCE20V8Q-15/4as20R4	DIP 24	
AMD	PALCE20V8Q-15/4as20R6	DIP 24	
AMD	PALCE20V8Q-15/4as20R8	DIP 24	
AMD	PALCE20V8Q-15/4as20RP4	DIP 24	
AMD	PALCE20V8Q-15/4as20RP6	DIP 24	
AMD	PALCE20V8Q-15/4as20RP8	DIP 24	
AMD	PALCE20V8Q-15/4	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-15/4as14H8	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-15/4as14L8	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-15/4as14P8	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-15/4as16H6	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-15/4as16L6	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-15/4as16P6	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-15/4as18H4	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-15/4as18L4	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-15/4as18P4	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-15/4as20H2	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-15/4as20L2	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-15/4as20P2	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-15/4as20H8	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-15/4as20L8	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-15/4as20P8	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-15/4as20R4	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-15/4as20R6	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-15/4as20R8	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-15/4as20RP4	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-15/4as20RP6	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-15/4as20RP8	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-25/4	DIP 24	
AMD	PALCE20V8Q-25/4as14H8	DIP 24	
AMD	PALCE20V8Q-25/4as14L8	DIP 24	

AMD	PALCE20V8Q-25/4as14P8	DIP 24	
AMD	PALCE20V8Q-25/4as16H6	DIP 24	
AMD	PALCE20V8Q-25/4as16L6	DIP 24	
AMD	PALCE20V8Q-25/4as16P6	DIP 24	
AMD	PALCE20V8Q-25/4as18H4	DIP 24	
AMD	PALCE20V8Q-25/4as18L4	DIP 24	
AMD	PALCE20V8Q-25/4as18P4	DIP 24	
AMD	PALCE20V8Q-25/4as20H2	DIP 24	
AMD	PALCE20V8Q-25/4as20L2	DIP 24	
AMD	PALCE20V8Q-25/4as20P2	DIP 24	
AMD	PALCE20V8Q-25/4as20H8	DIP 24	
AMD	PALCE20V8Q-25/4as20L8	DIP 24	
AMD	PALCE20V8Q-25/4as20P8	DIP 24	
AMD	PALCE20V8Q-25/4as20R4	DIP 24	
AMD	PALCE20V8Q-25/4as20R6	DIP 24	
AMD	PALCE20V8Q-25/4as20R8	DIP 24	
AMD	PALCE20V8Q-25/4as20RP4	DIP 24	
AMD	PALCE20V8Q-25/4as20RP6	DIP 24	
AMD	PALCE20V8Q-25/4as20RP8	DIP 24	
AMD	PALCE20V8Q-25/4	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-25/4as14H8	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-25/4as14L8	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-25/4as14P8	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-25/4as16H6	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-25/4as16L6	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-25/4as16P6	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-25/4as18H4	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-25/4as18L4	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-25/4as18P4	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-25/4as20H2	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-25/4as20L2	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-25/4as20P2	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-25/4as20H8	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-25/4as20L8	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-25/4as20P8	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-25/4as20R4	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-25/4as20R6	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-25/4as20R8	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-25/4as20RP4	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-25/4as20RP6	PLCC 28	PA28PL28D
AMD	PALCE20V8Q-25/4as20RP8	PLCC 28	PA28PL28D
AMD	PALLV16V8as10H8	DIP 20	
AMD	PALLV16V8as10L8	DIP 20	
AMD	PALLV16V8as10P8	DIP 20	
AMD	PALLV16V8as12H6	DIP 20	
AMD	PALLV16V8as12L6	DIP 20	
AMD	PALLV16V8as12P6	DIP 20	
AMD	PALLV16V8as14H4	DIP 20	
AMD	PALLV16V8as14L4	DIP 20	
AMD	PALLV16V8as14P4	DIP 20	
AMD	PALLV16V8as16H2	DIP 20	
AMD	PALLV16V8as16L2	DIP 20	
AMD	PALLV16V8as16P2	DIP 20	
AMD	PALLV16V8as16H8	DIP 20	
AMD	PALLV16V8as16L8	DIP 20	
AMD	PALLV16V8as16P8	DIP 20	
AMD	PALLV16V8as16R4	DIP 20	
AMD	PALLV16V8as16R6	DIP 20	
AMD	PALLV16V8as16R8	DIP 20	
AMD	PALLV16V8as16RP4	DIP 20	
AMD	PALLV16V8as16RP6	DIP 20	
AMD	PALLV16V8as16RP8	DIP 20	
AMD	PALLV16V8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as10H8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as10L8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as10P8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as12H6	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as12L6	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as12P6	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as14H4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as14L4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as14P4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as16H2	PLCC 20	PA20LC20D[Dead Bug]

AMD	PALLV16V8as16L2	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as16P2	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as16H8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as16L8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as16P8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as16R4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as16R6	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as16R8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as16RP4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as16RP6	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as16RP8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8as10H8	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8as10L8	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8as10P8	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8as12H6	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8as12L6	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8as12P6	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8as14H4	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8as14L4	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8as14P4	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8as16H2	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8as16L2	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8as16P2	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8as16H8	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8as16L8	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8as16P8	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8as16R4	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8as16R6	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8as16R8	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8as16RP4	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8as16RP6	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8as16RP8	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8Z	DIP 20	
AMD	PALLV16V8Zas10H8	DIP 20	
AMD	PALLV16V8Zas10L8	DIP 20	
AMD	PALLV16V8Zas10P8	DIP 20	
AMD	PALLV16V8Zas12H6	DIP 20	
AMD	PALLV16V8Zas12L6	DIP 20	
AMD	PALLV16V8Zas12P6	DIP 20	
AMD	PALLV16V8Zas14H4	DIP 20	
AMD	PALLV16V8Zas14L4	DIP 20	
AMD	PALLV16V8Zas14P4	DIP 20	
AMD	PALLV16V8Zas16H2	DIP 20	
AMD	PALLV16V8Zas16L2	DIP 20	
AMD	PALLV16V8Zas16P2	DIP 20	
AMD	PALLV16V8Zas16H8	DIP 20	
AMD	PALLV16V8Zas16L8	DIP 20	
AMD	PALLV16V8Zas16P8	DIP 20	
AMD	PALLV16V8Zas16R4	DIP 20	
AMD	PALLV16V8Zas16R6	DIP 20	
AMD	PALLV16V8Zas16R8	DIP 20	
AMD	PALLV16V8Zas16RP4	DIP 20	
AMD	PALLV16V8Zas16RP6	DIP 20	
AMD	PALLV16V8Zas16RP8	DIP 20	
AMD	PALLV16V8Z	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas10H8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas10L8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas10P8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas12H6	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas12L6	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas12P6	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas14H4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas14L4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas14P4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas16H2	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas16L2	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas16P2	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas16H8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas16L8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas16P8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas16R4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas16R6	PLCC 20	PA20LC20D[Dead Bug]

AMD	PALLV16V8Zas16R8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas16RP4	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas16RP6	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas16RP8	PLCC 20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Z	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8Zas10H8	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8Zas10L8	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8Zas10P8	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8Zas12H6	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8Zas12L6	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8Zas12P6	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8Zas14H4	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8Zas14L4	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8Zas14P4	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8Zas16H2	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8Zas16L2	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8Zas16P2	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8Zas16H8	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8Zas16L8	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8Zas16P8	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8Zas16R4	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8Zas16R6	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8Zas16R8	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8Zas16RP4	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8Zas16RP6	SOIC 20	PA20SO20D-EO-210
AMD	PALLV16V8Zas16RP8	SOIC 20	PA20SO20D-EO-210
AMD	PALLV22V10	DIP 24	
AMD	PALLV22V10	PLCC 28	PA28PL28D
AMD	PALLV22V10Z	DIP 24	
AMD	PALLV22V10Z	PLCC 28	PA28PL28D
AMD	PALCE22V10H	DIP 24	
AMD	PALCE22V10H	PLCC 28	PA28PL28D
AMD	PALCE22V10Q	DIP 24	
AMD	PALCE22V10Q	PLCC 28	PA28PL28D
AMD	PALCE22V10Z	DIP 24	
AMD	PALCE22V10Z	PLCC 28	PA28PL28D
AMD	PALCE20RA10H	DIP 24	
AMD	PALCE20RA10H	PLCC 28	PA28PL28D
AMD	PALCE20RA10Q	DIP 24	
AMD	PALCE20RA10Q	PLCC 28	PA28PL28D
AMD	PALCE26V12H	DIP 28	
AMD	PALCE26V12H	PLCC 28	PA28PL28D
AMD	PALCE26V12H/4	DIP 28	
AMD	PALCE26V12H/4	PLCC 28	PA28PL28D
AMD	PALCE26V12H/4-10	DIP 28	
AMD	PALCE26V12H/4-10	PLCC 28	PA28PL28D
AMD	PALCE610H	DIP 24	
AMD	PALCE610H	PLCC 28	PA28PL28D
AMD	PALCE29M16H	DIP 24	
AMD	PALCE29M16H	PLCC 28	PA28PL28D
AMD	PALCE29MA16H	DIP 24	
AMD	PALCE29MA16H	PLCC 28	PA28PL28D
AMD	MACH110	PLCC 44	PA-MACH1
AMD	MACH110	PLCC 44	PA44-48U
AMD	MACH111	PLCC 44	PA-MACH1
AMD	MACH111	PLCC 44	PA44-48U
AMD	MACH120	PLCC 68	PA-MACH4
AMD	MACH130	PLCC 84	PA-MACH2
AMD	MACH131	PLCC 84	PA-MACH2
AMD	MACH210	PLCC 44	PA-MACH1
AMD	MACH210	PLCC 44	PA44-48U
AMD	MACHLV210	PLCC 44	PA-MACH1
AMD	MACHLV210	PLCC 44	PA44-48U
AMD	MACH211	PLCC 44	PA-MACH1
AMD	MACH211	PLCC 44	PA44-48U
AMD	MACH215	PLCC 44	PA-MACH1
AMD	MACH215	PLCC 44	PA44-48U
AMD	MACH220	PLCC 68	PA-MACH4
AMD	MACH230	PLCC 84	PA-MACH2
AMD	MACH231-7	PLCC 84	PA-MACH2
AMD	MACH231-20JC/1	PLCC 84	PA-MACH2
AMD	MACH111SP	PLCC 44	PA-MACH1
AMD	MACH111SP	PLCC 44	PA44-48U

AMD	MACH211SP	PLCC 44	PA-MACH1
AMD	MACH211SP	PLCC 44	PA44-48U
ATMEL	AT22V10	DIP 24	
ATMEL	AT22V10L	DIP 24	
ATMEL	AT22V10B	DIP 24	
ATMEL	AT22V10BL	DIP 24	
ATMEL	AT22LV10	DIP 24	
ATMEL	AT22LV10L	DIP 24	
ATMEL	AT22V10	SOIC 24	PA28SO28D-EO-300
ATMEL	AT22V10L	SOIC 24	PA28SO28D-EO-300
ATMEL	AT22V10B	SOIC 24	PA28SO28D-EO-300
ATMEL	AT22V10BL	SOIC 24	PA28SO28D-EO-300
ATMEL	AT22LV10	SOIC 24	PA28SO28D-EO-300
ATMEL	AT22LV10L	SOIC 24	PA28SO28D-EO-300
ATMEL	AT22V10	PLCC 28	PA28PL24D2P6-YA
ATMEL	AT22V10L	PLCC 28	PA28PL24D2P6-YA
ATMEL	AT22V10B	PLCC 28	PA28PL24D2P6-YA
ATMEL	AT22V10BL	PLCC 28	PA28PL24D2P6-YA
ATMEL	AT22LV10	PLCC 28	PA28PL24D2P6-YA
ATMEL	AT22LV10L	PLCC 28	PA28PL24D2P6-YA
ATMEL	ATV750	DIP 24	
ATMEL	ATV750L	DIP 24	
ATMEL	ATV750B	DIP 24	
ATMEL	ATV750BL	DIP 24	
ATMEL	ATV750BQ	DIP 24	
ATMEL	ATV750BQL	DIP 24	
ATMEL	ATV750	PLCC 28	PA28PL24D2P6-YA
ATMEL	ATV750L	PLCC 28	PA28PL24D2P6-YA
ATMEL	ATV750B	PLCC 28	PA28PL24D2P6-YA
ATMEL	ATV750BL	PLCC 28	PA28PL24D2P6-YA
ATMEL	ATV750BQ	PLCC 28	PA28PL24D2P6-YA
ATMEL	ATV750BQL	PLCC 28	PA28PL24D2P6-YA
ATMEL	ATV2500	DIP 40	
ATMEL	ATV2500H	DIP 40	
ATMEL	ATV2500L	DIP 40	
ATMEL	ATV2500B	DIP 40	
ATMEL	ATV2500BL	DIP 40	
ATMEL	ATV2500BQ	DIP 40	
ATMEL	ATV2500BQL	DIP 40	
ATMEL	ATV2500	PLCC 44	PA44-48U
ATMEL	ATV2500H	PLCC 44	PA44-48U
ATMEL	ATV2500L	PLCC 44	PA44-48U
ATMEL	ATV2500B	PLCC 44	PA44-48U
ATMEL	ATV2500BL	PLCC 44	PA44-48U
ATMEL	ATV2500BQ	PLCC 44	PA44-48U
ATMEL	ATV2500BQL	PLCC 44	PA44-48U
ATMEL	ATF2500C(V2500)	DIP 40	
ATMEL	ATF2500CL(V2500)	DIP 40	
ATMEL	ATF2500C(V2500B)	DIP 40	
ATMEL	ATF2500CQ(V2500B)	DIP 40	
ATMEL	ATF2500CL(V2500B)	DIP 40	
ATMEL	ATF2500CQL(V2500B)	DIP 40	
ATMEL	ATF2500C	DIP 40	
ATMEL	ATF2500CQ	DIP 40	
ATMEL	ATF2500CL	DIP 40	
ATMEL	ATF2500CQL	DIP 40	
ATMEL	ATF2500C(V2500)	PLCC 44	PA44-48U
ATMEL	ATF2500CL(V2500)	PLCC 44	PA44-48U
ATMEL	ATF2500C(V2500B)	PLCC 44	PA44-48U
ATMEL	ATF2500CQ(V2500B)	PLCC 44	PA44-48U
ATMEL	ATF2500CL(V2500B)	PLCC 44	PA44-48U
ATMEL	ATF2500CQL(V2500B)	PLCC 44	PA44-48U
ATMEL	ATF2500C	PLCC 44	PA44-48U
ATMEL	ATF2500CQ	PLCC 44	PA44-48U
ATMEL	ATF2500CL	PLCC 44	PA44-48U
ATMEL	ATF2500CQL	PLCC 44	PA44-48U
ATMEL	ATF2500C(V2500)	TQFP 44	PA44QF44D
ATMEL	ATF2500CL(V2500)	TQFP 44	PA44QF44D
ATMEL	ATF2500C(V2500B)	TQFP 44	PA44QF44D
ATMEL	ATF2500CQ(V2500B)	TQFP 44	PA44QF44D
ATMEL	ATF2500CL(V2500B)	TQFP 44	PA44QF44D
ATMEL	ATF2500CQL(V2500B)	TQFP 44	PA44QF44D
ATMEL	ATF2500C	TQFP 44	PA44QF44D

ATMEL	ATF2500CQ	TQFP 44	PA44QF44D
ATMEL	ATF2500CL	TQFP 44	PA44QF44D
ATMEL	ATF2500CQL	TQFP 44	PA44QF44D
ATMEL	ATF1500	PLCC 44	PA44-48U
ATMEL	ATF1500	QFP 44	PA44QF44D
ATMEL	ATF1500A	PLCC 44	PA44-48U
ATMEL	ATF1500A	QFP 44	PA44QF44D
ATMEL	ATF1500AL	PLCC 44	PA44-48U
ATMEL	ATF1500AB	QFP 44	PA44QF44D
ATMEL	ATF1500ABV	PLCC 44	PA44-48U
ATMEL	ATF1500ABV	QFP 44	PA44QF44D
ATMEL	ATF1502AS	PLCC 44	PA44-48U
ATMEL	ATF1502AS	QFP 44	PA44QF44D
ATMEL	ATF1502ASL	PLCC 44	PA44-48U
ATMEL	ATF1502ASL	QFP 44	PA44QF44D
ATMEL	ATF1502ASV	PLCC 44	PA44-48U
ATMEL	ATF1502ASV	QFP 44	PA44QF44D
ATMEL	ATF1504AS	PLCC 44	PA44-48U
ATMEL	ATF1504AS	PLCC 68	PA150X-68LC
ATMEL	ATF1504AS	PLCC 84	PA150X-84LC
ATMEL	ATF1504ASV	PLCC 44	PA44-48U
ATMEL	ATF1504ASV	PLCC 68	PA150X-68LC
ATMEL	ATF1504ASV	PLCC 84	PA150X-84LC
ATMEL	ATF1504ASV	PLCC 84	PA150X-84LC
ATMEL	ATF1508AS	PLCC 84	PA150X-84LC
ATMEL	ATF1508AS	TQFP 100	PA100TQ48D
ATMEL	ATF1508ASV	PLCC 84	PA150X-84LC
ATMEL	ATF1502BE-A44	QFP 44	PA44QF44D
ATMEL	ATF1504BE-A44	QFP 44	PA44QF44D
ATMEL	ATF1504BE-A100	TQFP 100	PA100TQ48DE
ATMEL	ATF16V8B	DIP 20	
ATMEL	ATF16V8Bas10H8	DIP 20	
ATMEL	ATF16V8Bas10L8	DIP 20	
ATMEL	ATF16V8Bas10P8	DIP 20	
ATMEL	ATF16V8Bas12H6	DIP 20	
ATMEL	ATF16V8Bas12L6	DIP 20	
ATMEL	ATF16V8Bas12P6	DIP 20	
ATMEL	ATF16V8Bas14H4	DIP 20	
ATMEL	ATF16V8Bas14L4	DIP 20	
ATMEL	ATF16V8Bas14P4	DIP 20	
ATMEL	ATF16V8Bas16H2	DIP 20	
ATMEL	ATF16V8Bas16L2	DIP 20	
ATMEL	ATF16V8Bas16P2	DIP 20	
ATMEL	ATF16V8Bas16H8	DIP 20	
ATMEL	ATF16V8Bas16L8	DIP 20	
ATMEL	ATF16V8Bas16P8	DIP 20	
ATMEL	ATF16V8Bas16R4	DIP 20	
ATMEL	ATF16V8Bas16R6	DIP 20	
ATMEL	ATF16V8Bas16R8	DIP 20	
ATMEL	ATF16V8Bas16RP4	DIP 20	
ATMEL	ATF16V8Bas16RP6	DIP 20	
ATMEL	ATF16V8Bas16RP8	DIP 20	
ATMEL	ATF16V8B	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas10H8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas10L8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas10P8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas12H6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas12L6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas12P6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas14H4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas14L4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas14P4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas16H2	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas16L2	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas16P2	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas16H8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas16L8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas16P8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas16R4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas16R6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas16R8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas16RP4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas16RP6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas16RP8	PLCC 20	PA20LC20D[Dead Bug]



ATMEL	ATF16V8B	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas10H8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas10L8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas10P8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas12H6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas12L6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas12P6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas14H4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas14L4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas14P4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas16H2	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas16L2	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas16P2	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas16H8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas16L8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas16P8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas16R4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas16R6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas16R8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas16RP4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas16RP6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas16RP8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8B	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Bas10H8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Bas10L8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Bas10P8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Bas12H6	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Bas12L6	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Bas12P6	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Bas14H4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Bas14L4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Bas14P4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Bas16H2	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Bas16L2	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Bas16P2	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Bas16H8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Bas16L8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Bas16P8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Bas16R4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Bas16R6	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Bas16R8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Bas16RP4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Bas16RP6	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Bas16RP8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQ	DIP 20	
ATMEL	ATF16V8BQas10H8	DIP 20	
ATMEL	ATF16V8BQas10L8	DIP 20	
ATMEL	ATF16V8BQas10P8	DIP 20	
ATMEL	ATF16V8BQas12H6	DIP 20	
ATMEL	ATF16V8BQas12L6	DIP 20	
ATMEL	ATF16V8BQas12P6	DIP 20	
ATMEL	ATF16V8BQas14H4	DIP 20	
ATMEL	ATF16V8BQas14L4	DIP 20	
ATMEL	ATF16V8BQas14P4	DIP 20	
ATMEL	ATF16V8BQas16H2	DIP 20	
ATMEL	ATF16V8BQas16L2	DIP 20	
ATMEL	ATF16V8BQas16P2	DIP 20	
ATMEL	ATF16V8BQas16H8	DIP 20	
ATMEL	ATF16V8BQas16L8	DIP 20	
ATMEL	ATF16V8BQas16P8	DIP 20	
ATMEL	ATF16V8BQas16R4	DIP 20	
ATMEL	ATF16V8BQas16R6	DIP 20	
ATMEL	ATF16V8BQas16R8	DIP 20	
ATMEL	ATF16V8BQas16RP4	DIP 20	
ATMEL	ATF16V8BQas16RP6	DIP 20	
ATMEL	ATF16V8BQas16RP8	DIP 20	
ATMEL	ATF16V8BQ	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas10H8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas10L8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas10P8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas12H6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas12L6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas12P6	PLCC 20	PA20LC20D[Dead Bug]

ATMEL	ATF16V8BQas14H4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas14L4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas14P4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas16H2	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas16L2	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas16P2	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas16H8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas16L8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas16P8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas16R4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas16R6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas16R8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas16RP4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas16RP6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas16RP8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQ	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas10H8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas10L8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas10P8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas12H6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas12L6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas12P6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas14H4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas14L4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas14P4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas16H2	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas16L2	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas16P2	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas16H8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas16L8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas16P8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas16R4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas16R6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas16R8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas16RP4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas16RP6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas16RP8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQ	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQas10H8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQas10L8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQas10P8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQas12H6	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQas12L6	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQas12P6	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQas14H4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQas14L4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQas14P4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQas16H2	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQas16L2	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQas16P2	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQas16H8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQas16L8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQas16P8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQas16R4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQas16R6	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQas16R8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQas16RP4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQas16RP6	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQas16RP8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQL	DIP 20	
ATMEL	ATF16V8BQLas10H8	DIP 20	
ATMEL	ATF16V8BQLas10L8	DIP 20	
ATMEL	ATF16V8BQLas10P8	DIP 20	
ATMEL	ATF16V8BQLas12H6	DIP 20	
ATMEL	ATF16V8BQLas12L6	DIP 20	
ATMEL	ATF16V8BQLas12P6	DIP 20	
ATMEL	ATF16V8BQLas14H4	DIP 20	
ATMEL	ATF16V8BQLas14L4	DIP 20	
ATMEL	ATF16V8BQLas14P4	DIP 20	
ATMEL	ATF16V8BQLas16H2	DIP 20	
ATMEL	ATF16V8BQLas16L2	DIP 20	
ATMEL	ATF16V8BQLas16P2	DIP 20	
ATMEL	ATF16V8BQLas16H8	DIP 20	

ATMEL	ATF16V8BQLas16L8	DIP 20	
ATMEL	ATF16V8BQLas16P8	DIP 20	
ATMEL	ATF16V8BQLas16R4	DIP 20	
ATMEL	ATF16V8BQLas16R6	DIP 20	
ATMEL	ATF16V8BQLas16R8	DIP 20	
ATMEL	ATF16V8BQLas16RP4	DIP 20	
ATMEL	ATF16V8BQLas16RP6	DIP 20	
ATMEL	ATF16V8BQLas16RP8	DIP 20	
ATMEL	ATF16V8BQL	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas10H8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas10L8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas10P8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas12H6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas12L6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas12P6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas14H4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas14L4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas14P4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas16H2	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas16L2	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas16P2	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas16H8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas16L8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas16P8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas16R4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas16R6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas16R8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas16RP4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas16RP6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas16RP8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQL	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas10H8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas10L8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas10P8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas12H6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas12L6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas12P6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas14H4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas14L4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas14P4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas16H2	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas16L2	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas16P2	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas16H8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas16L8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas16P8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas16R4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas16R6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas16R8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas16RP4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas16RP6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas16RP8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8BQL	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQLas10H8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQLas10L8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQLas10P8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQLas12H6	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQLas12L6	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQLas12P6	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQLas14H4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQLas14L4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQLas14P4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQLas16H2	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQLas16L2	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQLas16P2	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQLas16H8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQLas16L8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQLas16P8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQLas16R4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQLas16R6	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQLas16R8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQLas16RP4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8BQLas16RP6	TSSOP 20	PA24TSS24D

ATMEL	ATF16V8BQLas16RP8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8C	DIP 20	
ATMEL	ATF16V8Cas10H8	DIP 20	
ATMEL	ATF16V8Cas10L8	DIP 20	
ATMEL	ATF16V8Cas10P8	DIP 20	
ATMEL	ATF16V8Cas12H6	DIP 20	
ATMEL	ATF16V8Cas12L6	DIP 20	
ATMEL	ATF16V8Cas12P6	DIP 20	
ATMEL	ATF16V8Cas14H4	DIP 20	
ATMEL	ATF16V8Cas14L4	DIP 20	
ATMEL	ATF16V8Cas14P4	DIP 20	
ATMEL	ATF16V8Cas16H2	DIP 20	
ATMEL	ATF16V8Cas16L2	DIP 20	
ATMEL	ATF16V8Cas16P2	DIP 20	
ATMEL	ATF16V8Cas16H8	DIP 20	
ATMEL	ATF16V8Cas16L8	DIP 20	
ATMEL	ATF16V8Cas16P8	DIP 20	
ATMEL	ATF16V8Cas16R4	DIP 20	
ATMEL	ATF16V8Cas16R6	DIP 20	
ATMEL	ATF16V8Cas16R8	DIP 20	
ATMEL	ATF16V8Cas16RP4	DIP 20	
ATMEL	ATF16V8Cas16RP6	DIP 20	
ATMEL	ATF16V8Cas16RP8	DIP 20	
ATMEL	ATF16V8C	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas10H8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas10L8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas10P8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas12H6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas12L6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas12P6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas14H4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas14L4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas14P4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas16H2	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas16L2	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas16P2	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas16H8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas16L8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas16P8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas16R4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas16R6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas16R8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas16RP4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas16RP6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas16RP8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8C	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas10H8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas10L8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas10P8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas12H6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas12L6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas12P6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas14H4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas14L4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas14P4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas16H2	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas16L2	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas16P2	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas16H8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas16L8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas16P8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas16R4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas16R6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas16R8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas16RP4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas16RP6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas16RP8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8C	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Cas10H8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Cas10L8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Cas10P8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Cas12H6	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Cas12L6	TSSOP 20	PA24TSS24D

ATMEL	ATF16V8Cas12P6	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Cas14H4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Cas14L4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Cas14P4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Cas16H2	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Cas16L2	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Cas16P2	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Cas16H8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Cas16L8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Cas16P8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Cas16R4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Cas16R6	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Cas16R8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Cas16RP4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Cas16RP6	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8Cas16RP8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8CZ	DIP 20	
ATMEL	ATF16V8CZas10H8	DIP 20	
ATMEL	ATF16V8CZas10L8	DIP 20	
ATMEL	ATF16V8CZas10P8	DIP 20	
ATMEL	ATF16V8CZas12H6	DIP 20	
ATMEL	ATF16V8CZas12L6	DIP 20	
ATMEL	ATF16V8CZas12P6	DIP 20	
ATMEL	ATF16V8CZas14H4	DIP 20	
ATMEL	ATF16V8CZas14L4	DIP 20	
ATMEL	ATF16V8CZas14P4	DIP 20	
ATMEL	ATF16V8CZas16H2	DIP 20	
ATMEL	ATF16V8CZas16L2	DIP 20	
ATMEL	ATF16V8CZas16P2	DIP 20	
ATMEL	ATF16V8CZas16H8	DIP 20	
ATMEL	ATF16V8CZas16L8	DIP 20	
ATMEL	ATF16V8CZas16P8	DIP 20	
ATMEL	ATF16V8CZas16R4	DIP 20	
ATMEL	ATF16V8CZas16R6	DIP 20	
ATMEL	ATF16V8CZas16R8	DIP 20	
ATMEL	ATF16V8CZas16RP4	DIP 20	
ATMEL	ATF16V8CZas16RP6	DIP 20	
ATMEL	ATF16V8CZas16RP8	DIP 20	
ATMEL	ATF16V8CZ	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas10H8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas10L8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas10P8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas12H6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas12L6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas12P6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas14H4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas14L4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas14P4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas16H2	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas16L2	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas16P2	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas16H8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas16L8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas16P8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas16R4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas16R6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas16R8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas16RP4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas16RP6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas16RP8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZ	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas10H8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas10L8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas10P8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas12H6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas12L6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas12P6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas14H4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas14L4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas14P4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas16H2	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas16L2	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas16P2	SOIC 20	PA20SO20D-EO-210

ATMEL	ATF16V8CZas16H8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas16L8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas16P8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas16R4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas16R6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas16R8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas16RP4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas16RP6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas16RP8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16V8CZ	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8CZas10H8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8CZas10L8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8CZas10P8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8CZas12H6	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8CZas12L6	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8CZas12P6	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8CZas14H4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8CZas14L4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8CZas14P4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8CZas16H2	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8CZas16L2	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8CZas16P2	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8CZas16H8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8CZas16L8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8CZas16P8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8CZas16R4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8CZas16R6	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8CZas16R8	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8CZas16RP4	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8CZas16RP6	TSSOP 20	PA24TSS24D
ATMEL	ATF16V8CZas16RP8	TSSOP 20	PA24TSS24D
ATMEL	ATF16LV8C	DIP 20	
ATMEL	ATF16LV8Cas10H8	DIP 20	
ATMEL	ATF16LV8Cas10L8	DIP 20	
ATMEL	ATF16LV8Cas10P8	DIP 20	
ATMEL	ATF16LV8Cas12H6	DIP 20	
ATMEL	ATF16LV8Cas12L6	DIP 20	
ATMEL	ATF16LV8Cas12P6	DIP 20	
ATMEL	ATF16LV8Cas14H4	DIP 20	
ATMEL	ATF16LV8Cas14L4	DIP 20	
ATMEL	ATF16LV8Cas14P4	DIP 20	
ATMEL	ATF16LV8Cas16H2	DIP 20	
ATMEL	ATF16LV8Cas16L2	DIP 20	
ATMEL	ATF16LV8Cas16P2	DIP 20	
ATMEL	ATF16LV8Cas16H8	DIP 20	
ATMEL	ATF16LV8Cas16L8	DIP 20	
ATMEL	ATF16LV8Cas16P8	DIP 20	
ATMEL	ATF16LV8Cas16R4	DIP 20	
ATMEL	ATF16LV8Cas16R6	DIP 20	
ATMEL	ATF16LV8Cas16R8	DIP 20	
ATMEL	ATF16LV8Cas16RP4	DIP 20	
ATMEL	ATF16LV8Cas16RP6	DIP 20	
ATMEL	ATF16LV8Cas16RP8	DIP 20	
ATMEL	ATF16LV8C	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas10H8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas10L8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas10P8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas12H6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas12L6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas12P6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas14H4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas14L4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas14P4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas16H2	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas16L2	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas16P2	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas16H8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas16L8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas16P8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas16R4	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas16R6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas16R8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas16RP4	PLCC 20	PA20LC20D[Dead Bug]

ATMEL	ATF16LV8Cas16RP6	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas16RP8	PLCC 20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8C	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas10H8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas10L8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas10P8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas12H6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas12L6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas12P6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas14H4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas14L4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas14P4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas16H2	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas16L2	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas16P2	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas16H8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas16L8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas16P8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas16R4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas16R6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas16R8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas16RP4	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas16RP6	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas16RP8	SOIC 20	PA20SO20D-EO-210
ATMEL	ATF16LV8C	TSSOP 20	PA24TSS24D
ATMEL	ATF16LV8Cas10H8	TSSOP 20	PA24TSS24D
ATMEL	ATF16LV8Cas10L8	TSSOP 20	PA24TSS24D
ATMEL	ATF16LV8Cas10P8	TSSOP 20	PA24TSS24D
ATMEL	ATF16LV8Cas12H6	TSSOP 20	PA24TSS24D
ATMEL	ATF16LV8Cas12L6	TSSOP 20	PA24TSS24D
ATMEL	ATF16LV8Cas12P6	TSSOP 20	PA24TSS24D
ATMEL	ATF16LV8Cas14H4	TSSOP 20	PA24TSS24D
ATMEL	ATF16LV8Cas14L4	TSSOP 20	PA24TSS24D
ATMEL	ATF16LV8Cas14P4	TSSOP 20	PA24TSS24D
ATMEL	ATF16LV8Cas16H2	TSSOP 20	PA24TSS24D
ATMEL	ATF16LV8Cas16L2	TSSOP 20	PA24TSS24D
ATMEL	ATF16LV8Cas16P2	TSSOP 20	PA24TSS24D
ATMEL	ATF16LV8Cas16H8	TSSOP 20	PA24TSS24D
ATMEL	ATF16LV8Cas16L8	TSSOP 20	PA24TSS24D
ATMEL	ATF16LV8Cas16P8	TSSOP 20	PA24TSS24D
ATMEL	ATF16LV8Cas16R4	TSSOP 20	PA24TSS24D
ATMEL	ATF16LV8Cas16R6	TSSOP 20	PA24TSS24D
ATMEL	ATF16LV8Cas16R8	TSSOP 20	PA24TSS24D
ATMEL	ATF16LV8Cas16RP4	TSSOP 20	PA24TSS24D
ATMEL	ATF16LV8Cas16RP6	TSSOP 20	PA24TSS24D
ATMEL	ATF16LV8Cas16RP8	TSSOP 20	PA24TSS24D
ATMEL	ATF20V8B	DIP 24	
ATMEL	ATF20V8Bas14H8	DIP 24	
ATMEL	ATF20V8Bas14L8	DIP 24	
ATMEL	ATF20V8Bas14P8	DIP 24	
ATMEL	ATF20V8Bas16H6	DIP 24	
ATMEL	ATF20V8Bas16L6	DIP 24	
ATMEL	ATF20V8Bas16P6	DIP 24	
ATMEL	ATF20V8Bas18H4	DIP 24	
ATMEL	ATF20V8Bas18L4	DIP 24	
ATMEL	ATF20V8Bas18P4	DIP 24	
ATMEL	ATF20V8Bas20H2	DIP 24	
ATMEL	ATF20V8Bas20L2	DIP 24	
ATMEL	ATF20V8Bas20P2	DIP 24	
ATMEL	ATF20V8Bas20H8	DIP 24	
ATMEL	ATF20V8Bas20L8	DIP 24	
ATMEL	ATF20V8Bas20P8	DIP 24	
ATMEL	ATF20V8Bas20R4	DIP 24	
ATMEL	ATF20V8Bas20R6	DIP 24	
ATMEL	ATF20V8Bas20R8	DIP 24	
ATMEL	ATF20V8Bas20RP4	DIP 24	
ATMEL	ATF20V8Bas20RP6	DIP 24	
ATMEL	ATF20V8Bas20RP8	DIP 24	
ATMEL	ATF20V8B	PLCC 28	PA28PL28D
ATMEL	ATF20V8Bas14H8	PLCC 28	PA28PL28D
ATMEL	ATF20V8Bas14L8	PLCC 28	PA28PL28D
ATMEL	ATF20V8Bas14P8	PLCC 28	PA28PL28D
ATMEL	ATF20V8Bas16H6	PLCC 28	PA28PL28D

ATMEL	ATF20V8Bas16L6	PLCC 28	PA28PL28D
ATMEL	ATF20V8Bas16P6	PLCC 28	PA28PL28D
ATMEL	ATF20V8Bas18H4	PLCC 28	PA28PL28D
ATMEL	ATF20V8Bas18L4	PLCC 28	PA28PL28D
ATMEL	ATF20V8Bas18P4	PLCC 28	PA28PL28D
ATMEL	ATF20V8Bas20H2	PLCC 28	PA28PL28D
ATMEL	ATF20V8Bas20L2	PLCC 28	PA28PL28D
ATMEL	ATF20V8Bas20P2	PLCC 28	PA28PL28D
ATMEL	ATF20V8Bas20H8	PLCC 28	PA28PL28D
ATMEL	ATF20V8Bas20L8	PLCC 28	PA28PL28D
ATMEL	ATF20V8Bas20P8	PLCC 28	PA28PL28D
ATMEL	ATF20V8Bas20R4	PLCC 28	PA28PL28D
ATMEL	ATF20V8Bas20R6	PLCC 28	PA28PL28D
ATMEL	ATF20V8Bas20R8	PLCC 28	PA28PL28D
ATMEL	ATF20V8Bas20RP4	PLCC 28	PA28PL28D
ATMEL	ATF20V8Bas20RP6	PLCC 28	PA28PL28D
ATMEL	ATF20V8Bas20RP8	PLCC 28	PA28PL28D
ATMEL	ATF20V8B	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas14H8	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas14L8	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas14P8	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas16H6	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas16L6	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas16P6	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas18H4	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas18L4	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas18P4	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas20H2	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas20L2	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas20P2	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas20H8	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas20L8	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas20P8	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas20R4	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas20R6	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas20R8	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas20RP4	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas20RP6	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas20RP8	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8B	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8Bas14H8	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8Bas14L8	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8Bas14P8	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8Bas16H6	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8Bas16L6	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8Bas16P6	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8Bas18H4	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8Bas18L4	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8Bas18P4	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8Bas20H2	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8Bas20L2	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8Bas20P2	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8Bas20H8	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8Bas20L8	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8Bas20P8	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8Bas20R4	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8Bas20R6	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8Bas20R8	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8Bas20RP4	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8Bas20RP6	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8Bas20RP8	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8BL	DIP 24	
ATMEL	ATF20V8BLas14H8	DIP 24	
ATMEL	ATF20V8BLas14L8	DIP 24	
ATMEL	ATF20V8BLas14P8	DIP 24	
ATMEL	ATF20V8BLas16H6	DIP 24	
ATMEL	ATF20V8BLas16L6	DIP 24	
ATMEL	ATF20V8BLas16P6	DIP 24	
ATMEL	ATF20V8BLas18H4	DIP 24	
ATMEL	ATF20V8BLas18L4	DIP 24	
ATMEL	ATF20V8BLas18P4	DIP 24	
ATMEL	ATF20V8BLas20H2	DIP 24	
ATMEL	ATF20V8BLas20L2	DIP 24	



ATMEL	ATF20V8BLas20P2	DIP 24	
ATMEL	ATF20V8BLas20H8	DIP 24	
ATMEL	ATF20V8BLas20L8	DIP 24	
ATMEL	ATF20V8BLas20P8	DIP 24	
ATMEL	ATF20V8BLas20R4	DIP 24	
ATMEL	ATF20V8BLas20R6	DIP 24	
ATMEL	ATF20V8BLas20R8	DIP 24	
ATMEL	ATF20V8BLas20RP4	DIP 24	
ATMEL	ATF20V8BLas20RP6	DIP 24	
ATMEL	ATF20V8BLas20RP8	DIP 24	
ATMEL	ATF20V8BL	PLCC 28	PA28PL28D
ATMEL	ATF20V8BLas14H8	PLCC 28	PA28PL28D
ATMEL	ATF20V8BLas14L8	PLCC 28	PA28PL28D
ATMEL	ATF20V8BLas14P8	PLCC 28	PA28PL28D
ATMEL	ATF20V8BLas16H6	PLCC 28	PA28PL28D
ATMEL	ATF20V8BLas16L6	PLCC 28	PA28PL28D
ATMEL	ATF20V8BLas16P6	PLCC 28	PA28PL28D
ATMEL	ATF20V8BLas18H4	PLCC 28	PA28PL28D
ATMEL	ATF20V8BLas18L4	PLCC 28	PA28PL28D
ATMEL	ATF20V8BLas18P4	PLCC 28	PA28PL28D
ATMEL	ATF20V8BLas20H2	PLCC 28	PA28PL28D
ATMEL	ATF20V8BLas20L2	PLCC 28	PA28PL28D
ATMEL	ATF20V8BLas20P2	PLCC 28	PA28PL28D
ATMEL	ATF20V8BLas20H8	PLCC 28	PA28PL28D
ATMEL	ATF20V8BLas20L8	PLCC 28	PA28PL28D
ATMEL	ATF20V8BLas20P8	PLCC 28	PA28PL28D
ATMEL	ATF20V8BLas20R4	PLCC 28	PA28PL28D
ATMEL	ATF20V8BLas20R6	PLCC 28	PA28PL28D
ATMEL	ATF20V8BLas20R8	PLCC 28	PA28PL28D
ATMEL	ATF20V8BLas20RP4	PLCC 28	PA28PL28D
ATMEL	ATF20V8BLas20RP6	PLCC 28	PA28PL28D
ATMEL	ATF20V8BLas20RP8	PLCC 28	PA28PL28D
ATMEL	ATF20V8BL	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas14H8	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas14L8	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas14P8	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas16H6	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas16L6	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas16P6	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas18H4	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas18L4	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas18P4	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas20H2	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas20L2	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas20P2	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas20H8	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas20L8	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas20P8	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas20R4	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas20R6	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas20R8	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas20RP4	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas20RP6	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas20RP8	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF20V8BL	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8BLas14H8	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8BLas14L8	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8BLas14P8	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8BLas16H6	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8BLas16L6	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8BLas16P6	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8BLas18H4	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8BLas18L4	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8BLas18P4	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8BLas20H2	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8BLas20L2	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8BLas20P2	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8BLas20H8	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8BLas20L8	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8BLas20P8	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8BLas20R4	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8BLas20R6	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8BLas20R8	TSSOP 24	PA24TSS24D

ATMEL	ATF20V8BLas20RP4	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8BLas20RP6	TSSOP 24	PA24TSS24D
ATMEL	ATF20V8BLas20RP8	TSSOP 24	PA24TSS24D
ATMEL	ATF22V10B	DIP 24	
ATMEL	ATF22V10B	PLCC 28	PA28PL28D
ATMEL	ATF22V10BL	DIP 24	
ATMEL	ATF22V10BL	PLCC 28	PA28PL28D
ATMEL	ATF22V10C	DIP 24	
ATMEL	ATF22V10C	PLCC 28	PA28PL28D
ATMEL	ATF22V10C(UES)	DIP 24	
ATMEL	ATF22V10C(UES)	PLCC 28	PA28PL28D
ATMEL	ATF22V10CEXT	DIP 24	
ATMEL	ATF22V10CEXT	PLCC 28	PA28PL28D
ATMEL	ATF22V10CZ	DIP 24	
ATMEL	ATF22V10CZ	PLCC 28	PA28PL28D
ATMEL	ATF22V10CZ(UES)	DIP 24	
ATMEL	ATF22V10CZ(UES)	PLCC 28	PA28PL28D
ATMEL	ATF22V10CQZ	DIP 24	
ATMEL	ATF22V10CQZ	PLCC 28	PA28PL28D
ATMEL	ATF22V10CQZ(UES)	DIP 24	
ATMEL	ATF22V10CQZ(UES)	PLCC 28	PA28PL28D
ATMEL	ATF22LV10C	DIP 24	
ATMEL	ATF22LV10C	PLCC 28	PA28PL28D
ATMEL	ATF22LV10C(UES)	DIP 24	
ATMEL	ATF22LV10C(UES)	PLCC 28	PA28PL28D
ATMEL	ATF22LV10CEXT	DIP 24	
ATMEL	ATF22LV10CEXT	PLCC 28	PA28PL28D
ATMEL	ATF22LV10CZ	DIP 24	
ATMEL	ATF22LV10CZ	PLCC 28	PA28PL28D
ATMEL	ATF22LV10CZ(UES)	DIP 24	
ATMEL	ATF22LV10CZ(UES)	PLCC 28	PA28PL28D
ATMEL	ATF22LV10CQZ	DIP 24	
ATMEL	ATF22LV10CQZ	PLCC 28	PA28PL28D
ATMEL	ATF22LV10CQZ(UES)	DIP 24	
ATMEL	ATF22LV10CQZ(UES)	PLCC 28	PA28PL28D
ATMEL	ATF750C(V750)	DIP 24	
ATMEL	ATF750CL(V750)	DIP 24	
ATMEL	ATF750LVC(V750)	DIP 24	
ATMEL	ATF750LVCL(V750)	DIP 24	
ATMEL	ATF750C(V750B)	DIP 24	
ATMEL	ATF750CL(V750B)	DIP 24	
ATMEL	ATF750LVC(V750B)	DIP 24	
ATMEL	ATF750LVCL(V750B)	DIP 24	
ATMEL	ATF750C	DIP 24	
ATMEL	ATF750CL	DIP 24	
ATMEL	ATF750LVC	DIP 24	
ATMEL	ATF750LVCL	DIP 24	
ATMEL	ATF750CEXT	DIP 24	
ATMEL	ATF750LVCEXT	DIP 24	
ATMEL	ATF750C(V750)	PLCC 28	PA28PL28D
ATMEL	ATF750CL(V750)	PLCC 28	PA28PL28D
ATMEL	ATF750LVC(V750)	PLCC 28	PA28PL28D
ATMEL	ATF750LVCL(V750)	PLCC 28	PA28PL28D
ATMEL	ATF750C(V750B)	PLCC 28	PA28PL28D
ATMEL	ATF750CL(V750B)	PLCC 28	PA28PL28D
ATMEL	ATF750LVC(V750B)	PLCC 28	PA28PL28D
ATMEL	ATF750LVCL(V750B)	PLCC 28	PA28PL28D
ATMEL	ATF750C	PLCC 28	PA28PL28D
ATMEL	ATF750CL	PLCC 28	PA28PL28D
ATMEL	ATF750LVC	PLCC 28	PA28PL28D
ATMEL	ATF750LVCL	PLCC 28	PA28PL28D
ATMEL	ATF750CEXT	PLCC 28	PA28PL28D
ATMEL	ATF750LVCEXT	PLCC 28	PA28PL28D
ATMEL	ATF750C(V750)	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF750CL(V750)	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF750LVC(V750)	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF750LVCL(V750)	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF750C(V750B)	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF750CL(V750B)	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF750LVC(V750B)	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF750LVCL(V750B)	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF750C	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF750LVC	SOIC 24	PA28SO28D-EO-300

ATMEL	ATF750CL	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF750LVCL	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF750CEXT	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF750LVCEXT	SOIC 24	PA28SO28D-EO-300
ATMEL	ATF750C(V750)	TSSOP 24	PA24TSS24D
ATMEL	ATF750CL(V750)	TSSOP 24	PA24TSS24D
ATMEL	ATF750LVC(V750)	TSSOP 24	PA24TSS24D
ATMEL	ATF750LVCL(V750)	TSSOP 24	PA24TSS24D
ATMEL	ATF750C(V750B)	TSSOP 24	PA24TSS24D
ATMEL	ATF750CL(V750B)	TSSOP 24	PA24TSS24D
ATMEL	ATF750LVC(V750B)	TSSOP 24	PA24TSS24D
ATMEL	ATF750LVCL(V750B)	TSSOP 24	PA24TSS24D
ATMEL	ATF750C	TSSOP 24	PA24TSS24D
ATMEL	ATF750LVC	TSSOP 24	PA24TSS24D
ATMEL	ATF750CL	TSSOP 24	PA24TSS24D
ATMEL	ATF750LVCL	TSSOP 24	PA24TSS24D
ATMEL	ATF750CEXT	TSSOP 24	PA24TSS24D
ATMEL	ATF750LVCEXT	TSSOP 24	PA24TSS24D
CYPRESS	PALC16L8	DIP 20	
CYPRESS	PALC16R4	DIP 20	
CYPRESS	PALC16R6	DIP 20	
CYPRESS	PALC16R8	DIP 20	
CYPRESS	PALC16L8	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALC16R4	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALC16R6	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALC16R8	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8	DIP 20	
CYPRESS	PALCE16V8as10H8	DIP 20	
CYPRESS	PALCE16V8as10L8	DIP 20	
CYPRESS	PALCE16V8as10P8	DIP 20	
CYPRESS	PALCE16V8as12H6	DIP 20	
CYPRESS	PALCE16V8as12L6	DIP 20	
CYPRESS	PALCE16V8as12P6	DIP 20	
CYPRESS	PALCE16V8as14H4	DIP 20	
CYPRESS	PALCE16V8as14L4	DIP 20	
CYPRESS	PALCE16V8as14P4	DIP 20	
CYPRESS	PALCE16V8as16H2	DIP 20	
CYPRESS	PALCE16V8as16L2	DIP 20	
CYPRESS	PALCE16V8as16P2	DIP 20	
CYPRESS	PALCE16V8as16H8	DIP 20	
CYPRESS	PALCE16V8as16L8	DIP 20	
CYPRESS	PALCE16V8as16P8	DIP 20	
CYPRESS	PALCE16V8as16R4	DIP 20	
CYPRESS	PALCE16V8as16R6	DIP 20	
CYPRESS	PALCE16V8as16R8	DIP 20	
CYPRESS	PALCE16V8as16RP4	DIP 20	
CYPRESS	PALCE16V8as16RP6	DIP 20	
CYPRESS	PALCE16V8as16RP8	DIP 20	
CYPRESS	PALCE16V8	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as10H8	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as10L8	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as10P8	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as12H6	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as12L6	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as12P6	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as14H4	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as14L4	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as14P4	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16H2	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16L2	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16P2	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16H8	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16L8	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16P8	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16R4	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16R6	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16R8	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16RP4	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16RP6	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16RP8	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as10H8	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as10L8	LCC 20	PA20LC20D[Dead Bug]

CYPRESS	PALCE16V8as10P8	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as12H6	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as12L6	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as12P6	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as14H4	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as14L4	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as14P4	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16H2	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16L2	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16P2	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16H8	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16L8	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16P8	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16R4	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16R6	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16R8	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16RP4	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16RP6	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16RP8	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8as10H8	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8as10L8	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8as10P8	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8as12H6	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8as12L6	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8as12P6	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8as14H4	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8as14L4	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8as14P4	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8as16H2	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8as16L2	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8as16P2	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8as16H8	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8as16L8	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8as16P8	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8as16R4	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8as16R6	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8as16R8	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8as16RP4	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8as16RP6	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8as16RP8	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8L	DIP 20	
CYPRESS	PALCE16V8Las10H8	DIP 20	
CYPRESS	PALCE16V8Las10L8	DIP 20	
CYPRESS	PALCE16V8Las10P8	DIP 20	
CYPRESS	PALCE16V8Las12H6	DIP 20	
CYPRESS	PALCE16V8Las12L6	DIP 20	
CYPRESS	PALCE16V8Las12P6	DIP 20	
CYPRESS	PALCE16V8Las14H4	DIP 20	
CYPRESS	PALCE16V8Las14L4	DIP 20	
CYPRESS	PALCE16V8Las14P4	DIP 20	
CYPRESS	PALCE16V8Las16H2	DIP 20	
CYPRESS	PALCE16V8Las16L2	DIP 20	
CYPRESS	PALCE16V8Las16P2	DIP 20	
CYPRESS	PALCE16V8Las16H8	DIP 20	
CYPRESS	PALCE16V8Las16L8	DIP 20	
CYPRESS	PALCE16V8Las16P8	DIP 20	
CYPRESS	PALCE16V8Las16R4	DIP 20	
CYPRESS	PALCE16V8Las16R6	DIP 20	
CYPRESS	PALCE16V8Las16R8	DIP 20	
CYPRESS	PALCE16V8Las16RP4	DIP 20	
CYPRESS	PALCE16V8Las16RP6	DIP 20	
CYPRESS	PALCE16V8Las16RP8	DIP 20	
CYPRESS	PALCE16V8L	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las10H8	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las10L8	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las10P8	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las12H6	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las12L6	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las12P6	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las14H4	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las14L4	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las14P4	PLCC 20	PA20LC20D[Dead Bug]

CYPRESS	PALCE16V8Las16H2	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16L2	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16P2	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16H8	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16L8	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16P8	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16R4	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16R6	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16R8	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16RP4	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16RP6	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16RP8	PLCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8L	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las10H8	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las10L8	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las10P8	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las12H6	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las12L6	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las12P6	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las14H4	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las14L4	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las14P4	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16H2	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16L2	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16P2	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16H8	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16L8	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16P8	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16R4	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16R6	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16R8	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16RP4	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16RP6	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16RP8	LCC 20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8L	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las10H8	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las10L8	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las10P8	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las12H6	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las12L6	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las12P6	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las14H4	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las14L4	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las14P4	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las16H2	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las16L2	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las16P2	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las16H8	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las16L8	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las16P8	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las16R4	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las16R6	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las16R8	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las16RP4	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las16RP6	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las16RP8	SOIC 20	PA20SO20D-EO-210
CYPRESS	PALCE20V8	DIP 24	
CYPRESS	PALCE20V8as14H8	DIP 24	
CYPRESS	PALCE20V8as14L8	DIP 24	
CYPRESS	PALCE20V8as14P8	DIP 24	
CYPRESS	PALCE20V8as16H6	DIP 24	
CYPRESS	PALCE20V8as16L6	DIP 24	
CYPRESS	PALCE20V8as16P6	DIP 24	
CYPRESS	PALCE20V8as18H4	DIP 24	
CYPRESS	PALCE20V8as18L4	DIP 24	
CYPRESS	PALCE20V8as18P4	DIP 24	
CYPRESS	PALCE20V8as20H2	DIP 24	
CYPRESS	PALCE20V8as20L2	DIP 24	
CYPRESS	PALCE20V8as20P2	DIP 24	
CYPRESS	PALCE20V8as20H8	DIP 24	
CYPRESS	PALCE20V8as20L8	DIP 24	
CYPRESS	PALCE20V8as20P8	DIP 24	
CYPRESS	PALCE20V8as20R4	DIP 24	

CYPRESS	PALCE20V8as20R6	DIP 24	
CYPRESS	PALCE20V8as20R8	DIP 24	
CYPRESS	PALCE20V8as20RP4	DIP 24	
CYPRESS	PALCE20V8as20RP6	DIP 24	
CYPRESS	PALCE20V8as20RP8	DIP 24	
CYPRESS	PALCE20V8	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8as14H8	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8as14L8	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8as14P8	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8as16H6	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8as16L6	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8as16P6	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8as18H4	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8as18L4	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8as18P4	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8as20H2	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8as20L2	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8as20P2	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8as20H8	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8as20L8	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8as20P8	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8as20R4	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8as20R6	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8as20R8	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8as20RP4	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8as20RP6	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8as20RP8	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8	LCC 28	PA28PL28D
CYPRESS	PALCE20V8as14H8	LCC 28	PA28PL28D
CYPRESS	PALCE20V8as14L8	LCC 28	PA28PL28D
CYPRESS	PALCE20V8as14P8	LCC 28	PA28PL28D
CYPRESS	PALCE20V8as16H6	LCC 28	PA28PL28D
CYPRESS	PALCE20V8as16L6	LCC 28	PA28PL28D
CYPRESS	PALCE20V8as16P6	LCC 28	PA28PL28D
CYPRESS	PALCE20V8as18H4	LCC 28	PA28PL28D
CYPRESS	PALCE20V8as18L4	LCC 28	PA28PL28D
CYPRESS	PALCE20V8as18P4	LCC 28	PA28PL28D
CYPRESS	PALCE20V8as20H2	LCC 28	PA28PL28D
CYPRESS	PALCE20V8as20L2	LCC 28	PA28PL28D
CYPRESS	PALCE20V8as20P2	LCC 28	PA28PL28D
CYPRESS	PALCE20V8as20H8	LCC 28	PA28PL28D
CYPRESS	PALCE20V8as20L8	LCC 28	PA28PL28D
CYPRESS	PALCE20V8as20P8	LCC 28	PA28PL28D
CYPRESS	PALCE20V8as20R4	LCC 28	PA28PL28D
CYPRESS	PALCE20V8as20R6	LCC 28	PA28PL28D
CYPRESS	PALCE20V8as20R8	LCC 28	PA28PL28D
CYPRESS	PALCE20V8as20RP4	LCC 28	PA28PL28D
CYPRESS	PALCE20V8as20RP6	LCC 28	PA28PL28D
CYPRESS	PALCE20V8as20RP8	LCC 28	PA28PL28D
CYPRESS	PALCE20V8	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as14H8	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as14L8	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as14P8	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as16H6	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as16L6	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as16P6	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as18H4	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as18L4	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as18P4	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as20H2	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as20L2	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as20P2	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as20H8	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as20L8	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as20P8	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as20R4	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as20R6	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as20R8	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as20RP4	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as20RP6	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as20RP8	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8L	DIP 24	
CYPRESS	PALCE20V8Las14H8	DIP 24	

CYPRESS	PALCE20V8Las14L8	DIP 24	
CYPRESS	PALCE20V8Las14P8	DIP 24	
CYPRESS	PALCE20V8Las16H6	DIP 24	
CYPRESS	PALCE20V8Las16L6	DIP 24	
CYPRESS	PALCE20V8Las16P6	DIP 24	
CYPRESS	PALCE20V8Las18H4	DIP 24	
CYPRESS	PALCE20V8Las18L4	DIP 24	
CYPRESS	PALCE20V8Las18P4	DIP 24	
CYPRESS	PALCE20V8Las20H2	DIP 24	
CYPRESS	PALCE20V8Las20L2	DIP 24	
CYPRESS	PALCE20V8Las20P2	DIP 24	
CYPRESS	PALCE20V8Las20H8	DIP 24	
CYPRESS	PALCE20V8Las20L8	DIP 24	
CYPRESS	PALCE20V8Las20P8	DIP 24	
CYPRESS	PALCE20V8Las20R4	DIP 24	
CYPRESS	PALCE20V8Las20R6	DIP 24	
CYPRESS	PALCE20V8Las20R8	DIP 24	
CYPRESS	PALCE20V8Las20RP4	DIP 24	
CYPRESS	PALCE20V8Las20RP6	DIP 24	
CYPRESS	PALCE20V8Las20RP8	DIP 24	
CYPRESS	PALCE20V8L	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8Las14H8	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8Las14L8	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8Las14P8	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8Las16H6	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8Las16L6	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8Las16P6	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8Las18H4	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8Las18L4	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8Las18P4	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8Las20H2	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8Las20L2	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8Las20P2	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8Las20H8	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8Las20L8	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8Las20P8	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8Las20R4	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8Las20R6	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8Las20R8	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8Las20RP4	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8Las20RP6	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8Las20RP8	PLCC 28	PA28PL28D
CYPRESS	PALCE20V8L	LCC 28	PA28PL28D
CYPRESS	PALCE20V8Las14H8	LCC 28	PA28PL28D
CYPRESS	PALCE20V8Las14L8	LCC 28	PA28PL28D
CYPRESS	PALCE20V8Las14P8	LCC 28	PA28PL28D
CYPRESS	PALCE20V8Las16H6	LCC 28	PA28PL28D
CYPRESS	PALCE20V8Las16L6	LCC 28	PA28PL28D
CYPRESS	PALCE20V8Las16P6	LCC 28	PA28PL28D
CYPRESS	PALCE20V8Las18H4	LCC 28	PA28PL28D
CYPRESS	PALCE20V8Las18L4	LCC 28	PA28PL28D
CYPRESS	PALCE20V8Las18P4	LCC 28	PA28PL28D
CYPRESS	PALCE20V8Las20H2	LCC 28	PA28PL28D
CYPRESS	PALCE20V8Las20L2	LCC 28	PA28PL28D
CYPRESS	PALCE20V8Las20P2	LCC 28	PA28PL28D
CYPRESS	PALCE20V8Las20H8	LCC 28	PA28PL28D
CYPRESS	PALCE20V8Las20L8	LCC 28	PA28PL28D
CYPRESS	PALCE20V8Las20P8	LCC 28	PA28PL28D
CYPRESS	PALCE20V8Las20R4	LCC 28	PA28PL28D
CYPRESS	PALCE20V8Las20R6	LCC 28	PA28PL28D
CYPRESS	PALCE20V8Las20R8	LCC 28	PA28PL28D
CYPRESS	PALCE20V8Las20RP4	LCC 28	PA28PL28D
CYPRESS	PALCE20V8Las20RP6	LCC 28	PA28PL28D
CYPRESS	PALCE20V8Las20RP8	LCC 28	PA28PL28D
CYPRESS	PALCE20V8L	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las14H8	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las14L8	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las14P8	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las16H6	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las16L6	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las16P6	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las18H4	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las18L4	SOP 24	PA28SO28D-EO-300

CYPRESS	PALCE20V8Las18P4	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las20H2	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las20L2	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las20P2	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las20H8	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las20L8	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las20P8	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las20R4	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las20R8	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las20RP4	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las20RP6	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las20RP8	SOP 24	PA28SO28D-EO-300
CYPRESS	PALCE22V10	DIP 24	
CYPRESS	PALCE22V10	PLCC 28	PA28PL28D
CYPRESS	PALC22V10D	DIP 24	
CYPRESS	PALC22V10D	PLCC 28	PA28PL28D
CYPRESS	PLDC20G10	DIP 24	
CYPRESS	PLDC20G10B	DIP 24	
CYPRESS	PLDC20RA10	DIP 24	
CYPRESS	PLDC20G10	PLCC 28	PA28PL24D2P6-YA
CYPRESS	PLDC20G10B	PLCC 28	PA28PL24D2P6-YA
CYPRESS	PLDC20RA10	PLCC 28	PA28PL24D2P6-YA
CYPRESS	PALC22V10	DIP 24	
CYPRESS	PALC22V10L	DIP 24	
CYPRESS	PALC22V10B	DIP 24	
CYPRESS	PALC22V10	PLCC 28	PA28PL24D2P6-YA
CYPRESS	PALC22V10L	PLCC 28	PA28PL24D2P6-YA
CYPRESS	PALC22V10B	PLCC 28	PA28PL24D2P6-YA
AMI	PEEL18CV8	DIP 20	
AMI	PEEL18CV8	SOIC 20	PA28SO28D-EO-300
AMI	PEEL18CV8	PLCC 20	PA20LC20D[Dead Bug]
AMI	PEEL18CV8	TSSOP 20	PA24TSS24D
AMI	PEEL22CV10	DIP 24	
AMI	PEEL22CV10	SOIC 24	PA28SO28D-EO-300
AMI	PEEL22CV10	PLCC 28	PA28PL28D
AMI	PEEL22CV10A	DIP 24	
AMI	PEEL22CV10A	SOIC 24	PA28SO28D-EO-300
AMI	PEEL22CV10A	PLCC 28	PA28PL28D
AMI	PEEL22CV10A	TSSOP 24	PA24TSS24D
AMI	PEEL22CV10A+	DIP 24	
AMI	PEEL22CV10A+	SOIC 24	PA28SO28D-EO-300
AMI	PEEL22CV10A+	PLCC 28	PA28PL28D
AMI	PEEL22CV10A+	TSSOP 24	PA24TSS24D
AMI	PEEL22CV10A++	DIP 24	
AMI	PEEL22CV10A++	SOIC 24	PA28SO28D-EO-300
AMI	PEEL22CV10A++	PLCC 28	PA28PL28D
AMI	PEEL22CV10A++	TSSOP 24	PA24TSS24D
AMI	PEEL22CV10AZ+	DIP 24	
AMI	PEEL22CV10AZ+	SOIC 24	PA28SO28D-EO-300
AMI	PEEL22CV10AZ+	PLCC 28	PA28PL28D
AMI	PEEL22CV10AZ+	TSSOP 24	PA24TSS24D
AMI	PEEL22CV10Z	DIP 24	
AMI	PEEL22CV10Z	SOIC 24	PA28SO28D-EO-300
AMI	PEEL22CV10Z	PLCC 28	PA28PL28D
ANACHIP	PEEL16CV8	DIP 20	
ANACHIP	PEEL16CV8	SOIC 20	PA28SO28D-EO-300
ANACHIP	PEEL16CV8	PLCC 20	PA20LC20D[Dead Bug]
ANACHIP	PEEL16CV8	TSSOP 20	PA24TSS24D
ANACHIP	PEEL18CV8	DIP 20	
ANACHIP	PEEL18CV8	SOIC 20	PA28SO28D-EO-300
ANACHIP	PEEL18CV8	PLCC 20	PA20LC20D[Dead Bug]
ANACHIP	PEEL18CV8	TSSOP 20	PA24TSS24D
ANACHIP	PEEL18CV8Z	DIP 20	
ANACHIP	PEEL18CV8Z	SOIC 20	PA28SO28D-EO-300
ANACHIP	PEEL18CV8Z	PLCC 20	PA20LC20D[Dead Bug]
ANACHIP	PEEL18CV8Z	TSSOP 20	PA24TSS24D
ANACHIP	PEEL18LV8Z	DIP 20	
ANACHIP	PEEL18LV8Z	SOIC 20	PA28SO28D-EO-300
ANACHIP	PEEL18LV8Z	PLCC 20	PA20LC20D[Dead Bug]
ANACHIP	PEEL18LV8Z	TSSOP 20	PA24TSS24D
ANACHIP	PEEL22CV10	DIP 24	
ANACHIP	PEEL22CV10	SOIC 24	PA28SO28D-EO-300



ANACHIP	PEEL22CV10	PLCC 28	PA28PL28D
ANACHIP	PEEL22CV10	TSSOP 24	PA24TSS24D
ANACHIP	PEEL22CV10A	DIP 24	
ANACHIP	PEEL22CV10A	SOIC 24	PA28SO28D-EO-300
ANACHIP	PEEL22CV10A	PLCC 28	PA28PL28D
ANACHIP	PEEL22CV10A	TSSOP 24	PA24TSS24D
ANACHIP	PEEL22CV10A+	DIP 24	
ANACHIP	PEEL22CV10A+	SOIC 24	PA28SO28D-EO-300
ANACHIP	PEEL22CV10A+	PLCC 28	PA28PL28D
ANACHIP	PEEL22CV10A+	TSSOP 24	PA24TSS24D
ANACHIP	PEEL22CV10A++	DIP 24	
ANACHIP	PEEL22CV10A++	SOIC 24	PA28SO28D-EO-300
ANACHIP	PEEL22CV10A++	PLCC 28	PA28PL28D
ANACHIP	PEEL22CV10A++	TSSOP 24	PA24TSS24D
ANACHIP	PEEL22CV10AZ	DIP 24	
ANACHIP	PEEL22CV10AZ	SOIC 24	PA28SO28D-EO-300
ANACHIP	PEEL22CV10AZ	PLCC 28	PA28PL28D
ANACHIP	PEEL22CV10AZ+	TSSOP 24	PA24TSS24D
ANACHIP	PEEL22CV10AZ+	DIP 24	
ANACHIP	PEEL22CV10AZ+	SOIC 24	PA28SO28D-EO-300
ANACHIP	PEEL22CV10AZ+	PLCC 28	PA28PL28D
ANACHIP	PEEL22CV10AZ+	TSSOP 24	PA24TSS24D
ANACHIP	PEEL22CV10AZ++	DIP 24	
ANACHIP	PEEL22CV10AZ++	SOIC 24	PA28SO28D-EO-300
ANACHIP	PEEL22CV10AZ++	PLCC 28	PA28PL28D
ANACHIP	PEEL22CV10AZ++	TSSOP 24	PA24TSS24D
ANACHIP	PEEL22CV10Z	DIP 24	
ANACHIP	PEEL22CV10Z	SOIC 24	PA28SO28D-EO-300
ANACHIP	PEEL22CV10Z	PLCC 28	PA28PL28D
ANACHIP	PEEL22CV10Z	TSSOP 24	PA24TSS24D
GOULD	PEEL153	DIP 20	
GOULD	PEEL253	DIP 20	
GOULD	PEEL173	DIP 24	
GOULD	PEEL273	DIP 24	
GOULD	PEEL18CV8	DIP 20	
GOULD	PEEL18CV8	SOIC 20	PA28SO28D-EO-300
GOULD	PEEL18CV8	PLCC 20	PA20LC20D[Dead Bug]
GOULD	PEEL18CV8	TSSOP 20	PA24TSS24D
GOULD	PEEL20CG10	DIP 24	
GOULD	PEEL22CV10	DIP 24	
GOULD	PEEL22CV10	DIP 24	
GOULD	PEEL22CV10	SOIC 24	PA28SO28D-EO-300
GOULD	PEEL22CV10	PLCC 28	PA28PL28D
GOULD	PEEL22CV10	TSSOP 24	PA24TSS24D
GOULD	PEEL22CV10A	DIP 24	
GOULD	PEEL22CV10A	SOIC 24	PA28SO28D-EO-300
GOULD	PEEL22CV10A	PLCC 28	PA28PL28D
GOULD	PEEL22CV10A	TSSOP 24	PA24TSS24D
GOULD	PEEL22CV10A+	DIP 24	
GOULD	PEEL22CV10A+	SOIC 24	PA28SO28D-EO-300
GOULD	PEEL22CV10A+	PLCC 28	PA28PL28D
GOULD	PEEL22CV10A+	TSSOP 24	PA24TSS24D
GOULD	PEEL22CV10A++	DIP 24	
GOULD	PEEL22CV10A++	SOIC 24	PA28SO28D-EO-300
GOULD	PEEL22CV10A++	PLCC 28	PA28PL28D
GOULD	PEEL22CV10A++	TSSOP 24	PA24TSS24D
GOULD	PEEL22CV10AZ+	DIP 24	
GOULD	PEEL22CV10AZ+	SOIC 24	PA28SO28D-EO-300
GOULD	PEEL22CV10AZ+	PLCC 28	PA28PL28D
GOULD	PEEL22CV10AZ+	TSSOP 24	PA24TSS24D
GOULD	PEEL22CV10AZ++	DIP 24	
GOULD	PEEL22CV10AZ++	SOIC 24	PA28SO28D-EO-300
GOULD	PEEL22CV10AZ++	PLCC 28	PA28PL28D
GOULD	PEEL22CV10AZ++	TSSOP 24	PA24TSS24D
GOULD	PEEL22CV10Z	DIP 24	
GOULD	PEEL22CV10Z	SOIC 24	PA28SO28D-EO-300
GOULD	PEEL22CV10Z	PLCC 28	PA28PL28D
GOULD	PEEL22CV10Z	TSSOP 24	PA24TSS24D
HYNIX	PEEL18CV8	DIP 20	
HYNIX	PEEL18CV8	SOIC 20	PA28SO28D-EO-300
HYNIX	PEEL18CV8	PLCC 20	PA20LC20D[Dead Bug]
HYNIX	PEEL18CV8	TSSOP 20	PA24TSS24D
ICT	PEEL16CV8	DIP 20	

ICT	PEEL16CV8	SOIC 20	PA28SO28D-EO-300
ICT	PEEL16CV8	PLCC 20	PA20LC20D[Dead Bug]
ICT	PEEL16CV8	TSSOP 20	PA20SS-P54
ICT	PEEL18CV8	DIP 20	
ICT	PEEL18CV8	SOIC 20	PA28SO28D-EO-300
ICT	PEEL18CV8	PLCC 20	PA20LC20D[Dead Bug]
ICT	PEEL18CV8	TSSOP 20	PA24TSS24D
ICT	PEEL18CV8Z	DIP 20	
ICT	PEEL18CV8Z	SOIC 20	PA28SO28D-EO-300
ICT	PEEL18CV8Z	PLCC 20	PA20LC20D[Dead Bug]
ICT	PEEL18CV8Z	TSSOP 20	PA24TSS24D
ICT	PEEL18LV8Z	DIP 20	
ICT	PEEL18LV8Z	SOIC 20	PA28SO28D-EO-300
ICT	PEEL18LV8Z	PLCC 20	PA20LC20D[Dead Bug]
ICT	PEEL18LV8Z	TSSOP 20	PA24TSS24D
ICT	PEEL20CG10	DIP 24	
ICT	PEEL20CG10A	DIP 24	
ICT	PEEL22CV10	DIP 24	
ICT	PEEL22CV10	SOIC 24	PA28SO28D-EO-300
ICT	PEEL22CV10	PLCC 28	PA28PL28D
ICT	PEEL22CV10	TSSOP 24	PA24TSS24D
ICT	PEEL22CV10A	DIP 24	
ICT	PEEL22CV10A	SOIC 24	PA28SO28D-EO-300
ICT	PEEL22CV10A	PLCC 28	PA28PL28D
ICT	PEEL22CV10A	TSSOP 24	PA24TSS24D
ICT	PEEL22CV10A+	DIP 24	
ICT	PEEL22CV10A+	SOIC 24	PA28SO28D-EO-300
ICT	PEEL22CV10A+	PLCC 28	PA28PL28D
ICT	PEEL22CV10A+	TSSOP 24	PA24TSS24D
ICT	PEEL22CV10A++	DIP 24	
ICT	PEEL22CV10A++	SOIC 24	PA28SO28D-EO-300
ICT	PEEL22CV10A++	PLCC 28	PA28PL28D
ICT	PEEL22CV10A++	TSSOP 24	PA24TSS24D
ICT	PEEL22CV10AZ	DIP 24	
ICT	PEEL22CV10AZ	SOIC 24	PA28SO28D-EO-300
ICT	PEEL22CV10AZ	PLCC 28	PA28PL28D
ICT	PEEL22CV10AZ	TSSOP 24	PA24TSS24D
ICT	PEEL22CV10AZ+	DIP 24	
ICT	PEEL22CV10AZ+	SOIC 24	PA28SO28D-EO-300
ICT	PEEL22CV10AZ+	PLCC 28	PA28PL28D
ICT	PEEL22CV10AZ+	TSSOP 24	PA24TSS24D
ICT	PEEL22CV10AZ++	DIP 24	
ICT	PEEL22CV10AZ++	SOIC 24	PA28SO28D-EO-300
ICT	PEEL22CV10AZ++	PLCC 28	PA28PL28D
ICT	PEEL22CV10AZ++	TSSOP 24	PA24TSS24D
ICT	PEEL22CV10Z	DIP 24	
ICT	PEEL22CV10Z	SOIC 24	PA28SO28D-EO-300
ICT	PEEL22CV10Z	PLCC 28	PA28PL28D
ICT	PEEL22CV10Z	TSSOP 24	PA24TSS24D
ICT	PEEL153	DIP 20	
ICT	PEEL253	DIP 20	
ICT	PEEL173	DIP 24	
ICT	PEEL273	DIP 24	
ICT	PA7024P	DIP 24	
ICT	PA7024J	PLCC 28	PA28PL28D
ICT	PA7128P	DIP 28	
ICT	PA7140P	DIP 40	
ICT	PA7140J	PLCC 44	PA44-48U
ICT	PA7536P	DIP 28	
ICT	PA7536J	PLCC 28	PA28PL28D
ICT	PA7536S	SOIC 28	PA28SO28D-EO-300
ICT	PA7540P	DIP 24	
ICT	PA7540J	PLCC 28	PA28PL28D
ICT	PA7572P	DIP 40	
ICT	PA7572J	PLCC 44	PA44-48U
ICT	PA7572Q	TQFP 44	PA44QF44D
INTEL	5C031	DIP 20	
INTEL	5C032	DIP 20	
INTEL	5C031	PLCC 20	PA20LC20D[Dead Bug]
INTEL	5C032	PLCC 20	PA20LC20D[Dead Bug]
INTEL	5C060	DIP 24	
INTEL	5C060	PLCC 28	PA28PL24D2P6-YA
INTEL	5C090	DIP 40	

INTEL	5C090	PLCC 44	PA900-44
INTEL	5C090	PLCC 44	PA44-48U
INTEL	5C180	PLCC 68	PA-EP1800
LATTICE	GAL16V8	DIP 20	
LATTICE	GAL16V8as10H8	DIP 20	
LATTICE	GAL16V8as10L8	DIP 20	
LATTICE	GAL16V8as10P8	DIP 20	
LATTICE	GAL16V8as12H6	DIP 20	
LATTICE	GAL16V8as12L6	DIP 20	
LATTICE	GAL16V8as12P6	DIP 20	
LATTICE	GAL16V8as14H4	DIP 20	
LATTICE	GAL16V8as14L4	DIP 20	
LATTICE	GAL16V8as14P4	DIP 20	
LATTICE	GAL16V8as16H2	DIP 20	
LATTICE	GAL16V8as16L2	DIP 20	
LATTICE	GAL16V8as16P2	DIP 20	
LATTICE	GAL16V8as16H8	DIP 20	
LATTICE	GAL16V8as16L8	DIP 20	
LATTICE	GAL16V8as16P8	DIP 20	
LATTICE	GAL16V8as16R4	DIP 20	
LATTICE	GAL16V8as16R6	DIP 20	
LATTICE	GAL16V8as16R8	DIP 20	
LATTICE	GAL16V8as16RP4	DIP 20	
LATTICE	GAL16V8as16RP6	DIP 20	
LATTICE	GAL16V8as16RP8	DIP 20	
LATTICE	GAL16V8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as10H8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as10L8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as10P8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as12H6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as12L6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as12P6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as14H4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as14L4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as14P4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as16H2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as16L2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as16P2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as16H8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as16L8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as16P8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as16R4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as16R6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as16R8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as16RP4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as16RP6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as16RP8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8as10H8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8as10L8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8as10P8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8as12H6	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8as12L6	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8as12P6	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8as14H4	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8as14L4	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8as14P4	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8as16H2	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8as16L2	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8as16P2	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8as16H8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8as16L8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8as16P8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8as16R4	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8as16R6	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8as16R8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8as16RP4	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8as16RP6	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8as16RP8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8A	DIP 20	
LATTICE	GAL16V8Aas10H8	DIP 20	
LATTICE	GAL16V8Aas10L8	DIP 20	
LATTICE	GAL16V8Aas10P8	DIP 20	

LATTICE	GAL16V8Aas12H6	DIP 20	
LATTICE	GAL16V8Aas12L6	DIP 20	
LATTICE	GAL16V8Aas12P6	DIP 20	
LATTICE	GAL16V8Aas14H4	DIP 20	
LATTICE	GAL16V8Aas14L4	DIP 20	
LATTICE	GAL16V8Aas14P4	DIP 20	
LATTICE	GAL16V8Aas16H2	DIP 20	
LATTICE	GAL16V8Aas16L2	DIP 20	
LATTICE	GAL16V8Aas16P2	DIP 20	
LATTICE	GAL16V8Aas16H8	DIP 20	
LATTICE	GAL16V8Aas16L8	DIP 20	
LATTICE	GAL16V8Aas16P8	DIP 20	
LATTICE	GAL16V8Aas16R4	DIP 20	
LATTICE	GAL16V8Aas16R6	DIP 20	
LATTICE	GAL16V8Aas16R8	DIP 20	
LATTICE	GAL16V8Aas16RP4	DIP 20	
LATTICE	GAL16V8Aas16RP6	DIP 20	
LATTICE	GAL16V8Aas16RP8	DIP 20	
LATTICE	GAL16V8A	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas10H8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas10L8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas10P8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas12H6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas12L6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas12P6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas14H4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas14L4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas14P4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas16H2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas16L2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas16P2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas16H8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas16L8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas16P8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas16R4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas16R6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas16R8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas16RP4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas16RP6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas16RP8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8A	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas10H8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas10L8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas10P8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas12H6	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas12L6	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas12P6	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas14H4	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas14L4	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas14P4	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas16H2	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas16L2	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas16P2	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas16H8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas16L8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas16P8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas16R4	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas16R6	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas16R8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas16RP4	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas16RP6	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas16RP8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8B	DIP 20	
LATTICE	GAL16V8Bas10H8	DIP 20	
LATTICE	GAL16V8Bas10L8	DIP 20	
LATTICE	GAL16V8Bas10P8	DIP 20	
LATTICE	GAL16V8Bas12H6	DIP 20	
LATTICE	GAL16V8Bas12L6	DIP 20	
LATTICE	GAL16V8Bas12P6	DIP 20	
LATTICE	GAL16V8Bas14H4	DIP 20	
LATTICE	GAL16V8Bas14L4	DIP 20	
LATTICE	GAL16V8Bas14P4	DIP 20	
LATTICE	GAL16V8Bas16H2	DIP 20	

LATTICE	GAL16V8Bas16L2	DIP 20	
LATTICE	GAL16V8Bas16P2	DIP 20	
LATTICE	GAL16V8Bas16H8	DIP 20	
LATTICE	GAL16V8Bas16L8	DIP 20	
LATTICE	GAL16V8Bas16P8	DIP 20	
LATTICE	GAL16V8Bas16R4	DIP 20	
LATTICE	GAL16V8Bas16R6	DIP 20	
LATTICE	GAL16V8Bas16R8	DIP 20	
LATTICE	GAL16V8Bas16RP4	DIP 20	
LATTICE	GAL16V8Bas16RP6	DIP 20	
LATTICE	GAL16V8Bas16RP8	DIP 20	
LATTICE	GAL16V8B	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas10H8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas10L8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas10P8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas12H6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas12L6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas12P6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas14H4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas14L4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas14P4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas16H2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas16L2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas16P2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas16H8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas16L8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas16P8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas16R4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas16R6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas16R8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas16RP4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas16RP6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas16RP8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8B	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas10H8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas10L8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas10P8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas12H6	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas12L6	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas12P6	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas14H4	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas14L4	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas14P4	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas16H2	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas16L2	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas16P2	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas16H8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas16L8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas16P8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas16R4	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas16R6	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas16R8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas16RP4	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas16RP6	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas16RP8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8C	DIP 20	
LATTICE	GAL16V8Cas10H8	DIP 20	
LATTICE	GAL16V8Cas10L8	DIP 20	
LATTICE	GAL16V8Cas10P8	DIP 20	
LATTICE	GAL16V8Cas12H6	DIP 20	
LATTICE	GAL16V8Cas12L6	DIP 20	
LATTICE	GAL16V8Cas12P6	DIP 20	
LATTICE	GAL16V8Cas14H4	DIP 20	
LATTICE	GAL16V8Cas14L4	DIP 20	
LATTICE	GAL16V8Cas14P4	DIP 20	
LATTICE	GAL16V8Cas16H2	DIP 20	
LATTICE	GAL16V8Cas16L2	DIP 20	
LATTICE	GAL16V8Cas16P2	DIP 20	
LATTICE	GAL16V8Cas16H8	DIP 20	
LATTICE	GAL16V8Cas16L8	DIP 20	
LATTICE	GAL16V8Cas16P8	DIP 20	
LATTICE	GAL16V8Cas16R4	DIP 20	
LATTICE	GAL16V8Cas16R6	DIP 20	

LATTICE	GAL16V8Cas16R8	DIP 20	
LATTICE	GAL16V8Cas16RP4	DIP 20	
LATTICE	GAL16V8Cas16RP6	DIP 20	
LATTICE	GAL16V8Cas16RP8	DIP 20	
LATTICE	GAL16V8C	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas10H8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas10L8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas10P8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas12H6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas12L6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas12P6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas14H4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas14L4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas14P4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas16H2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas16L2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas16P2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas16H8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas16L8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas16P8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas16R4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas16R6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas16R8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas16RP4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas16RP6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas16RP8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8C	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas10H8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas10L8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas10P8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas12H6	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas12L6	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas12P6	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas14H4	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas14L4	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas14P4	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas16H2	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas16L2	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas16P2	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas16H8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas16L8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas16P8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas16R4	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas16R6	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas16R8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas16RP4	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas16RP6	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas16RP8	SOIC 20	PA20SO20D-EO-210
LATTICE	GAL16V8D	DIP 20	
LATTICE	GAL16V8Das10H8	DIP 20	
LATTICE	GAL16V8Das10L8	DIP 20	
LATTICE	GAL16V8Das10P8	DIP 20	
LATTICE	GAL16V8Das12H6	DIP 20	
LATTICE	GAL16V8Das12L6	DIP 20	
LATTICE	GAL16V8Das12P6	DIP 20	
LATTICE	GAL16V8Das14H4	DIP 20	
LATTICE	GAL16V8Das14L4	DIP 20	
LATTICE	GAL16V8Das14P4	DIP 20	
LATTICE	GAL16V8Das16H2	DIP 20	
LATTICE	GAL16V8Das16L2	DIP 20	
LATTICE	GAL16V8Das16P2	DIP 20	
LATTICE	GAL16V8Das16H8	DIP 20	
LATTICE	GAL16V8Das16L8	DIP 20	
LATTICE	GAL16V8Das16P8	DIP 20	
LATTICE	GAL16V8Das16R4	DIP 20	
LATTICE	GAL16V8Das16R6	DIP 20	
LATTICE	GAL16V8Das16R8	DIP 20	
LATTICE	GAL16V8Das16RP4	DIP 20	
LATTICE	GAL16V8Das16RP6	DIP 20	
LATTICE	GAL16V8Das16RP8	DIP 20	
LATTICE	GAL16V8D	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Das10H8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Das10L8	PLCC 20	PA20LC20D[Dead Bug]



LATTICE	GAL16LV8Das14P4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das16H2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das16L2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das16P2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das16H8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das16L8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das16P8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das16R4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das16R6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das16R8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das16RP4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das16RP6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das16RP8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Z	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas10H8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas10L8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas10P8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas12H6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas12L6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas12P6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas14H4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas14L4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas14P4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas16H2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas16L2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas16P2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas16H8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas16L8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas16P8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas16R4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas16R6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas16R8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas16RP4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas16RP6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas16RP8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL20V8	DIP 24	
LATTICE	GAL20V8as14H8	DIP 24	
LATTICE	GAL20V8as14L8	DIP 24	
LATTICE	GAL20V8as14P8	DIP 24	
LATTICE	GAL20V8as16H6	DIP 24	
LATTICE	GAL20V8as16L6	DIP 24	
LATTICE	GAL20V8as16P6	DIP 24	
LATTICE	GAL20V8as18H4	DIP 24	
LATTICE	GAL20V8as18L4	DIP 24	
LATTICE	GAL20V8as18P4	DIP 24	
LATTICE	GAL20V8as20H2	DIP 24	
LATTICE	GAL20V8as20L2	DIP 24	
LATTICE	GAL20V8as20P2	DIP 24	
LATTICE	GAL20V8as20H8	DIP 24	
LATTICE	GAL20V8as20L8	DIP 24	
LATTICE	GAL20V8as20P8	DIP 24	
LATTICE	GAL20V8as20R4	DIP 24	
LATTICE	GAL20V8as20R6	DIP 24	
LATTICE	GAL20V8as20R8	DIP 24	
LATTICE	GAL20V8as20RP4	DIP 24	
LATTICE	GAL20V8as20RP6	DIP 24	
LATTICE	GAL20V8as20RP8	DIP 24	
LATTICE	GAL20V8	PLCC 28	PA28PL28D
LATTICE	GAL20V8as14H8	PLCC 28	PA28PL28D
LATTICE	GAL20V8as14L8	PLCC 28	PA28PL28D
LATTICE	GAL20V8as14P8	PLCC 28	PA28PL28D
LATTICE	GAL20V8as16H6	PLCC 28	PA28PL28D
LATTICE	GAL20V8as16L6	PLCC 28	PA28PL28D
LATTICE	GAL20V8as16P6	PLCC 28	PA28PL28D
LATTICE	GAL20V8as18H4	PLCC 28	PA28PL28D
LATTICE	GAL20V8as18L4	PLCC 28	PA28PL28D
LATTICE	GAL20V8as18P4	PLCC 28	PA28PL28D
LATTICE	GAL20V8as20H2	PLCC 28	PA28PL28D
LATTICE	GAL20V8as20L2	PLCC 28	PA28PL28D
LATTICE	GAL20V8as20P2	PLCC 28	PA28PL28D
LATTICE	GAL20V8as20H8	PLCC 28	PA28PL28D
LATTICE	GAL20V8as20L8	PLCC 28	PA28PL28D
LATTICE	GAL20V8as20P8	PLCC 28	PA28PL28D



LATTICE	GAL20V8as20R4	PLCC 28	PA28PL28D
LATTICE	GAL20V8as20R6	PLCC 28	PA28PL28D
LATTICE	GAL20V8as20R8	PLCC 28	PA28PL28D
LATTICE	GAL20V8as20RP4	PLCC 28	PA28PL28D
LATTICE	GAL20V8as20RP6	PLCC 28	PA28PL28D
LATTICE	GAL20V8as20RP8	PLCC 28	PA28PL28D
LATTICE	GAL20V8A	DIP 24	
LATTICE	GAL20V8Aas14H8	DIP 24	
LATTICE	GAL20V8Aas14L8	DIP 24	
LATTICE	GAL20V8Aas14P8	DIP 24	
LATTICE	GAL20V8Aas16H6	DIP 24	
LATTICE	GAL20V8Aas16L6	DIP 24	
LATTICE	GAL20V8Aas16P6	DIP 24	
LATTICE	GAL20V8Aas18H4	DIP 24	
LATTICE	GAL20V8Aas18L4	DIP 24	
LATTICE	GAL20V8Aas18P4	DIP 24	
LATTICE	GAL20V8Aas20H2	DIP 24	
LATTICE	GAL20V8Aas20L2	DIP 24	
LATTICE	GAL20V8Aas20P2	DIP 24	
LATTICE	GAL20V8Aas20H8	DIP 24	
LATTICE	GAL20V8Aas20L8	DIP 24	
LATTICE	GAL20V8Aas20P8	DIP 24	
LATTICE	GAL20V8Aas20R4	DIP 24	
LATTICE	GAL20V8Aas20R6	DIP 24	
LATTICE	GAL20V8Aas20R8	DIP 24	
LATTICE	GAL20V8Aas20RP4	DIP 24	
LATTICE	GAL20V8Aas20RP6	DIP 24	
LATTICE	GAL20V8Aas20RP8	DIP 24	
LATTICE	GAL20V8A	PLCC 28	PA28PL28D
LATTICE	GAL20V8Aas14H8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Aas14L8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Aas14P8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Aas16H6	PLCC 28	PA28PL28D
LATTICE	GAL20V8Aas16L6	PLCC 28	PA28PL28D
LATTICE	GAL20V8Aas16P6	PLCC 28	PA28PL28D
LATTICE	GAL20V8Aas18H4	PLCC 28	PA28PL28D
LATTICE	GAL20V8Aas18L4	PLCC 28	PA28PL28D
LATTICE	GAL20V8Aas18P4	PLCC 28	PA28PL28D
LATTICE	GAL20V8Aas20H2	PLCC 28	PA28PL28D
LATTICE	GAL20V8Aas20L2	PLCC 28	PA28PL28D
LATTICE	GAL20V8Aas20P2	PLCC 28	PA28PL28D
LATTICE	GAL20V8Aas20H8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Aas20L8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Aas20P8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Aas20R4	PLCC 28	PA28PL28D
LATTICE	GAL20V8Aas20R6	PLCC 28	PA28PL28D
LATTICE	GAL20V8Aas20R8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Aas20RP4	PLCC 28	PA28PL28D
LATTICE	GAL20V8Aas20RP6	PLCC 28	PA28PL28D
LATTICE	GAL20V8Aas20RP8	PLCC 28	PA28PL28D
LATTICE	GAL20V8B	DIP 24	
LATTICE	GAL20V8Bas14H8	DIP 24	
LATTICE	GAL20V8Bas14L8	DIP 24	
LATTICE	GAL20V8Bas14P8	DIP 24	
LATTICE	GAL20V8Bas16H6	DIP 24	
LATTICE	GAL20V8Bas16L6	DIP 24	
LATTICE	GAL20V8Bas16P6	DIP 24	
LATTICE	GAL20V8Bas18H4	DIP 24	
LATTICE	GAL20V8Bas18L4	DIP 24	
LATTICE	GAL20V8Bas18P4	DIP 24	
LATTICE	GAL20V8Bas20H2	DIP 24	
LATTICE	GAL20V8Bas20L2	DIP 24	
LATTICE	GAL20V8Bas20P2	DIP 24	
LATTICE	GAL20V8Bas20H8	DIP 24	
LATTICE	GAL20V8Bas20L8	DIP 24	
LATTICE	GAL20V8Bas20P8	DIP 24	
LATTICE	GAL20V8Bas20R4	DIP 24	
LATTICE	GAL20V8Bas20R6	DIP 24	
LATTICE	GAL20V8Bas20R8	DIP 24	
LATTICE	GAL20V8Bas20RP4	DIP 24	
LATTICE	GAL20V8Bas20RP6	DIP 24	
LATTICE	GAL20V8Bas20RP8	DIP 24	
LATTICE	GAL20V8B	PLCC 28	PA28PL28D

LATTICE	GAL20V8Bas14H8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Bas14L8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Bas14P8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Bas16H6	PLCC 28	PA28PL28D
LATTICE	GAL20V8Bas16L6	PLCC 28	PA28PL28D
LATTICE	GAL20V8Bas16P6	PLCC 28	PA28PL28D
LATTICE	GAL20V8Bas18H4	PLCC 28	PA28PL28D
LATTICE	GAL20V8Bas18L4	PLCC 28	PA28PL28D
LATTICE	GAL20V8Bas18P4	PLCC 28	PA28PL28D
LATTICE	GAL20V8Bas20H2	PLCC 28	PA28PL28D
LATTICE	GAL20V8Bas20L2	PLCC 28	PA28PL28D
LATTICE	GAL20V8Bas20P2	PLCC 28	PA28PL28D
LATTICE	GAL20V8Bas20H8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Bas20L8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Bas20P8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Bas20R4	PLCC 28	PA28PL28D
LATTICE	GAL20V8Bas20R6	PLCC 28	PA28PL28D
LATTICE	GAL20V8Bas20R8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Bas20RP4	PLCC 28	PA28PL28D
LATTICE	GAL20V8Bas20RP6	PLCC 28	PA28PL28D
LATTICE	GAL20V8Bas20RP8	PLCC 28	PA28PL28D
LATTICE	GAL20V8C	DIP 24	
LATTICE	GAL20V8Cas14H8	DIP 24	
LATTICE	GAL20V8Cas14L8	DIP 24	
LATTICE	GAL20V8Cas14P8	DIP 24	
LATTICE	GAL20V8Cas16H6	DIP 24	
LATTICE	GAL20V8Cas16L6	DIP 24	
LATTICE	GAL20V8Cas16P6	DIP 24	
LATTICE	GAL20V8Cas18H4	DIP 24	
LATTICE	GAL20V8Cas18L4	DIP 24	
LATTICE	GAL20V8Cas18P4	DIP 24	
LATTICE	GAL20V8Cas20H2	DIP 24	
LATTICE	GAL20V8Cas20L2	DIP 24	
LATTICE	GAL20V8Cas20P2	DIP 24	
LATTICE	GAL20V8Cas20H8	DIP 24	
LATTICE	GAL20V8Cas20L8	DIP 24	
LATTICE	GAL20V8Cas20P8	DIP 24	
LATTICE	GAL20V8Cas20R4	DIP 24	
LATTICE	GAL20V8Cas20R6	DIP 24	
LATTICE	GAL20V8Cas20R8	DIP 24	
LATTICE	GAL20V8Cas20RP4	DIP 24	
LATTICE	GAL20V8Cas20RP6	DIP 24	
LATTICE	GAL20V8Cas20RP8	DIP 24	
LATTICE	GAL20V8C	PLCC 28	PA28PL28D
LATTICE	GAL20V8Cas14H8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Cas14L8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Cas14P8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Cas16H6	PLCC 28	PA28PL28D
LATTICE	GAL20V8Cas16L6	PLCC 28	PA28PL28D
LATTICE	GAL20V8Cas16P6	PLCC 28	PA28PL28D
LATTICE	GAL20V8Cas18H4	PLCC 28	PA28PL28D
LATTICE	GAL20V8Cas18L4	PLCC 28	PA28PL28D
LATTICE	GAL20V8Cas18P4	PLCC 28	PA28PL28D
LATTICE	GAL20V8Cas20H2	PLCC 28	PA28PL28D
LATTICE	GAL20V8Cas20L2	PLCC 28	PA28PL28D
LATTICE	GAL20V8Cas20P2	PLCC 28	PA28PL28D
LATTICE	GAL20V8Cas20H8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Cas20L8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Cas20P8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Cas20R4	PLCC 28	PA28PL28D
LATTICE	GAL20V8Cas20R6	PLCC 28	PA28PL28D
LATTICE	GAL20V8Cas20R8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Cas20RP4	PLCC 28	PA28PL28D
LATTICE	GAL20V8Cas20RP6	PLCC 28	PA28PL28D
LATTICE	GAL20V8Cas20RP8	PLCC 28	PA28PL28D
LATTICE	GAL20V8D	DIP 24	
LATTICE	GAL20V8Das14H8	DIP 24	
LATTICE	GAL20V8Das14L8	DIP 24	
LATTICE	GAL20V8Das14P8	DIP 24	
LATTICE	GAL20V8Das16H6	DIP 24	
LATTICE	GAL20V8Das16L6	DIP 24	
LATTICE	GAL20V8Das16P6	DIP 24	
LATTICE	GAL20V8Das18H4	DIP 24	

LATTICE	GAL20V8Das18L4	DIP 24	
LATTICE	GAL20V8Das18P4	DIP 24	
LATTICE	GAL20V8Das20H2	DIP 24	
LATTICE	GAL20V8Das20L2	DIP 24	
LATTICE	GAL20V8Das20P2	DIP 24	
LATTICE	GAL20V8Das20H8	DIP 24	
LATTICE	GAL20V8Das20L8	DIP 24	
LATTICE	GAL20V8Das20P8	DIP 24	
LATTICE	GAL20V8Das20R4	DIP 24	
LATTICE	GAL20V8Das20R6	DIP 24	
LATTICE	GAL20V8Das20R8	DIP 24	
LATTICE	GAL20V8Das20RP4	DIP 24	
LATTICE	GAL20V8Das20RP6	DIP 24	
LATTICE	GAL20V8Das20RP8	DIP 24	
LATTICE	GAL20V8D	PLCC 28	PA28PL28D
LATTICE	GAL20V8Das14H8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Das14L8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Das14P8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Das16H6	PLCC 28	PA28PL28D
LATTICE	GAL20V8Das16L6	PLCC 28	PA28PL28D
LATTICE	GAL20V8Das16P6	PLCC 28	PA28PL28D
LATTICE	GAL20V8Das18H4	PLCC 28	PA28PL28D
LATTICE	GAL20V8Das18L4	PLCC 28	PA28PL28D
LATTICE	GAL20V8Das18P4	PLCC 28	PA28PL28D
LATTICE	GAL20V8Das20H2	PLCC 28	PA28PL28D
LATTICE	GAL20V8Das20L2	PLCC 28	PA28PL28D
LATTICE	GAL20V8Das20P2	PLCC 28	PA28PL28D
LATTICE	GAL20V8Das20H8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Das20L8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Das20P8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Das20R4	PLCC 28	PA28PL28D
LATTICE	GAL20V8Das20R6	PLCC 28	PA28PL28D
LATTICE	GAL20V8Das20R8	PLCC 28	PA28PL28D
LATTICE	GAL20V8Das20RP4	PLCC 28	PA28PL28D
LATTICE	GAL20V8Das20RP6	PLCC 28	PA28PL28D
LATTICE	GAL20V8Das20RP8	PLCC 28	PA28PL28D
LATTICE	GAL20LV8C	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Cas14H8	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Cas14L8	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Cas14P8	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Cas16H6	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Cas16L6	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Cas16P6	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Cas18H4	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Cas18L4	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Cas18P4	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Cas20H2	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Cas20L2	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Cas20P2	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Cas20H8	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Cas20L8	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Cas20P8	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Cas20R4	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Cas20R6	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Cas20R8	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Cas20RP4	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Cas20RP6	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Cas20RP8	PLCC 28	PA28PL28D
LATTICE	GAL20LV8D	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Das14H8	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Das14L8	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Das14P8	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Das16H6	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Das16L6	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Das16P6	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Das18H4	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Das18L4	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Das18P4	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Das20H2	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Das20L2	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Das20P2	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Das20H8	PLCC 28	PA28PL28D
LATTICE	GAL20LV8Das20L8	PLCC 28	PA28PL28D



LATTICE	GAL20LV8Z	PLCC 28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas14H8	PLCC 28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas14L8	PLCC 28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas14P8	PLCC 28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas16H6	PLCC 28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas16L6	PLCC 28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas16P6	PLCC 28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas18H4	PLCC 28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas18L4	PLCC 28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas18P4	PLCC 28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas20H2	PLCC 28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas20L2	PLCC 28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas20P2	PLCC 28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas20H8	PLCC 28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas20L8	PLCC 28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas20P8	PLCC 28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas20R4	PLCC 28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas20R6	PLCC 28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas20R8	PLCC 28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas20RP4	PLCC 28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas20RP6	PLCC 28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas20RP8	PLCC 28	PA28PL24D2P6-YA
LATTICE	GAL16VP8B	DIP 20	
LATTICE	GAL16VP8B	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL20VP8B	DIP 24	
LATTICE	GAL20VP8B	PLCC 28	PA28PL28D
LATTICE	GAL18V10	DIP 20	
LATTICE	GAL18V10B	DIP 20	
LATTICE	GAL18V10	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL18V10B	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	GAL20RA10	DIP 24	
LATTICE	GAL20RA10B	DIP 24	
LATTICE	GAL20RA10	PLCC 28	PA28PL28D
LATTICE	GAL20RA10B	PLCC 28	PA28PL28D
LATTICE	GAL20XV10	DIP 24	
LATTICE	GAL20XV10B	DIP 24	
LATTICE	GAL20XV10	PLCC 28	PA28PL28D
LATTICE	GAL20XV10B	PLCC 28	PA28PL28D
LATTICE	GAL22V10	DIP 24	
LATTICE	GAL22V10B	DIP 24	
LATTICE	GAL22V10C	DIP 24	
LATTICE	GAL22V10D	DIP 24	
LATTICE	GAL22V10	PLCC 28	PA28PL28D
LATTICE	GAL22V10B	PLCC 28	PA28PL28D
LATTICE	GAL22V10C	PLCC 28	PA28PL28D
LATTICE	GAL22V10D	PLCC 28	PA28PL28D
LATTICE	GAL22LV10C	PLCC 28	PA28PL28D
LATTICE	GAL22LV10D	PLCC 28	PA28PL28D
LATTICE	GAL22LV10Z	PLCC 28	PA28PL28D
LATTICE	GAL22LV10ZD	PLCC 28	PA28PL28D
LATTICE	GAL26CLV12C	DIP 28	
LATTICE	GAL26CLV12D	DIP 28	
LATTICE	GAL26CLV12Z	DIP 28	
LATTICE	GAL26CLV12ZD	DIP 28	
LATTICE	GAL26CLV12C	PLCC 28	PA28PL28D
LATTICE	GAL26CLV12D	PLCC 28	PA28PL28D
LATTICE	GAL26CLV12Z	PLCC 28	PA28PL28D
LATTICE	GAL26CLV12ZD	PLCC 28	PA28PL28D
LATTICE	GAL26CV12	DIP 28	
LATTICE	GAL26CV12B	DIP 28	
LATTICE	GAL26CV12	PLCC 28	PA28PL28D
LATTICE	GAL26CV12B	PLCC 28	PA28PL28D
LATTICE	GAL26V12C	DIP 28	
LATTICE	GAL26V12C	PLCC 28	PA28PL28D
LATTICE	GAL6001	DIP 24	
LATTICE	GAL6001B	DIP 24	
LATTICE	GAL6002B	DIP 24	
LATTICE	GAL6001	PLCC 28	PA28PL28D
LATTICE	GAL6001B	PLCC 28	PA28PL28D
LATTICE	GAL6002B	PLCC 28	PA28PL28D
LATTICE	ispGAL22LV10	PLCC 28	PA28PL28D
LATTICE	ispGAL22V10	DIP 28	
LATTICE	ispGAL22V10B	DIP 28	

LATTICE	ispGAL22V10C	DIP 28	
LATTICE	ispGAL22V10	PLCC 28	PA28PL28D
LATTICE	ispGAL22V10B	PLCC 28	PA28PL28D
LATTICE	ispGAL22V10C	PLCC 28	PA28PL28D
LATTICE	ispGAL22V10AV	PLCC 28	PA28PL28D
LATTICE	ispGAL22V10AB	PLCC 28	PA28PL28D
LATTICE	ispGAL22V10AC	PLCC 28	PA28PL28D
LATTICE	ispGDS14	DIP 20	
LATTICE	ispGDS14	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	ispGDS18	DIP 24	
LATTICE	ispGDS22	DIP 28	
LATTICE	ispGDS22	PLCC 28	PA28PL28D
LATTICE	ispLSI1016	PLCC 44	PA44-48U
LATTICE	ispLSI1016E	PLCC 44	PA44-48U
LATTICE	ispLSI1032	PLCC 84	AS-84-28-02P-6YAM
LATTICE	ispLSI1032	TQFP 100	PA100TQ28DA
LATTICE	ispLSI1032E	PLCC 84	AS-84-28-02P-6YAM
LATTICE	ispLSI1032E	TQFP 100	PA100TQ28DA
LATTICE	ispLSI2032	PLCC 44	PA44-48U
LATTICE	ispLSI2032A	PLCC 44	PA44-48U
LATTICE	ispLSI2064	PLCC 84	AS-84-28-02P-6YAM
LATTICE	ispLSI2064A	PLCC 84	AS-84-28-02P-6YAM
LATTICE	ispLSI1016EA	PLCC 44	PA44-48U
LATTICE	ispLSI2032V	PLCC 44	PA44-48U
LATTICE	ispLSI2032E	PLCC 44	PA44-48U
LATTICE	ispLSI2032VE	PLCC 44	PA44-48U
LATTICE	ispLSI2192VE	BGA 144	PA144BGA40DA
LATTICE	ispPAC-POWR1014	TQFP 48	HA48TQ48DB
LATTICE	LC4032V	TQFP 48	HA48TQ48D
LATTICE	LC4032V	TQFP 44	PA44QF44D
LATTICE	LC4032B	TQFP 44	PA44QF44D
LATTICE	LC4064V	TQFP 48	HA48TQ48D
LATTICE	LC4064V	TQFP 44	PA44QF44D
LATTICE	LC4064B	TQFP 44	PA44QF44D
LATTICE	LC4064V	TQFP 100	PA100TQ28D-YC
LATTICE	LC4064B	TQFP 100	PA100TQ28D-YC
LATTICE	LC4064C	TQFP 100	PA100TQ28D-YC
LATTICE	LC4128V	TQFP 100	PA100TQ28D-YC
LATTICE	LC4128B	TQFP 100	PA100TQ28D-YC
LATTICE	LC4128C	TQFP 100	PA100TQ28D-YC
LATTICE	LC4128ZC	TQFP 100	PA100TQ28D-YC
LATTICE	LC4128ZC	BGA 132	HA132BG48D
LATTICE	MACH211	PLCC 44	PA-MACH1
LATTICE	MACH211	PLCC 44	PA44-48U
LATTICE	MACH211SP	PLCC 44	PA-MACH1
LATTICE	MACH211SP	PLCC 44	PA44-48U
LATTICE	M4A3-32/32	PLCC 44	PA44-48U
LATTICE	M4A5-32/32	PLCC 44	PA44-48U
LATTICE	M4A3-64/32	PLCC 44	PA44-48U
LATTICE	M4A5-64/32	PLCC 44	PA44-48U
LATTICE	PALCE16V8H	DIP 20	
LATTICE	PALCE16V8Has10H8	DIP 20	
LATTICE	PALCE16V8Has10L8	DIP 20	
LATTICE	PALCE16V8Has10P8	DIP 20	
LATTICE	PALCE16V8Has12H6	DIP 20	
LATTICE	PALCE16V8Has12L6	DIP 20	
LATTICE	PALCE16V8Has12P6	DIP 20	
LATTICE	PALCE16V8Has14H4	DIP 20	
LATTICE	PALCE16V8Has14L4	DIP 20	
LATTICE	PALCE16V8Has14P4	DIP 20	
LATTICE	PALCE16V8Has16H2	DIP 20	
LATTICE	PALCE16V8Has16L2	DIP 20	
LATTICE	PALCE16V8Has16P2	DIP 20	
LATTICE	PALCE16V8Has16H8	DIP 20	
LATTICE	PALCE16V8Has16L8	DIP 20	
LATTICE	PALCE16V8Has16P8	DIP 20	
LATTICE	PALCE16V8Has16R4	DIP 20	
LATTICE	PALCE16V8Has16R6	DIP 20	
LATTICE	PALCE16V8Has16R8	DIP 20	
LATTICE	PALCE16V8Has16RP4	DIP 20	
LATTICE	PALCE16V8Has16RP6	DIP 20	
LATTICE	PALCE16V8Has16RP8	DIP 20	
LATTICE	PALCE16V8H	PLCC 20	PA20LC20D[Dead Bug]



LATTICE	PALCE16V8Qas14L4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas14P4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas16H2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas16L2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas16P2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas16H8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas16L8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas16P8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas16R4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas16R6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas16R8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas16RP4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas16RP6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas16RP8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Q	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas10H8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas10L8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas10P8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas12H6	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas12L6	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas12P6	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas14H4	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas14L4	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas14P4	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas16H2	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas16L2	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas16P2	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas16H8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas16L8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas16P8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas16R4	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas16R6	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas16R8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas16RP4	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas16RP6	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas16RP8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Z	DIP 20	
LATTICE	PALCE16V8Zas10H8	DIP 20	
LATTICE	PALCE16V8Zas10L8	DIP 20	
LATTICE	PALCE16V8Zas10P8	DIP 20	
LATTICE	PALCE16V8Zas12H6	DIP 20	
LATTICE	PALCE16V8Zas12L6	DIP 20	
LATTICE	PALCE16V8Zas12P6	DIP 20	
LATTICE	PALCE16V8Zas14H4	DIP 20	
LATTICE	PALCE16V8Zas14L4	DIP 20	
LATTICE	PALCE16V8Zas14P4	DIP 20	
LATTICE	PALCE16V8Zas16H2	DIP 20	
LATTICE	PALCE16V8Zas16L2	DIP 20	
LATTICE	PALCE16V8Zas16P2	DIP 20	
LATTICE	PALCE16V8Zas16H8	DIP 20	
LATTICE	PALCE16V8Zas16L8	DIP 20	
LATTICE	PALCE16V8Zas16P8	DIP 20	
LATTICE	PALCE16V8Zas16R4	DIP 20	
LATTICE	PALCE16V8Zas16R6	DIP 20	
LATTICE	PALCE16V8Zas16R8	DIP 20	
LATTICE	PALCE16V8Zas16RP4	DIP 20	
LATTICE	PALCE16V8Zas16RP6	DIP 20	
LATTICE	PALCE16V8Zas16RP8	DIP 20	
LATTICE	PALCE16V8Z	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas10H8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas10L8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas10P8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas12H6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas12L6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas12P6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas14H4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas14L4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas14P4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas16H2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas16L2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas16P2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas16H8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas16L8	PLCC 20	PA20LC20D[Dead Bug]



LATTICE	PALCE16V8Zas16P8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas16R4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas16R6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas16R8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas16RP4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas16RP6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas16RP8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Z	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas10H8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas10L8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas10P8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas12H6	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas12L6	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas12P6	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas14H4	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas14L4	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas14P4	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas16H2	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas16L2	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas16P2	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas16H8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas16L8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas16P8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas16R4	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas16R6	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas16R8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas16RP4	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas16RP6	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas16RP8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALCE20V8H-25	DIP 24	
LATTICE	PALCE20V8H-25as14H8	DIP 24	
LATTICE	PALCE20V8H-25as14L8	DIP 24	
LATTICE	PALCE20V8H-25as14P8	DIP 24	
LATTICE	PALCE20V8H-25as16H6	DIP 24	
LATTICE	PALCE20V8H-25as16L6	DIP 24	
LATTICE	PALCE20V8H-25as16P6	DIP 24	
LATTICE	PALCE20V8H-25as18H4	DIP 24	
LATTICE	PALCE20V8H-25as18L4	DIP 24	
LATTICE	PALCE20V8H-25as18P4	DIP 24	
LATTICE	PALCE20V8H-25as20H2	DIP 24	
LATTICE	PALCE20V8H-25as20L2	DIP 24	
LATTICE	PALCE20V8H-25as20P2	DIP 24	
LATTICE	PALCE20V8H-25as20H8	DIP 24	
LATTICE	PALCE20V8H-25as20L8	DIP 24	
LATTICE	PALCE20V8H-25as20P8	DIP 24	
LATTICE	PALCE20V8H-25as20R4	DIP 24	
LATTICE	PALCE20V8H-25as20R6	DIP 24	
LATTICE	PALCE20V8H-25as20R8	DIP 24	
LATTICE	PALCE20V8H-25as20RP4	DIP 24	
LATTICE	PALCE20V8H-25as20RP6	DIP 24	
LATTICE	PALCE20V8H-25as20RP8	DIP 24	
LATTICE	PALCE20V8H-25	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25as14H8	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25as14L8	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25as14P8	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25as16H6	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25as16L6	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25as16P6	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25as18H4	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25as18L4	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25as18P4	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25as20H2	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25as20L2	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25as20P2	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25as20H8	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25as20L8	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25as20P8	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25as20R4	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25as20R6	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25as20R8	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25as20RP4	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25as20RP6	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25as20RP8	PLCC 28	PA28PL28D



LATTICE	PALCE20V8H-15/4as18H4	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-15/4as18L4	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-15/4as18P4	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-15/4as20H2	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-15/4as20L2	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-15/4as20P2	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-15/4as20H8	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-15/4as20L8	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-15/4as20P8	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-15/4as20R4	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-15/4as20R6	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-15/4as20R8	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-15/4as20RP4	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-15/4as20RP6	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-15/4as20RP8	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25/4	DIP 24	
LATTICE	PALCE20V8H-25/4as14H8	DIP 24	
LATTICE	PALCE20V8H-25/4as14L8	DIP 24	
LATTICE	PALCE20V8H-25/4as14P8	DIP 24	
LATTICE	PALCE20V8H-25/4as16H6	DIP 24	
LATTICE	PALCE20V8H-25/4as16L6	DIP 24	
LATTICE	PALCE20V8H-25/4as16P6	DIP 24	
LATTICE	PALCE20V8H-25/4as18H4	DIP 24	
LATTICE	PALCE20V8H-25/4as18L4	DIP 24	
LATTICE	PALCE20V8H-25/4as18P4	DIP 24	
LATTICE	PALCE20V8H-25/4as20H2	DIP 24	
LATTICE	PALCE20V8H-25/4as20L2	DIP 24	
LATTICE	PALCE20V8H-25/4as20P2	DIP 24	
LATTICE	PALCE20V8H-25/4as20H8	DIP 24	
LATTICE	PALCE20V8H-25/4as20L8	DIP 24	
LATTICE	PALCE20V8H-25/4as20P8	DIP 24	
LATTICE	PALCE20V8H-25/4as20R4	DIP 24	
LATTICE	PALCE20V8H-25/4as20R6	DIP 24	
LATTICE	PALCE20V8H-25/4as20R8	DIP 24	
LATTICE	PALCE20V8H-25/4as20RP4	DIP 24	
LATTICE	PALCE20V8H-25/4as20RP6	DIP 24	
LATTICE	PALCE20V8H-25/4as20RP8	DIP 24	
LATTICE	PALCE20V8H-25/4	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25/4as14H8	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25/4as14L8	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25/4as14P8	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25/4as16H6	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25/4as16L6	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25/4as16P6	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25/4as18H4	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25/4as18L4	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25/4as18P4	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25/4as20H2	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25/4as20L2	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25/4as20P2	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25/4as20H8	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25/4as20L8	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25/4as20P8	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25/4as20R4	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25/4as20R6	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25/4as20R8	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25/4as20RP4	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25/4as20RP6	PLCC 28	PA28PL28D
LATTICE	PALCE20V8H-25/4as20RP8	PLCC 28	PA28PL28D
LATTICE	PALCE20V8Q-15/4	DIP 24	
LATTICE	PALCE20V8Q-15/4as14H8	DIP 24	
LATTICE	PALCE20V8Q-15/4as14L8	DIP 24	
LATTICE	PALCE20V8Q-15/4as14P8	DIP 24	
LATTICE	PALCE20V8Q-15/4as16H6	DIP 24	
LATTICE	PALCE20V8Q-15/4as16L6	DIP 24	
LATTICE	PALCE20V8Q-15/4as16P6	DIP 24	
LATTICE	PALCE20V8Q-15/4as18H4	DIP 24	
LATTICE	PALCE20V8Q-15/4as18L4	DIP 24	
LATTICE	PALCE20V8Q-15/4as18P4	DIP 24	
LATTICE	PALCE20V8Q-15/4as20H2	DIP 24	
LATTICE	PALCE20V8Q-15/4as20L2	DIP 24	
LATTICE	PALCE20V8Q-15/4as20P2	DIP 24	
LATTICE	PALCE20V8Q-15/4as20H8	DIP 24	



LATTICE	PALCE20V8Q-25/4as20RP8	PLCC 28	PA28PL28D
LATTICE	PALLV16V8	DIP 20	
LATTICE	PALLV16V8as10H8	DIP 20	
LATTICE	PALLV16V8as10L8	DIP 20	
LATTICE	PALLV16V8as10P8	DIP 20	
LATTICE	PALLV16V8as12H6	DIP 20	
LATTICE	PALLV16V8as12L6	DIP 20	
LATTICE	PALLV16V8as12P6	DIP 20	
LATTICE	PALLV16V8as14H4	DIP 20	
LATTICE	PALLV16V8as14L4	DIP 20	
LATTICE	PALLV16V8as14P4	DIP 20	
LATTICE	PALLV16V8as16H2	DIP 20	
LATTICE	PALLV16V8as16L2	DIP 20	
LATTICE	PALLV16V8as16P2	DIP 20	
LATTICE	PALLV16V8as16H8	DIP 20	
LATTICE	PALLV16V8as16L8	DIP 20	
LATTICE	PALLV16V8as16P8	DIP 20	
LATTICE	PALLV16V8as16R4	DIP 20	
LATTICE	PALLV16V8as16R6	DIP 20	
LATTICE	PALLV16V8as16R8	DIP 20	
LATTICE	PALLV16V8as16RP4	DIP 20	
LATTICE	PALLV16V8as16RP6	DIP 20	
LATTICE	PALLV16V8as16RP8	DIP 20	
LATTICE	PALLV16V8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as10H8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as10L8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as10P8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as12H6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as12L6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as12P6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as14H4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as14L4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as14P4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as16H2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as16L2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as16P2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as16H8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as16L8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as16P8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as16R4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as16R6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as16R8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as16RP4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as16RP6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as16RP8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8as10H8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8as10L8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8as10P8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8as12H6	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8as12L6	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8as12P6	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8as14H4	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8as14L4	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8as14P4	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8as16H2	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8as16L2	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8as16P2	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8as16H8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8as16L8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8as16P8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8as16R4	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8as16R6	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8as16R8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8as16RP4	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8as16RP6	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8as16RP8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8Z	DIP 20	
LATTICE	PALLV16V8Zas10H8	DIP 20	
LATTICE	PALLV16V8Zas10L8	DIP 20	
LATTICE	PALLV16V8Zas10P8	DIP 20	
LATTICE	PALLV16V8Zas12H6	DIP 20	
LATTICE	PALLV16V8Zas12L6	DIP 20	

LATTICE	PALLV16V8Zas12P6	DIP 20	
LATTICE	PALLV16V8Zas14H4	DIP 20	
LATTICE	PALLV16V8Zas14L4	DIP 20	
LATTICE	PALLV16V8Zas14P4	DIP 20	
LATTICE	PALLV16V8Zas16H2	DIP 20	
LATTICE	PALLV16V8Zas16L2	DIP 20	
LATTICE	PALLV16V8Zas16P2	DIP 20	
LATTICE	PALLV16V8Zas16H8	DIP 20	
LATTICE	PALLV16V8Zas16L8	DIP 20	
LATTICE	PALLV16V8Zas16P8	DIP 20	
LATTICE	PALLV16V8Zas16R4	DIP 20	
LATTICE	PALLV16V8Zas16R6	DIP 20	
LATTICE	PALLV16V8Zas16R8	DIP 20	
LATTICE	PALLV16V8Zas16RP4	DIP 20	
LATTICE	PALLV16V8Zas16RP6	DIP 20	
LATTICE	PALLV16V8Zas16RP8	DIP 20	
LATTICE	PALLV16V8Z	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas10H8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas10L8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas10P8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas12H6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas12L6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas12P6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas14H4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas14L4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas14P4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas16H2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas16L2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas16P2	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas16H8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas16L8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas16P8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas16R4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas16R6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas16R8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas16RP4	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas16RP6	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas16RP8	PLCC 20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Z	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas10H8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas10L8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas10P8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas12H6	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas12L6	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas12P6	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas14H4	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas14L4	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas14P4	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas16H2	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas16L2	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas16P2	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas16H8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas16L8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas16P8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas16R4	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas16R6	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas16R8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas16RP4	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas16RP6	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas16RP8	SOIC 20	PA20SO20D-EO-210
LATTICE	PALLV22V10	DIP 24	
LATTICE	PALLV22V10	PLCC 28	PA28PL28D
LATTICE	PALLV22V10Z	DIP 24	
LATTICE	PALLV22V10Z	PLCC 28	PA28PL28D
LATTICE	PALCE22V10H	DIP 24	
LATTICE	PALCE22V10H	PLCC 28	PA28PL28D
LATTICE	PALCE22V10Q	DIP 24	
LATTICE	PALCE22V10Q	PLCC 28	PA28PL28D
LATTICE	PALCE22V10Z	DIP 24	
LATTICE	PALCE22V10Z	PLCC 28	PA28PL28D
LATTICE	PALCE20RA10H	DIP 24	
LATTICE	PALCE20RA10H	PLCC 28	PA28PL28D
LATTICE	PALCE20RA10Q	DIP 24	

LATTICE	PALCE20RA10Q	PLCC 28	PA28PL28D
LATTICE	PALCE26V12H	DIP 28	
LATTICE	PALCE26V12H	PLCC 28	PA28PL28D
LATTICE	PALCE26V12H/4	DIP 28	
LATTICE	PALCE26V12H/4	PLCC 28	PA28PL28D
LATTICE	PALCE26V12H/4-10	DIP 28	
LATTICE	PALCE26V12H/4-10	PLCC 28	PA28PL28D
LATTICE	PALCE610H	DIP 24	
LATTICE	PALCE610H	PLCC 28	PA28PL28D
LATTICE	PALCE29M16H	DIP 24	
LATTICE	PALCE29M16H	PLCC 28	PA28PL28D
LATTICE	PALCE29MA16H	DIP 24	
LATTICE	PALCE29MA16H	PLCC 28	PA28PL28D
NATIONAL	GAL16V8	DIP 20	
NATIONAL	GAL16V8QS	DIP 20	
NATIONAL	GAL16V8as10H8	DIP 20	
NATIONAL	GAL16V8as10L8	DIP 20	
NATIONAL	GAL16V8as10P8	DIP 20	
NATIONAL	GAL16V8as12H6	DIP 20	
NATIONAL	GAL16V8as12L6	DIP 20	
NATIONAL	GAL16V8as12P6	DIP 20	
NATIONAL	GAL16V8as14H4	DIP 20	
NATIONAL	GAL16V8as14L4	DIP 20	
NATIONAL	GAL16V8as14P4	DIP 20	
NATIONAL	GAL16V8as16H2	DIP 20	
NATIONAL	GAL16V8as16L2	DIP 20	
NATIONAL	GAL16V8as16P2	DIP 20	
NATIONAL	GAL16V8as16H8	DIP 20	
NATIONAL	GAL16V8as16L8	DIP 20	
NATIONAL	GAL16V8as16P8	DIP 20	
NATIONAL	GAL16V8as16R4	DIP 20	
NATIONAL	GAL16V8as16R6	DIP 20	
NATIONAL	GAL16V8as16R8	DIP 20	
NATIONAL	GAL16V8as16RP4	DIP 20	
NATIONAL	GAL16V8as16RP6	DIP 20	
NATIONAL	GAL16V8as16RP8	DIP 20	
NATIONAL	GAL16V8	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as10H8	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as10L8	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as10P8	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as12H6	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as12L6	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as12P6	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as14H4	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as14L4	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as14P4	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as16H2	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as16L2	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as16P2	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as16H8	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as16L8	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as16P8	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as16R4	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as16R6	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as16R8	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as16RP4	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as16RP6	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as16RP8	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8A	DIP 20	
NATIONAL	GAL16V8Aas10H8	DIP 20	
NATIONAL	GAL16V8Aas10L8	DIP 20	
NATIONAL	GAL16V8Aas10P8	DIP 20	
NATIONAL	GAL16V8Aas12H6	DIP 20	
NATIONAL	GAL16V8Aas12L6	DIP 20	
NATIONAL	GAL16V8Aas12P6	DIP 20	
NATIONAL	GAL16V8Aas14H4	DIP 20	
NATIONAL	GAL16V8Aas14L4	DIP 20	
NATIONAL	GAL16V8Aas14P4	DIP 20	
NATIONAL	GAL16V8Aas16H2	DIP 20	
NATIONAL	GAL16V8Aas16L2	DIP 20	
NATIONAL	GAL16V8Aas16P2	DIP 20	
NATIONAL	GAL16V8Aas16H8	DIP 20	
NATIONAL	GAL16V8Aas16L8	DIP 20	

NATIONAL	GAL16V8Aas16P8	DIP 20	
NATIONAL	GAL16V8Aas16R4	DIP 20	
NATIONAL	GAL16V8Aas16R6	DIP 20	
NATIONAL	GAL16V8Aas16R8	DIP 20	
NATIONAL	GAL16V8Aas16RP4	DIP 20	
NATIONAL	GAL16V8Aas16RP6	DIP 20	
NATIONAL	GAL16V8Aas16RP8	DIP 20	
NATIONAL	GAL16V8A	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas10H8	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas10L8	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas10P8	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas12H6	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas12L6	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas12P6	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas14H4	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas14L4	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas14P4	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas16H2	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas16L2	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas16P2	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas16H8	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas16L8	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas16P8	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas16R4	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas16R6	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas16R8	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas16RP4	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas16RP6	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas16RP8	PLCC 20	PA20LC20D[Dead Bug]
NATIONAL	GAL20V8	DIP 24	
NATIONAL	GAL20V8as14H8	DIP 24	
NATIONAL	GAL20V8as14L8	DIP 24	
NATIONAL	GAL20V8as14P8	DIP 24	
NATIONAL	GAL20V8as16H6	DIP 24	
NATIONAL	GAL20V8as16L6	DIP 24	
NATIONAL	GAL20V8as16P6	DIP 24	
NATIONAL	GAL20V8as18H4	DIP 24	
NATIONAL	GAL20V8as18L4	DIP 24	
NATIONAL	GAL20V8as18P4	DIP 24	
NATIONAL	GAL20V8as20H2	DIP 24	
NATIONAL	GAL20V8as20L2	DIP 24	
NATIONAL	GAL20V8as20P2	DIP 24	
NATIONAL	GAL20V8as20H8	DIP 24	
NATIONAL	GAL20V8as20L8	DIP 24	
NATIONAL	GAL20V8as20P8	DIP 24	
NATIONAL	GAL20V8as20R4	DIP 24	
NATIONAL	GAL20V8as20R6	DIP 24	
NATIONAL	GAL20V8as20R8	DIP 24	
NATIONAL	GAL20V8as20RP4	DIP 24	
NATIONAL	GAL20V8as20RP6	DIP 24	
NATIONAL	GAL20V8as20RP8	DIP 24	
NATIONAL	GAL20V8	PLCC 28	PA28PL28D
NATIONAL	GAL20V8as14H8	PLCC 28	PA28PL28D
NATIONAL	GAL20V8as14L8	PLCC 28	PA28PL28D
NATIONAL	GAL20V8as14P8	PLCC 28	PA28PL28D
NATIONAL	GAL20V8as16H6	PLCC 28	PA28PL28D
NATIONAL	GAL20V8as16L6	PLCC 28	PA28PL28D
NATIONAL	GAL20V8as16P6	PLCC 28	PA28PL28D
NATIONAL	GAL20V8as18H4	PLCC 28	PA28PL28D
NATIONAL	GAL20V8as18L4	PLCC 28	PA28PL28D
NATIONAL	GAL20V8as18P4	PLCC 28	PA28PL28D
NATIONAL	GAL20V8as20H2	PLCC 28	PA28PL28D
NATIONAL	GAL20V8as20L2	PLCC 28	PA28PL28D
NATIONAL	GAL20V8as20P2	PLCC 28	PA28PL28D
NATIONAL	GAL20V8as20H8	PLCC 28	PA28PL28D
NATIONAL	GAL20V8as20L8	PLCC 28	PA28PL28D
NATIONAL	GAL20V8as20P8	PLCC 28	PA28PL28D
NATIONAL	GAL20V8as20R4	PLCC 28	PA28PL28D
NATIONAL	GAL20V8as20R6	PLCC 28	PA28PL28D
NATIONAL	GAL20V8as20R8	PLCC 28	PA28PL28D
NATIONAL	GAL20V8as20RP4	PLCC 28	PA28PL28D
NATIONAL	GAL20V8as20RP6	PLCC 28	PA28PL28D
NATIONAL	GAL20V8as20RP8	PLCC 28	PA28PL28D



NATIONAL	GAL20V8A	DIP 24	
NATIONAL	GAL20V8Aas14H8	DIP 24	
NATIONAL	GAL20V8Aas14L8	DIP 24	
NATIONAL	GAL20V8Aas14P8	DIP 24	
NATIONAL	GAL20V8Aas16H6	DIP 24	
NATIONAL	GAL20V8Aas16L6	DIP 24	
NATIONAL	GAL20V8Aas16P6	DIP 24	
NATIONAL	GAL20V8Aas18H4	DIP 24	
NATIONAL	GAL20V8Aas18L4	DIP 24	
NATIONAL	GAL20V8Aas18P4	DIP 24	
NATIONAL	GAL20V8Aas20H2	DIP 24	
NATIONAL	GAL20V8Aas20L2	DIP 24	
NATIONAL	GAL20V8Aas20P2	DIP 24	
NATIONAL	GAL20V8Aas20H8	DIP 24	
NATIONAL	GAL20V8Aas20L8	DIP 24	
NATIONAL	GAL20V8Aas20P8	DIP 24	
NATIONAL	GAL20V8Aas20R4	DIP 24	
NATIONAL	GAL20V8Aas20R6	DIP 24	
NATIONAL	GAL20V8Aas20R8	DIP 24	
NATIONAL	GAL20V8Aas20RP4	DIP 24	
NATIONAL	GAL20V8Aas20RP6	DIP 24	
NATIONAL	GAL20V8Aas20RP8	DIP 24	
NATIONAL	GAL20V8A	PLCC 28	PA28PL28D
NATIONAL	GAL20V8Aas14H8	PLCC 28	PA28PL28D
NATIONAL	GAL20V8Aas14L8	PLCC 28	PA28PL28D
NATIONAL	GAL20V8Aas14P8	PLCC 28	PA28PL28D
NATIONAL	GAL20V8Aas16H6	PLCC 28	PA28PL28D
NATIONAL	GAL20V8Aas16L6	PLCC 28	PA28PL28D
NATIONAL	GAL20V8Aas16P6	PLCC 28	PA28PL28D
NATIONAL	GAL20V8Aas18H4	PLCC 28	PA28PL28D
NATIONAL	GAL20V8Aas18L4	PLCC 28	PA28PL28D
NATIONAL	GAL20V8Aas18P4	PLCC 28	PA28PL28D
NATIONAL	GAL20V8Aas20H2	PLCC 28	PA28PL28D
NATIONAL	GAL20V8Aas20L2	PLCC 28	PA28PL28D
NATIONAL	GAL20V8Aas20P2	PLCC 28	PA28PL28D
NATIONAL	GAL20V8Aas20H8	PLCC 28	PA28PL28D
NATIONAL	GAL20V8Aas20L8	PLCC 28	PA28PL28D
NATIONAL	GAL20V8Aas20P8	PLCC 28	PA28PL28D
NATIONAL	GAL20V8Aas20R4	PLCC 28	PA28PL28D
NATIONAL	GAL20V8Aas20R6	PLCC 28	PA28PL28D
NATIONAL	GAL20V8Aas20R8	PLCC 28	PA28PL28D
NATIONAL	GAL20V8Aas20RP4	PLCC 28	PA28PL28D
NATIONAL	GAL20V8Aas20RP6	PLCC 28	PA28PL28D
NATIONAL	GAL20V8Aas20RP8	PLCC 28	PA28PL28D
NATIONAL	GAL20RA10	DIP 24	
NATIONAL	GAL20RA10	PLCC 28	PA28PL28D
NATIONAL	GAL22V10	DIP 24	
NATIONAL	GAL22V10	PLCC 28	PA28PL28D
NATIONAL	GAL6001	DIP 24	
NATIONAL	GAL6001	PLCC 28	PA28PL28D
SAMSUNG	CPL16L8	DIP 20	
SAMSUNG	CPL16R4	DIP 20	
SAMSUNG	CPL16R6	DIP 20	
SAMSUNG	CPL16R8	DIP 20	
SAMSUNG	CPL16L8L	DIP 20	
SAMSUNG	CPL16R4L	DIP 20	
SAMSUNG	CPL16R6L	DIP 20	
SAMSUNG	CPL16R8L	DIP 20	
SAMSUNG	CPL16L8	PLCC 20	PA20LC20D[Dead Bug]
SAMSUNG	CPL16R4	PLCC 20	PA20LC20D[Dead Bug]
SAMSUNG	CPL16R6	PLCC 20	PA20LC20D[Dead Bug]
SAMSUNG	CPL16R8	PLCC 20	PA20LC20D[Dead Bug]
SAMSUNG	CPL16L8L	PLCC 20	PA20LC20D[Dead Bug]
SAMSUNG	CPL16R4L	PLCC 20	PA20LC20D[Dead Bug]
SAMSUNG	CPL16R6L	PLCC 20	PA20LC20D[Dead Bug]
SAMSUNG	CPL16R8L	PLCC 20	PA20LC20D[Dead Bug]
SAMSUNG	CPL20L8	DIP 24	
SAMSUNG	CPL20R4	DIP 24	
SAMSUNG	CPL20R6	DIP 24	
SAMSUNG	CPL20R8	DIP 24	
SAMSUNG	CPL20L8	PLCC 28	PA28PL24D2P6-YA
SAMSUNG	CPL20R4	PLCC 28	PA28PL24D2P6-YA
SAMSUNG	CPL20R6	PLCC 28	PA28PL24D2P6-YA

SAMSUNG	CPL20R8	PLCC 28	PA28PL24D2P6-YA
SAMSUNG	CPL20L10	DIP 24	
SAMSUNG	CPL20L10	PLCC 28	PA28PL24D2P6-YA
SAMSUNG	CPL22V10	DIP 24	
SAMSUNG	CPL22V10	PLCC 28	PA28PL24D2P6-YA
ST	GAL16V8	DIP 20	
ST	GAL16V8as10H8	DIP 20	
ST	GAL16V8as10L8	DIP 20	
ST	GAL16V8as10P8	DIP 20	
ST	GAL16V8as12H6	DIP 20	
ST	GAL16V8as12L6	DIP 20	
ST	GAL16V8as12P6	DIP 20	
ST	GAL16V8as14H4	DIP 20	
ST	GAL16V8as14L4	DIP 20	
ST	GAL16V8as14P4	DIP 20	
ST	GAL16V8as16H2	DIP 20	
ST	GAL16V8as16L2	DIP 20	
ST	GAL16V8as16P2	DIP 20	
ST	GAL16V8as16H8	DIP 20	
ST	GAL16V8as16L8	DIP 20	
ST	GAL16V8as16P8	DIP 20	
ST	GAL16V8as16R4	DIP 20	
ST	GAL16V8as16R6	DIP 20	
ST	GAL16V8as16R8	DIP 20	
ST	GAL16V8as16RP4	DIP 20	
ST	GAL16V8as16RP6	DIP 20	
ST	GAL16V8as16RP8	DIP 20	
ST	GAL16V8	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8as10H8	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8as10L8	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8as10P8	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8as12H6	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8as12L6	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8as12P6	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8as14H4	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8as14L4	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8as14P4	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8as16H2	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8as16L2	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8as16P2	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8as16H8	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8as16L8	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8as16P8	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8as16R4	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8as16R6	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8as16R8	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8as16RP4	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8as16RP6	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8as16RP8	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8A	DIP 20	
ST	GAL16V8Aas10H8	DIP 20	
ST	GAL16V8Aas10L8	DIP 20	
ST	GAL16V8Aas10P8	DIP 20	
ST	GAL16V8Aas12H6	DIP 20	
ST	GAL16V8Aas12L6	DIP 20	
ST	GAL16V8Aas12P6	DIP 20	
ST	GAL16V8Aas14H4	DIP 20	
ST	GAL16V8Aas14L4	DIP 20	
ST	GAL16V8Aas14P4	DIP 20	
ST	GAL16V8Aas16H2	DIP 20	
ST	GAL16V8Aas16L2	DIP 20	
ST	GAL16V8Aas16P2	DIP 20	
ST	GAL16V8Aas16H8	DIP 20	
ST	GAL16V8Aas16L8	DIP 20	
ST	GAL16V8Aas16P8	DIP 20	
ST	GAL16V8Aas16R4	DIP 20	
ST	GAL16V8Aas16R6	DIP 20	
ST	GAL16V8Aas16R8	DIP 20	
ST	GAL16V8Aas16RP4	DIP 20	
ST	GAL16V8Aas16RP6	DIP 20	
ST	GAL16V8Aas16RP8	DIP 20	
ST	GAL16V8A	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas10H8	PLCC 20	PA20LC20D[Dead Bug]

ST	GAL16V8Aas10L8	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas10P8	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas12H6	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas12L6	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas12P6	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas14H4	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas14L4	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas14P4	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas16H2	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas16L2	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas16P2	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas16H8	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas16L8	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas16P8	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas16R4	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas16R6	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas16R8	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas16RP4	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas16RP6	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas16RP8	PLCC 20	PA20LC20D[Dead Bug]
ST	GAL20V8	DIP 24	
ST	GAL20V8as14H8	DIP 24	
ST	GAL20V8as14L8	DIP 24	
ST	GAL20V8as14P8	DIP 24	
ST	GAL20V8as16H6	DIP 24	
ST	GAL20V8as16L6	DIP 24	
ST	GAL20V8as16P6	DIP 24	
ST	GAL20V8as18H4	DIP 24	
ST	GAL20V8as18L4	DIP 24	
ST	GAL20V8as18P4	DIP 24	
ST	GAL20V8as20H2	DIP 24	
ST	GAL20V8as20L2	DIP 24	
ST	GAL20V8as20P2	DIP 24	
ST	GAL20V8as20H8	DIP 24	
ST	GAL20V8as20L8	DIP 24	
ST	GAL20V8as20P8	DIP 24	
ST	GAL20V8as20R4	DIP 24	
ST	GAL20V8as20R6	DIP 24	
ST	GAL20V8as20R8	DIP 24	
ST	GAL20V8as20RP4	DIP 24	
ST	GAL20V8as20RP6	DIP 24	
ST	GAL20V8as20RP8	DIP 24	
ST	GAL20V8	PLCC 28	PA28PL28D
ST	GAL20V8as14H8	PLCC 28	PA28PL28D
ST	GAL20V8as14L8	PLCC 28	PA28PL28D
ST	GAL20V8as14P8	PLCC 28	PA28PL28D
ST	GAL20V8as16H6	PLCC 28	PA28PL28D
ST	GAL20V8as16L6	PLCC 28	PA28PL28D
ST	GAL20V8as16P6	PLCC 28	PA28PL28D
ST	GAL20V8as18H4	PLCC 28	PA28PL28D
ST	GAL20V8as18L4	PLCC 28	PA28PL28D
ST	GAL20V8as18P4	PLCC 28	PA28PL28D
ST	GAL20V8as20H2	PLCC 28	PA28PL28D
ST	GAL20V8as20L2	PLCC 28	PA28PL28D
ST	GAL20V8as20P2	PLCC 28	PA28PL28D
ST	GAL20V8as20H8	PLCC 28	PA28PL28D
ST	GAL20V8as20L8	PLCC 28	PA28PL28D
ST	GAL20V8as20P8	PLCC 28	PA28PL28D
ST	GAL20V8as20R4	PLCC 28	PA28PL28D
ST	GAL20V8as20R6	PLCC 28	PA28PL28D
ST	GAL20V8as20R8	PLCC 28	PA28PL28D
ST	GAL20V8as20RP4	PLCC 28	PA28PL28D
ST	GAL20V8as20RP6	PLCC 28	PA28PL28D
ST	GAL20V8as20RP8	PLCC 28	PA28PL28D
ST	GAL20V8A	DIP 24	
ST	GAL20V8Aas14H8	DIP 24	
ST	GAL20V8Aas14L8	DIP 24	
ST	GAL20V8Aas14P8	DIP 24	
ST	GAL20V8Aas16H6	DIP 24	
ST	GAL20V8Aas16L6	DIP 24	
ST	GAL20V8Aas16P6	DIP 24	
ST	GAL20V8Aas18H4	DIP 24	
ST	GAL20V8Aas18L4	DIP 24	

ST	GAL20V8Aas18P4	DIP 24	
ST	GAL20V8Aas20H2	DIP 24	
ST	GAL20V8Aas20L2	DIP 24	
ST	GAL20V8Aas20P2	DIP 24	
ST	GAL20V8Aas20H8	DIP 24	
ST	GAL20V8Aas20L8	DIP 24	
ST	GAL20V8Aas20P8	DIP 24	
ST	GAL20V8Aas20R4	DIP 24	
ST	GAL20V8Aas20R6	DIP 24	
ST	GAL20V8Aas20R8	DIP 24	
ST	GAL20V8Aas20RP4	DIP 24	
ST	GAL20V8Aas20RP6	DIP 24	
ST	GAL20V8Aas20RP8	DIP 24	
ST	GAL20V8A	PLCC 28	PA28PL28D
ST	GAL20V8Aas14H8	PLCC 28	PA28PL28D
ST	GAL20V8Aas14L8	PLCC 28	PA28PL28D
ST	GAL20V8Aas14P8	PLCC 28	PA28PL28D
ST	GAL20V8Aas16H6	PLCC 28	PA28PL28D
ST	GAL20V8Aas16L6	PLCC 28	PA28PL28D
ST	GAL20V8Aas16P6	PLCC 28	PA28PL28D
ST	GAL20V8Aas18H4	PLCC 28	PA28PL28D
ST	GAL20V8Aas18L4	PLCC 28	PA28PL28D
ST	GAL20V8Aas18P4	PLCC 28	PA28PL28D
ST	GAL20V8Aas20H2	PLCC 28	PA28PL28D
ST	GAL20V8Aas20L2	PLCC 28	PA28PL28D
ST	GAL20V8Aas20P2	PLCC 28	PA28PL28D
ST	GAL20V8Aas20H8	PLCC 28	PA28PL28D
ST	GAL20V8Aas20L8	PLCC 28	PA28PL28D
ST	GAL20V8Aas20P8	PLCC 28	PA28PL28D
ST	GAL20V8Aas20R4	PLCC 28	PA28PL28D
ST	GAL20V8Aas20R6	PLCC 28	PA28PL28D
ST	GAL20V8Aas20R8	PLCC 28	PA28PL28D
ST	GAL20V8Aas20RP4	PLCC 28	PA28PL28D
ST	GAL20V8Aas20RP6	PLCC 28	PA28PL28D
ST	GAL20V8Aas20RP8	PLCC 28	PA28PL28D
ST	GAL6001	DIP 24	
ST	GAL6001	PLCC 28	PA28PL28D
SIGNETICS(PHILIPS)	PLC18V8Z	DIP 20	
SIGNETICS(PHILIPS)	PLC18V8Z	PLCC 20	PA20LC20D[Dead Bug]
PHILIPS	P3Z22V10	DIP 24	
PHILIPS	P3Z22V10	PLCC 28	PA28PL28D
PHILIPS	P5Z22V10	DIP 24	
PHILIPS	P5Z22V10	PLCC 28	PA28PL28D
PHILIPS	PZ3032	PLCC 44	PA44-48U
PHILIPS	PZ3032	TQFP 44	PA44QF44D
PHILIPS	PZ5032	PLCC 44	PA44-48U
PHILIPS	PZ5032	TQFP 44	PA44QF44D
TEXAS INSTRUMENTS	TICPAL16L8-55	DIP 20	
TEXAS INSTRUMENTS	TICPAL16R4-55	DIP 20	
TEXAS INSTRUMENTS	TICPAL16R6-55	DIP 20	
TEXAS INSTRUMENTS	TICPAL16R8-55	DIP 20	
TEXAS INSTRUMENTS	TICPAL16L8-55	PLCC 20	PA20LC20D[Dead Bug]
TEXAS INSTRUMENTS	TICPAL16R4-55	PLCC 20	PA20LC20D[Dead Bug]
TEXAS INSTRUMENTS	TICPAL16R6-55	PLCC 20	PA20LC20D[Dead Bug]
TEXAS INSTRUMENTS	TICPAL16R8-55	PLCC 20	PA20LC20D[Dead Bug]
TEXAS INSTRUMENTS	TICPAL22V10Z(T)	DIP 24	
TEXAS INSTRUMENTS	TICPAL22V10Z(ZP)	DIP 24	
TEXAS INSTRUMENTS	TICPAL22V10Z(T)	PLCC 28	PA28PL24D2P6-YA
TEXAS INSTRUMENTS	TICPAL22V10Z(ZP)	PLCC 28	PA28PL24D2P6-YA
VANTIS	ispGAL22V10	DIP 28	
VANTIS	ispGAL22V10B	DIP 28	
VANTIS	ispGAL22V10C	DIP 28	
VANTIS	ispGAL22V10	PLCC 28	PA28PL28D
VANTIS	ispGAL22V10B	PLCC 28	PA28PL28D
VANTIS	ispGAL22V10C	PLCC 28	PA28PL28D
VANTIS	PALCE16V8H	DIP 20	
VANTIS	PALCE16V8Has10H8	DIP 20	
VANTIS	PALCE16V8Has10L8	DIP 20	
VANTIS	PALCE16V8Has10P8	DIP 20	
VANTIS	PALCE16V8Has12H6	DIP 20	
VANTIS	PALCE16V8Has12L6	DIP 20	
VANTIS	PALCE16V8Has12P6	DIP 20	
VANTIS	PALCE16V8Has14H4	DIP 20	

VANTIS	PALCE16V8Has14L4	DIP 20	
VANTIS	PALCE16V8Has14P4	DIP 20	
VANTIS	PALCE16V8Has16H2	DIP 20	
VANTIS	PALCE16V8Has16L2	DIP 20	
VANTIS	PALCE16V8Has16P2	DIP 20	
VANTIS	PALCE16V8Has16H8	DIP 20	
VANTIS	PALCE16V8Has16L8	DIP 20	
VANTIS	PALCE16V8Has16P8	DIP 20	
VANTIS	PALCE16V8Has16R4	DIP 20	
VANTIS	PALCE16V8Has16R6	DIP 20	
VANTIS	PALCE16V8Has16R8	DIP 20	
VANTIS	PALCE16V8Has16RP4	DIP 20	
VANTIS	PALCE16V8Has16RP6	DIP 20	
VANTIS	PALCE16V8Has16RP8	DIP 20	
VANTIS	PALCE16V8H	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has10H8	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has10L8	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has10P8	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has12H6	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has12L6	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has12P6	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has14H4	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has14L4	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has14P4	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has16H2	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has16L2	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has16P2	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has16H8	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has16L8	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has16P8	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has16R4	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has16R6	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has16R8	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has16RP4	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has16RP6	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has16RP8	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8H	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has10H8	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has10L8	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has10P8	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has12H6	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has12L6	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has12P6	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has14H4	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has14L4	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has14P4	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has16H2	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has16L2	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has16P2	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has16H8	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has16L8	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has16P8	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has16R4	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has16R6	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has16R8	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has16RP4	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has16RP6	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has16RP8	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Q	DIP 20	
VANTIS	PALCE16V8Qas10H8	DIP 20	
VANTIS	PALCE16V8Qas10L8	DIP 20	
VANTIS	PALCE16V8Qas10P8	DIP 20	
VANTIS	PALCE16V8Qas12H6	DIP 20	
VANTIS	PALCE16V8Qas12L6	DIP 20	
VANTIS	PALCE16V8Qas12P6	DIP 20	
VANTIS	PALCE16V8Qas14H4	DIP 20	
VANTIS	PALCE16V8Qas14L4	DIP 20	
VANTIS	PALCE16V8Qas14P4	DIP 20	
VANTIS	PALCE16V8Qas16H2	DIP 20	
VANTIS	PALCE16V8Qas16L2	DIP 20	
VANTIS	PALCE16V8Qas16P2	DIP 20	
VANTIS	PALCE16V8Qas16H8	DIP 20	
VANTIS	PALCE16V8Qas16L8	DIP 20	

VANTIS	PALCE16V8Qas16P8	DIP 20	
VANTIS	PALCE16V8Qas16R4	DIP 20	
VANTIS	PALCE16V8Qas16R6	DIP 20	
VANTIS	PALCE16V8Qas16R8	DIP 20	
VANTIS	PALCE16V8Qas16RP4	DIP 20	
VANTIS	PALCE16V8Qas16RP6	DIP 20	
VANTIS	PALCE16V8Qas16RP8	DIP 20	
VANTIS	PALCE16V8Q	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas10H8	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas10L8	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas10P8	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas12H6	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas12L6	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas12P6	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas14H4	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas14L4	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas14P4	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas16H2	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas16L2	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas16P2	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas16H8	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas16L8	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas16P8	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas16R4	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas16R6	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas16R8	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas16RP4	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas16RP6	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas16RP8	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Q	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas10H8	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas10L8	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas10P8	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas12H6	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas12L6	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas12P6	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas14H4	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas14L4	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas14P4	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas16H2	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas16L2	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas16P2	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas16H8	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas16L8	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas16P8	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas16R4	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas16R6	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas16R8	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas16RP4	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas16RP6	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas16RP8	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Z	DIP 20	
VANTIS	PALCE16V8Zas10H8	DIP 20	
VANTIS	PALCE16V8Zas10L8	DIP 20	
VANTIS	PALCE16V8Zas10P8	DIP 20	
VANTIS	PALCE16V8Zas12H6	DIP 20	
VANTIS	PALCE16V8Zas12L6	DIP 20	
VANTIS	PALCE16V8Zas12P6	DIP 20	
VANTIS	PALCE16V8Zas14H4	DIP 20	
VANTIS	PALCE16V8Zas14L4	DIP 20	
VANTIS	PALCE16V8Zas14P4	DIP 20	
VANTIS	PALCE16V8Zas16H2	DIP 20	
VANTIS	PALCE16V8Zas16L2	DIP 20	
VANTIS	PALCE16V8Zas16P2	DIP 20	
VANTIS	PALCE16V8Zas16H8	DIP 20	
VANTIS	PALCE16V8Zas16L8	DIP 20	
VANTIS	PALCE16V8Zas16P8	DIP 20	
VANTIS	PALCE16V8Zas16R4	DIP 20	
VANTIS	PALCE16V8Zas16R6	DIP 20	
VANTIS	PALCE16V8Zas16R8	DIP 20	
VANTIS	PALCE16V8Zas16RP4	DIP 20	
VANTIS	PALCE16V8Zas16RP6	DIP 20	
VANTIS	PALCE16V8Zas16RP8	DIP 20	

VANTIS	PALCE16V8Z	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas10H8	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas10L8	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas10P8	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas12H6	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas12L6	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas12P6	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas14H4	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas14L4	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas14P4	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas16H2	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas16L2	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas16P2	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas16H8	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas16L8	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas16P8	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas16R4	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas16R6	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas16R8	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas16RP4	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas16RP6	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas16RP8	PLCC 20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Z	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas10H8	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas10L8	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas10P8	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas12H6	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas12L6	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas12P6	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas14H4	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas14L4	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas14P4	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas16H2	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas16L2	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas16P2	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas16H8	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas16L8	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas16P8	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas16R4	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas16R6	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas16R8	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas16RP4	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas16RP6	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas16RP8	SOIC 20	PA20SO20D-EO-210
VANTIS	PALCE20V8H-25	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25as14H8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25as14L8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25as14P8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25as16H6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25as16L6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25as16P6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25as18H4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25as18L4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25as18P4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25as20H2	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25as20L2	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25as20P2	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25as20H8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25as20L8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25as20P8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25as20R4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25as20R6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25as20R8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25as20RP4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25as20RP6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25as20RP8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-10/4	DIP 24	
VANTIS	PALCE20V8H-10/4as14H8	DIP 24	
VANTIS	PALCE20V8H-10/4as14L8	DIP 24	
VANTIS	PALCE20V8H-10/4as14P8	DIP 24	
VANTIS	PALCE20V8H-10/4as16H6	DIP 24	
VANTIS	PALCE20V8H-10/4as16L6	DIP 24	
VANTIS	PALCE20V8H-10/4as16P6	DIP 24	

VANTIS	PALCE20V8H-10/4as18H4	DIP 24	
VANTIS	PALCE20V8H-10/4as18L4	DIP 24	
VANTIS	PALCE20V8H-10/4as18P4	DIP 24	
VANTIS	PALCE20V8H-10/4as20H2	DIP 24	
VANTIS	PALCE20V8H-10/4as20L2	DIP 24	
VANTIS	PALCE20V8H-10/4as20P2	DIP 24	
VANTIS	PALCE20V8H-10/4as20H8	DIP 24	
VANTIS	PALCE20V8H-10/4as20L8	DIP 24	
VANTIS	PALCE20V8H-10/4as20P8	DIP 24	
VANTIS	PALCE20V8H-10/4as20R4	DIP 24	
VANTIS	PALCE20V8H-10/4as20R6	DIP 24	
VANTIS	PALCE20V8H-10/4as20R8	DIP 24	
VANTIS	PALCE20V8H-10/4as20RP4	DIP 24	
VANTIS	PALCE20V8H-10/4as20RP6	DIP 24	
VANTIS	PALCE20V8H-10/4as20RP8	DIP 24	
VANTIS	PALCE20V8H-10/4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-10/4as14H8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-10/4as14L8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-10/4as14P8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-10/4as16H6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-10/4as16L6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-10/4as16P6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-10/4as18H4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-10/4as18L4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-10/4as18P4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-10/4as20H2	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-10/4as20L2	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-10/4as20P2	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-10/4as20H8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-10/4as20L8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-10/4as20P8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-10/4as20R4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-10/4as20R6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-10/4as20R8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-10/4as20RP4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-10/4as20RP6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-10/4as20RP8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-15/4	DIP 24	
VANTIS	PALCE20V8H-15/4as14H8	DIP 24	
VANTIS	PALCE20V8H-15/4as14L8	DIP 24	
VANTIS	PALCE20V8H-15/4as14P8	DIP 24	
VANTIS	PALCE20V8H-15/4as16H6	DIP 24	
VANTIS	PALCE20V8H-15/4as16L6	DIP 24	
VANTIS	PALCE20V8H-15/4as16P6	DIP 24	
VANTIS	PALCE20V8H-15/4as18H4	DIP 24	
VANTIS	PALCE20V8H-15/4as18L4	DIP 24	
VANTIS	PALCE20V8H-15/4as18P4	DIP 24	
VANTIS	PALCE20V8H-15/4as20H2	DIP 24	
VANTIS	PALCE20V8H-15/4as20L2	DIP 24	
VANTIS	PALCE20V8H-15/4as20P2	DIP 24	
VANTIS	PALCE20V8H-15/4as20H8	DIP 24	
VANTIS	PALCE20V8H-15/4as20L8	DIP 24	
VANTIS	PALCE20V8H-15/4as20P8	DIP 24	
VANTIS	PALCE20V8H-15/4as20R4	DIP 24	
VANTIS	PALCE20V8H-15/4as20R6	DIP 24	
VANTIS	PALCE20V8H-15/4as20R8	DIP 24	
VANTIS	PALCE20V8H-15/4as20RP4	DIP 24	
VANTIS	PALCE20V8H-15/4as20RP6	DIP 24	
VANTIS	PALCE20V8H-15/4as20RP8	DIP 24	
VANTIS	PALCE20V8H-15/4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-15/4as14H8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-15/4as14L8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-15/4as14P8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-15/4as16H6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-15/4as16L6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-15/4as16P6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-15/4as18H4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-15/4as18L4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-15/4as18P4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-15/4as20H2	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-15/4as20L2	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-15/4as20P2	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-15/4as20H8	PLCC 28	PA28PL28D



VANTIS	PALCE20V8H-15/4as20L8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-15/4as20P8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-15/4as20R4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-15/4as20R6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-15/4as20R8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-15/4as20RP4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-15/4as20RP6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-15/4as20RP8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25/4	DIP 24	
VANTIS	PALCE20V8H-25/4as14H8	DIP 24	
VANTIS	PALCE20V8H-25/4as14L8	DIP 24	
VANTIS	PALCE20V8H-25/4as14P8	DIP 24	
VANTIS	PALCE20V8H-25/4as16H6	DIP 24	
VANTIS	PALCE20V8H-25/4as16L6	DIP 24	
VANTIS	PALCE20V8H-25/4as16P6	DIP 24	
VANTIS	PALCE20V8H-25/4as18H4	DIP 24	
VANTIS	PALCE20V8H-25/4as18L4	DIP 24	
VANTIS	PALCE20V8H-25/4as18P4	DIP 24	
VANTIS	PALCE20V8H-25/4as20H2	DIP 24	
VANTIS	PALCE20V8H-25/4as20L2	DIP 24	
VANTIS	PALCE20V8H-25/4as20P2	DIP 24	
VANTIS	PALCE20V8H-25/4as20H8	DIP 24	
VANTIS	PALCE20V8H-25/4as20L8	DIP 24	
VANTIS	PALCE20V8H-25/4as20P8	DIP 24	
VANTIS	PALCE20V8H-25/4as20R4	DIP 24	
VANTIS	PALCE20V8H-25/4as20R6	DIP 24	
VANTIS	PALCE20V8H-25/4as20R8	DIP 24	
VANTIS	PALCE20V8H-25/4as20RP4	DIP 24	
VANTIS	PALCE20V8H-25/4as20RP6	DIP 24	
VANTIS	PALCE20V8H-25/4as20RP8	DIP 24	
VANTIS	PALCE20V8H-25/4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25/4as14H8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25/4as14L8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25/4as14P8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25/4as16H6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25/4as16L6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25/4as16P6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25/4as18H4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25/4as18L4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25/4as18P4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25/4as20H2	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25/4as20L2	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25/4as20P2	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25/4as20H8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25/4as20L8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25/4as20P8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25/4as20R4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25/4as20R6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25/4as20R8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25/4as20RP4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25/4as20RP6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8H-25/4as20RP8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-15/4	DIP 24	
VANTIS	PALCE20V8Q-15/4as14H8	DIP 24	
VANTIS	PALCE20V8Q-15/4as14L8	DIP 24	
VANTIS	PALCE20V8Q-15/4as14P8	DIP 24	
VANTIS	PALCE20V8Q-15/4as16H6	DIP 24	
VANTIS	PALCE20V8Q-15/4as16L6	DIP 24	
VANTIS	PALCE20V8Q-15/4as16P6	DIP 24	
VANTIS	PALCE20V8Q-15/4as18H4	DIP 24	
VANTIS	PALCE20V8Q-15/4as18L4	DIP 24	
VANTIS	PALCE20V8Q-15/4as18P4	DIP 24	
VANTIS	PALCE20V8Q-15/4as20H2	DIP 24	
VANTIS	PALCE20V8Q-15/4as20L2	DIP 24	
VANTIS	PALCE20V8Q-15/4as20P2	DIP 24	
VANTIS	PALCE20V8Q-15/4as20H8	DIP 24	
VANTIS	PALCE20V8Q-15/4as20L8	DIP 24	
VANTIS	PALCE20V8Q-15/4as20P8	DIP 24	
VANTIS	PALCE20V8Q-15/4as20R4	DIP 24	
VANTIS	PALCE20V8Q-15/4as20R6	DIP 24	
VANTIS	PALCE20V8Q-15/4as20R8	DIP 24	
VANTIS	PALCE20V8Q-15/4as20RP4	DIP 24	
VANTIS	PALCE20V8Q-15/4as20RP6	DIP 24	

VANTIS	PALCE20V8Q-15/4as20RP8	DIP 24	
VANTIS	PALCE20V8Q-15/4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as14H8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as14L8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as14P8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as16H6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as16L6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as16P6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as18H4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as18L4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as18P4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as20H2	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as20L2	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as20P2	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as20H8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as20L8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as20P8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as20R4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as20R6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as20R8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as20RP4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as20RP6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as20RP8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-25/4	DIP 24	
VANTIS	PALCE20V8Q-25/4as14H8	DIP 24	
VANTIS	PALCE20V8Q-25/4as14L8	DIP 24	
VANTIS	PALCE20V8Q-25/4as14P8	DIP 24	
VANTIS	PALCE20V8Q-25/4as16H6	DIP 24	
VANTIS	PALCE20V8Q-25/4as16L6	DIP 24	
VANTIS	PALCE20V8Q-25/4as16P6	DIP 24	
VANTIS	PALCE20V8Q-25/4as18H4	DIP 24	
VANTIS	PALCE20V8Q-25/4as18L4	DIP 24	
VANTIS	PALCE20V8Q-25/4as18P4	DIP 24	
VANTIS	PALCE20V8Q-25/4as20H2	DIP 24	
VANTIS	PALCE20V8Q-25/4as20L2	DIP 24	
VANTIS	PALCE20V8Q-25/4as20P2	DIP 24	
VANTIS	PALCE20V8Q-25/4as20H8	DIP 24	
VANTIS	PALCE20V8Q-25/4as20L8	DIP 24	
VANTIS	PALCE20V8Q-25/4as20P8	DIP 24	
VANTIS	PALCE20V8Q-25/4as20R4	DIP 24	
VANTIS	PALCE20V8Q-25/4as20R6	DIP 24	
VANTIS	PALCE20V8Q-25/4as20R8	DIP 24	
VANTIS	PALCE20V8Q-25/4as20RP4	DIP 24	
VANTIS	PALCE20V8Q-25/4as20RP6	DIP 24	
VANTIS	PALCE20V8Q-25/4as20RP8	DIP 24	
VANTIS	PALCE20V8Q-25/4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as14H8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as14L8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as14P8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as16H6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as16L6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as16P6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as18H4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as18L4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as18P4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as20H2	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as20L2	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as20P2	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as20H8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as20L8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as20P8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as20R4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as20R6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as20R8	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as20RP4	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as20RP6	PLCC 28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as20RP8	PLCC 28	PA28PL28D
VANTIS	PALLV22V10	DIP 24	
VANTIS	PALLV22V10	PLCC 28	PA28PL28D
VANTIS	PALLV22V10Z	DIP 24	
VANTIS	PALLV22V10Z	PLCC 28	PA28PL28D
VANTIS	PALCE22V10H	DIP 24	
VANTIS	PALCE22V10H	PLCC 28	PA28PL28D

VANTIS	PALCE22V10Q	DIP 24	
VANTIS	PALCE22V10Q	PLCC 28	PA28PL28D
VANTIS	PALCE22V10Z	DIP 24	
VANTIS	PALCE22V10Z	PLCC 28	PA28PL28D
VANTIS	PALCE20RA10H	DIP 24	
VANTIS	PALCE20RA10H	PLCC 28	PA28PL28D
VANTIS	PALCE20RA10Q	DIP 24	
VANTIS	PALCE20RA10Q	PLCC 28	PA28PL28D
VANTIS	PALCE26V12H	DIP 28	
VANTIS	PALCE26V12H	PLCC 28	PA28PL28D
VANTIS	PALCE26V12H/4	DIP 28	
VANTIS	PALCE26V12H/4	PLCC 28	PA28PL28D
VANTIS	PALCE26V12H/4-10	DIP 28	
VANTIS	PALCE26V12H/4-10	PLCC 28	PA28PL28D
VANTIS	PALCE610H	DIP 24	
VANTIS	PALCE610H	PLCC 28	PA28PL28D
VANTIS	PALCE29M16H	DIP 24	
VANTIS	PALCE29M16H	PLCC 28	PA28PL28D
VANTIS	PALCE29MA16H	DIP 24	
VANTIS	PALCE29MA16H	PLCC 28	PA28PL28D
XILINX	XC7236A	PLCC 44	PA44-48U
XILINX	XC7318	PLCC 44	PA44-48U
XILINX	XC7318A	PLCC 44	PA44-48U
XILINX	XC7336	PLCC 44	PA44-48U
XILINX	XC7336A	PLCC 44	PA44-48U
XILINX	XC7336Q	PLCC 44	PA44-48U
XILINX	XC7354	PLCC 44	PA44-48U
XILINX	XC7354	PLCC 68	PA68-48B
XILINX	XC7372	PLCC 68	PA68-48C
XILINX	XC7372	PLCC 84	PA84-48B
XILINX	XC73108A	PLCC 84	PA84-48B
XILINX	XC9536	PLCC 44	PA44-48U
XILINX	XC9536	VQFP 44	PA44TQ44D-EO
XILINX	XC9572	PLCC 44	PA44-48U
XILINX	XC9572	PLCC 84	PA84-48F
XILINX	XC95108	PLCC 84	PA84-48B
XILINX	XC9536XL	PLCC 44	PA44-48U
XILINX	XC9536XL	VQFP 44	PA44TQ44D-EO
XILINX	XC9536XL	VQFP 64	PA64TQ48D
XILINX	XC9572XL	PLCC 44	PA44-48U
XILINX	XC9572XL	TQFP 100	PA100QF48DG
XILINX	XCS3032A/D	PLCC 44	PA44-48U
XILINX	XCR3032XL	PLCC 44	PA44-48U
XILINX	XCR3032XL	VQFP 44	PA44VQ44D
XILINX	XCR3064XL	PLCC 44	PA44-48U
XILINX	XCR3064XL	VQFP 44	PA44VQ44D
XILINX	XCR3128XL	VQFP 100	WA100QF48D
XILINX	XC2C32	VQFP 44	PA44QF44D
XILINX	XC2C32A	VQFP 44	PA44QF44D
XILINX	XC2C64	VQFP 44	PA44QF44D
XILINX	XC2C64A	VQFP 44	PA44QF44D
ALi	M6759	PLCC 44	PA44-48U
AMD	8751H	DIP 40	
AMD	8753H	DIP 40	
AMD	87C51	DIP 40	
AMD	87C521T2	DIP 40	
AMD	87C521	DIP 40	
AMD	87C541	DIP 40	
ATMEL	AT87F51RC	DIP 40	
ATMEL	AT87F51RC	PLCC 44	PA44-48U
ATMEL	AT87F55	DIP 40	
ATMEL	AT87F55	PLCC 44	PA44-48U
ATMEL	AT87F55WD	DIP 40	
ATMEL	AT87F55WD	PLCC 44	PA44-48U
ATMEL	AT87F51	DIP 40	
ATMEL	AT87F51	PLCC 44	PA44-48U
ATMEL	AT87F52	DIP 40	
ATMEL	AT87F52	PLCC 44	PA44-48U
ATMEL	AT89C51	DIP 40	
ATMEL	AT89C51	PLCC 44	PA44-48U
ATMEL	AT89C51RC	DIP 40	
ATMEL	AT89C51RC	PLCC 44	PA44-48U
ATMEL	AT89C51B2-xM_5V	PLCC 44	PA44-48U

ATMEL	AT89C51B2-xM_5V	QFP 44	PA44QF44D
ATMEL	AT89C51B2-xL_3V	PLCC 44	PA44-48U
ATMEL	AT89C51B2-xL_3V	QFP 44	PA44QF44D
ATMEL	AT89C51IC2-xM_5V	PLCC 44	PA44-48U
ATMEL	AT89C51IC2-xM_5V	QFP 44	PA44QF44D
ATMEL	AT89C51IC2-xL_3V	PLCC 44	PA44-48U
ATMEL	AT89C51IC2-xL_3V	QFP 44	PA44QF44D
ATMEL	AT89C51RB2-xM_5V	DIP 40	
ATMEL	AT89C51RB2-xM_5V	PLCC 44	PA44-48U
ATMEL	AT89C51RB2-xM_5V	QFP 44	PA44QF44D
ATMEL	AT89C51RB2-xL_3V	DIP 40	
ATMEL	AT89C51RB2-xL_3V	PLCC 44	PA44-48U
ATMEL	AT89C51RB2-xL_3V	QFP 44	PA44QF44D
ATMEL	AT89C51RC2-xM_5V	DIP 40	
ATMEL	AT89C51RC2-xM_5V	PLCC 44	PA44-48U
ATMEL	AT89C51RC2-xM_5V	QFP 44	PA44QF44D
ATMEL	AT89C51RC2-xL_3V	DIP 40	
ATMEL	AT89C51RC2-xL_3V	PLCC 44	PA44-48U
ATMEL	AT89C51RC2-xL_3V	QFP 44	PA44QF44D
ATMEL	AT89C52	DIP 40	
ATMEL	AT89C52	PLCC 44	PA44-48U
ATMEL	AT89C55	DIP 40	
ATMEL	AT89C55	PLCC 44	PA44-48U
ATMEL	AT89C55WD	DIP 40	
ATMEL	AT89C55WD	PLCC 44	PA44-48U
ATMEL	AT89C51AC3	PLCC 44	PA44-48U
ATMEL	AT89C51AC3	TQFP 44	PA44QF44D
ATMEL	AT89C51CC03	PLCC 44	PA44-48U
ATMEL	AT89C51CC03	TQFP 44	PA44QF44D
ATMEL	AT89C51ED2	DIP 40	
ATMEL	AT89C51ED2	PLCC 44	PA44-48U
ATMEL	AT89C51ED2	QFP 44	PA44QF44D
ATMEL	AT89C51ED2	PLCC 68	PA68PL40DG
ATMEL	AT89C51ED2	VQFP 64	PA64VQ40D
ATMEL	AT89C51ID2	PLCC 44	PA44-48U
ATMEL	AT89C51ID2	QFP 44	PA44QF44D
ATMEL	AT89C51ID2	PLCC 68	PA68PL40DG
ATMEL	AT89C51ID2	VQFP 64	PA64VQ40D
ATMEL	AT89C51RD2	DIP 40	
ATMEL	AT89C51RD2	PLCC 44	PA44-48U
ATMEL	AT89C51RD2	QFP 44	PA44QF44D
ATMEL	AT89C51RD2	PLCC 68	PA68PL40DG
ATMEL	AT89C51RD2	VQFP 64	PA64VQ40D
ATMEL	AT89LV51	DIP 40	
ATMEL	AT89LV51	PLCC 44	PA44-48U
ATMEL	AT89LV51	TQFP 44	PA44VQ44D
ATMEL	AT89LV52	DIP 40	
ATMEL	AT89LV52	PLCC 44	PA44-48U
ATMEL	AT89LV52	TQFP 44	PA44VQ44D
ATMEL	AT89LV55	TQFP 44	PA44VQ44D
ATMEL	AT89S51	DIP 40	
ATMEL	AT89S51	PLCC 44	PA44-48U
ATMEL	AT89S51	TQFP 44	PA44VQ44D
ATMEL	AT89S52	DIP 40	
ATMEL	AT89S52	PLCC 44	PA44-48U
ATMEL	AT89S52	TQFP 44	PA44VQ44D
ATMEL	AT89S53	DIP 40	
ATMEL	AT89S53	PLCC 44	PA44-48U
ATMEL	AT89S53	TQFP 44	PA44VQ44D
ATMEL	AT89S8252	DIP 40	
ATMEL	AT89S8252	PLCC 44	PA44-48U
ATMEL	AT89S8252	TQFP 44	PA44VQ44D
ATMEL	AT89LS51	DIP 40	
ATMEL	AT89LS51	PLCC 44	PA44-48U
ATMEL	AT89LS51	TQFP 44	PA44VQ44D
ATMEL	AT89LS52	DIP 40	
ATMEL	AT89LS52	PLCC 44	PA44-48U
ATMEL	AT89LS52	TQFP 44	PA44VQ44D
ATMEL	AT89LS8252	DIP 40	
ATMEL	AT89LS8252	PLCC 44	PA44-48U
ATMEL	AT89LS8252	TQFP 44	PA44VQ44D
ATMEL	AT89S8253	DIP 40	
ATMEL	AT89S8253	PLCC 44	PA44-48U

ATMEL	AT89S8253	QFP 44	PA44QF44D
ATMEL	AT89C1051	DIP 20	
ATMEL	AT89C1051	SOP 20	PA28SO28D-EO-300
ATMEL	AT89C1051U	DIP 20	
ATMEL	AT89C1051U	SOP 20	PA28SO28D-EO-300
ATMEL	AT89C2051	DIP 20	
ATMEL	AT89C2051	SOP 20	PA28SO28D-EO-300
ATMEL	AT89C2051X2	DIP 20	
ATMEL	AT89C2051X2	SOP 20	PA28SO28D-EO-300
ATMEL	AT89C4051	DIP 20	
ATMEL	AT89C4051	SOP 20	PA28SO28D-EO-300
ATMEL	AT89LP2052	DIP 20	
ATMEL	AT89LP2052	SOP 20	PA28SO28D-EO-300
ATMEL	AT89LP2052	TSSOP 20	PA24TSS24D
ATMEL	AT89LP4052	DIP 20	
ATMEL	AT89LP4052	SOP 20	PA28SO28D-EO-300
ATMEL	AT89LP4052	TSSOP 20	PA24TSS24D
ATMEL	AT89S2051	DIP 20	
ATMEL	AT89S2051	SOP 20	PA28SO28D-EO-300
ATMEL	AT89S2051	TSSOP 20	PA24TSS24D
ATMEL	AT89S4051	DIP 20	
ATMEL	AT89S4051	SOP 20	PA28SO28D-EO-300
ATMEL	AT89S4051	TSSOP 20	PA24TSS24D
ATMEL	AT90LS2333	DIP 28	
ATMEL	AT90LS4433	DIP 28	
ATMEL	AT90LS2323	DIP 8	
ATMEL	AT90LS2343	DIP 8	
ATMEL	AT90LS4434	DIP 40	
ATMEL	AT90LS4434	PLCC 44	PA44-48U
ATMEL	AT90LS8535	DIP 40	
ATMEL	AT90LS8535	PLCC 44	PA44-48U
ATMEL	AT90S1200	DIP 20	
ATMEL	AT90S1200	SOIC 20	PA28SO28D-EO-300
ATMEL	AT90S1200	SSOP 20	PA28SS28D
ATMEL	AT90S1200A	DIP 20	
ATMEL	AT90S1200A	SOIC 20	PA28SO28D-EO-300
ATMEL	AT90S1200A	SSOP 20	PA28SS28D
ATMEL	AT90S2333	DIP 28	
ATMEL	AT90S4433	DIP 28	
ATMEL	AT90S2313	DIP 20	
ATMEL	AT90S2323	DIP 8	
ATMEL	AT90S2343	DIP 8	
ATMEL	AT90S8515	DIP 40	
ATMEL	AT90S8515	PLCC 44	PA44-48U
ATMEL	AT90S4414	DIP 40	
ATMEL	AT90S4414	PLCC 44	PA44-48U
ATMEL	AT90S4434	DIP 40	
ATMEL	AT90S4434	PLCC 44	PA44-48U
ATMEL	AT90S8535	DIP 40	
ATMEL	AT90S8535	PLCC 44	PA44-48U
ATMEL	AT91SAM7S64	QFP 64	PA64QF48DC
ATMEL	AT91SAM7S128	QFP 64	PA64QF48DC
ATMEL	AT91SAM7S256	QFP 64	PA64QF48DC
ATMEL	ATTINY10	DIP 8	
ATMEL	ATTINY10	SOIC 8	PA20SO20D-EO-210
ATMEL	ATTINY10L	DIP 8	
ATMEL	ATTINY10L	SOIC 8	PA20SO20D-EO-210
ATMEL	ATTINY11	DIP 8	
ATMEL	ATTINY11	SOIC 8	PA20SO20D-EO-210
ATMEL	ATTINY11L	DIP 8	
ATMEL	ATTINY11L	SOIC 8	PA20SO20D-EO-210
ATMEL	ATTINY12	DIP 8	
ATMEL	ATTINY12	SOIC 8	PA20SO20D-EO-210
ATMEL	ATTINY12L	DIP 8	
ATMEL	ATTINY12L	SOIC 8	PA20SO20D-EO-210
ATMEL	ATTINY13	DIP 8	
ATMEL	ATTINY13	SOIC 8	PA16SO16D-EO-150
ATMEL	ATTINY13	SOIC 8	PA20SO20D-EO-210
ATMEL	ATTINY13V	DIP 8	
ATMEL	ATTINY13V	SOIC 8	PA16SO16D-EO-150
ATMEL	ATTINY13V	SOIC 8	PA20SO20D-EO-210
ATMEL	ATTINY15L	DIP 8	
ATMEL	ATTINY15L	SOIC 8	PA20SO20D-EO-210

ATMEL	ATTINY22	DIP 8	
ATMEL	ATTINY22	SOIC 8	PA20SO20D-EO-210
ATMEL	ATTINY22L	DIP 8	
ATMEL	ATTINY22L	SOIC 8	PA20SO20D-EO-210
ATMEL	ATTINY2313	DIP 20	
ATMEL	ATTINY2313	SOIC 20	PA28SO28D-EO-300
ATMEL	ATTINY2313V	DIP 20	
ATMEL	ATTINY2313V	SOIC 20	PA28SO28D-EO-300
ATMEL	ATTINY24	DIP 14	
ATMEL	ATTINY24	SOIC 14	PA16SO16D-EO-150
ATMEL	ATTINY44	DIP 14	
ATMEL	ATTINY44	SOIC 14	PA16SO16D-EO-150
ATMEL	ATTINY84	DIP 14	
ATMEL	ATTINY24V	DIP 14	
ATMEL	ATTINY24V	SOIC 14	PA16SO16D-EO-150
ATMEL	ATTINY44V	DIP 14	
ATMEL	ATTINY44V	SOIC 14	PA16SO16D-EO-150
ATMEL	ATTINY84V	DIP 14	
ATMEL	ATTINY25	DIP 8	
ATMEL	ATTINY25	SOIC 8	PA20SO20D-EO-210
ATMEL	ATTINY45	DIP 8	
ATMEL	ATTINY45	SOIC 8	PA20SO20D-EO-210
ATMEL	ATTINY85	DIP 8	
ATMEL	ATTINY85	SOIC 8	PA20SO20D-EO-210
ATMEL	ATTINY25V	DIP 8	
ATMEL	ATTINY25V	SOIC 8	PA20SO20D-EO-210
ATMEL	ATTINY45V	DIP 8	
ATMEL	ATTINY45V	SOIC 8	PA20SO20D-EO-210
ATMEL	ATTINY85V	DIP 8	
ATMEL	ATTINY85V	SOIC 8	PA20SO20D-EO-210
ATMEL	ATTINY261	DIP 20	
ATMEL	ATTINY261	SOIC 20	PA28SO28D-EO-300
ATMEL	ATTINY461	DIP 20	
ATMEL	ATTINY461	SOIC 20	PA28SO28D-EO-300
ATMEL	ATTINY861	DIP 20	
ATMEL	ATTINY861	SOIC 20	PA28SO28D-EO-300
ATMEL	ATTINY261V	DIP 20	
ATMEL	ATTINY261V	SOIC 20	PA28SO28D-EO-300
ATMEL	ATTINY461V	DIP 20	
ATMEL	ATTINY461V	SOIC 20	PA28SO28D-EO-300
ATMEL	ATTINY828-AU	TQFP 32	PA32TQ32D-YC
ATMEL	ATTINY861V	DIP 20	
ATMEL	ATTINY861V	SOIC 20	PA28SO28D-EO-300
ATMEL	ATTINY26	DIP 20	
ATMEL	ATTINY26	SOIC 20	PA28SO28D-EO-300
ATMEL	ATTINY26	MLF 32	PA32QFN28D
ATMEL	ATTINY26L	DIP 20	
ATMEL	ATTINY26L	SOIC 20	PA28SO28D-EO-300
ATMEL	ATTINY26L	MLF 32	PA32QFN28D
ATMEL	ATTINY28L	DIP 28	
ATMEL	ATTINY28V	DIP 28	
ATMEL	ATTINY28L	QFP 32	PA32TQ32D-YC
ATMEL	ATTINY28V	QFP 32	PA32TQ32D-YC
ATMEL	ATMEGA161	DIP 40	
ATMEL	ATMEGA161	PLCC 44	PA44-48U
ATMEL	ATMEGA161	QFP 44	PA44QF44D
ATMEL	ATMEGA161L	DIP 40	
ATMEL	ATMEGA161L	PLCC 44	PA44-48U
ATMEL	ATMEGA161L	QFP 44	PA44QF44D
ATMEL	ATMEGA162	DIP 40	
ATMEL	ATMEGA162	QFP 44	PA44QF44D
ATMEL	ATMEGA162V	DIP 40	
ATMEL	ATMEGA162V	QFP 44	PA44QF44D
ATMEL	ATMEGA163	DIP 40	
ATMEL	ATMEGA163	QFP 44	PA44QF44D
ATMEL	ATMEGA163L	DIP 40	
ATMEL	ATMEGA163L	QFP 44	PA44QF44D
ATMEL	ATMEGA8	DIP 28	
ATMEL	ATMEGA8	MLF 32	PA32QFN28D
ATMEL	ATMEGA8	TQFP 32	PA32TQ32DA
ATMEL	ATMEGA8A	DIP 28	
ATMEL	ATMEGA8A	MLF 32	PA32QFN28D
ATMEL	ATMEGA8A	TQFP 32	PA32TQ32DA

ATMEL	ATMEGA8L	DIP 28	
ATMEL	ATMEGA8L	MLF 32	PA32QFN28D
ATMEL	ATMEGA8L	TQFP 32	PA32TQ32DA
ATMEL	ATMEGA48	DIP 28	
ATMEL	ATMEGA48	MLF 32	PA32QFN28D
ATMEL	ATMEGA48	TQFP 32	PA32TQ32DA
ATMEL	ATMEGA48V	DIP 28	
ATMEL	ATMEGA48V	MLF 32	PA32QFN28D
ATMEL	ATMEGA48V	TQFP 32	PA32TQ32DA
ATMEL	ATMEGA88	DIP 28	
ATMEL	ATMEGA88	MLF 32	PA32QFN28D
ATMEL	ATMEGA88	TQFP 32	PA32TQ32DA
ATMEL	ATMEGA88V	DIP 28	
ATMEL	ATMEGA88V	MLF 32	PA32QFN28D
ATMEL	ATMEGA88V	TQFP 32	PA32TQ32DA
ATMEL	ATMEGA168	DIP 28	
ATMEL	ATMEGA168	MLF 32	PA32QFN28D
ATMEL	ATMEGA168	TQFP 32	PA32TQ32DA
ATMEL	ATMEGA168V	DIP 28	
ATMEL	ATMEGA168V	MLF 32	PA32QFN28D
ATMEL	ATMEGA168V	TQFP 32	PA32TQ32DA
ATMEL	ATMEGA328P	TQFP 32	PA32TQ32DA
ATMEL	ATMEGA328P	DIP 28	
ATMEL	ATMEGA16	DIP 40	
ATMEL	ATMEGA16	QFP 44	PA44QF44D
ATMEL	ATMEGA16A	DIP 40	
ATMEL	ATMEGA16A	QFP 44	PA44QF44D
ATMEL	ATMEGA16L	DIP 40	
ATMEL	ATMEGA16L	QFP 44	PA44QF44D
ATMEL	ATMEGA32	DIP 40	
ATMEL	ATMEGA32	QFP 44	PA44QF44D
ATMEL	ATMEGA32	MLF 44	PA44ML44D
ATMEL	ATMEGA32L	DIP 40	
ATMEL	ATMEGA32L	QFP 44	PA44QF44D
ATMEL	ATMEGA32L	MLF 44	PA44ML44D
ATMEL	ATMEGA164P	QFP 44	PA44VQ44D
ATMEL	ATMEGA324P	MLF 44	PA44ML44D
ATMEL	ATMEGA324P	QFP 44	PA44VQ44D
ATMEL	ATMEGA64	TQFP 64	PA64QF48DD
ATMEL	ATMEGA64L	TQFP 64	PA64QF48DD
ATMEL	ATMEGA128	TQFP 64	PA64QF48DD
ATMEL	ATMEGA128L	TQFP 64	PA64QF48DD
ATMEL	ATMEGA8515	DIP 40	
ATMEL	ATMEGA8515	PLCC 44	PA44-48U
ATMEL	ATMEGA8515	QFP 44	PA44QF44D
ATMEL	ATMEGA8515L	DIP 40	
ATMEL	ATMEGA8515L	PLCC 44	PA44-48U
ATMEL	ATMEGA8515L	QFP 44	PA44QF44D
ATMEL	ATMEGA8535	DIP 40	
ATMEL	ATMEGA8535	PLCC 44	PA44-48U
ATMEL	ATMEGA8535	QFP 44	PA44QF44D
ATMEL	ATMEGA8535L	DIP 40	
ATMEL	ATMEGA8535L	PLCC 44	PA44-48U
ATMEL	ATMEGA8535L	QFP 44	PA44QF44D
ATMEL	AT90USB647	TQFP 64	PA64QF48DD
ATMEL	AT90USB1287	TQFP 64	PA64QF48DD
ATMEL	AT90CAN32	TQFP 64	PA64QF48DD
ATMEL	AT90CAN64	TQFP 64	PA64QF48DD
ATMEL	AT90CAN128	TQFP 64	PA64QF48DD
ATMEL	AT90PWM2	SOIC 24	PA28SO28D-EO-300
ATMEL	AT90PWM2B	SOIC 24	PA28SO28D-EO-300
CYPRESS	CY7C63000A	DIP 20	
CYPRESS	CY7C63001A	DIP 20	
CYPRESS	CY7C63100A	DIP 24	
CYPRESS	CY7C63101A	DIP 24	
CYPRESS	CY7C63000A	SOIC 20	PA28SO28D-EO-300
CYPRESS	CY7C63001A	SOIC 20	PA28SO28D-EO-300
CYPRESS	CY7C63100A	SOIC 24	PA28SO28D-EO-300
CYPRESS	CY7C63101A	SOIC 24	PA28SO28D-EO-300
CYPRESS	CY7C63411	DIP 40	
CYPRESS	CY7C63412	DIP 40	
CYPRESS	CY7C63413	DIP 40	
CYPRESS	CY7C63411	DIP 48	

CYPRESS	CY7C63412	DIP 48	
CYPRESS	CY7C63413	DIP 48	
CYPRESS	CY7C63511	DIP 48	
CYPRESS	CY7C63512	DIP 48	
CYPRESS	CY7C63513	DIP 48	
CYPRESS	CY7C63612	SOIC 24	PA28-S01-08-6
CYPRESS	CY7C63613	SOIC 24	PA28-S01-08-6
CYPRESS	CY7C63221A	DIP 16	PA28-S01-08-6
CYPRESS	CY7C63231A	DIP 18	PA28-S01-08-6
CYPRESS	CY7C63231A	SOIC 18	PA28-S01-08-6
CYPRESS	CY8C27243	SSOP 20	PA28SS28D
DALLAS	DS5000/T-8	DIP 40	
DALLAS	DS5000/T-32	DIP 40	
DALLAS	DS87C520	DIP 40	
DALLAS	DS87C520	PLCC 44	PA44-48U
DALLAS	DS87C530	PLCC 52	PA530-52
DALLAS	DS87C530	PLCC 52	PA52PL40DD
DALLAS	DS89C420	DIP 40	
DALLAS	DS89C420	PLCC 44	PA44-48U
DALLAS	DS89C420REVB4	DIP 40	
DALLAS	DS89C420REVB4	PLCC 44	PA44-48U
DALLAS	DS89C420REVB4	TQFP 44	PA44QF44D
DALLAS	DS89C430	DIP 40	
DALLAS	DS89C430	PLCC 44	PA44-48U
DALLAS	DS89C430	TQFP 44	PA44QF44D
DALLAS	DS89C440	DIP 40	
DALLAS	DS89C440	PLCC 44	PA44-48U
DALLAS	DS89C440	TQFP 44	PA44QF44D
DALLAS	DS89C450	DIP 40	
DALLAS	DS89C450	PLCC 44	PA44-48U
DALLAS	DS89C450	TQFP 44	PA44QF44D
FAIRCHILD	ACE1101	DIP 8	
FAIRCHILD	ACE1202	DIP 8	
FUJITSU	MBL8742H	DIP 40	
GENCORE	GC87C520A0	DIP 40	
GENCORE	GC87C520A0	PLCC 44	PA44-48U
GENCORE	GC87C520A0	VQFP 44	PA44VQ44D
HITACHI	HD6473228P(H8/322)	SDIP 64	mqp AD372
HITACHI	HD6473238P(H8/323)	SDIP 64	mqp AD372
HITACHI	HD6473258P(H8/325)	SDIP 64	mqp AD372
HITACHI	H8/532	PLCC 84	PA84PL40DD
HITACHI	H8/534	PLCC 84	PA84PL40DD
HITACHI	H8/534(S)	PLCC 84	PA84PL40DD
HITACHI	H8/536	PLCC 84	PA84PL40DD
HITACHI	HD64F2238	DIP 40	PAH8SBGA112
HYNIX	GMS34004TM	DIP 16	
HYNIX	GMS34112TM	DIP 20	
HYNIX	GMS34140TM	DIP 24	
HYNIX	GMS34004TK	DIP 16	
HYNIX	GMS34112TK	DIP 20	
HYNIX	GMS34140TK	DIP 24	
HYNIX	GMS77C1000	DIP 18	
HYNIX	GMS77C1001	DIP 18	
HYNIX	GMS81004T	DIP 20	
HYNIX	GMS81004T	DIP 24	
HYNIX	GMS81004T	DIP 28	
HYNIX	GMS81008T	DIP 20	
HYNIX	GMS81008T	DIP 24	
HYNIX	GMS81008T	DIP 28	
HYNIX	GMS81016T	DIP 20	
HYNIX	GMS81016T	DIP 24	
HYNIX	GMS81016T	DIP 28	
HYNIX	GMS81024T	DIP 20	
HYNIX	GMS81024T	DIP 24	
HYNIX	GMS81024T	DIP 28	
HYNIX	GMS81032T	DIP 20	
HYNIX	GMS81032T	DIP 24	
HYNIX	GMS81032T	DIP 28	
HYNIX	GMS87C1102	DIP 16	
HYNIX	GMS87C1202	DIP 20	
HYNIX	GMS97C1051	DIP 20	
HYNIX	GMS97C2051	DIP 20	
HYNIX	GMS97C51	DIP 40	



HYNIX	GMS97C51		PLCC 44	PA44-48U
HYNIX	GMS97C52		DIP 40	
HYNIX	GMS97C52		PLCC 44	PA44-48U
HYNIX	GMS97C54		DIP 40	
HYNIX	GMS97C54		PLCC 44	PA44-48U
HYNIX	GMS97C54		QFP 44	PA44QF44D
HYNIX	GMS97C56		DIP 40	
HYNIX	GMS97C56		PLCC 44	PA44-48U
HYNIX	GMS97C58		DIP 40	
HYNIX	GMS97C58		PLCC 44	PA44-48U
HYNIX	GMS97L51		DIP 40	
HYNIX	GMS97L51		PLCC 44	PA44-48U
HYNIX	GMS97L52		DIP 40	
HYNIX	GMS97L52		PLCC 44	PA44-48U
HYNIX	GMS99C58		DIP 40	
HYNIX	GMS99C58		PLCC 44	PA44-48U
HYNIX	HMS99C52		DIP 40	
HYNIX	HMS99C51S		DIP 40	
HYNIX	HMS99C52S		DIP 40	
HYNIX	HMS99C54S		DIP 40	
HYNIX	HMS99C56S		DIP 40	
HYNIX	HMS99C58S		DIP 40	
HYNIX	HMS77C2000		DIP 8	
HYNIX	HMS77C2001		DIP 8	
HYNIX	HMS97C8032		QFP 80	PA97C8032
INTEL	8741A		DIP 40	
INTEL	8741AH		DIP 40	
INTEL		8742	DIP 40	
INTEL	8742AH		DIP 40	
INTEL		8748	DIP 40	
INTEL	8748H		DIP 40	
INTEL	8749H		DIP 40	
INTEL	8751BH		DIP 40	
INTEL	8752BH		DIP 40	
INTEL	8751H(10ms)		DIP 40	
INTEL	8751H(50ms)		DIP 40	
INTEL	8755A		DIP 40	
INTEL	87C196CA		PLCC 68	PA68-40E
INTEL	87C196JQ		PLCC 52	PA52-40C
INTEL	87C196JR		PLCC 52	PA52-40C
INTEL	87C196JT		PLCC 52	PA52-40C
INTEL	87C196JV		PLCC 52	PA52-40C
INTEL	87C196KB		PLCC 68	PA68-40D
INTEL	87C196KC		PLCC 68	PA68-40D
INTEL	87C196KD		PLCC 68	PA68-40D
INTEL	87C196KQ		PLCC 68	PA68-40C
INTEL	87C196KR		PLCC 68	PA68-40C
INTEL	87C196KS		PLCC 68	PA68-40C
INTEL	87C196KT		PLCC 68	PA68-40C
INTEL	87C196MC		PLCC 84	PA84-40C
INTEL	87C196MD		PLCC 84	PA84-40C
INTEL	87C196MH		PLCC 84	PA84-40C
INTEL	87C251SB		DIP 40	
INTEL	87C251SB		PLCC 44	PA44-48U
INTEL	87C42		DIP 40	
INTEL	87C51		DIP 40	
INTEL	87C51		PLCC 44	PA44-48U
INTEL	87C521		DIP 40	
INTEL	87C521		PLCC 44	PA44-48U
INTEL	87C511		DIP 40	
INTEL	87C511		PLCC 44	PA44-48U
INTEL	87C511		QFP 44	PA44QF44D
INTEL	87C51FA		DIP 40	
INTEL	87C51FB		DIP 40	
INTEL	87C51FC		DIP 40	
INTEL	87C51FA		PLCC 44	PA44-48U
INTEL	87C51FB		PLCC 44	PA44-48U
INTEL	87C51FC		PLCC 44	PA44-48U
INTEL	87C51FA		QFP 44	PA44QF44D
INTEL	87C51FB		QFP 44	PA44QF44D
INTEL	87C51FC		QFP 44	PA44QF44D
INTEL	87C51RA		DIP 40	
INTEL	87C51RA		PLCC 44	PA44-48U

INTEL	87C51RB	DIP 40	
INTEL	87C51RB	PLCC 44	PA44-48U
INTEL	87C51RC	DIP 40	
INTEL	87C51RC	PLCC 44	PA44-48U
INTEL	87C52	DIP 40	
INTEL	87C52	PLCC 44	PA44-48U
INTEL	87C54	DIP 40	
INTEL	87C54	PLCC 44	PA44-48U
INTEL	87L51FA	PLCC 44	PA44-48U
INTEL	87L51FB	PLCC 44	PA44-48U
INTEL	87L51FC	PLCC 44	PA44-48U
ICSI	IS89C52A	DIP 40	
ICSI	IS89C52A	PLCC 44	PA44-48U
ICSI	IS89C54	DIP 40	
ICSI	IS89C54	PLCC 44	PA44-48U
ICSI	IS89C58	DIP 40	
ICSI	IS89C58	PLCC 44	PA44-48U
ICSI	IS89C64	DIP 40	
ICSI	IS89C64	PLCC 44	PA44-48U
ISSI	IS89C51	DIP 40	
ISSI	IS89C51	PLCC 44	PA44-48U
ISSI	IS89C52	DIP 40	
ISSI	IS89C52	PLCC 44	PA44-48U
ISSI	IS89C51A	DIP 40	
ISSI	IS89C51A	PLCC 44	PA44-48U
ISSI	IS89C52A	DIP 40	
ISSI	IS89C52A	PLCC 44	PA44-48U
ISSI	IS89C54A	DIP 40	
ISSI	IS89C54A	PLCC 44	PA44-48U
MACRONIX	MX10FMAXDPC	DIP 40	
MACRONIX	MX10FMAXDQC	PLCC 44	PA44-48U
MEDIA REALITY TECH.	M8064	PLCC 44	PA44-48U
MICROCHIP	dsPIC30F2010	DIP 28	
MICROCHIP	dsPIC30F2010	SOIC 28	PA28SO28D-EO-300
MICROCHIP	dsPIC30F2010	QFN 28	PA28QFN28D
MICROCHIP	dsPIC30F2011	DIP 18	
MICROCHIP	dsPIC30F2011	SOIC 18	PA28SO28D-EO-300
MICROCHIP	dsPIC30F2011	QFN 28	PA28QFN28D
MICROCHIP	dsPIC30F2012	DIP 28	
MICROCHIP	dsPIC30F2012	SOIC 28	PA28SO28D-EO-300
MICROCHIP	dsPIC30F2012	QFN 28	PA28QFN28D
MICROCHIP	dsPIC30F3010	DIP 28	
MICROCHIP	dsPIC30F3010	SOIC 28	PA28SO28D-EO-300
MICROCHIP	dsPIC30F3010	QFN 44	PA44QFN44D
MICROCHIP	dsPIC30F3011	DIP 40	
MICROCHIP	dsPIC30F3011	TQFP 44	PA44TQ44D-EO
MICROCHIP	dsPIC30F3011	QFN 44	PA44QFN44D
MICROCHIP	dsPIC30F3012	DIP 18	
MICROCHIP	dsPIC30F3012	SOIC 18	PA28SO28D-EO-300
MICROCHIP	dsPIC30F3012	QFN 44	PA44QFN44D
MICROCHIP	dsPIC30F3013	DIP 28	
MICROCHIP	dsPIC30F3013	SOIC 28	PA28SO28D-EO-300
MICROCHIP	dsPIC30F3013	QFN 44	PA44QFN44D
MICROCHIP	dsPIC30F3014	DIP 40	
MICROCHIP	dsPIC30F3014	TQFP 44	PA44TQ44D-EO
MICROCHIP	dsPIC30F3014	QFN 44	PA44QFN44D
MICROCHIP	dsPIC30F4011	DIP 40	
MICROCHIP	dsPIC30F4011	TQFP 44	PA44TQ44D-EO
MICROCHIP	dsPIC30F4011	QFN 44	PA44QFN44D
MICROCHIP	dsPIC30F4012	DIP 28	
MICROCHIP	dsPIC30F4012	SOIC 28	PA28SO28D-EO-300
MICROCHIP	dsPIC30F4012	QFN 44	PA44QFN44D
MICROCHIP	dsPIC30F4013	DIP 40	
MICROCHIP	dsPIC30F4013	TQFP 44	PA44TQ44D-EO
MICROCHIP	dsPIC30F4013	QFN 44	PA44QFN44D
MICROCHIP	PIC10F200	DIP 8	
MICROCHIP	PIC10F200	SOT23- 6	PA6SS6D-23
MICROCHIP	PIC10F202	DIP 8	
MICROCHIP	PIC10F202	SOT23- 6	PA6SS6D-23
MICROCHIP	PIC10F204	DIP 8	
MICROCHIP	PIC10F204	SOT23- 6	PA6SS6D-23
MICROCHIP	PIC10F206	DIP 8	
MICROCHIP	PIC10F206	SOT23- 6	PA6SS6D-23

MICROCHIP	PIC10F220	DIP 8	
MICROCHIP	PIC10F220	SOT23- 6	PA6SS6D-23
MICROCHIP	PIC10F222	DIP 8	
MICROCHIP	PIC10F222	SOT23- 6	PA6SS6D-23
MICROCHIP	PIC12C508	DIP 8	
MICROCHIP	PIC12C508A	DIP 8	
MICROCHIP	PIC12C508	SOIC 8	PA20SO20D-EO-210
MICROCHIP	PIC12C508A	SOIC 8	PA20SO20D-EO-210
MICROCHIP	PIC12C509	DIP 8	
MICROCHIP	PIC12C509A	DIP 8	
MICROCHIP	PIC12C509AG	DIP 18	
MICROCHIP	PIC12C509AF	DIP 20	
MICROCHIP	PIC12CE508	DIP 8	
MICROCHIP	PIC12CE508A	DIP 8	
MICROCHIP	PIC12CE509	DIP 8	
MICROCHIP	PIC12CE509A	DIP 8	
MICROCHIP	PIC12CE518	DIP 8	
MICROCHIP	PIC12CE519	DIP 8	
MICROCHIP	PIC12C671	DIP 8	
MICROCHIP	PIC12C672	DIP 8	
MICROCHIP	PIC12F508	DIP 8	
MICROCHIP	PIC12F508	SOIC 8	PA16SO16D-EO-150
MICROCHIP	PIC12F508	MSOP 8	HA8MSOP48D
MICROCHIP	PIC12F509	DIP 8	
MICROCHIP	PIC12F509	SOIC 8	PA16SO16D-EO-150
MICROCHIP	PIC12F509	MSOP 8	HA8MSOP48D
MICROCHIP	PIC12F510	DIP 8	
MICROCHIP	PIC12F510	SOIC 8	PA16SO16D-EO-150
MICROCHIP	PIC12F510	MSOP 8	HA8MSOP48D
MICROCHIP	PIC12F519	DIP 8	
MICROCHIP	PIC12F519	SOIC 8	PA16SO16D-EO-150
MICROCHIP	PIC12F519	DFN 8	PA8QFN8D
MICROCHIP	PIC12F519	MSOP 8	HA8MSOP48D
MICROCHIP	PIC12LF1822	SOIC 8	PA8SO8D-EO-150
MICROCHIP	PIC12F609	DIP 8	
MICROCHIP	PIC12F629	DIP 8	
MICROCHIP	PIC12F629	SOIC 8	PA16SO16D-EO-150
MICROCHIP	PIC12F675	DIP 8	
MICROCHIP	PIC12F675	SOIC 8	PA16SO16D-EO-150
MICROCHIP	PIC14000(OPT)	DIP 28	
MICROCHIP	PIC14000(OPT)	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC16C505	DIP 14	
MICROCHIP	PIC16C52	DIP 18	
MICROCHIP	PIC16C52(OTP)	DIP 18	
MICROCHIP	PIC16C54	DIP 18	
MICROCHIP	PIC16C54(OTP)	DIP 18	
MICROCHIP	PIC16C54A	DIP 18	
MICROCHIP	PIC16C54B	DIP 18	
MICROCHIP	PIC16C54C	DIP 18	
MICROCHIP	PIC16CR54A	DIP 18	
MICROCHIP	PIC16CR54B	DIP 18	
MICROCHIP	PIC16CR54C	DIP 18	
MICROCHIP	PIC16HV540	DIP 18	
MICROCHIP	PIC16C55	DIP 28	
MICROCHIP	PIC16C55(OTP)	DIP 28	
MICROCHIP	PIC16C55A	DIP 28	
MICROCHIP	PIC16C55A	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC16C56	DIP 18	
MICROCHIP	PIC16C56(OTP)	DIP 18	
MICROCHIP	PIC16C56A	DIP 18	
MICROCHIP	PIC16CR56A	DIP 18	
MICROCHIP	PIC16C57	DIP 28	
MICROCHIP	PIC16C57(OTP)	DIP 28	
MICROCHIP	PIC16C57C	DIP 28	
MICROCHIP	PIC16CR57B	DIP 28	
MICROCHIP	PIC16CR57C	DIP 28	
MICROCHIP	PIC16C58A	DIP 18	
MICROCHIP	PIC16C58B	DIP 18	
MICROCHIP	PIC16CR58A	DIP 18	
MICROCHIP	PIC16CR58B	DIP 18	
MICROCHIP	PIC16C554	DIP 18	
MICROCHIP	PIC16C556	DIP 18	
MICROCHIP	PIC16C558	DIP 18	

MICROCHIP	PIC16C61	DIP 18	
MICROCHIP	PIC16C62	DIP 28	
MICROCHIP	PIC16C62A	DIP 28	
MICROCHIP	PIC16C62B	DIP 28	
MICROCHIP	PIC16LC62B	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC16C620	DIP 18	
MICROCHIP	PIC16C620A	DIP 18	
MICROCHIP	PIC16C621	DIP 18	
MICROCHIP	PIC16C621A	DIP 18	
MICROCHIP	PIC16C622	DIP 18	
MICROCHIP	PIC16C622A	DIP 18	
MICROCHIP	PIC16C63	DIP 28	
MICROCHIP	PIC16C63A	DIP 28	
MICROCHIP	PIC16C64	DIP 40	
MICROCHIP	PIC16C64	PLCC 44	PA44-48U
MICROCHIP	PIC16C64A	DIP 40	
MICROCHIP	PIC16C64A	PLCC 44	PA44-48U
MICROCHIP	PIC16C65	DIP 40	
MICROCHIP	PIC16C65	PLCC 44	PA44-48U
MICROCHIP	PIC16C65A	DIP 40	
MICROCHIP	PIC16C65A	PLCC 44	PA44-48U
MICROCHIP	PIC16C65B	DIP 40	
MICROCHIP	PIC16C65B	PLCC 44	PA44-48U
MICROCHIP	PIC16C66	DIP 28	
MICROCHIP	PIC16C67	DIP 40	
MICROCHIP	PIC16C67	PLCC 44	PA44-48U
MICROCHIP	PIC16C71	DIP 18	
MICROCHIP	PIC16C72	DIP 28	
MICROCHIP	PIC16C72A	DIP 28	
MICROCHIP	PIC16C73	DIP 28	
MICROCHIP	PIC16C73A	DIP 28	
MICROCHIP	PIC16C73B	DIP 28	
MICROCHIP	PIC16C73B	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC16C74	DIP 40	
MICROCHIP	PIC16C74	PLCC 44	PA44-48U
MICROCHIP	PIC16C74A	DIP 40	
MICROCHIP	PIC16C74A	PLCC 44	PA44-48U
MICROCHIP	PIC16C74B	DIP 40	
MICROCHIP	PIC16C74B	PLCC 44	PA44-48U
MICROCHIP	PIC16C76	DIP 28	
MICROCHIP	PIC16C77	DIP 40	
MICROCHIP	PIC16C773	DIP 28	
MICROCHIP	PIC16C774	DIP 40	
MICROCHIP	PIC16C774	PLCC 44	PA44-48U
MICROCHIP	PIC16CE623	DIP 18	
MICROCHIP	PIC16CE624	DIP 18	
MICROCHIP	PIC16CE625	DIP 18	
MICROCHIP	PIC16C641	DIP 28	
MICROCHIP	PIC16C642	DIP 28	
MICROCHIP	PIC16C661	DIP 40	
MICROCHIP	PIC16C662	DIP 40	
MICROCHIP	PIC16C710	DIP 18	
MICROCHIP	PIC16C711	DIP 18	
MICROCHIP	PIC16C712	DIP 18	
MICROCHIP	PIC16C716	DIP 18	
MICROCHIP	PIC16C715	DIP 18	
MICROCHIP	PIC16C745	DIP 28	
MICROCHIP	PIC16C765	DIP 40	
MICROCHIP	PIC16C717	DIP 18	
MICROCHIP	PIC16C770	DIP 20	
MICROCHIP	PIC16C771	DIP 20	
MICROCHIP	PIC16C781	DIP 20	
MICROCHIP	PIC16C782	DIP 20	
MICROCHIP	PIC16C84	DIP 18	
MICROCHIP	PIC16CR83	DIP 18	
MICROCHIP	PIC16CR84	DIP 18	
MICROCHIP	PIC16C923	PLCC 68	PA756-68Z
MICROCHIP	PIC16C924	PLCC 68	PA756-68Z
MICROCHIP	PIC16F505	DIP 14	
MICROCHIP	PIC16F505	SOIC 14	PA16SO16D-EO-150
MICROCHIP	PIC16F505	TSSOP 14	PA24TSS24D
MICROCHIP	PIC16F506	DIP 14	
MICROCHIP	PIC16F506	SOIC 14	PA16SO16D-EO-150

MICROCHIP	PIC16F506	TSSOP 14	PA24TSS24D
MICROCHIP	PIC16F54	DIP 18	
MICROCHIP	PIC16F54	SOIC 18	PA28SO28D-EO-310
MICROCHIP	PIC16F54	SSOP 20	PA20SS-P54
MICROCHIP	PIC16F54	SSOP 20	PA24TSS24D
MICROCHIP	PIC16F57	DIP 28	
MICROCHIP	PIC16F57	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC16F57	SSOP 28	PA28TS28D-EO
MICROCHIP	PIC16F630	DIP 14	
MICROCHIP	PIC16F676	DIP 14	
MICROCHIP	PIC16F676	SOIC 14	PA16SO16D-EO-150
MICROCHIP	PIC16F72	DIP 28	
MICROCHIP	PIC16F722	DIP 28	
MICROCHIP	PIC16LF72	DIP 28	
MICROCHIP	PIC16F73	DIP 28	
MICROCHIP	PIC16F74	DIP 40	
MICROCHIP	PIC16F74	PLCC 44	PA44-48U
MICROCHIP	PIC16F74	TQFP 44	PA44QF44D
MICROCHIP	PIC16F76	DIP 28	
MICROCHIP	PIC16F77	DIP 40	
MICROCHIP	PIC16F77	PLCC 44	PA44-48U
MICROCHIP	PIC16F77	TQFP 44	PA44QF44D
MICROCHIP	PIC16F83	DIP 18	
MICROCHIP	PIC16F84	DIP 18	
MICROCHIP	PIC16F84A	DIP 18	
MICROCHIP	PIC16F87	DIP 18	
MICROCHIP	PIC16F87	SOIC 18	PA28SO28D-EO-310
MICROCHIP	PIC16F87	SSOP 20	PA20SS-P54
MICROCHIP	PIC16F88	DIP 18	
MICROCHIP	PIC16F88	SOIC 18	PA28SO28D-EO-310
MICROCHIP	PIC16F88	SSOP 20	PA20SS-P54
MICROCHIP	PIC16F616	SOIC 14	PA16SO16D-EO-150
MICROCHIP	PIC16HV616	SOIC 14	PA16SO16D-EO-150
MICROCHIP	PIC12F635	DIP 8	
MICROCHIP	PIC12F635	SOIC 8	PA16SO16D-EO-150
MICROCHIP	PIC12F683	DIP 8	
MICROCHIP	PIC12F683	SOIC 8	PA16SO16D-EO-150
MICROCHIP	PIC16F631	DIP 20	
MICROCHIP	PIC16F631	SOIC 20	PA28SO28D-EO-300
MICROCHIP	PIC16F631	SSOP 20	PA28SS28D
MICROCHIP	PIC16F636	DIP 14	
MICROCHIP	PIC16F636	SOIC 14	PA16SO16D-EO-150
MICROCHIP	PIC16F636	TSSOP 14	PA24TSS24D
MICROCHIP	PIC16F677	DIP 20	
MICROCHIP	PIC16F677	SOIC 20	PA28SO28D-EO-300
MICROCHIP	PIC16F677	SSOP 20	PA28SS28D
MICROCHIP	PIC16F684	DIP 14	
MICROCHIP	PIC16F684	SOIC 14	PA16SO16D-EO-150
MICROCHIP	PIC16F684	TSSOP 14	PA24TSS24D
MICROCHIP	PIC16F685	DIP 20	
MICROCHIP	PIC16F685	SOIC 20	PA28SO28D-EO-300
MICROCHIP	PIC16F685	SSOP 20	PA28SS28D
MICROCHIP	PIC16F688	DIP 14	
MICROCHIP	PIC16F688	SOIC 14	PA16SO16D-EO-150
MICROCHIP	PIC16F688	TSSOP 14	PA24TSS24D
MICROCHIP	PIC16F689	DIP 20	
MICROCHIP	PIC16F689	SOIC 20	PA28SO28D-EO-300
MICROCHIP	PIC16F689	SSOP 20	PA28SS28D
MICROCHIP	PIC16F690	DIP 20	
MICROCHIP	PIC16F690	SOIC 20	PA28SO28D-EO-300
MICROCHIP	PIC16F690	SSOP 20	PA28SS28D
MICROCHIP	PIC16F627	DIP 18	
MICROCHIP	PIC16F627A	DIP 18	
MICROCHIP	PIC16F627A	SOIC 18	PA28SO28D-EO-300
MICROCHIP	PIC16F627A	SSOP 20	PA20SS-P54
MICROCHIP	PIC16F628	DIP 18	
MICROCHIP	PIC16F628A	DIP 18	
MICROCHIP	PIC16F628A	SOIC 18	PA28SO28D-EO-310
MICROCHIP	PIC16F628A	SSOP 20	PA20SS-P54
MICROCHIP	PIC16F648A	DIP 18	
MICROCHIP	PIC16F648A	SOIC 18	PA28SO28D-EO-310
MICROCHIP	PIC16F648A	SSOP 20	PA20SS-P54
MICROCHIP	PIC16F716	DIP 18	

MICROCHIP	PIC16F716	SOIC 18	PA28SO28D-EO-310
MICROCHIP	PIC16F716	SSOP 20	PA20SS-P54
MICROCHIP	PIC16F737	DIP 28	
MICROCHIP	PIC16F737	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC16F767	DIP 28	
MICROCHIP	PIC16F767	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC16F818	DIP 18	
MICROCHIP	PIC16F818	SOIC 18	PA28SO28D-EO-310
MICROCHIP	PIC16F818	SSOP 20	PA20SS-P54
MICROCHIP	PIC16F819	DIP 18	
MICROCHIP	PIC16F819	SOIC 18	PA28SO28D-EO-310
MICROCHIP	PIC16F819	SSOP 20	PA20SS-P54
MICROCHIP	PIC16F870	DIP 28	
MICROCHIP	PIC16F870	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC16F871	DIP 40	
MICROCHIP	PIC16F871	TQFP 44	PA44QF44D
MICROCHIP	PIC16F871	PLCC 44	PA44-48U
MICROCHIP	PIC16F872	DIP 28	
MICROCHIP	PIC16F872	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC16F873	DIP 28	
MICROCHIP	PIC16F873	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC16F874	DIP 40	
MICROCHIP	PIC16F874	PLCC 44	PA44-48U
MICROCHIP	PIC16F874	TQFP 44	PA44QF44D
MICROCHIP	PIC16F876	DIP 28	
MICROCHIP	PIC16F876	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC16F877	DIP 40	
MICROCHIP	PIC16F877	PLCC 44	PA44-48U
MICROCHIP	PIC16F877	TQFP 44	PA44QF44D
MICROCHIP	PIC16F873A	DIP 28	
MICROCHIP	PIC16F873A	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC16F874A	DIP 40	
MICROCHIP	PIC16F874A	PLCC 44	PA44-48U
MICROCHIP	PIC16F874A	TQFP 44	PA44QF44D
MICROCHIP	PIC16F876A	DIP 28	
MICROCHIP	PIC16F876A	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC16F876A	SSOP 28	PA28SS28D
MICROCHIP	PIC16F877A	DIP 40	
MICROCHIP	PIC16F877A	PLCC 44	PA44-48U
MICROCHIP	PIC16F877A	TQFP 44	PA44QF44D
MICROCHIP	PIC16LF873A	DIP 28	
MICROCHIP	PIC16LF873A	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC16LF876A	DIP 28	
MICROCHIP	PIC16F882	DIP 28	
MICROCHIP	PIC16F882	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC16F882	SSOP 28	PA28SS28D
MICROCHIP	PIC16F882	QFN 28	PA28QFN28D
MICROCHIP	PIC16F883	DIP 28	
MICROCHIP	PIC16F883	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC16F883	SSOP 28	PA28SS28D
MICROCHIP	PIC16F883	QFN 28	PA28QFN28D
MICROCHIP	PIC16F884	DIP 40	
MICROCHIP	PIC16F884	TQFP 44	PA44QF44D
MICROCHIP	PIC16F884	QFN 44	PA44QFN44D
MICROCHIP	PIC16F886	DIP 28	
MICROCHIP	PIC16F886	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC16F886	SSOP 28	PA28SS28D
MICROCHIP	PIC16F886	QFN 28	PA28QFN28D
MICROCHIP	PIC16F887	DIP 40	
MICROCHIP	PIC16F887	TQFP 44	PA44QF44D
MICROCHIP	PIC16F887	QFN 44	PA44QFN44D
MICROCHIP	PIC16LC73A	DIP 28	
MICROCHIP	PIC16LC73B	DIP 28	
MICROCHIP	PIC16LC74A	DIP 40	
MICROCHIP	PIC16LC74A	PLCC 44	PA44-48U
MICROCHIP	PIC16LC74B	DIP 40	
MICROCHIP	PIC16LC74B	PLCC 44	PA44-48U
MICROCHIP	PIC16LC77	DIP 40	
MICROCHIP	PIC16LC77	PLCC 44	PA44-48U
MICROCHIP	PIC16F1937	DIP 40	
MICROCHIP	PIC16F1934	DIP 40	
MICROCHIP	PIC16F1823	DIP 14	
MICROCHIP	PIC16F1823	SOIC 14	PA16SO16D-EO-150

MICROCHIP	PIC17C42	DIP 40	
MICROCHIP	PIC17C42	PLCC 44	PA44-48U
MICROCHIP	PIC17C42A	DIP 40	
MICROCHIP	PIC17C42A	PLCC 44	PA44-48U
MICROCHIP	PIC17C43	DIP 40	
MICROCHIP	PIC17C43	PLCC 44	PA44-48U
MICROCHIP	PIC17C44	DIP 40	
MICROCHIP	PIC17C44	PLCC 44	PA44-48U
MICROCHIP	PIC17LC44	DIP 40	
MICROCHIP	PIC17LC44	PLCC 44	PA44-48U
MICROCHIP	PIC17C752	PLCC 68	PA756-68Z
MICROCHIP	PIC17C756	PLCC 68	PA756-68Z
MICROCHIP	PIC17C756	SDIP 64	PA923-SD
MICROCHIP	PIC17C756A	PLCC 68	PA756-68Z
MICROCHIP	PIC17C756A	SDIP 64	PA923-SD
MICROCHIP	PIC18C242	DIP 28	
MICROCHIP	PIC18C252	DIP 28	
MICROCHIP	PIC18C442	DIP 40	
MICROCHIP	PIC18C442	PLCC 44	PA44-48U
MICROCHIP	PIC18C452	DIP 40	
MICROCHIP	PIC18C452	PLCC 44	PA44-48U
MICROCHIP	PIC18C658	TQFP 64	PA64TQ40D
MICROCHIP	PIC18F2331	DIP 28	
MICROCHIP	PIC18F2331	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F2431	DIP 28	
MICROCHIP	PIC18F2431	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F4331	DIP 40	
MICROCHIP	PIC18F4331	TQFP 44	PA44QF44D
MICROCHIP	PIC18F4331	QFN 44	PA44QFN44D
MICROCHIP	PIC18F4431	DIP 40	
MICROCHIP	PIC18F4431	TQFP 44	PA44QF44D
MICROCHIP	PIC18F4431	QFN 44	PA44QFN44D
MICROCHIP	PIC18F242	DIP 28	
MICROCHIP	PIC18F248	DIP 28	
MICROCHIP	PIC18F252	DIP 28	
MICROCHIP	PIC18LF252	DIP 28	
MICROCHIP	PIC18LF252	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F258	DIP 28	
MICROCHIP	PIC18F442	DIP 40	
MICROCHIP	PIC18F442	PLCC 44	PA44-48U
MICROCHIP	PIC18F442	TQFP 44	PA44QF44D
MICROCHIP	PIC18F448	DIP 40	
MICROCHIP	PIC18F448	PLCC 44	PA44-48U
MICROCHIP	PIC18F448	TQFP 44	PA44QF44D
MICROCHIP	PIC18F452	DIP 40	
MICROCHIP	PIC18F452	PLCC 44	PA44-48U
MICROCHIP	PIC18F452	TQFP 44	PA44QF44D
MICROCHIP	PIC18F458	DIP 40	
MICROCHIP	PIC18F458	PLCC 44	PA44-48U
MICROCHIP	PIC18F458	TQFP 44	PA44QF44D
MICROCHIP	PIC18F1220	DIP 18	
MICROCHIP	PIC18F1220	SOIC 18	PA28SO28D-EO-300
MICROCHIP	PIC18F1220	SSOP 20	PA20SS-P54
MICROCHIP	PIC18F1320	DIP 18	
MICROCHIP	PIC18F1320	SOIC 18	PA28SO28D-EO-300
MICROCHIP	PIC18F1320	SSOP 20	PA20SS-P54
MICROCHIP	PIC18F1320	QFN 28	PA28QFN28D
MICROCHIP	PIC18F2220	DIP 28	
MICROCHIP	PIC18F2220	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F2320	DIP 28	
MICROCHIP	PIC18F2320	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F4220	DIP 40	
MICROCHIP	PIC18F4220	TQFP 44	PA44QF44D
MICROCHIP	PIC18F4320	DIP 40	
MICROCHIP	PIC18F4320	TQFP 44	PA44QF44D
MICROCHIP	PIC18F6520	TQFP 64	PA64TQ40D
MICROCHIP	PIC18F6620	TQFP 64	PA64TQ40D
MICROCHIP	PIC18F6585	PLCC 68	PA68PL40DH
MICROCHIP	PIC18F6680	PLCC 68	PA68PL40DH
MICROCHIP	PIC18F6720	TQFP 64	PA64TQ40D
MICROCHIP	PIC18F8520	TQFP 80	PA80TQ40D
MICROCHIP	PIC18F8410	TQFP 80	PA80TQ40D
MICROCHIP	PIC18F8620	TQFP 80	PA80TQ40D

MICROCHIP	PIC18F8720	TQFP 80	PA80TQ40D
MICROCHIP	PIC18F2221	DIP 28	
MICROCHIP	PIC18F2221	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F2221	QFN 28	PA28QFN28D
MICROCHIP	PIC18F2321	DIP 28	
MICROCHIP	PIC18F2321	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F2321	QFN 28	PA28QFN28D
MICROCHIP	PIC18F2410	DIP 28	
MICROCHIP	PIC18F2410	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F2410	QFN 28	PA28QFN28D
MICROCHIP	PIC18F2420	DIP 28	
MICROCHIP	PIC18F2420	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F2420	QFN 28	PA28QFN28D
MICROCHIP	PIC18F2423	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F2450	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F2455	DIP 28	
MICROCHIP	PIC18F2455	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F2480	DIP 28	
MICROCHIP	PIC18F2480	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F2480	QFN 28	PA28QFN28D
MICROCHIP	PIC18F2510	DIP 28	
MICROCHIP	PIC18F2510	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F2510	QFN 28	PA28QFN28D
MICROCHIP	PIC18F2515	DIP 28	
MICROCHIP	PIC18F2515	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F2520	DIP 28	
MICROCHIP	PIC18F2520	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F2520	QFN 28	PA28QFN28D
MICROCHIP	PIC18F2525	DIP 28	
MICROCHIP	PIC18F2525	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F2550	DIP 28	
MICROCHIP	PIC18F2550	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F2580	DIP 28	
MICROCHIP	PIC18F2580	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F2580	QFN 28	PA28QFN28D
MICROCHIP	PIC18F2585	DIP 28	
MICROCHIP	PIC18F2585	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F2610	DIP 28	
MICROCHIP	PIC18F2610	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F2620	DIP 28	
MICROCHIP	PIC18F2620	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F2680	DIP 28	
MICROCHIP	PIC18F2680	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F4221	DIP 40	
MICROCHIP	PIC18F4221	TQFP 44	PA44QF44D
MICROCHIP	PIC18F4221	QFN 44	PA44QFN44D
MICROCHIP	PIC18F4321	DIP 40	
MICROCHIP	PIC18F4321	TQFP 44	PA44QF44D
MICROCHIP	PIC18F4321	QFN 44	PA44QFN44D
MICROCHIP	PIC18F4410	DIP 40	
MICROCHIP	PIC18F4410	TQFP 44	PA44QF44D
MICROCHIP	PIC18F4410	QFN 44	PA44QFN44D
MICROCHIP	PIC18F4420	DIP 40	
MICROCHIP	PIC18F4420	TQFP 44	PA44QF44D
MICROCHIP	PIC18F4420	QFN 44	PA44QFN44D
MICROCHIP	PIC18F4455	DIP 40	
MICROCHIP	PIC18F4455	TQFP 44	PA44QF44D
MICROCHIP	PIC18F4455	QFN 44	PA44QFN44D
MICROCHIP	PIC18F4480	DIP 40	
MICROCHIP	PIC18F4480	TQFP 44	PA44QF44D
MICROCHIP	PIC18F4480	QFN 44	PA44QFN44D
MICROCHIP	PIC18F4510	DIP 40	
MICROCHIP	PIC18F4510	TQFP 44	PA44QF44D
MICROCHIP	PIC18F4510	QFN 44	PA44QFN44D
MICROCHIP	PIC18F4515	DIP 40	
MICROCHIP	PIC18F4515	TQFP 44	PA44QF44D
MICROCHIP	PIC18F4515	QFN 44	PA44QFN44D
MICROCHIP	PIC18F4520	DIP 40	
MICROCHIP	PIC18F4520	TQFP 44	PA44QF44D
MICROCHIP	PIC18F4520	QFN 44	PA44QFN44D
MICROCHIP	PIC18F45K20	TQFP 44	PA44VQ44D
MICROCHIP	PIC18F4525	DIP 40	
MICROCHIP	PIC18F4525	TQFP 44	PA44QF44D



MICROCHIP	PIC18F4525	QFN 44	PA44QFN44D
MICROCHIP	PIC18F4550	DIP 40	
MICROCHIP	PIC18F4550	TQFP 44	PA44QF44D
MICROCHIP	PIC18F4550	QFN 44	PA44QFN44D
MICROCHIP	PIC18F4580	DIP 40	
MICROCHIP	PIC18F4580	TQFP 44	PA44QF44D
MICROCHIP	PIC18F4580	QFN 44	PA44QFN44D
MICROCHIP	PIC18F4585	DIP 40	
MICROCHIP	PIC18F4585	TQFP 44	PA44QF44D
MICROCHIP	PIC18F4585	QFN 44	PA44QFN44D
MICROCHIP	PIC18F4610	DIP 40	
MICROCHIP	PIC18F4610	TQFP 44	PA44QF44D
MICROCHIP	PIC18F14K22	SSOP 20	PA28SS28D
MICROCHIP	PIC18F46K22	TQFP 44	PA44QF44D
MICROCHIP	PIC18F4610	QFN 44	PA44QFN44D
MICROCHIP	PIC18F4620	DIP 40	
MICROCHIP	PIC18F4620	TQFP 44	PA44QF44D
MICROCHIP	PIC18F4620	QFN 44	PA44QFN44D
MICROCHIP	PIC18F4680	DIP 40	
MICROCHIP	PIC18F4680	TQFP 44	PA44QF44D
MICROCHIP	PIC18F4680	QFN 44	PA44QFN44D
MICROCHIP	PIC18F4685	DIP 40	
MICROCHIP	PIC18LF2221	DIP 28	
MICROCHIP	PIC18LF2221	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2221	QFN 28	PA28QFN28D
MICROCHIP	PIC18LF2321	DIP 28	
MICROCHIP	PIC18LF2321	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2321	QFN 28	PA28QFN28D
MICROCHIP	PIC18LF2410	DIP 28	
MICROCHIP	PIC18LF2410	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2410	QFN 28	PA28QFN28D
MICROCHIP	PIC18LF2420	DIP 28	
MICROCHIP	PIC18LF2420	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2420	QFN 28	PA28QFN28D
MICROCHIP	PIC18LF2455	DIP 28	
MICROCHIP	PIC18LF2455	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2480	DIP 28	
MICROCHIP	PIC18LF2480	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2480	QFN 28	PA28QFN28D
MICROCHIP	PIC18LF2510	DIP 28	
MICROCHIP	PIC18LF2510	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2510	QFN 28	PA28QFN28D
MICROCHIP	PIC18LF2515	DIP 28	
MICROCHIP	PIC18LF2515	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2520	DIP 28	
MICROCHIP	PIC18LF2520	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2520	QFN 28	PA28QFN28D
MICROCHIP	PIC18LF2525	DIP 28	
MICROCHIP	PIC18LF2525	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2550	DIP 28	
MICROCHIP	PIC18LF2550	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2580	DIP 28	
MICROCHIP	PIC18LF2580	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2580	QFN 28	PA28QFN28D
MICROCHIP	PIC18LF2585	DIP 28	
MICROCHIP	PIC18LF2585	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2610	DIP 28	
MICROCHIP	PIC18LF2610	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2620	DIP 28	
MICROCHIP	PIC18LF2620	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2680	DIP 28	
MICROCHIP	PIC18LF2680	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18LF4221	DIP 40	
MICROCHIP	PIC18LF4221	TQFP 44	PA44QF44D
MICROCHIP	PIC18LF4221	QFN 44	PA44QFN44D
MICROCHIP	PIC18LF4321	DIP 40	
MICROCHIP	PIC18LF4321	TQFP 44	PA44QF44D
MICROCHIP	PIC18LF4321	QFN 44	PA44QFN44D
MICROCHIP	PIC18LF4410	DIP 40	
MICROCHIP	PIC18LF4410	TQFP 44	PA44QF44D
MICROCHIP	PIC18LF4410	QFN 44	PA44QFN44D
MICROCHIP	PIC18LF4420	DIP 40	
MICROCHIP	PIC18LF4420	TQFP 44	PA44QF44D

MICROCHIP	PIC18LF4420	QFN 44	PA44QFN44D
MICROCHIP	PIC18LF4455	DIP 40	
MICROCHIP	PIC18LF4455	TQFP 44	PA44QF44D
MICROCHIP	PIC18LF4455	QFN 44	PA44QFN44D
MICROCHIP	PIC18LF4480	DIP 40	
MICROCHIP	PIC18LF4480	TQFP 44	PA44QF44D
MICROCHIP	PIC18LF4480	QFN 44	PA44QFN44D
MICROCHIP	PIC18LF4510	DIP 40	
MICROCHIP	PIC18LF4510	TQFP 44	PA44QF44D
MICROCHIP	PIC18LF4510	QFN 44	PA44QFN44D
MICROCHIP	PIC18LF4515	DIP 40	
MICROCHIP	PIC18LF4515	TQFP 44	PA44QF44D
MICROCHIP	PIC18LF4515	QFN 44	PA44QFN44D
MICROCHIP	PIC18LF4520	DIP 40	
MICROCHIP	PIC18LF4520	TQFP 44	PA44QF44D
MICROCHIP	PIC18LF4520	QFN 44	PA44QFN44D
MICROCHIP	PIC18LF4525	DIP 40	
MICROCHIP	PIC18LF4525	TQFP 44	PA44QF44D
MICROCHIP	PIC18LF4525	QFN 44	PA44QFN44D
MICROCHIP	PIC18LF4550	DIP 40	
MICROCHIP	PIC18LF4550	TQFP 44	PA44QF44D
MICROCHIP	PIC18LF4550	QFN 44	PA44QFN44D
MICROCHIP	PIC18LF4580	DIP 40	
MICROCHIP	PIC18LF4580	TQFP 44	PA44QF44D
MICROCHIP	PIC18LF4580	QFN 44	PA44QFN44D
MICROCHIP	PIC18LF4585	DIP 40	
MICROCHIP	PIC18LF4585	TQFP 44	PA44QF44D
MICROCHIP	PIC18LF4585	QFN 44	PA44QFN44D
MICROCHIP	PIC18LF4610	DIP 40	
MICROCHIP	PIC18LF4610	TQFP 44	PA44QF44D
MICROCHIP	PIC18LF4610	QFN 44	PA44QFN44D
MICROCHIP	PIC18LF4620	DIP 40	
MICROCHIP	PIC18LF4620	TQFP 44	PA44QF44D
MICROCHIP	PIC18LF4620	QFN 44	PA44QFN44D
MICROCHIP	PIC18LF4680	DIP 40	
MICROCHIP	PIC18LF4680	TQFP 44	PA44QF44D
MICROCHIP	PIC18LF4680	QFN 44	PA44QFN44D
MICROCHIP	PIC18F6527	TQFP 64	PA64TQ40D
MICROCHIP	PIC18F6522	TQFP 64	PA64TQ40D
MICROCHIP	PIC18F6627	TQFP 64	PA64TQ40D
MICROCHIP	PIC18F6722	TQFP 64	PA64TQ40D
MICROCHIP	PIC18F8527	TQFP 80	PA80TQ40D
MICROCHIP	PIC18F8622	TQFP 80	PA80TQ40D
MICROCHIP	PIC18F8627	TQFP 80	PA80TQ40D
MICROCHIP	PIC18F8722	TQFP 80	PA80TQ40D
MICROCHIP	PIC18LF6527	TQFP 64	PA64TQ40D
MICROCHIP	PIC18LF6522	TQFP 64	PA64TQ40D
MICROCHIP	PIC18LF6627	TQFP 64	PA64TQ40D
MICROCHIP	PIC18LF6722	TQFP 64	PA64TQ40D
MICROCHIP	PIC18LF8527	TQFP 80	PA80TQ40D
MICROCHIP	PIC18LF8622	TQFP 80	PA80TQ40D
MICROCHIP	PIC18LF8627	TQFP 80	PA80TQ40D
MICROCHIP	PIC18LF8722	TQFP 80	PA80TQ40D
MICROCHIP	PIC18LF6520	TQFP 64	PA64TQ40D
MICROCHIP	PIC18LF6620	TQFP 64	PA64TQ40D
MICROCHIP	PIC18LF6585	PLCC 68	PA68PL40DH
MICROCHIP	PIC18LF6680	PLCC 68	PA68PL40DH
MICROCHIP	PIC18LF6720	TQFP 64	PA64TQ40D
MICROCHIP	PIC18LF8520	TQFP 80	PA80TQ40D
MICROCHIP	PIC18LF8620	TQFP 80	PA80TQ40D
MICROCHIP	PIC18LF8720	TQFP 80	PA80TQ40D
MICROCHIP	PIC18F24J10	DIP 28	
MICROCHIP	PIC18F24J10	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F24J10	SSOP 28	PA28SS28D
MICROCHIP	PIC18F24J10	QFN 28	AS-28-28-02ML-6
MICROCHIP	PIC18F25J10	DIP 28	
MICROCHIP	PIC18F25J10	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18F25J10	SSOP 28	PA28SS28D
MICROCHIP	PIC18F25J10	QFN 28	AS-28-28-02ML-6
MICROCHIP	PIC18LF24J10	DIP 28	
MICROCHIP	PIC18LF24J10	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18LF24J10	SSOP 28	PA28SS28D
MICROCHIP	PIC18LF24J10	QFN 28	AS-28-28-02ML-6

MICROCHIP	PIC18LF25J10	DIP 28	
MICROCHIP	PIC18LF25J10	SOIC 28	PA28SO28D-EO-300
MICROCHIP	PIC18LF25J10	SSOP 28	PA28SS28D
MICROCHIP	PIC18LF25J10	QFN 28	AS-28-28-02ML-6
MICROCHIP	PIC18F44J10	DIP 40	
MICROCHIP	PIC18F44J10	TQFP 44	PA44VQ44D
MICROCHIP	PIC18F45J10	DIP 40	
MICROCHIP	PIC18F45J10	TQFP 44	PA44VQ44D
MICROCHIP	PIC18LF44J10	DIP 40	
MICROCHIP	PIC18LF44J10	TQFP 44	PA44VQ44D
MICROCHIP	PIC18LF45J10	DIP 40	
MICROCHIP	PIC18LF45J10	TQFP 44	PA44VQ44D
MICROCHIP	PIC24HJ128GP206A	QFP 64	PA64TQ48D
NOVATEK MICROELECTRONICS	NT68F63LA	PLCC 44	HA44PL48DZ4
NOVATEK MICROELECTRONICS	NT68F63LG	PLCC 44	HA44PL48DZ4
NOVATEK MICROELECTRONICS	NT68F631L	PLCC 44	HA44PL48DZ4
NOVATEK MICROELECTRONICS	NT68F632L	PLCC 44	HA44PL48DZ4
MEGAWIN	MPC89L51AE	DIP 40	
MEGAWIN	MPC89L51AP	PLCC 44	PA44-48U
MEGAWIN	MPC89L51AF	PQFP 44	PA44PQ48D
MEGAWIN	MPC89E51AE	DIP 40	
MEGAWIN	MPC89E51AP	PLCC 44	PA44-48U
MEGAWIN	MPC89E51AF	PQFP 44	PA44PQ48D
MEGAWIN	MPC89L52AE	DIP 40	
MEGAWIN	MPC89L52AP	PLCC 44	PA44-48U
MEGAWIN	MPC89L52AF	PQFP 44	PA44PQ48D
MEGAWIN	MPC89E52AE	DIP 40	
MEGAWIN	MPC89E52AP	PLCC 44	PA44-48U
MEGAWIN	MPC89E52AF	PQFP 44	PA44PQ48D
MEGAWIN	MPC89L53AE	DIP 40	
MEGAWIN	MPC89L53AP	PLCC 44	PA44-48U
MEGAWIN	MPC89L53AF	PQFP 44	PA44PQ48D
MEGAWIN	MPC89E53AE	DIP 40	
MEGAWIN	MPC89E53AP	PLCC 44	PA44-48U
MEGAWIN	MPC89E53AF	PQFP 44	PA44PQ48D
MEGAWIN	MPC89L54AE	DIP 40	
MEGAWIN	MPC89L54AP	PLCC 44	PA44-48U
MEGAWIN	MPC89L54AF	PQFP 44	PA44PQ48D
MEGAWIN	MPC89E54AE	DIP 40	
MEGAWIN	MPC89E54AP	PLCC 44	PA44-48U
MEGAWIN	MPC89E54AF	PQFP 44	PA44PQ48D
MEGAWIN	MPC89L58AE	DIP 40	
MEGAWIN	MPC89L58AP	PLCC 44	PA44-48U
MEGAWIN	MPC89L58AF	PQFP 44	PA44PQ48D
MEGAWIN	MPC89E58AE	DIP 40	
MEGAWIN	MPC89E58AP	PLCC 44	PA44-48U
MEGAWIN	MPC89E58AF	PQFP 44	PA44PQ48D
MEGAWIN	MPC89L515AE	DIP 40	
MEGAWIN	MPC89L515AP	PLCC 44	PA44-48U
MEGAWIN	MPC89L515AF	PQFP 44	PA44PQ48D
MEGAWIN	MPC89E515AE	DIP 40	
MEGAWIN	MPC89E515AP	PLCC 44	PA44-48U
MEGAWIN	MPC89E515AF	PQFP 44	PA44PQ48D
MITSUBISHI	M37531E4	DIP 32	PCA7435SP
MITSUBISHI	M37531E8	DIP 32	PCA7435SP
MOTOROLA	MC68705P3	DIP 28	
MOTOROLA	MC68705P5	DIP 28	
MOTOROLA	MC68705R3	DIP 40	
MOTOROLA	MC68705R5	DIP 40	
MOTOROLA	MC68705U3	DIP 40	
MOTOROLA	MC68705U5	DIP 40	
MOTOROLA	MC68HC705J1A	DIP 20	
MOTOROLA	MC68HC705J1A	SOP 20	PA28SO28D-EO-300
MOTOROLA	MC68HC705KJ1	DIP 16	
MOTOROLA	MC68HC705KJ1	SOP 16	PA28SO28D-EO-300
MOTOROLA	MC68HC705C4AP	DIP 40	
MOTOROLA	MC68HC705C4AFN	PLCC 44	PA44-48U
MOTOROLA	MC68HC705C8P	DIP 40	
MOTOROLA	MC68HC705C8FN	PLCC 44	PA44-48U
MOTOROLA	MC68HC705C8AP	DIP 40	
MOTOROLA	MC68HC705C8AFN	PLCC 44	PA44-48U
MOTOROLA	MC68HC705C8AFB	QFP 44	PA44QF44D
MOTOROLA	MC68HC705C9P	DIP 40	

MOTOROLA	MC68HC705C9FN	PLCC 44	PA44-48U
MOTOROLA	MC68HC705C9AP	DIP 40	
MOTOROLA	MC68HC705C9AFN	PLCC 44	PA44-48U
MOTOROLA	MC68HC705C9AFB	QFP 44	PA44QF44D
MOTOROLA	MC68HC705C9ACFN	PLCC 44	PA44-48U
MOTOROLA	MC68HC705D9P	DIP 40	
MOTOROLA	MC68HC705D9FN	PLCC 44	PA44-48U
MOTOROLA	MC68HC705D32P	DIP 40	
MOTOROLA	MC68HC705D32FN	PLCC 44	PA44-48U
MOTOROLA	MC68HC705D32AP	DIP 40	
MOTOROLA	MC68HC705D32AFN	PLCC 44	PA44-48U
MOTOROLA	MC68HC05B16FN	PLCC 52	PA52-48-01P-Y
MOTOROLA	MC68HC05B16CFN	PLCC 52	PA52-48-01P-Y
MOTOROLA	MC68HC05B16VFN	PLCC 52	PA52-48-01P-Y
MOTOROLA	MC68HC05B16MFN	PLCC 52	PA52-48-01P-Y
MOTOROLA	MC68HC705B16FN	PLCC 52	PA52-48-01P-Y
MOTOROLA	MC68HC705B16CFN	PLCC 52	PA52-48-01P-Y
MOTOROLA	MC68HC705B16VFN	PLCC 52	PA52-48-01P-Y
MOTOROLA	MC68HC705B16MFN	PLCC 52	PA52-48-01P-Y
MOTOROLA	MC68HC05B16NFN	PLCC 52	PA52-48-01P-Y
MOTOROLA	MC68HC05B16NCFN	PLCC 52	PA52-48-01P-Y
MOTOROLA	MC68HC05B16NVFN	PLCC 52	PA52-48-01P-Y
MOTOROLA	MC68HC05B16NMFN	PLCC 52	PA52-48-01P-Y
MOTOROLA	MC68HC705B16NFN	PLCC 52	PA52-48-01P-Y
MOTOROLA	MC68HC705B16NCFN	PLCC 52	PA52-48-01P-Y
MOTOROLA	MC68HC705B16NVFN	PLCC 52	PA52-48-01P-Y
MOTOROLA	MC68HC705B16NMFN	PLCC 52	PA52-48-01P-Y
MOTOROLA	MC68HC705B16NCFN	PLCC 52	PA52-48-01P-Y
MOTOROLA	MC68HC705B16NVFN	PLCC 52	PA52-48-01P-Y
MOTOROLA	MC68HC705B16NMFN	PLCC 52	PA52-48-01P-Y
MOTOROLA	MC68HC705B16NCFN	PLCC 52	PA52-48-01P-Y
MOTOROLA	MC68HC705B16NVFN	PLCC 52	PA52-48-01P-Y
MOTOROLA	MC68HC705B16NMFN	PLCC 52	PA52-48-01P-Y
MOTOROLA	MC68HC705B32FN	PLCC 52	PA52-48-01P-Y
MOTOROLA	MC68HC05B16FN	PLCC 52	PA52PL48DF
MOTOROLA	MC68HC05B16CFN	PLCC 52	PA52PL48DF
MOTOROLA	MC68HC05B16VFN	PLCC 52	PA52PL48DF
MOTOROLA	MC68HC05B16MFN	PLCC 52	PA52PL48DF
MOTOROLA	MC68HC705B16FN	PLCC 52	PA52PL48DF
MOTOROLA	MC68HC705B16CFN	PLCC 52	PA52PL48DF
MOTOROLA	MC68HC705B16VFN	PLCC 52	PA52PL48DF
MOTOROLA	MC68HC705B16MFN	PLCC 52	PA52PL48DF
MOTOROLA	MC68HC05B16NFN	PLCC 52	PA52PL48DF
MOTOROLA	MC68HC05B16NCFN	PLCC 52	PA52PL48DF
MOTOROLA	MC68HC05B16NVFN	PLCC 52	PA52PL48DF
MOTOROLA	MC68HC05B16NMFN	PLCC 52	PA52PL48DF
MOTOROLA	MC68HC705B16NFN	PLCC 52	PA52PL48DF
MOTOROLA	MC68HC705B16NCFN	PLCC 52	PA52PL48DF
MOTOROLA	MC68HC705B16NVFN	PLCC 52	PA52PL48DF
MOTOROLA	MC68HC705B16NMFN	PLCC 52	PA52PL48DF
MOTOROLA	MC68HC705B32FN	PLCC 52	PA52PL48DF
MOTOROLA	MC68HC705JJ7	DIP 20	
FREESCALE	MC68HC705JJ7	SOIC 20	PA28SO28D-EO-300
MOTOROLA	MC68HC705JP7	DIP 28	
MOTOROLA	XC68HC705JP7	DIP 28	
MOTOROLA	MC68HC705P6P	DIP 28	
MOTOROLA	MC68HC705P6DW	SOIC 28	PA28SO28D-EO-300
MOTOROLA	MC68HC705P6AP	DIP 28	
MOTOROLA	MC68HC705P6ADW	SOIC 28	PA28SO28D-EO-300
MOTOROLA	MC68HC705P6ACP	DIP 28	
FREESCALE	MC705P6ACPE	DIP 28	
FREESCALE	MC705P6ACDWE	SOIC 28	PA28SO28D-EO-300
MOTOROLA	MC68HC705P6ACDW	SOIC 28	PA28SO28D-EO-300
MOTOROLA	MC68HC705P9P	DIP 28	
MOTOROLA	MC68HC705P9DW	SOIC 28	PA28SO28D-EO-300
MOTOROLA	MC68HC705P9CP	DIP 28	
MOTOROLA	MC68HC705P9CDW	SOIC 28	PA28SO28D-EO-300
MOTOROLA	MC68HC705SR3	DIP 40	
MOTOROLA	MC68HC705SR3	SDIP 42	PA42SD42D
MOTOROLA	MC68HC705SR3	QFP 44	PA44QF44D
MOTOROLA	MC68HC705X4DW	SOP 28	PA28-S01-08-6
MOTOROLA	MC68HC705X4CDW	SOP 28	PA28-S01-08-6
MOTOROLA	MC68HC11A1P	DIP 48	
MOTOROLA	MC68HCP11A1P	DIP 48	
MOTOROLA	MC68HC11A1FN	PLCC 52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC11A8P	DIP 48	
MOTOROLA	MC68HC11A8FN	PLCC 52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC11E1FN	PLCC 52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC11E9CFN2	PLCC 52	PA52-48A-1/HA52PL48DB

MOTOROLA	MC68HC11E9CFN3	PLCC 52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC11E9VFN2	PLCC 52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC11E9MFN2	PLCC 52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC11E9CFU2	QFP 64	PA64TQ40D-HCx11E
MOTOROLA	MC68HC11E9CFU3	QFP 64	PA64TQ40D-HCx11E
MOTOROLA	MC68HC11E9CVU2	QFP 64	PA64TQ40D-HCx11E
MOTOROLA	MC68HC11E9CMU2	QFP 64	PA64TQ40D-HCx11E
MOTOROLA	MC68HC11F1FN	PLCC 68	PA68-48E
MOTOROLA	MC68HC11K4CFN	PLCC 84	PA84-48C
MOTOROLA	MC68HC11K4CFN2	PLCC 84	PA84-48C
MOTOROLA	MC68HC11K4CFN3	PLCC 84	PA84-48C
MOTOROLA	MC68HC11K4CFN4	PLCC 84	PA84-48C
MOTOROLA	MC68HC11K4VFN2	PLCC 84	PA84-48C
MOTOROLA	MC68HC11K4VFN3	PLCC 84	PA84-48C
MOTOROLA	MC68HC11K4VFN4	PLCC 84	PA84-48C
MOTOROLA	MC68HC11K4MFN2	PLCC 84	PA84-48C
MOTOROLA	MC68HC11K4MFN3	PLCC 84	PA84-48C
MOTOROLA	MC68HC11K4MFN4	PLCC 84	PA84-48C
MOTOROLA	MC68HC11P2FN	PLCC 84	PA84-48D
MOTOROLA	MC68HC711D3S	DIP 40	
MOTOROLA	MC68HC711D3P	DIP 40	
MOTOROLA	MC68HC711D3CP	DIP 40	
MOTOROLA	MC68HC711D3FS	PLCC 44	PA44-48U
MOTOROLA	MC68HC711D3FN	PLCC 44	PA44-48U
MOTOROLA	MC68HC711D3CFN	PLCC 44	PA44-48U
MOTOROLA	MC68HC711D3CFNE2	PLCC 44	PA44-48U
MOTOROLA	MC68HC711E9CFN2	PLCC 52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC711E9CFN3	PLCC 52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC711E9VFN2	PLCC 52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC711E9MFN2	PLCC 52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC711E9CFU2	QFP 64	PA64TQ40D-HCx11E
MOTOROLA	MC68HC711E9CFU3	QFP 64	PA64TQ40D-HCx11E
MOTOROLA	MC68HC711E9CVU2	QFP 64	PA64TQ40D-HCx11E
MOTOROLA	MC68HC711E9CMU2	QFP 64	PA64TQ40D-HCx11E
MOTOROLA	MC68S711E9CFN2	PLCC 52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC11E20FN3	PLCC 52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC11E20CFN2	PLCC 52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC11E20CFN3	PLCC 52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC11E20VFN2	PLCC 52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC11E20MFN2	PLCC 52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC711E20FN3	PLCC 52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC711E20CFN2	PLCC 52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC711E20CFN3	PLCC 52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC711E20VFN2	PLCC 52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC711E20MFN2	PLCC 52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC711K4CFN	PLCC 84	PA84-48C
MOTOROLA	MC68HC711K4CFN2	PLCC 84	PA84-48C
MOTOROLA	MC68HC711K4CFN3	PLCC 84	PA84-48C
MOTOROLA	MC68HC711K4CFN4	PLCC 84	PA84-48C
MOTOROLA	MC68HC711K4VFN2	PLCC 84	PA84-48C
MOTOROLA	MC68HC711K4VFN3	PLCC 84	PA84-48C
MOTOROLA	MC68HC711K4VFN4	PLCC 84	PA84-48C
MOTOROLA	MC68HC711K4MFN2	PLCC 84	PA84-48C
MOTOROLA	MC68HC711K4MFN3	PLCC 84	PA84-48C
MOTOROLA	MC68HC711K4MFN4	PLCC 84	PA84-48C
MOTOROLA	MC68HC11L6FN	PLCC 68	PA68-48D
MOTOROLA	MC68HC711L6FN	PLCC 68	PA68-48D
MOTOROLA	MC68HC11L6FU	QFP 64	PA64QF48DF
MOTOROLA	MC68HC711L6FU	QFP 64	PA64QF48DF
MOTOROLA	MC68HC711P2FN	PLCC 84	PA84-48D
MOTOROLA	MC68HC711KS2VFN	PLCC 68	PA68-48H
MOTOROLA	MC68HC811E2FN	PLCC 52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC811E2CFN	PLCC 52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC811E2P	DIP 48	
MOTOROLA	MC68HC908JK1CP	DIP 20	
MOTOROLA	MC68HC908JK1MP	DIP 20	
MOTOROLA	MC68HC908JK1CDW	SOP 20	PA28SO28D-EO-300
MOTOROLA	MC68HC908JK1MDW	SOP 20	PA28SO28D-EO-300
MOTOROLA	MC68HC908JK3CP	DIP 20	
MOTOROLA	MC68HC908JK3MP	DIP 20	
MOTOROLA	MC68HC908JK3CDW	SOP 20	PA28SO28D-EO-300
MOTOROLA	MC68HC908JK3MDW	SOP 20	PA28SO28D-EO-300
MOTOROLA	MC68HC908JL3CP	DIP 28	

MOTOROLA	MC68HC908JL3MP	DIP 28	
MOTOROLA	MC68HC908JL3CDW	SOP 28	PA28SO28D-EO-300
MOTOROLA	MC68HC908JL3MDW	SOP 28	PA28SO28D-EO-300
MOTOROLA	MC68HC908GP32CP	DIP 40	
MOTOROLA	MC68HC908GP32VP	DIP 40	
MOTOROLA	MC68HC908GP32MP	DIP 40	
MOTOROLA	MC68HC908GP32CB	SDIP 42	PA-MACH4
MOTOROLA	MC68HC908GP32VB	SDIP 42	PA-MACH4
MOTOROLA	MC68HC908GP32MB	SDIP 42	PA-MACH4
MOTOROLA	MC68HC908GP32CFB	TQFP 44	PA44QF44D
MOTOROLA	MC68HC908GP32VFB	TQFP 44	PA44QF44D
MOTOROLA	MC68HC908GP32MFB	TQFP 44	PA44QF44D
MOTOROLA	MC68HC908GT8CB	SDIP 42	PA-MACH4
MOTOROLA	MC68HC908GT8CFB	TQFP 44	PA44QF44D
MOTOROLA	MC68HC908GT16CB	SDIP 42	PA-MACH4
MOTOROLA	MC68HC908GT16CFB	TQFP 44	PA44QF44D
MOTOROLA	MC68HC908QT1CP	DIP 8	
MOTOROLA	MC68HC908QT1CDW	SOIC 8	PA20SO20D-EO-210
MOTOROLA	MC68HC908QT1CFQ	DFN 8	PA8SON8D
MOTOROLA	MC68HC908QT2CP	DIP 8	
MOTOROLA	MC68HC908QT2CDW	SOIC 8	PA20SO20D-EO-210
MOTOROLA	MC68HC908QT2CFQ	DFN 8	PA8SON8D
MOTOROLA	MC68HC908QT4CP	DIP 8	
MOTOROLA	MC68HC908QT4CDW	SOIC 8	PA20SO20D-EO-210
MOTOROLA	MC68HC908QT4CFQ	DFN 8	PA8SON8D
MOTOROLA	MC68HC908QY1CP	DIP 16	
MOTOROLA	MC68HC908QY1CDW	SOIC 16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QY1CDT	TSSOP 16	PA24TSS24D
MOTOROLA	MC68HC908QY2CP	DIP 16	
MOTOROLA	MC68HC908QY2CDW	SOIC 16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QY2CDT	TSSOP 16	PA24TSS24D
MOTOROLA	MC68HC908QY4CP	DIP 16	
MOTOROLA	MC68HC908QY4CDW	SOIC 16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QY4CDT	TSSOP 16	PA24TSS24D
MOTOROLA	MC68HC908QY8CP	DIP 16	
MOTOROLA	MC68HC908QY8CDW	SOIC 16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QY8CDT	TSSOP 16	PA24TSS24D
MOTOROLA	MC68HC908QB4CP	DIP 16	
MOTOROLA	MC68HC908QB4CDW	SOIC 16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QB4CDT	TSSOP 16	PA24TSS24D
MOTOROLA	MC68HC908QB8CP	DIP 16	
MOTOROLA	MC68HC908QB8CDW	SOIC 16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QB8CDT	TSSOP 16	PA24TSS24D
MOTOROLA	MC68HC908LB8CPE	DIP 20	
MOTOROLA	MC68HC908LB8VPE	DIP 20	
MOTOROLA	MC68HC908LB8MPE	DIP 20	
MOTOROLA	MC68HC908LB8CDWE	SOIC 20	PA28SO28D-EO-300
MOTOROLA	MC68HC908LB8VDWE	SOIC 20	PA28SO28D-EO-300
MOTOROLA	MC68HC908LB8MDWE	SOIC 20	PA28SO28D-EO-300
MOTOROLA	MC68HC908QL2CDW	SOIC 16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QL2VDW	SOIC 16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QL2MDW	SOIC 16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QL2CDT	TSSOP 16	PA24TSS24D
MOTOROLA	MC68HC908QL2VDT	TSSOP 16	PA24TSS24D
MOTOROLA	MC68HC908QL2MDT	TSSOP 16	PA24TSS24D
MOTOROLA	MC68HC908QL3CDW	SOIC 16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QL3VDW	SOIC 16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QL3MDW	SOIC 16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QL3CDT	TSSOP 16	PA24TSS24D
MOTOROLA	MC68HC908QL3VDT	TSSOP 16	PA24TSS24D
MOTOROLA	MC68HC908QL3MDT	TSSOP 16	PA24TSS24D
MOTOROLA	MC68HC908QL4CDW	SOIC 16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QL4VDW	SOIC 16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QL4MDW	SOIC 16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QL4CDT	TSSOP 16	PA24TSS24D
MOTOROLA	MC68HC908QL4VDT	TSSOP 16	PA24TSS24D
MOTOROLA	MC68HC908QL4MDT	TSSOP 16	PA24TSS24D
MOTOROLA	MC9S08GT16CFB	TQFP 44	PA44QF44D
MOTOROLA	MC9S08GT32CFB	TQFP 44	PA44QF44D
MOTOROLA	MC9S08AW16	TQFP 44	PA44QF44D
MOTOROLA	MC9S08AC8	TQFP 32	PA32TQ32D
MOTOROLA	MC9S08DV32	TQFP 32	PA32TQ32D
NATIONAL	COP8SAA716	DIP 16	

NATIONAL	COP8SAA720	DIP 20	
NATIONAL	COP8SAA728	DIP 28	
NATIONAL	COP8SAB720	DIP 20	
NATIONAL	COP8SAB728	DIP 28	
NATIONAL	COP8SAC720	DIP 20	
NATIONAL	COP8SAC728	DIP 28	
NATIONAL	COP8SAC740	DIP 40	
NATIONAL	COP8SAC744	PLCC 44	PA44-48U
NATIONAL	COP8SGE720	DIP 20	
NATIONAL	COP8SGE728	DIP 28	
NATIONAL	COP8SGE740	DIP 40	
NATIONAL	COP8SGE744	PLCC 44	PA44-48U
NATIONAL	COP8SGR720	DIP 20	
NATIONAL	COP8SGR728	DIP 28	
NATIONAL	COP8SGR740	DIP 40	
NATIONAL	COP8SGR744	PLCC 44	PA44-48U
NEC	8749H	DIP 40	
NEC	uPD78P054GK	QFP 80	PA80QF48DD
NEC	uPD78F0546	LQFP 80	PA80QF48DC
NEC	uPD78F9234	SSOP 30	PA30SS30D
SAMSUNG	KS57P0408	QFP 44	SS-QFP44
SAMSUNG	KS57P0504	SDIP 30	SS-SDIP
SAMSUNG	KS57P0504	SOP 32	SS-SOP
SAMSUNG	KS57P0616	QFP 44	SS-QFP44
SAMSUNG	KS57P0616	SDIP 42	SS-SDIP
SAMSUNG	KS57P21516	QFP 100	SS-QFP100
SAMSUNG	KS57P21208	QFP 44	SS-QFP44
SAMSUNG	KS57P21208	SDIP 42	SS-SDIP
SAMSUNG	KS57P21408	QFP 100	SS-QFP100
SAMSUNG	KS57P21632	QFP 100	SS-QFP100
SAMSUNG	KS57P21708	QFP 64	SS-QFP64
SAMSUNG	KS57P21832	QFP 100	SS-QFP100
SAMSUNG	KS57P2304	QFP 64	SS-QFP64
SAMSUNG	KS57P2308	QFP 80	SS-QFP80
SAMSUNG	KS57P2316	QFP 80	SS-QFP80
SAMSUNG	KS57P2916	QFP 80	SS-QFP80
SAMSUNG	KS57P3204	QFP 64	SS-QFP64
SAMSUNG	KS57P4104	QFP 44	SS-QFP44
SAMSUNG	KS57P4104	SDIP 42	SS-SDIP
SAMSUNG	KS57P4204	SDIP 30	SS-SDIP
SAMSUNG	KS57P4204	SOP 28	SS-SOP
SAMSUNG	KS57P4304	QFP 44	SS-QFP44
SAMSUNG	KS57P4304	SDIP 42	SS-SDIP
SAMSUNG	KS57P5116	SDIP 64	SS-SDIP
SAMSUNG	KS57P5208	SDIP 42	SS-SDIP
SAMSUNG	KS57P5208	QFP 44	SS-QFP44
SAMSUNG	KS57P5308	SDIP 30	SS-SDIP
SAMSUNG	KS57P5308	SOP 32	SS-SOP
SAMSUNG	KS57P5312	SOP 32	SS-SOP
SAMSUNG	KS57P5312	SDIP 30	SS-SDIP
SAMSUNG	KS57P5404	SDIP 24	SS-SDIP
SAMSUNG	KS57P5404	SOP 24	SS-SOP
SAMSUNG	KS57P5404	SOP 24	PA28SO28D-EO-300
SAMSUNG	KS57P5532	SDIP 64	SS-SDIP
SAMSUNG	KS57P5616	QFP 100	SS-QFP100
SAMSUNG	KS86F4404	DIP 8	
SAMSUNG	KS86F4504	DIP 16	
SAMSUNG	KS86F4504	DIP 20	
SAMSUNG	KS86F4504	SOP 20	PA28SO28D-EO-300
SAMSUNG	KS86P4004	SDIP 30	SS-SDIP
SAMSUNG	KS86P4004	SOP 32	SS-SOP
SAMSUNG	KS86P4104	SDIP 24	SS-SDIP
SAMSUNG	KS86P4104	SOP 24	SS-SOP
SAMSUNG	KS86P4208	SDIP 30	SS-SDIP
SAMSUNG	KS86P4208	SOP 28	SS-SOP
SAMSUNG	KS86P4208	SOP 32	SS-SOP
SAMSUNG	KS86P4304	DIP 20	SS-DIP
SAMSUNG	KS86P6008	QFP 44	SS-QFP44
SAMSUNG	KS86P6008	SDIP 42	SS-SDIP
SAMSUNG	KS86P6104	DIP 20	SS-DIP
SAMSUNG	KS86P6104	SOP 24	SS-SOP
SAMSUNG	KS86P6408	QFP 44	SS-QFP44
SAMSUNG	KS86P6408	SDIP 42	SS-SDIP

SAMSUNG	KS88P0716	SDIP 64	SS-SDIP
SAMSUNG	KS88P0716	QFP 64	SS-QFP64
SAMSUNG	KS88P2148	QFP 80	SS-QFP80
SAMSUNG	KS88P2416	QFP 80	SS-QFP80
SAMSUNG	KS88P2432	QFP 80	SS-QFP80
SAMSUNG	KS88P4504	QFP 80	SS-QFP80
SAMSUNG	KS88P4632	SDIP 64	SS-SDIP
SAMSUNG	KS88P4632	QFP 64	SS-QFP64
SAMSUNG	KS88P4716	QFP 44	SS-QFP44
SAMSUNG	KS88P4716	SDIP 42	SS-SDIP
SAMSUNG	KS88P6116	QFP 44	SS-QFP44
SAMSUNG	KS88P6232	SDIP 42	SS-SDIP
SAMSUNG	KS88P8324	SDIP 42	SS-SDIP
SAMSUNG	KS88C8432	SDIP 42	SS-SDIP
SAMSUNG	KS88P8432	SDIP 42	SS-SDIP
SAMSUNG	KS88P0416	SOP 32	SS-SOP
SAMSUNG	KS88P0416	SDIP 32	SS-SDIP
SAMSUNG	KS88P0416	DIP 40	
SAMSUNG	KS88P0424	SOP 32	SS-SOP
SAMSUNG	KS88P0424	SDIP 32	SS-SDIP
SAMSUNG	KS88P0424	DIP 40	
SAMSUNG	KS88P0424	DIP 40	
SAMSUNG	S3P80A4	SOP 24	PA28SO28D-EO-300
SAMSUNG	S3P80A8	SOP 24	PA28SO28D-EO-300
SAMSUNG	S3P80A5	SOP 24	PA28SO28D-EO-300
SAMSUNG	S3P80B4	SOP 24	PA28SO28D-EO-300
SAMSUNG	S3P80B8	SOP 24	PA28SO28D-EO-300
SAMSUNG	S3P80B5	SOP 24	PA28SO28D-EO-300
ST	ST62E20	DIP 20	
ST	ST62E20B	DIP 20	
ST	ST62E25	DIP 28	
ST	ST62E25B	DIP 28	
ST	ST62E60	DIP 20	
ST	ST62E60B	DIP 20	
ST	ST62E65	DIP 28	
ST	ST62E65B	DIP 28	
ST	ST62T10	DIP 20	
ST	ST62T10B	DIP 20	
ST	ST62T15	DIP 28	
ST	ST62T15B	DIP 28	
ST	ST62T20	DIP 20	
ST	ST62T20B	DIP 20	
ST	ST62T25	DIP 28	
ST	ST62T25B	DIP 28	
ST	ST62T60	DIP 20	
ST	ST62T60B	DIP 20	
ST	ST62T65	DIP 28	
ST	ST62T65B	DIP 28	
ST	ST62E01C	DIP 16	
ST	ST62E03C	DIP 16	
ST	ST62E20C	DIP 20	
ST	ST62E25C	DIP 28	
ST	ST62E28C	DIP 28	
ST	ST62E30B	DIP 28	
ST	ST62E60C	DIP 20	
ST	ST62E65C	DIP 28	
ST	ST62T00C	DIP 16	
ST	ST62T01C	DIP 16	
ST	ST62T03C	DIP 16	
ST	ST62T08C	DIP 20	
ST	ST62T09C	DIP 20	
ST	ST62T10C	DIP 20	
ST	ST62T15C	DIP 28	
ST	ST62T20C	DIP 20	
ST	ST62T25C	DIP 28	
ST	ST62T28C	DIP 28	
ST	ST62T30B	DIP 28	
ST	ST62T53C	DIP 20	
ST	ST62T55C	DIP 28	
ST	ST62T60C	DIP 20	
ST	ST62T63C	DIP 20	
ST	ST62T65C	DIP 28	
ST	ST62T00C	SOIC 16	PA28SO28D-EO-300



ST	ST62T01C	SOIC 16	PA28SO28D-EO-300
ST	ST62T03C	SOIC 16	PA28SO28D-EO-300
ST	ST62T08C	SOIC 20	PA28SO28D-EO-300
ST	ST62T09C	SOIC 20	PA28SO28D-EO-300
ST	ST62T10C	SOIC 20	PA28SO28D-EO-300
ST	ST62T15C	SOIC 28	PA28SO28D-EO-300
ST	ST62T20C	SOIC 20	PA28SO28D-EO-300
ST	ST62T25C	SOIC 28	PA28SO28D-EO-300
ST	ST62T28C	SOIC 28	PA28SO28D-EO-300
ST	ST62T30B	SOIC 28	PA28SO28D-EO-300
ST	ST62T53C	SOIC 20	PA28SO28D-EO-300
ST	ST62T55C	SOIC 28	PA28SO28D-EO-300
ST	ST62T60C	SOIC 20	PA28SO28D-EO-300
ST	ST62T63C	SOIC 20	PA28SO28D-EO-300
ST	ST62T65C	SOIC 28	PA28SO28D-EO-300
ST	ST62T00C	SSOP 16	PA20SO20D-EO-210
ST	ST62T01C	SSOP 16	PA20SO20D-EO-210
ST	ST62T03C	SSOP 16	PA20SO20D-EO-210
ST	ST62T08C	SSOP 20	PA20SO20D-EO-210
ST	ST62T09C	SSOP 20	PA20SO20D-EO-210
ST	ST62T10C	SSOP 20	PA20SO20D-EO-210
ST	ST62T15C	SSOP 28	PA28SO28D-EO-210
ST	ST62T20C	SSOP 20	PA20SO20D-EO-210
ST	ST62T25C	SSOP 28	PA28SO28D-EO-210
ST	ST62T28C	SSOP 28	PA28SO28D-EO-210
ST	ST62T55C	SSOP 28	PA28SO28D-EO-210
ST	ST62T65C	SSOP 28	PA28SO28D-EO-210
ST	ST72F260G1B	SDIP 32	PA32SD32D
ST	ST72F260G2B	SDIP 32	PA32SD32D
ST	ST72F262G1B	SDIP 32	PA32SD32D
ST	ST72F262G2B	SDIP 32	PA32SD32D
ST	ST72F264G1B	SDIP 32	PA32SD32D
ST	ST72F264G2B	SDIP 32	PA32SD32D
ST	ST72F260G1M	SOIC 28	PA28SO28D-EO-300
ST	ST72F260G2M	SOIC 28	PA28SO28D-EO-300
ST	ST72F262G1M	SOIC 28	PA28SO28D-EO-300
ST	ST72F262G2M	SOIC 28	PA28SO28D-EO-300
ST	ST72F264G1M	SOIC 28	PA28SO28D-EO-300
ST	ST72F264G2M	SOIC 28	PA28SO28D-EO-300
ST	STM8S103F2	TSSOP 20	HA20TSS48DB
ST	STM8S103F3	TSSOP 20	HA20TSS48DB
ST	STM8S103K3	LQFP 32	PA32LQ48D
ST	STM8S105S4T	LQFP 44	PA44LQ48D
ST	STM8S105C4T	LQFP 48	PA48LQ48DC
ST	STM8S207C6	LQFP 48	PA48LQ48DC
CYROD	CRD89C51RD	PLCC 44	PA44-48U
SYNCMOS	SM5964	DIP 40	
SYNCMOS	SM5964	PLCC 44	PA44-48U
SYNCMOS	SM5964	QFP 44	PA44QF44D
SYNCMOS	SM8951	DIP 40	
SYNCMOS	SM8951	PLCC 44	PA44-48U
SYNCMOS	SM8952	DIP 40	
SYNCMOS	SM8952	PLCC 44	PA44-48U
SYNCMOS	SM8954	DIP 40	
SYNCMOS	SM8954	PLCC 44	PA44-48U
SYNCMOS	SM8958	DIP 40	
SYNCMOS	SM8958	PLCC 44	PA44-48U
SYNCMOS	SM8951A	DIP 40	
SYNCMOS	SM8951A	PLCC 44	PA44-48U
SYNCMOS	SM8951A	QFP 44	PA44QF44D
SYNCMOS	SM8952A	DIP 40	
SYNCMOS	SM8952A	PLCC 44	PA44-48U
SYNCMOS	SM8952A	QFP 44	PA44QF44D
SYNCMOS	SM89516	DIP 40	
SYNCMOS	SM89516	PLCC 44	PA44-48U
SYNCMOS	SM89516	QFP 44	PA44QF44D
SYNCMOS	SM8954A	DIP 40	
SYNCMOS	SM8954A	PLCC 44	PA44-48U
SYNCMOS	SM8954A	QFP 44	PA44QF44D
SYNCMOS	SM8958A	DIP 40	
SYNCMOS	SM8958A	PLCC 44	PA44-48U
SYNCMOS	SM8958A	QFP 44	PA44QF44D
SYNCMOS	SM89516A	DIP 40	

SYNCMOS	SM89516A	PLCC 44	PA44-48U
SYNCMOS	SM89516A	QFP 44	PA44QF44D
SIGNETICS(PHILIPS)	87C51	DIP 40	
SIGNETICS(PHILIPS)	87C51	PLCC 44	PA44-48U
SIGNETICS(PHILIPS)	87C51FA	DIP 40	
SIGNETICS(PHILIPS)	87C51FA	PLCC 44	PA44-48U
SIGNETICS(PHILIPS)	87C51FB	DIP 40	
SIGNETICS(PHILIPS)	87C51FB	PLCC 44	PA44-48U
SIGNETICS(PHILIPS)	87C51FC	DIP 40	
SIGNETICS(PHILIPS)	87C51FC	PLCC 44	PA44-48U
SIGNETICS(PHILIPS)	87C52	DIP 40	
SIGNETICS(PHILIPS)	87C52	PLCC 44	PA44-48U
SIGNETICS(PHILIPS)	87C524	DIP 40	
SIGNETICS(PHILIPS)	87C524	PLCC 44	PA44-48U
SIGNETICS(PHILIPS)	87C528	DIP 40	
SIGNETICS(PHILIPS)	87C528	PLCC 44	PA44-48U
SIGNETICS(PHILIPS)	87C550	DIP 40	
SIGNETICS(PHILIPS)	87C550	PLCC 44	PA44-48U
SIGNETICS(PHILIPS)	87C552	PLCC 68	PA552-68
SIGNETICS(PHILIPS)	87C554	PLCC 68	PA552-68
SIGNETICS(PHILIPS)	87C575	DIP 40	
SIGNETICS(PHILIPS)	87C575	PLCC 44	PA44-48U
SIGNETICS(PHILIPS)	87C576	DIP 40	
SIGNETICS(PHILIPS)	87C576	PLCC 44	PA44-48U
SIGNETICS(PHILIPS)	87C592	DIP 40	PA592-68
SIGNETICS(PHILIPS)	87C652	DIP 40	
SIGNETICS(PHILIPS)	87C652	PLCC 44	PA44-48U
SIGNETICS(PHILIPS)	87C654	DIP 40	
SIGNETICS(PHILIPS)	87C654	PLCC 44	PA44-48U
SIGNETICS(PHILIPS)	87C750	DIP 24	
SIGNETICS(PHILIPS)	87C750	PLCC 28	PA28PL28D
SIGNETICS(PHILIPS)	87C751	DIP 24	
SIGNETICS(PHILIPS)	87C751	PLCC 28	PA28PL28D
SIGNETICS(PHILIPS)	87C752	DIP 28	
SIGNETICS(PHILIPS)	87C752	PLCC 28	PA28PL28D
SIGNETICS(PHILIPS)	87C749	DIP 28	
SIGNETICS(PHILIPS)	87C749	PLCC 28	PA28PL28D
SIGNETICS(PHILIPS)	89C52	DIP 40	
SIGNETICS(PHILIPS)	89C52	PLCC 44	PA44-48U
SIGNETICS(PHILIPS)	89C52	TQFP 44	PA44QF44D
SIGNETICS(PHILIPS)	89C54	DIP 40	
SIGNETICS(PHILIPS)	89C54	PLCC 44	PA44-48U
SIGNETICS(PHILIPS)	89C54	TQFP 44	PA44QF44D
SIGNETICS(PHILIPS)	89C536	PLCC 44	PA44-48U
SIGNETICS(PHILIPS)	89C536	TQFP 44	PA44QF44D
SIGNETICS(PHILIPS)	89C538	PLCC 44	PA44-48U
SIGNETICS(PHILIPS)	89C538	TQFP 44	PA44QF44D
SIGNETICS(PHILIPS)	89C738	DIP 40	
SIGNETICS(PHILIPS)	89C738	PLCC 44	PA44-48U
SIGNETICS(PHILIPS)	89C738	TQFP 44	PA44QF44D
SIEMENS	C501-1E	DIP 40	
SIEMENS	C501-1E	PLCC 44	PA44-48U
SIEMENS	C504-2E	QFP 44	PA44Q-16
SIEMENS	C504-2E	QFP 44	PA44Q-16
SIEMENS	C505A-4E	QFP 44	PA44Q-16
SIEMENS	C505CA-4E	QFP 44	PA44Q-16
MICROCHIP	65P542R	SOIC 28	PA28SO28D-EO-300
MICROCHIP	89C54	DIP 40	
MICROCHIP	89C54	PLCC 44	PA44-48U
MICROCHIP	89C54	QFP 44	PA44QF44D
MICROCHIP	89C58	DIP 40	
MICROCHIP	89C58	PLCC 44	PA44-48U
MICROCHIP	89C58	QFP 44	PA44QF44D
MICROCHIP	89C59	DIP 40	
MICROCHIP	89C59	PLCC 44	PA44-48U
MICROCHIP	89C59	QFP 44	PA44QF44D
MICROCHIP	89E564RD	DIP 40	
MICROCHIP	89E564RD	PLCC 44	PA44-48U
MICROCHIP	89E564RD	WQFN 40	PA40WQ40D
MICROCHIP	89V564RD	DIP 40	
MICROCHIP	89V564RD	PLCC 44	PA44-48U
MICROCHIP	89V564RD	WQFN 40	PA40WQ40D
MICROCHIP	89E554RC	DIP 40	

MICROCHIP	89E554RC	PLCC 44	PA44-48U
MICROCHIP	89V554RC	DIP 40	
MICROCHIP	89V554RC	PLCC 44	PA44-48U
MICROCHIP	89V52RD	DIP 40	
MICROCHIP	89V52RD	PLCC 44	PA44-48U
MICROCHIP	89V52RD	QFP 44	PA44QF44D
MICROCHIP	89V54RD	DIP 40	
MICROCHIP	89V54RD	PLCC 44	PA44-48U
MICROCHIP	89V54RD	TQFP 44	PA44QF44D
MICROCHIP	89V58RD	DIP 40	
MICROCHIP	89V58RD	PLCC 44	PA44-48U
MICROCHIP	89V58RD	TQFP 44	PA44QF44D
MICROCHIP	89V52RD2	PLCC 44	PA44-48U
MICROCHIP	89V52RD2	TQFP 44	PA44QF44D
MICROCHIP	89V54RD2	PLCC 44	PA44-48U
MICROCHIP	89V54RD2	TQFP 44	PA44QF44D
MICROCHIP	89V58RD2	PLCC 44	PA44-48U
MICROCHIP	89V58RD2	TQFP 44	PA44QF44D
MICROCHIP	89V516RD	DIP 40	
MICROCHIP	89V516RD	PLCC 44	PA44-48U
MICROCHIP	89V516RD	TQFP 44	PA44QF44D
MICROCHIP	89V516RD2	PLCC 44	PA44-48U
MICROCHIP	89V516RD2	TQFP 44	PA44QF44D
MICROCHIP	89E52RD	DIP 40	
MICROCHIP	89E52RD	PLCC 44	PA44-48U
MICROCHIP	89E52RD	TQFP 44	PA44QF44D
MICROCHIP	89E54RD	DIP 40	
MICROCHIP	89E54RD	PLCC 44	PA44-48U
MICROCHIP	89E54RD	TQFP 44	PA44QF44D
MICROCHIP	SST89E58RDA	DIP 40	
MICROCHIP	89E58RD	DIP 40	
MICROCHIP	89E58RD	PLCC 44	PA44-48U
MICROCHIP	89E58RD	TQFP 44	PA44QF44D
MICROCHIP	89E52RD2	PLCC 44	PA44-48U
MICROCHIP	89E52RD2	TQFP 44	PA44QF44D
MICROCHIP	89E54RD2	PLCC 44	PA44-48U
MICROCHIP	89E54RD2	TQFP 44	PA44QF44D
MICROCHIP	89E58RD2	PLCC 44	PA44-48U
MICROCHIP	89E58RD2	TQFP 44	PA44QF44D
MICROCHIP	89E516RD	DIP 40	
MICROCHIP	89E516RD	PLCC 44	PA44-48U
MICROCHIP	89E516RD	TQFP 44	PA44QF44D
MICROCHIP	89E516RD2	PLCC 44	PA44-48U
MICROCHIP	89E516RD2	TQFP 44	PA44QF44D
MICROCHIP	89F54	DIP 40	
MICROCHIP	89F54	PLCC 44	PA44-48U
MICROCHIP	89F58	DIP 40	
MICROCHIP	89F58	PLCC 44	PA44-48U
SST	65P542R	SOIC 28	PA28SO28D-EO-300
SST	89C54	DIP 40	
SST	89C54	PLCC 44	PA44-48U
SST	89C54	QFP 44	PA44QF44D
SST	89C58	DIP 40	
SST	89C58	PLCC 44	PA44-48U
SST	89C58	QFP 44	PA44QF44D
SST	SST89C58RC-TQJE	QFP 44	PA44QF44D
SST	SST89C58RC-NJE	PLCC 44	PA44-48U
SST	89C59	DIP 40	
SST	89C59	PLCC 44	PA44-48U
SST	89C59	QFP 44	PA44QF44D
SST	89E564RD	DIP 40	
SST	89E564RD	PLCC 44	PA44-48U
SST	89E564RD	WQFN 40	PA40WQ40D
SST	89V564RD	DIP 40	
SST	89V564RD	PLCC 44	PA44-48U
SST	89V564RD	WQFN 40	PA40WQ40D
SST	89E554RC	DIP 40	
SST	89E554RC	PLCC 44	PA44-48U
SST	89V554RC	DIP 40	
SST	89V554RC	PLCC 44	PA44-48U
SST	89V52RD	DIP 40	
SST	89V52RD	PLCC 44	PA44-48U
SST	89V52RD	QFP 44	PA44QF44D

SST	89V54RD	DIP 40	
SST	89V54RD	PLCC 44	PA44-48U
SST	89V54RD	TQFP 44	PA44QF44D
SST	89V58RD	DIP 40	
SST	89V58RD	PLCC 44	PA44-48U
SST	89V58RD	TQFP 44	PA44QF44D
SST	89V52RD2	PLCC 44	PA44-48U
SST	89V52RD2	TQFP 44	PA44QF44D
SST	89V54RD2	PLCC 44	PA44-48U
SST	89V54RD2	TQFP 44	PA44QF44D
SST	89V58RD2	PLCC 44	PA44-48U
SST	89V58RD2	TQFP 44	PA44QF44D
SST	89V516RD	DIP 40	
SST	89V516RD	PLCC 44	PA44-48U
SST	89V516RD	TQFP 44	PA44QF44D
SST	89V516RD2	PLCC 44	PA44-48U
SST	89V516RD2	TQFP 44	PA44QF44D
SST	89E52RD	DIP 40	
SST	89E52RD	PLCC 44	PA44-48U
SST	89E52RD	TQFP 44	PA44QF44D
SST	89E54RD	DIP 40	
SST	89E54RD	PLCC 44	PA44-48U
SST	89E54RD	TQFP 44	PA44QF44D
SST	89E58RD	DIP 40	
SST	89E58RD	PLCC 44	PA44-48U
SST	89E58RD	TQFP 44	PA44QF44D
SST	89E52RD2	PLCC 44	PA44-48U
SST	89E52RD2	TQFP 44	PA44QF44D
SST	89E54RD2	PLCC 44	PA44-48U
SST	89E54RD2	TQFP 44	PA44QF44D
SST	89E58RD2	PLCC 44	PA44-48U
SST	89E58RD2	TQFP 44	PA44QF44D
SST	89E516RD	DIP 40	
SST	89E516RD	PLCC 44	PA44-48U
SST	89E516RD	TQFP 44	PA44QF44D
SST	89E516RD2	PLCC 44	PA44-48U
SST	89E516RD2	TQFP 44	PA44QF44D
SST	SST89E516RD2-NJE	PLCC 44	PA44-48U
SST	SST89E516RD2-TQJE	TQFP 44	PA44QF44D
SST	SST89E516RD-PIE	DIP 40	
SST	89F54	DIP 40	
SST	89F54	PLCC 44	PA44-48U
SST	89F58	DIP 40	
SST	89F58	PLCC 44	PA44-48U
PHILIPS	P87C51	DIP 40	
PHILIPS	P87C51	PLCC 44	PA44-48U
PHILIPS	P87C51FA	DIP 40	
PHILIPS	P87C51FA	PLCC 44	PA44-48U
PHILIPS	P87C51FB	DIP 40	
PHILIPS	P87C51FB	PLCC 44	PA44-48U
PHILIPS	P87C51FC	DIP 40	
PHILIPS	P87C51FC	PLCC 44	PA44-48U
PHILIPS	P87C51MA2	PLCC 44	PA44-48U
PHILIPS	P87C51MB2	PLCC 44	PA44-48U
PHILIPS	P87C51MC2	PLCC 44	PA44-48U
PHILIPS	P87C51RA+	DIP 40	
PHILIPS	P87C51RA+	PLCC 44	PA44-48U
PHILIPS	P87C51RB+	DIP 40	
PHILIPS	P87C51RB+	PLCC 44	PA44-48U
PHILIPS	P87C51RC+	DIP 40	
PHILIPS	P87C51RC+	PLCC 44	PA44-48U
PHILIPS	P87C51RD+	DIP 40	
PHILIPS	P87C51RD+	PLCC 44	PA44-48U
PHILIPS	P87C52	DIP 40	
PHILIPS	P87C52	PLCC 44	PA44-48U
PHILIPS	P87C52	QFP 44	PA44QF44D
NXP	P87C52UBAA	PLCC 44	PA44-48U
PHILIPS	P87C54	DIP 40	
PHILIPS	P87C54	PLCC 44	PA44-48U
PHILIPS	P87C58	DIP 40	
PHILIPS	P87C58	PLCC 44	PA44-48U
PHILIPS	P87C51RA2BA	PLCC 44	PA44-48U
PHILIPS	P87C51RA2BBD	QFP 44	PA44QF44D

PHILIPS	P87C51RB2BN	DIP 40	
PHILIPS	P87C51RB2BA	PLCC 44	PA44-48U
PHILIPS	P87C51RB2BBD	QFP 44	PA44QF44D
PHILIPS	P87C51RC2BN	DIP 40	
PHILIPS	P87C51RC2BA	PLCC 44	PA44-48U
PHILIPS	P87C51RC2BBD	QFP 44	PA44QF44D
PHILIPS	P87C51RD2BN	DIP 40	
PHILIPS	P87C51RD2BA	PLCC 44	PA44-48U
PHILIPS	P87C51RD2BBD	QFP 44	PA44QF44D
PHILIPS	P87C51X2	DIP 40	
PHILIPS	P87C51X2	PLCC 44	PA44-48U
PHILIPS	P87C52X2	DIP 40	
PHILIPS	P87C52X2	PLCC 44	PA44-48U
PHILIPS	P87C54X2	DIP 40	
PHILIPS	P87C54X2	PLCC 44	PA44-48U
PHILIPS	P87C58X2	DIP 40	
PHILIPS	P87C58X2	PLCC 44	PA44-48U
PHILIPS	P87C591	PLCC 44	PA44-48U
PHILIPS	P87C654X2FA	PLCC 44	PA44-48U
PHILIPS	P87C654X2BBD	QFP 44	PA44QF44D
PHILIPS	P87C660X2FA	PLCC 44	PA44-48U
PHILIPS	P87C660X2BBD	QFP 44	PA44QF44D
PHILIPS	P87C661X2FA	PLCC 44	PA44-48U
PHILIPS	P87C661X2BBD	QFP 44	PA44QF44D
PHILIPS	P87LC52X2FA	PLCC 44	PA44-48U
PHILIPS	P87LC52X2BBD	QFP 44	PA44QF44D
PHILIPS	P87LC54X2FA	PLCC 44	PA44-48U
PHILIPS	P87LC54X2BBD	QFP 44	PA44QF44D
PHILIPS	P85LPC764	PLCC 44	PA44-48U
PHILIPS	P87LPC761	DIP 16	
PHILIPS	P87LPC762	DIP 20	
PHILIPS	P87LPC762	SOIC 20	PA28SO28D-EO-300
PHILIPS	P87LPC762	DIP 16	
PHILIPS	P87LPC762	DIP 8	
PHILIPS	P87LPC764	DIP 20	
PHILIPS	P87LPC764	SOIC 20	PA28SO28D-EO-300
PHILIPS	P87LPC764	DIP 16	
PHILIPS	P87LPC764	DIP 8	
PHILIPS	P87LPC767	DIP 20	
PHILIPS	P87LPC767	SOIC 20	PA28SO28D-EO-300
PHILIPS	P87LPC768	DIP 20	
PHILIPS	P87LPC768	SOIC 20	PA28SO28D-EO-300
PHILIPS	P87LPC769	DIP 20	
PHILIPS	P87LPC769	SOIC 20	PA28SO28D-EO-300
PHILIPS	P87LPC778	TSSOP 20	PA24TSS24D
NXP	P87LPC778	TSSOP 20	PA24TSS24D
PHILIPS	P89LPC901FN(ICP)	DIP 8	
PHILIPS	P89LPC901FD(ICP)	SOP 8	PA16SO16D-EO-150
PHILIPS	P89LPC902FN(ICP)	DIP 8	
PHILIPS	P89LPC902FD(ICP)	SOP 8	PA16SO16D-EO-150
PHILIPS	P89LPC903FD(ICP)	DIP 8	
PHILIPS	P89LPC903FD(ICP)	SOP 8	PA16SO16D-EO-150
PHILIPS	P89LPC904FN(ICP)	DIP 8	
PHILIPS	P89LPC904FD(ICP)	SOP 8	PA16SO16D-EO-150
PHILIPS	P89LPC906FD(ICP)	SOP 8	PA16SO16D-EO-150
PHILIPS	P89LPC907FD(ICP)	SOP 8	PA16SO16D-EO-150
PHILIPS	P89LPC908FD(ICP)	SOP 8	PA16SO16D-EO-150
PHILIPS	P89LPC9102FTK(ICP)	CASON 10	PA10SON10D
PHILIPS	P89LPC9103FTK(ICP)	CASON 10	PA10SON10D
PHILIPS	P89LPC9107FN(ICP)	DIP 14	
PHILIPS	P89LPC9107FDH(ICP)	TSSOP 14	PA28TSS28D-EO
PHILIPS	P89LPC912FD(ICP)	TSSOP 14	PA28TSS28D-EO
PHILIPS	P89LPC913FD(ICP)	TSSOP 14	PA28TSS28D-EO
PHILIPS	P89LPC914FD(ICP)	TSSOP 14	PA28TSS28D-EO
PHILIPS	P89LPC915FD(ICP)	TSSOP 14	PA28TSS28D-EO
PHILIPS	P89LPC916FD(ICP)	TSSOP 16	PA28TSS28D-EO
PHILIPS	P89LPC917FD(ICP)	TSSOP 16	PA28TSS28D-EO
PHILIPS	P89LPC920FD(ICP)	TSSOP 20	PA28TSS28D-EO
PHILIPS	P89LPC921FD(ICP)	TSSOP 20	PA28TSS28D-EO
PHILIPS	P89LPC922FD(ICP)	TSSOP 20	PA28TSS28D-EO
PHILIPS	P89LPC922FN(ICP)	DIP 20	
PHILIPS	P89LPC9221FD(ICP)	TSSOP 20	PA28TSS28D-EO
PHILIPS	P89LPC9221FN(ICP)	DIP 20	

PHILIPS	P89LPC924FD(ICP)	TSSOP 20	PA28TSS28D-EO
PHILIPS	P89LPC925FN(ICP)	DIP 20	
PHILIPS	P89LPC925FD(ICP)	TSSOP 20	PA28TSS28D-EO
PHILIPS	P89LPC930FD(ICP)	TSSOP 28	PA28TSS28D-EO
PHILIPS	P89LPC931FD(ICP)	TSSOP 28	PA28TSS28D-EO
PHILIPS	P89LPC933FDH(ICP)	TSSOP 28	PA28TSS28D-EO
PHILIPS	P89LPC934FDH(ICP)	TSSOP 28	PA28TSS28D-EO
PHILIPS	P89LPC935FA(ICP)	PLCC 28	PA28PL28D
PHILIPS	P89LPC935FDH(ICP)	TSSOP 28	PA28TSS28D-EO
PHILIPS	P89LPC935FHN(ICP)	QFN 28	PA28QFN28D
PHILIPS	P89LPC936FDH(ICP)	TSSOP 28	PA28TSS28D-EO
PHILIPS	P89LPC938FA(ICP)	PLCC 28	PA28PL28D
PHILIPS	P89LPC938FDH(ICP)	TSSOP 28	PA28TSS28D-EO
PHILIPS	P89LPC938FHN(ICP)	QFN 28	PA28QFN28D
PHILIPS	P89LPC920FD	TSSOP 20	PA28TSS28D-EO
PHILIPS	P89LPC921FD	TSSOP 20	PA28TSS28D-EO
PHILIPS	P89LPC922FD	TSSOP 20	PA28TSS28D-EO
PHILIPS	P89LPC922FN	DIP 20	
PHILIPS	P89LPC924FD	TSSOP 20	PA28TSS28D-EO
PHILIPS	P89LPC925FN	DIP 20	
PHILIPS	P89LPC925FD	TSSOP 20	PA28TSS28D-EO
PHILIPS	P89LPC930FD	TSSOP 28	PA28TSS28D-EO
PHILIPS	P89LPC931FD	TSSOP 28	PA28TSS28D-EO
PHILIPS	P89LPC932BA	PLCC 28	PA28PL28D
PHILIPS	P89LPC932BDB	TSSOP 28	PA28TSS28D-EO
PHILIPS	P89LPC932FDH	TSSOP 28	PA28TSS28D-EO
PHILIPS	P89LPC932FHN	QFN 28	PA28QFN28D
PHILIPS	P89LPC932A1FA	PLCC 28	PA28PL28D
PHILIPS	P89LPC932A1FDH	TSSOP 28	PA28TSS28D-EO
PHILIPS	P89LPC932A1FHN	QFN 28	PA28QFN28D
PHILIPS	P89LPC933FDH	TSSOP 28	PA28TSS28D-EO
PHILIPS	P89LPC934FDH	TSSOP 28	PA28TSS28D-EO
PHILIPS	P89LPC935FA	PLCC 28	PA28PL28D
PHILIPS	P89LPC935FDH	TSSOP 28	PA28TSS28D-EO
PHILIPS	P89LPC935FHN	QFN 28	PA28QFN28D
PHILIPS	P89LPC936FDH	TSSOP 28	PA28TSS28D-EO
PHILIPS	P89LPC938FA	PLCC 28	PA28PL28D
PHILIPS	P89LPC938FDH	TSSOP 28	PA28TSS28D-EO
PHILIPS	P89LPC938FHN	QFN 28	PA28QFN28D
PHILIPS	P89C51RA+	DIP 40	
PHILIPS	P89C51RA+	PLCC 44	PA44-48U
PHILIPS	P89C51RB+	DIP 40	
PHILIPS	P89C51RB+	PLCC 44	PA44-48U
PHILIPS	P89C51RC+	DIP 40	
PHILIPS	P89C51RC+	PLCC 44	PA44-48U
PHILIPS	P89C51RD+	DIP 40	
PHILIPS	P89C51RD+	PLCC 44	PA44-48U
PHILIPS	P89C51RB2H	DIP 40	
PHILIPS	P89C51RB2H	PLCC 44	PA44-48U
PHILIPS	P89C51RC2H	DIP 40	
PHILIPS	P89C51RC2H	PLCC 44	PA44-48U
PHILIPS	P89C51RD2H	DIP 40	
PHILIPS	P89C51RD2H	PLCC 44	PA44-48U
PHILIPS	P89C51RA2BN	DIP 40	
PHILIPS	P89C51RA2BA	PLCC 44	PA44-48U
PHILIPS	P89C51RA2BB	QFP 44	PA44QF44D
PHILIPS	P89C51RB2BN	DIP 40	
PHILIPS	P89C51RB2BA	PLCC 44	PA44-48U
PHILIPS	P89C51RB2BB	QFP 44	PA44QF44D
PHILIPS	P89C51RC2BN	DIP 40	
PHILIPS	P89C51RC2BA	PLCC 44	PA44-48U
PHILIPS	P89C51RC2FA	PLCC 44	PA44-48U
PHILIPS	P89C51RC2BB	QFP 44	PA44QF44D
PHILIPS	P89C51RC2FB	QFP 44	PA44QF44D
PHILIPS	P89C51RD2BN	DIP 40	
PHILIPS	P89C51RD2BA	PLCC 44	PA44-48U
PHILIPS	P89C51RD2BA	PLCC 44	PA44-48U
NXP	P89C51RD2FA	PLCC 44	PA44-48U
PHILIPS	P89C51RD2BB	QFP 44	PA44QF44D
NXP	P89V52X2FN	DIP 40	
NXP	P89V52X2FA	PLCC 44	PA44-48U
PHILIPS	P89C60X2BA	PLCC 44	PA44-48U
PHILIPS	P89C61X2BN	DIP 40	

PHILIPS	P89C61X2BA	QFP 44	PA44QF44D
PHILIPS	P89C660	DIP 40	
PHILIPS	P89C660	PLCC 44	PA44-48U
PHILIPS	P89C662	DIP 40	
PHILIPS	P89C662	PLCC 44	PA44-48U
PHILIPS	P89C664	DIP 40	
PHILIPS	P89C664	PLCC 44	PA44-48U
PHILIPS	P89C668	DIP 40	
PHILIPS	P89C668	PLCC 44	PA44-48U
PHILIPS	P89V660FA	PLCC 44	PA44-48U
PHILIPS	P89V660FBC	QFP 44	PA44QF44D
PHILIPS	P89V662FA	PLCC 44	PA44-48U
PHILIPS	P89V662FBC	QFP 44	PA44QF44D
PHILIPS	P89V664FA	PLCC 44	PA44-48U
PHILIPS	P89V664FBC	QFP 44	PA44QF44D
PHILIPS	P89CV51RB2FA	PLCC 44	PA44-48U
PHILIPS	P89CV51RB2FBC	QFP 44	PA44QF44D
PHILIPS	P89CV51RC2FA	PLCC 44	PA44-48U
PHILIPS	P89CV51RC2FBC	QFP 44	PA44QF44D
PHILIPS	P89CV51RD2FA	PLCC 44	PA44-48U
PHILIPS	P89CV51RD2FBC	QFP 44	PA44QF44D
NXP	P87C51SBPN	DIP 40	
NXP	P87C51SBAA	PLCC 44	PA44-48U
NXP	P89V660FA	PLCC 44	PA44-48U
NXP	P89V660FBC	QFP 44	PA44QF44D
NXP	P89V662FA	PLCC 44	PA44-48U
NXP	P89V662FBC	QFP 44	PA44QF44D
NXP	P89V664FA	PLCC 44	PA44-48U
NXP	P89V664FBC	QFP 44	PA44QF44D
NXP	P89CV51RB2FA	PLCC 44	PA44-48U
NXP	P89CV51RB2FBC	QFP 44	PA44QF44D
NXP	P89CV51RC2FA	PLCC 44	PA44-48U
NXP	P89CV51RC2FBC	QFP 44	PA44QF44D
NXP	P89CV51RD2FA	PLCC 44	PA44-48U
NXP	P89CV51RD2FBC	QFP 44	PA44QF44D
NXP	P89V51RD2BN	DIP 40	
NXP	P89V51RD2FN	DIP 40	
NXP	P89V51RD2FA	PLCC 44	PA44-48U
NXP	P89V51RD2FBC	TQFP 44	PA44QF44D
NXP	LPC2134	LQFP 64	HA64QF48DH
NXP	LPC2134FBD	LQFP 64	HA64QF48DH
PHILIPS	P89C51U	DIP 40	
PHILIPS	P89C51U	PLCC 44	PA44-48U
PHILIPS	P89C52U	DIP 40	
PHILIPS	P89C52U	PLCC 44	PA44-48U
PHILIPS	P89C54U	DIP 40	
PHILIPS	P89C54U	PLCC 44	PA44-48U
PHILIPS	P89C58U	DIP 40	
PHILIPS	P89C58U	PLCC 44	PA44-48U
PHILIPS	P89C51B	DIP 40	
PHILIPS	P89C51B	PLCC 44	PA44-48U
PHILIPS	P89C52B	DIP 40	
PHILIPS	P89C52B	PLCC 44	PA44-48U
PHILIPS	P89C54B	DIP 40	
PHILIPS	P89C54B	PLCC 44	PA44-48U
PHILIPS	P89C58B	DIP 40	
PHILIPS	P89C58B	PLCC 44	PA44-48U
PHILIPS	P89C51X2BN	DIP 40	
PHILIPS	P89C51X2BA	PLCC 44	PA44-48U
PHILIPS	P89C51X2FA	PLCC 44	PA44-48U
PHILIPS	P89C51X2BBD	QFP 44	PA44QF44D
PHILIPS	P89C52X2BN	DIP 40	
PHILIPS	P89C52X2FN	DIP 40	
PHILIPS	P89C52X2BA	PLCC 44	PA44-48U
PHILIPS	P89C52X2FA	PLCC 44	PA44-48U
PHILIPS	P89C52X2BBD	QFP 44	PA44QF44D
PHILIPS	P89C52X2FBD	QFP 44	PA44QF44D
PHILIPS	P89C54X2BN	DIP 40	
PHILIPS	P89C54X2BA	PLCC 44	PA44-48U
PHILIPS	P89C54X2FA	PLCC 44	PA44-48U
PHILIPS	P89C54X2BBD	QFP 44	PA44QF44D
PHILIPS	P89C58X2BN	DIP 40	
PHILIPS	P89C58X2BA	PLCC 44	PA44-48U

PHILIPS	P89C58X2FA	PLCC 44	PA44-48U
PHILIPS	P89C58X2BBD	QFP 44	PA44QF44D
PHILIPS	P89C669FA	PLCC 44	PA44-48U
PHILIPS	P89C669BBB	QFP 44	PA44QF44D
PHILIPS	P89LV51RB2BA	PLCC 44	PA44-48U
PHILIPS	P89LV51RB2BBC	TQFP 44	PA44QF44D
PHILIPS	P89LV51RC2BN	DIP 40	
PHILIPS	P89LV51RC2FA	PLCC 44	PA44-48U
PHILIPS	P89LV51RC2FBC	TQFP 44	PA44QF44D
PHILIPS	P89LV51RD2BN	DIP 40	
PHILIPS	P89LV51RD2BA	PLCC 44	PA44-48U
PHILIPS	P89LV51RD2FA	PLCC 44	PA44-48U
PHILIPS	P89LV51RD2BBC	TQFP 44	PA44QF44D
PHILIPS	P89V51RB2BA	PLCC 44	PA44-48U
PHILIPS	P89V51RB2BBC	TQFP 44	PA44QF44D
PHILIPS	P89V51RC2BN	DIP 40	
PHILIPS	P89V51RC2FA	PLCC 44	PA44-48U
PHILIPS	P89V51RC2FBC	TQFP 44	PA44QF44D
PHILIPS	P89V51RD2BN	DIP 40	
PHILIPS	P89V51RD2FN	DIP 40	
PHILIPS	P89V51RD2FA	PLCC 44	PA44-48U
PHILIPS	P89V51RD2FBC	TQFP 44	PA44QF44D
PHILIPS	P87C51XAG37	PLCC 44	PA44-48U
PHILIPS	P87C51XAS37	PLCC 44	PA44-48U
PHILIPS	PXAG37KBA	PLCC 44	PA44-48U
PHILIPS	PXAG37KBBB	TQFP 44	PA44QF44D
PHILIPS	PXAG37KFA	PLCC 44	PA44-48U
PHILIPS	PXAG37KFBD	TQFP 44	PA44QF44D
PHILIPS	PXAC37	PLCC 44	PA44-48U
PHILIPS	PXAS37	PLCC 44	PA44-48U
PHILIPS	P89C51XAG49	PLCC 44	PA44-48U
PHILIPS	PXAG49	PLCC 44	PA44-48U
PHILIPS	PCD3755A	SOP 28	PA28S-08
SILICONLABS	C8051F320	QFP 32	PA32TQ32D
TELECHIP	TCC766H303-A	BGA 232	PA232BG48D
TELECHIP	TCC767H301-A	BGA 225	PA225BG48D
TELECHIP	TCC763H309-A	BGA 144	PA144BG48D
TELECHIP	TCC764H309-A	BGA 144	PA144BG48D
TEMIC	T87C5101	DIP 24	
TEMIC	T87C5101	SOP 24	PA28SO28D-EO-300
TEMIC	T87C5103	DIP 16	
TEMIC	T87C5103	DIP 24	
TEMIC	T87C5103	SSOP 16	PA28SS-OT
TEMIC	T87C5103	SSOP 24	PA28SS-OT
TEMIC	T87C5111	SSOP 16	PA24TSS24D
TEMIC	T87C5111	DIP 24	
TEMIC	T87C5111	SOP 24	PA28SO-08(C)
TEMIC	T87C5111	SSOP 24	PA24TSS24D
TEMIC	T89C51CC02	SOP 24	PA28SO28D-EO-300
TEMIC	T89C51CC02	SOP 28	PA28SO28D-EO-300
TEMIC	T89C51CC02	PLCC 28	PA28PL28D
TEMIC	T89C51CC02	QFP 32	PA32TQ32D-YC
TEMIC	T89C5115	SOP 24	PA28SO28D-EO-300
TEMIC	T89C5115	SOP 28	PA28SO28D-EO-300
TEMIC	T89C5115	PLCC 28	PA28PL28D
TEMIC	T89C5115	QFP 32	PA32TQ32D
TEMIC	T89C51CC01	PLCC 44	PA44-48U
TEMIC	T89C51CC01	TQFP 44	PA44TQ44D-EO
TEMIC	T89C51AC2	PLCC 44	PA44-48U
TEMIC	T89C51IB2-xM_5V	PLCC 44	PA44-48U
TEMIC	T89C51IB2-xM_5V	QFP 44	PA44QF44D
TEMIC	T89C51IB2-xL_3V	PLCC 44	PA44-48U
TEMIC	T89C51IB2-xL_3V	QFP 44	PA44QF44D
TEMIC	T89C51IC2-xM_5V	PLCC 44	PA44-48U
TEMIC	T89C51IC2-xM_5V	QFP 44	PA44QF44D
TEMIC	T89C51IC2-xL_3V	PLCC 44	PA44-48U
TEMIC	T89C51IC2-xL_3V	QFP 44	PA44QF44D
TEMIC	T89C51RB2-xM_5V	DIP 40	
TEMIC	T89C51RB2-xM_5V	PLCC 44	PA44-48U
TEMIC	T89C51RB2-xM_5V	QFP 44	PA44QF44D
TEMIC	T89C51RB2-xL_3V	DIP 40	
TEMIC	T89C51RB2-xL_3V	PLCC 44	PA44-48U
TEMIC	T89C51RB2-xL_3V	QFP 44	PA44QF44D



TEMIC	T89C51RC2-xM_5V	DIP 40	
TEMIC	T89C51RC2-xM_5V	PLCC 44	PA44-48U
TEMIC	T89C51RC2-xM_5V	QFP 44	PA44QF44D
TEMIC	T89C51RC2-xL_3V	DIP 40	
TEMIC	T89C51RC2-xL_3V	PLCC 44	PA44-48U
TEMIC	T89C51RC2-xL_3V	QFP 44	PA44QF44D
TEMIC	T89C51RD2-xM_5V	DIP 40	
TEMIC	T89C51RD2-xM_5V	PLCC 44	PA44-48U
TEMIC	T89C51RD2-xL_3V	DIP 40	
TEMIC	T89C51RD2-xL_3V	PLCC 44	PA44-48U
TEMIC	TS87C51U2	DIP 40	
TEMIC	TS87C51U2	PLCC 44	PA44-48U
TEMIC	TS87C51U2	TQFP 44	PA44VQ44D
TEMIC	TSC71RBX2	DIP 40	
TEMIC	TSC71RBX2	PLCC 44	PA44-48U
TEMIC	TSC71RCX2	DIP 40	
TEMIC	TSC71RCX2	PLCC 44	PA44-48U
TEMIC	TSC71RDX2	DIP 40	
TEMIC	TSC71RDX2	PLCC 44	PA44-48U
TEMIC	TSC87251G1A	DIP 40	
TEMIC	TSC87251G1A	PLCC 44	PA44-48U
TEMIC	TSC87251G1D	DIP 40	
TEMIC	TSC87251G1D	PLCC 44	PA44-48U
TEMIC	TSC87251G2D	DIP 40	
TEMIC	TSC87251G2D	PLCC 44	PA44-48U
TEMIC	TSC87C51	DIP 40	
TEMIC	TSC87C51	PLCC 44	PA44-48U
TEMIC	TSC87C51RB2	DIP 40	
TEMIC	TSC87C51RB2	PLCC 44	PA44-48U
TEMIC	TSC87C51RC2	DIP 40	
TEMIC	TSC87C51RC2	PLCC 44	PA44-48U
TEMIC	TSC87C51RD2	DIP 40	
TEMIC	TSC87C51RD2	PLCC 44	PA44-48U
TEMIC	TSC87C52	DIP 40	
TEMIC	TSC87C52	PLCC 44	PA44-48U
TEMIC	TSC87C52X2	DIP 40	
TEMIC	TSC87C52X2	PLCC 44	PA44-48U
TEMIC	TSC87C54	DIP 40	
TEMIC	TSC87C54	PLCC 44	PA44-48U
TEMIC	TSC87C58	DIP 40	
TEMIC	TSC87C58	PLCC 44	PA44-48U
TEMIC	TS87C58X2	DIP 40	
TEMIC	TS87C58X2	PLCC 44	PA44-48U
TOSHIBA	TMP86PM29AF	QFP 64	BM11163
TOSHIBA	TMP87PH40	DIP 28	
TOSHIBA	TMP87PH46N	DIP 28	
TOSHIBA	TMP87PH808N	DIP 28	
TOSHIBA	TMP87PP21FG	QFP 80	BM11604
TOSHIBA	TMP88PS49F	DIP 32	
WINBOND	W77E58	DIP 40	
WINBOND	W77E58P	PLCC 44	PA44-48U
WINBOND	W77E58F	QFP 44	PA44QF44D
WINBOND	W77E516	DIP 40	
WINBOND	W77E516P	PLCC 44	PA44-48U
WINBOND	W77E516F	QFP 44	PA44QF44D
WINBOND	W77E532-40	DIP 40	
WINBOND	W77E532P-40	PLCC 44	PA44-48U
WINBOND	W77E532F-40	QFP 44	PA44QF44D
WINBOND	W77E532A40DL	DIP 40	
WINBOND	W77E532A40PL	PLCC 44	PA44-48U
WINBOND	W77E532A40FL	QFP 44	PA44QF44D
WINBOND	W77LE532-25	DIP 40	
WINBOND	W77LE532P-25	PLCC 44	PA44-48U
WINBOND	W77LE532F-25	QFP 44	PA44QF44D
WINBOND	W77LE532A25DL	DIP 40	
WINBOND	W77LE532A25PL	PLCC 44	PA44-48U
WINBOND	W77LE532A25FL	QFP 44	PA44QF44D
WINBOND	W78E365A	DIP 40	
WINBOND	W78E365A	PLCC 44	PA44-48U
WINBOND	W78E365A	QFP 44	PA44QF44D
NUVOTON	W78E516DPG	PLCC 44	PA44-48U
NUVOTON	W78E052D	DIP 40	
WINBOND	W78E378P	PLCC 44	PA44-48U

WINBOND	W78E516	DIP 40	
WINBOND	W78E516P	PLCC 44	PA44-48U
WINBOND	W78E516F	QFP 44	PA44QF44D
WINBOND	W78E516B	DIP 40	
WINBOND	W78E516BP	PLCC 44	PA44-48U
WINBOND	W78E516BF	QFP 44	PA44QF44D
WINBOND	W78E51	DIP 40	
WINBOND	W78E51P	PLCC 44	PA44-48U
WINBOND	W78E51F	QFP 44	PA44QF44D
WINBOND	W78E51B	DIP 40	
WINBOND	W78E51BP	PLCC 44	PA44-48U
WINBOND	W78E51BF	QFP 44	PA44QF44D
WINBOND	W78E51C	DIP 40	
WINBOND	W78E51CP	PLCC 44	PA44-48U
WINBOND	W78E51CF	QFP 44	PA44QF44D
WINBOND	W78E52	DIP 40	
WINBOND	W78E52P	PLCC 44	PA44-48U
WINBOND	W78E52F	QFP 44	PA44QF44D
WINBOND	W78E52B	DIP 40	
WINBOND	W78E52BP	PLCC 44	PA44-48U
WINBOND	W78E52BF	QFP 44	PA44QF44D
WINBOND	W78E52C	DIP 40	
WINBOND	W78E52CP	PLCC 44	PA44-48U
WINBOND	W78E52CF	QFP 44	PA44QF44D
WINBOND	W78E54	DIP 40	
WINBOND	W78E54P	PLCC 44	PA44-48U
WINBOND	W78E54F	QFP 44	PA44QF44D
WINBOND	W78E54B	DIP 40	
WINBOND	W78E54BP	PLCC 44	PA44-48U
WINBOND	W78E54BF	QFP 44	PA44QF44D
WINBOND	W78E54C	DIP 40	
WINBOND	W78E54CP	PLCC 44	PA44-48U
WINBOND	W78E54CF	QFP 44	PA44QF44D
WINBOND	W78E58	DIP 40	
WINBOND	W78E58P	PLCC 44	PA44-48U
WINBOND	W78E58F	QFP 44	PA44QF44D
WINBOND	W78E058B	DIP 40	
WINBOND	W78E58B	DIP 40	
WINBOND	W78E58BP	PLCC 44	PA44-48U
WINBOND	W78E58BF	QFP 44	PA44QF44D
WINBOND	W78E62BP	PLCC 44	PA44-48U
WINBOND	W78E62BF	QFP 44	PA44QF44D
WINBOND	W78E65P	PLCC 44	PA44-48U
WINBOND	W78E065A	PLCC 44	PA44-48U
WINBOND	W78E65F	QFP 44	PA44QF44D
WINBOND	W78LE51	DIP 40	
WINBOND	W78ERD2A40DN	DIP 40	
WINBOND	W78ERD2A40PN	PLCC 44	PA44-48U
WINBOND	W78ERD2A40FN	QFP 44	PA44QF44D
WINBOND	W78LE51P	PLCC 44	PA44-48U
WINBOND	W78LE51F	QFP 44	PA44QF44D
WINBOND	W78LE51C	DIP 40	
WINBOND	W78LE51CP	PLCC 44	PA44-48U
WINBOND	W78LE51CF	QFP 44	PA44QF44D
WINBOND	W78LE52	DIP 40	
WINBOND	W78LE52P	PLCC 44	PA44-48U
WINBOND	W78LE52F	QFP 44	PA44QF44D
WINBOND	W78LE52C	DIP 40	
WINBOND	W78LE52CP	PLCC 44	PA44-48U
WINBOND	W78LE52CF	QFP 44	PA44QF44D
WINBOND	W78LE54	DIP 40	
WINBOND	W78LE54P	PLCC 44	PA44-48U
WINBOND	W78LE54F	QFP 44	PA44QF44D
WINBOND	W78LE54C	DIP 40	
WINBOND	W78LE54CP	PLCC 44	PA44-48U
WINBOND	W78LE54CF	QFP 44	PA44QF44D
WINBOND	W77LE58	DIP 40	
WINBOND	W77LE58P	PLCC 44	PA44-48U
WINBOND	W77LE58F	QFP 44	PA44QF44D
WINBOND	W78LE516	DIP 40	
WINBOND	W78LE516P	PLCC 44	PA44-48U
WINBOND	W78LE516F	QFP 44	PA44QF44D
WINBOND	W78LE516B	DIP 40	

WINBOND	W78LE516BP	PLCC 44	PA44-48U
WINBOND	W78LE516BF	QFP 44	PA44QF44D
WINBOND	W78LE58	DIP 40	
WINBOND	W78LE58P	PLCC 44	PA44-48U
WINBOND	W78LE58F	QFP 44	PA44QF44D
WINBOND	W78LE812	DIP 40	
WINBOND	W78LE812P	PLCC 44	PA44-48U
WINBOND	W78LE812F	QFP 44	PA44QF44D
WINBOND	W79E532A40DN	DIP 40	
WINBOND	W79E532A40PN	PLCC 44	PA44-48U
WINBOND	W79E532A40FN	QFP 44	PA44QF44D
WINBOND	W79E632A40DN	DIP 40	
WINBOND	W79E632A40PN	PLCC 44	PA44-48U
WINBOND	W79E632A40FN	QFP 44	PA44QF44D
WINBOND	W79L532A40DN	DIP 40	
WINBOND	W79L532A40PN	PLCC 44	PA44-48U
WINBOND	W79L532A40FN	QFP 44	PA44QF44D
WINBOND	W79L632A40DN	DIP 40	
WINBOND	W79L632A40PN	PLCC 44	PA44-48U
WINBOND	W79L632A40FN	QFP 44	PA44QF44D
ZILOG	Z86E0308PSC	DIP 18	
ZILOG	Z86E0308SSC	SOIC 18	PA28SO28D-EO-300
ZILOG	Z86E0312PSC	DIP 18	
ZILOG	Z86E0312SSC	SOIC 18	PA28SO28D-EO-300
ZILOG	Z86E0608PSC	DIP 18	
ZILOG	Z86E0608SSC	SOIC 18	PA28SO28D-EO-300
ZILOG	Z86E0612PSC	DIP 18	
ZILOG	Z86E0612SSC	SOIC 18	PA28SO28D-EO-300
ZILOG	Z86E02(1925)	DIP 18	
ZILOG	Z86E0208PSC	DIP 18	
ZILOG	Z86E0208PSC1866	DIP 18	
ZILOG	Z86E0208PSC1903	DIP 18	
ZILOG	Z86E0208SSC	SOIC 18	PA28SO28D-EO-300
ZILOG	Z86E0208SSC1866	SOIC 18	PA28SO28D-EO-300
ZILOG	Z86E0208SSC1903	SOIC 18	PA28SO28D-EO-300
ZILOG	Z86E04	DIP 18	
ZILOG	Z86E04(1925)	DIP 18	
ZILOG	Z86E0408PEC	DIP 18	
ZILOG	Z86E0408PSC1866	DIP 18	
ZILOG	Z86E0408PSC1903	DIP 18	
ZILOG	Z86E0408PEC1903	DIP 18	
ZILOG	Z86E0408SEC	SOIC 18	PA28SO28D-EO-300
ZILOG	Z86E0408SSC1866	SOIC 18	PA28SO28D-EO-300
ZILOG	Z86E0408SSC1903	SOIC 18	PA28SO28D-EO-300
ZILOG	Z86E0408SEC1903	SOIC 18	PA28SO28D-EO-300
ZILOG	Z86E0412PEC	DIP 18	
ZILOG	Z86E0412PSC1866	DIP 18	
ZILOG	Z86E0412PSC1903	DIP 18	
ZILOG	Z86E0412PEC1903	DIP 18	
ZILOG	Z86E0412SEC	SOIC 18	PA28SO28D-EO-300
ZILOG	Z86E0412SSC1866	SOIC 18	PA28SO28D-EO-300
ZILOG	Z86E0412SSC1903	SOIC 18	PA28SO28D-EO-300
ZILOG	Z86E0412SEC1903	SOIC 18	PA28SO28D-EO-300
ZILOG	Z86E08	DIP 18	
ZILOG	Z86E08(1925)	DIP 18	
ZILOG	Z86E0808PEC	DIP 18	
ZILOG	Z86E0808PSC1866	DIP 18	
ZILOG	Z86E0808PSC1903	DIP 18	
ZILOG	Z86E0808PEC1903	DIP 18	
ZILOG	Z86E0808SEC	SOIC 18	PA28SO28D-EO-300
ZILOG	Z86E0808SSC1866	SOIC 18	PA28SO28D-EO-300
ZILOG	Z86E0808SSC1903	SOIC 18	PA28SO28D-EO-300
ZILOG	Z86E0808SEC1903	SOIC 18	PA28SO28D-EO-300
ZILOG	Z86E0812PEC	DIP 18	
ZILOG	Z86E0812PSC1866	DIP 18	
ZILOG	Z86E0812PSC1903	DIP 18	
ZILOG	Z86E0812PEC1903	DIP 18	
ZILOG	Z86E0812SEC	SOIC 18	PA28SO28D-EO-300
ZILOG	Z86E0812SSC1866	SOIC 18	PA28SO28D-EO-300
ZILOG	Z86E0812SSC1903	SOIC 18	PA28SO28D-EO-300
ZILOG	Z86E0812SEC1903	SOIC 18	PA28SO28D-EO-300
ZILOG	Z86E21	DIP 40	
ZILOG	Z86E30	DIP 28	

ZILOG	Z86E30(1873)	DIP 28	
ZILOG	Z86E31	DIP 28	
ZILOG	Z86E40	DIP 40	
ZILOG	Z86E40	PLCC 44	PA44-48U
ZILOG	Z86E40(1873)	DIP 40	
ZILOG	Z86E40(1873)	PLCC 44	PA44-48U
ZILOG	Z86E61	DIP 40	
ZILOG	Z86E61	PLCC 44	PA44-48U
ZILOG	Z86E63	DIP 40	
ZILOG	Z86E63	PLCC 44	PA44-48U
ZILOG	Z86E33	DIP 28	
ZILOG	Z86E34	DIP 28	
ZILOG	Z86E43	DIP 40	
ZILOG	Z86E44	DIP 40	
ZILOG	Z86733	DIP 28	
ZILOG	Z86743	DIP 40	
MCS-LOGIC	MLC1043D	DIP 24	
MCS-LOGIC	MLC1043D	SOIC 24	PA28SO28D-EO-300
CYPRESS	CY7C270	PLCC 44	PA44-48U
CYPRESS	CY7C276	PLCC 44	PA44-48U
CYPRESS	CY7C225	DIP 24	
CYPRESS	CY7C225	PLCC 28	PA28PL28D
CYPRESS	CY7C225A	DIP 24	
CYPRESS	CY7C225A	PLCC 28	PA28PL28D
CYPRESS	CY7C235	DIP 24	
CYPRESS	CY7C235	PLCC 28	PA28PL28D
CYPRESS	CY7C235A	DIP 24	
CYPRESS	CY7C235A	PLCC 28	PA28PL28D
CYPRESS	CY7C245	DIP 24	
CYPRESS	CY7C245	PLCC 28	PA28PL28D
CYPRESS	CY7C245A	DIP 24	
CYPRESS	CY7C245A	PLCC 28	PA28PL28D
CYPRESS	CY7C251	DIP 28	
CYPRESS	CY7C254	DIP 28	
CYPRESS	CY7C261	DIP 24	
CYPRESS	CY7C261	PLCC 28	PA28PL28D
CYPRESS	CY7C263	DIP 24	
CYPRESS	CY7C263	PLCC 28	PA28PL28D
CYPRESS	CY7C264	DIP 24	
CYPRESS	CY7C264	PLCC 28	PA28PL28D
CYPRESS	CY7C265	DIP 28	
CYPRESS	CY7C265	PLCC 28	PA28PL28D
CYPRESS	CY7C266	DIP 28	
CYPRESS	CY7C266	PLCC 32	PA32PL32D
CYPRESS	CY7C268	DIP 32	
CYPRESS	CY7C269	DIP 28	
CYPRESS	CY7C271	DIP 28	
CYPRESS	CY7C271	PLCC 32	PA32PL32D
CYPRESS	CY7C271A	DIP 28	
CYPRESS	CY7C271A	PLCC 32	PA32PL32D
CYPRESS	CY7C274	DIP 28	
CYPRESS	CY7C274	PLCC 32	PA32PL32D
CYPRESS	CY7C274A	DIP 28	
CYPRESS	CY7C274A	PLCC 32	PA32PL32D
CYPRESS	CY7C277	DIP 28	
CYPRESS	CY7C279	DIP 28	
CYPRESS	CY7C281	DIP 24	
CYPRESS	CY7C281	PLCC 28	PA28PL28D
CYPRESS	CY7C281A	DIP 24	
CYPRESS	CY7C281A	PLCC 28	PA28PL28D
CYPRESS	CY7C282	DIP 24	
CYPRESS	CY7C282	PLCC 28	PA28PL28D
CYPRESS	CY7C282A	DIP 24	
CYPRESS	CY7C282A	PLCC 28	PA28PL28D
CYPRESS	CY7C285	DIP 28	
CYPRESS	CY7C286	DIP 28	
CYPRESS	CY7C287	DIP 28	
CYPRESS	CY7C289	DIP 32	
CYPRESS	CY7C291	DIP 24	
CYPRESS	CY7C291	PLCC 28	PA28PL28D
CYPRESS	CY7C291A	DIP 24	
CYPRESS	CY7C291A	PLCC 28	PA28PL28D
CYPRESS	CY7C292	DIP 24	

CYPRESS	CY7C292	PLCC 28	PA28PL28D
CYPRESS	CY7C292A	DIP 24	
CYPRESS	CY7C292A	PLCC 28	PA28PL28D
CYPRESS	CY7C293A	DIP 24	
CYPRESS	CY7C293A	PLCC 28	PA28PL28D
WAFERSCALE INTEGRATION	57C49	DIP 24	
WAFERSCALE INTEGRATION	57C49B	DIP 24	
WAFERSCALE INTEGRATION	57C49C	DIP 24	
WAFERSCALE INTEGRATION	57C51	DIP 28	
WAFERSCALE INTEGRATION	57C51C	DIP 28	
WAFERSCALE INTEGRATION	57C51	PLCC 28	PA28PL28D
WAFERSCALE INTEGRATION	57C51C	PLCC 28	PA28PL28D
GENERIC RAM	4164(64K*1)	DIP 16	
GENERIC RAM	41256(256K*1)	DIP 16	
GENERIC RAM	41000(1M*1)	DIP 18	
GENERIC RAM	44000(4M*1)	DIP 20	
GENERIC RAM	41416(16K*4)	DIP 18	
GENERIC RAM	41464(64K*4)	DIP 18	
GENERIC RAM	414256(256K*4)	DIP 20	
GENERIC RAM	6116(5V)	DIP 24	
GENERIC RAM	6116(3.3V)	DIP 24	
GENERIC RAM	6164(5V)	DIP 28	
GENERIC RAM	6164(3.3V)	DIP 28	
GENERIC RAM	61256(5V)	DIP 28	
GENERIC RAM	61256(3.3V)	DIP 28	
GENERIC RAM	621000(5V)	DIP 32	
GENERIC RAM	621000(3.3V)	DIP 32	
GENERIC RAM	624000(5V)	DIP 32	
GENERIC RAM	624000(3.3V)	DIP 32	
HYNIX	HY27UF084G2M(Nt)	TSOP 48	PA48TS48D
SAMSUNG	K9F4G08U0A(Nt)	TSOP 48	PA48TS48D
SAMSUNG	K9F8G08U0M(Nt)	TSOP 48	PA48TS48D
INTEL	DA28F320J5	SSOP 56	PA56SS48DB/CIC-56SS-48D-B6-TI
INTEL	DA28F320J5A	SSOP 56	PA56SS48DB/CIC-56SS-48D-B6-TI
INTEL	DA28F640J5	SSOP 56	PA56SS48DB/CIC-56SS-48D-B6-TI
INTEL	DT28F160S3	SSOP 56	PA56SS48DB/CIC-56SS-48D-B6-TI
INTEL	DT28F320S3	SSOP 56	PA56SS48DB/CIC-56SS-48D-B6-TI
INTEL	E28F160S3	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	E28F160S5	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	E28F160S5	SSOP 56	PA56SS48DB/CIC-56SS-48D-B6-TI
INTEL	E28F320J3A	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	E28F640J3A	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	E28F128J3A	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	E28F640J3C	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	E28F128J3C	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	E28F320J5	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	E28F640J5	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	RD28F128J3AM	BGA 80	PA80BGA48D-A
INTEL	RD28F192SJ3AM	BGA 80	PA80BGA48D-A
INTEL	RD28F256SJ3AM	BGA 80	PA80BGA48D-A
INTEL	G28F320J5	BGA 48	CIC-56uBGA-48D-A6-YAM
INTEL	G28F640J5	BGA 48	CIC-56uBGA-48D-A6-YAM
INTEL	RC28F320J3A	EBGA 64	PA64BGA48D
INTEL	RC28F320J3A	EBGA 64	HA64BGA48D
INTEL	RC28F640J3A	EBGA 64	PA64BGA48D
INTEL	RC28F640J3A	EBGA 64	HA64BGA48D
INTEL	RC28F128J3A	EBGA 64	PA64BGA48D
INTEL	RC28F128J3A	EBGA 64	HA64BGA48D
INTEL	RC28F320J3C	EBGA 64	PA64BGA48D
INTEL	RC28F320J3C	EBGA 64	HA64BGA48D
INTEL	RC28F640J3C	EBGA 64	PA64BGA48D
INTEL	RC28F640J3C	EBGA 64	HA64BGA48D
INTEL	RC28F128J3C	EBGA 64	PA64BGA48D
INTEL	RC28F128J3C	EBGA 64	HA64BGA48D
INTEL	RC28F320J3D	EBGA 64	PA64BGA48D
INTEL	RC28F320J3D	EBGA 64	HA64BGA48D
INTEL	RC28F640J3D	EBGA 64	PA64BGA48D
INTEL	RC28F640J3D	EBGA 64	HA64BGA48D
INTEL	RC28F128J3D	EBGA 64	PA64BGA48D
INTEL	RC28F128J3D	EBGA 64	HA64BGA48D
INTEL	RC28F640K3	EBGA 64	PA64BGA48DA
INTEL	RC28F128K3	EBGA 64	PA64BGA48DA
INTEL	RC28F256K3	EBGA 64	PA64BGA48DA

INTEL	RC28F128K18	EBGA 64	HA64BG48DN
INTEL	TE28F320J3C	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	TE28F640J3C	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	TE28F128J3C	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	TE28F320J3D	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	TE28F640J3D	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	TE28F128J3D	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	JS28F320J3C	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	JS28F640J3C	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	JS28F128J3C	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	JS28F320J3D	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	JS28F640J3D	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	JS28F128J3D	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	JS28F320J3F	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	JS28F640J3F	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	JS28F128J3F	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
MACRONIX	MX26F128J3	EBGA 64	PA64BGA48D
MACRONIX	MX26F128J3	EBGA 64	HA64BGA48D
MACRONIX	MX26F640J3	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
MACRONIX	MX26F640J3	EBGA 64	PA64BGA48D
MACRONIX	MX26F640J3	EBGA 64	HA64BGA48D
MACRONIX	MX26L6419	TSOP 48	PA48TS48D
MACRONIX	MX26LV128J3	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
MICRON	MT28F320J3	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
MICRON	MT28F640J3	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
MICRON	MT28F128J3	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
ST	M58LW032A	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
ST	M58LW032A-ZA	EBGA 64	PA64BGA48D
ST	M58LW032A-ZA	EBGA 64	HA64BGA48D
ST	M58LW032C	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
ST	M58LW032C-ZA	EBGA 64	PA64BGA48D
ST	M58LW032C-ZA	EBGA 64	HA64BGA48D
ST	M58LW032D	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
ST	M58LW032D-ZA	EBGA 64	PA64BGA48D
ST	M58LW032D-ZA	EBGA 64	HA64BGA48D
ST	M30LW128D	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
ST	M30LW128D	EBGA 64	PA64BGA48D
ST	M30LW128D	EBGA 64	HA64BGA48D
SHARP	LH28F160S5	SSOP 56	PA56SS48DB/CIC-56SS-48D-B6-TI
SHARP	LH28F160S3	SSOP 56	PA56SS48DB/CIC-56SS-48D-B6-TI
SHARP	LH28F160S3	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
SHARP	LH28F320BFN-PTTL	SOP 44	PA44SO44D
SHARP	LH28F640BFN-PTTL	SOP 44	PA44SO44D
PARALLAX	SX28AC/DP	DIP 28	
KHIC	KH29LV320DB	TSOP 48	PA48TS48D1
KHIC	KH29LV320DT	TSOP 48	PA48TS48D1
KHIC	KH25L6405D	SOIC 16	PA28SO28D-EO-300
MICRON	MT28EW128ABA1HJS	TSOP 56	HA56TS48DI
MICRON	MT28EW128ABA1HPC	BGA 64	PA64BG48DR
MICRON	MT28EW256ABA1HJS	TSOP 56	HA56TS48DI
MICRON	MT28EW256ABA1HPC	BGA 64	PA64BG48DR
MICRON	MT28EW512ABA1HJS	TSOP 56	HA56TS48DI
MICRON	MT28EW512ABA1HPC	BGA 64	PA64BG48DR
MICRON	MT28EW01GABA1HJS	TSOP 56	HA56TS48DI
MICRON	MT28EW01GABA1HPC	BGA 64	PA64BG48DR
NUMONYX	JS28F256M29EWH	TSOP 56	PA56TS48DD
NUMONYX	PC28F256M29EWH	BGA 64	PA64BG48DK
NUMONYX	RC28F256M29EWH	BGA 64	PA64BG48DK
NUMONYX	JS28F256M29EWL	TSOP 56	PA56TS48DD
NUMONYX	PC28F256M29EWL	BGA 64	PA64BG48DK
NUMONYX	RC28F256M29EWL	BGA 64	PA64BG48DK
NUMONYX	JS28F512M29EWH	TSOP 56	PA56TS48DD
NUMONYX	JS28F512M29EWL	TSOP 56	PA56TS48DD
NUMONYX	RC28F256J3D	EBGA 64	PA64BGA48D
NUMONYX	RC28F256J3D	EBGA 64	HA64BGA48D
NUMONYX	RC28F256J3F	EBGA 64	HA64BGA48D
NUMONYX	RC28F128P33BF	EBGA 64	NA64BG48DO
NUMONYX	RC28F128P33TF	EBGA 64	NA64BG48DO
NUMONYX	PC28F128P33BF	EBGA 64	NA64BG48DO
NUMONYX	PC28F128P33TF	EBGA 64	NA64BG48DO
NUMONYX	PC28F256P33BF	EBGA 64	HA64BG48DM
NUMONYX	PC28F256P33BF	EBGA 64	HA64BG48DM
NUMONYX	RC28F256P33TF	EBGA 64	HA64BG48DM
NUMONYX	RC28F256P33TF	EBGA 64	HA64BG48DM

NUMONYX	PC28F256P33TF	EBGA 64	HA64BG48DM
NUMONYX	PC28F00AP33TF	BGA 64	HA64BG48DAA
NUMONYX	TE28F256P33BF	TSOP 56	HA56TS48DF
NUMONYX	JS28F256P33BF	TSOP 56	HA56TS48DF
NUMONYX	TE28F256P33TF	TSOP 56	HA56TS48DF
NUMONYX	JS28F256P33TF	TSOP 56	HA56TS48DF
NUMONYX	RC28F256P30BF	EBGA 64	PA64BGA48DI
NUMONYX	PC28F256P30BF	EBGA 64	PA64BGA48DI
NUMONYX	RC28F256P30TF	EBGA 64	PA64BGA48DI
NUMONYX	PC28F256P30TF	EBGA 64	PA64BGA48DI
NUMONYX	PC28F512P30TF	EBGA 64	PA64BG48DAB
ESMT	F25D04QA-P	SOIC 8	HA8SO48DAD
ESMT	F25D04QA-V	SOIC 8	HA8SO48DAD
ESMT	F25D04QA-H	WSON 8	HA8SON48DG
ESMT	F25D08QA-P	SOIC 8	HA8SO48DAD
ESMT	F25D08QA-PA	SOIC 8	HA8SO48DAC
ESMT	F25D08QA-V	SOIC 8	HA8SO48DAD
ESMT	F25D08QA-H	WSON 8	HA8SON48DG
ESMT	F25D64QA-PA	SOIC 8	HA8SO48DAC
ESMT	F25D64QA-VA	SOIC 8	HA8SO48DAC
ESMT	F25D64QA-H	WSON 8	HA8SON48DG
ESMT	F25L004A	SOIC 8	PA16SO16D-EO-150
ESMT	F25L004A	SOIC 8	PA20SO20D-EO-210
ESMT	F25L004A	DIP 8	
ESMT	F25L008A	SOIC 8	PA20SO20D-EO-210
ESMT	F25L008A	DIP 8	
ESMT	F25L016A	SOIC 8	PA20SO20D-EO-210
ESMT	F25L016A	DIP 8	
ESMT	F25L05PA	SOIC 8	PA8SO8D-EO-150
ESMT	F25L05PA	TSSOP 8	PA8TSS8D
ESMT	F25L01PA-P	SOIC 8	PA16SO16D-EO-150
ESMT	F25L01PA-S	TSSOP 8	PA8TSS8D
ESMT	F25L02PA-P	SOIC 8	PA16SO16D-EO-150
ESMT	F25L02PA-PA	SOIC 8	PA20SO20D-EO-210
ESMT	F25L02PA-H	WSON 8	PA8SON8D
ESMT	F25L08PA	SOIC 8	PA20SO20D-EO-210
ESMT	F25L08PA	DIP 8	
ESMT	F25L04PA-P	SOIC 8	PA16SO16D-EO-150
ESMT	F25L04PA-PA	SOIC 8	PA20SO20D-EO-210
ESMT	F25L04PA-D	DIP 8	
ESMT	F25L04PA-H	WSON 8	PA8SON8D
ESMT	F25L16PA	SOIC 8	PA20SO20D-EO-210
ESMT	F25L32PA	SOIC 8	PA20SO20D-EO-210
ESMT	F25L32PA	WSON 8	PA8SON8D
ESMT	F25L32PA	SOIC 16	PA28SO28D-EO-300
ESMT	F25L32QA	SOIC 8	PA20SO20D-EO-210
ESMT	F25L32QA	SOIC 16	PA28SO28D-EO-300
ESMT	F25L64QA-PA	SOIC 8	PA20SO20D-EO-210
ESMT	F25L64QA-H	WSON 8	PA8SON8D
ESMT	F25L64QA-PH	SOIC 16	PA28SO28D-EO-300
ESMT	F25L64QA-B	BGA 24	NA24BG48D-D
ST	M58LW064D	TSOP 56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
ST	M58LW064D-ZA	EBGA 64	PA64BGA48D
ST	M58LW064D-ZA	EBGA 64	HA64BGA48D
ST	M58LT256-B	EBGA 64	HA64BG48DP
ST	M58LT256-T	EBGA 64	HA64BG48DP
RAMTRON	FM25L256	SOIC 8	PA16SO16D-EO-150
RAMTRON	FM25L256B	SOIC 8	PA16SO16D-EO-150