



TROLLEY 7 DRAWERS COMPOSITION OF 435 TOOLS IN FOAM MODULES FOR TROLLEYS **417-435MM**

SAM Outillage


10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:59:46






PROFESSIONS AND SETS

DESCRIPTION

MODULES MOUSSE



TROLLEY 7 DRAWERS COMPOSITION OF 435 TOOLS IN FOAM MODULES FOR TROLLEYS

New tool compositions in 5, 6, and 7 complete drawers, with quality tools, combining essential tools and specific tools for industrial and automotive maintenance.

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:59:46



Available in 5, 6, 7, or 9 drawer tool chests. 3 new compositions carefully designed.

Each configuration has been designed to meet the real needs of professionals.

BECAUSE LISTENING TO YOU MEANS PROVIDING EXACTLY WHAT YOU NEED.

SPECIFIC DATA

Designation	SERVANTE 41 - 7 DRAWERS - RED - 435 TOOLS
Sales reference	417-435MM
Weight (kg)	138.3
Guarantee	O SAM TOOL guarantee.

Guarantee applied

O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

[>> Find out more](#)

Toolset



x 1

Large volume tool trolley- 41 series - new generation - 7 drawers
417H



x 1

Selection of tightening tools - foam module 3/3
CP-138PM



x 1

Screw driving bits ph + hex
E-900J10

Ref : E-900J10



x 1

Screw driving bits pz +tx
E-910J10

Ref : E-910J10



x 1

Screw driving bits fte +txr
E-920J10

Ref : E-920J10

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>



	x 1	3/8" sliding handle J-120 Ref : J-120
	x 1	1/2" site ratchet with lever reversion J-157B Ref : J-157B
	x 2	Straight 3/8" extensions J-2... Ref : J-208 - J-210
	x 1	3/8" joint J-240 Ref : J-240
	x 17	3/8" short hexagonal sockets in mm JH-... Ref : 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 20 - 21 - 22
	x 2	LONG SOCKET 6-FLAT 3/8" 28 MM JHL-... Ref : 16 - 21
	x 5	3/8" sockets for Torx® head JTX-... Ref : 10 - 11 - 12 - 14 - 16
	x 15	1/4" short hexagonal key socket (mm) R-...Douilles_1/4_MM Ref : 3,5 - 4 - 4,5 - 5 - 5,5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15
	x 1	1/4" sliding handle R-120 Ref : R-120
	x 1	Site 1/4" ratchet R-157B Ref : R-157B
	x 2	Straight 1/4" extensions R-21... Ref : R-210 - R-211
	x 1	Flexible 1/4" extension R-220 Ref : R-220
	x 1	Fitted 1/4" extension R-225 Ref : R-225
	x 1	1/4" joint R-240 Ref : R-240



x 1

1/4" bit holder socket

RD-1

Ref : RD-1



x 6

1/4" single-piece screwdriver sockets for hollow hexagonal screws

RS-...

Ref : 3 - 4 - 5 - 6 - 7 - 8



x 1

Sets of 6 screwdriver sockets 1/4" for 6-flat socket head screws on storage rack

RS-J6R

Ref : RS-J6R



x 1

Set of 8 screwdriver sockets 1/4" for Torx® imprint on storage rack

RT-J8R

Ref : RT-J8R



x 5

1/4" sockets for Torx® head

RTX-...

Ref : 4 - 5 - 6 - 7 - 8



x 1

1/2" sliding locking handle

S-120

Ref : S-120



x 1

1/2" site ratchet with lever reversion

S-157B

Ref : S-157B



x 1

Straight 1/2" extensions

S-2...

Ref : S-215



x 1

1/2" joint

S-240

Ref : S-240



x 18

1/2" short hexagonal sockets in mm

SH-...

Ref : 10 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 20 - 21 - 22 - 23 - 24 - 27 - 30 - 32



x 5

1/2" long bi-hexagonal sockets in mm

SL-...Douilles_MM

Ref : 14 - 15 - 17 - 19 - 22



x 3

1/2" sockets for Torx® head

STX-...

Ref : 18 - 20 - 24



x 1

3/3 FOAM MODULE 12 PLIERS

CP-12MM



x 1

Polished chrome-plated universal pliers with spring

204-R...G

Ref : 204-R18G



x 1

Mechanic's diagonal chrome-plated cutting pliers with spring

232-R...G

Ref : 232-R18G



x 1

Straight half-round nose pliers, polished chrome-plate

237-...G

Ref : 237-20G



x 1

Polished chrome-plated angled half-round nose pliers with spring

239-R20G



x 1

Mat chrome-plated straight nose outer circlips pliers

195-...A

Ref : 195-17A



x 1

Mat chrome-plated 90° elbowed nose outer circlips pliers

196-...A

Ref : 196-17A



x 1

Burnished finish straight nose inner circlips pliers

190-...A

Ref : 190-17A



x 1

Mat chrome-plated 90° elbowed nose inner circlips pliers

191-...A

Ref : 191-17A



x 1

High-capacity lock grip pliers

212-25



x 1

Crimping pliers

241-42



x 1

Polished chrome-plated stacked-branch multigrip pliers

209-25B



x 1

Mechanic's end nippers

229-...

Ref : 229-25



x 1

MODM 3/3 88 SCREWDRIVER+WRENCHES MA.

CP-88MM



x 1

Flexible screwdriver 6 mm

23-...

Ref : 7 mm



x 1

Ratchet telescopic screwdriver with magnetic bit holder

T-PE

	x 9	Rack of 9 male 6-flat keys with spherical head in mm 67-AR9A Ref : 1,5 - 2 - 2,5 - 3 - 4 - 5 - 6 - 8 - 10 mm
	x 9	Rack of 9 Torx® male keys 66-R9A Ref : T8 - T9 - T10 - T15 - T20 - T25 - T27 - T30 - T40
	x 9	Torx® S1 round blade screwdriver T-...X Ref : T8 - T9 - T10 - T15 - T20 - T25 - T27 - T30 - T40
	x 2	Testing screwdriver 268-... Ref : 6-24V et 100-500V
	x 3	SCREWDRIVER ELECTRICIAN INSULATED 1000V ZTC-...E Ref : N°2 - N°3 - N°4
	x 2	SCREWDRIVER PHILLIPS® INSULATED 1000V ZTC-...P Ref : N°1 - N°2
	x 1	Electrician's S1 round blade slotted head screwdriver T-...E Ref : 4x100 mm
	x 3	Mechanic's S1 round blade slotted head screwdriver T-...M Ref : 5,5x100 - 6,5x100 - 8x150 mm
	x 3	Phillips® S1 round blade screwdriver T-...P Ref : N°1 - N°2 - N°3
	x 1	Phillips® S1 round blade tom thumb screwdriver T-...P_Tom_pouce Ref : N°2
	x 1	Electrician's S1 round blade tom thumb slotted head screwdriver T-...E_Tom_pouce Ref : 6,5x35 mm
	x 30	31-piece screwdriver bit set E900-J30B
	x 1	3/3 FOAM MOD 24 STRIK TOOLS CP-24MM
	x 1	SAMSOPLUS® riveting hammer, three-material handle 310-...TM Ref : 32 mm

	x 1	Mallets with interchangeable tips 320-...D Ref : 32 mm
	x 1	Short tape measures with two-material casings UB-...N Ref : 2 m
	x 1	Slide callipers with 1/2"0 mm precision 710-P-8
	x 1	Plastic body scriber 665-11
	x 6	Short drift punches 7-C...A Ref : 1,9 - 2,9 - 3,9 - 4,9 - 5,9 - 7,9 mm
	x 1	Knife with retractable blade 378-7
	x 5	Set of 5 helix pullers 761-C-5
	x 1	Fitted flat hand file LPM-...E Ref : 250 mm
	x 1	Fitted round files LR-...-E Ref : 250 mm
	x 1	Fitted half-round files LDR-...-E Ref : 250 mm
	x 2	Constant section chisels with comfortable handle 3-...-G Ref : 175 - 200 mm
	x 1	Punch 10 mm 8N-...A Ref : 8 mm



x 1

3/3 FOAM MOD 40 WRENCHES
CP-40MM

	x 19	Extra-thin combination wrench 50N-... Ref : 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 20 - 21 - 22 - 23 - 24 mm
---	------	--

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:59:46





x 1



x 9

Set of 9 multi-nut inch / metric ratchet combination spanners

50-HCJ9

Ref : 10 - 11 - 12 - 13 - 14 - 16 - 17 - 18 - 19 mm



x 8

Set of 8 offset ring wrenches in mm

105-J8D



x 4

Torx® polygonal straight wrench

9T-...

Ref : E6xE8 - E10xE12 - E14xE18 - E20xE24 mm

MODM 3/3 78 SOCKET+SCREWDRIVER

CP-78MM



x 10

Set of sockets for rounded nuts and pins

74NJ-J10

Ref : 6 - 8 - 10 - 11 - 12 - 13 - 14 - 15 - 17 - 19 - 21 - 24 - 27 mm



x 9

1/2" short hexagonal sockets in mm

SH-...

Ref : 10 - 11 - 12 - 14 - 16 - 18 - 20 - 22 - 24 mm



x 5

Socket sets 1/2" long impact car wheel nuts

19141-95

Ref : 15 - 17 - 19 - 21 - 22 mm



x 10

1/2" long hexagonal impact sockets in mm

NS-...L

Ref : 10 - 12 - 13 - 14 - 15 - 19 - 21 - 22 - 30 - 32 mm



x 1

Shock socket extra-long slim 1/2" "

19141-...M

Ref : 36 mm



x 7

1/2" screwdriver socket - hexagonal

SC-...1/2_6_pans

Ref : H5 - H6 - H7 - H8 - H10 - H12 - H14



x 8

1/2" Torx® screwdriver socket

ST-...-...

Ref : T25 - T27 - T30 - T40 - T45 - T50 - T55 - T70



x 10

1/2" XZN® screwdriver socket

SD-...-...

Ref : L55 : M6 - M8 - M10 - M12 - M14L100 : M6 - M8 - M10 - M12 - M14



x 8

1/2" ribes screwdriver socket

SR-...

Ref : L100 : RB5 - RB6 - RB7 - RB8 - RB10 - RB12L200 : RB8 - RB9



x 1

MODM 3/3 55 OUT REV AUTOMOBILE

CP-55MM

	x 1	Pneumatic disc brake piston pushing tool FD1-PN
	x 1	Quick tips for fitting 1906.../1907... Ref : 19062
	x 1	Universal 2 pins brake piston pusher flange adapter P3110-25
	x 1	Universal 3 pins brake piston pusher flange adapter P3110-26
	x 3	Set of hexagonal flare nut ring wrenches in mm 104-H-... Ref : 10x11 - 11x13 - 12x14
	x 3	5 sides socket 1/2" 10 mm 3122-... Ref : 10 - 14 - 19 mm
	x 1	Caliper for brake disc 3510B
	x 1	8 brake lining thickness gauge FD-J8
	x 1	Wire brush 2880
	x 1	Down brake pad cleaning file 2760
	x 7	Petrol spark plug 3/8" socket with joint BDC-...-JC Ref : 8 - 9 - 10 - 12 - 14 - 16 - 21 mm
	x 4	Set of 4 clamps for flexible pipes FT-4
	x 1	Two angles self locking pliers 208-35
	x 17	3/8" engine drain socket set 628-SET

 x 1 Torx® socket t55, square drive 3/8"
3953-T55

 x 1 1/2" breakthrough XZN® drain socket
SDP-18

 x 1 3-finger car oil filter wrench
628-3

 x 1 Universel pliers slotted for oil filter
3930

 x 6 Cap sockets 3/8" for oil filters
628-...Douilles_coiffes
Ref : 24 - 27 - 30 - 32 - 36 - 38 mm

 x 1 Bell oil filter socket 106/15
3955-...-...
Ref : 3955-76-14