



30 series trolley 6 drawers + composition of 242 mechanical tools

CPP-242PM

SAM Outillage



10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>


Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:59:33





DESCRIPTION

MODULES MOUSSE



SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:59:33



30 series trolley 6 drawers + composition of 242 mechanical tools

Composition with the following 4 trays:

CP-138PM - CP-48PM - CP37PM - CP-19PM

SPECIFIC DATA

Designation	30N TROLLEY 6 DRAWERS - GREY - MECHANICAL - 242 TOOLS
Sales reference	CPP-242PM
Guarantee	O SAM TOOL guarantee.

Guarantee applied

O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

[>> Find out more](#)

Toolset



x 1

6-drawer tool trolley, grey
SERVI-630NG



x 1

Selection of tightening tools - foam module 3/3
CP-138PM



x 1

Screw driving bits ph + hex
E-900J10
Ref : E-900J10



x 1

Screw driving bits pz +tx
E-910J10
Ref : E-910J10



x 1

Screw driving bits fte +txr
E-920J10
Ref : E-920J10

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:59:33



	x 1	3/8" sliding handle J-120 Ref : J-120
	x 1	1/2" site ratchet with lever reversion J-157B Ref : J-157B
	x 2	Straight 3/8" extensions J-2... Ref : J-208 - J-210
	x 1	3/8" joint J-240 Ref : J-240
	x 17	3/8" short hexagonal sockets in mm JH-... Ref : 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 20 - 21 - 22
	x 2	LONG SOCKET 6-FLAT 3/8" 28 MM JHL-... Ref : 16 - 21
	x 5	3/8" sockets for Torx® head JTX-... Ref : 10 - 11 - 12 - 14 - 16
	x 15	1/4" short hexagonal key socket (mm) R-...Douilles 1/4_MM Ref : 3,5 - 4 - 4,5 - 5 - 5,5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15
	x 1	1/4" sliding handle R-120 Ref : R-120
	x 1	Site 1/4" ratchet R-157B Ref : R-157B
	x 2	Straight 1/4" extensions R-21... Ref : R-210 - R-211
	x 1	Flexible 1/4" extension R-220 Ref : R-220
	x 1	Fitted 1/4" extension R-225 Ref : R-225
	x 1	1/4" joint R-240 Ref : R-240



x 1

1/4" bit holder socket

RD-1

Ref : RD-1



x 6

1/4" single-piece screwdriver sockets for hollow hexagonal screws

RS-...

Ref : 3 - 4 - 5 - 6 - 7 - 8



x 1

Sets of 6 screwdriver sockets 1/4" for 6-flat socket head screws on storage rack

RS-J6R

Ref : RS-J6R



x 1

Set of 8 screwdriver sockets 1/4" for Torx® imprint on storage rack

RT-J8R

Ref : RT-J8R



x 5

1/4" sockets for Torx® head

RTX-...

Ref : 4 - 5 - 6 - 7 - 8



x 1

1/2" sliding locking handle

S-120

Ref : S-120



x 1

1/2" site ratchet with lever reversion

S-157B

Ref : S-157B



x 1

Straight 1/2" extensions

S-2...

Ref : S-215



x 1

1/2" joint

S-240

Ref : S-240



x 18

1/2" short hexagonal sockets in mm

SH-...

Ref : 10 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 20 - 21 - 22 - 23 - 24 - 27 - 30 - 32



x 5

1/2" long bi-hexagonal sockets in mm

SL-...Douilles_MM

Ref : 14 - 15 - 17 - 19 - 22



x 3

1/2" sockets for Torx® head

STX-...

Ref : 18 - 20 - 24



x 1

Selection of pliers - hammers - foam module 3/3

CP-48PM



x 1

Bodyworker's chisel

1-...

Ref : 1-B

	x 1	Polished chrome-plated universal pliers 204-...G Ref : 204-16G
	x 1	Polished burnished finish stacked-branch multigrip pliers 209-25PA Ref : 209-25PA
	x 1	Chrome-plated polished diagonal cutting pliers 232-...G Ref : 232-16G
	x 1	Riveting hammers 310-...N Ref : 310-32N
	x 1	Mallets with interchangeable tips 320-...D Ref : 320-32D
	x 1	Universal hand shears 331-16 Ref : 331-16
	x 1	Rack of 9 Resistorx® male keys 59-R9A Ref : 59-R9A
	x 1	Rack of 9 hexagonal keys 62-R9A Ref : 62-R9A
	x 1	Rack of 9 long 6-flat male keys 1/4" 63-R9A Ref : 63-R9A
	x 1	Rack of 9 male 6-flat keys with spherical head in mm 67-AR9A Ref : 67-AR9A
	x 5	Long drift punches 7-...A Ref : 7-25A - 7-35A - 7-50A - 7-70A - 7-90A
	x 1	Selection of screwing tools - foam module 3/3 CP-37PM
	x 14	Combination wrenches in mm 50A-... Ref : 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19
	x 3	Electrician's slotted screwdriver TA-...E Ref : TA-3E50 - TA-4E100 - TA-55E125

	x 2	Mechanic's slotted screwdriver TA-...M Ref : TA-65M150 - TA-8M150
	x 2	Phillips® screwdriver TA-...P Ref : TA-1P100 - TA-2P125
	x 2	Phillips® screwdriver TA-...PZ Ref : TA-1PZ100 - TA-2PZ125
	x 10	Torx® screwdriver TA-...X Ref : TA-6X50 - TA-7X50 - TA-8X50 - TA-9X75 - TA-10X75 - TA-20X100 - TA-25X100 - TA-27X100 - TA-30X125 - TA-40X125