



M18 FUEL™

M18 FFN-502C

M18 FUEL™ 34° FRAMING NAILER 2-MODE

Excellent power to consistently seat nails sub-flush to the surface in hardwoods

Ready to Fire Nail Technology eliminates ramp-up time between each nail discharge

No gas cartridges and no cleaning required, designed to deliver durability and reliability to the most demanding users with very little maintenance

Two mode selection allows for sequential fire for precision or bump fire for speed

Tool-free, quick and easy depth adjustment to assure nails are driven sub-flush

Dry-Fire lockout stops the tool being fired when there are no nails left in the magazine

Fires up to 700 nails per charge on a REDLITHIUM™ 5.0 Ah battery pack for maximum productivity

Fires standard framing nails which fits an angled magazine at 30° or 34°

Quick access and easy clearing of jams


LED work light illuminates the work surface for better placement of nails

The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability

Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



Collation angle [degrees]	30 - 34
Nail diameter [mm]	2.8 - 3.3
Nail type [mm]	50 - 90
Magazine capacity nails	51
Weight with battery pack (EPTA) (kg)	5.1 (M18 B5)
Kit included	2 x M18 B5 Battery packs, M12-18 FC Charger, Kitbox
Article Number	4933471404