


# BF-PB

三通中部螺纹接头  
Barb tee branch



| 型号MODEL    | L1 | L2   | H  | D    | S  | T    | 气管Tube |
|------------|----|------|----|------|----|------|--------|
| BF-PB4-M5  | 34 | 15   | 8  | Φ2.5 | 8  | M5   | Φ4     |
| BF-PB4-01  | 34 | 17.5 | 8  | Φ2.5 | 10 | R1/8 |        |
| BF-PB4-02  | 34 | 20   | 8  | Φ2.5 | 14 | R1/4 |        |
| BF-PB6-M5  | 38 | 15   | 10 | Φ4   | 12 | M5   | Φ6     |
| BF-PB6-01  | 38 | 18   | 10 | Φ4   | 12 | R1/8 |        |
| BF-PB6-02  | 38 | 19.5 | 10 | Φ4   | 14 | R1/4 |        |
| BF-PB6-03  | 38 | 20   | 10 | Φ4   | 17 | R3/8 |        |
| BF-PB6-04  | 38 | 22.5 | 10 | Φ4   | 21 | R1/2 | Φ8     |
| BF-PB8-01  | 48 | 21.5 | 14 | Φ5   | 12 | R1/8 |        |
| BF-PB8-02  | 48 | 23   | 14 | Φ5   | 14 | R1/4 |        |
| BF-PB8-03  | 48 | 23.5 | 14 | Φ5   | 17 | R3/8 |        |
| BF-PB8-04  | 48 | 26   | 14 | Φ5   | 21 | R1/2 | Φ10    |
| BF-PB10-01 | 56 | 23.5 | 15 | Φ6.5 | 14 | R1/8 |        |
| BF-PB10-02 | 56 | 25   | 15 | Φ6.5 | 14 | R1/4 |        |
| BF-PB10-03 | 56 | 25.5 | 15 | Φ6.5 | 17 | R3/8 |        |
| BF-PB10-04 | 56 | 28   | 15 | Φ6.5 | 21 | R1/2 | Φ12    |
| BF-PB12-01 | 60 | 25   | 17 | Φ8   | 17 | R1/8 |        |
| BF-PB12-02 | 60 | 26.5 | 17 | Φ8   | 17 | R1/4 |        |
| BF-PB12-03 | 60 | 27   | 17 | Φ8   | 19 | R3/8 |        |
| BF-PB12-04 | 60 | 29.5 | 17 | Φ8   | 21 | R1/2 | Φ14    |
| BF-PB14-02 | 66 | 29   | 19 | Φ10  | 19 | R1/4 |        |
| BF-PB14-03 | 66 | 30.5 | 19 | Φ10  | 19 | R3/8 |        |
| BF-PB14-04 | 66 | 33   | 21 | Φ10  | 21 | R1/2 |        |
| BF-PB16-03 | 70 | 32   | 21 | Φ12  | 19 | R3/8 | Φ16    |
| BF-PB16-04 | 70 | 34.5 | 21 | Φ12  | 21 | R1/2 |        |
| BF-PB16-06 | 70 | -    |    | Φ12  | -  | -    |        |