



CPP-200PM3



DESCRIPTION



Selection of 200 tools tray no 3 in foam module 3/3

DETAIL OF THE SELECTION: Tray No 3: x1 small hammer. x1 hammer, 32mm. x1 multigrip pliers. x1 cutting pliers. x1 combination pliers. x1 straight-nose pliers. x1 vice-grip. x9 long 6-flat spherical head keys. x9 short Torx® keys. x9 short Resistorx keys. x5 pin-drifts: 2.5-3.5-5-7-9 mm. x1 punch. x1 short tape measure. x1 set of thickness gauges.

COMFORT:

Hydrocarbon-resistance machined foam.

L 540mm x P 410mm x H 40mm

TIME SAVINGS:

Easy tool storage and identification.

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:50:49



Tool quick to grasp thanks to the finger hole.

SPECIFIC DATA

Designation	SET OF 200 TOOLS TRAY NO 3 IN FOAM MODULE 3/3
Sales reference	CPP-200PM3
Weight (kg)	3.800
Container	foam module
Number of tools	43
Compatibility	All ranges of trolleys
Guarantee	O SAM TOOL guarantee.

Guarantee applied

O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

[>> Find out more](#)

Toolset

	x 1	Riveting hammers 310-...N Ref : 310-32N
	x 5	Long drift punches 7-...A Ref : 7-25A 7-35A 7-50A 7-70A 7-90A
	x 1	Bodyworker's chisel 1-... Ref : 1-B
	x 1	Punch 10 mm 8N-...A Ref : 8N-3A

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:50:49



	x 1	Polished chrome-plated stacked-branch multigrip pliers 209-25B Ref : Pince Multiprise
	x 1	Mechanic's diagonal chrome-plated cutting pliers with spring 232-R...G Ref : Pince 232-R16G
	x 1	Polished chrome-plated universal pliers with spring 204-R...G Ref : Pince Universelle 204-R16G
	x 1	Polished chrome-plated half-round nose pliers with spring 237-R20G Ref : Pince à bec demi-rond droit 237-R20G
	x 1	Short measures with twin-material casings UB-... Ref : Mesure courte boîtier bi-matière
	x 1	Thickness gauges 770-... Ref : Jauge d'épaisseur 770-R
	x 1	Rack of 9 male 6-flat keys with spherical head in mm 67-AR9A
	x 1	Rack of 9 Resistorx® male keys 59-R9A Ref : Jeu de 9 clés mâles Resistorx®
	x 9	ResisTorx® elbow hexagonal keys 59-... Ref : T8 - T9 - T10 - T15 - T20 - T25 - T27 - T30 - T40
	x 1	Rack of 9 Torx® male keys 66-R9A Ref : Jeu de 9 clés mâles Torx®
	x 9	Torx® elbow hexagonal keys 66-... Ref : T8 T9 T10 T15 T20 T25 T27 T30 T40
	x 1	Mallets with interchangeable tips 320-...D Ref : 320-32D
	x 1	Spare tips for mallets 320-...d and 322 320-C-...N / 322-C...