



M12 FUEL™

M12 FJS-422X

M12 FUEL™ BODYGRIP JIGSAW

Delivering outstanding power, durability with a run time of up to 24 m in 19 mm OSB (on a 4.0 Ah battery pack)

Patented FIXTEC™ blade clamp for fast and easy blade change

6-speed settings with auto controlled start mode allows the tool to start slow and ramp up to full speed when load is detected for smooth and accurate cut starts

3500 SPM delivers smooth cuts, minimised chipping and vibration

Dust blower keeps the cut line free of wood dust

Integrated LED light for workspace illumination, can be manually switched off

Detachable soft shoe avoids marks and scratches when cutting soft materials


Supplied with 1 x blade, dust extraction adapter, dust cover, splinter guard, soft shoe

The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability

Flexible battery system: works with all MILWAUKEE® M12™ batteries



REDLITHIUM™



No load stroke rate (spm)	800 - 3,000
Max. cutting capacity wood steel aluminium [mm]	70/ 3/ 3
Bevel capacity (°)	45
Stroke length (mm)	22
Weight with battery pack (EPTA) (kg)	1.7 (M12 B2)
Kit included	1 x M12 B4, 1 x M12 B2 Battery packs, C12 C Charger, HD Box
Article number	4933500575