

Technical data sheet

Article number:
924-00423

QDF5-6P

Product Group	Quick Connect/Disconnect Piggy Back Female/Male Funnel Entry
Product Family	Double Grip Pre-Insulated Terminals
Material	Brass (BS), Polyvinylchloride (PVC)
Colour	Yellow (YE)
Application Range	Low Voltage
Conductor Size Range mm²	4.0-6.0 mm ²
Diameter (D)	7 mm
Halogen-free	No
Length (L)	26 mm
Length (L2)	14 mm
Length (L3)	12 mm
Max Current	24 A
Max Voltage	300 V
Operating Temperature	+75 °C
Package Content	25 pcs.
Package Content packed in	bag
REACH Reg. Art.33 does not contain SVHC	Yes
ROHS compliant	Yes
Width (W)	6.7 mm
Width (W2)	6.2 mm

