



FACK2Spm



FACK4bkpm



FKFbkpm



KBNC1275pm



KBNC50pm



KBNC75pm



KC3.5whpm



KCFbkpm



KCHD90pm



KCHDbkpm



KCK66pm



KCUAA290pm



KCUAA2bkpm



KCUAA311pm



KCUAA3bkpm



KCUABbkpm



KCUABpm



KGB1pm +
KGB3pm



KOCMMpm



KOCSMpm



KOLMMDXpm



KOTMMpm



KOTSmpm



KOTSmpm



KRCAwhwhpm



KSH66whpm



KSPrdpm



KUA2whpm



SACK3Spm



SACK4whpm



SEKjepm



SGACK2Spm



SGACK90pm



SGKSjepm



SGKSLJpm



SGKSsupm



SKFwhpm



SKMcbkpm




SLJwhpm



KCHD90pm

Panel Mount Adaptor (KApma)



Code	Code
FACK2Spm	Category 5e female to female coupler, shielded
FACK4bkpm	Category 5e unshielded compact coupler
FKFbkpm	Category 5e tool-less IDC socket, unshielded
KBNC1275pm	BNC coupler Ultra HD 75 ohm 12Ghz
KBNC50pm	BNC 50 ohm female to female coupler
KBNC75pm	BNC true 75 ohm female to female coupler(capable of data rates up to 3 Gb/s or higher)
KC3.5whpm	3.5mm coupler
KCFbk	F connector, female to female coupler
KCHD90pm	90° HDMI female to female coupler
KCHDbkpm	HDMI female to female coupler
KCK66pm	RJ12 6P6C female to female coupler
KCUAA290pm	90° USB2 A to A coupler
KCUAA2bkpm	USB2.0 A female to A female coupler
KCUAA311pm	USB3 female to female coupler, wired 1:1
KCUAA3bkpm	USB3 female to female coupler, cross-wired
KCUABbkpm	USB A female to B female adaptor, reversible
KCUABpm	USB A female to B female adaptor, reversible
KGB1pm	UK telephone socket - PSTN Master (Slave/Secondary version also available)
KGB3pm	UK telephone secondary socket
KOCMMpm	Fibre female to female coupler SC to SC, multi mode simplex
KOCSMpm	Fibre female to female coupler SC to SC, single mode simplex
KOLMMDXpm	Fibre female to female coupler LC to LC, multi mode duplex
KOTMMpm	Fibre female to female coupler ST to ST, multi mode simplex, black dustcover
KOTSMpm	Fibre female to female coupler ST to ST, single mode simplex, yellow dustcover
KOTSMpm	Fibre female to female coupler ST to ST, single mode simplex, yellow dustcover
KRCAwhwhpm	RCA coupler - available with black/white/yellow/red insert
KSH66whpm	RJ12 6p6c socket
KSPrdpm	Speaker module in black with red elastic identifier
KUA2whpm	USB 2 A Screw Termination Socket
SACK3Spm	Category 6 female to female coupler, shielded
SACK4whpm	Category 6 unshielded compact coupler
SEKjepm	Category 8 socket
SGACK2Spm	Category 6A female to female coupler, shielded (Cat 6 coupler, shielded also available)
SGACK90pm	Cat 6A female to female coupler, w/rear outlet 90° to front outlet, shielded (also available in UTP Cat 6 version)
SGKSjepm	Category 6A Contractor grade Shielded Socket
SGKSLJpm	LOKJAC Category 6A tool-less locking socket
SGKSsupm	Category 6A tool-less component level socket
SKFwhpm	Category 6 tool-less IDC socket, unshielded
SKMcbkpm	Category 6 IDC socket, LSA-Plus and 110 type termination, unshielded
SLJwhpm	LOKJAC Category 6 tool-less locking socket

*: Black = bk, Red = rd, White = wh, Yellow = yw

More Information:

TUK's Panel Mount Connectors Range offers a wide variety of audio, video and data connectors which can easily be mounted into panels of virtually any thickness.

Die cast adaptor KApma is robust and ensures easy mounting (into standard cut-out) and reliable earthing. Can be purchased separately in packs of 20 pcs.

Each connector is supplied as a kit. Kit includes coupler/connector, panel mount adaptor, pair of round head zinc-plated steel self-tapping screws and pair of round head zinc-plated steel M3 screws.

For USA style installations, users might prefer to use #4-40 UNC 2A machine screws. These are available separately in zinc-plated steel in bags of 100."

27th August, 2020

Rear View

FACK2Spm



FACK4bkpm



FKfbkpm



KBNC1275pm



KBNC50pm



KBNC75pm



KC3.5whpm



KCFbkpm



KCHD90pm



KCHDbkpm



KCK66pm



KCUAA290pm



KCUAA2bkpm



KCUAA311wh




KCUAA3bkpm



KCUABbkpm



KCUABpm



KGB1pm +
KGB3pm



KOCMMpm



KOCSMpm



KOLMMDXpm



KOTMMpm



KOTSMPm



KOTSMPm



KRCAwhwhpm



KSH66whpm



KSPrdpm



KUA2whpm



SACK3Spm



SACK4whpm



SEKjepm



SGACK2Spm



SGACK90pm



SGKSjepm



SGKSLJpm



SGKSupm



SKFwhpm



SKMcbkpm



SLJwhpm



KCHD90pm

Specifications:

- Kit includes coupler/connector, panel mount adaptor, pair of round head nickel-plated steel self-tapping screws and pair of round head nickel-plated steel M3 screws
- For specifications of couplers and sockets, see separate web pages as follows:

USB A female to B female coupler: <http://www.tuk.co.uk/product/usb-a-female-to-b-female-keystone-coupler/>

USB2.0 A female to A female: <http://www.tuk.co.uk/product/usb-2-0-a-female-to-a-female-keystone-coupler/>

USB2.0 A female to A female, reversible: <http://www.tuk.co.uk/product/usb-2-0-a-female-to-a-female-keystone-coupler/>

USB3 female to female coupler, cross-wired: <http://www.tuk.co.uk/product/usb3-female-to-female-keystone-coupler-cross-wired/>

USB3 female to female coupler, wired 1:1: <http://www.tuk.co.uk/product/usb3-female-to-female-keystone-coupler-wired-11/>

HDMI female to female coupler: <http://www.tuk.co.uk/product/hdmi-female-to-female-keystone-coupler/>

RJ12 female to female coupler: <http://www.tuk.co.uk/product/rj12-6p6c-keystone-coupler/>

Fibre female to female couplers: <http://www.tuk.co.uk/product/fibre-keystone-coupler/>

Cat 6 IDC UTP socket: <http://www.tuk.co.uk/product/category-6-component-level-keystone-socket/>

Cat 5e UTP and FTP female to female coupler: <http://www.tuk.co.uk/product/category-5e-shielded-keystone-panel-mount-coupler/>

Cat 6A FTP socket: <http://www.tuk.co.uk/product/shielded-keystone-jack-category-6a/>

Cat 6A FTP female to female coupler: <http://www.tuk.co.uk/product/category-6a-shielded-keystone-panel-mount-coupler/>

90° Cat 6A panel mount female to female coupler: <http://www.tuk.co.uk/product/90°-keystone-panel-mount-coupler-category-6/>

BNC 50 ohm female to female coupler: <http://www.tuk.co.uk/product/bnc-keystone-coupler-50-ohm/>

BNC true 75 ohm female to female coupler: <http://www.tuk.co.uk/product/bnc-keystone-coupler-hd-75-ohm/>

Speaker module: <http://www.tuk.co.uk/product/keystone-speaker-connector/>

Cat 5e and Cat6 tool-less UTP socket: <http://www.tuk.co.uk/product/keystone-socket-tool-less-category-6/>

Cat 6A tool-less STP socket: <http://www.tuk.co.uk/product/category-6a-shielded-keystone-jack/>

RJ12 6p6c socket: <http://www.tuk.co.uk/product/rj12-6p6c-keystone-socket/>

F connector female to female coupler: <http://www.tuk.co.uk/product/f-connector-female-to-female-keystone-coupler/>

UK telephone socket: <http://www.tuk.co.uk/product/uk-telephone-keystone-master-or-secondary-socket/>

RCA coupler: <http://www.tuk.co.uk/product/rca-keystone-coupler/>

3.5mm coupler: http://www.tuk.co.uk/tuk_live/product_details.php?category_id=1&pld=309

LOKJAC Category 6 tool-less locking keystone: <http://www.tuk.co.uk/product/lokjac-category-6-tool-less-locking-keystone/>

TUK Ltd, Unit 4, Wimbledon Stadium Business Centre, Riverside Road, London SW17 0BA

Panel Mount Adaptor for Keystones



Panel Mount Adaptor for Keystones (KAPMA#20)

These adaptors enable most keystones to be mounted easily into panels of virtually any thickness.

Features

- Die cast adaptor is robust and ensures easy mounting (into standard cut-out) and reliable earthing
- Supplied with 2 pairs of screws
 - 2 x round head nickel-plated steel self-tapping screws. T3.0x10
 - 2 x round head nickel-plated steel machine screws. (4.40 x 1/4") M3x6


Specifications

- Weight: 12g approx. each
Packs of 20: 245g approx
- Dimensions: 35.50 x 19.12 x 9.80 mm
- Colour: Silver
- Material: Nickel plated zinc alloy



Code: KAPMA#20


ROHS Compliant



Materials:
 1. Nickel plated zinc alloy
 2&3. Nickel plated steel

Code: **KAPMscr4**

ROHS Compliant



TUK Ltd, Unit 4, Wimbledon Stadium Business Centre, Riverside Road, London SW17 0BA