

KERN 317-11

KERN

Individual weight, OIML Class E2, 1 kg, Knob, stainless steel polished



Category

Brand	KERN
Product category	Individual weight
Product group	OIML E2
Product family	317

Measuring System

Test weight - nominal value	1 kg
Test weight - volume uncertainty (cm ³)	1,5625
Weight OIML class	E2
Test weight - volume (cm ³)	125
Permissible tolerance according to OIML (+/-)	1,6 mg
OIML-compliant	✓
Test weight - Density [Min] (OIML)	7810
Test weight - Density [Max] (OIML)	8210
Test weight - Density (kg/m ³)	7950
Test weight - Density uncertainty (kg/m ³)	140

Construction

Shape weight	Knob
Dimensions (Ø×H)	48×82 mm
Material	stainless steel polished
Adjustment method	Polishing

Services (optional)

Article number for DAkkS calibration	962-341
Article number for guaranteed plus-deviation	921-341

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	48×48×82 mm
Shipping method	Parcel service
Net weight approx.	1,00 kg
Gross weight approx.	1,00 kg
Shipping weight	1 kg
Shipping volume weight	0,1 kg

Optional cases

Case - Plastic article number	317-110-400
Case - Aluminium article number	317-110-600
Case - Wood article number	317-110-100

Product information

GTIN/EAN number	4045761003705
Trade number	84239090
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

