

KERN 347-14

KERN

Individual weight, OIML Class M1, 10 kg, Knob, stainless steel fine turned



Category

Brand	KERN
Product category	Individual weight
Product group	OIML M1
Product family	347

Measuring System

Test weight - nominal value	10 kg
Test weight - volume uncertainty (cm ³)	15,625
Weight OIML class	M1
Test weight - volume (cm ³)	1250
Permissible tolerance according to OIML (+/-)	500 mg
OIML-compliant	✓
Test weight - Density [Min] (OIML)	2600
Test weight - Density (kg/m ³)	7950
Test weight - Density uncertainty (kg/m ³)	140

Construction

Shape weight	Knob
Dimensions (Ø×H)	100×185 mm
Material	stainless steel fine turned
Adjustment method	Adjusting cavity - Seal

Services (optional)

Article number for DAkkS calibration	962-644
--------------------------------------	---------

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	100×100×185 mm
Shipping method	Parcel service
Net weight approx.	10 kg
Gross weight approx.	10 kg
Shipping weight	10 kg
Shipping volume weight	0,4 kg

Optional cases

Case - Plastic article number	347-140-400
Case - Aluminium article number	317-140-600
Case - Wood article number	337-140-200

Product information

GTIN/EAN number	404576 1008892
Trade number	84239090
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

