

Features

- Heavy-duty caution safety tag.
- 0.7 mm thick high-impact flexible PVC.
- Resistant to water, oil, grease, and temperature extremes.
- Bold black & yellow "CAUTION" header.
- Write-on surface for identification details.
- Reverse side for additional notes.
- Brass eyelet for secure attachment.
- Ideal for inspection, servicing, and maintenance work.

RS PRO Lockout Tags - Caution Unsafe Do Not Use - Yellow

RS Stock No.: 0802241



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- **Clear Visual Hazard Warning** - Designed to alert workers to unsafe equipment, hazardous conditions, or maintenance in progress, helping prevent accidental operation.
- **High-Visibility "CAUTION" Design** - Bold black and yellow colour scheme ensures instant recognition from a distance in industrial environments.
- **Durable 0.7 mm High-Impact PVC Construction** - Manufactured from flexible polyvinyl (PVC) sheets that are resistant to water, oil, grease, and extreme temperatures.
- **Tear-Proof & Long-Lasting** - Engineered for durability in demanding industrial conditions, ensuring extended service life.
- **Write-On Information Surface** - Front side allows entry of key details such as name, department, date, and reason for tagging.
- **Reverse-Side Note Area** - Additional space on the back for maintenance details, inspection notes, or safety instructions.
- **Brass Eyelet for Secure Attachment** - Reinforced brass eyelet enables easy fastening using string, wire, cable ties, or padlocks.
- **Compatible with Lockout Systems** - Suitable for use with lockout devices, cable lockouts, or tag holders for comprehensive LOTO procedures.

General Specifications

Type	Lockout Tags
Material	PVC
Colour	Yellow
Padlock holes	01
Package	Individual Box

Mechanical Specifications

Dimensions	143mm x 80mm
Height	143mm
Width	80mm
Thickness	0.7mm
Weight	120 Grams

Operation Environment Specifications

Withstand temperature	-20°C to 60°C
-----------------------	---------------

