



MY2Z 24VDC

Relay, plug-in, DPDT (bifurcated), 3 A, mechanical indicator, 24 VDC

Specifications

Mounting method	With plug-in socket
Usage	General purpose
Poles	2
Rated carry current	3 A
Coil voltage	24 V
Operation voltage	DC
Contact material	Ag
Contact description	DPDT
Features	Bifurcated contacts, With mechanical indicator
Terminal type	Plug-in

Fits to



PYF-08-PU

Socket, DIN rail/surface mounting, 31 mm, 8-pin, Push-in terminals



PYF-08-PU-L

Socket, DIN rail/surface mounting, 31 mm, 8-pin, Push-in terminals



PYF08S

Socket, DIN rail mounting, 8-pin, screwless terminals



PYFZ-08-E

Socket, DIN rail/surface mounting, 8-pin, screw terminals (standard)

CAD Library



Industrial Relays Brochure

EN PDF 2.77 MB



MY(S) Miniature Power Relays Datasheet

EN PDF 9.24 MB



OMRON Manufacturing Know-How: High Quality Relays

Leaflet

EN PDF 449 KB



Panel Building Brochure

EN PDF 3.11 MB



Solution case study No.8 Environment resistance Brochure

EN PDF 623 KB