

2518 : Former and Counter-Former for Eurostem® II / III


Description



Aluminium formers to optimise resistance to wear and bending loads. Fiberglass reinforced PA6 counter-formers for improved pipe sliding and better resistance to effort.

*Ø18 and 22 mm for Ministem® / Eurostem® III - 3/8 GAS and 1/2 GAS only for Eurostem® III.

** Ref. 251864 / 251865 / 251867: In a Virabox case.



References

Sku	Type	Pipe O.D.	For pipe	Bending radius mm	MINISTEM®	EUROSTEM® II / III	kg
251810	Formers and counter-former	10 mm	Copper, Electro-galvanized steel, Stainless steel	40	ok	ok	0,260
251812	Former	12mm	Copper, Electro-galvanized steel, Stainless steel	45	ok	ok	0,220

Sku	Type	Pipe O.D.	For pipe	Bending radius mm	MINISTEM®	EUROSTEM® II / III	kg
251814	Former	14mm	Copper, Multilayer, Electro-galvanized steel, Stainless steel	50	ok	ok	0,290
251815	Former	15mm	Copper, Multilayer, Electro-galvanized steel, Stainless steel	55	ok	ok	0,325
251816	Former	16mm	Copper, Multilayer, Electro-galvanized steel, Stainless steel	60	ok	ok	0,380
251818	Former	18mm	Copper, Electro-galvanized steel, Stainless steel	70	ok*	ok	0,590
251820	Formers and counter-former	20 mm	Copper, Multilayer, Electro-galvanized steel, Stainless steel	77	-	ok	0,930
251822	Former	22mm	Copper	77	ok*	ok	0,710
251825	Formers and counter-former	25 mm	Copper, Multilayer, Electro-galvanized steel, Stainless steel	98	-	ok	1,720
251826	Formers and counter-former	26 mm	Multilayer	98	-	ok	1,700
251828	Formers and counter-former	28 mm - 3/4 GAS	Copper, Multilayer, Electro-galvanized steel	98	-	ok	1,560
251829	Formers and counter-former	28 mm	Stainless steel thickness 1,2mm	112	-	ok	1,820
251831	Formers and counter-former	32 mm	Multilayer	112	-	ok	1,620
251867	Formers and counter-former**	32 mm	Copper, Multilayer	140	-	only Eurostem® III	3,270
251864	Formers and counter-former**	35 mm	Copper, Multilayer	140	-	only Eurostem® III	5,170
251865	Formers and counter-former**	40 mm	Multilayer	140	-	only Eurostem® III	4,900
251860	Formers and counter-former	3/8"	Copper refrigeration	40	-	ok	0,270
251863	Former	1/2"	Copper refrigeration	45	ok	ok	0,240
251866	Former	5/8"	Copper refrigeration	55	ok	ok	0,320
251869	Former	3/4"	Copper refrigeration	70	ok	ok	0,600

Sku	Type	Pipe O.D.	For pipe	Bending radius mm	MINISTEM®	EUROSTEM® II / III	kg
251872	Former	7/8"	Copper refrigeration	77	ok	ok	0,690
251879	Formers and counter-former	1.1/8"	Copper refrigeration	98	-	ok	1,600
251832	Counter-former	12 - 15 mm	Copper, Multilayer, Electro-galvanized steel, Stainless steel	-	-	ok	0,055
251833	Counter-former	14 - 16 mm	Copper, Multilayer, Electro-galvanized steel, Stainless steel	-	-	ok	0,065
251834	Counter-former	18 - 22 mm - 3/8 GAS - 1/2 GAS	Copper, Multilayer, Electro-galvanized steel, Stainless steel	-	-	ok*	0,085
887562	Counter-former	28 mm - 3/4 GAS	Copper, Multilayer, Electro-galvanized steel	-	-	ok	0,050
251882	Counter-former	1/2" - 5/8"	Copper refrigeration	-	-	ok	0,050
251883	Counter-former	3/4" - 7/8"	Copper refrigeration	-	-	ok	0,080

