



Hinged hook and pin wrenches for peripheral drill nuts

114-...

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:49:28





DESCRIPTION

Hinged hook and pin wrenches for peripheral drill nuts

Sliding head which allow to hold a large nut's range with the same wrench
burnish presentation

SPECIFIC DATA

SAM Outillage


10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:49:28





Sales reference	L (mm)	Weight (g)	C (mm)	e (mm)	Capacity	Guarantee
114-35	135	50	3	4	20 - 35 mm	O
114-155	290	460	6	8	95 - 155 mm	O
114-90	250	280	5.5	7	60 - 90 mm	O
114-60	175	170	4	5	35 - 60 mm	O

Guarantee applied

O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

[>> Find out more](#)

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:49:28

