



**MADE IN
GERMANY**

5 YEARS
MANUFACTURER
GUARANTEE



Product number 9202334110
EAN 4007123688456

DESCRIPTION

- Cable reel with all-round roll-over protection.
- Stable on all four sides – perfect cable routing on all four sides.
- Large, stable folding twist grip for effortless winding and unwinding of the cable.
- Robust carrying handles and plug garage on all four sides.
- Housing and drum made of a plastic-rubber compound – extremely impact-resistant and suitable for long-term use under the toughest conditions.
- Drum body resistant to cold impact down to -25 °C and drum brake.
- The RN cable is very robust, oil-resistant and particularly suitable for professional use.
- RN cable is approved for difficult construction conditions according to VDE 0100 part 704.
- 5 splash-proof 230 V protective contact sockets.
- With thermal cut-out protection against overheating.
- With visual readiness display in the socket insert.
- Category 2 equipment (K2 DGUV 203-005): For use in harsh operating conditions with high mechanical, physical and chemical impacts.

TECHNICAL DATA

Cable quality	Rubber-Neoprene
Cable length	33 m
Cable designation	H07RN-F 3G2,5
Cable colour	red
Reel diameter	320 mm
Plug system CEE socket	Without

Plug system socket	Type E (FR)
Plug system plug	Type E (FR)
Max. current carrying capacity	16 A
Nominal input voltage	230 V
Degree of protection (IP)	IP44

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1
Weight of product (without packaging)	9.81 kg
Dimension LxWxH (without packing)	22 cm x 37 cm x 37 cm

Weight of product (including packaging)	9.81 kg
Dimension LxWxH (incl. packing)	25 cm x 38.5 cm x 40 cm

SCOPE OF DELIVERY

Professional Construction site cable reel KA 3204

Hugo Brennenstuhl GmbH & Co. KG

www.brennenstuhl.com

All products are subject to technical changes.