

POES 160/12KA-SG

Wheel, with 'Blickle SoftMotion' soft rubber tyre, with nylon wheel centre, non-marking, grey, with synthetic thread guard, small

EAN 4047526384227

ID 934518

Customs tariff number 87169090



Tyre:

- high-quality elastic solid rubber "Blickle SoftMotion", hardness 55 Shore A
- maximum operational comfort
- excellent floor preservation, particularly quiet operation
- low rolling resistance
- colour grey, non-marking
- vulcanised onto the wheel centre

Wheel centre:

- high-quality nylon 6, impact resistant
- colour black

Other features:

- with synthetic thread guard, small
- high chemical resistance to many aggressive substances, except oils
- operating temperature: -20 °C to +80 °C, temporarily up to +100 °C, reduced load capacity over +35 °C

Technical data:

Wheel Ø (D)	☉	160 mm
Wheel width	⌈⌋	50 mm
Load capacity at 4 km/h	⚖	300 kg
Load capacity (static)	⚖	750 kg
Bearing type	☉	ball bearing (CC)
Axle bore Ø (d)		12 mm
Hub keyway (T1)	⌈⌋	62 mm
Temperature resistance min		-20 °C
Temperature resistance max		80 °C
Tread and tyre hardness		55 Shore A
Unit weight	⚖	1 kg
Non-marking		✓
Non-staining		✓
Antistatic	⚡	✗
ESD		✗
Electrically conductive	⚡	✗
Corrosion-resistant		✗
Heat-resistant	🔥	✗
Suitable for autoclaves		✗



Tread and tyre hardness

■ ■ ■ ■ ■ 55 Shore A

Rolling resistance

■ ■ ■ ■ ■ very good

Wear resistance

■ ■ ■ ■ ■ good

Operating noise / floor surface preservation

■ ■ ■ ■ ■ excellent

