

KERN 366-91

KERN

Individual weight, OIML Class M3, 100 g, Cylinders, cast iron lacquered



Category	
Brand	KERN
Product category	Individual weight
Product group	OIML M3
Product family	366

Measuring System	
Test weight - nominal value	100 g
Test weight - volume uncertainty (cm ³)	1,1902
Weight OIML class	M3
Conformity assessment possible	no
Test weight - volume (cm ³)	14,0845
Permissible tolerance according to OIML (+/-)	50 mg
OIML-compliant	✓
Test weight - Density [Min] (OIML)	1500
Test weight - Density (kg/m ³)	7100
Test weight - Density uncertainty (kg/m ³)	600

Construction	
Shape weight	Cylinders
Dimensions (Ø×H)	31×22 mm
Material	cast iron lacquered
Adjustment method	Adjusting cavity - Seal

Services (optional)	
Article number for DAkkS calibration	962-637

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	31×31×22 mm
Shipping method	Parcel service
Net weight approx.	0,10 kg
Gross weight approx.	0,10 kg
Shipping weight	0,1 kg
Shipping volume weight	0,1 kg

Product information

GTIN/EAN number	4045761012035
Trade number	84239090
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

