

HTH 60x35/15-35K

Rollers for pallet trucks, with Blickle Extrathane® polyurethane tread, with steel wheel centre

EAN 4047526425821

ID 425827

Customs tariff number 83022000



Tread:

- high-quality polyurethane elastomer Blickle Extrathane®, hardness 92 Shore A
- low rolling resistance
- high abrasion resistance
- high cut and tear propagation resistance
- colour yellow, non-marking, non-staining
- excellent chemical connection with the wheel centre

Wheel centre:

- metal

Other features:

- high chemical resistance to many aggressive substances
- operating temperature: -20 °C to +70 °C, temporarily up to +90 °C, reduced load capacity over +40 °C



Technical data:

Wheel Ø (D)		60 mm
Wheel width		35 mm
Load capacity at 4 km/h		220 kg
Load capacity (static)		550 kg
Bearing type		ball bearing
Ball bearing		6002 ZZ
Axle bore Ø (d)		15 mm
Clamping length (T5)		35 mm
Temperature resistance min		-20 °C
Temperature resistance max		70 °C
Tread and tyre hardness		92 Shore A
Unit weight		0.3 kg
Non-marking		✓
Non-staining		✓
Antistatic		✗
ESD		✗
Electrically conductive		✗
Corrosion-resistant		✗
Heat-resistant		✗
Tread hydrolysis-resistant		✗
Suitable for autoclaves		✗

Tread and tyre hardness

 92 Shore A

Rolling resistance

 very good


Wear resistance

 excellent

Operating noise / floor surface preservation

 good

Product references



**Corresponding castor (No ball bearing) RK-HTH
060x035/32x09-35-Z**