

M18 ONEFHIWF12-O

M18 FUEL™ ONE-KEY™ 1/2" HIGH TORQUE IMPACT WRENCH WITH FRICTION RING

The M18 FUEL™ high torque impact wrench with ONE-KEY™ technology delivers 1356 Nm of fastening torque in a compact size of 213 mm, which gives more access in tight spaces

The 4 -Mode DRIVE CONTROL allows the user to shift into four different speed and torque settings to maximise application versatility

Mode 4 bolt removal, provides a maximum nut-busting torque of 1898 Nm then shifts to 750 rpm for outstanding control when removing fasteners

The integrated blow counting sensor enhances the consistent repeatability of the chosen torque setting

ONE-KEY™ tool tracking & security offers a free of charge cloud-based tracking network and inventory management platform for your tools.

ONE-KEY™ also features a remote locking functionality. Customisation function allows for precise tool adjustment to application

The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability

1/2" friction ring reception

-



REDLITHIUM™



No load speed (rpm)	0-550/0-1400/0-1750/0-1750
Impact rate (ipm)	0-950/0-1750/0-2100/0-2100
Tool reception	1/2" square
Max. torque (Nm)	
Nut busting torque (Nm)	1898
Weight with battery pack (EPTA) (kg)	3.3 (M18 B5)
Kit included	
Article number	4933499163