


RACCORDS MÉTALLIQUES DE SÉCURITÉ - CSM 11

CSM 11 - Raccord pour flexibles

Profil : ISO 6150C



16	Débit à 6 bar 4120 (l/min)	Ø de passage (mm) 11 mm
----	--------------------------------------	-----------------------------------

Référence	Pour tuyaux Ø int.	Cote A (mm)	Cote B (mm)	Cote C (mm)
CSM 111810	10 mm	119	33	30
CSM 111813	13 mm	112	33	30
CSM 111816	16 mm	111	33	30
CSM 111819	19 mm	147	33	30