

KERN 328-33

Milligram weights, F1, 5 mg, Wire, stainless steel polished

KERN



Category

Brand	KERN
Product category	Individual weight
Product group	OIML F1
Product family	328

Measuring System

Test weight - nominal value	5 mg
Test weight - volume uncertainty (cm ³)	0,0001
Weight OIML class	F1
Test weight - volume (cm ³)	0,0006
Permissible tolerance according to OIML (+/-)	0,02 mg
OIML-compliant	✓
Test weight - Density (kg/m ³)	8000
Test weight - Density uncertainty (kg/m ³)	160

Construction

Shape weight	Wire
Dimensions weight (W×D×H)	12×12×3 mm
Material	stainless steel polished
Adjustment method	Filing

Services (optional)

Article number for DAkkS calibration	962-453
--------------------------------------	---------

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	12×12×3 mm

Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,05 kg
Shipping weight	0,1 kg
Shipping volume weight	0,1 kg

Optional cases

Case - Plastic article number	347-009-400
Case - Aluminium article number	317-009-600
Case - Wood article number	338-090-200

Product information

GTIN/EAN number	4045761478602
Trade number	84239090
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

