

KERN 327-141

KERN

Individual weight, OIML Class F1, 10 kg, Check weight, stainless steel polished



Category

Brand	KERN
Product category	Individual weight
Product group	OIML F1
Product family	327

Measuring System

Test weight - nominal value	10 kg
Test weight - volume uncertainty (cm ³)	15,625
Weight OIML class	F1
Test weight - volume (cm ³)	1250
Permissible tolerance according to OIML (+/-)	50 mg
OIML-compliant	✓
Test weight - Density [Min] (OIML)	7390
Test weight - Density [Max] (OIML)	8730
Test weight - Density (kg/m ³)	7950
Test weight - Density uncertainty (kg/m ³)	140

Construction

Shape weight	Check weight
Dimensions (Ø×H)	136×132 mm
Material	stainless steel polished
Adjustment method	Adjusting cavity - Seal

Services (optional)

Article number for DAkkS calibration	962-444
Article number for guaranteed plus-deviation	921-444

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	136×136×132 mm
Shipping method	Parcel service
Net weight approx.	10 kg
Gross weight approx.	10 kg
Shipping weight	10 kg
Shipping volume weight	0,5 kg

Optional cases

Case - Plastic article number	nicht verfügbar
Case - Aluminium article number	nicht verfügbar
Case - Wood article number	337-141-100

Product information

GTIN/EAN number	404576 1004856
Trade number	84239090
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

