


KERN YKA-49

Power adapter (EURO, AUS, UK, US, CH)

KERN



Category

Brand	KERN
Product category	Balance
Product group	Power adapter

Construction

Dimension (W×D×H)	70×70×40 mm
Material	plastic
Cable length	2 m

Power Supply

Power supply type	Power adapter
	EURO
Plug-in power supply / adapter for countries - included with the delivery	AUS UK US CH
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 1.6 A
Power socket for mains adapter	Hollow plug, inside minus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 9,5 mm

Environmental conditions

Storage temperature [Min]	-10 °C
Storage temperature [Max]	50 °C

Approval

CE mark	✓
---------	---

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	120×150×63 mm

Shipping method	Parcel service
Net weight approx.	0,25 kg
Gross weight approx.	0,25 kg
Shipping weight	0,25 kg
Shipping volume weight	0,2 kg

Product information

GTIN/EAN number	4045761314160
Trade number	85044095
REACH classification	no prohibited substances

Pictograms

STANDARD

