



M18 FJS-O

M18 FUEL™ TOP HANDLE JIGSAW

- Dust blower keeps the cut line free of wood dust
- Keyless bevel facility on the base plate allows for adjustment between 0 - 45°
- Patented FIXTEC™ blade clamp for fast and easy blade change
- 5 stage pendulum action for increased cutting performance
- Brushless POWERSTATE™ motor for fast cutting, long tool life and up to 32m in 19mm OSB (on a 5.0 Ah pack)
- Integrated LED light for workspace illumination
- Detachable soft shoe avoids marks and scratches when cutting soft materials
- The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



M18 FJS-O		No load stroke rate (spm)
0 - 3,500	Bevel capacity (°)	
45	Stroke length (mm)	
25	Kit included	
No batteries supplied, No charger supplied, No kitbox or bag supplied		Article number

