


16 NES/J 250

Power supply connectors



Power supply plug, long, straight version, with solder eyes

16 NES/J 250



Environmental conditions

Temperature range -20 °C/+70 °C

Materials

Insulating body	PC
Contact	CuZn, nickel-plated
Insulation	ABS/PVC
Housing	ABS

Mechanical data

Outer diameter	5.5 mm
Inner diameter	2.5 mm

Connectable conductors for solder area

Cable diameter 4 mm

Electrical data (at T_{amb} 20 °C)

Rated current	1 A
Rated voltage	12 V DC
Rated impulse voltage	500 V/60 s
Insulation resistance	≥ 100 MΩ

Associated products

Counterparts		
☞ 1610 05	☞ 1610 07	☞ 1613 21
☞ 1613 33	☞ 1614 10	☞ 1614 15
☞ 1614 20	☞ NEB/J 25	☞ NEB/J 25 C
☞ NEK/J 250		

16

NES/J 250

Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
NES/J 250	2	100	500

Packaging:

in bulk, in a cardboard box or a plastic bag