

KERN 317-14

KERN

Individual weight, OIML Class E2, 10 kg, Knob, stainless steel polished



Category

Brand	KERN
Product category	Individual weight
Product group	OIML E2
Product family	317

Measuring System

Test weight - nominal value	10 kg
Test weight - volume uncertainty (cm ³)	15,625
Weight OIML class	E2
Test weight - volume (cm ³)	1250
Permissible tolerance according to OIML (+/-)	16 mg
OIML-compliant	✓
Test weight - Density [Min] (OIML)	7810
Test weight - Density [Max] (OIML)	8210
Test weight - Density (kg/m ³)	7950
Test weight - Density uncertainty (kg/m ³)	140

Construction

Shape weight	Knob
Dimensions (Ø×H)	100×185 mm
Material	stainless steel polished
Adjustment method	Polishing

Services (optional)

Article number for DAkkS calibration	962-344
Article number for guaranteed plus-deviation	921-344

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	100×100×185 mm
Shipping method	Parcel service
Net weight approx.	10 kg
Gross weight approx.	10 kg
Shipping weight	10 kg
Shipping volume weight	0,4 kg

Optional cases

Case - Plastic article number	317-140-400
Case - Aluminium article number	317-140-600
Case - Wood article number	317-140-100

Product information

GTIN/EAN number	4045761003767
Trade number	84239090
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

