


20A DP Switches



Description

This uniquely shaped range is easy to install, with clear bold terminal markings and is supplied in individual protective polybags suitable for display.

This wide range includes engraved, flex outlet and neon versions.

Features

- Contemporary designed profile
- Concave rockers
- Only one size 4mm screwdriver needed
- Bold terminal markings
- Grey font engraving
- Neon versions available
- Neon leads enclosed
- Flex outlet option available
- 2 earth terminals
- Terminals have large lead-ins
- 25-year guarantee

Range

Switch	VP1390
Switch with neon	VP1391
Switch with flex outlet	VP1392
Switch with neon and flex outlet	VP1393

Technical Specification

Voltage rating	250Vac
Current Rating	20A
Contact gap	3mm
Front plate material	Urea formaldehyde

Urea flammability classification UL94 grade V-C

No user serviceable parts

Standards

- BS EN 60669-1

Back Boxes

Minimum recommended depth

	Flush 25mm	Dry lining 35mm	Surface 25mm
1g	DB162	DB2540	VP1221

Terminal Capacity

	2.5mm ²	4mm ²	6mm ²	10mm ²
L & N	4	2	2	1