



M18 FSX-801C

M18 FUEL™ SUPER SAWZALL™

The M18 FUEL™ Super SAWZALL™ delivers the power to cut at the same speed as an equivalent AC reciprocating saw - with the ability to cut 150 pieces of 290 mm x 45 mm pine on one 12.0 Ah battery charge

The HIGH OUTPUT™ system of tools elevates the M18 FUEL™ technologies to a new level and delivers extended performance and extended run time. These tools are designed to maximise the partnership with HIGH OUTPUT™ and FORGE™ batteries

Orbital action allows the saw to clear the cut of debris giving a faster cut in wood materials

3000 SPM with a 32 mm stroke length delivers fast and effortless cutting in a wide range of materials

5 variable speed settings from 1500 SPM to 3000 SPM to allow the correct speed to be set for the material being cut

FIXTEC™ blade clamp for fast and easy blade changes without any key

Durable metal rafter hang hook for work space management and safety

Adjustable shoe for optimised use of blades

Integrated LED light for workspace illumination

-



REDLITHIUM™



No load stroke rate (spm)	0 - 3,000
Stroke length (mm)	32
Weight with battery pack (EPTA) (kg)	5.06 (M18 FB8)
Kit included	1 x M18 FB8 Battery pack, M12-18 FC Charger, Kitbox
Article number	4933499177