


32695 DPZ-20-40-P-A Twin cylinder - Series: All



32695 DPZ-20-40-P-A Twin cylinder - Series: All

Pos.	Part no.	Type	Note	Qty.	Unit
A	383823	DPZ - 20-P-A Set of wearing parts	Spare parts: 3, 5, 7, 9, 10	1	PC
1	343442	DPZ- 20- P-A Grooved nut	Tightening torque 7 Nm / 5.2 lbf ft Use locking compound 8181256 CYBERBOND TM44	2	PC
2	343426	DPZ- 20- P-A End plate		1	PC
3		DPZ-20/25/32-... Buffer element	Not available separately, see position A	1	PC
4	237673	JV-21 Retaining ring		4	PC
5	386133	WIFC4-10X16,2X6,2-TPE-U Wiper seal	Lubricate with 684474 LUB-KC1 during assembly	2	PC
6	347320	ARA-10-S0079,0-BHS Piston rod	Tightening torque 8 Nm / 5.9 lbf ft	2	PC
7		B-19X1 -N-NBR70 O-ring ISO3601	Not available separately, see position A Lubricate with 684474 LUB-KC1 during assembly	4	PC
8	354370	DPZ- 20- P-A Bearing		2	PC
9		DSN- 20 Cushioning ring	Not available separately, see position A Lubricate with 684474 LUB-KC1 during assembly	4	PC
10		LEFC2-20X14X2,55-TPE-U Lip seal	Not available separately, see position A Lubricate with 684474 LUB-KC1 during assembly	4	PC
11	760705	DSNU- 20- PA ET Piston magnet		2	PC
12	209264	ISO 4017-M6X16-8.8 Hexagon head screw	Tightening torque 7 Nm / 5.2 lbf ft	1	PC
13	200601	DIN 439-B-M6-04 Hex nut		1	PC
14			Not available	1	PC
15	343434	DPZ-20 End cap		2	PC