

TROLLEYS



250 KG

Modular grid trolleys

These modular trolleys can be adapted to suit your needs. Extremely robust, they have been designed for intensive use.

- This range is available in a variety of configurations, and can be adapted in record time to the operator's needs. Choice of 1 or 2 removable backrests, 1 or 2 removable sides.
- The side panels are positioned in guides.
- 50 x 50 mm mesh screen to handle bulk loads.
- Reinforced welded steel frame for maximum durability.
- Backrest in Ø 28 mm tube for a good grip. Ergonomic pushing height: 945 mm. Useful backrest height: 530 mm, useful ½ panel height: 275 mm.
- 2 fixed + 2 swivel wheels with brakes, mounted on ball bearings, non-marking, silent. Start-up effort reduced by 50%. Complies with EN 1757.
- Delivered assembled.

Depending on model :

- Recessed melamine top, 16 mm thick, easy-care.
- Tray in galvanised sheet metal: 2 mm thick, suitable for corrosive environments, easy maintenance, reversible (side with or without 16 mm rim).



806 724 241



806 724 246



806 724 242



806 724 254




806 724 255



Reference	Tray material	Cabinet design	Tray dimensions	Dimensions excl. L x l x h	Ø Wheels	Bandage	Weight
806 724 141	Melamine wood	1 folder	835 x 500	1040 x 540 x 945	125	VSES	19,5
806 724 241			985 x 600	1190 x 640 x 945			22,5
806 724 146		1 backrest + 3 ½ panels	815 x 455	1075 x 540 x 945			25,5
806 724 246			965 x 555	1225 x 640 x 945			29
806 724 142		2 files	815 x 500	1075 x 540 x 945			26
806 724 242			965 x 600	1225 x 640 x 945			28,5
806 724 144		2 backrests + 1 side panel	815 x 480	1075 x 540 x 945			28,5
806 724 244			965 x 580	1225 x 640 x 945			32,5
806 724 145		2 backrests + 2 side panels	815 x 455	1075 x 540 x 945			32
806 724 245			965 x 555	1225 x 640 x 945			36
806 724 251	Galvanised sheet metal	1 folder	985 x 600	1190 x 640 x 945			26
806 724 256		1 backrest + 3 ½ panels	965 x 555	1225 x 640 x 945			32,5
806 724 252		2 files	965 x 600	1225 x 640 x 945			32
806 724 254		2 backrests + 1 side panel	965 x 580	1225 x 640 x 945			36
806 724 255		2 backrests + 2 side panels	965 x 555	1225 x 640 x 945			39,5

TPE: thermoplastic elastomer / All dimensions in mm

OPTIONS



Reel
882 006 152
For rolls Ø 300 mm max.



A4 portrait document holder
882 006 150



Showerhead holder
882 006 149

OTHER MODELS AVAILABLE



500 kg version
Medium wood tray



500 kg version
Medium wooden tray with
rubber mat