

Features

- Available in uncoated and polyester coated stainless steel
- Flame retardant
High tensile strength
- Self-locking design
- Suitable for both indoors and outdoors
- excellent resistance to high temperature, chemicals, weather and abrasion
- Can be tightened by hand or tool

RS PRO Cable Ties

RS Stock No.: 0843086



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

In situations where Nylon 66 cable ties are unsuitable—such as in harsh environments or areas exposed to high heat— consider using stainless steel cable ties. These innovative ties feature a self-locking roller ball design, making them quick and easy to install. The locking ball bearing effectively grips the tie strap, securing it as tension is applied.

Manufactured from 316 stainless steel, these cable ties offer exceptional resistance to:

- Abrasion
- Corrosion
- Radiation
- Weathering
- Extreme temperatures

Additionally, they possess a greater load-carrying capacity, making them ideal for a variety of general strapping applications.

General Specifications

Series	Stainless Steel 316
Type	Non-Releasable
Colour	Natural
Material	Stainless Steel 316
Finish	Natural
Application	Bundling wire together / Tightening labels to poles
Resistant To	Chemical and Ultraviolet resistance
UV Resistant	Yes

Mechanical Specifications

Length	200mm
Width	4.6mm
Tensile Strength	1200
Thickness	0.25

Approvals

Standards Met	REACH, RoHS
---------------	-------------