



M18 FUEL™

M18 FBLG3-802

M18 FUEL™ BLOWER

- Up to 14.2 m³/min of air volume at 193 km/h to clear debris
- Consistent blowing force of 12.2 N throughout the entire battery discharge
- Reaches full throttle in under 1 second
- Ambidextrous variable speed lock allowing the user to lock on to any speed for precise applications and optimum run time
- Compatible with interchangeable nozzle attachments to optimise the blowing pattern for various applications
- The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



Air speed [km per hour]	193
Air volume (m ³ per minute)	14.2
Clearing force [N]	12.2
Weight with battery pack (EPTA) 3.5 (M18 HB8) (kg)	
Kit included	2 x M18 FB8 Battery packs, M12-18 FC Charger, No kitbox or bag supplied
Article number	4933499233