


FILTRAZIONE PREVOST - GRUPPI DI TRATTAMENTO

Filtro regolatore lubrificatore con
valvola manuale - 3 moduli



Pressione max. di utilizzo

10 bar

Filtrazione (µm)

25.00

Codice	Maschiatura	Portata a 6 bar (l/min) (ΔP= 1.00 bar)		Peso netto (Kg)	Dim. A (mm)	Dim. B (mm)
ATU VB2585100	G1/8	400	0.5 / 8.5	0	80	215
ATU VB2585101	G1/4	700	0.5 / 8.5	0	97	302
ATU VB2585102	G3/8	2000	0.5 / 8.5	2.546	97	302
ATU VB2585103	G1/2	3300	0.5 / 8.5	2.546	97	302