

Han 1A y-Distributor mff 2,5mm²+1,5mm²



Image is for illustration purposes only. Please refer to product description.

Part number	61 12 203 0012 00
Specification	Han 1A y-Distributor mff 2,5mm ² +1,5mm ²
HARTING eCatalogue	https://harting.com/6112203001200

Identification

Category	Energy distributors
Element	Energy distributor
Specification	Han [®] 1A

Version

Number of contacts	3
PE contact	Yes

Technical characteristics

Rated current	16 A
Rated voltage	400 V
Rated impulse voltage	6 kV
Pollution degree	3
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IPX5 mated condition

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	RAL 9005 (jet black)
Colour (hood/housing)	Black



Pushing Performance
Since 1945

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140190610
eCl@ss	27142409 Small distribution board
ETIM	EC000214
UNSPSC 24.0	39121303