


Shaver Socket



Description

This uniquely shaped socket is designed to match the Deta Vimark Pro range and has a dual voltage output. supplied in hangable box suitable for display.

Features

- Contemporary designed profile
- Dual voltage socket
- Only one size 4mm screwdriver needed
- Discreet Neon
- Terminals have large lead-ins
- 2-year guarantee

Range

Shaver Socket Dual Voltage

VP1305

Technical Specification

Voltage rating	250Vac
Output voltage	240V ~ or 115V ~
Current Rating	20VA
Isolation	Safety isolation transformer
Plate size	146 x 86 x 8mm
Front plate material	Urea formaldehyde

Urea flammability classification UL94 grade V-C

no user serviceable parts

Not suitable for continuous use or for loads of 20VA

Back Boxes

Minimum recommended depth

Flush	dry lining
47mm	46mm
DB168	DB2543

Standards

- BS EN 61558-2-5
- BS 4573

Terminal Capacity

	1mm ²	1.5mm ²
L	4	3