

Features

- Design for quick and effortless installation on machines.
- Supports up to 4 padlocks, enabling multi-user lockout for improved safety.
- Dual-side warning labels enhance visibility and reinforce safety compliance.
- Lightweight and easy-to-use construction suitable for various industrial applications.
- Ensures secure isolation of energy sources during maintenance or repair tasks.
- Highly durable build designed for reliable long-term performance in demanding environments.

RS PRO Labelled Lockout Tagout Hasp with 4 mm Shackle for 4 Locks

RS Stock No.: 0750825



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- *Lockout hasp is engineered for simple and rapid installation on machinery requiring isolation.*
- *Designed to hold up to four padlocks, allowing multiple technicians to secure the same lockout point simultaneously.*
- *Equipped with warning labels on both sides, reminding personnel to keep the hasp attached during ongoing maintenance.*
- *Ideal for group lockout procedures, ensuring that equipment cannot be inadvertently energised.*
- *Compact, user-friendly, and rugged, making it perfect for industrial workplaces focused on safety compliance.*
- *Suitable for electrical, mechanical, and general industrial lockout/tagout applications where reliable isolation is required.*

General Specifications

Type	Lockout Hasp
Material	Stainless Steel / ABS
Colour	Red
Padlock holes	04
Package	BOPP

Mechanical Specifications

Dia (Jaw Size)	26 / 40 mm
Body - Width	50 mm
Body - Height	127 mm
Shackle Dia	4mm
Weight	50 Grams

Operation Environment Specifications

Withstand temperature	-40 °C to +150 °C
-----------------------	-------------------