


162117 DPZJ-25-10-P-A-KF-S2 Twin cylinder - Series: All



162117 DPZJ-25-10-P-A-KF-S2 Twin cylinder - Series: All

Pos.	Part no.	Type	Note	Qty.	Unit
A	383824	DPZ - 25-P-A Set of wearing parts	Spare parts: 3, 10, 13, 15	1	PC
1	343442	DPZ- 20- P-A Grooved nut	Tightening torque 10 Nm / 7.4 lbf ft Use locking compound. See position 19	4	PC
2	343427	DPZ- 25- P-A End plate		2	PC
3	660771	DPZ-20/25/32-... Buffer element		1	PC
4	209264	ISO 4017-M6X16-8.8 Hexagon head screw		2	PC
5	200601	DIN 439-B-M6-04 Hex nut		2	PC
6	201028	J-26 Retaining ring		4	PC
7		13X26X1,8-1.0330 Disc	Not available	4	PC
8	8178689	12X19X28:Q Ball bushing		4	PC
9		DPZ- 25-P-A-KF Retaining	Not available	4	PC
10	229982	B-23X1,5-N-NBR75 O-ring ISO3601	Grease using during assembly. See position 18 Not included in wearing-parts kit	4	PC
11	242834	RIFC1-12X19X4,5-NBR Rod seal	Grease using during assembly. See position 18 Not included in wearing-parts kit	4	PC
12	353145	ARA-12-S0066,7-DHS Piston rod	Tightening torque 15 Nm / 11.1 lbf ft Use locking compound. See position 19	4	PC
13	209553	DSN- 25-P Cushioning ring		4	PC
14		DPZJ- 25- 10PA-KF- Housing	Not available	1	PC
15	248171	LEFC2-25X19X4-TPE-U Lip seal	Grease using during assembly. See position 18	4	PC
16	760706	DSNU- 25- PA ET Piston magnet		1	PC
17	660771	DPZ-20/25/32-... Buffer element	Not included in wearing-parts kit	1	PC
18	684474	LUB-KC1 SILIKONFREI 20ML Lubricating grease		1	PC
19	8181256	CYBERBOND TM44 TB1ML Adhesive bonding agent		1	PC