


BNC Plug to 2x SMD Test Clips, 1m



Specification

Rated Voltage	≤30 VAC , ≤60 VDC
Length	1 m
Rated Current	3 A
Wire	50 Ohm, 75 Ohm , Ø3.9 mm
Contacts	Ground: Brass/Ni coated - Conductor: Brass Au
Insulation	PP-PA6

RND Part Nr.

RND 350-00077

